



# UniStrip G4 – Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

## UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

# UniStrip G4

## Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort


## Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

## Warnings and Safety



- For outdoor use only

## Versions





BCP381

## Dimensional drawing



UniStrip G4

Dimensional drawing



Product details


UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo




UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



Product details

159A3691 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



| General Information          |           |
|------------------------------|-----------|
| Driver included              | No        |
| Light Technical              |           |
| Color rendering index (CRI)  | 80        |
| Controls and Dimming         |           |
| Dimmable                     | No        |
| Mechanical and Housing       |           |
| Housing Color                | Dark gray |
| Mech. impact protection code | IK06      |
| Ingress protection code      | IP66      |
| Approval and Application     |           |
| CE mark                      | Yes       |

General Information

| Order Code   | Full Product Name            | Light source replaceable |
|--------------|------------------------------|--------------------------|
| 911401779982 | BCP386 12LED 27K 24V 60 L30  | -                        |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | -                        |

| Order Code   | Full Product Name            | Light source replaceable |
|--------------|------------------------------|--------------------------|
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | -                        |
| 911401780192 | BCP386 30LED 30K 24V 45 L50  | -                        |

| Order Code   | Full Product Name            | Light source replaceable |
|--------------|------------------------------|--------------------------|
| 911401780232 | BCP386 30LED 27K 24V 60 L50  | -                        |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | -                        |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | -                        |
| 911401780442 | BCP386 60LED 30K 24V 45 L100 | -                        |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | -                        |

| Order Code   | Full Product Name             | Light source replaceable |
|--------------|-------------------------------|--------------------------|
| 911401780502 | BCP386 60LED 30K 24V 60 L100  | -                        |
| 911401780522 | BCP386 60LED 40K 24V 60 L100  | -                        |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | -                        |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | -                        |
| 911401738802 | BCP381 24LED 30K 24V A2 L100  | No                       |

Light Technical

| Order Code   | Full Product Name            | Luminaire         | Light         | Correlated Color  | Luminous Flux |
|--------------|------------------------------|-------------------|---------------|-------------------|---------------|
|              |                              | light beam spread | source color  | Temperature (Nom) |               |
| 911401779982 | BCP386 12LED 27K 24V 60 L30  | -                 | Warm white    | 2700 K            | 200 lm        |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | -                 | Warm white    | 3000 K            | 195 lm        |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | -                 | Neutral white | 4000 K            | 205 lm        |
| 911401780192 | BCP386 30LED 30K 24V 45 L50  | -                 | Warm white    | 3000 K            | 490 lm        |
| 911401780232 | BCP386 30LED 27K 24V 60 L50  | -                 | Warm white    | 2700 K            | 495 lm        |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | -                 | Warm white    | 2700 K            | 485 lm        |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | -                 | Neutral white | 4000 K            | 515 lm        |
| 911401780442 | BCP386 60LED 30K 24V 45 L100 | -                 | Warm white    | 3000 K            | 975 lm        |

| Order Code   | Full Product Name             | Luminaire         | Light         | Correlated Color  | Luminous Flux |
|--------------|-------------------------------|-------------------|---------------|-------------------|---------------|
|              |                               | light beam spread | source color  | Temperature (Nom) |               |
| 911401780482 | BCP386 60LED 27K 24V 60 L100  | -                 | Warm white    | 2700 K            | 985 lm        |
| 911401780502 | BCP386 60LED 30K 24V 60 L100  | -                 | Warm white    | 3000 K            | 985 lm        |
| 911401780522 | BCP386 60LED 40K 24V 60 L100  | -                 | Neutral white | 4000 K            | 1,045 lm      |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | -                 | Warm white    | 3000 K            | 960 lm        |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | -                 | Neutral white | 4000 K            | 1,020 lm      |
| 911401738802 | BCP381 24LED 30K 24V A2 L100  | 16° x 35°         | Warm white    | 3000 K            | 1,663 lm      |

Operating and Electrical

| Order Code   | Full Product Name            | Power Consumption |
|--------------|------------------------------|-------------------|
| 911401779982 | BCP386 12LED 27K 24V 60 L30  | 3 W               |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | 3 W               |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | 3 W               |
| 911401780192 | BCP386 30LED 30K 24V 45 L50  | 7.5 W             |
| 911401780232 | BCP386 30LED 27K 24V 60 L50  | 7.5 W             |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | 7.5 W             |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | 7.5 W             |

| Order Code   | Full Product Name             | Power Consumption |
|--------------|-------------------------------|-------------------|
| 911401780442 | BCP386 60LED 30K 24V 45 L100  | 15 W              |
| 911401780482 | BCP386 60LED 27K 24V 60 L100  | 15 W              |
| 911401780502 | BCP386 60LED 30K 24V 60 L100  | 15 W              |
| 911401780522 | BCP386 60LED 40K 24V 60 L100  | 15 W              |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | 15 W              |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | 15 W              |
| 911401738802 | BCP381 24LED 30K 24V A2 L100  | 24 W              |

Mechanical and Housing

| Order Code   | Full Product Name            | Optical cover type |
|--------------|------------------------------|--------------------|
| 911401779982 | BCP386 12LED 27K 24V 60 L30  | Clear glass        |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | Clear glass        |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | Clear glass        |
| 911401780192 | BCP386 30LED 30K 24V 45 L50  | Clear glass        |

| Order Code   | Full Product Name            | Optical cover type |
|--------------|------------------------------|--------------------|
| 911401780232 | BCP386 30LED 27K 24V 60 L50  | Clear glass        |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | Clear glass        |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | Clear glass        |
| 911401780442 | BCP386 60LED 30K 24V 45 L100 | Clear glass        |

| Order Code   | Full Product Name            | Optical cover type |
|--------------|------------------------------|--------------------|
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | Clear glass        |
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | Clear glass        |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | Clear glass        |

| Order Code   | Full Product Name             | Optical cover type |
|--------------|-------------------------------|--------------------|
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | Clear glass        |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | Clear glass        |
| 911401738802 | BCP381 24LED 30K 24V A2 L100  | Clear flat         |

Approval and Application

| Order Code   | Full Product Name            | Flammability mark |
|--------------|------------------------------|-------------------|
| 911401779982 | BCP386 12LED 27K 24V 60 L30  | -                 |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | -                 |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | -                 |
| 911401780192 | BCP386 30LED 30K 24V 45 L50  | -                 |
| 911401780232 | BCP386 30LED 27K 24V 60 L50  | -                 |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | -                 |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | -                 |
| 911401780442 | BCP386 60LED 30K 24V 45 L100 | -                 |

| Order Code   | Full Product Name             | Flammability mark                           |
|--------------|-------------------------------|---------------------------------------------|
| 911401780482 | BCP386 60LED 27K 24V 60 L100  | -                                           |
| 911401780502 | BCP386 60LED 30K 24V 60 L100  | -                                           |
| 911401780522 | BCP386 60LED 40K 24V 60 L100  | -                                           |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | -                                           |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | -                                           |
| 911401738802 | BCP381 24LED 30K 24V A2 L100  | For mounting on normally flammable surfaces |

