



## UniEdge – Make Your Boundaries Stand Out

UniEdge is a surface-mounted, exterior-rated and compact-sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments.

### Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Lightweight and Tilttable Brackets.
- Through wiring for power and DMX512 Signal.

### Applications

- Bridges, Monuments, Facades
- Landscape
- Parks and squares

### Features


- Robust design and IP66 for outdoor use
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors
- For outdoor use only

**Versions**

UniEdge 4LED



**Dimensional drawing**



BCP390 4LED 27K 24V 3x90 D3

| General Information                 |                                              |
|-------------------------------------|----------------------------------------------|
| Driver included                     | No                                           |
| Light Technical                     |                                              |
| Correlated Colour Temperature (Nom) | -                                            |
| Colour rendering index (CRI)        | 80                                           |
| Operating and Electrical            |                                              |
| Power Consumption                   | 10 W                                         |
| Controls and Dimming                |                                              |
| Dimmable                            | No                                           |
| Mechanical and Housing              |                                              |
| Housing Colour                      | Dark grey                                    |
| Ingress protection code             | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code        | IK06 [1 J]                                   |
| Optical cover type                  | Tempered glass                               |

## Approval and Application

|                   |                                             |
|-------------------|---------------------------------------------|
| Flammability mark | For mounting on normally flammable surfaces |
| CE mark           | No                                          |

## Light Technical

| Order Code   | Full Product Name           | Luminous Flux | Light source colour |
|--------------|-----------------------------|---------------|---------------------|
| 911401737283 | BCP390 4LED 27K 24V 3x90 D3 | 118 lm        | Warm white          |
| 911401737303 | BCP390 4LED 30K 24V 3x90 D3 | 127 lm        | Warm white          |
| 911401737323 | BCP390 4LED 40K 24V 3x90 D3 | 144 lm        | Neutral white       |