



UniEdge – Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface-mounted, exterior-rated and compact-sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Lightweight and Tilttable Brackets.
- Through wiring for power and DMX512 Signal.

Features

- Robust design and IP66 for outdoor use
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors


Application

- Bridges, Monuments, Facades
- Landscape
- Parks and squares

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information	
Driver included	No
Light Technical	
Correlated Colour Temperature (Nom)	-
Colour rendering index (CRI)	80
Operating and Electrical	
Power Consumption	10 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Tempered glass
Housing Colour	Dark grey
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	No
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source colour	Luminous Flux
92350899	BCP390 4LED 27K 24V 3x90 D3	Warm white	118 lm
92352299	BCP390 4LED 30K 24V 3x90 D3	Warm white	127 lm
92354699	BCP390 4LED 40K 24V 3x90 D3	Neutral white	144 lm

