



UniEdge – Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface-mounted, exterior-rated and compact-sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Lightweight and Tilttable Brackets.
- Through wiring for power and DMX512 Signal.

Features

- Robust design and IP66 for outdoor use
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and squares

Warnings and Safety

- For outdoor use only

General Information

Driver included No

Light Technical

Correlated Colour Temperature (Nom) -

Colour rendering index (CRI) 80

Operating and Electrical

Power Consumption 10 W

Controls and Dimming

Dimmable No

Mechanical and Housing

Optical cover type Tempered glass

Housing Colour Dark grey

Mech. impact protection code IK06

Ingress protection code IP66

Approval and Application

CE mark No

Flammability mark For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source colour	Luminous Flux
911401737283	BCP390 4LED 27K 24V 3x90 D3	Warm white	118 lm
911401737303	BCP390 4LED 30K 24V 3x90 D3	Warm white	127 lm
911401737323	BCP390 4LED 40K 24V 3x90 D3	Neutral white	144 lm

