



UniEdge - Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Light Weight and Tilttable Brackets.
- Through Wiring for power and DMX512 Signal.

Features

- Robust design & IP66 for outdoor applications
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors


Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information	
Driver included	No
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	10 W
Mechanical and Housing	
Optical cover type	Tempered glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	No
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source color	Luminous Flux
911401737283	BCP390 4LED 27K 24V 3x90 D3	Warm white	118 lm
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Warm white	115 lm
911401737303	BCP390 4LED 30K 24V 3x90 D3	Warm white	127 lm
911401737323	BCP390 4LED 40K 24V 3x90 D3	Neutral white	144 lm

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401737283	BCP390 4LED 27K 24V 3x90 D3	No	911401737303	BCP390 4LED 30K 24V 3x90 D3	No
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Yes	911401737323	BCP390 4LED 40K 24V 3x90 D3	No

