



UniEdge - Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Light Weight and Tilttable Brackets.
- Through Wiring for power and DMX512 Signal.

Features

- Robust design & IP66 for outdoor applications
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

