



TownGuide Performer – flexible, modern designs for every application need

TownGuide Performer

The TownGuide Performer family consists of six recognizable, yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic T, T and Tzero. Each luminaire has the option of a clear (PCC), translucent (PCTR) or frosted (PCF) bowl (except Tzero, which is only available with a clear bowl). With an extensive range of lumen packages, neutral white or warm white LED lights sources, and a range of dedicated optics for lower mounting heights, it's easy to select the version that best suits the specific requirements of your project. All this combined with a long life expectancy of 100,000 operating hours. In addition, TownGuide Performer has a variety of control system options that can make this luminaire an integral part of smart energy-reduction programs. This includes LumiStep, DynaDimmer, and LineSwitch stand-alone dim control, and Coded Mains group control, right up to seamless remote connectivity with Interact lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, there's no need to open the luminaire for installation. The Signify Service tag app offers direct access to all relevant data, ensuring maintenance is easy too. We have made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, there are significant energy and maintenance cost savings compared with conventional lighting.

TownGuide Performer

Benefits

- Choice of LED light sources, light colors (2700K, 3000K, 4000K) and optics
- Significant energy and carbon savings compared to HPL mercury, SON-T and PL-L compact fluorescent lamps (up to 80% with CLO and/or dimming options)
- Minimum Total Cost of Ownership
- Long lifetime: 100,000 hours from L80 up to L98 (depending on configuration and light color)
- Easy installation: no need to open luminaire with bayonet whistle connector

Features

- Six designs that blend in with, and enhance, their surroundings
- New installations or one-to-one replacements
- Dedicated lumen packages (1,200 to 12,000 lm)
- 3 bowl finishes: clear (highest performance), frosted (smooth atmosphere), translucent (enhanced visual comfort)
- 5-year standard warranty, extended warranties or lifecycle services available
- Service tag for easy installation and maintenance.

Application


- Residential areas: residential streets, cycle paths and footpaths, roundabouts, squares, parks and playgrounds, parking areas
- City centers: side streets, squares, parks and playgrounds, cycle paths and footpaths, parking areas, roundabouts, shopping and pedestrian areas
- Area and Transportation: industrial areas, parking areas, petrol stations, airports, harbors, public transport areas
- Sports: parking areas, connecting footpaths

Versions



BDP104 TownGuide Performer T, frosted

Dimensional drawing



Product details



Product details

OPDP_BDP100i_0003-Detail
photo



OPDP_BDP100i_0007-Detail
photo



OPDP_BDP100i_0009-Detail
photo



TownGuide Performer BDP101
pedestian luminaire with clear
bowl



TownGuide Performer BDP102
pedestian luminaire with frosted
bowl



TownGuide_Performe-
BDP100_105-DPP.TIF



General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Approval and Application	
CE mark	Yes
Flammability mark	-

Order Code	Full Product Name	Lamp family code
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	LED70
910925866477	BDP105 LED60/740 DW PCC SI 62P	LED60
910925866625	BDP105 LED50/830 II DW PCC GR 62P	LED50
910925866626	BDP105 LED70/830 II DW PCC GR 62P	LED70
910925866627	BDP105 LED70/830 II DS PCC GR 62P	LED70
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	LED30
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	LED40
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	LED40
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	LED50
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	LED60
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	LED40
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	LED50
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	LED60
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	LED40

Order Code	Full Product Name	Lamp family code
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	LED50
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	LED60
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	LED40
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	LED50
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	LED60
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	LED30
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	LED40
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	LED80
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	LED70
910925866272	BDP100 LED40/830 II DW PCC GR 62P	LED40
910925866276	BDP100 LED40/740 II DW PCC GR 62P	LED40
910925866277	BDP100 LED50/740 II DW PCC GR 62P	LED50
910925866278	BDP100 LED70/740 II DW PCC GR 62P	LED70
910925866282	BDP100 LED30/740 II DS PCC GR 62P	LED30
910925866283	BDP100 LED50/740 II DS PCC GR 62P	LED50
910925866284	BDP100 LED70/740 II DS PCC GR 62P	LED70
910925866288	BDP100 LED50/830 II DW PCC GR 62P	LED50
910925866289	BDP100 LED70/830 II DW PCC GR 62P	LED70
910925866293	BDP100 LED30/830 II DS PCC GR 62P	LED30
910925866294	BDP100 LED50/830 II DS PCC GR 62P	LED50
910925866295	BDP100 LED70/830 II DS PCC GR 62P	LED70
910925866302	BDP100 LED40/740 II DS PCC GR 62P	LED40
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	LED40
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	LED50
910925866487	BDP100 LED60/740 DW PCC SI 62P	LED60
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	LED40
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	LED40
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	LED120
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	LED120
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	LED70
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	LED70
910925868057	BDP100 LED40/730 II DW PCC GR 62P	LED40
910925868060	BDP100 LED50/730 II DS PCC GR 62P	LED50
910925868063	BDP100 LED50/730 II DW PCC GR 62P	LED50
910925868066	BDP100 LED70/730 II DS PCC GR 62P	LED70
910925868067	BDP100 LED70/730 II DW PCC GR 62P	LED70
910925868095	BDP100 LED40/830 DS PCC ALU 76P	LED40
910925868114	BDP100 LED70/730 II DS PCC GR 62P	LED70
910925868115	BDP100 LED40/730 II DW PCC GR 62P	LED40
910925868116	BDP100 LED50/730 II DS PCC GR 62P	LED50
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	LED50
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	LED50
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	LED60
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	LED40
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	LED50
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	LED60
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	LED40
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	LED50
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	LED60
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	LED40
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	LED50
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	LED60

Order Code	Full Product Name	Lamp family code
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	LED20
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	LED50
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	LED100
910500991153	BDP100 LED50/740 DW PCF SI 62P	LED50
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	LED30
910925439711	BDP100 LED60/740 II DS PCF SI 62P	LED60
910925439715	BDP100 LED60/830 II DS PCF SI 62P	LED60
910925866273	BDP100 LED50/830 II DS PCF GR 62P	LED50
910925866279	BDP100 LED30/740 II DW PCF GR 62P	LED30
910925866281	BDP100 LED70/740 II DW PCF GR 62P	LED70
910925866285	BDP100 LED30/740 II DS PCF GR 62P	LED30
910925866286	BDP100 LED50/740 II DS PCF GR 62P	LED50
910925866287	BDP100 LED70/740 II DS PCF GR 62P	LED70
910925866290	BDP100 LED30/830 II DW PCF GR 62P	LED30
910925866291	BDP100 LED50/830 II DW PCF GR 62P	LED50
910925866292	BDP100 LED70/830 II DW PCF GR 62P	LED70
910925866296	BDP100 LED30/830 II DS PCF GR 62P	LED30
910925866297	BDP100 LED70/830 II DS PCF GR 62P	LED70
910925866298	BDP100 LED20/830 DS PCF GR 62P	LED20
910925866299	BDP100 LED30/830 DS PCF GR 62P	LED30
910925866301	BDP100 LED40/830 DS PCF GR 62P	LED40
910925866486	BDP100 LED60/740 DW PCF SI 62P	LED60
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	LED70
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	LED60
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	LED30
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	LED35
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	LED100
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	LED20
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	LED35
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	LED60
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	LED60
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	LED60
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	LED40
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	LED40
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	LED40
910925866275	BDP101 LED50/830 II DS PCF GR 62P	LED50
910925866484	BDP101 LED60/740 DW PCF SI 62P	LED60
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	LED60
910925866274	BDP101 LED40/830 II DW PCC GR 62P	LED40
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	LED40
910925866485	BDP101 LED60/740 DW PCC SI 62P	LED60
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	LED40
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	LED40
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	LED50
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	LED60
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	LED40
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	LED50
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	LED60
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	LED40
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	LED50
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	LED60
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	LED40

Order Code	Full Product Name	Lamp family code
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	LED50
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	LED60
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	LED50
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	LED50
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	LED50
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	LED50
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	LED70
910925866483	BDP102 LED60/740 DW PCC SI 62P	LED60
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	LED50
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	LED50
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	LED50
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	LED50
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	LED35
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	LED50
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	LED40
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	LED50
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	LED60
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	LED40
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	LED50
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	LED60
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	LED40
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	LED50
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	LED60
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	LED40
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	LED50
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	LED60
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	LED20
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	LED30
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	LED35
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	LED50
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	LED70
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	LED20
910500991221	BDP102 LED20/830 II DW PCF SI 62P	LED20
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	LED35
910500991223	BDP102 LED35/830 II DW PCF SI 62P	LED35
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	LED60
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	LED40
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	LED40
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	LED40
910925439714	BDP102 LED60/740 II DS PCF SI 62P	LED60
910925866482	BDP102 LED60/740 DW PCF SI 62P	LED60
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	LED25
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	LED20
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	LED35
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	LED50
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	LED120
910925866480	BDP103 LED60/740 DW PCF SI 62P	LED60
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	LED70
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	LED15
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	LED15
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	LED25
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	LED25

Order Code	Full Product Name	Lamp family code
910925866481	BDP103 LED60/740 DW PCC SI 62P	LED60
910925866624	BDP103 LED70/830 II DW PCC GR 62P	LED70
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	LED30
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	LED50
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	LED60
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	LED70
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	LED30
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	LED70
910925866479	BDP104 LED60/740 DW PCC SI 62P	LED60
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	LED40
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	LED40
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	LED50
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	LED100
910925866478	BDP104 LED60/740 DW PCF SI 62P	LED60

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	75°	740 neutral white	4000 K	70
910925866477	BDP105 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910925866625	BDP105 LED50/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866626	BDP105 LED70/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866627	BDP105 LED70/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	32° x 29°	740 neutral white	4000 K	70
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	53° x 71°	830 warm white	3000 K	80
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	53° x 71°	740 neutral white	4000 K	70
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	75°	740 neutral white	4000 K	70
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	75°	740 neutral white	4000 K	70
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	75°	740 neutral white	4000 K	70
910925866272	BDP100 LED40/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866276	BDP100 LED40/740 II DW PCC GR 62P	50° x 70°	740 neutral white	4000 K	70
910925866277	BDP100 LED50/740 II DW PCC GR 62P	50° x 70°	740 neutral white	4000 K	70
910925866278	BDP100 LED70/740 II DW PCC GR 62P	50° x 70°	740 neutral white	4000 K	70
910925866282	BDP100 LED30/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
910925866283	BDP100 LED50/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
910925866284	BDP100 LED70/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
910925866288	BDP100 LED50/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866289	BDP100 LED70/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866293	BDP100 LED30/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80
910925866294	BDP100 LED50/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866295	BDP100 LED70/830 II DS PCC GR 62P	75°	830 warm white	3000 K	80
910925866302	BDP100 LED40/740 II DS PCC GR 62P	75°	740 neutral white	4000 K	70
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	50° x 70°	740 neutral white	4000 K	70
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	75°	830 warm white	3000 K	80
910925866487	BDP100 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	75°	830 warm white	3000 K	80
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	75°	740 neutral white	4000 K	70
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	39° x 96°	740 neutral white	4000 K	70
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	39° x 96°	740 neutral white	4000 K	70
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	39° x 96°	740 neutral white	4000 K	70
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	39° x 96°	740 neutral white	4000 K	70
910925868057	BDP100 LED40/730 II DW PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868060	BDP100 LED50/730 II DS PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868063	BDP100 LED50/730 II DW PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868066	BDP100 LED70/730 II DS PCC GR 62P	50° x 70°	730 warm white	3000 K	70

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868067	BDP100 LED70/730 II DW PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868095	BDP100 LED40/830 DS PCC ALU 76P	75°	830 warm white	3000 K	80
910925868114	BDP100 LED70/730 II DS PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868115	BDP100 LED40/730 II DW PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910925868116	BDP100 LED50/730 II DS PCC GR 62P	50° x 70°	730 warm white	3000 K	70
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	75°	830 warm white	3000 K	80
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	75°	840 neutral white	4000 K	70
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991153	BDP100 LED50/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	75°	740 neutral white	4000 K	70
910925439711	BDP100 LED60/740 II DS PCF SI 62P	75°	740 neutral white	4000 K	70
910925439715	BDP100 LED60/830 II DS PCF SI 62P	75°	830 warm white	3000 K	80
910925866273	BDP100 LED50/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866279	BDP100 LED30/740 II DW PCF GR 62P	50° x 70°	740 neutral white	4000 K	70
910925866281	BDP100 LED70/740 II DW PCF GR 62P	50° x 70°	740 neutral white	4000 K	70
910925866285	BDP100 LED30/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
910925866286	BDP100 LED50/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
910925866287	BDP100 LED70/740 II DS PCF GR 62P	75°	740 neutral white	4000 K	70
910925866290	BDP100 LED30/830 II DW PCF GR 62P	50° x 70°	830 warm white	3000 K	80
910925866291	BDP100 LED50/830 II DW PCF GR 62P	50° x 70°	830 warm white	3000 K	80

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866292	BDP100 LED70/830 II DW PCF GR 62P	50° x 70°	830 warm white	3000 K	80
910925866296	BDP100 LED30/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866297	BDP100 LED70/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866298	BDP100 LED20/830 DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866299	BDP100 LED30/830 DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866301	BDP100 LED40/830 DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866486	BDP100 LED60/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70
910925866223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	53° x 71°	730 warm white	3000 K	73
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	75°	830 warm white	3000 K	80
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	53° x 71°	830 warm white	3000 K	80
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	53° x 71°	740 neutral white	4000 K	70
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	75°	830 warm white	3000 K	80
910925866275	BDP101 LED50/830 II DS PCF GR 62P	75°	830 warm white	3000 K	80
910925866484	BDP101 LED60/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	53° x 71°	830 warm white	3000 K	80
910925866274	BDP101 LED40/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	75°	740 neutral white	4000 K	70
910925866485	BDP101 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	50° x 70°	830 warm white	3000 K	80
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	75°	830 warm white	3000 K	80
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	75°	830 warm white	3000 K	80
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	53° x 71°	830 warm white	3000 K	80
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	75°	740 neutral white	4000 K	70
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	53° x 71°	740 neutral white	4000 K	70
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	39° x 96°	740 neutral white	4000 K	70
910925866483	BDP102 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	75°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	53° x 71°	830 warm white	3000 K	80
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	75°	740 neutral white	4000 K	70
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	53° x 71°	740 neutral white	4000 K	70
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	39° x 96°	730 warm white	3000 K	70
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	75°	830 warm white	3000 K	80
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	75°	740 neutral white	4000 K	70
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	50° x 70°	830 warm white	3000 K	80
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	75°	830 warm white	3000 K	80
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80
910500991221	BDP102 LED20/830 II DW PCF SI 62P	50° x 70°	830 warm white	3000 K	80
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80
910500991223	BDP102 LED35/830 II DW PCF SI 62P	50° x 70°	830 warm white	3000 K	80
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	50° x 70°	830 warm white	3000 K	80
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	53° x 71°	830 warm white	3000 K	80
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	53° x 71°	740 neutral white	4000 K	70
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	75°	740 neutral white	4000 K	70
910925439714	BDP102 LED60/740 II DS PCF SI 62P	75°	840 neutral white	4000 K	70
910925866482	BDP102 LED60/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868224	BDP102 LED25/740 DRW PCTR GR CLO- DDF2 D1	39° x 96°	740 neutral white	4000 K	74
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910925866480	BDP103 LED60/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	75°	740 neutral white	4000 K	70
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	39° x 96°	740 neutral white	4000 K	70
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	39° x 96°	740 neutral white	4000 K	70
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	39° x 96°	740 neutral white	4000 K	70
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	39° x 96°	740 neutral white	4000 K	70
910925866481	BDP103 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910925866624	BDP103 LED70/830 II DW PCC GR 62P	50° x 70°	830 warm white	3000 K	80
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	75°	740 neutral white	4000 K	70
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	75°	740 neutral white	4000 K	70
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	75°	740 neutral white	4000 K	70

TownGuide Performer

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	75°	740 neutral white	4000 K	70
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	53° x 71°	740 neutral white	4000 K	70
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	39° x 96°	740 neutral white	4000 K	70
910925866479	BDP104 LED60/740 DW PCC SI 62P	50° x 70°	740 neutral white	4000 K	70
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	75°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	50° x 70°	740 neutral white	4000 K	70
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	50° x 70°	830 warm white	3000 K	80
910925866478	BDP104 LED60/740 DW PCF SI 62P	50° x 70°	740 neutral white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	4,830 lm	8	Distribution symmetrical	0
910925866477	BDP105 LED60/740 DW PCC SI 62P	4,020 lm	-	Distribution wide	0
910925866625	BDP105 LED50/830 II DW PCC GR 62P	3,400 lm	-	Distribution wide	0
910925866626	BDP105 LED70/830 II DW PCC GR 62P	4,620 lm	-	Distribution symmetrical	0
910925866627	BDP105 LED70/830 II DS PCC GR 62P	4,830 lm	-	Distribution wide	0
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	2,291 lm	4	Distribution narrow	3
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	2,888 lm	4	Distribution medium	3
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	3,040 lm	3	Distribution wide	3
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	3,750 lm	4	Distribution wide	3
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	4,500 lm	4	Distribution wide	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	3,080 lm	3	Distribution symmetrical	3
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	3,800 lm	4	Distribution symmetrical	3
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	4,500 lm	4	Distribution symmetrical	3
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	3,040 lm	3	Distribution wide	3
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	3,700 lm	4	Distribution wide	3
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	4,500 lm	4	Distribution wide	3
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	3,080 lm	3	Distribution symmetrical	3
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	3,800 lm	4	Distribution symmetrical	3

TownGuide Performer

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	4,500 lm	4	Distribution symmetrical	3
910500991164	BDP100 LED30/740 DM PCC SI CLO- DDF1 76P	2,204 lm	4	Distribution medium	3
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	3,080 lm	-	Distribution symmetrical	3
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	7,835 lm	-	Distribution symmetrical	3
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	5,250 lm	8	Distribution symmetrical	3
910925866272	BDP100 LED40/830 II DW PCC GR 62P	3,040 lm	-	Distribution wide	3
910925866276	BDP100 LED40/740 II DW PCC GR 62P	3,040 lm	-	Distribution wide	3
910925866277	BDP100 LED50/740 II DW PCC GR 62P	3,750 lm	-	Distribution wide	3
910925866278	BDP100 LED70/740 II DW PCC GR 62P	5,250 lm	-	Distribution wide	3
910925866282	BDP100 LED30/740 II DS PCC GR 62P	2,340 lm	-	Distribution symmetrical	3
910925866283	BDP100 LED50/740 II DS PCC GR 62P	3,800 lm	-	Distribution symmetrical	3
910925866284	BDP100 LED70/740 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
910925866288	BDP100 LED50/830 II DW PCC GR 62P	3,700 lm	-	Distribution wide	3
910925866289	BDP100 LED70/830 II DW PCC GR 62P	5,250 lm	-	Distribution wide	3
910925866293	BDP100 LED30/830 II DS PCC GR 62P	2,340 lm	-	Distribution symmetrical	3
910925866294	BDP100 LED50/830 II DS PCC GR 62P	3,800 lm	-	Distribution symmetrical	3
910925866295	BDP100 LED70/830 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
910925866302	BDP100 LED40/740 II DS PCC GR 62P	3,080 lm	-	Distribution symmetrical	3
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	3,040 lm	-	Distribution wide	3
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	3,800 lm	-	Distribution symmetrical	3
910925866487	BDP100 LED60/740 DW PCC SI 62P	4,500 lm	-	Distribution wide	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	3,080 lm	-	Distribution symmetrical	3
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	3,080 lm	-	Distribution symmetrical	3
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	8,400 lm	-	Distribution residential wide	0
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	8,400 lm	-	Distribution residential wide	0
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	4,690 lm	-	Distribution residential wide	0
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	4,690 lm	-	Distribution residential wide	0
910925868057	BDP100 LED40/730 II DW PCC GR 62P	3,080 lm	-	Distribution wide	3
910925868060	BDP100 LED50/730 II DS PCC GR 62P	3,700 lm	-	Distribution symmetrical	3
910925868063	BDP100 LED50/730 II DW PCC GR 62P	3,700 lm	-	Distribution wide	3
910925868066	BDP100 LED70/730 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
910925868067	BDP100 LED70/730 II DW PCC GR 62P	5,250 lm	-	Distribution wide	3
910925868095	BDP100 LED40/830 DS PCC ALU 76P	3,080 lm	-	Distribution symmetrical	3
910925868114	BDP100 LED70/730 II DS PCC GR 62P	5,250 lm	-	Distribution symmetrical	3
910925868115	BDP100 LED40/730 II DW PCC GR 62P	3,040 lm	-	Distribution wide	3
910925868116	BDP100 LED50/730 II DS PCC GR 62P	3,700 lm	-	Distribution symmetrical	3
910500991011	BDP100 LED50/830 II DS PCF SI CLO- LS-6 6	1,862 lm	6	Distribution symmetrical	3
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	2,700 lm	4	Distribution wide	3
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	3,240 lm	4	Distribution wide	3
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	2,280 lm	3	Distribution symmetrical	3

TownGuide Performer

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	2,800 lm	4	Distribution symmetrical	3
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	3,240 lm	4	Distribution symmetrical	3
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	2,160 lm	3	Distribution wide	3
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	2,650 lm	4	Distribution wide	3
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	3,240 lm	4	Distribution wide	3
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	2,280 lm	3	Distribution symmetrical	3
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	2,800 lm	4	Distribution symmetrical	3
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	3,240 lm	4	Distribution symmetrical	3
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	1,160 lm	4	Distribution wide	3
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	2,576 lm	6	Distribution wide	3
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	4,240 lm	6	Distribution wide	3
910500991153	BDP100 LED50/740 DW PCF SI 62P	2,700 lm	6	Distribution wide	3
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	1,250 lm	4	Distribution symmetrical	3
910925439711	BDP100 LED60/740 II DS PCF SI 62P	3,240 lm	4	Distribution symmetrical	3
910925439715	BDP100 LED60/830 II DS PCF SI 62P	3,240 lm	4	Distribution symmetrical	3
910925866273	BDP100 LED50/830 II DS PCF GR 62P	2,800 lm	-	Distribution symmetrical	3
910925866279	BDP100 LED30/740 II DW PCF GR 62P	1,650 lm	-	Distribution wide	3
910925866281	BDP100 LED70/740 II DW PCF GR 62P	3,780 lm	-	Distribution wide	3
910925866285	BDP100 LED30/740 II DS PCF GR 62P	1,710 lm	-	Distribution symmetrical	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910925866286	BDP100 LED50/740 II DS PCF GR 62P	2,800 lm	-	Distribution symmetrical	3
910925866287	BDP100 LED70/740 II DS PCF GR 62P	3,780 lm	-	Distribution symmetrical	3
910925866290	BDP100 LED30/830 II DW PCF GR 62P	1,650 lm	-	Distribution wide	3
910925866291	BDP100 LED50/830 II DW PCF GR 62P	2,650 lm	-	Distribution wide	3
910925866292	BDP100 LED70/830 II DW PCF GR 62P	3,710 lm	-	Distribution wide	3
910925866296	BDP100 LED30/830 II DS PCF GR 62P	1,710 lm	-	Distribution symmetrical	3
910925866297	BDP100 LED70/830 II DS PCF GR 62P	3,780 lm	-	Distribution symmetrical	3
910925866298	BDP100 LED20/830 DS PCF GR 62P	1,160 lm	-	Distribution symmetrical	3
910925866299	BDP100 LED30/830 DS PCF GR 62P	1,710 lm	-	Distribution symmetrical	3
910925866301	BDP100 LED40/830 DS PCF GR 62P	2,280 lm	-	Distribution symmetrical	3
910925866486	BDP100 LED60/740 DW PCF SI 62P	3,240 lm	-	Distribution wide	3
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	4,620 lm	-	Distribution medium	9
910500991015	BDP101 LED60/830 II DS PCF SI CLO- DDF2 6	2,300 lm	8	Distribution symmetrical	15
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	1,798 lm	4	Distribution wide	15
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	2,013 lm	4	Distribution wide	15
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	4,560 lm	6	Distribution wide	15
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	1,200 lm	4	Distribution wide	15
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	2,065 lm	4	Distribution wide	15
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	3,420 lm	8	Distribution wide	15
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	3,420 lm	4	Distribution wide	15
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	3,540 lm	4	Distribution symmetrical	15

TownGuide Performer

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	2,320 lm	4	Distribution medium	15
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	2,320 lm	4	Distribution medium	15
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	2,440 lm	4	Distribution symmetrical	15
910925866275	BDP101 LED50/830 II DS PCF GR 62P	3,000 lm	-	Distribution symmetrical	15
910925866484	BDP101 LED60/740 DW PCF SI 62P	3,420 lm	-	Distribution wide	3
910500991014	BDP101 LED60/830 II DM PCC SI CLO- DDF2 6	4,424 lm	8	Distribution medium	3
910925866274	BDP101 LED40/830 II DW PCC GR 62P	3,200 lm	-	Distribution wide	3
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	3,320 lm	-	Distribution symmetrical	3
910925866485	BDP101 LED60/740 DW PCC SI 62P	5,965 lm	-	Distribution wide	3
910500991021	BDP102 LED40/830 II DW PCC SI CLO- DDF1 6	3,116 lm	4	Distribution wide	3
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	3,160 lm	3	Distribution wide	3
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	4,891 lm	4	Distribution wide	3
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	4,680 lm	4	Distribution wide	3
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	3,280 lm	3	Distribution symmetrical	3
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	4,891 lm	4	Distribution symmetrical	3
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	4,740 lm	4	Distribution symmetrical	3
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	3,160 lm	3	Distribution wide	3
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	3,850 lm	4	Distribution wide	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	4,680 lm	4	Distribution wide	3
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	3,280 lm	3	Distribution symmetrical	3
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	4,000 lm	4	Distribution symmetrical	3
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	4,740 lm	4	Distribution symmetrical	3
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	4,000 lm	6	Distribution symmetrical	3
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	3,900 lm	6	Distribution medium	3
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	4,891 lm	6	Distribution symmetrical	3
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	4,891 lm	4	Distribution medium	3
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	4,900 lm	8	Distribution residential wide	3
910925866483	BDP102 LED60/740 DW PCC SI 62P	4,680 lm	-	Distribution wide	3
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	4,000 lm	-	Distribution symmetrical	3
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	3,900 lm	-	Distribution medium	3
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	4,050 lm	-	Distribution symmetrical	3
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	3,950 lm	-	Distribution medium	3
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	2,380 lm	-	Distribution residential wide	3
910500991023	BDP102 LED50/830 II DS PCF SI CLO- DDF1 6	1,900 lm	4	Distribution symmetrical	10

TownGuide Performer

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	2,280 lm	3	Distribution wide	10
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	4,891 lm	4	Distribution wide	10
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	3,300 lm	4	Distribution wide	10
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	2,360 lm	3	Distribution symmetrical	10
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	4,891 lm	4	Distribution symmetrical	10
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	3,360 lm	4	Distribution symmetrical	10
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	2,280 lm	3	Distribution wide	10
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	2,800 lm	4	Distribution wide	10
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	3,300 lm	4	Distribution wide	10
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	2,360 lm	3	Distribution symmetrical	10
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	2,900 lm	4	Distribution symmetrical	10
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	3,360 lm	4	Distribution symmetrical	10
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	1,200 lm	4	Distribution wide	10
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	1,740 lm	4	Distribution wide	10
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	1,947 lm	4	Distribution wide	10
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	2,714 lm	6	Distribution wide	10
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	3,584 lm	8	Distribution wide	10
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	1,160 lm	4	Distribution wide	10

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910500991221	BDP102 LED20/830 II DW PCF SI 62P	1,160 lm	4	Distribution wide	10
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	1,995 lm	4	Distribution wide	10
910500991223	BDP102 LED35/830 II DW PCF SI 62P	1,995 lm	4	Distribution wide	10
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	3,300 lm	8	Distribution wide	10
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	2,240 lm	4	Distribution medium	10
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	2,240 lm	4	Distribution medium	10
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	2,360 lm	4	Distribution symmetrical	10
910925439714	BDP102 LED60/740 II DS PCF SI 62P	3,360 lm	4	Distribution symmetrical	10
910925866482	BDP102 LED60/740 DW PCF SI 62P	3,300 lm	-	Distribution wide	3
910925868224	BDP102 LED25/740 DRW PCTR GR CLO- DDF2 D1	1,600 lm	-	Distribution residential wide	12
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	1,060 lm	4	Distribution wide	4
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	1,716 lm	4	Distribution wide	4
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	2,346 lm	6	Distribution wide	4
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	4,800 lm	8	Distribution wide	4
910925866480	BDP103 LED60/740 DW PCF SI 62P	2,940 lm	-	Distribution wide	3
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	5,320 lm	8	Distribution symmetrical	3
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	1,110 lm	-	Distribution residential wide	3
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	1,110 lm	-	Distribution residential wide	3
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	1,625 lm	-	Distribution residential wide	3
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	1,625 lm	-	Distribution residential wide	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910925866481	BDP103 LED60/740 DW PCC SI 62P	5,965 lm	-	Distribution wide	3
910925866624	BDP103 LED70/830 II DW PCC GR 62P	5,180 lm	-	Distribution symmetrical	4
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	2,204 lm	-	Distribution symmetrical	3
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	3,800 lm	-	Distribution symmetrical	3
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	4,500 lm	-	Distribution symmetrical	3
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	5,250 lm	-	Distribution symmetrical	3
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	2,204 lm	4	Distribution medium	3

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type outdoor	Upward light output ratio
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	4,620 lm	8	Distribution residential wide	3
910925866479	BDP104 LED60/740 DW PCC SI 62P	4,380 lm	-	Distribution wide	3
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	1,386 lm	3	Distribution symmetrical	3
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	2,160 lm	3	Distribution wide	3
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	2,208 lm	6	Distribution wide	3
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	3,680 lm	6	Distribution wide	3
910925866478	BDP104 LED60/740 DW PCF SI 62P	2,760 lm	-	Distribution wide	3

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866477	BDP105 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866625	BDP105 LED50/830 II DW PCC GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866626	BDP105 LED70/830 II DW PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866627	BDP105 LED70/830 II DS PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode

TownGuide Performer

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	53 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866272	BDP100 LED40/830 II DW PCC GR 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866276	BDP100 LED40/740 II DW PCC GR 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866277	BDP100 LED50/740 II DW PCC GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866278	BDP100 LED70/740 II DW PCC GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866282	BDP100 LED30/740 II DS PCC GR 62P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866283	BDP100 LED50/740 II DS PCC GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866284	BDP100 LED70/740 II DS PCC GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866288	BDP100 LED50/830 II DW PCC GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866289	BDP100 LED70/830 II DW PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866293	BDP100 LED30/830 II DS PCC GR 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866294	BDP100 LED50/830 II DS PCC GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866295	BDP100 LED70/830 II DS PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866302	BDP100 LED40/740 II DS PCC GR 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866487	BDP100 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	79 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	79 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868057	BDP100 LED40/730 II DW PCC GR 62P	29.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868060	BDP100 LED50/730 II DS PCC GR 62P	36.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868063	BDP100 LED50/730 II DW PCC GR 62P	36.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868066	BDP100 LED70/730 II DS PCC GR 62P	49.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868067	BDP100 LED70/730 II DW PCC GR 62P	49.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

TownGuide Performer

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925868095	BDP100 LED40/830 DS PCC ALU 76P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868114	BDP100 LED70/730 II DS PCC GR 62P	49.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868115	BDP100 LED40/730 II DW PCC GR 62P	29.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868116	BDP100 LED50/730 II DS PCC GR 62P	36.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 4 kV differential mode and 4 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991153	BDP100 LED50/740 DW PCF SI 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	16.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925439711	BDP100 LED60/740 II DS PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925439715	BDP100 LED60/830 II DS PCF SI 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866273	BDP100 LED50/830 II DS PCF GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866279	BDP100 LED30/740 II DW PCF GR 62P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866281	BDP100 LED70/740 II DW PCF GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866285	BDP100 LED30/740 II DS PCF GR 62P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866286	BDP100 LED50/740 II DS PCF GR 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866287	BDP100 LED70/740 II DS PCF GR 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866290	BDP100 LED30/830 II DW PCF GR 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866291	BDP100 LED50/830 II DW PCF GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866292	BDP100 LED70/830 II DW PCF GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866296	BDP100 LED30/830 II DS PCF GR 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866297	BDP100 LED70/830 II DS PCF GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866298	BDP100 LED20/830 DS PCF GR 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866299	BDP100 LED30/830 DS PCF GR 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866301	BDP100 LED40/830 DS PCF GR 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866486	BDP100 LED60/740 DW PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	49.5 W	Surge protection level until 6 kV differential mode and 10 kV common mode
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866275	BDP101 LED50/830 II DS PCF GR 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866484	BDP101 LED60/740 DW PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	46.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866274	BDP101 LED40/830 II DW PCC GR 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866485	BDP101 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866483	BDP102 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	25 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	34 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	41 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	23.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	54 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991221	BDP102 LED20/830 II DW PCF SI 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910500991223	BDP102 LED35/830 II DW PCF SI 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	47 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	32.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925439714	BDP102 LED60/740 II DS PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866482	BDP102 LED60/740 DW PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868224	BDP102 LED25/740 DRW PCTR GR CLO- DDF2 D1	16.4 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	15.8 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	92 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866480	BDP103 LED60/740 DW PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	11 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	11 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	16.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	16.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866481	BDP103 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866624	BDP103 LED70/830 II DW PCC GR 62P	56 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	35 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	49.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	19.6 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	45.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866479	BDP104 LED60/740 DW PCC SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	27 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	27.5 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	40 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	74 W	Surge protection level until 6 kV differential mode and 6 kV common mode
910925866478	BDP104 LED60/740 DW PCF SI 62P	39 W	Surge protection level until 6 kV differential mode and 6 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	Yes	0% (digital)
910925866477	BDP105 LED60/740 DW PCC SI 62P	No	Not applicable
910925866625	BDP105 LED50/830 II DW PCC GR 62P	No	Not applicable
910925866626	BDP105 LED70/830 II DW PCC GR 62P	No	Not applicable
910925866627	BDP105 LED70/830 II DS PCC GR 62P	No	Not applicable
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Yes	50%
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Yes	50%
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	Yes	50%
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	Yes	50%
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	Yes	50%
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	Yes	50%
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	Yes	50%
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	Yes	50%
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	Yes	50%
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	Yes	50%
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	Yes	50%
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	Yes	50%
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	Yes	50%
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	Yes	50%
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Yes	50%
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	Yes	50%
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	Yes	50%
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	Yes	0% (digital)
910925866272	BDP100 LED40/830 II DW PCC GR 62P	No	Not applicable
910925866276	BDP100 LED40/740 II DW PCC GR 62P	No	Not applicable
910925866277	BDP100 LED50/740 II DW PCC GR 62P	No	Not applicable
910925866278	BDP100 LED70/740 II DW PCC GR 62P	No	Not applicable
910925866282	BDP100 LED30/740 II DS PCC GR 62P	No	Not applicable
910925866283	BDP100 LED50/740 II DS PCC GR 62P	No	Not applicable
910925866284	BDP100 LED70/740 II DS PCC GR 62P	No	Not applicable
910925866288	BDP100 LED50/830 II DW PCC GR 62P	No	Not applicable
910925866289	BDP100 LED70/830 II DW PCC GR 62P	No	Not applicable
910925866293	BDP100 LED30/830 II DS PCC GR 62P	No	Not applicable
910925866294	BDP100 LED50/830 II DS PCC GR 62P	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866295	BDP100 LED70/830 II DS PCC GR 62P	No	Not applicable
910925866302	BDP100 LED40/740 II DS PCC GR 62P	No	Not applicable
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	No	Not applicable
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	No	Not applicable
910925866487	BDP100 LED60/740 DW PCC SI 62P	No	Not applicable
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	No	Not applicable
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	No	Not applicable
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	Yes	50%
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	Yes	50%
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	Yes	50%
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	Yes	50%
910925868057	BDP100 LED40/730 II DW PCC GR 62P	No	Not applicable
910925868060	BDP100 LED50/730 II DS PCC GR 62P	No	Not applicable
910925868063	BDP100 LED50/730 II DW PCC GR 62P	No	Not applicable
910925868066	BDP100 LED70/730 II DS PCC GR 62P	No	Not applicable
910925868067	BDP100 LED70/730 II DW PCC GR 62P	No	Not applicable
910925868095	BDP100 LED40/830 DS PCC ALU 76P	No	Not applicable
910925868114	BDP100 LED70/730 II DS PCC GR 62P	No	Not applicable
910925868115	BDP100 LED40/730 II DW PCC GR 62P	No	Not applicable
910925868116	BDP100 LED50/730 II DS PCC GR 62P	No	Not applicable
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Yes	50%
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	Yes	50%
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	Yes	50%
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	Yes	50%
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	Yes	50%
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	Yes	50%
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	Yes	50%
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	Yes	50%
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	Yes	50%
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	Yes	50%
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	Yes	50%

TownGuide Performer

Order Code	Full Product Name	Dimmable	Maximum dim level
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	Yes	50%
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	No	Not applicable
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	No	Not applicable
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	No	Not applicable
910500991153	BDP100 LED50/740 DW PCF SI 62P	No	Not applicable
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	No	Not applicable
910925439711	BDP100 LED60/740 II DS PCF SI 62P	No	Not applicable
910925439715	BDP100 LED60/830 II DS PCF SI 62P	No	Not applicable
910925866273	BDP100 LED50/830 II DS PCF GR 62P	No	Not applicable
910925866279	BDP100 LED30/740 II DW PCF GR 62P	No	Not applicable
910925866281	BDP100 LED70/740 II DW PCF GR 62P	No	Not applicable
910925866285	BDP100 LED30/740 II DS PCF GR 62P	No	Not applicable
910925866286	BDP100 LED50/740 II DS PCF GR 62P	No	Not applicable
910925866287	BDP100 LED70/740 II DS PCF GR 62P	No	Not applicable
910925866290	BDP100 LED30/830 II DW PCF GR 62P	No	Not applicable
910925866291	BDP100 LED50/830 II DW PCF GR 62P	No	Not applicable
910925866292	BDP100 LED70/830 II DW PCF GR 62P	No	Not applicable
910925866296	BDP100 LED30/830 II DS PCF GR 62P	No	Not applicable
910925866297	BDP100 LED70/830 II DS PCF GR 62P	No	Not applicable
910925866298	BDP100 LED20/830 DS PCF GR 62P	No	Not applicable
910925866299	BDP100 LED30/830 DS PCF GR 62P	No	Not applicable
910925866301	BDP100 LED40/830 DS PCF GR 62P	No	Not applicable
910925866486	BDP100 LED60/740 DW PCF SI 62P	No	Not applicable
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	Yes	Not applicable
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Yes	50%
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	No	Not applicable
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	No	Not applicable
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	No	Not applicable
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	Yes	50%
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	Yes	50%
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	Yes	50%
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	Yes	50%
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	Yes	50%
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	No	Not applicable
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	No	Not applicable
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	No	Not applicable
910925866275	BDP101 LED50/830 II DS PCF GR 62P	No	Not applicable
910925866484	BDP101 LED60/740 DW PCF SI 62P	No	Not applicable
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Yes	50%
910925866274	BDP101 LED40/830 II DW PCC GR 62P	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	No	Not applicable
910925866485	BDP101 LED60/740 DW PCC SI 62P	No	Not applicable
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Yes	50%
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	Yes	50%
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	Yes	50%
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	Yes	50%
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	Yes	50%
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	Yes	50%
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	Yes	50%
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	Yes	50%
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	Yes	50%
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	Yes	50%
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	Yes	50%
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	Yes	50%
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	Yes	50%
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	No	Not applicable
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	No	Not applicable
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	No	Not applicable
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	No	Not applicable
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	Yes	0% (digital)
910925866483	BDP102 LED60/740 DW PCC SI 62P	No	Not applicable
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	No	Not applicable
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	No	Not applicable
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	No	Not applicable
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	No	Not applicable
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	No	Not applicable

TownGuide Performer

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Yes	50%
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	Yes	50%
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	Yes	50%
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	Yes	50%
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	Yes	50%
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	Yes	50%
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	Yes	50%
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	Yes	50%
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	Yes	50%
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	Yes	50%
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	Yes	50%
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	Yes	50%
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	Yes	50%
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	No	Not applicable
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	No	Not applicable
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	No	Not applicable
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	No	Not applicable
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	No	Not applicable
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	Yes	50%
910500991221	BDP102 LED20/830 II DW PCF SI 62P	No	Not applicable
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	Yes	50%
910500991223	BDP102 LED35/830 II DW PCF SI 62P	No	Not applicable
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	Yes	50%
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing
			Color
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	Polycarbonate bowl/cover clear	Gray
910925866477	BDP105 LED60/740 DW PCC SI 62P	Polycarbonate bowl/cover clear	Silver
910925866625	BDP105 LED50/830 II DW PCC GR 62P	Polycarbonate bowl/cover clear	Gray

Order Code	Full Product Name	Dimmable	Maximum dim
			level
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	No	Not applicable
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	No	Not applicable
910925439714	BDP102 LED60/740 II DS PCF SI 62P	No	Not applicable
910925866482	BDP102 LED60/740 DW PCF SI 62P	No	Not applicable
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	Yes	50%
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	No	Not applicable
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	No	Not applicable
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	No	Not applicable
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	No	Not applicable
910925866480	BDP103 LED60/740 DW PCF SI 62P	No	Not applicable
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	Yes	0% (digital)
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	No	Not applicable
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	No	Not applicable
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	No	Not applicable
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	No	Not applicable
910925866481	BDP103 LED60/740 DW PCC SI 62P	No	Not applicable
910925866624	BDP103 LED70/830 II DW PCC GR 62P	No	Not applicable
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	No	Not applicable
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	No	Not applicable
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	No	Not applicable
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	No	Not applicable
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Yes	50%
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	Yes	0% (digital)
910925866479	BDP104 LED60/740 DW PCC SI 62P	No	Not applicable
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Yes	50%
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	Yes	50%
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	No	Not applicable
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	No	Not applicable
910925866478	BDP104 LED60/740 DW PCF SI 62P	No	Not applicable

Order Code	Full Product Name	Optical cover type	Housing
			Color
910925866626	BDP105 LED70/830 II DW PCC GR 62P	Polycarbonate bowl/cover clear	Gray
910925866627	BDP105 LED70/830 II DS PCC GR 62P	Polycarbonate bowl/cover clear	Gray
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Polycarbonate bowl/cover clear	Silver

TownGuide Performer

			Housing	
Order Code	Full Product Name	Optical cover type	Color	
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Polycarbonate bowl/ cover clear	Silver	
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver	
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Polycarbonate bowl/ cover clear	Silver	
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	Polycarbonate bowl/ cover clear	Gray	
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	Polycarbonate bowl/ cover clear	Gray	
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray	
910925866272	BDP100 LED40/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866276	BDP100 LED40/740 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866277	BDP100 LED50/740 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866278	BDP100 LED70/740 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866282	BDP100 LED30/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866283	BDP100 LED50/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866284	BDP100 LED70/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866288	BDP100 LED50/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	

			Housing	
Order Code	Full Product Name	Optical cover type	Color	
910925866289	BDP100 LED70/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866293	BDP100 LED30/830 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866294	BDP100 LED50/830 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866295	BDP100 LED70/830 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866302	BDP100 LED40/740 II DS PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray	
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray	
910925866487	BDP100 LED60/740 DW PCC SI 62P	Polycarbonate bowl/ cover frosted	Silver	
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray	
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray	
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	Polycarbonate bowl/ cover clear	Gray	
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	Polycarbonate bowl/ cover clear	Gray	
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	Polycarbonate bowl/ cover clear	Gray	
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	Polycarbonate bowl/ cover clear	Gray	
910925868057	BDP100 LED40/730 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray	
910925868060	BDP100 LED50/730 II DS PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray	
910925868063	BDP100 LED50/730 II DW PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray	
910925868066	BDP100 LED70/730 II DS PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray	
910925868067	BDP100 LED70/730 II DW PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray	
910925868095	BDP100 LED40/830 DS PCC ALU 76P	Polycarbonate bowl/ cover frosted	Silver	
910925868114	BDP100 LED70/730 II DS PCC GR 62P	Polycarbonate bowl/ cover frosted	Grey	
910925868115	BDP100 LED40/730 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Grey	
910925868116	BDP100 LED50/730 II DS PCC GR 62P	Polycarbonate bowl/ cover frosted	Grey	
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Polycarbonate bowl/ cover frosted	Silver	
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver	

TownGuide Performer

Order Code	Full Product Name	Optical cover type	Housing Color
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991153	BDP100 LED50/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910925439711	BDP100 LED60/740 II DS PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925439715	BDP100 LED60/830 II DS PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925866273	BDP100 LED50/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866279	BDP100 LED30/740 II DW PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866281	BDP100 LED70/740 II DW PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866285	BDP100 LED30/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866286	BDP100 LED50/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866287	BDP100 LED70/740 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866290	BDP100 LED30/830 II DW PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866291	BDP100 LED50/830 II DW PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray

Order Code	Full Product Name	Optical cover type	Housing Color
910925866292	BDP100 LED70/830 II DW PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866296	BDP100 LED30/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866297	BDP100 LED70/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866298	BDP100 LED20/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866299	BDP100 LED30/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866301	BDP100 LED40/830 DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866486	BDP100 LED60/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	Polycarbonate bowl/ cover frosted	Gray
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Polycarbonate bowl/ cover frosted	Silver
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver
910925866275	BDP101 LED50/830 II DS PCF GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866484	BDP101 LED60/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	Polycarbonate bowl/ cover clear	Silver
910925866274	BDP101 LED40/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray

TownGuide Performer

Order Code	Full Product Name	Optical cover type	Housing Color
910925866485	BDP101 LED60/740 DW PCC SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	Polycarbonate bowl/ cover clear	Silver
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	Polycarbonate bowl/ cover clear	Silver
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	Polycarbonate bowl/ cover clear	Gray
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray
910925866483	BDP102 LED60/740 DW PCC SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	Polycarbonate bowl/ cover frosted	Gray
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	Polycarbonate bowl/ cover clear	Silver

Order Code	Full Product Name	Optical cover type	Housing Color
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	Polycarbonate bowl/ cover frosted	Silver
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991221	BDP102 LED20/830 II DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991223	BDP102 LED35/830 II DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	Polycarbonate bowl/ cover frosted	Silver
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver

Order Code	Full Product Name	Optical cover type	Housing Color
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	Polycarbonate bowl/ cover frosted	Silver
910925439714	BDP102 LED60/740 II DS PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925866482	BDP102 LED60/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	Polycarbonate bowl/ cover frosted	Gray
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910925866480	BDP103 LED60/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	Polycarbonate bowl/ cover frosted	Gray
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	Polycarbonate bowl/ cover frosted	Gray
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	Polycarbonate bowl/ cover frosted	Gray

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	Temperature 650 °C, duration 5 s
910925866477	BDP105 LED60/740 DW PCC SI 62P	-
910925866625	BDP105 LED50/830 II DW PCC GR 62P	-
910925866626	BDP105 LED70/830 II DW PCC GR 62P	-
910925866627	BDP105 LED70/830 II DS PCC GR 62P	-
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	Temperature 650 °C, duration 5 s
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	Temperature 650 °C, duration 5 s
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Optical cover type	Housing Color
910925866481	BDP103 LED60/740 DW PCC SI 62P	Polycarbonate bowl/ cover frosted	Silver
910925866624	BDP103 LED70/830 II DW PCC GR 62P	Polycarbonate bowl/ cover clear	Gray
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	Polycarbonate bowl/ cover clear	Black
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	Polycarbonate bowl/ cover clear	Black
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	Polycarbonate bowl/ cover clear	Black
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	Polycarbonate bowl/ cover clear	Black
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Polycarbonate bowl/ cover clear	Silver
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	Polycarbonate bowl/ cover clear	Gray
910925866479	BDP104 LED60/740 DW PCC SI 62P	Polycarbonate bowl/ cover frosted	Silver
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Polycarbonate bowl/ cover frosted	Silver
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	Polycarbonate bowl/ cover frosted	Silver
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	Polycarbonate bowl/ cover frosted	Silver
910925866478	BDP104 LED60/740 DW PCF SI 62P	Polycarbonate bowl/ cover frosted	Silver

Order Code	Full Product Name	Glow-wire test
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	Temperature 650 °C, duration 5 s

TownGuide Performer

Order Code	Full Product Name	Glow-wire test
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	-
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	-
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	Temperature 650 °C, duration 5 s
910925866272	BDP100 LED40/830 II DW PCC GR 62P	-
910925866276	BDP100 LED40/740 II DW PCC GR 62P	-
910925866277	BDP100 LED50/740 II DW PCC GR 62P	-
910925866278	BDP100 LED70/740 II DW PCC GR 62P	-
910925866282	BDP100 LED30/740 II DS PCC GR 62P	-
910925866283	BDP100 LED50/740 II DS PCC GR 62P	-
910925866284	BDP100 LED70/740 II DS PCC GR 62P	-
910925866288	BDP100 LED50/830 II DW PCC GR 62P	-
910925866289	BDP100 LED70/830 II DW PCC GR 62P	-
910925866293	BDP100 LED30/830 II DS PCC GR 62P	-
910925866294	BDP100 LED50/830 II DS PCC GR 62P	-
910925866295	BDP100 LED70/830 II DS PCC GR 62P	-
910925866302	BDP100 LED40/740 II DS PCC GR 62P	-
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	-
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	-
910925866487	BDP100 LED60/740 DW PCC SI 62P	-
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	-
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	-
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	-
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	-
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	-
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	-
910925868057	BDP100 LED40/730 II DW PCC GR 62P	-
910925868060	BDP100 LED50/730 II DS PCC GR 62P	-
910925868063	BDP100 LED50/730 II DW PCC GR 62P	-
910925868066	BDP100 LED70/730 II DS PCC GR 62P	-
910925868067	BDP100 LED70/730 II DW PCC GR 62P	-
910925868095	BDP100 LED40/830 DS PCC ALU 76P	-
910925868114	BDP100 LED70/730 II DS PCC GR 62P	-
910925868115	BDP100 LED40/730 II DW PCC GR 62P	-
910925868116	BDP100 LED50/730 II DS PCC GR 62P	-
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	Temperature 650 °C, duration 5 s
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991153	BDP100 LED50/740 DW PCF SI 62P	Temperature 650 °C, duration 5 s
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910925439711	BDP100 LED60/740 II DS PCF SI 62P	Temperature 650 °C, duration 5 s
910925439715	BDP100 LED60/830 II DS PCF SI 62P	Temperature 650 °C, duration 5 s
910925866273	BDP100 LED50/830 II DS PCF GR 62P	-
910925866279	BDP100 LED30/740 II DW PCF GR 62P	-
910925866281	BDP100 LED70/740 II DW PCF GR 62P	-
910925866285	BDP100 LED30/740 II DS PCF GR 62P	-
910925866286	BDP100 LED50/740 II DS PCF GR 62P	-
910925866287	BDP100 LED70/740 II DS PCF GR 62P	-
910925866290	BDP100 LED30/830 II DW PCF GR 62P	-
910925866291	BDP100 LED50/830 II DW PCF GR 62P	-
910925866292	BDP100 LED70/830 II DW PCF GR 62P	-
910925866296	BDP100 LED30/830 II DS PCF GR 62P	-
910925866297	BDP100 LED70/830 II DS PCF GR 62P	-
910925866298	BDP100 LED20/830 DS PCF GR 62P	-
910925866299	BDP100 LED30/830 DS PCF GR 62P	-
910925866301	BDP100 LED40/830 DS PCF GR 62P	-
910925866486	BDP100 LED60/740 DW PCF SI 62P	-
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	-
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	Temperature 650 °C, duration 5 s
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s

TownGuide Performer

Order Code	Full Product Name	Glow-wire test
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	Temperature 650 °C, duration 5 s
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	Temperature 650 °C, duration 5 s
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	Temperature 650 °C, duration 5 s
910925866275	BDP101 LED50/830 II DS PCF GR 62P	-
910925866484	BDP101 LED60/740 DW PCF SI 62P	-
910500991014	BDP101 LED60/830 II DM PCC SI CLO- DDF2 6	Temperature 650 °C, duration 5 s
910925866274	BDP101 LED40/830 II DW PCC GR 62P	-
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	-
910925866485	BDP101 LED60/740 DW PCC SI 62P	-
910500991021	BDP102 LED40/830 II DW PCC SI CLO- DDF1 6	Temperature 650 °C, duration 5 s
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	Temperature 650 °C, duration 5 s
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	Temperature 650 °C, duration 5 s
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	Temperature 650 °C, duration 5 s
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	Temperature 650 °C, duration 5 s
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	Temperature 650 °C, duration 5 s
910925866483	BDP102 LED60/740 DW PCC SI 62P	-
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	-
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	-
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	-
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	-
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	-
910500991023	BDP102 LED50/830 II DS PCF SI CLO- DDF1 6	Temperature 650 °C, duration 5 s
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s

TownGuide Performer

Order Code	Full Product Name	Glow-wire test
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991221	BDP102 LED20/830 II DW PCF SI 62P	Temperature 650 °C, duration 5 s
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991223	BDP102 LED35/830 II DW PCF SI 62P	Temperature 650 °C, duration 5 s
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	Temperature 650 °C, duration 5 s
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	Temperature 650 °C, duration 5 s
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	Temperature 650 °C, duration 5 s
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	Temperature 650 °C, duration 5 s
910925439714	BDP102 LED60/740 II DS PCF SI 62P	Temperature 650 °C, duration 5 s
910925866482	BDP102 LED60/740 DW PCF SI 62P	-
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	-
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s

Order Code	Full Product Name	Glow-wire test
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910925866480	BDP103 LED60/740 DW PCF SI 62P	-
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	Temperature 650 °C, duration 5 s
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	-
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	-
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	-
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	-
910925866481	BDP103 LED60/740 DW PCC SI 62P	-
910925866624	BDP103 LED70/830 II DW PCC GR 62P	-
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	-
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	-
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	-
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	-
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	Temperature 650 °C, duration 5 s
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	Temperature 650 °C, duration 5 s
910925866479	BDP104 LED60/740 DW PCC SI 62P	-
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	Temperature 650 °C, duration 5 s
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	Temperature 650 °C, duration 5 s
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	Temperature 650 °C, duration 5 s
910925866478	BDP104 LED60/740 DW PCF SI 62P	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	0.5 %
910925866477	BDP105 LED60/740 DW PCC SI 62P	0.5 %
910925866625	BDP105 LED50/830 II DW PCC GR 62P	0.5 %
910925866626	BDP105 LED70/830 II DW PCC GR 62P	0.5 %
910925866627	BDP105 LED70/830 II DS PCC GR 62P	0.5 %
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	0.5 %
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	0.5 %
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	0.5 %
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	0.5 %
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	0.5 %
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	0.5 %
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	0.5 %
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	0.5 %
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	0.5 %
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	0.5 %
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	0.5 %
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	0.5 %
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	0.5 %
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	0.5 %
910925452181	BDP100 LED40/740 DS PCC GR DDF27 62P	0.5 %
910925452182	BDP100 LED80/740 DS PCC GR DDF27 62P	0.5 %
910925863295	BDP100 LED70/740 DS PCC GR D9 62P	0.5 %
910925866272	BDP100 LED40/830 II DW PCC GR 62P	0.5 %
910925866276	BDP100 LED40/740 II DW PCC GR 62P	0.5 %
910925866277	BDP100 LED50/740 II DW PCC GR 62P	0.5 %
910925866278	BDP100 LED70/740 II DW PCC GR 62P	0.5 %
910925866282	BDP100 LED30/740 II DS PCC GR 62P	0.5 %
910925866283	BDP100 LED50/740 II DS PCC GR 62P	0.5 %
910925866284	BDP100 LED70/740 II DS PCC GR 62P	0.5 %
910925866288	BDP100 LED50/830 II DW PCC GR 62P	0.5 %
910925866289	BDP100 LED70/830 II DW PCC GR 62P	0.5 %

TownGuide Performer

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866293	BDP100 LED30/830 II DS PCC GR 62P	0.5 %
910925866294	BDP100 LED50/830 II DS PCC GR 62P	0.5 %
910925866295	BDP100 LED70/830 II DS PCC GR 62P	0.5 %
910925866302	BDP100 LED40/740 II DS PCC GR 62P	0.5 %
910925866303	BDP100 LED40/740 II DW PCC GR MSP 62P	0.5 %
910925866305	BDP100 LED50/830 II DS PCC GR MSP 62P	0.5 %
910925866487	BDP100 LED60/740 DW PCC SI 62P	0.5 %
910925866546	BDP100 LED40/830 DS PCC GR MSP 62P	0.5 %
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	0.5 %
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	0.5 %
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	0.5 %
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	0.5 %
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	0.5 %
910925868057	BDP100 LED40/730 II DW PCC GR 62P	-
910925868060	BDP100 LED50/730 II DS PCC GR 62P	-
910925868063	BDP100 LED50/730 II DW PCC GR 62P	-
910925868066	BDP100 LED70/730 II DS PCC GR 62P	-
910925868067	BDP100 LED70/730 II DW PCC GR 62P	-
910925868095	BDP100 LED40/830 DS PCC ALU 76P	-
910925868114	BDP100 LED70/730 II DS PCC GR 62P	-
910925868115	BDP100 LED40/730 II DW PCC GR 62P	-
910925868116	BDP100 LED50/730 II DS PCC GR 62P	-
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	0.5 %
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	0.5 %
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	0.5 %
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	0.5 %
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	0.5 %
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	0.5 %
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	0.5 %
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	0.5 %
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	0.5 %
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	0.5 %
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	0.5 %
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	0.5 %
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	0.5 %
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	0.5 %
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	0.5 %
910500991153	BDP100 LED50/740 DW PCF SI 62P	0.5 %
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	0.5 %
910925439711	BDP100 LED60/740 II DS PCF SI 62P	0.5 %
910925439715	BDP100 LED60/830 II DS PCF SI 62P	0.5 %
910925866273	BDP100 LED50/830 II DS PCF GR 62P	0.5 %
910925866279	BDP100 LED30/740 II DW PCF GR 62P	0.5 %
910925866281	BDP100 LED70/740 II DW PCF GR 62P	0.5 %
910925866285	BDP100 LED30/740 II DS PCF GR 62P	0.5 %
910925866286	BDP100 LED50/740 II DS PCF GR 62P	0.5 %
910925866287	BDP100 LED70/740 II DS PCF GR 62P	0.5 %
910925866290	BDP100 LED30/830 II DW PCF GR 62P	0.5 %
910925866291	BDP100 LED50/830 II DW PCF GR 62P	0.5 %
910925866292	BDP100 LED70/830 II DW PCF GR 62P	0.5 %
910925866296	BDP100 LED30/830 II DS PCF GR 62P	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866297	BDP100 LED70/830 II DS PCF GR 62P	0.5 %
910925866298	BDP100 LED20/830 DS PCF GR 62P	0.5 %
910925866299	BDP100 LED30/830 DS PCF GR 62P	0.5 %
910925866301	BDP100 LED40/830 DS PCF GR 62P	0.5 %
910925866486	BDP100 LED60/740 DW PCF SI 62P	0.5 %
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	-
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	0.5 %
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	0.5 %
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	0.5 %
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	0.5 %
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	0.5 %
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	0.5 %
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	0.5 %
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	0.5 %
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	0.5 %
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	0.5 %
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	0.5 %
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	0.5 %
910925866275	BDP101 LED50/830 II DS PCF GR 62P	0.5 %
910925866484	BDP101 LED60/740 DW PCF SI 62P	0.5 %
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	0.5 %
910925866274	BDP101 LED40/830 II DW PCC GR 62P	0.5 %
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	0.5 %
910925866485	BDP101 LED60/740 DW PCC SI 62P	0.5 %
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	0.5 %
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	0.5 %
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	0.5 %
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	0.5 %
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	0.5 %
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	0.5 %
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	0.5 %
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	0.5 %
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	0.5 %
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	0.5 %
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	0.5 %
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	0.5 %
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	0.5 %
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	0.5 %
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	0.5 %
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	0.5 %
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	0.5 %
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	0.5 %
910925866483	BDP102 LED60/740 DW PCC SI 62P	0.5 %
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	0.5 %
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	0.5 %
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	0.5 %
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	0.5 %
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	-
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	0.5 %
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	0.5 %
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	0.5 %
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	0.5 %
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	0.5 %
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	0.5 %
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	0.5 %
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	0.5 %
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	0.5 %
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	0.5 %
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	0.5 %
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	0.5 %
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	0.5 %
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	0.5 %
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	0.5 %
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	0.5 %
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	0.5 %
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	0.5 %
910500991221	BDP102 LED20/830 II DW PCF SI 62P	0.5 %
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	0.5 %
910500991223	BDP102 LED35/830 II DW PCF SI 62P	0.5 %
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	0.5 %
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	0.5 %
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	0.5 %
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	0.5 %
910925439714	BDP102 LED60/740 II DS PCF SI 62P	0.5 %
910925866482	BDP102 LED60/740 DW PCF SI 62P	0.5 %
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	-

Product Data

Order Code	Full Product Name	Product family code
910925863304	BDP105 LED70/740 DS PCC GR D9 62P	BDP105
910925866477	BDP105 LED60/740 DW PCC SI 62P	BDP105
910925866625	BDP105 LED50/830 II DW PCC GR 62P	BDP105
910925866626	BDP105 LED70/830 II DW PCC GR 62P	BDP104
910925866627	BDP105 LED70/830 II DS PCC GR 62P	BDP105
910500991009	BDP100 LED30/740 DN PCC SI CLO-LS-6 76P	BDP100
910500991010	BDP100 LED40/830 II DM PCC SI CLO-LS-6 6	BDP100
910500991056	BDP100 LED40/740 II DW PCC SI LS-6 62P	BDP100
910500991057	BDP100 LED50/740 II DW PCC SI LS-6 62P	BDP100
910500991058	BDP100 LED60/740 II DW PCC SI LS-6 62P	BDP100
910500991062	BDP100 LED40/740 II DS PCC SI LS-6 62P	BDP100
910500991063	BDP100 LED50/740 II DS PCC SI LS-6 62P	BDP100
910500991064	BDP100 LED60/740 II DS PCC SI LS-6 62P	BDP100
910500991068	BDP100 LED40/830 II DW PCC SI LS-6 62P	BDP100
910500991069	BDP100 LED50/830 II DW PCC SI LS-6 62P	BDP100
910500991070	BDP100 LED60/830 II DW PCC SI LS-6 62P	BDP100
910500991074	BDP100 LED40/830 II DS PCC SI LS-6 62P	BDP100
910500991075	BDP100 LED50/830 II DS PCC SI LS-6 62P	BDP100
910500991076	BDP100 LED60/830 II DS PCC SI LS-6 62P	BDP100
910500991164	BDP100 LED30/740 DM PCC SI CLO-DDF1 76P	BDP100

Order Code	Full Product Name	Driver failure rate at 5000 h
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	0.5 %
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	0.5 %
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	0.5 %
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	0.5 %
910925866480	BDP103 LED60/740 DW PCF SI 62P	0.5 %
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	0.5 %
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	0.5 %
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	0.5 %
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	0.5 %
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	0.5 %
910925866481	BDP103 LED60/740 DW PCC SI 62P	0.5 %
910925866624	BDP103 LED70/830 II DW PCC GR 62P	0.5 %
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	-
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	-
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	-
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	-
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	0.5 %
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	0.5 %
910925866479	BDP104 LED60/740 DW PCC SI 62P	0.5 %
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	0.5 %
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	0.5 %
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	0.5 %
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	0.5 %
910925866478	BDP104 LED60/740 DW PCF SI 62P	0.5 %



Order Code	Full Product Name	Product family code
910925866547	BDP100 LED40/740 DS PCC GR MSP 62P	BDP100
910925867796	BDP100 LED120/740 II DRW PCC GR-900 D11	BDP100
910925867797	BDP100 LED120/740 II DRW PCC GR-900 D11	BDP100
910925867798	BDP100 LED70/740 II DRW PCC GR-900 D11 5	BDP100
910925867799	BDP100 LED70/740 II DRW PCC GR-900 D11 5	BDP100
910925868057	BDP100 LED40/730 II DW PCC GR 62P	BDP100
910925868060	BDP100 LED50/730 II DS PCC GR 62P	BDP100
910925868063	BDP100 LED50/730 II DW PCC GR 62P	BDP100
910925868066	BDP100 LED70/730 II DS PCC GR 62P	BDP100
910925868067	BDP100 LED70/730 II DW PCC GR 62P	BDP100
910925868095	BDP100 LED40/830 DS PCC ALU 76P	BDP100
910925868114	BDP100 LED70/730 II DS PCC GR 62P	BDP100
910925868115	BDP100 LED40/730 II DW PCC GR 62P	BDP100
910925868116	BDP100 LED50/730 II DS PCC GR 62P	BDP100
910500991011	BDP100 LED50/830 II DS PCF SI CLO-LS-6 6	BDP100
910500991060	BDP100 LED50/740 II DW PCF SI LS-6 62P	BDP100
910500991061	BDP100 LED60/740 II DW PCF SI LS-6 62P	BDP100
910500991065	BDP100 LED40/740 II DS PCF SI LS-6 62P	BDP100
910500991066	BDP100 LED50/740 II DS PCF SI LS-6 62P	BDP100
910500991067	BDP100 LED60/740 II DS PCF SI LS-6 62P	BDP100
910500991071	BDP100 LED40/830 II DW PCF SI LS-6 62P	BDP100
910500991072	BDP100 LED50/830 II DW PCF SI LS-6 62P	BDP100
910500991073	BDP100 LED60/830 II DW PCF SI LS-6 62P	BDP100
910500991077	BDP100 LED40/830 II DS PCF SI LS-6 62P	BDP100
910500991078	BDP100 LED50/830 II DS PCF SI LS-6 62P	BDP100
910500991079	BDP100 LED60/830 II DS PCF SI LS-6 62P	BDP100
910500991112	BDP100 LED20/830 DW PCF SI CLO 62P	BDP100
910500991115	BDP100 LED50/830 DW PCF SI CLO 62P	BDP100
910500991117	BDP100 LED100/830 DW PCF SI CLO 62P	BDP100
910500991153	BDP100 LED50/740 DW PCF SI 62P	BDP100
910500991190	BDP100 LED30/740 II DS PCF SI CLO 62P	BDP100
910925439711	BDP100 LED60/740 II DS PCF SI 62P	BDP100
910925439715	BDP100 LED60/830 II DS PCF SI 62P	BDP100
910925866273	BDP100 LED50/830 II DS PCF GR 62P	BDP100
910925866279	BDP100 LED30/740 II DW PCF GR 62P	BDP100
910925866281	BDP100 LED70/740 II DW PCF GR 62P	BDP100
910925866285	BDP100 LED30/740 II DS PCF GR 62P	BDP100
910925866286	BDP100 LED50/740 II DS PCF GR 62P	BDP100
910925866287	BDP100 LED70/740 II DS PCF GR 62P	BDP100
910925866290	BDP100 LED30/830 II DW PCF GR 62P	BDP100
910925866291	BDP100 LED50/830 II DW PCF GR 62P	BDP100
910925866292	BDP100 LED70/830 II DW PCF GR 62P	BDP100
910925866296	BDP100 LED30/830 II DS PCF GR 62P	BDP100
910925866297	BDP100 LED70/830 II DS PCF GR 62P	BDP100
910925866298	BDP100 LED20/830 DS PCF GR 62P	BDP100
910925866299	BDP100 LED30/830 DS PCF GR 62P	BDP100
910925866301	BDP100 LED40/830 DS PCF GR 62P	BDP100
910925866486	BDP100 LED60/740 DW PCF SI 62P	BDP100
910925868223	BDP100 LED70/730 II DM PCTR GR D9 SDM10	BDP100
910500991015	BDP101 LED60/830 II DS PCF SI CLO-DDF2 6	BDP101
910500991121	BDP101 LED30/830 DW PCF SI CLO 62P	BDP101
910500991122	BDP101 LED35/830 DW PCF SI CLO 62P	BDP101

Order Code	Full Product Name	Product family code
910500991125	BDP101 LED100/830 DW PCF SI CLO 62P	BDP101
910500991214	BDP101 LED20/830 II DW PCF SI LS-8 62P	BDP101
910500991216	BDP101 LED35/830 II DW PCF SI LS-8 62P	BDP101
910500991218	BDP101 LED60/830 II DW PCF SI LS-8 62P	BDP101
910500991226	BDP101 LED60/830 II DW PCF SI LS-6 62P	BDP101
910500991228	BDP101 LED60/830 II DS PCF SI LS-6 62P	BDP101
910500991230	BDP101 LED40/830 II DM PCF SI 6 62P	BDP101
910500991231	BDP101 LED40/740 II DM PCF SI 6 62P	BDP101
910925439673	BDP101 LED40/830 II DS PCF SI 6 62P	BDP101
910925866275	BDP101 LED50/830 II DS PCF GR 62P	BDP101
910925866484	BDP101 LED60/740 DW PCF SI 62P	BDP101
910500991014	BDP101 LED60/830 II DM PCC SI CLO-DDF2 6	BDP101
910925866274	BDP101 LED40/830 II DW PCC GR 62P	BDP101
910925866304	BDP101 LED40/740 II DS PCC GR MSP 62P	BDP101
910925866485	BDP101 LED60/740 DW PCC SI 62P	BDP101
910500991021	BDP102 LED40/830 II DW PCC SI CLO-DDF1 6	BDP102
910500991080	BDP102 LED40/740 II DW PCC SI LS-6 62P	BDP102
910500991081	BDP102 LED50/740 II DW PCC SI LS-6 62P	BDP102
910500991082	BDP102 LED60/740 II DW PCC SI LS-6 62P	BDP102
910500991086	BDP102 LED40/740 II DS PCC SI LS-6 62P	BDP102
910500991087	BDP102 LED50/740 II DS PCC SI LS-6 62P	BDP102
910500991088	BDP102 LED60/740 II DS PCC SI LS-6 62P	BDP102
910500991092	BDP102 LED40/830 II DW PCC SI LS-6 62P	BDP102
910500991093	BDP102 LED50/830 II DW PCC SI LS-6 62P	BDP102
910500991094	BDP102 LED60/830 II DW PCC SI LS-6 62P	BDP102
910500991098	BDP102 LED40/830 II DS PCC SI LS-6 62P	BDP102
910500991099	BDP102 LED50/830 II DS PCC SI LS-6 62P	BDP102
910500991101	BDP102 LED60/830 II DS PCC SI LS-6 62P	BDP102
910500991210	BDP102 LED50/830 DS PCC GR MSP 62P	BDP102
910500991211	BDP102 LED50/830 DM PCC GR MSP 62P	BDP102
910500991212	BDP102 LED50/740 DS PCC GR MSP 62P	BDP102
910500991213	BDP102 LED50/740 DM PCC GR MSP 62P	BDP102
910925863297	BDP102 LED70/740 DRW PCC GR D9 62P	BDP102
910925866483	BDP102 LED60/740 DW PCC SI 62P	BDP102
910925866548	BDP102 LED50/830 DS PCC GR MSP 62P	BDP102
910925866549	BDP102 LED50/830 DM PCC GR MSP 62P	BDP102
910925866550	BDP102 LED50/740 DS PCC GR MSP 62P	BDP102
910925866551	BDP102 LED50/740 DM PCC GR MSP 62P	BDP102
910925868219	BDP102 LED35/730 II DRW PCC SI MSP CLO 6	BDP102
910500991023	BDP102 LED50/830 II DS PCF SI CLO-DDF1 6	BDP102
910500991083	BDP102 LED40/740 II DW PCF SI LS-6 62P	BDP102
910500991084	BDP102 LED50/740 II DW PCF SI LS-6 62P	BDP102
910500991085	BDP102 LED60/740 II DW PCF SI LS-6 62P	BDP102
910500991089	BDP102 LED40/740 II DS PCF SI LS-6 62P	BDP102
910500991090	BDP102 LED50/740 II DS PCF SI LS-6 62P	BDP102
910500991091	BDP102 LED60/740 II DS PCF SI LS-6 62P	BDP102
910500991095	BDP102 LED40/830 II DW PCF SI LS-6 62P	BDP102
910500991096	BDP102 LED50/830 II DW PCF SI LS-6 62P	BDP102
910500991097	BDP102 LED60/830 II DW PCF SI LS-6 62P	BDP102
910500991102	BDP102 LED40/830 II DS PCF SI LS-6 62P	BDP102
910500991103	BDP102 LED50/830 II DS PCF SI LS-6 62P	BDP102
910500991104	BDP102 LED60/830 II DS PCF SI LS-6 62P	BDP102

Order Code	Full Product Name	Product family code
910500991128	BDP102 LED20/830 DW PCF SI CLO 62P	BDP102
910500991129	BDP102 LED30/830 DW PCF SI CLO 62P	BDP102
910500991130	BDP102 LED35/830 DW PCF SI CLO 62P	BDP102
910500991131	BDP102 LED50/830 DW PCF SI CLO 62P	BDP102
910500991132	BDP102 LED70/830 DW PCF SI CLO 62P	BDP102
910500991220	BDP102 LED20/830 II DW PCF SI LS-8 62P	BDP102
910500991221	BDP102 LED20/830 II DW PCF SI 62P	BDP102
910500991222	BDP102 LED35/830 II DW PCF SI LS-8 62P	BDP102
910500991223	BDP102 LED35/830 II DW PCF SI 62P	BDP102
910500991224	BDP102 LED60/830 II DW PCF SI LS-8 62P	BDP102
910500991232	BDP102 LED40/830 II DM PCF SI 6 62P	BDP102
910500991233	BDP102 LED40/740 II DM PCF SI 6 62P	BDP102
910925439676	BDP102 LED40/740 II DS PCF SI 6 62P	BDP102
910925439714	BDP102 LED60/740 II DS PCF SI 62P	BDP102
910925866482	BDP102 LED60/740 DW PCF SI 62P	BDP102
910925868224	BDP102 LED25/740 DRW PCTR GR CLO-DDF2 D1	BDP102
910500991136	BDP103 LED20/830 DW PCF SI CLO 62P	BDP103
910500991138	BDP103 LED35/830 DW PCF SI CLO 62P	BDP103
910500991139	BDP103 LED50/830 DW PCF SI CLO 62P	BDP103
910500991142	BDP103 LED120/830 DW PCF SI CLO 62P	BDP103


Order Code	Full Product Name	Product family code
910925866480	BDP103 LED60/740 DW PCF SI 62P	BDP103
910925863301	BDP103 LED70/740 DS PCC GR D9 62P	BDP103
910925866471	BDP103 LED15/740 II DRW PCC GR 62P	BDP103
910925866472	BDP103 LED15/740 II DRW PCC GR 76P	BDP103
910925866473	BDP103 LED25/740 II DRW PCC GR 62P	BDP103
910925866474	BDP103 LED25/740 II DRW PCC GR 76P	BDP103
910925866481	BDP103 LED60/740 DW PCC SI 62P	BDP103
910925866624	BDP103 LED70/830 II DW PCC GR 62P	BDP103
910925868807	BDP103 LED30/740 II DS PCC BK CLO 76P	BDP103
910925868808	BDP103 LED50/740 II DS PCC BK CLO 76P	BDP103
910925868809	BDP103 LED60/740 II DS PCC BK CLO 76P	BDP103
910925868810	BDP103 LED70/740 II DS PCC BK CLO 76P	BDP103
910500991024	BDP104 LED30/740 II DM PCC SI CLO-LS-8 6	BDP104
910925863302	BDP104 LED70/740 DRW PCC GR D9 62P	BDP104
910925866479	BDP104 LED60/740 DW PCC SI 62P	BDP104
910500991025	BDP104 LED40/830 II DS PCF SI CLO-LS-8 6	BDP104
910500991059	BDP100 LED40/740 II DW PCF SI LS-6 62P	BDP100
910500991147	BDP104 LED50/830 DW PCF SI CLO 62P	BDP104
910500991149	BDP104 LED100/830 DW PCF SI CLO 62P	BDP104
910925866478	BDP104 LED60/740 DW PCF SI 62P	BDP104

Polar Wide Diagrams






Polar Normal (separate) - BDP100I - 910500991089

Polar Normal (separate) - BDP100I - 910500991064



Polar Normal (separate) - BDP100I - 910500991080




Polar Normal (separate) - BDP100I - 910500991074


Polar Normal (separate) - BDP100I - 910500991010

Polar Normal (separate) - BDP100I - 910500991104


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991136




Polar Normal (separate) - BDP100I - 910500991021




Polar Normal (separate) - BDP100I - 910500991062




Polar Normal (separate) - BDP100I - 910500991085




Polar Normal (separate) - BDP100I - 910500991093




Polar Normal (separate) - BDP100I - 910500991066



Polar Normal (separate) - BDP100I - 910500991073




Polar Normal (separate) - BDP100I - 910500991082




Polar Normal (separate) - BDP100I - 910500991014


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991090




Polar Normal (separate) - BDP100I - 910500991112




Polar Normal (separate) - BDP100I - 910500991077




Polar Normal (separate) - BDP100I - 910500991024




Polar Normal (separate) - BDP100I - 910500991079




Polar Normal (separate) - BDP100I - 910500991223



Polar Normal (separate) - BDP100I - 910500991103




Polar Normal (separate) - BDP100I - 910500991149




Polar Normal (separate) - BDP100I - 910500991069


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991084




Polar Normal (separate) - BDP100I - 910500991071




Polar Normal (separate) - BDP100I - 910500991078




Polar Normal (separate) - BDP100I - 910500991081




Polar Normal (separate) - BDP100I - 910500991086




Polar Normal (separate) - BDP100I - 910500991083



Polar Normal (separate) - BDP100I - 910500991096




Polar Normal (separate) - BDP100I - 910500991094




Polar Normal (separate) - BDP100I - 910500991058


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991139




Polar Normal (separate) - BDP100I - 910500991015




Polar Normal (separate) - BDP100I - 910500991097




Polar Normal (separate) - BDP100I - 910500991025




Polar Normal (separate) - BDP100I - 910500991009




Polar Normal (separate) - BDP100I - 910500991076



Polar Normal (separate) - BDP100I - 910500991057




Polar Normal (separate) - BDP100I - 910500991060




Polar Normal (separate) - BDP100I - 910500991098


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991087




Polar Normal (separate) - BDP100I - 910500991132




Polar Normal (separate) - BDP100I - 910500991190




Polar Normal (separate) - BDP100I - 910500991063




Polar Normal (separate) - BDP100I - 910500991068




Polar Normal (separate) - BDP100I - 910500991059



Polar Normal (separate) - BDP100I - 910500991128




Polar Normal (separate) - BDP100I - 910500991065




Polar Normal (separate) - BDP100I - 910500991072


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991101




Polar Normal (separate) - BDP100I - 910500991088




Polar Normal (separate) - BDP100I - 910500991164




Polar Normal (separate) - BDP100I - 910500991061




Polar Normal (separate) - BDP100I - 910500991056




Polar Normal (separate) - BDP100I - 910500991122



Polar Normal (separate) - BDP100I - 910500991091




Polar Normal (separate) - BDP100I - 910500991125




Polar Normal (separate) - BDP100I - 910500991095


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991129




Polar Normal (separate) - BDP100I - 910500991210




Polar Normal (separate) - BDP100I - 910500991067




Polar Normal (separate) - BDP100I - 910500991121




Polar Normal (separate) - BDP100I - 910500991147




Polar Normal (separate) - BDP100I - 910500991070



Polar Normal (separate) - BDP100I - 910500991102




Polar Normal (separate) - BDP100I - 910500991117




Polar Normal (separate) - BDP100I - 910500991211


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991075




Polar Normal (separate) - BDP100I - 910500991213




Polar Normal (separate) - BDP100I - 910500991142




Polar Normal (separate) - BDP100I - 910500991138




Polar Normal (separate) - BDP100I - 910925866295




Polar Normal (separate) - BDP100I - 910925866299



Polar Normal (separate) - BDP100I - 910925866304




Polar Normal (separate) - BDP100I - 910925863297




Polar Normal (separate) - BDP100I - 910925863295


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925439673




Polar Normal (separate) - BDP100I - 910925866282




Polar Normal (separate) - BDP100I - 910925866289




Polar Normal (separate) - BDP100I - 910925866287




Polar Normal (separate) - BDP100I - 910925866298




Polar Normal (separate) - BDP100I - 910925866293



Polar Normal (separate) - BDP100I - 910925866297




Polar Normal (separate) - BDP100I - 910925866275




Polar Normal (separate) - BDP100I - 910925866278


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925866626




Polar Normal (separate) - BDP100I - 910925866627




**Polar Normal (separate) - BDP100I -
910925867796**




Polar Normal (separate) - BDP100I - 910925866479




Polar Normal (separate) - BDP100I - 910925866478




**Polar Normal (separate) - BDP100I -
910925866477**



Polar Normal (separate) - BDP100I - 910925866480




Polar Normal (separate) - BDP100I - 910925866484




Polar Normal (separate) - BDP100I - 910925868114


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925868115




Polar Normal (separate) - BDP100I - 910925868116




Polar Normal (separate) - BDP100I - 910925868219




Polar Normal (separate) - BDP100I - 910925868808




Polar Normal (separate) - BDP100I - 910925868807




Polar Normal (separate) - BDP100I - 910925868810



Polar Normal (separate) - BDP100I - 910925868809




Polar Normal (separate) - BDP100I - 910925452182




Polar Normal (separate) - BDP100I - 910500991218


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910500991214




Polar Normal (separate) - BDP100I - 910500991231




Polar Normal (separate) - BDP100I - 910500991230




Polar Normal (separate) - BDP100I - 910500991232




Polar Normal (separate) - BDP100I - 910500991233




Polar Normal (separate) - BDP100I - 910925863304



Polar Normal (separate) - BDP100I - 910925863302




Polar Normal (separate) - BDP100I - 910925866472




Polar Normal (separate) - BDP100I - 910925866473


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925866481




Polar Normal (separate) - BDP100I - 910925866485




Polar Normal (separate) - BDP100I - 910925866624




Polar Normal (separate) - BDP100I - 910925866625




Polar Normal (separate) - BDP100I - 910925866274




Polar Normal (separate) - BDP100I - 910925866279



Polar Normal (separate) - BDP100I - 910925866281




Polar Normal (separate) - BDP100I - 910925866290




Polar Normal (separate) - BDP100I - 910925866292


Polar Wide Diagrams




Polar Normal (separate) - BDP100I - 910925867798




Polar Normal (separate) - BDP100I - 910925868063



Polar Normal (separate) - BDP100I - 910925868067



Polar Normal (separate) - BDP100I - 910925868223



Polar Normal (separate) - BDP100I - 910925868224

