



# TownTune Central Post Top - Extending the home feel onto the street

## TownTune Central Post-Top

Designed to enhance existing and scalable urban spaces, the TownTune family offers all the latest lighting innovations in terms of performance, quality of light and connectivity. The family consists of four solutions: a Central Post Top (CPT), an Asymmetric Spigot Post Top / Side Entry version (ASY), a version with an extending Lyre post top bracket (Lyre), and a Central Post Top with a Conical Comfort Bowl (CCB). Each TownTune luminaire can be customized with a choice of different shapes on top of the housing, plus there's the option to add a decorative ring, which comes in two colors (excluding CCB). Design options that enable you to create your very own lighting signature and bring a distinctive identity to districts and cities. In addition, every luminaire in the TownTune family is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programming operations faster and easier and enables you to create your digital library of lighting assets and spare parts. TownTune also uses the LEDGINE-O lighting platform, ensuring you always have the right amount and direction of light on your street. Furthermore, thanks to being system ready (SR), TownTune is also future proof. A solution that's ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.

# TownTune Central Post-Top

## Benefits

- LEDGINE-O platform for great performance, choice color temperatures and light distributions
- Optimized Total Cost of Ownership (L-Tune for flux tuning, standalone controls e.g., LumiStep, Dynadimmer, CLO (Constant Light output), LineSwitch)
- Ready to pair with advanced systems and software applications e.g., Interact City
- Long lifetime: 100,000 hours @L85 and higher
- Easy access to gear, vandal resistant (IK10), high ingress protection (IP66)

## Features

- Simple design for easy integration into urban spaces, wide range of accessories for customization
- Suitable for new and retrofit installations
- Range of lumen packages (1200 to 12000 lm) and CCTs (2200K, 2700K, 3000K, 4000K)
- Dedicated bowl for visual comfort and comfortable lighting experiences
- Service tag for easy installation and maintenance

## Application


- Urban and residential areas
- Cycle paths, footpaths and pedestrian crossings
- City centers and squares
- Car parks

## Versions

BDP260, TownTune Central Post-  
Top Ral 7035



## Dimensional drawing



|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| General Information                    |                                             |
| Driver included                        | Yes                                         |
| Light source replaceable               | Yes                                         |
| Number of gear units                   | 1 unit                                      |
| Service tag                            | Yes                                         |
| Light Technical                        |                                             |
| Upward light output ratio              | 0                                           |
| Operating and Electrical               |                                             |
| Surge Protection (Common/Differential) | Standard surge protection level             |
| Controls and Dimming                   |                                             |
| Maximum dim level                      | 10%                                         |
| Mechanical and Housing                 |                                             |
| Optical cover type                     | Polycarbonate bowl/cover UV-resistant       |
| Housing Color                          | Gray                                        |
| Mech. impact protection code           | IK10                                        |
| Ingress protection code                | IP66                                        |
| Standard tilt angle side entry         | -                                           |
| Standard tilt angle posttop            | 0°                                          |
| Approval and Application               |                                             |
| CE mark                                | Yes                                         |
| Flammability mark                      | For mounting on normally flammable surfaces |
| Product Data                           |                                             |
| Product family code                    | BDP260                                      |

General Information

| Order Code | Full Product Name                        | Lamp family code |
|------------|------------------------------------------|------------------|
| 88449900   | BDP260 LED35-4S/740 PSU II DS50 CLO 62P  | LED35            |
| 49024900   | BDP260 LED39-4S/830 DM50 CLO DDF3 62P    | LED39            |
| 49028700   | BDP260 LED14-4S/740 DW10 CLO SRTB 76P    | LED14            |
| 49455100   | BDP260 LED35-4S/830 DW50 62P             | LED35            |
| 49456800   | BDP260 LED79-4S/740 DM30 62P             | LED79            |
| 86490300   | BDP260 LED39-4S/830 II DS50 62P          | LED39            |
| 86491000   | BDP260 LED39-4S/740 II DS50 62P          | LED39            |
| 86492700   | BDP260 LED39-4S/830 II DM10 62P          | LED39            |
| 86493400   | BDP260 LED39-4S/740 II DM10 62P          | LED39            |
| 86494100   | BDP260 LED39-4S/830 II DW10 62P          | LED39            |
| 86496500   | BDP260 LED50-4S/830 II DS50 62P          | LED50            |
| 86497200   | BDP260 LED50-4S/740 II DS50 62P          | LED50            |
| 86498900   | BDP260 LED50-4S/830 II DM10 62P          | LED50            |
| 86499600   | BDP260 LED50-4S/740 II DM10 62P          | LED50            |
| 86500900   | BDP260 LED50-4S/830 II DW10 62P          | LED50            |
| 86501600   | BDP260 LED50-4S/740 II DW10 62P          | LED50            |
| 86502300   | BDP260 LED74-4S/830 II DS50 62P          | LED74            |
| 86503000   | BDP260 LED74-4S/740 II DS50 62P          | LED74            |
| 86504700   | BDP260 LED74-4S/830 II DM10 62P          | LED74            |
| 86505400   | BDP260 LED74-4S/740 II DM10 62P          | LED74            |
| 86506100   | BDP260 LED74-4S/830 II DW10 62P          | LED74            |
| 86507800   | BDP260 LED74-4S/740 II DW10 62P          | LED74            |
| 87861000   | BDP260 LED35-4S/830 PSU II DS50 CLO 62P  | LED35            |
| 89449800   | BDP260 LED100/740 PSR II DS50 PCC DGR 62 | LED100           |
| 89450400   | BDP260 LED100/740 PSR II DS50 PCC DGR 76 | LED100           |
| 21432300   | BDP260 LED69-4S/740 PSDD II DS50 DGR DF2 | LED69            |

Light Technical (1/2)

| Order Code | Full Product Name                       | Luminaire         | Light             | Correlated              | Color                 |
|------------|-----------------------------------------|-------------------|-------------------|-------------------------|-----------------------|
|            |                                         | light beam spread | source color      | Color Temperature (Nom) | rendering index (CRI) |
| 88449900   | BDP260 LED35-4S/740 PSU II DS50 CLO 62P | 152° x 155°       | 740 neutral white | 4000 K                  | 70                    |
| 49024900   | BDP260 LED39-4S/830 DM50 CLO DDF3 62P   | 30° - 5° x 153°   | 830 warm white    | 3000 K                  | 80                    |
| 49028700   | BDP260 LED14-4S/740                     | 7° - 52° x 150°   | 740 neutral white | 4000 K                  | 70                    |

| Order Code | Full Product Name               | Luminaire         | Light             | Correlated              | Color                 |
|------------|---------------------------------|-------------------|-------------------|-------------------------|-----------------------|
|            |                                 | light beam spread | source color      | Color Temperature (Nom) | rendering index (CRI) |
|            | DW10 CLO SRTB 76P               |                   |                   |                         |                       |
| 49455100   | BDP260 LED35-4S/830 DW50 62P    | 23° - 8° x 152°   | 830 warm white    | 3000 K                  | 80                    |
| 49456800   | BDP260 LED79-4S/740 DM30 62P    | 4° - 57° x 149°   | 740 neutral white | 4000 K                  | 70                    |
| 86490300   | BDP260 LED39-4S/830 II DS50 62P | 152° x 155°       | 830 warm white    | 3000 K                  | 80                    |

TownTune Central Post-Top

| Order Code | Full Product Name | Luminaire         | Light        | Correlated              | Color                 |
|------------|-------------------|-------------------|--------------|-------------------------|-----------------------|
|            |                   | light beam spread | source color | Color Temperature (Nom) | rendering index (CRI) |
| 86491000   | BDP260            | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED39-4S/740 II   |                   | neutral      |                         |                       |
|            | DS50 62P          |                   | white        |                         |                       |
| 86492700   | BDP260            | 77° - 11° x 156°  | 830          | 3000 K                  | 80                    |
|            | LED39-4S/830 II   |                   | warm         |                         |                       |
|            | DM10 62P          |                   | white        |                         |                       |
| 86493400   | BDP260            | 77° - 11° x 156°  | 740          | 4000 K                  | 70                    |
|            | LED39-4S/740 II   |                   | neutral      |                         |                       |
|            | DM10 62P          |                   | white        |                         |                       |
| 86494100   | BDP260            | 7° - 52° x 150°   | 830          | 3000 K                  | 80                    |
|            | LED39-4S/830 II   |                   | warm         |                         |                       |
|            | DW10 62P          |                   | white        |                         |                       |
| 86496500   | BDP260            | 152° x 155°       | 830          | 3000 K                  | 80                    |
|            | LED50-4S/830 II   |                   | warm         |                         |                       |
|            | DS50 62P          |                   | white        |                         |                       |
| 86497200   | BDP260            | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED50-4S/740 II   |                   | neutral      |                         |                       |
|            | DS50 62P          |                   | white        |                         |                       |
| 86498900   | BDP260            | 77° - 11° x 156°  | 830          | 3000 K                  | 80                    |
|            | LED50-4S/830 II   |                   | warm         |                         |                       |
|            | DM10 62P          |                   | white        |                         |                       |
| 86499600   | BDP260            | 77° - 11° x 156°  | 740          | 4000 K                  | 70                    |
|            | LED50-4S/740 II   |                   | neutral      |                         |                       |
|            | DM10 62P          |                   | white        |                         |                       |
| 86500900   | BDP260            | 7° - 52° x 150°   | 830          | 3000 K                  | 80                    |
|            | LED50-4S/830 II   |                   | warm         |                         |                       |
|            | DW10 62P          |                   | white        |                         |                       |
| 86501600   | BDP260            | 7° - 52° x 150°   | 740          | 4000 K                  | 70                    |
|            | LED50-4S/740 II   |                   | neutral      |                         |                       |
|            | DW10 62P          |                   | white        |                         |                       |
| 86502300   | BDP260            | 152° x 155°       | 830          | 3000 K                  | 80                    |
|            | LED74-4S/830 II   |                   | warm         |                         |                       |
|            | DS50 62P          |                   | white        |                         |                       |

| Order Code | Full Product Name    | Luminaire         | Light        | Correlated              | Color                 |
|------------|----------------------|-------------------|--------------|-------------------------|-----------------------|
|            |                      | light beam spread | source color | Color Temperature (Nom) | rendering index (CRI) |
| 86503000   | BDP260               | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED74-4S/740 II      |                   | neutral      |                         |                       |
|            | DS50 62P             |                   | white        |                         |                       |
| 86504700   | BDP260               | 77° - 11° x 156°  | 830          | 3000 K                  | 80                    |
|            | LED74-4S/830 II      |                   | warm         |                         |                       |
|            | DM10 62P             |                   | white        |                         |                       |
| 86505400   | BDP260               | 77° - 11° x 156°  | 740          | 4000 K                  | 70                    |
|            | LED74-4S/740 II      |                   | neutral      |                         |                       |
|            | DM10 62P             |                   | white        |                         |                       |
| 86506100   | BDP260               | 7° - 52° x 150°   | 830          | 3000 K                  | 80                    |
|            | LED74-4S/830 II      |                   | warm         |                         |                       |
|            | DW10 62P             |                   | white        |                         |                       |
| 86507800   | BDP260               | 7° - 52° x 150°   | 740          | 4000 K                  | 70                    |
|            | LED74-4S/740 II      |                   | neutral      |                         |                       |
|            | DW10 62P             |                   | white        |                         |                       |
| 87861000   | BDP260               | 152° x 155°       | 830          | 3000 K                  | 80                    |
|            | LED35-4S/830         |                   | warm         |                         |                       |
|            | PSU II DS50 CLO 62P  |                   | white        |                         |                       |
| 89449800   | BDP260               | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED100/740 PSR       |                   | neutral      |                         |                       |
|            | II DS50 PCC DGR 62   |                   | white        |                         |                       |
| 89450400   | BDP260               | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED100/740 PSR       |                   | neutral      |                         |                       |
|            | II DS50 PCC DGR 76   |                   | white        |                         |                       |
| 21432300   | BDP260               | 152° x 155°       | 740          | 4000 K                  | 70                    |
|            | LED69-4S/740         |                   | neutral      |                         |                       |
|            | PSDD II DS50 DGR DF2 |                   | white        |                         |                       |

Light Technical (2/2)

| Order Code | Full Product Name                          | Luminous | Number           | Optic type                  |
|------------|--------------------------------------------|----------|------------------|-----------------------------|
|            |                                            | Flux     | of light sources | outdoor                     |
| 88449900   | BDP260 LED35-4S/740<br>PSU II DS50 CLO 62P | 2,482 lm | 12               | Distribution symmetrical 50 |
| 49024900   | BDP260 LED39-4S/830<br>DM50 CLO DDF3 62P   | 2,546 lm | -                | Distribution medium 50      |
| 49028700   | BDP260 LED14-4S/740<br>DW10 CLO SRTB 76P   | 1,078 lm | -                | Distribution wide 10        |
| 49455100   | BDP260 LED35-4S/830<br>DW50 62P            | 2,380 lm | -                | Distribution wide 50        |
| 49456800   | BDP260 LED79-4S/740<br>DM30 62P            | 5,760 lm | -                | Distribution medium 30      |

| Order Code | Full Product Name                  | Luminous | Number           | Optic type                  |
|------------|------------------------------------|----------|------------------|-----------------------------|
|            |                                    | Flux     | of light sources | outdoor                     |
| 86490300   | BDP260 LED39-4S/830 II<br>DS50 62P | 2,769 lm | -                | Distribution symmetrical 50 |
| 86491000   | BDP260 LED39-4S/740 II<br>DS50 62P | 2,808 lm | -                | Distribution symmetrical 50 |
| 86492700   | BDP260 LED39-4S/830 II<br>DM10 62P | 2,769 lm | -                | Distribution medium 10      |
| 86493400   | BDP260 LED39-4S/740 II<br>DM10 62P | 2,808 lm | -                | Distribution medium 10      |
| 86494100   | BDP260 LED39-4S/830 II<br>DW10 62P | 2,925 lm | -                | Distribution wide 10        |

TownTune Central Post-Top

| Order Code | Full Product Name               | Luminous Flux | Number of light sources | Optic type outdoor          |
|------------|---------------------------------|---------------|-------------------------|-----------------------------|
| 86496500   | BDP260 LED50-4S/830 II DS50 62P | 3,500 lm      | -                       | Distribution symmetrical 50 |
| 86497200   | BDP260 LED50-4S/740 II DS50 62P | 3,550 lm      | -                       | Distribution symmetrical 50 |
| 86498900   | BDP260 LED50-4S/830 II DM10 62P | 3,500 lm      | -                       | Distribution medium 10      |
| 86499600   | BDP260 LED50-4S/740 II DM10 62P | 3,550 lm      | -                       | Distribution medium 10      |
| 86500900   | BDP260 LED50-4S/830 II DW10 62P | 3,700 lm      | -                       | Distribution wide 10        |
| 86501600   | BDP260 LED50-4S/740 II DW10 62P | 3,750 lm      | -                       | Distribution wide 10        |
| 86502300   | BDP260 LED74-4S/830 II DS50 62P | 5,106 lm      | -                       | Distribution symmetrical 50 |
| 86503000   | BDP260 LED74-4S/740 II DS50 62P | 5,254 lm      | -                       | Distribution symmetrical 50 |

Operating and Electrical

| Order Code | Full Product Name                       | Power Consumption |
|------------|-----------------------------------------|-------------------|
| 88449900   | BDP260 LED35-4S/740 PSU II DS50 CLO 62P | 21.5 W            |
| 49024900   | BDP260 LED39-4S/830 DM50 CLO DDF3 62P   | 30 W              |
| 49028700   | BDP260 LED14-4S/740 DW10 CLO SRTB 76P   | 9.3 W             |
| 49455100   | BDP260 LED35-4S/830 DW50 62P            | 27.5 W            |
| 49456800   | BDP260 LED79-4S/740 DM30 62P            | 46 W              |
| 86490300   | BDP260 LED39-4S/830 II DS50 62P         | 31 W              |
| 86491000   | BDP260 LED39-4S/740 II DS50 62P         | 24 W              |
| 86492700   | BDP260 LED39-4S/830 II DM10 62P         | 31 W              |
| 86493400   | BDP260 LED39-4S/740 II DM10 62P         | 24 W              |
| 86494100   | BDP260 LED39-4S/830 II DW10 62P         | 31 W              |
| 86496500   | BDP260 LED50-4S/830 II DS50 62P         | 40.5 W            |
| 86497200   | BDP260 LED50-4S/740 II DS50 62P         | 31 W              |
| 86498900   | BDP260 LED50-4S/830 II DM10 62P         | 40.5 W            |

Controls and Dimming

| Order Code | Full Product Name                       | Dimmable |
|------------|-----------------------------------------|----------|
| 88449900   | BDP260 LED35-4S/740 PSU II DS50 CLO 62P | Yes      |
| 49024900   | BDP260 LED39-4S/830 DM50 CLO DDF3 62P   | Yes      |
| 49028700   | BDP260 LED14-4S/740 DW10 CLO SRTB 76P   | Yes      |
| 49455100   | BDP260 LED35-4S/830 DW50 62P            | No       |
| 49456800   | BDP260 LED79-4S/740 DM30 62P            | No       |
| 86490300   | BDP260 LED39-4S/830 II DS50 62P         | No       |
| 86491000   | BDP260 LED39-4S/740 II DS50 62P         | No       |
| 86492700   | BDP260 LED39-4S/830 II DM10 62P         | No       |
| 86493400   | BDP260 LED39-4S/740 II DM10 62P         | No       |
| 86494100   | BDP260 LED39-4S/830 II DW10 62P         | No       |
| 86496500   | BDP260 LED50-4S/830 II DS50 62P         | No       |
| 86497200   | BDP260 LED50-4S/740 II DS50 62P         | No       |

| Order Code | Full Product Name                        | Luminous Flux | Number of light sources | Optic type outdoor          |
|------------|------------------------------------------|---------------|-------------------------|-----------------------------|
| 86504700   | BDP260 LED74-4S/830 II DM10 62P          | 5,106 lm      | -                       | Distribution medium 10      |
| 86505400   | BDP260 LED74-4S/740 II DM10 62P          | 5,254 lm      | -                       | Distribution medium 10      |
| 86506100   | BDP260 LED74-4S/830 II DW10 62P          | 5,402 lm      | -                       | Distribution wide 10        |
| 86507800   | BDP260 LED74-4S/740 II DW10 62P          | 5,550 lm      | -                       | Distribution wide 10        |
| 87861000   | BDP260 LED35-4S/830 PSU II DS50 CLO 62P  | 2,448 lm      | 20                      | Distribution symmetrical 50 |
| 89449800   | BDP260 LED100/740 PSR II DS50 PCC DGR 62 | 6,900 lm      | 40                      | Distribution symmetrical 50 |
| 89450400   | BDP260 LED100/740 PSR II DS50 PCC DGR 76 | 6,900 lm      | 40                      | Distribution symmetrical 50 |
| 21432300   | BDP260 LED69-4S/740 PSDD II DS50 DGR DF2 | 4,970 lm      | 40                      | Distribution symmetrical 50 |

| Order Code | Full Product Name                        | Power Consumption |
|------------|------------------------------------------|-------------------|
| 86499600   | BDP260 LED50-4S/740 II DM10 62P          | 31 W              |
| 86500900   | BDP260 LED50-4S/830 II DW10 62P          | 40.5 W            |
| 86501600   | BDP260 LED50-4S/740 II DW10 62P          | 31 W              |
| 86502300   | BDP260 LED74-4S/830 II DS50 62P          | 56 W              |
| 86503000   | BDP260 LED74-4S/740 II DS50 62P          | 43 W              |
| 86504700   | BDP260 LED74-4S/830 II DM10 62P          | 56 W              |
| 86505400   | BDP260 LED74-4S/740 II DM10 62P          | 43 W              |
| 86506100   | BDP260 LED74-4S/830 II DW10 62P          | 56 W              |
| 86507800   | BDP260 LED74-4S/740 II DW10 62P          | 43 W              |
| 87861000   | BDP260 LED35-4S/830 PSU II DS50 CLO 62P  | 26.5 W            |
| 89449800   | BDP260 LED100/740 PSR II DS50 PCC DGR 62 | 59 W              |
| 89450400   | BDP260 LED100/740 PSR II DS50 PCC DGR 76 | 59 W              |
| 21432300   | BDP260 LED69-4S/740 PSDD II DS50 DGR DF2 | 40.5 W            |

| Order Code | Full Product Name                        | Dimmable |
|------------|------------------------------------------|----------|
| 86498900   | BDP260 LED50-4S/830 II DM10 62P          | No       |
| 86499600   | BDP260 LED50-4S/740 II DM10 62P          | No       |
| 86500900   | BDP260 LED50-4S/830 II DW10 62P          | No       |
| 86501600   | BDP260 LED50-4S/740 II DW10 62P          | No       |
| 86502300   | BDP260 LED74-4S/830 II DS50 62P          | No       |
| 86503000   | BDP260 LED74-4S/740 II DS50 62P          | No       |
| 86504700   | BDP260 LED74-4S/830 II DM10 62P          | No       |
| 86505400   | BDP260 LED74-4S/740 II DM10 62P          | No       |
| 86506100   | BDP260 LED74-4S/830 II DW10 62P          | No       |
| 86507800   | BDP260 LED74-4S/740 II DW10 62P          | No       |
| 87861000   | BDP260 LED35-4S/830 PSU II DS50 CLO 62P  | Yes      |
| 89449800   | BDP260 LED100/740 PSR II DS50 PCC DGR 62 | Yes      |

## TownTune Central Post-Top

| Order Code | Full Product Name                        | Dimmable |
|------------|------------------------------------------|----------|
| 89450400   | BDP260 LED100/740 PSR II DS50 PCC DGR 76 | Yes      |


| Order Code | Full Product Name                        | Dimmable |
|------------|------------------------------------------|----------|
| 21432300   | BDP260 LED69-4S/740 PSDD II DS50 DGR DF2 | Yes      |

### Over Time Performance (IEC Compliant)


| Order Code | Full Product Name                       | Driver failure rate at 5000 h |
|------------|-----------------------------------------|-------------------------------|
| 88449900   | BDP260 LED35-4S/740 PSU II DS50 CLO 62P | 0.5 %                         |
| 49024900   | BDP260 LED39-4S/830 DM50 CLO DDF3 62P   | 0.5 %                         |
| 49028700   | BDP260 LED14-4S/740 DW10 CLO SRTB 76P   | 0.5 %                         |
| 49455100   | BDP260 LED35-4S/830 DW50 62P            | 0.5 %                         |
| 49456800   | BDP260 LED79-4S/740 DM30 62P            | 0.5 %                         |
| 86490300   | BDP260 LED39-4S/830 II DS50 62P         | 0.5 %                         |
| 86491000   | BDP260 LED39-4S/740 II DS50 62P         | 0.5 %                         |
| 86492700   | BDP260 LED39-4S/830 II DM10 62P         | 0.5 %                         |
| 86493400   | BDP260 LED39-4S/740 II DM10 62P         | 0.5 %                         |
| 86494100   | BDP260 LED39-4S/830 II DW10 62P         | 0.5 %                         |
| 86496500   | BDP260 LED50-4S/830 II DS50 62P         | 0.5 %                         |
| 86497200   | BDP260 LED50-4S/740 II DS50 62P         | 0.5 %                         |
| 86498900   | BDP260 LED50-4S/830 II DM10 62P         | 0.5 %                         |

| Order Code | Full Product Name                        | Driver failure rate at 5000 h |
|------------|------------------------------------------|-------------------------------|
| 86499600   | BDP260 LED50-4S/740 II DM10 62P          | 0.5 %                         |
| 86500900   | BDP260 LED50-4S/830 II DW10 62P          | 0.5 %                         |
| 86501600   | BDP260 LED50-4S/740 II DW10 62P          | 0.5 %                         |
| 86502300   | BDP260 LED74-4S/830 II DS50 62P          | 0.5 %                         |
| 86503000   | BDP260 LED74-4S/740 II DS50 62P          | 0.5 %                         |
| 86504700   | BDP260 LED74-4S/830 II DM10 62P          | 0.5 %                         |
| 86505400   | BDP260 LED74-4S/740 II DM10 62P          | 0.5 %                         |
| 86506100   | BDP260 LED74-4S/830 II DW10 62P          | 0.5 %                         |
| 86507800   | BDP260 LED74-4S/740 II DW10 62P          | 0.5 %                         |
| 87861000   | BDP260 LED35-4S/830 PSU II DS50 CLO 62P  | 0.5 %                         |
| 89449800   | BDP260 LED100/740 PSR II DS50 PCC DGR 62 | 0.5 %                         |
| 89450400   | BDP260 LED100/740 PSR II DS50 PCC DGR 76 | 0.5 %                         |
| 21432300   | BDP260 LED69-4S/740 PSDD II DS50 DGR DF2 | -                             |


### Polar Wide Diagrams




Polar Normal (separate) - BDP260I - 912300024155




Polar Normal (separate) - BDP260I - 912300024159




Polar Normal (separate) - BDP260I - 912300024404



Polar Normal (separate) - BDP260I - 912300024479




Polar Normal (separate) - BDP260I - 912300024173




Polar Normal (separate) - BDP260I - 912300024172


Polar Wide Diagrams




Polar Normal (separate) - BDP260I - 912300024255




Polar Normal (separate) - BDP260I - 912300024253




Polar Normal (separate) - BDP260I - 912300024257




Polar Normal (separate) - BDP260I - 912300024254




Polar Normal (separate) - BDP260I - 912300024262




Polar Normal (separate) - BDP260I - 912300024259



Polar Normal (separate) - BDP260I - 912300024263




Polar Normal (separate) - BDP260I - 912300024264




Polar Normal (separate) - BDP260I - 912300024260


Polar Wide Diagrams




Polar Normal (separate) - BDP260I - 912300024261




Polar Normal (separate) - BDP260I - 912300024265




Polar Normal (separate) - BDP260I - 912300024267




Polar Normal (separate) - BDP260I - 912300024268




Polar Normal (separate) - BDP260I - 912300024270




Polar Normal (separate) - BDP260I - 912300024269



Polar Normal (separate) - BDP260I - 912300024266




Polar Normal (separate) - BDP260I - 912300024564




Polar Normal (separate) - BDP260I - 912300024565

Polar Wide Diagrams



Polar Normal (separate) - BDP260I - 912300024873



Polar Normal (separate) - BDP260I - 912300024256

