



# **Jargeau LED gen3: combining historical design with modern lighting technology**

## **Jargeau LED gen3**

Jargeau LED gen3 combines the iconic character of the first four-sided street lamps of the 19th century with the technical performance of 21st-century luminaires.

Thanks to the energy-efficient LEDGINE-O engine, and wide range of high performance, application-tailored optics, Jargeau LED gen3 delivers the right amount light in the right direction on roads and streets, as well as offering excellent energy savings. Designed for installation at heights of four to six meters, this street lantern is well suited to urban landscapes and is ideal for illuminating city centers, historical areas, old villages, streets, alleys, squares and parks. Jargeau LED gen3 is also future ready with a choice of one or two Signify System Ready (SR) sockets that enable the luminaire to be paired with both standalone and advanced control and lighting software applications such as Interact from Signify. This urban lighting solution can also be equipped with our dedicated light recipe that preserves dark skies. In addition, every Jargeau LED gen3 luminaire is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programing operations faster and easier, and enables you to create a digital library of lighting assets and spare parts.

# Jargeau LED gen3

## Benefits

- Iconic luminaire for contemporary and historical environments
- Covers a wide range of applications for roads and streets with different geometries
- Future-proof thanks to SR socket compatible with all standard and advanced lighting controls
- Service tag for easy installation and maintenance

## Features

- Historical shape
- Large choice of different beams, internal louvers to minimize glare
- Variety of mounting options: luminaire can be combined with different columns, brackets and multiple-arm brackets

## Application



- Main urban roads and streets, side and residential roads and streets
- City centers and historical areas
- Cycle and pedestrian paths, squares, parks and playgrounds

## Versions




BDP768 BDP651 without spigot RET

## Dimensional drawing



# Jargeau LED gen3

## Dimensional drawing



General Information			General Information		
Driver included	Yes		Order Code	Full Product Name	Lamp family code
Light source replaceable	Yes		912300024529	BDP651 LED50/830 II DM50 MK-BK PCC BALL	LED50
Number of gear units	1 unit		912300024426	BSP651 LW LED50/830 II DM50 MK-BK PCC BA	LED50
Service tag	Yes		912300060160	BSP651 LED50/830 II DM50 MK-BK FG BALL 3	LED50
			912300060161	BSP651 LED50/830 II DM50 MK-BK GF BALL 3	LED50
			912300060162	BSP651 LED50/830 II DM50 MK-WH FG BALL 3	LED50
			912300060163	BSP651 LED50/830 II DM50 MK-WH GF BALL 3	LED50
			912300060275	BSP651 LED50/830 II DM50 MK-WH PCC BALL	LED50
			912300024425	BDP651 LW LED50/830 II DM50 MK-BK PCC BA	LED50
			912300060156	BDP651 LED50/830 II DM50 MK-BK FG BALL 6	LED50
			912300060157	BDP651 LED50/830 II DM50 MK-BK GF BALL 6	LED50
			912300060158	BDP651 LED50/830 II DM50 MK-WH FG BALL 6	LED50
			912300060159	BDP651 LED50/830 II DM50 MK-WH GF BALL 6	LED50
			912300060274	BDP651 LED50/830 II DM50 MK-WH PCC BALL	LED50
			912300060296	BDP651 LED40-4S/830 PSD-SR II DS50 FG BK	LED40
			912300060297	BDP651 LED55-4S/830 PSD-SR II DS50 FG BK	LED55
			912300060298	BDP651 LED40-4S/830 PSD-SR II DS50 GF BK	LED40
			912300060299	BDP651 LED55-4S/830 PSD-SR II DS50 GF BK	LED55
Light Technical			Mechanical and Housing		
Light source color	830 warm white		Housing Color	Black	
Correlated Color Temperature (Nom)	3000 K		Mech. impact protection code	IK09	
Color rendering index (CRI)	80		Ingress protection code	IP66	
			Standard tilt angle side entry	-	
			Standard tilt angle posttop	-	
Approval and Application			Approval and Application		
CE mark	Yes		CE mark	Yes	
Flammability mark	-		Flammability mark	-	

## Light Technical

Order Code	Full Product	Luminaire			Upward light output	Order Code	Full Product	Luminaire			Upward light output
		Name	light beam spread	Luminous Flux	Optic type outdoor			Name	light beam spread	Luminous Flux	
912300024529	BDP651 LED50/830 II	30° - 5° x 153°	3,250 lm	Distribution medium 50	0.01	DM50 MK-BK PCC BALL					

## Jargeau LED gen3

Order Code	Full Product Name	Luminaire				Upward light output
		light beam spread	Luminous Flux	Optic type outdoor	ratio	
912300024426	BSP651 LW	30° - 5° x	3,250 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK					
	PCC BA					
912300060160	BSP651	30° - 5° x	3,450 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK FG					
	BALL 3					
912300060161	BSP651	30° - 5° x	3,100 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK GF					
	BALL 3					
912300060162	BSP651	30° - 5° x	3,700 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	FG BALL 3					
912300060163	BSP651	30° - 5° x	3,250 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	GF BALL 3					
912300060275	BSP651	30° - 5° x	3,400 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	PCC BALL					
912300024425	BDP651 LW	30° - 5° x	3,250 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK					
	PCC BA					
912300060156	BDP651	30° - 5° x	3,450 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK FG					
	BALL 6					

Order Code	Full Product	Luminaire				Upward light output
		light beam spread	Luminous Flux	Optic type outdoor	ratio	
912300060157	BDP651	30° - 5° x	3,100 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-BK GF					
	BALL 6					
912300060158	BDP651	30° - 5° x	3,700 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	FG BALL 6					
912300060159	BDP651	30° - 5° x	3,250 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	GF BALL 6					
912300060274	BDP651	30° - 5° x	3,400 lm	Distribution	0.01	
	LED50/830 II	153°		medium 50		
	DM50 MK-WH					
	PCC BALL					
912300060296	BDP651	152° x 155°	2,760 lm	Distribution	0	
	LED40-4S/830			symmetrical		
	PSD-SR II DS50			50		
	FG BK					
912300060297	BDP651	152° x 155°	3,808 lm	Distribution	0	
	LED55-4S/830			symmetrical		
	PSD-SR II DS50			50		
	FG BK					
912300060298	BDP651	152° x 155°	2,400 lm	Distribution	0	
	LED40-4S/830			symmetrical		
	PSD-SR II DS50			50		
	GF BK					
912300060299	BDP651	152° x 155°	3,360 lm	Distribution	0	
	LED55-4S/830			symmetrical		
	PSD-SR II DS50			50		
	GF BK					

### Operating and Electrical

Order Code	Full Product Name	Power Consumption		
912300024529	BDP651 LED50/830 II DM50 MK-BK PCC BALL	38 W		
912300024426	BSP651 LW LED50/830 II DM50 MK-BK PCC BA	38 W		
912300060160	BSP651 LED50/830 II DM50 MK-BK FG BALL 3	38 W		
912300060161	BSP651 LED50/830 II DM50 MK-BK GF BALL 3	38 W		
912300060162	BSP651 LED50/830 II DM50 MK-WH FG BALL 3	38 W		
912300060163	BSP651 LED50/830 II DM50 MK-WH GF BALL 3	38 W		
912300060275	BSP651 LED50/830 II DM50 MK-WH PCC BALL	38 W		
912300024425	BDP651 LW LED50/830 II DM50 MK-BK PCC BA	38 W		
912300060156	BDP651 LED50/830 II DM50 MK-BK FG BALL 6	38 W		

Order Code	Full Product Name	Power Consumption		
912300060157	BDP651 LED50/830 II DM50 MK-BK GF BALL 6	38 W		
912300060158	BDP651 LED50/830 II DM50 MK-WH FG BALL 6	38 W		
912300060159	BDP651 LED50/830 II DM50 MK-WH GF BALL 6	38 W		
912300060274	BDP651 LED50/830 II DM50 MK-WH PCC BALL	38 W		
912300060296	BDP651 LED40-4S/830 PSD-SR II DS50 FG BK	30.5 W		
912300060297	BDP651 LED55-4S/830 PSD-SR II DS50 FG BK	42 W		
912300060298	BDP651 LED40-4S/830 PSD-SR II DS50 GF BK	30.5 W		
912300060299	BDP651 LED55-4S/830 PSD-SR II DS50 GF BK	42 W		

### Controls and Dimming

## Jargeau LED gen3

Order Code	Full Product Name	Dimmable
912300024529	BDP651 LED50/830 II DM50 MK-BK PCC BALL	No
912300024426	BSP651 LW LED50/830 II DM50 MK-BK PCC BA	No
912300060160	BSP651 LED50/830 II DM50 MK-BK FG BALL 3	No
912300060161	BSP651 LED50/830 II DM50 MK-BK GF BALL 3	No
912300060162	BSP651 LED50/830 II DM50 MK-WH FG BALL 3	No
912300060163	BSP651 LED50/830 II DM50 MK-WH GF BALL 3	No
912300060275	BSP651 LED50/830 II DM50 MK-WH PCC BALL	No
912300024425	BDP651 LW LED50/830 II DM50 MK-BK PCC BA	No
912300060156	BDP651 LED50/830 II DM50 MK-BK FG BALL 6	No

Order Code	Full Product Name	Dimmable
912300060157	BDP651 LED50/830 II DM50 MK-BK GF BALL 6	No
912300060158	BDP651 LED50/830 II DM50 MK-WH FG BALL 6	No
912300060159	BDP651 LED50/830 II DM50 MK-WH GF BALL 6	No
912300060274	BDP651 LED50/830 II DM50 MK-WH PCC BALL	No
912300060296	BDP651 LED40-4S/830 PSD-SR II DS50 FG BK	Yes
912300060297	BDP651 LED55-4S/830 PSD-SR II DS50 FG BK	Yes
912300060298	BDP651 LED40-4S/830 PSD-SR II DS50 GF BK	Yes
912300060299	BDP651 LED55-4S/830 PSD-SR II DS50 GF BK	Yes

### Mechanical and Housing

Order Code	Full Product Name	Optical cover type
912300024529	BDP651 LED50/830 II DM50 MK-BK PCC BALL	Polycarbonate bowl/ cover clear
912300024426	BSP651 LW LED50/830 II DM50 MK-BK PCC BA	Polycarbonate bowl/ cover clear
912300060160	BSP651 LED50/830 II DM50 MK-BK FG BALL 3	Flat glass
912300060161	BSP651 LED50/830 II DM50 MK-BK GF BALL 3	Glass frosted
912300060162	BSP651 LED50/830 II DM50 MK-WH FG BALL 3	Flat glass
912300060163	BSP651 LED50/830 II DM50 MK-WH GF BALL 3	Glass frosted
912300060275	BSP651 LED50/830 II DM50 MK-WH PCC BALL	Polycarbonate bowl/ cover clear
912300024425	BDP651 LW LED50/830 II DM50 MK-BK PCC BA	Polycarbonate bowl/ cover clear
912300060156	BDP651 LED50/830 II DM50 MK-BK FG BALL 6	Flat glass

Order Code	Full Product Name	Optical cover type
912300060157	BDP651 LED50/830 II DM50 MK-BK GF BALL 6	Glass frosted
912300060158	BDP651 LED50/830 II DM50 MK-WH FG BALL 6	Flat glass
912300060159	BDP651 LED50/830 II DM50 MK-WH GF BALL 6	Glass frosted
912300060274	BDP651 LED50/830 II DM50 MK-WH PCC BALL	Polycarbonate bowl/ cover clear
912300060296	BDP651 LED40-4S/830 PSD-SR II DS50 FG BK	Flat glass
912300060297	BDP651 LED55-4S/830 PSD-SR II DS50 FG BK	Flat glass
912300060298	BDP651 LED40-4S/830 PSD-SR II DS50 GF BK	Glass frosted
912300060299	BDP651 LED55-4S/830 PSD-SR II DS50 GF BK	Glass frosted


### Product Data

Order Code	Full Product Name	Product family code
912300024529	BDP651 LED50/830 II DM50 MK-BK PCC BALL	BDP651
912300024426	BSP651 LW LED50/830 II DM50 MK-BK PCC BA	BSP651
912300060160	BSP651 LED50/830 II DM50 MK-BK FG BALL 3	BSP651
912300060161	BSP651 LED50/830 II DM50 MK-BK GF BALL 3	BSP651
912300060162	BSP651 LED50/830 II DM50 MK-WH FG BALL 3	BSP651
912300060163	BSP651 LED50/830 II DM50 MK-WH GF BALL 3	BSP651
912300060275	BSP651 LED50/830 II DM50 MK-WH PCC BALL	BSP651
912300024425	BDP651 LW LED50/830 II DM50 MK-BK PCC BA	BDP651
912300060156	BDP651 LED50/830 II DM50 MK-BK FG BALL 6	BDP651


Order Code	Full Product Name	Product family code
912300060157	BDP651 LED50/830 II DM50 MK-BK GF BALL 6	BDP651
912300060158	BDP651 LED50/830 II DM50 MK-WH FG BALL 6	BDP651
912300060159	BDP651 LED50/830 II DM50 MK-WH GF BALL 6	BDP651
912300060274	BDP651 LED50/830 II DM50 MK-WH PCC BALL	BDP651
912300060296	BDP651 LED40-4S/830 PSD-SR II DS50 FG BK	BDP651
912300060297	BDP651 LED55-4S/830 PSD-SR II DS50 FG BK	BDP651
912300060298	BDP651 LED40-4S/830 PSD-SR II DS50 GF BK	BDP651
912300060299	BDP651 LED55-4S/830 PSD-SR II DS50 GF BK	BDP651

# Jargeau LED gen3


## Polar Wide Diagrams




Polar Normal (separate) - BDP768I -  
912300024425




Polar Normal (separate) - BDP768I -  
912300024426




Polar Normal (separate) - BDP768I -  
912300024529




Polar Normal (separate) - BDP768I -  
912300060274




Polar Normal (separate) - BDP768I -  
912300060157




Polar Normal (separate) - BDP768I -  
912300060159



Polar Normal (separate) - BDP768I -  
912300060156




Polar Normal (separate) - BDP768I -  
912300060158




Polar Normal (separate) - BDP768I -  
912300060160

# Jargeau LED gen3


## Polar Wide Diagrams




Polar Normal (separate) - BDP768I -  
912300060161




Polar Normal (separate) - BDP768I -  
912300060163




Polar Normal (separate) - BDP768I -  
912300060162




Polar Normal (separate) - BDP768I -  
912300060275




Polar Normal (separate) - BDP768I -  
912300060296



Polar Normal (separate) - BDP768I -  
912300060297



Polar Normal (separate) - BDP768I -  
912300060298



Polar Normal (separate) - BDP768I -  
912300060299

