



## CityCharm: combining visual comfort and performance

The CityCharm range is designed for use in urban areas where comfortable lighting, ambience, and design play an important role. It offers three iconic, timeless designs: CityCharm cordoba (BDS490), CityCharm cone (BDS491), and CityCharm fluid (BDS492) along with a range of decorative and practical accessories. This enables you to create a lighting solution that carries the signature of your municipality, both by day and by night. Whether you specify cordoba, cone or fluid LED lights, CityCharm provides high visual comfort while maintaining excellent performance. It offers a choice of two innovative Lighting technologies: GentleBeam, which maximizes visual comfort, or ClearGuide (cordoba or cone), which optimizes vertical illumination and visual guidance. To personalize your CityCharm lighting solution further, decorative accessories for this range make it possible to define the volume of the bowl and change its appearance. A variety of dedicated brackets and masts are also available to

enable you to reshape your residential areas and city centers in the most elegant way imaginable.

## Benefits

- Elegant, iconic range enhanced by dedicated poles and brackets to create distinctive styles
- Comfortable lighting with GentleBeam or ClearGuide technologies
- Multiple geometries for visual comfort in all urban spaces
- Excellent lighting performance, high-quality finishing
- Future-ready with Zhaga-D4i system ready (SR) top socket to connect with Interact controls
- Service tag for easy installation and maintenance

## Applications

- Residential
- Footpaths and cycle lanes
- Parks and boulevards

## Versions




CityCharm Cone with grey decorative bowl

## Features

- Choice of luminaire shapes, color effects, poles and brackets
- Diffusing tools for visual comfort, colored inserts to enhance ambiance
- Wide range of lumen outputs and optics for maximum efficiency at all lighting levels
- Choice of color temperatures and color rendering for different ambiances: 2200K, 2700K, 3000K and 4000K
- Efficacy up to 144 lm/W
- Cordoba and fluid versions available with ULR < 1%
- Lifetime up to 100,000 hours @L96 B10
- 5-year standard warranty (option to extend up to 10 years)

## Dimensional drawing



CityCharm Cone - LED module 7000 lm - LED - 830 warm white - Power supply unit regulating - 220 to 240 V - 50 to 60 Hz - Safety class I - Symmetrical - Polycarbonate bowl/cover - Gray - Luminaire surge protection level until 6 kV differential mode and 8 kV common mode - Cable 0.2 m without plug - Spigot for diameter 60 mm

### General Information

Lamp family code	LED70 [LED module 7000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

### Light Technical

Upward light output ratio	0.0136
Luminous Flux	5,670 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Light source color	830 warm white
Luminaire light beam spread	360°
Optic type outdoor	Symmetrical

## Operating and Electrical

Power Consumption	53 W
Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode

## Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Color	Gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Polycarbonate bowl/cover


## Approval and Application

Flammability mark	-
CE mark	Yes

## Product Data

Product family code	BDS491 [CITYCHARM CONE]
---------------------	-------------------------

## Polar normal diagrams



BDS490I - 912300024687

