



Versatile and cost-efficient LED lighting

ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay Gen2 significantly improves the most important aspects of the street lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

Benefits

- A range of benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information

Applications

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads
- Parking lots

Features

- One flexible design that offers different options depending on application needs

- Includes a dedicated light recipe that preserves dark night skies
- Compact and efficient design
- Tilt regulation with no need to open the cover

Versions

ClearWay gen2 Performer-BGP307




ClearWay gen2 Core-BGP307



Clearway gen2



Dimensional drawing



BGP307 LED54-4S/740 I DM50 48/60S

BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Upward light output ratio 0

Operating and Electrical

Surge Protection (Common/Differential) Surge protection level until 6 kV differential mode and 8 kV common mode

Mechanical and Housing

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK09 [10 J]

Standard tilt angle posttop 0°

Standard tilt angle side entry 0°

Optical cover type Flat glass

Approval and Application

Flammability mark -

CE mark Yes

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h 0.5 %

Product Data

Product family code BGP307 [CLEARWAY GEN2]

General Information

Order Code	Full Product Name	Lamp family code	Driver included
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	LED18	Yes
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	LED25	Yes
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	LED30	Yes
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	LED35	Yes
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	LED40	Yes
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	LED45	Yes
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	LED54	Yes
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	LED69	Yes
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	LED84	Yes
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	LED99	Yes
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	LED109	Yes

Order Code	Full Product Name	Lamp family code	Driver included
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	LED120	Yes
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	LED18	Yes
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	LED25	Yes
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	LED30	Yes
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	LED35	Yes
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	LED40	Yes
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	LED45	Yes
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	LED54	Yes
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	LED69	Yes
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	LED84	Yes
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	LED99	Yes
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	LED109	Yes
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	LED120	Yes
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	LED18	Yes
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	LED30	Yes
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	LED35	Yes
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	LED54	Yes
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	LED69	Yes
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	LED120	Yes
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	LED18	Yes
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	LED35	Yes
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	LED69	Yes
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	LED120	Yes
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	LED25	Yes
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	LED25	Yes
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	LED25	Yes
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	LED25	Yes
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	LED25	Yes
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	LED54	Yes
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	LED25	Yes
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	LED18	Yes
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	LED25	Yes
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	LED35	Yes
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	LED45	Yes
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	LED54	Yes
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	LED18	Yes
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	LED25	Yes
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	LED35	Yes
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	LED45	Yes
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	LED54	Yes

Order Code	Full Product Name	Lamp family code	Driver included
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	LED18	Yes
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	LED25	Yes
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	LED35	Yes
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	LED45	Yes
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	LED54	Yes
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	LED18	Yes
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	LED25	Yes
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	LED35	Yes
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	LED45	Yes
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	LED54	Yes
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	LED18	Yes
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	LED25	Yes
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	LED35	Yes
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	LED45	Yes
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	LED54	Yes
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	LED18	Yes
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	LED25	Yes
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	LED35	Yes
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	LED45	Yes
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	LED54	Yes
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	LED69	Yes
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	LED84	Yes
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	LED99	Yes
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	LED109	Yes
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	LED120	Yes
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	LED69	Yes
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	LED84	Yes
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	LED99	Yes
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	LED109	Yes
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	LED120	Yes
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	LED69	Yes
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	LED84	Yes
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	LED99	Yes
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	LED109	Yes
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	LED120	Yes
910925865352	BGP307 LED35/740 II DM11 CLL C10	LED35	Yes
910925865374	BGP307 LED45/740 II DM11 CLL C10	LED45	Yes
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	LED45	Yes
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	LED54	Yes
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	LED18	Yes

Order Code	Full Product Name	Lamp family code	Driver included
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	LED25	Yes
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	LED35	Yes
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	LED45	Yes
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	LED54	Yes
910925865405	BGP307 LED69/740 II DM11 C10	LED69	Yes
910925865406	BGP307 LED84/740 II DM11 C10	LED84	Yes
910925865407	BGP307 LED99/740 II DM11 C10	LED99	Yes
910925865408	BGP307 LED109/740 II DM11 C10	LED109	Yes
910925865409	BGP307 LED120/740 II DM11 C10	LED120	Yes
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	LED69	Yes
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	LED84	Yes
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	LED99	Yes
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	LED109	Yes
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	LED120	Yes
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	LED69	Yes
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	LED84	Yes
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	LED99	Yes
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	LED109	Yes
910925865419	BGP307 LED25/740 II DM11 CLL C10	LED25	Yes
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	LED120	Yes
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	LED54	Yes
910925865690	BGP307 LED18/830 II DM11 SR C10	LED18	Yes
910925865691	BGP307 LED54/830 II DM11 SRT C10	LED54	Yes
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	LED18	Yes
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	LED54	Yes
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	LED18	Yes
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	LED54	Yes
910925865696	BGP307 LED18/740 II DM11 SR C10	LED18	Yes
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	LED18	Yes
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	LED18	Yes
910925865699	BGP307 LED69/740 II DM11 SR C10	LED69	Yes
910925865701	BGP307 LED84/740 II DM11 SR C10	LED84	Yes
910925865702	BGP307 LED99/740 II DM11 SR C10	LED99	Yes
910925865703	BGP307 LED109/740 II DM11 SR C10	LED109	Yes
910925865704	BGP307 LED120/740 II DM11 SR C10	LED120	Yes
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	LED69	Yes
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	LED84	Yes
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	LED99	Yes
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	LED109	Yes
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	LED120	Yes

Order Code	Full Product Name	Lamp family code	Driver included
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	LED69	Yes
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	LED84	Yes
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	LED99	Yes
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	LED109	Yes
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	LED120	Yes
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	LED35	Yes
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	LED45	Yes
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	LED45	Yes
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	LED69	Yes
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	LED69	Yes
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	LED84	Yes
910925865378	BGP307 LED54/740 II DM11 C10	LED54	Yes
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	LED18	Yes
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	LED54	Yes
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	LED18	Yes
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	LED54	Yes
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	LED18	Yes
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	LED25	Yes
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	LED35	Yes
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	LED45	Yes
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	LED54	Yes
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	LED18	Yes
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	LED25	Yes
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	LED54	Yes
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	LED130	Yes
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	LED25	No
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	LED25	Yes
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	LED25	No
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	LED25	Yes
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	LED25	No
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	LED25	Yes
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	LED25	No
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	LED25	Yes
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	LED35	Yes
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	LED35	Yes
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	LED35	Yes
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	LED35	Yes
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	LED35	Yes
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	LED35	Yes
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	LED35	Yes

Order Code	Full Product Name	Lamp family code	Driver included
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	LED35	Yes
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	LED45	Yes
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	LED45	Yes
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	LED45	Yes
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	LED45	Yes
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	LED54	Yes
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	LED54	Yes
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	LED54	Yes
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	LED54	Yes
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	LED69	Yes
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	LED69	Yes
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	LED69	Yes
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	LED69	Yes
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	LED99	Yes
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	LED99	Yes
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	LED99	Yes
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	LED99	Yes
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	LED120	Yes
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	LED45	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	1,584 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	2,175 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	2,610 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	3,080 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	3,520 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	3,960 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	4,698 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	6,160 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	7,308 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	8,600 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	9,460 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	10,200 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	1,584 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	2,175 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	2,610 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	3,080 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	3,520 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	3,960 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	4,698 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	6,160 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	7,308 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	8,600 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	9,460 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	10,200 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	1,584 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	2,610 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	3,080 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	4,698 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	6,160 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	10,200 lm	4000 K	70	740 neutral white	154° - 31° x 54°	Distribution medium 50
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	1,566 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	3,045 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	6,090 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	10,200 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	2,958 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	3,741 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	2,958 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3,741 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	2,088 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	2,958 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3,741 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	2,958 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	2,958 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	2,958 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865244	BGP307 LED120-4S/740 II DM11 CLO-48/60S	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865352	BGP307 LED35/740 II DM11 CLL C10	3,045 lm	4000 K	70	740 neutral white	-	Distribution medium 11
910925865374	BGP307 LED45/740 II DM11 CLL C10	3,915 lm	4000 K	70	740 neutral white	-	Distribution medium 11
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	2,958 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865405	BGP307 LED69/740 II DM11 C10	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865406	BGP307 LED84/740 II DM11 C10	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865407	BGP307 LED99/740 II DM11 C10	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865408	BGP307 LED109/740 II DM11 C10	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865409	BGP307 LED120/740 II DM11 C10	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865419	BGP307 LED25/740 II DM11 CLL C10	2,175 lm	3000 K	80	740 neutral white	61° x 150°	Distribution medium 11
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865690	BGP307 LED18/830 II DM11 SR C10	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865691	BGP307 LED54/830 II DM11 SRT C10	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865696	BGP307 LED18/740 II DM11 SR C10	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865699	BGP307 LED69/740 II DM11 SR C10	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865701	BGP307 LED84/740 II DM11 SR C10	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865702	BGP307 LED99/740 II DM11 SR C10	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865703	BGP307 LED109/740 II DM11 SR C10	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865704	BGP307 LED120/740 II DM11 SR C10	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	5,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	7,134 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	8,256 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	9,030 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	9,775 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	2,958 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	3,780 lm	4000 K	70	740 neutral white	-	Distribution extra wide 10
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	5,880 lm	4000 K	70	740 neutral white	-	Distribution extra wide 10
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	5,880 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution extra wide 10

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	6,972 lm	4000 K	70	740 neutral white	152° - 25° x 66°	Distribution extra wide 10
910925865378	BGP307 LED54/740 II DM11 C10	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	1,522.5 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	4,524 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 11
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	2,958 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	3,828 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	1,522.5 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	2,088 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4,524 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	10,920 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 11
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	2,136 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	2,136 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	2,136 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	2,136 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	2,112 lm	4000 K	70	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	2,112 lm	4000 K	70	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	2,112 lm	4000 K	70	830 warm white	160° - 42° x 54°	Distribution medium 12

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	2,112 lm	4000 K	70	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	3,026 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	3,026 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	3,026 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	3,026 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	3,026 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	3,026 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	3,026 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	3,026 lm	3000 K	80	830 warm white	160° - 42° x 54°	Distribution medium 12
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	3,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	3,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	3,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	3,916 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	4,576 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	4,576 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	4,576 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	4,576 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	6,052 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	6,052 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	6,052 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	6,052 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	8,352 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread	Optic type outdoor
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	8,352 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	8,352 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	8,352 lm	4000 K	70	740 neutral white	160° - 42° x 54°	Distribution medium 12
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	9,890 lm	3000 K	70	730 warm white	160° - 42° x 54°	Distribution medium 11
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	3,741 lm	4000 K	70	830 warm white	160° - 42° x 54°	Distribution medium 11

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	11.6 W
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	16.2 W
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	19.6 W
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	21.5 W
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	24.5 W
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	27.5 W
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	33.5 W
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	40.5 W
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	49.5 W
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	59 W
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	65 W
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	72 W
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	11.6 W
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	16.2 W
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	19.6 W
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	21.5 W
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	24.5 W
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	27.5 W
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	33.5 W
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	40.5 W
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	49.5 W
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	59 W
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	65 W
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	72 W
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	11.6 W

Order Code	Full Product Name	Power Consumption
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	19.6 W
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	21.5 W
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	33.5 W
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	40.5 W
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	72 W
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	11.6 W
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	21.5 W
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	40.5 W
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	72 W
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	20 W
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	20 W
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	20 W
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	15.6 W
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	15.6 W
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	32 W
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	15.6 W
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	14.4 W
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	20 W
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	26.5 W
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	34.5 W
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	39 W
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	14.4 W
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	20 W
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	26.5 W
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	34.5 W
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	39 W
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	14.4 W
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	20 W
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	26.5 W
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	34.5 W
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	39 W
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	11.4 W
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	15.6 W
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	21 W
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	27 W
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	32 W
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	11.4 W
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	15.6 W
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	21 W
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	27 W

Order Code	Full Product Name	Power Consumption
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	32 W
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	11.4 W
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	15.6 W
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	21 W
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	27 W
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	32 W
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	39.5 W
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	48 W
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	56 W
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	62 W
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	69 W
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	39.5 W
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	48 W
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	56 W
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	62 W
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	69 W
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	39.5 W
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	48 W
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	56 W
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	62 W
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	69 W
910925865352	BGP307 LED35/740 II DM11 CLL C10	21.5 W
910925865374	BGP307 LED45/740 II DM11 CLL C10	27.5 W
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	27 W
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	32 W
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	11.4 W
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	15.6 W
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	21 W
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	27 W
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	32 W
910925865405	BGP307 LED69/740 II DM11 C10	39.5 W
910925865406	BGP307 LED84/740 II DM11 C10	48 W
910925865407	BGP307 LED99/740 II DM11 C10	56 W
910925865408	BGP307 LED109/740 II DM11 C10	62 W
910925865409	BGP307 LED120/740 II DM11 C10	69 W
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	39.5 W
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	48 W
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	56 W
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	62 W
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	69 W

Order Code	Full Product Name	Power Consumption
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	39.5 W
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	48 W
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	56 W
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	62 W
910925865419	BGP307 LED25/740 II DM11 CLL C10	16.2 W
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	69 W
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	32 W
910925865690	BGP307 LED18/830 II DM11 SR C10	14.4 W
910925865691	BGP307 LED54/830 II DM11 SRT C10	39 W
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	14.4 W
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	39 W
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	14.4 W
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	39 W
910925865696	BGP307 LED18/740 II DM11 SR C10	11.4 W
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	11.4 W
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	11.4 W
910925865699	BGP307 LED69/740 II DM11 SR C10	39.5 W
910925865701	BGP307 LED84/740 II DM11 SR C10	48 W
910925865702	BGP307 LED99/740 II DM11 SR C10	56 W
910925865703	BGP307 LED109/740 II DM11 SR C10	62 W
910925865704	BGP307 LED120/740 II DM11 SR C10	69 W
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	39.5 W
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	48 W
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	56 W
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	62 W
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	69 W
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	39.5 W
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	48 W
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	56 W
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	62 W
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	69 W
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	26.5 W
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	27 W
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	27.5 W
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	40.5 W
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	40.5 W
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	49.5 W
910925865378	BGP307 LED54/740 II DM11 C10	32 W
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	14.4 W
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	39 W

Order Code	Full Product Name	Power Consumption
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	14.4 W
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	39 W
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	11.4 W
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	15.6 W
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	21 W
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	27 W
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	32 W
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	11.4 W
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	15.6 W
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	32 W
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	79 W
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	15.6 W
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	15.6 W
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	15.6 W
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	15.6 W
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	20 W
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	20 W
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	20 W
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	20 W
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	21 W
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	21 W
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	21 W
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	21 W
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	26.5 W
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	26.5 W
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	26.5 W
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	26.5 W
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	27 W
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	27 W
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	27 W
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	27 W
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	32 W
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	32 W
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	32 W
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	32 W
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	39.5 W
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	39.5 W
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	39.5 W
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	39.5 W
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	56 W

Order Code	Full Product Name	Power Consumption
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	56 W
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	56 W
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	56 W
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	73 W
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	34.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	No	Not applicable
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	No	Not applicable
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	No	Not applicable
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	No	Not applicable
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	No	Not applicable
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	No	Not applicable
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	No	Not applicable
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	No	Not applicable
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	No	Not applicable
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	No	Not applicable
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	No	Not applicable
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	No	Not applicable
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	No	Not applicable
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	No	Not applicable
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	No	Not applicable
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	No	Not applicable
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	No	Not applicable
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	No	Not applicable
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	No	Not applicable
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	No	Not applicable
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	No	Not applicable
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	No	Not applicable
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	No	Not applicable
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	No	Not applicable
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Yes	0% (digital)
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	No	Not applicable
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	No	Not applicable
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	No	Not applicable
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Yes	0% (digital)
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Yes	0% (digital)
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Yes	0% (digital)
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Yes	0% (digital)
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Yes	0% (digital)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Yes	0% (digital)
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865352	BGP307 LED35/740 II DM11 CLL C10	No	Not applicable
910925865374	BGP307 LED45/740 II DM11 CLL C10	No	Not applicable
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865405	BGP307 LED69/740 II DM11 C10	No	0% (digital)
910925865406	BGP307 LED84/740 II DM11 C10	Yes	0% (digital)
910925865407	BGP307 LED99/740 II DM11 C10	Yes	0% (digital)
910925865408	BGP307 LED109/740 II DM11 C10	No	0% (digital)
910925865409	BGP307 LED120/740 II DM11 C10	Yes	0% (digital)
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865419	BGP307 LED25/740 II DM11 CLL C10	Yes	Not applicable
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865690	BGP307 LED18/830 II DM11 SR C10	Yes	0% (digital)
910925865691	BGP307 LED54/830 II DM11 SRT C10	Yes	0% (digital)
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Yes	0% (digital)
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865696	BGP307 LED18/740 II DM11 SR C10	Yes	0% (digital)
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865699	BGP307 LED69/740 II DM11 SR C10	Yes	0% (digital)
910925865701	BGP307 LED84/740 II DM11 SR C10	Yes	0% (digital)
910925865702	BGP307 LED99/740 II DM11 SR C10	Yes	0% (digital)
910925865703	BGP307 LED109/740 II DM11 SR C10	Yes	0% (digital)
910925865704	BGP307 LED120/740 II DM11 SR C10	Yes	0% (digital)
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Yes	0% (digital)
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Yes	0% (digital)
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	No	Not applicable
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	No	Not applicable
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	No	Not applicable
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	No	Not applicable
910925865378	BGP307 LED54/740 II DM11 C10	Yes	0% (digital)
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Yes	0% (digital)
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Yes	0% (digital)
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Yes	0% (digital)
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Yes	0% (digital)
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	No	Not applicable
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes	Not applicable
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	0% (digital)
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	Yes	0% (digital)
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	0% (digital)
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	Yes	0% (digital)
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	0% (digital)
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	0% (digital)
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	0% (digital)
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	0% (digital)
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	No	0% (digital)
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	No	0% (digital)
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Yes	0% (digital)
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	Yes	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Gray
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Gray
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Gray
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Gray
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Gray
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Gray
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Gray
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Gray
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Gray
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Gray
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Gray
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Gray
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Gray
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Gray
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Gray
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Gray
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Gray
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Gray
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Gray
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Gray
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Gray
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Gray
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Gray
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Gray
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Gray
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Gray
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Gray
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Gray
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Gray
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Gray
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Gray
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Gray
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Gray
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Gray
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Gray
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Gray
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Gray


Order Code	Full Product Name	Housing Color
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Gray
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Gray
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Gray
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Gray
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Gray
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Gray
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Gray
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Gray
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Gray
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Gray
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Gray
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Gray
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Gray
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Gray
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Gray
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Gray
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Gray
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Gray
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Gray
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Gray

Order Code	Full Product Name	Housing Color
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865352	BGP307 LED35/740 II DM11 CLL C10	Gray
910925865374	BGP307 LED45/740 II DM11 CLL C10	Gray
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865405	BGP307 LED69/740 II DM11 C10	Gray
910925865406	BGP307 LED84/740 II DM11 C10	Gray
910925865407	BGP307 LED99/740 II DM11 C10	Gray
910925865408	BGP307 LED109/740 II DM11 C10	Gray
910925865409	BGP307 LED120/740 II DM11 C10	Gray
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865419	BGP307 LED25/740 II DM11 CLL C10	Grey
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Gray
910925865690	BGP307 LED18/830 II DM11 SR C10	Gray
910925865691	BGP307 LED54/830 II DM11 SRT C10	Gray
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Gray
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Gray
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Gray


Order Code	Full Product Name	Housing Color
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Gray
910925865696	BGP307 LED18/740 II DM11 SR C10	Gray
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Gray
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Gray
910925865699	BGP307 LED69/740 II DM11 SR C10	Gray
910925865701	BGP307 LED84/740 II DM11 SR C10	Gray
910925865702	BGP307 LED99/740 II DM11 SR C10	Gray
910925865703	BGP307 LED109/740 II DM11 SR C10	Gray
910925865704	BGP307 LED120/740 II DM11 SR C10	Gray
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Gray
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Gray
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Gray
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Gray
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Gray
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Gray
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Gray
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Gray
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Gray
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Gray
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Gray
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Gray
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	Gray
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	Gray
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	Gray
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	Gray
910925865378	BGP307 LED54/740 II DM11 C10	Gray
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Gray
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Grey
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Grey
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	Gray

Order Code	Full Product Name	Housing Color
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	Gray
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	Gray
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	Gray
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	Gray
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Gray
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	Gray
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Gray
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Gray
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Gray
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Gray
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Gray
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Gray
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Gray
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Gray
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Gray
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Gray
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Gray
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Gray
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Gray
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Gray
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Gray
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Grey
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	Gray


Polar normal diagrams




BGP307I - 910925864604




BGP307I - 910925864592




BGP307I - 910925864597




BGP307I - 910925864587




BGP307I - 910925864586




BGP307I - 910925864590




BGP307I - 910925865134




BGP307I - 910925865226




BGP307I - 910925865248




BGP307I - 910925865213




BGP307I - 910925865215




BGP307I - 910925865151




BGP307I - 910925865235




BGP307I - 910925865211




BGP307I - 910925865551




BGP307I - 910925864593




BGP307I - 910925864595




BGP307I - 910925864584




BGP307I - 910925864588




BGP307I - 910925864589




BGP307I - 910925865153




BGP307I - 910925865214




BGP307I - 910925865222




BGP307I - 910925865234




BGP307I - 910925865238




BGP307I - 910925865251




BGP307I - 910925865245




BGP307I - 910925865242




BGP307I - 910925867804




BGP307I - 910925868886




BGP307I - 910925868892




BGP307I - 910925868941




BGP307I - 910925865206




BGP307I - 910925865378



BGP307I - 910925867801



BGP307I - 910925867802



BGP307I - 910925865391