



Versatile and cost-efficient LED lighting

ClearWay gen2

ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay Gen2 significantly improves the most important aspects of the street lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good quality light with all the added benefits of LED - energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

Benefits

- A range of benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information

Features


- One flexible design that offers different options depending on application needs
- Includes a dedicated light recipe that preserves dark night skies
- Compact and efficient design
- Tilt regulation with no need to open the cover

ClearWay gen2

Application

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads
- Parking lots

Dimensional drawing



General Information

Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Upward light output ratio	0
---------------------------	---

Operating and Electrical

Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode
--	--

Mechanical and Housing

Optical cover type	Flat glass
Mech. impact protection code	IK09
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°

Approval and Application

CE mark	Yes
Flammability mark	-

Product Data

Product family code	BGP307
---------------------	--------

General Information

Order Code	Full Product Name	Driver included	Lamp family code
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Yes	LED18
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Yes	LED25
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Yes	LED30
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Yes	LED35
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Yes	LED40
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Yes	LED45
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Yes	LED54
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Yes	LED69
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Yes	LED84
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Yes	LED99
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Yes	LED109
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Yes	LED120
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Yes	LED18
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Yes	LED25
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Yes	LED30
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Yes	LED35
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Yes	LED40
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Yes	LED45
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Yes	LED54
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Yes	LED69
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Yes	LED84
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Yes	LED99
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Yes	LED109
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Yes	LED120
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Yes	LED18
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Yes	LED30
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Yes	LED35
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Yes	LED54
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Yes	LED69

Order Code	Full Product Name	Driver included	Lamp family code
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Yes	LED120
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Yes	LED18
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Yes	LED35
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Yes	LED69
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Yes	LED120
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Yes	LED25
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Yes	LED25
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Yes	LED25
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Yes	LED25
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Yes	LED25
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Yes	LED54
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Yes	LED25
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Yes	LED18
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Yes	LED25
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Yes	LED35
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Yes	LED45
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Yes	LED54
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	LED18
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes	LED25
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes	LED35
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes	LED45
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	LED54
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	LED18
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes	LED25
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes	LED35
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes	LED45
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	LED54
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Yes	LED18
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Yes	LED25
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Yes	LED35
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Yes	LED45
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Yes	LED54
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	LED18
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	LED25
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes	LED35
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	LED45
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	LED54
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	LED18
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	LED25
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	LED35
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	LED45
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	LED54
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Yes	LED69
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Yes	LED84
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Yes	LED99
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Yes	LED109
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Yes	LED120
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	LED69
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	LED84
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	LED99
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	LED109
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	LED120

Order Code	Full Product Name	Driver included	Lamp family code
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	LED69
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	LED84
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	LED99
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	LED109
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	LED120
910925865352	BGP307 LED35/740 II DM11 CLL C10	Yes	LED35
910925865374	BGP307 LED45/740 II DM11 CLL C10	Yes	LED45
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	LED45
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	LED54
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	LED18
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	LED25
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	LED35
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	LED45
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	LED54
910925865405	BGP307 LED69/740 II DM11 C10	Yes	LED69
910925865406	BGP307 LED84/740 II DM11 C10	Yes	LED84
910925865407	BGP307 LED99/740 II DM11 C10	Yes	LED99
910925865408	BGP307 LED109/740 II DM11 C10	Yes	LED109
910925865409	BGP307 LED120/740 II DM11 C10	Yes	LED120
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	LED69
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	LED84
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	LED99
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	LED109
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	LED120
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	LED69
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	LED84
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	LED99
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	LED109
910925865419	BGP307 LED25/740 II DM11 CLL C10	Yes	LED25
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	LED120
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Yes	LED54
910925865690	BGP307 LED18/830 II DM11 SR C10	Yes	LED18
910925865691	BGP307 LED54/830 II DM11 SRT C10	Yes	LED54
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Yes	LED18
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Yes	LED54
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Yes	LED18
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Yes	LED54
910925865696	BGP307 LED18/740 II DM11 SR C10	Yes	LED18
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Yes	LED18
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Yes	LED18
910925865699	BGP307 LED69/740 II DM11 SR C10	Yes	LED69
910925865701	BGP307 LED84/740 II DM11 SR C10	Yes	LED84
910925865702	BGP307 LED99/740 II DM11 SR C10	Yes	LED99
910925865703	BGP307 LED109/740 II DM11 SR C10	Yes	LED109
910925865704	BGP307 LED120/740 II DM11 SR C10	Yes	LED120
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Yes	LED69
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Yes	LED84
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Yes	LED99
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Yes	LED109
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Yes	LED120
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Yes	LED69
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Yes	LED84

Order Code	Full Product Name	Driver included	Lamp family code
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Yes	LED99
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Yes	LED109
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Yes	LED120
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Yes	LED35
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Yes	LED45
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	Yes	LED45
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	Yes	LED69
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	Yes	LED69
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	Yes	LED84
910925865378	BGP307 LED54/740 II DM11 C10	Yes	LED54
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	LED18
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	LED54
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	LED18
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	LED54
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Yes	LED18
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Yes	LED25
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Yes	LED35
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Yes	LED45
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Yes	LED54
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	LED18
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	LED25
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Yes	LED54
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes	LED130
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	LED25
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	Yes	LED25
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	LED25
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	Yes	LED25
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	LED25
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	LED25
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	LED25
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	LED25
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Yes	LED35
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	LED35
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Yes	LED35
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	LED35
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Yes	LED35
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	LED35
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Yes	LED35
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	LED35
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Yes	LED45
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	LED45
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Yes	LED45
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	LED45
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Yes	LED54
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	LED54
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Yes	LED54
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	LED54
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Yes	LED69
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	LED69
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Yes	LED69
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	LED69
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Yes	LED99

Order Code	Full Product Name	Driver included	Lamp family code
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	LED99
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Yes	LED99
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	LED99
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Yes	LED120
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	Yes	LED45

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	154° - 31° x 54°	740 neutral white	4000 K	70
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	4000 K	70
910925865130	BGP307 LED30-4S/740 I	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	DM50 DDF27 D18 48/				
910925865131	BGP307 LED35-4S/740 I	154° - 31° x 54°	740 neutral	4000 K	70
	DM50 DDF27 D18 48/		white		
910925865132	BGP307 LED54-4S/740 I	154° - 31° x 54°	740 neutral	4000 K	70
	DM50 DDF27 D18 48/		white		
910925865133	BGP307 LED69-4S/740 I	154° - 31° x 54°	740 neutral	4000 K	70
	DM50 DDF27 D18 48/		white		
910925865134	BGP307 LED120-4S/740 I	154° - 31° x 54°	740 neutral	4000 K	70
	DM50 DDF27 D18 48		white		
910925865150	BGP307 LED18-4S/740 I	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 48/76S		white		
910925865151	BGP307 LED35-4S/740 I	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 48/76S		white		
910925865152	BGP307 LED69-4S/740 I	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 48/76S		white		
910925865153	BGP307 LED120-4S/740 I	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 48/76S		white		
910925865202	BGP307 LED25/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLL SR C10		white		
910925865203	BGP307 LED25/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLL DDF1 SR C10		white		
910925865204	BGP307 LED25/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLL DDF2 SR C10		white		
910925865205	BGP307 LED25/740 II	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 CLL SR C10		white		
910925865207	BGP307 LED25/740 II	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 CLL DDF1 SR C10		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865208	BGP307 LED54/740 II	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 DDF1 SR C10		white		
910925865209	BGP307 LED25/740 II	160° - 42° x 54°	740 neutral	4000 K	70
	DM11 CLL DDF2 SR C10		white		
910925865210	BGP307 LED18-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO 48/60S		white		
910925865211	BGP307 LED25-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO 48/60S		white		
910925865212	BGP307 LED35-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO 48/60S		white		
910925865213	BGP307 LED45-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO 48/60S		white		
910925865214	BGP307 LED54-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO 48/60S		white		
910925865215	BGP307 LED18-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO-DDF1 D18		white		
910925865216	BGP307 LED25-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO-DDF1 D18		white		
910925865217	BGP307 LED35-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO-DDF1 D18		white		
910925865218	BGP307 LED45-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO-DDF1 D18		white		
910925865219	BGP307 LED54-4S/830 II	160° - 42° x 54°	830 warm	3000 K	80
	DM11 CLO-DDF1 D18		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865248	BGP307 LED109-4S/740 II DM11 CLO- DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865249	BGP307 LED120-4S/740 II DM11 CLO- DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865253	BGP307 LED109-4S/740 II DM11 CLO- DDF2 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865254	BGP307 LED120-4S/740 II DM11 CLO- DDF2 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865352	BGP307 LED35/740 II DM11 CLL C10	-	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865374	BGP307 LED45/740 II DM11 CLL C10	-	740 neutral white	4000 K	70
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865405	BGP307 LED69/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865406	BGP307 LED84/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865407	BGP307 LED99/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865408	BGP307 LED109/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865409	BGP307 LED120/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865410	BGP307 LED69-4S/740 II	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
	DM11 CLO-DDF1 D18				
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865419	BGP307 LED25/740 II DM11 CLL C10	61° x 150°	740 neutral white	3000 K	80
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865690	BGP307 LED18/830 II DM11 SR C10	160° - 42° x 54°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865691	BGP307 LED54/830 II DM11 SRT C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865696	BGP307 LED18/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865699	BGP307 LED69/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865701	BGP307 LED84/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865702	BGP307 LED99/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865703	BGP307 LED109/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865704	BGP307 LED120/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	160° - 42° x 54°	830 warm white	3000 K	80
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	-	740 neutral white	4000 K	70
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	-	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	152° - 25° x 66°	740 neutral white	4000 K	70
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	152° - 25° x 66°	740 neutral white	4000 K	70
910925865378	BGP307 LED54/740 II DM11 C10	160° - 42° x 54°	740 neutral white	4000 K	70
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	160° - 42° x 54°	740 neutral white	4000 K	70
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	160° - 42° x 54°	830 warm white	4000 K	70
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	160° - 42° x 54°	830 warm white	4000 K	70
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	160° - 42° x 54°	830 warm white	4000 K	70
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	160° - 42° x 54°	830 warm white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	160° - 42° x 54°	740 neutral white	4000 K	70
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	160° - 42° x 54°	740 neutral white	4000 K	70
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	160° - 42° x 54°	830 warm white	3000 K	80
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	160° - 42° x 54°	830 warm white	3000 K	80
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	160° - 42° x 54°	830 warm white	3000 K	80
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	160° - 42° x 54°	830 warm white	3000 K	80
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	160° - 42° x 54°	740 neutral white	4000 K	70
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO- DDF2	160° - 42° x 54°	740 neutral white	4000 K	70
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO- DDF2	160° - 42° x 54°	740 neutral white	4000 K	70
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868894	BGP307 LED120-4S/730 II DM32 7042 MSP CL	160° - 42° x 54°	730 warm white	3000 K	70
9109258688948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	4000 K	70

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	1,584 lm	Distribution medium 50
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	2,175 lm	Distribution medium 50
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	2,610 lm	Distribution medium 50
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	3,080 lm	Distribution medium 50
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	3,520 lm	Distribution medium 50
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	3,960 lm	Distribution medium 50
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	4,698 lm	Distribution medium 50
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	6,160 lm	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	7,308 lm	Distribution medium 50
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	8,600 lm	Distribution medium 50
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	9,460 lm	Distribution medium 50
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	10,200 lm	Distribution medium 50
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	1,584 lm	Distribution medium 50
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	2,175 lm	Distribution medium 50
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	2,610 lm	Distribution medium 50
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	3,080 lm	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	3,520 lm	Distribution medium 50
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	3,960 lm	Distribution medium 50
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	4,698 lm	Distribution medium 50
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	6,160 lm	Distribution medium 50
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	7,308 lm	Distribution medium 50
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	8,600 lm	Distribution medium 50
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	9,460 lm	Distribution medium 50
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	10,200 lm	Distribution medium 50
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	1,584 lm	Distribution medium 50
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	2,610 lm	Distribution medium 50
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	3,080 lm	Distribution medium 50
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	4,698 lm	Distribution medium 50
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	6,160 lm	Distribution medium 50
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	10,200 lm	Distribution medium 50
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	1,566 lm	Distribution medium 11
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	3,045 lm	Distribution medium 11
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	6,090 lm	Distribution medium 11
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	10,200 lm	Distribution medium 11
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	2,088 lm	Distribution medium 11
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	2,088 lm	Distribution medium 11
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	2,088 lm	Distribution medium 11
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	2,088 lm	Distribution medium 11
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	2,088 lm	Distribution medium 11
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	4,524 lm	Distribution medium 11
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	2,088 lm	Distribution medium 11
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	1,522.5 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	2,088 lm	Distribution medium 11
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	2,958 lm	Distribution medium 11
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	3,741 lm	Distribution medium 11
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	4,524 lm	Distribution medium 11
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	1,522.5 lm	Distribution medium 11
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	2,088 lm	Distribution medium 11
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	2,958 lm	Distribution medium 11
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3,741 lm	Distribution medium 11
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	4,524 lm	Distribution medium 11
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	1,522.5 lm	Distribution medium 11
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	2,088 lm	Distribution medium 11
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	2,958 lm	Distribution medium 11
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3,741 lm	Distribution medium 11
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	4,524 lm	Distribution medium 11
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	1,522.5 lm	Distribution medium 11
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	2,088 lm	Distribution medium 11
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	2,958 lm	Distribution medium 11
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	3,828 lm	Distribution medium 11
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4,524 lm	Distribution medium 11
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	1,522.5 lm	Distribution medium 11
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	2,088 lm	Distribution medium 11
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	2,958 lm	Distribution medium 11
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	3,828 lm	Distribution medium 11
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4,524 lm	Distribution medium 11
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	1,522.5 lm	Distribution medium 11
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	2,088 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	2,958 lm	Distribution medium 11
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	3,828 lm	Distribution medium 11
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4,524 lm	Distribution medium 11
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	5,916 lm	Distribution medium 11
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	7,134 lm	Distribution medium 11
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	8,256 lm	Distribution medium 11
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	9,030 lm	Distribution medium 11
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	9,775 lm	Distribution medium 11
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	5,916 lm	Distribution medium 11
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	7,134 lm	Distribution medium 11
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	8,256 lm	Distribution medium 11
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	9,030 lm	Distribution medium 11
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	9,775 lm	Distribution medium 11
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	5,916 lm	Distribution medium 11
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	7,134 lm	Distribution medium 11
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	8,256 lm	Distribution medium 11
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	9,030 lm	Distribution medium 11
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	9,775 lm	Distribution medium 11
910925865352	BGP307 LED35/740 II DM11 CLL C10	3,045 lm	Distribution medium 11
910925865374	BGP307 LED45/740 II DM11 CLL C10	3,915 lm	Distribution medium 11
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	3,828 lm	Distribution medium 11
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4,524 lm	Distribution medium 11
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	1,522.5 lm	Distribution medium 11
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	2,088 lm	Distribution medium 11
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	2,958 lm	Distribution medium 11
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	3,828 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4,524 lm	Distribution medium 11
910925865405	BGP307 LED69/740 II DM11 C10	5,916 lm	Distribution medium 11
910925865406	BGP307 LED84/740 II DM11 C10	7,134 lm	Distribution medium 11
910925865407	BGP307 LED99/740 II DM11 C10	8,256 lm	Distribution medium 11
910925865408	BGP307 LED109/740 II DM11 C10	9,030 lm	Distribution medium 11
910925865409	BGP307 LED120/740 II DM11 C10	9,775 lm	Distribution medium 11
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	5,916 lm	Distribution medium 11
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	7,134 lm	Distribution medium 11
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	8,256 lm	Distribution medium 11
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	9,030 lm	Distribution medium 11
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	9,775 lm	Distribution medium 11
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	5,916 lm	Distribution medium 11
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	7,134 lm	Distribution medium 11
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	8,256 lm	Distribution medium 11
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	9,030 lm	Distribution medium 11
910925865419	BGP307 LED25/740 II DM11 CLL C10	2,175 lm	Distribution medium 11
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	9,775 lm	Distribution medium 11
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	4,524 lm	Distribution medium 11
910925865690	BGP307 LED18/830 II DM11 SR C10	1,522.5 lm	Distribution medium 11
910925865691	BGP307 LED54/830 II DM11 SRT C10	4,524 lm	Distribution medium 11
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	1,522.5 lm	Distribution medium 11
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	4,524 lm	Distribution medium 11
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	1,522.5 lm	Distribution medium 11
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	4,524 lm	Distribution medium 11
910925865696	BGP307 LED18/740 II DM11 SR C10	1,522.5 lm	Distribution medium 11
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	1,522.5 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	1,522.5 lm	Distribution medium 11
910925865699	BGP307 LED69/740 II DM11 SR C10	5,916 lm	Distribution medium 11
910925865701	BGP307 LED84/740 II DM11 SR C10	7,134 lm	Distribution medium 11
910925865702	BGP307 LED99/740 II DM11 SR C10	8,256 lm	Distribution medium 11
910925865703	BGP307 LED109/740 II DM11 SR C10	9,030 lm	Distribution medium 11
910925865704	BGP307 LED120/740 II DM11 SR C10	9,775 lm	Distribution medium 11
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	5,916 lm	Distribution medium 11
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	7,134 lm	Distribution medium 11
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	8,256 lm	Distribution medium 11
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	9,030 lm	Distribution medium 11
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	9,775 lm	Distribution medium 11
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	5,916 lm	Distribution medium 11
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	7,134 lm	Distribution medium 11
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	8,256 lm	Distribution medium 11
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	9,030 lm	Distribution medium 11
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	9,775 lm	Distribution medium 11
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	2,958 lm	Distribution medium 11
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	3,828 lm	Distribution medium 11
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	3,780 lm	Distribution extra wide 10
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	5,880 lm	Distribution extra wide 10
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	5,880 lm	Distribution extra wide 10
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	6,972 lm	Distribution extra wide 10
910925865378	BGP307 LED54/740 II DM11 C10	4,524 lm	Distribution medium 11
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	1,522.5 lm	Distribution medium 11
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	4,524 lm	Distribution medium 11
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	1,522.5 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	4,524 lm	Distribution medium 11
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	1,522.5 lm	Distribution medium 11
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	2,088 lm	Distribution medium 11
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	2,958 lm	Distribution medium 11
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	3,828 lm	Distribution medium 11
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	4,524 lm	Distribution medium 11
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	1,522.5 lm	Distribution medium 11
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	2,088 lm	Distribution medium 11
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4,524 lm	Distribution medium 11
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	10,920 lm	Distribution medium 11
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	2,136 lm	Distribution medium 12
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	2,136 lm	Distribution medium 12
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	2,136 lm	Distribution medium 12
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	2,136 lm	Distribution medium 12
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	2,112 lm	Distribution medium 12
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	2,112 lm	Distribution medium 12
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	2,112 lm	Distribution medium 12
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	2,112 lm	Distribution medium 12
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	3,026 lm	Distribution medium 12
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	3,026 lm	Distribution medium 12
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	3,026 lm	Distribution medium 12
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	3,026 lm	Distribution medium 12
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	3,026 lm	Distribution medium 12
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	3,026 lm	Distribution medium 12
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	3,026 lm	Distribution medium 12
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	3,026 lm	Distribution medium 12

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	3,916 lm	Distribution medium 12
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	3,916 lm	Distribution medium 12
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	3,916 lm	Distribution medium 12
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	3,916 lm	Distribution medium 12
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	4,576 lm	Distribution medium 12
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	4,576 lm	Distribution medium 12
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	4,576 lm	Distribution medium 12
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	4,576 lm	Distribution medium 12
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	6,052 lm	Distribution medium 12

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	6,052 lm	Distribution medium 12
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	6,052 lm	Distribution medium 12
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	6,052 lm	Distribution medium 12
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	8,352 lm	Distribution medium 12
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	8,352 lm	Distribution medium 12
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	8,352 lm	Distribution medium 12
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	8,352 lm	Distribution medium 12
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	9,890 lm	Distribution medium 11
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	3,741 lm	Distribution medium 11

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	11.6 W
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	16.2 W
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	19.6 W
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	21.5 W
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	24.5 W
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	27.5 W
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	33.5 W
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	40.5 W
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	49.5 W
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	59 W
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	65 W
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	72 W
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	11.6 W
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	16.2 W
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	19.6 W
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	21.5 W
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	24.5 W
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	27.5 W
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	33.5 W
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	40.5 W
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	49.5 W
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	59 W
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	65 W
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	72 W
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	11.6 W
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	19.6 W
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	21.5 W
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	33.5 W
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	40.5 W
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	72 W

Order Code	Full Product Name	Power Consumption
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	11.6 W
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	21.5 W
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	40.5 W
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	72 W
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	20 W
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	20 W
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	20 W
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	15.6 W
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	15.6 W
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	32 W
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	15.6 W
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	14.4 W
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	20 W
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	26.5 W
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	34.5 W
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	39 W
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	14.4 W
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	20 W
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	26.5 W
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	34.5 W
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	39 W
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	14.4 W
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	20 W
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	26.5 W
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	34.5 W
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	39 W
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	11.4 W
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	15.6 W
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	21 W
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	27 W

Order Code	Full Product Name	Power Consumption
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	32 W
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	11.4 W
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	15.6 W
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	21 W
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	27 W
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	32 W
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	11.4 W
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	15.6 W
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	21 W
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	27 W
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	32 W
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	39.5 W
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	48 W
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	56 W
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	62 W
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	69 W
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	39.5 W
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	48 W
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	56 W
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	62 W
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	69 W
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	39.5 W
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	48 W
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	56 W
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	62 W
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	69 W
910925865352	BGP307 LED35/740 II DM11 CLL C10	21.5 W
910925865374	BGP307 LED45/740 II DM11 CLL C10	27.5 W
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	27 W
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	32 W
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	11.4 W
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	15.6 W
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	21 W
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	27 W
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	32 W
910925865405	BGP307 LED69/740 II DM11 C10	39.5 W
910925865406	BGP307 LED84/740 II DM11 C10	48 W
910925865407	BGP307 LED99/740 II DM11 C10	56 W
910925865408	BGP307 LED109/740 II DM11 C10	62 W
910925865409	BGP307 LED120/740 II DM11 C10	69 W
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	39.5 W
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	48 W
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	56 W
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	62 W
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	69 W
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	39.5 W
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	48 W
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	56 W
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	62 W
910925865419	BGP307 LED25/740 II DM11 CLL C10	16.2 W
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	69 W
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	32 W

Order Code	Full Product Name	Power Consumption
910925865690	BGP307 LED18/830 II DM11 SR C10	14.4 W
910925865691	BGP307 LED54/830 II DM11 SRT C10	39 W
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	14.4 W
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	39 W
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	14.4 W
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	39 W
910925865696	BGP307 LED18/740 II DM11 SR C10	11.4 W
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	11.4 W
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	11.4 W
910925865699	BGP307 LED69/740 II DM11 SR C10	39.5 W
910925865701	BGP307 LED84/740 II DM11 SR C10	48 W
910925865702	BGP307 LED99/740 II DM11 SR C10	56 W
910925865703	BGP307 LED109/740 II DM11 SR C10	62 W
910925865704	BGP307 LED120/740 II DM11 SR C10	69 W
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	39.5 W
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	48 W
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	56 W
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	62 W
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	69 W
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	39.5 W
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	48 W
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	56 W
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	62 W
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	69 W
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	26.5 W
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	27 W
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	27.5 W
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	40.5 W
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	40.5 W
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	49.5 W
910925865378	BGP307 LED54/740 II DM11 C10	32 W
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	14.4 W
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	39 W
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	14.4 W
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	39 W
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	11.4 W
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	15.6 W
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	21 W
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	27 W
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	32 W
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	11.4 W
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	15.6 W
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	32 W
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	79 W
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	15.6 W
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	15.6 W
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	15.6 W
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	15.6 W
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	20 W
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	20 W
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	20 W
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	20 W

Order Code	Full Product Name	Power Consumption
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	21 W
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	21 W
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	21 W
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	21 W
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	26.5 W
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	26.5 W
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	26.5 W
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	26.5 W
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	27 W
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	27 W
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	27 W
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	27 W
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	32 W

Order Code	Full Product Name	Power Consumption
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	32 W
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	32 W
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	32 W
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	39.5 W
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	39.5 W
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	39.5 W
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	39.5 W
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	56 W
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	56 W
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	56 W
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	56 W
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	73 W
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	34.5 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	No	Not applicable
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	No	Not applicable
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	No	Not applicable
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	No	Not applicable
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	No	Not applicable
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	No	Not applicable
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	No	Not applicable
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	No	Not applicable
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	No	Not applicable
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	No	Not applicable
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	No	Not applicable
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	No	Not applicable
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	No	Not applicable
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	No	Not applicable
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	No	Not applicable
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	No	Not applicable
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	No	Not applicable
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	No	Not applicable
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	No	Not applicable
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	No	Not applicable
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	No	Not applicable
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	No	Not applicable
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	No	Not applicable
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Yes	0% (digital)
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Yes	0% (digital)
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	No	Not applicable
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	No	Not applicable
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	No	Not applicable
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	No	Not applicable
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Yes	0% (digital)
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Yes	0% (digital)
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Yes	0% (digital)
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Yes	0% (digital)
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Yes	0% (digital)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Yes	0% (digital)
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865211	BGP307 LED25-4S/830 II DM11 CLO-48/60S	No	0% (digital)
910925865212	BGP307 LED35-4S/830 II DM11 CLO-48/60S	No	0% (digital)
910925865213	BGP307 LED45-4S/830 II DM11 CLO-48/60S	No	0% (digital)
910925865214	BGP307 LED54-4S/830 II DM11 CLO-48/60S	No	0% (digital)
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865225	BGP307 LED18-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865226	BGP307 LED25-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865227	BGP307 LED35-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865228	BGP307 LED45-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865229	BGP307 LED54-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865240	BGP307 LED69-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865241	BGP307 LED84-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865242	BGP307 LED99-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865243	BGP307 LED109-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865244	BGP307 LED120-4S/740 II DM11 CLO-48/60S	No	0% (digital)
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865352	BGP307 LED35/740 II DM11 CLL C10	No	Not applicable
910925865374	BGP307 LED45/740 II DM11 CLL C10	No	Not applicable
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865405	BGP307 LED69/740 II DM11 C10	No	0% (digital)
910925865406	BGP307 LED84/740 II DM11 C10	Yes	0% (digital)
910925865407	BGP307 LED99/740 II DM11 C10	Yes	0% (digital)
910925865408	BGP307 LED109/740 II DM11 C10	No	0% (digital)
910925865409	BGP307 LED120/740 II DM11 C10	Yes	0% (digital)
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes	0% (digital)
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865419	BGP307 LED25/740 II DM11 CLL C10	Yes	Not applicable
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes	0% (digital)
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865690	BGP307 LED18/830 II DM11 SR C10	Yes	0% (digital)
910925865691	BGP307 LED54/830 II DM11 SRT C10	Yes	0% (digital)
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Yes	0% (digital)
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865696	BGP307 LED18/740 II DM11 SR C10	Yes	0% (digital)
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865699	BGP307 LED69/740 II DM11 SR C10	Yes	0% (digital)
910925865701	BGP307 LED84/740 II DM11 SR C10	Yes	0% (digital)
910925865702	BGP307 LED99/740 II DM11 SR C10	Yes	0% (digital)
910925865703	BGP307 LED109/740 II DM11 SR C10	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865704	BGP307 LED120/740 II DM11 SR C10	Yes	0% (digital)
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Yes	0% (digital)
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Yes	0% (digital)
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Yes	0% (digital)
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Yes	0% (digital)
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	No	Not applicable
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	No	Not applicable
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	No	Not applicable
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	No	Not applicable
910925865378	BGP307 LED54/740 II DM11 C10	Yes	0% (digital)
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes	0% (digital)
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	Yes	0% (digital)
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	Yes	0% (digital)
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	Yes	0% (digital)
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Yes	0% (digital)
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	No	Not applicable
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes	Not applicable
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	0% (digital)
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	Yes	0% (digital)
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	No	0% (digital)
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	Yes	0% (digital)
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	0% (digital)
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	0% (digital)
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	No	0% (digital)
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Yes	0% (digital)
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	No	0% (digital)
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	No	0% (digital)
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Yes	0% (digital)
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	No	0% (digital)
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Yes	0% (digital)
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Yes	0% (digital)
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	Yes	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Gray
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Gray
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Gray
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Gray
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Gray
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Gray
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Gray
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Gray
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Gray

Order Code	Full Product Name	Housing Color
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Gray
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Gray
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Gray
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Gray
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Gray
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Gray
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Gray
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Gray
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Gray

ClearWay gen2

Order Code	Full Product Name	Housing Color	Order Code	Full Product Name	Housing Color
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Gray	910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Gray
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Gray	910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Gray
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Gray	910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Gray
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Gray	910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Gray
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Gray	910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Gray
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Gray	910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Gray
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Gray	910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Gray	910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Gray	910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Gray	910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Gray	910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Gray	910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Gray	910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Gray	910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Gray	910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Gray	910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Gray	910925865352	BGP307 LED35/740 II DM11 CLL C10	Gray
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Gray	910925865374	BGP307 LED45/740 II DM11 CLL C10	Gray
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Gray	910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Gray	910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Gray	910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Gray	910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Gray	910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Gray	910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Gray	910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Gray	910925865405	BGP307 LED69/740 II DM11 C10	Gray
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Gray	910925865406	BGP307 LED84/740 II DM11 C10	Gray
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Gray	910925865407	BGP307 LED99/740 II DM11 C10	Gray
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Gray	910925865408	BGP307 LED109/740 II DM11 C10	Gray
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Gray	910925865409	BGP307 LED120/740 II DM11 C10	Gray
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Gray	910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Gray	910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Gray	910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Gray	910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Gray	910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Gray
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Gray	910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Gray	910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Gray	910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Gray
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Gray	910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Gray	910925865419	BGP307 LED25/740 II DM11 CLL C10	Grey
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Gray	910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Gray
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Gray	910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Gray
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Gray	910925865690	BGP307 LED18/830 II DM11 SR C10	Gray
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Gray	910925865691	BGP307 LED54/830 II DM11 SRT C10	Gray
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Gray	910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Gray
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Gray	910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Gray
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray	910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Gray
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Gray	910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Gray
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Gray	910925865696	BGP307 LED18/740 II DM11 SR C10	Gray
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Gray	910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Gray
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Gray	910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Gray
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Gray	910925865699	BGP307 LED69/740 II DM11 SR C10	Gray

Order Code	Full Product Name	Housing Color
910925865701	BGP307 LED84/740 II DM11 SR C10	Gray
910925865702	BGP307 LED99/740 II DM11 SR C10	Gray
910925865703	BGP307 LED109/740 II DM11 SR C10	Gray
910925865704	BGP307 LED120/740 II DM11 SR C10	Gray
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Gray
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Gray
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Gray
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Gray
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Gray
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Gray
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Gray
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Gray
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Gray
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Gray
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Gray
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Gray
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	Gray
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	Gray
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	Gray
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	Gray
910925865378	BGP307 LED54/740 II DM11 C10	Gray
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Gray
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Gray
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Gray
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Gray
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Gray
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Grey
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Grey

Order Code	Full Product Name	Housing Color
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	Gray
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	Gray
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	Gray
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	Gray
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	Gray
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Gray
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	Gray
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	Gray
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Gray
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	Gray
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Gray
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Gray
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	Gray
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	Gray
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Gray
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	Gray
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Gray
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	Gray
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	Gray
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Gray
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	Gray
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868890	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Gray
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	Gray
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	Gray
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	Grey
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	Gray

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	0.5 %
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	0.5 %
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	0.5 %
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	0.5 %
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	0.5 %
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	0.5 %
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	0.5 %
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	0.5 %
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	0.5 %
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	0.5 %
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	0.5 %
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	0.5 %
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	0.5 %
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	0.5 %
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	0.5 %
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	0.5 %
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	0.5 %
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	0.5 %
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	0.5 %
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	0.5 %
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	0.5 %
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	0.5 %
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	0.5 %
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	0.5 %
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	0.5 %


Order Code	Full Product Name	Driver failure rate at 5000 h
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	0.5 %
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	0.5 %
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	0.5 %
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	0.5 %
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	0.5 %
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	0.5 %
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	0.5 %
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	0.5 %
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	0.5 %
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	0.5 %
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	0.5 %
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	0.5 %
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	0.5 %
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	0.5 %
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	0.5 %
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	-
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	0.5 %
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	-
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	0.5 %
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	-
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	0.5 %
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	0.5 %
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	-
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	0.5 %
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	-
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	0.5 %
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	-
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	0.5 %
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	-
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	0.5 %
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	-
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	0.5 %
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	-
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	0.5 %
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	0.5 %
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-
910925865352	BGP307 LED35/740 II DM11 CLL C10	-
910925865374	BGP307 LED45/740 II DM11 CLL C10	-
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	0.5 %
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-
910925865405	BGP307 LED69/740 II DM11 C10	-
910925865406	BGP307 LED84/740 II DM11 C10	0.5 %
910925865407	BGP307 LED99/740 II DM11 C10	-
910925865408	BGP307 LED109/740 II DM11 C10	0.5 %
910925865409	BGP307 LED120/740 II DM11 C10	-
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-
910925865419	BGP307 LED25/740 II DM11 CLL C10	-
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	0.5 %
910925865690	BGP307 LED18/830 II DM11 SR C10	0.5 %
910925865691	BGP307 LED54/830 II DM11 SRT C10	0.5 %
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	0.5 %
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	0.5 %
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	0.5 %
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	0.5 %
910925865696	BGP307 LED18/740 II DM11 SR C10	0.5 %
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	0.5 %
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	0.5 %
910925865699	BGP307 LED69/740 II DM11 SR C10	0.5 %
910925865701	BGP307 LED84/740 II DM11 SR C10	0.5 %
910925865702	BGP307 LED99/740 II DM11 SR C10	0.5 %
910925865703	BGP307 LED109/740 II DM11 SR C10	0.5 %
910925865704	BGP307 LED120/740 II DM11 SR C10	0.5 %
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	0.5 %
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	0.5 %


Order Code	Full Product Name	Driver failure rate at 5000 h
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	0.5 %
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	0.5 %
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	0.5 %
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	0.5 %
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	0.5 %
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	0.5 %
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	0.5 %
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	0.5 %
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	0.5 %
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	0.5 %
910925867801	BGP307 LED45-4S/740 II DX10 D11 48/76S	-
910925867802	BGP307 LED69-4S/740 II DX10 D11 48/76S	-
910925867803	BGP307 LED69-4S/740 II DX10 BL1 D11 48/7	-
910925867804	BGP307 LED84-4S/740 II DX10 BL1 D11 48/7	-
910925865378	BGP307 LED54/740 II DM11 C10	-
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	-
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	-
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	-
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	0.5 %
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	-
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	0.5 %
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	0.5 %
910925868862	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	-
910925868863	BGP307 LED25-4S/740 II DM12 CLL CLO D18	-
910925868864	BGP307 LED-HB-4S/740 II DM12 CLL CLO 48/	-
910925868865	BGP307 LED-HB-4S/740 II DM12 CLL CLO D18	-
910925868866	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	-
910925868867	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	-
910925868868	BGP307 LED-HB-4S/830 II DM12 CLL CLO 48/	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868869	BGP307 LED-HB-4S/830 II DM12 CLL CLO D18	-
910925868870	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	-
910925868871	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	-
910925868872	BGP307 LED35-4S/740 II DM12 CLL CLO 48/6	-
910925868873	BGP307 LED35-4S/740 II DM12 CLL CLO-DDF2	-
910925868874	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	-
910925868875	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	-
910925868876	BGP307 LED35-4S/830 II DM12 CLL CLO 48/6	-
910925868877	BGP307 LED35-4S/830 II DM12 CLL CLO-DDF2	-
910925868878	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	-
910925868879	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	-
910925868880	BGP307 LED45-4S/740 II DM12 CLL CLO 48/6	-
910925868881	BGP307 LED45-4S/740 II DM12 CLL CLO-DDF2	-
910925868882	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	-
910925868883	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	-
910925868884	BGP307 LED54-4S/740 II DM12 CLL CLO 48/6	-
910925868885	BGP307 LED54-4S/740 II DM12 CLL CLO-DDF2	-
910925868886	BGP307 LED69-4S/740 II DM12 CLO 48/60S	-
910925868887	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	-
910925868888	BGP307 LED69-4S/740 II DM12 CLO 48/60S	-
910925868889	BGP307 LED69-4S/740 II DM12 CLO-DDF2 D18	-
91092586889	BGP307 LED99-4S/740 II DM12 CLO 48/60S	0
910925868891	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	-
910925868892	BGP307 LED99-4S/740 II DM12 CLO 48/60S	-
910925868893	BGP307 LED99-4S/740 II DM12 CLO-DDF2 D18	-
910925868941	BGP307 LED120-4S/730 II DM32 7042 MSP CL	-
910925868948	BGP307 LED45-4S/740 I DM11 CLO 48/60S	-


Polar Wide Diagrams



Polar Normal (separate) - BGP307I - 910925864604




Polar Normal (separate) - BGP307I - 910925864592




Polar Normal (separate) - BGP307I - 910925864597


Polar Wide Diagrams




Polar Normal (separate) - BGP3071 -
910925864587




Polar Normal (separate) - BGP3071 -
910925864586




Polar Normal (separate) - BGP3071 -
910925864590




Polar Normal (separate) - BGP3071 -
910925865134




Polar Normal (separate) - BGP3071 -
910925865226




Polar Normal (separate) - BGP3071 -
910925865248



Polar Normal (separate) - BGP3071 -
910925865213




Polar Normal (separate) - BGP3071 -
910925865215




Polar Normal (separate) - BGP3071 -
910925865151


Polar Wide Diagrams




Polar Normal (separate) - BGP3071 - 910925865235




Polar Normal (separate) - BGP3071 - 910925865211




Polar Normal (separate) - BGP3071 - 910925865551




Polar Normal (separate) - BGP3071 - 910925864593




Polar Normal (separate) - BGP3071 - 910925864595




Polar Normal (separate) - BGP3071 - 910925864584



Polar Normal (separate) - BGP3071 - 910925864588




Polar Normal (separate) - BGP3071 - 910925864589




Polar Normal (separate) - BGP3071 - 910925865153


Polar Wide Diagrams




Polar Normal (separate) - BGP3071 - 910925865214




Polar Normal (separate) - BGP3071 - 910925865222




Polar Normal (separate) - BGP3071 - 910925865234




Polar Normal (separate) - BGP3071 - 910925865238




Polar Normal (separate) - BGP3071 - 910925865251




Polar Normal (separate) - BGP3071 - 910925865245



Polar Normal (separate) - BGP3071 - 910925865242




Polar Normal (separate) - BGP3071 - 910925867804




Polar Normal (separate) - BGP3071 - 910925868862


Polar Wide Diagrams




Polar Normal (separate) - BGP3071 - 910925868868




Polar Normal (separate) - BGP3071 - 910925868870




Polar Normal (separate) - BGP3071 - 910925868874




Polar Normal (separate) - BGP3071 - 910925868880




Polar Normal (separate) - BGP3071 - 910925868882




Polar Normal (separate) - BGP3071 - 910925868886



Polar Normal (separate) - BGP3071 - 910925868892




Polar Normal (separate) - BGP3071 - 910925868941




Polar Normal (separate) - BGP3071 - 910925865206


Polar Wide Diagrams




Polar Normal (separate) - BGP3071 - 910925865378




Polar Normal (separate) - BGP3071 - 910925867801




Polar Normal (separate) - BGP3071 - 910925867802




Polar Normal (separate) - 910925865395




Polar Normal (separate) - 910925865397




Polar Normal (separate) - 910925865401



Polar Normal (separate) - 910925865403



Polar Normal (separate) - 910925865402



Polar Normal (separate) - BGP3071 - 910925865391

