



Get your city ready for the future with DigiStreet

DigiStreet

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

Benefits

- Prepared for the future, it is easy to upgrade directly after installation or later with future CMS nodes and sensors to enable new functionalities
- Large availability of lense optics to match international road and street geometries
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information


Features

- Easy luminaire identification due to the Service tag
- High efficacy up to 161 lm/W
- Choice of 30+ different beams and different internal louvers
- Surge protection, 10 kV
- L-tune tool available
- Lifetime 100Khrs up to L96 at Tq +25 °C
- Internal louver (optional)

Application

- Traffic routes and main access road
- Urban and residential area
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings

Dimensional drawing



Product details

Digistreet-BGP760-DP06.tif



Digistreet-BGP760-DP09.tif



Digistreet-BGP760-DP10.tif



Digistreet-BGP760-DP11.tif




Digistreet-BGP761-DP17.tif



Digistreet-BGP761-DP18.tif



Digistreet-BGP761-DP19.tif



Digistreet-BGP761-DP20.tif



Product details



Digistreet-BGP761-DP21.tif



Digistreet-BGP761-DP22.tif



Digistreet-BGP761-DP23.tif



Digistreet-BGP761-DP24.tif



Digistreet-BGP761-DP25.tif



Digistreet-BGP761-DP26.tif

| General Information | |
|--------------------------------|------------|
| Driver included | Yes |
| Light source replaceable | Yes |
| Service tag | Yes |
| Light Technical | |
| Upward light output ratio | 0 |
| Mechanical and Housing | |
| Optical cover type | Flat glass |
| Mech. impact protection code | IK09 |
| Ingress protection code | IP66 |
| Standard tilt angle side entry | 0° |
| Standard tilt angle posttop | 0° |
| Approval and Application | |
| CE mark | Yes |
| Flammability mark | - |

General Information

| Order Code | Full Product Name | Lamp family | | Number of gear units |
|--------------|--|-------------|--------|----------------------|
| | | Gear | code | |
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | - | LED95 | 1 unit |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | - | LED95 | 1 unit |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | - | LED120 | 1 unit |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | - | LED159 | 1 unit |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | - | LED129 | 1 unit |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | - | LED169 | 1 unit |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | - | LED110 | 1 unit |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | - | LED149 | 1 unit |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | - | LED180 | 1 unit |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | - | LED100 | 1 unit |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | - | LED139 | 1 unit |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | - | LED170 | 1 unit |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | - | LED95 | 1 unit |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | - | LED169 | 1 unit |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | - | LED200 | 1 unit |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | - | LED210 | 1 unit |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | - | LED190 | 1 unit |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | - | LED220 | 1 unit |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | - | LED120 | 1 unit |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | - | LED159 | 1 unit |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | - | LED239 | 1 unit |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | - | LED220 | 1 unit |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | - | LED239 | 1 unit |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | - | LED239 | 1 unit |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | - | LED149 | 1 unit |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | - | LED239 | 1 unit |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | EB | LED10 | 1 unit |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | EB | LED12 | 1 unit |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | EB | LED14 | 1 unit |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | EB | LED16 | 1 unit |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | EB | LED22 | 1 unit |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | EB | LED24 | 1 unit |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | EB | LED27 | 1 unit |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | EB | LED30 | 1 unit |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | EB | LED34 | 1 unit |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | EB | LED44 | 1 unit |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | EB | LED49 | 1 unit |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | - | LED24 | 1 unit |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | - | LED44 | 1 unit |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | - | LED16 | 1 unit |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | - | LED16 | 1 unit |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | - | LED60 | 1 unit |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | - | LED60 | 1 unit |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | - | LED60 | 1 unit |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | - | LED49 | 1 unit |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | - | LED49 | 1 unit |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | - | LED280 | 2 units |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | - | LED300 | 2 units |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | - | LED260 | 2 units |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | - | LED340 | 2 units |

| Order Code | Full Product Name | Lamp family | | |
|--------------|--|-------------|--------|----------------------|
| | | Gear | code | Number of gear units |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | - | LED320 | 2 units |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | - | LED260 | 2 units |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | - | LED360 | 2 units |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | - | LED340 | 2 units |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | - | LED360 | 2 units |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | - | LED360 | 2 units |
| 910925865604 | BGP761 LED45-/4S/518 II DM11 DGR 62 | - | LED45 | 1 unit |
| 910925865605 | BGP761 LED45-/4S/420 II DM11 DGR 62 | - | LED45 | 1 unit |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | - | LED45 | 1 unit |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | - | LED74 | 1 unit |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | - | LED94 | 1 unit |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | - | LED109 | 1 unit |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | - | LED55 | 1 unit |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | - | LED84 | 1 unit |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | - | LED55 | 1 unit |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | - | LED84 | 1 unit |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | - | LED50 | 1 unit |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | - | LED79 | 1 unit |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | - | LED59 | 1 unit |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | - | LED90 | 1 unit |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | - | LED74 | 1 unit |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | - | LED84 | 1 unit |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | - | LED119 | 1 unit |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | - | LED119 | 1 unit |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | - | LED84 | 1 unit |

Light Technical (1/2)

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color | Color rendering | Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color | Color rendering |
|--------------|-------------------|-----------------------------|--------------------|-------------------|-----------------|--------------|-------------------|-----------------------------|--------------------|-------------------|-----------------|
| | | | | Temperature (Nom) | index (CRI) | | | | | Temperature (Nom) | index (CRI) |
| 910925865607 | BGP762 | 160° - 42° x | 518 | 1800 K | 50 | 910925866224 | BGP762 | 68° x 158° | 740 | 4000 K | 70 |
| | LED95-/4S/518 II | 53° | ClearStar | | | | LED110-/740 I | | neutral | | |
| | DM11 DGR 62 | | WW | | | | DN10 DGR 32-48 | | white | | |
| 910925865608 | BGP762 | 160° - 42° x | 420 | 2000 K | 40 | 910925866225 | BGP762 | 154° - 31° x | 740 | 4000 K | 70 |
| | LED95-/4S/420 II | 53° | ClearStar | | | | LED149-/740 I | 54° | neutral | | |
| 910925866220 | BGP762 | 53° x 71° | 830 warm | 3000 K | 80 | 910925866226 | BGP762 | 150° - 43° x | 740 | 4000 K | 70 |
| | LED120-/830 II | | white | | | | LED180-/740 I | 67° | neutral | | |
| 910925866221 | BGP762 | - | 830 warm | 3000 K | 80 | 910925866227 | BGP762 | 160° - 42° x | 830 warm | 3000 K | 80 |
| | LED159-/830 II | | white | | | | LED100-/830 II | 54° | white | | |
| 910925866222 | BGP762 | 160° - 42° x | 740 | 4000 K | 70 | 910925866228 | BGP762 | 160° - 42° x | 830 warm | 3000 K | 80 |
| | LED129-/740 I | 54° | neutral | | | | LED139-/830 II | 54° | white | | |
| 910925866223 | BGP762 | 32° x 29° | 740 | 4000 K | 70 | 910925866229 | BGP762 | 61° x 150° | 830 warm | 3000 K | 80 |
| | LED169-/740 I | | neutral | | | | LED170-/830 II | | white | | |
| | DS50 DGR 62 | | white | | | DW10 DGR 76 | | | | | |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | 30° | 740 neutral white | 4000 K | 70 |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | 152° - 24° x 66° | 740 neutral white | 4000 K | 70 |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | 106° x 86° | 740 neutral white | 4000 K | 70 |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | 61° x 150° | 740 neutral white | 4000 K | 70 |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | 61° x 150° | 740 neutral white | 4000 K | 70 |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | 152° - 25° x 66° | 740 neutral white | 4000 K | 70 |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | 151° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | 152° - 25° x 66° | 740 neutral white | 4000 K | 70 |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | 160° - 42° x 54° | 830 warm white | 3000 K | 80 |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | 68° x 157° | 740 neutral white | 4000 K | 70 |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | 53° x 71° | 830 warm white | 3000 K | 80 |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | 154° - 31° x 54° | 740 neutral white | 4000 K | 70 |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | - | 830 warm white | 3000 K | 80 |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | 32° x 29° | 740 neutral white | 4000 K | 70 |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | 61° x 150° | 830 warm white | 3000 K | 80 |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | 150° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | 152° - 24° x 66° | 740 neutral white | 4000 K | 70 |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | 106° x 44° | 740 neutral white | 4000 K | 70 |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|--|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | 160° - 42° x 53° | 518 ClearStar WW | 1800 K | 50 |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | 160° - 42° x 53° | 420 ClearStar NW | 2000 K | 40 |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | 151° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | 152° - 25° x 66° | 740 neutral white | 4000 K | 70 |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |
| 910925867995 | BGP760 LED- HB/740 II DM32 DGR MSP CLO D1 | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | 61° x 150° | 830 warm white | 3000 K | 80 |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | 152° - 24° x 66° | 740 neutral white | 4000 K | 70 |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | 150° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | 61° x 150° | 740 neutral white | 4000 K | 70 |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | 106° x 44° | 740 neutral white | 4000 K | 70 |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | 152° - 25° x 66° | 740 neutral white | 4000 K | 70 |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | 151° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | 152° - 25° x 66° | 740 neutral white | 4000 K | 70 |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | 160° - 42° x 53° | 518 ClearStar WW | 1800 K | 50 |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | 160° - 42° x 53° | 420 ClearStar NW | 2000 K | 40 |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | 154° - 31° x 54° | 740 neutral white | 4000 K | 70 |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | 150° - 43° x 67° | 740 neutral white | 4000 K | 70 |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | 68° x 157° | 740 neutral white | 4000 K | 70 |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | 32° x 29° | 740 neutral white | 4000 K | 70 |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | 160° - 42° x 54° | 740 neutral white | 4000 K | 70 |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | 157° - 33° x 55° | 740 neutral white | 4000 K | 70 |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|--|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | 160° - 42° x 54° | 830 warm white | 3000 K | 80 |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | - | 830 warm white | 3000 K | 80 |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | 53° x 71° | 830 warm white | 3000 K | 80 |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | 61° x 150° | 740 neutral white | 4000 K | 70 |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | 154° - 31° x 54° | 740 neutral white | 4000 K | 70 |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Color rendering index (CRI) |
|--------------|---|-----------------------------|-------------------------|------------------------------------|-----------------------------|
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | 157° - 33° x | 740 neutral white | 4000 K | 70 |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | 157° - 33° x | 740 neutral white | 4000 K | 70 |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | 152° - 25° x | 740 neutral white | 4000 K | 70 |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | 149° - 10° x 57° | 740 neutral white | 4000 K | 70 |

Light Technical (2/2)

| Order Code | Full Product Name | Luminous Flux | Number of light sources | Optic type outdoor |
|--------------|---|---------------|-------------------------|-----------------------------|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | 5,952 lm | - | Distribution medium 11 |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | 5,952 lm | - | Distribution medium 11 |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | 10,800 lm | - | Distribution narrow 11 |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | 13,920 lm | - | Distribution medium 70 |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | 11,830 lm | - | Distribution medium 11 |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | 14,960 lm | - | Distribution symmetrical 50 |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | 10,010 lm | - | Distribution narrow 10 |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | 13,500 lm | - | Distribution medium 50 |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | 15,480 lm | - | Distribution extra wide 10 |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | 9,100 lm | - | Distribution medium 11 |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | 12,740 lm | - | Distribution medium 11 |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | 15,300 lm | - | Distribution wide 10 |

| Order Code | Full Product Name | Luminous Flux | Number of light sources | Optic type outdoor |
|--------------|--|---------------|-------------------------|-----------------------------|
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | 8,640 lm | - | Distribution medium 10 |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | 14,960 lm | - | Distribution symmetrical 50 |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | 17,200 lm | - | Distribution wide 50 |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | 18,060 lm | - | Distribution extra wide 70 |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | 17,100 lm | - | Distribution wide 10 |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | 19,800 lm | - | Distribution wide 10 |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | 10,800 lm | - | Distribution medium 10 |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | 14,240 lm | - | Distribution medium 10 |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 20,700 lm | - | Distribution medium 32 |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | 18,920 lm | - | Distribution wide 50 |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | 19,550 lm | - | Distribution extra wide 10 |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | 13,800 lm | - | Distribution wide 50 |

| Order Code | Full Product Name | Luminous Flux | Number of light sources | Optic type outdoor |
|--------------|---|---------------|-------------------------|-----------------------------|
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | 13,195 lm | - | Distribution medium 32 |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 20,700 lm | - | Distribution medium 32 |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | 900 lm | 1 | Distribution medium 10 |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | 1,092 lm | 1 | Distribution medium 11 |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | 1,274 lm | 1 | Distribution narrow 10 |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | 1,456 lm | 1 | Distribution narrow 11 |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | 2,002 lm | 1 | Distribution medium 50 |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | 2,136 lm | 1 | Distribution medium 70 |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | 2,403 lm | 1 | Distribution symmetrical 50 |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | 2,730 lm | 1 | Distribution wide 10 |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | 2,958 lm | 1 | Distribution extra wide 10 |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | 3,784 lm | 1 | Distribution wide 50 |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | 4,263 lm | 1 | Distribution extra wide 70 |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | 2,070 lm | - | Distribution medium 10 |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | 3,827 lm | - | Distribution medium 10 |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | 992 lm | - | Distribution medium 11 |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | 992 lm | - | Distribution medium 11 |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | 5,340 lm | - | Distribution medium 10 |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | 4,988 lm | - | Distribution extra wide 10 |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | 4,988 lm | - | Distribution wide 50 |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | 3,588 lm | - | Distribution medium 32 |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | 4,900 lm | - | Distribution medium 32 |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | 21,360 lm | - | Distribution wide 10 |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | 25,200 lm | - | Distribution wide 50 |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | 22,100 lm | - | Distribution extra wide 10 |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | 29,920 lm | - | Distribution wide 10 |

| Order Code | Full Product Name | Luminous Flux | Number of light sources | Optic type outdoor |
|--------------|---|---------------|-------------------------|-----------------------------|
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | 26,880 lm | - | Distribution extra wide 70 |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | 23,140 lm | - | Distribution medium 10 |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | 31,320 lm | - | Distribution medium 10 |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | 28,560 lm | - | Distribution medium 50 |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | 28,560 lm | - | Distribution extra wide 10 |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | 20,060 lm | - | Distribution wide 50 |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | 2,790 lm | - | Distribution medium 11 |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | 2,790 lm | - | Distribution medium 11 |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | 4,050 lm | - | Distribution medium 10 |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | 6,660 lm | - | Distribution medium 50 |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | 8,084 lm | - | Distribution extra wide 10 |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | 9,790 lm | - | Distribution medium 10 |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | 5,096 lm | - | Distribution narrow 10 |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | 7,392 lm | - | Distribution symmetrical 50 |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | 5,096 lm | - | Distribution medium 11 |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | 7,476 lm | - | Distribution medium 10 |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | 4,550 lm | - | Distribution medium 11 |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | 6,688 lm | - | Distribution medium 70 |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | 5,400 lm | - | Distribution narrow 11 |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | 8,100 lm | - | Distribution wide 10 |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | 6,660 lm | - | Distribution medium 50 |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | 7,476 lm | - | Distribution medium 10 |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | 10,680 lm | - | Distribution medium 10 |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | 6,900 lm | - | Distribution wide 50 |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | 7,462 lm | - | Distribution medium 32 |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|--|-------------------|--|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | 69 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | 55 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | 81 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | 106 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | 72 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | 98 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | 61 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | 85 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | 100 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | 66 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | 91 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | 114 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | 53 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | 99 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | 114 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | 120 W | Surge protection level until 6 kV differential mode and 8 kV common mode |

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|--|-------------------|--|
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | 106 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | 126 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | 70 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | 91 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 138 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | 126 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | 138 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | 138 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | 86 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | 138 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | 6.8 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | 8 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | 9 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | 11.8 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | 13.8 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | 17 W | Surge protection level until 6 kV differential mode and 8 kV common mode |

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|--|-------------------|--|
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | 16 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | 21 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | 20 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | 26 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | 29.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | 15 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | 26 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | 13.6 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | 11.2 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | 38 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | 37 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | 37 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | 29.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | 33.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | 160 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | 176 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | 150 W | Surge protection level until 6 kV differential mode and 8 kV common mode |

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|--|-------------------|--|
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | 196 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | 182 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | 154 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | 215 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | 196 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | 198 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | 198 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | 34 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | 27.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | 27 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | 43.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | 54 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | 63 W | Surge protection level until 10 kV differential mode and 10 kV common mode |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | 31.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | 49.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | 31.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | 50 W | Surge protection level until 10 kV differential mode and 10 kV common mode |

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|---|-------------------|--|
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | 34 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | 54 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | 41 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | 51 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | 43.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |

| Order Code | Full Product Name | Power Consumption | Surge Protection (Common/Differential) |
|--------------|--|-------------------|--|
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | 49.5 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | 72 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | 70 W | Surge protection level until 6 kV differential mode and 8 kV common mode |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | 50 W | Surge protection level until 6 kV differential mode and 8 kV common mode |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | Yes | Not applicable |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | Yes | Not applicable |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | Yes | Not applicable |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | Yes | 50% |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | No | Not applicable |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | No | Not applicable |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | No | Not applicable |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | No | Not applicable |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | No | Not applicable |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | Yes | Not applicable |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | Yes | Not applicable |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | No | Not applicable |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | Yes | 0% (digital) |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | Yes | Not applicable |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | No | Not applicable |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | No | Not applicable |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | No | Not applicable |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | No | Not applicable |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | Yes | Not applicable |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | No | Not applicable |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | Yes | 0% (digital) |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | Yes | Not applicable |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | Yes | 0% (digital) |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | Yes | 0% (digital) |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | Yes | 50% |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | Yes | 0% (digital) |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | No | Not applicable |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | Yes | Not applicable |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | No | Not applicable |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | Yes | Not applicable |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | No | Not applicable |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | Yes | 50% |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | No | Not applicable |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | No | Not applicable |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | No | Not applicable |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | No | Not applicable |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | No | Not applicable |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | Yes | 50% |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | Yes | 50% |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | Yes | Not applicable |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | Yes | Not applicable |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | Yes | Not applicable |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | Yes | 0% (digital) |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | Yes | 0% (digital) |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | Yes | 50% |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | Yes | 50% |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | No | Not applicable |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | No | Not applicable |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | No | Not applicable |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | No | Not applicable |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | No | Not applicable |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | Yes | Not applicable |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | Yes | Not applicable |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | Yes | Not applicable |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | No | 0% (digital) |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | No | 0% (digital) |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | Yes | Not applicable |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | Yes | Not applicable |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | No | Not applicable |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | No | Not applicable |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | No | Not applicable |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | Yes | 50% |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | No | Not applicable |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | No | Not applicable |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | Yes | Not applicable |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | Yes | 50% |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | Yes | Not applicable |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | Yes | 50% |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | Yes | Not applicable |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | No | Not applicable |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | Yes | Not applicable |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | No | Not applicable |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | Yes | Not applicable |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | Yes | 0% (digital) |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | Yes | 50% |

Mechanical and Housing

| Order Code | Full Product Name | Housing Color |
|--------------|--|---------------|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | Dark gray |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | Dark gray |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | Dark gray |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | Dark gray |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | Dark gray |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | Dark gray |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | Dark gray |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | Dark gray |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | Dark gray |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | Dark gray |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | Dark gray |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | Dark gray |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | Dark gray |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | Dark gray |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | Dark gray |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | Dark gray |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | Dark gray |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | Dark gray |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | Dark gray |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | Dark gray |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | Gray |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | Dark gray |

| Order Code | Full Product Name | Housing Color |
|--------------|--|---------------|
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | Dark gray |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | Dark gray |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | Gray |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | Gray |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | Dark gray |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | Dark gray |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | Dark gray |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | Dark gray |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | Dark gray |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | Dark gray |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | Dark gray |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | Dark gray |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | Dark gray |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | Dark gray |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | Dark gray |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | Dark gray |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | Dark gray |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | Dark gray |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | Dark gray |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | Dark gray |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | Dark gray |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | Dark gray |

| Order Code | Full Product Name | Housing Color |
|--------------|--|---------------|
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | Gray |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | Dark gray |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | Dark gray |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | Dark gray |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | Dark gray |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | Dark gray |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | Dark gray |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | Dark gray |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | Dark gray |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | Dark gray |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | Dark gray |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | Dark gray |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | Dark gray |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | Dark gray |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | Dark gray |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | Dark gray |

| Order Code | Full Product Name | Housing Color |
|--------------|--|---------------|
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | Dark gray |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | Dark gray |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | Dark gray |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | Dark gray |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | Dark gray |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | Dark gray |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | Dark gray |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | Dark gray |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | Dark gray |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | Dark gray |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | Dark gray |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | Dark gray |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | Dark gray |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | Dark gray |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | Gray |

Approval and Application

| Order Code | Full Product Name | Glow-wire test |
|--------------|--|----------------------------------|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | - |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | - |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | - |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | - |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | - |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | - |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | - |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | - |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | - |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | - |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | - |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | - |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | - |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | - |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | - |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | - |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | - |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | - |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | - |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | - |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | - |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | - |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | - |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | - |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | - |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | - |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | Temperature 650 °C, duration 5 s |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | Temperature 650 °C, duration 5 s |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | Temperature 650 °C, duration 5 s |

| Order Code | Full Product Name | Glow-wire test |
|--------------|--|----------------------------------|
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | Temperature 650 °C, duration 5 s |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | Temperature 650 °C, duration 5 s |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | Temperature 650 °C, duration 5 s |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | Temperature 650 °C, duration 5 s |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | Temperature 650 °C, duration 5 s |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | Temperature 650 °C, duration 5 s |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | Temperature 650 °C, duration 5 s |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | Temperature 650 °C, duration 5 s |
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | - |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | - |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | - |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | - |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | - |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | - |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | - |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | - |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | - |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | - |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | - |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | - |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | - |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | - |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | - |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | - |

| Order Code | Full Product Name | Glow-wire test |
|--------------|--|----------------|
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | - |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | - |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | - |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | - |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | - |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | - |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | - |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | - |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | - |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | - |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | - |

| Order Code | Full Product Name | Glow-wire test |
|--------------|--|----------------|
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | - |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | - |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | - |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | - |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | - |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | - |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | - |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | - |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | - |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | - |
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | - |




Product Data

| Order Code | Full Product Name | Product family code |
|--------------|--|---------------------|
| 910925865607 | BGP762 LED95-4S/518 II DM11 DGR 62 | BGP762 |
| 910925865608 | BGP762 LED95-4S/420 II DM11 DGR 62 | BGP762 |
| 910925866220 | BGP762 LED120-/830 II DN11 DGR D11 76 | BGP762 |
| 910925866221 | BGP762 LED159-/830 II DM70 DGR DDF27 D18 | BGP762 |
| 910925866222 | BGP762 LED129-/740 I DM11 DGR 32-48 | BGP762 |
| 910925866223 | BGP762 LED169-/740 I DS50 DGR 62 | BGP762 |
| 910925866224 | BGP762 LED110-/740 I DN10 DGR 32-48 | BGP762 |
| 910925866225 | BGP762 LED149-/740 I DM50 DGR 32-48 | BGP762 |
| 910925866226 | BGP762 LED180-/740 I DX10 DGR 32-48 | BGP762 |
| 910925866227 | BGP762 LED100-/830 II DM11 DGR D9 62 | BGP762 |
| 910925866228 | BGP762 LED139-/830 II DM11 DGR D9 62 | BGP762 |
| 910925866229 | BGP762 LED170-/830 II DW10 DGR 76 | BGP762 |
| 910925866243 | BGP762 LW10 LED95-/740 I DM10 DGR SRB 32 | BGP762 |
| 910925866244 | BGP762 LED169-/740 I DS50 DGR SRB 62 | BGP762 |
| 910925866245 | BGP762 LED200-/740 I DW50 DGR 62 | BGP762 |
| 910925866246 | BGP762 LED210-/740 II DX70 DGR 76 | BGP762 |
| 910925866247 | BGP762 LED190-/740 II DW10 DGR SRG10 62 | BGP762 |
| 910925866252 | BGP762 LED220-/740 II DW10 DGR SRG10 62 | BGP762 |
| 910925866492 | BGP762 LED120/740 I DM10 DGR 62 S | BGP762 |
| 910925866493 | BGP762 LED159/740 I DM10 DGR 62 S | BGP762 |
| 910925866963 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | BGP762 |
| 910925867851 | BGP762 LED220/740 I DW50 DGR D9 62 S | BGP762 |
| 910925867982 | BGP762 LED239/740 I DX10 DGR CLO IACZ-4- | BGP762 |
| 910925867983 | BGP762 LED239/740 I DW50 BL1 DGR CLO IAC | BGP762 |
| 910925867989 | BGP762 LED149/740 II DM32 7042 MSP CLO-D | BGP762 |
| 910925867990 | BGP762 LED239/740 II DM32 7042 MSP CLO-D | BGP762 |
| 910925863554 | BGP760 LED10-/740 I DM10 DGR 32-48 | BGP760 |
| 910925863555 | BGP760 LED12-/830 II DM11 DGR D9 62 | BGP760 |
| 910925863556 | BGP760 LED14-/740 I DN10 DGR 32-48 | BGP760 |
| 910925863557 | BGP760 LED16-/830 II DN11 DGR D11 62 | BGP760 |
| 910925863560 | BGP760 LED22-/740 I DM50 DGR 32-48 | BGP760 |
| 910925863561 | BGP760 LED24-/830 II DM70 DGR DDF27 D18 | BGP760 |
| 910925863562 | BGP760 LED27-/740 I DS50 DGR 32-48 | BGP760 |
| 910925863563 | BGP760 LED30-/830 II DW10 DGR 62 | BGP760 |
| 910925863564 | BGP760 LED34-/740 I DX10 DGR 32-48 | BGP760 |
| 910925863566 | BGP760 LED44-/740 I DW50 DGR 32-48 | BGP760 |
| 910925863567 | BGP760 LED49-/740 II DX70 DGR 62 | BGP760 |

| Order Code | Full Product Name | Product family code |
|--------------|--|---------------------|
| 910925864083 | BGP760 LED24-/740 I DM10 DGR DDF27 D18 S | BGP760 |
| 910925864084 | BGP760 LED44-/740 I DM10 DGR DDF27 D18 S | BGP760 |
| 910925866306 | BGP760 LED16-/518 II DM11 DGR 62 S | BGP760 |
| 910925866307 | BGP760 LED16-/420 II DM11 DGR 62 S | BGP760 |
| 910925866495 | BGP760 LED60-/740 I DM10 DGR 62 S | BGP760 |
| 910925867978 | BGP760 LED60/740 I DX10 DGR CLO IACZ-4-D | BGP760 |
| 910925867979 | BGP760 LED60/740 I DW50 BL1 DGR CLO IACZ | BGP760 |
| 910925867987 | BGP760 LED49/740 II DM32 7042 MSP CLO-DD | BGP760 |
| 910925867995 | BGP760 LED-HB/740 II DM32 DGR MSP CLO D1 | BGP760 |
| 910925866248 | BGP763 LED240-/830 II DW10 DGR SRG10 62 | BGP763 |
| 910925866249 | BGP763 LED300-/740 I DW50 DGR 62 | BGP763 |
| 910925866250 | BGP763 LED260-/740 I DX10 DGR 32-48 | BGP763 |
| 910925866251 | BGP763 LED340-/740 II DW10 DGR SRG10 62 | BGP763 |
| 910925866253 | BGP763 LED320-/740 II DX70 DGR 76 | BGP763 |
| 910925866494 | BGP763 LED260/740 I DM10 DGR 62 S | BGP763 |
| 910925866498 | BGP763 LED360/740 I DM10 DGR 62 S | BGP763 |
| 910925867852 | BGP763 LED340/740 I DW50 DGR D9 62 S | BGP763 |
| 910925867984 | BGP763 LED360/740 I DX10 DGR CLO IACZ-4- | BGP763 |
| 910925867985 | BGP763 LED360/740 I DW50 BL1 DGR IACZ-4- | BGP763 |
| 910925865604 | BGP761 LED45-4S/518 II DM11 DGR 62 | BGP761 |
| 910925865605 | BGP761 LED45-4S/420 II DM11 DGR 62 | BGP761 |
| 910925866230 | BGP761 LED45-/740 I DM10 DGR 32-48 | BGP761 |
| 910925866231 | BGP761 LED74-/740 I DM50 DGR 32-48 | BGP761 |
| 910925866232 | BGP761 LED94-/740 I DX10 DGR 32-48 | BGP761 |
| 910925866233 | BGP761 LED109-/740 I DM10 DGR DDF27 D18 | BGP761 |
| 910925866234 | BGP761 LED55-/740 I DN10 DGR 32-48 | BGP761 |
| 910925866235 | BGP761 LED84-/740 I DS50 DGR 32-48 | BGP761 |
| 910925866236 | BGP761 LED55-/740 I DM11 DGR SRB 62 | BGP761 |
| 910925866237 | BGP761 LED84-/740 I DM10 DGR DDF27 D18 S | BGP761 |
| 910925866238 | BGP761 LED50-/830 II DM11 DGR D9 62 | BGP761 |
| 910925866239 | BGP761 LED79-/830 II DM70 DGR DDF27 D18 | BGP761 |
| 910925866240 | BGP761 LED59-/830 II DN11 DGR D11 62 | BGP761 |
| 910925866241 | BGP761 LED90-/740 II DW10 DGR 62 | BGP761 |
| 910925866242 | BGP761 LED74-/740 I DM50 DGR SRB 62 | BGP761 |
| 910925866496 | BGP761 LED84/740 I DM10 DGR 62 S | BGP761 |
| 910925866497 | BGP761 LED119/740 I DM10 DGR 62 S | BGP761 |
| 910925867981 | BGP761 LED119/740 I DW50 BL1 DGR CLO IAC | BGP761 |

| Order Code | Full Product Name | Product family code |
|--------------|--|---------------------|
| 910925867988 | BGP761 LED84/740 II DM32 7042 MSP CLO-DD | BGP761 |




Polar Wide Diagrams



Polar Normal (separate) - BGP762I - 910925866229

Polar Normal (separate) - BGP761I - 910925866232




Polar Normal (separate) - BGP761I - 910925866242



Polar Normal (separate) - BGP762I - 910925866225

Polar Normal (separate) - BGP763I - 910925866249

Polar Normal (separate) - BGP762I - 910925866228




Polar Normal (separate) - BGP763I - 910925866251


Polar Normal (separate) - BGP762I - 910925866220

Polar Normal (separate) - BGP762I - 910925866221


Polar Wide Diagrams




Polar Normal (separate) - BGP7621 - 910925866246




Polar Normal (separate) - BGP7611 - 910925866497




Polar Normal (separate) - BGP7621 - 910925866492




Polar Normal (separate) - BGP7601 - 910925863562




Polar Normal (separate) - BGP7601 - 910925863561




Polar Normal (separate) - BGP7601 - 910925863564



Polar Normal (separate) - BGP7601 - 910925863554






Polar Normal (separate) - BGP7601 - 910925863567



Polar Normal (separate) - BGP7601 - 910925863563




Polar Wide Diagrams



Polar Normal (separate) - BGP760I - 910925863566

Polar Normal (separate) - BGP760I - 910925863560




Polar Normal (separate) - BGP760I - 910925864083



Polar Normal (separate) - BGP762I - 910925866223

Polar Normal (separate) - BGP761I - 910925866230

Polar Normal (separate) - BGP761I - 910925866238




Polar Normal (separate) - BGP763I - 910925866250


Polar Normal (separate) - BGP762I - 910925866227

Polar Normal (separate) - BGP761I - 910925866233


Polar Wide Diagrams




Polar Normal (separate) - BGP762I - 910925866224




Polar Normal (separate) - BGP761I - 910925866235




Polar Normal (separate) - BGP761I - 910925866241




Polar Normal (separate) - BGP762I - 910925866222




Polar Normal (separate) - BGP761I - 910925866234




Polar Normal (separate) - BGP762I - 910925866247



Polar Normal (separate) - BGP762I - 910925866252






Polar Normal (separate) - BGP763I - 910925866248



Polar Normal (separate) - BGP762I - 910925866226




Polar Wide Diagrams



Polar Normal (separate) - BGP7611 - 910925866237

Polar Normal (separate) - BGP7611 - 910925866239




Polar Normal (separate) - BGP7611 - 910925866240



Polar Normal (separate) - BGP7621 - 910925866245

Polar Normal (separate) - BGP7631 - 910925866253

Polar Normal (separate) - BGP7601 - 910925863556






Polar Normal (separate) - BGP7601 - 910925863557

Polar Normal (separate) - BGP7601 - 910925863555

Polar Normal (separate) - BGP7601 - 910925864084




Polar Wide Diagrams



Polar Normal (separate) - BGP7601 - 910925868855

Polar Normal (separate) - BGP7621 - 910925866493




Polar Normal (separate) - BGP7631 - 910925866494



Polar Normal (separate) - BGP7601 - 910925866495

Polar Normal (separate) - BGP7631 - 910925866498

Polar Normal (separate) - BGP7621 - 910925866963




Polar Normal (separate) - BGP7621 - 910925868786


Polar Normal (separate) - BGP7631 - 910925867852

Polar Normal (separate) - BGP7621 - 910925867851


Polar Wide Diagrams




Polar Normal (separate) - BGP760I - 910925867978




Polar Normal (separate) - BGP760I - 910925867979




Polar Normal (separate) - BGP762I - 910925867982




Polar Normal (separate) - BGP762I - 910925867983




Polar Normal (separate) - BGP761I - 910925867981



Polar Normal (separate) - BGP763I - 910925867984



Polar Normal (separate) - BGP761I - 910925867988



Polar Normal (separate) - BGP760I - 910925867995

