PHILIPS

Lighting



RoadFlair - Sleek and superior Beyond anticipation

RoadFlair

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Benefits

- High lumen efficacy 120 to 140 lumen per watt – much higher than currently available solutions
- Unique functional design Sleek, light-weight and well-designed luminaire
- Control and dimming ready Supports CityTouch connect application, 7-Pin Nema socket and standard outdoor dimming protocols
- Value for money Most competitive product in its segment Perfect for renovation, upgrading projects
- Best-in-class LED lighting technology at an unmatched, competitive price
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

RoadFlair

Features

- Excellent thermal management operating Temperature -40 to 50C
- Exposed Optic - Transparent and weather resistant grade polycarbonate optics
- Multipule optic - Options to meet all road and street lighting application requirements
- Lightweight housing design
- Available in 3000K, 40000K, 5000K and 5700K CCT options
- 10kV or 15kV Surge protection Device

Application


- Pedestrian Road
- Highway Road
- Residential Road
- Interchange

Versions





RoadFlair BRP394 DM


Dimensional drawing





Dimensional drawing














Product details



BRP393 back

General Information	
Driver included	Yes
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>70
Mechanical and Housing	
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP66
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
CE mark	Yes

General Information

Order Code	Full Product Name	Light source replaceable
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	-
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	-
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	-
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	-
911401861398	BRP390 LED81/NW 57W 220-240V DM	No
911401861598	BRP390 LED68/NW 48W 220-240V DM	No
911401861698	BRP390 LED62/NW 46W 220-240V DM	No
911401861798	BRP390 LED56/NW 41W 220-240V DM	No
911401861898	BRP390 LED50/NW 36W 220-240V DM	No
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	No
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	No
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	No
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	No
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	No
911401865198	BRP390 LED76/WW 57W 220-240V DM	No
911401865398	BRP390 LED64/WW 48W 220-240V DM	No
911401865598	BRP390 LED52/WW 41W 220-240V DM	No
911401865698	BRP390 LED46/WW 36W 220-240V DM	No
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	No
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	No
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	No
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	No
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	No
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	No
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	No
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	No
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	No
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	No
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	No
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	No
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	No
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	No
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	No
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	No
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	No
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	No
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	No
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	No
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	No
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	No
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	-
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	-
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	-
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	-

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	740 neutral white	4000 K	2,300 lm
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	740 neutral white	4000 K	3,600 lm
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	740 neutral white	4000 K	6,500 lm
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	740 neutral white	4000 K	10,400 lm
911401861398	BRP390 LED81/NW 57W 220-240V DM	740 neutral white	4000 K	8,123 lm
911401861598	BRP390 LED68/NW 48W 220-240V DM	740 neutral white	4000 K	6,874 lm
911401861698	BRP390 LED62/NW 46W 220-240V DM	740 neutral white	4000 K	6,249 lm
911401861798	BRP390 LED56/NW 41W 220-240V DM	740 neutral white	4000 K	5,624 lm
911401861898	BRP390 LED50/NW 36W 220-240V DM	740 neutral white	4000 K	4,999 lm
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	740 neutral white	4000 K	11,201 lm
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	740 neutral white	4000 K	10,579 lm
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	740 neutral white	4000 K	9,957 lm
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	740 neutral white	4000 K	9,334 lm
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	740 neutral white	4000 K	8,712 lm
911401865198	BRP390 LED76/WW 57W 220-240V DM	730 warm white	3000 K	7,615 lm
911401865398	BRP390 LED64/WW 48W 220-240V DM	730 warm white	3000 K	6,444 lm
911401865598	BRP390 LED52/WW 41W 220-240V DM	730 warm white	3000 K	5,272 lm
911401865698	BRP390 LED46/WW 36W 220-240V DM	730 warm white	3000 K	4,687 lm
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	730 warm white	3000 K	10,501 lm
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	740 neutral white	4000 K	22,495 lm
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	740 neutral white	4000 K	21,246 lm
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	740 neutral white	4000 K	19,914 lm
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	740 neutral white	4000 K	18,669 lm
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	740 neutral white	4000 K	17,425 lm
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	740 neutral white	4000 K	16,179 lm
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	740 neutral white	4000 K	14,935 lm
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	740 neutral white	4000 K	13,690 lm
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	740 neutral white	4000 K	12,446 lm
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	740 neutral white	4000 K	32,360 lm
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	740 neutral white	4000 K	28,626 lm
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	740 neutral white	4000 K	26,136 lm
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	740 neutral white	4000 K	23,647 lm
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	730 warm white	3000 K	21,089 lm
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	730 warm white	3000 K	19,918 lm
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	730 warm white	3000 K	16,336 lm
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	730 warm white	3000 K	15,168 lm
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	730 warm white	3000 K	11,668 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	730 warm white	3000 K	22,169 lm
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	740 neutral white	4000 K	44,991 lm
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	740 neutral white	4000 K	38,583 lm
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	Neutral white	4000 K	7,300 lm
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	Neutral white	4000 K	10,700 lm
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	Neutral white	4000 K	20,100 lm
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	Neutral white	4000 K	30,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	16 W
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	25 W
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	46 W
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	74 W
911401861398	BRP390 LED81/NW 57W 220-240V DM	57 W
911401861598	BRP390 LED68/NW 48W 220-240V DM	48 W
911401861698	BRP390 LED62/NW 46W 220-240V DM	46 W
911401861798	BRP390 LED56/NW 41W 220-240V DM	41 W
911401861898	BRP390 LED50/NW 36W 220-240V DM	36 W
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	80 W
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	75 W
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	70 W
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	67 W
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	63 W
911401865198	BRP390 LED76/WW 57W 220-240V DM	57 W
911401865398	BRP390 LED64/WW 48W 220-240V DM	48 W
911401865598	BRP390 LED52/WW 41W 220-240V DM	41 W
911401865698	BRP390 LED46/WW 36W 220-240V DM	36 W
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	80 W
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	158 W
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	150 W
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	138 W
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	130 W
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	121 W
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	113 W
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	104 W
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	96 W
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	88 W
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	225 W
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	200 W
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	183 W
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	166 W
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	158 W
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	150 W
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	121 W
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	113 W
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	88 W
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	166 W
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	316 W
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	268 W
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	47 W
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	74 W
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	137 W
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	221 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	Yes	-
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	Yes	-
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	Yes	-
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	Yes	-
911401861398	BRP390 LED81/NW 57W 220-240V DM	No	-
911401861598	BRP390 LED68/NW 48W 220-240V DM	No	-
911401861698	BRP390 LED62/NW 46W 220-240V DM	No	-
911401861798	BRP390 LED56/NW 41W 220-240V DM	No	-
911401861898	BRP390 LED50/NW 36W 220-240V DM	No	-
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	Yes	10%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	Yes	10%
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	Yes	10%
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	Yes	10%
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	Yes	10%
911401865198	BRP390 LED76/WW 57W 220-240V DM	No	-
911401865398	BRP390 LED64/WW 48W 220-240V DM	No	-
911401865598	BRP390 LED52/WW 41W 220-240V DM	No	-
911401865698	BRP390 LED46/WW 36W 220-240V DM	No	-
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	Yes	10%
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	Yes	10%
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	Yes	10%
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	Yes	10%
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	Yes	10%
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	Yes	10%
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	Yes	10%
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	Yes	10%
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	Yes	10%
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	Yes	10%
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	Yes	10%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	Yes	10%
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	Yes	10%
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	Yes	10%
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	Yes	10%
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	Yes	10%
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	Yes	10%
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	Yes	10%
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	Yes	10%
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	Yes	10%
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	Yes	10%
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	Yes	10%
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	Yes	-
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	Yes	-
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	Yes	-
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	Polycarbonate
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	Polycarbonate
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	Polycarbonate
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	Polycarbonate
911401861398	BRP390 LED81/NW 57W 220-240V DM	Polycarbonate micro lens optic
911401861598	BRP390 LED68/NW 48W 220-240V DM	Polycarbonate micro lens optic
911401861698	BRP390 LED62/NW 46W 220-240V DM	Polycarbonate micro lens optic

Order Code	Full Product Name	Optical cover type
911401861798	BRP390 LED56/NW 41W 220-240V DM	Polycarbonate micro lens optic
911401861898	BRP390 LED50/NW 36W 220-240V DM	Polycarbonate micro lens optic
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	Polycarbonate micro lens optic
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	Polycarbonate micro lens optic
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	Polycarbonate micro lens optic
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	Polycarbonate micro lens optic
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	Polycarbonate micro lens optic

Order Code	Full Product Name	Optical cover type
911401865198	BRP390 LED76/WW 57W 220-240V DM	Polycarbonate micro lens optic
911401865398	BRP390 LED64/WW 48W 220-240V DM	Polycarbonate micro lens optic
911401865598	BRP390 LED52/WW 41W 220-240V DM	Polycarbonate micro lens optic
911401865698	BRP390 LED46/WW 36W 220-240V DM	Polycarbonate micro lens optic
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	Polycarbonate micro lens optic
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	Polycarbonate micro lens optic
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	Polycarbonate micro lens optic
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	Polycarbonate micro lens optic
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	Polycarbonate micro lens optic
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	Polycarbonate micro lens optic
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	Polycarbonate micro lens optic
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	Polycarbonate micro lens optic
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	Polycarbonate micro lens optic
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	Polycarbonate micro lens optic
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	Polycarbonate micro lens optic
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	Polycarbonate micro lens optic
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	Polycarbonate micro lens optic
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	Polycarbonate micro lens optic
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	Polycarbonate micro lens optic
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	Polycarbonate micro lens optic
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	Polycarbonate micro lens optic
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	Polycarbonate micro lens optic
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	Polycarbonate micro lens optic
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	Polycarbonate micro lens optic
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	Polycarbonate micro lens optic
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	Polycarbonate micro lens optic
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	Clear dome
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	Clear dome
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	Clear dome
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	Clear dome

Approval and Application

Order Code	Full Product Name	Flammability mark
911401667506	BRP391 LED23/NW 16W DWP PSD P7 ANZ	For mounting on normally flammable surfaces
911401667606	BRP391 LED36/NW 25W DWP3 PSD P7 ANZ	For mounting on normally flammable surfaces
911401667706	BRP391 LED65/NW 46W DWV PSD P7 ANZ	For mounting on normally flammable surfaces
911401667806	BRP391 LED104/NW 74W DWV PSD P7 ANZ	For mounting on normally flammable surfaces
911401861398	BRP390 LED81/NW 57W 220-240V DM	For mounting on normally flammable surfaces
911401861598	BRP390 LED68/NW 48W 220-240V DM	For mounting on normally flammable surfaces
911401861698	BRP390 LED62/NW 46W 220-240V DM	For mounting on normally flammable surfaces
911401861798	BRP390 LED56/NW 41W 220-240V DM	For mounting on normally flammable surfaces
911401861898	BRP390 LED50/NW 36W 220-240V DM	For mounting on normally flammable surfaces
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	For mounting on normally flammable surfaces
911401865198	BRP390 LED76/WW 57W 220-240V DM	For mounting on normally flammable surfaces
911401865398	BRP390 LED64/WW 48W 220-240V DM	For mounting on normally flammable surfaces
911401865598	BRP390 LED52/WW 41W 220-240V DM	For mounting on normally flammable surfaces
911401865698	BRP390 LED46/WW 36W 220-240V DM	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	For mounting on normally flammable surfaces
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	For mounting on normally flammable surfaces
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	For mounting on normally flammable surfaces
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	For mounting on normally flammable surfaces
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	For mounting on normally flammable surfaces
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	For mounting on normally flammable surfaces
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	For mounting on normally flammable surfaces
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	For mounting on normally flammable surfaces
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	For mounting on normally flammable surfaces
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	For mounting on normally flammable surfaces
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	For mounting on normally flammable surfaces
911401603608	BRP391 LED73/NW 47W DWV P7T SRB SA LM6	-
911401603708	BRP391 LED107/NW 74W DWV P7T SRB SA LM6	-
911401603808	BRP392 LED201/NW 137W DWV P7T SRB SA LM6	-
911401603908	BRP393 LED305/NW 221W DWV P7T SRB SA LM6	-

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.