



Reliable, Energy saving LED Floodlight

Essential SmartBright G6 LED Floodlight

Essential SmartBright G6 LED Floodlight is the new successor with robust die-cast aluminum housing and corrosion-proof coating which suitable for general outdoor application. Product has high efficacy which is energy saving for customers. Product has anti-siphon function to ensure a reliable performance in the long lifetime.

Benefits

- Reliable quality and performance, complies to CB/CCC & IEC safety standards
- Outstanding savings
- 360 deg rotatable with offset bracket & Easy to install & adjust

Features

- CCT: 3000K, 4000K, 6500K
- Power: 10W, 20W, 30W, 50W, 70W, 100W, 150W and 200W
- Input voltage: 220V-240V
- Lumen efficacy up to 100lm/w
- Working temperature: -40°C to +50°C
- IP65, IK06
- 20khrs life
- PF0.9

Application

- Landscape
- Parking area lighting
- Plaza square
- Architectural lighting
- Security

Essential SmartBright G6 LED Floodlight

Versions

Essential SmartBright G6 LED Floodlight




Essential SmartBright G6 LED Floodlight




Dimensional drawing


BVP150 G4 20W SWB MDU




BVP150 G4 30W SWB MDU




BVP150 G4 50W SWB




BVP150 G4 30W SWB



100W




BVP150 G4 70W SWB




Essential SmartBright G6 LED Floodlight

Dimensional drawing


BVP150 G4 20W SWB




BVP150 G4 50W SWB MDU




200W



BVP150 G4 10W SWB



150W



Essential SmartBright G6 LED Floodlight

General Information

Driver included	Yes
Gear	EB
Number of gear units	1 unit

Light Technical

Color rendering index (CRI)	≥80
Number of light sources	1

Controls and Dimming

Dimmable	-
Maximum dim level	Not applicable

Mechanical and Housing

Optical cover type	Tempered glass
Housing Color	Black
Ingress protection code	IP65

Approval and Application

CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Light Technical

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature		Luminous Flux
				(Nom)		
911401862488	BVP150 LED200/WW PSU 200W SWB G4 CN	110°	830 warm white	3000 K		18,800 lm
911401862588	BVP150 LED200/NW PSU 200W SWB G4 CN	110°	840 neutral white	4000 K		20,000 lm
911401862688	BVP150 LED200/CW PSU 200W SWB G4 CN	110°	865 cool daylight	6500 K		20,000 lm
911401864888	BVP150 LED200/WW PSU 200W SWB G4	110°	830 warm white	3000 K		18,800 lm
911401864988	BVP150 LED200/NW PSU 200W SWB G4	110°	840 neutral white	4000 K		20,000 lm
911401865088	BVP150 LED200/CW PSU 200W SWB G4	110°	865 cool daylight	6500 K		20,000 lm
911401873588	BVP150 LED200/WW PSU 200W SWB G4 MA	110°	830 warm white	3000 K		18,800 lm
911401873688	BVP150 LED200/NW PSU 200W SWB G4 MA	110°	840 neutral white	4000 K		20,000 lm
911401873788	BVP150 LED200/CW PSU 200W SWB G4 MA	110°	865 cool daylight	6500 K		20,000 lm
911401860388	BVP150 LED10/WW PSU 10W SWB G4 CN	100°	830 warm white	3000 K		940 lm
911401860488	BVP150 LED10/NW PSU 10W SWB G4 CN	100°	840 neutral white	4000 K		1,000 lm
911401860588	BVP150 LED10/CW PSU 10W SWB G4 CN	100°	865 cool daylight	6500 K		1,000 lm
911401862788	BVP150 LED10/WW PSU 10W SWB G4	100°	830 warm white	3000 K		940 lm
911401862888	BVP150 LED10/NW PSU 10W SWB G4	100°	840 neutral white	4000 K		1,000 lm
911401862988	BVP150 LED10/CW PSU 10W SWB G4	100°	865 cool daylight	6500 K		1,000 lm
911401871488	BVP150 LED10/WW PSU 10W SWB G4 MA	100°	830 warm white	3000 K		940 lm
911401871588	BVP150 LED10/NW PSU 10W SWB G4 MA	100°	840 neutral white	4000 K		1,000 lm
911401871688	BVP150 LED10/CW PSU 10W SWB G4 MA	100°	865 cool daylight	6500 K		1,000 lm
911401861888	BVP150 LED100/WW PSU 100W SWB G4 CN	110°	830 warm white	3000 K		9,400 lm
911401861988	BVP150 LED100/NW PSU 100W SWB G4 CN	110°	840 neutral white	4000 K		10,000 lm
911401862088	BVP150 LED100/CW PSU 100W SWB G4 CN	110°	865 cool daylight	6500 K		10,000 lm
911401864288	BVP150 LED100/WW PSU 100W SWB G4	110°	830 warm white	3000 K		9,400 lm
911401864388	BVP150 LED100/NW PSU 100W SWB G4	110°	840 neutral white	4000 K		10,000 lm
911401864488	BVP150 LED100/CW PSU 100W SWB G4	110°	865 cool daylight	6500 K		10,000 lm

Essential SmartBright G6 LED Floodlight

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature		Luminous Flux
				(Nom)		
911401872988	BVP150 LED100/WW PSU 100W SWB G4 MA	110°	830 warm white	3000 K		9,400 lm
911401873088	BVP150 LED100/NW PSU 100W SWB G4 MA	110°	840 neutral white	4000 K		10,000 lm
911401873188	BVP150 LED100/CW PSU 100W SWB G4 MA	110°	865 cool daylight	6500 K		10,000 lm
911401862188	BVP150 LED150/WW PSU 150W SWB G4 CN	110°	830 warm white	3000 K		14,100 lm
911401862288	BVP150 LED150/NW PSU 150W SWB G4 CN	110°	840 neutral white	4000 K		15,000 lm
911401862388	BVP150 LED150/CW PSU 150W SWB G4 CN	110°	865 cool daylight	6500 K		15,000 lm
911401864588	BVP150 LED150/WW PSU 150W SWB G4	110°	830 warm white	3000 K		14,100 lm
911401864688	BVP150 LED150/NW PSU 150W SWB G4	110°	840 neutral white	4000 K		15,000 lm
911401864788	BVP150 LED150/CW PSU 150W SWB G4	110°	865 cool daylight	6500 K		15,000 lm
911401873288	BVP150 LED150/WW PSU 150W SWB G4 MA	110°	830 warm white	3000 K		14,100 lm
911401873388	BVP150 LED150/NW PSU 150W SWB G4 MA	110°	840 neutral white	4000 K		15,000 lm
911401873488	BVP150 LED150/CW PSU 150W SWB G4 MA	110°	865 cool daylight	6500 K		15,000 lm
911401861588	BVP150 LED70/WW PSU 70W SWB G4 CN	110°	830 warm white	3000 K		6,580 lm
911401861688	BVP150 LED70/NW PSU 70W SWB G4 CN	110°	840 neutral white	4000 K		7,000 lm
911401861788	BVP150 LED70/CW PSU 70W SWB G4 CN	110°	865 cool daylight	6500 K		7,000 lm
911401863988	BVP150 LED70/WW PSU 70W SWB G4	110°	830 warm white	3000 K		6,580 lm
911401864088	BVP150 LED70/NW PSU 70W SWB G4	110°	840 neutral white	4000 K		7,000 lm
911401864188	BVP150 LED70/CW PSU 70W SWB G4	110°	865 cool daylight	6500 K		7,000 lm
911401872688	BVP150 LED70/WW PSU 70W SWB G4 MA	110°	830 warm white	3000 K		6,580 lm
911401872788	BVP150 LED70/NW PSU 70W SWB G4 MA	110°	840 neutral white	4000 K		7,000 lm
911401872888	BVP150 LED70/CW PSU 70W SWB G4 MA	110°	865 cool daylight	6500 K		7,000 lm
911401861288	BVP150 LED50/WW PSU 50W SWB G4 CN	110°	830 warm white	3000 K		4,700 lm
911401861388	BVP150 LED50/NW PSU 50W SWB G4 CN	110°	840 neutral white	4000 K		5,000 lm
911401861488	BVP150 LED50/CW PSU 50W SWB G4 CN	110°	865 cool daylight	6500 K		5,000 lm
911401863688	BVP150 LED50/WW PSU 50W SWB G4	110°	830 warm white	3000 K		4,700 lm

Essential SmartBright G6 LED Floodlight

Order Code	Full Product Name	Luminaire	Light source	Correlated Color	Luminous Flux
		light beam spread	color	Temperature (Nom)	
911401863788	BVP150 LED50/NW PSU 50W SWB G4	110°	840 neutral white	4000 K	5,000 lm
911401863888	BVP150 LED50/CW PSU 50W SWB G4	110°	865 cool daylight	6500 K	5,000 lm
911401865688	BVP150 LED50/WW PSU 50W SWB MDU G4	110°	830 warm white	3000 K	4,700 lm
911401865788	BVP150 LED50/NW PSU 50W SWB MDU G4	110°	840 neutral white	4000 K	5,000 lm
911401865888	BVP150 LED50/CW PSU 50W SWB MDU G4	110°	865 cool daylight	6500 K	5,000 lm
911401872388	BVP150 LED50/WW PSU 50W SWB G4 MA	110°	830 warm white	3000 K	4,700 lm
911401872488	BVP150 LED50/NW PSU 50W SWB G4 MA	110°	840 neutral white	4000 K	5,000 lm
911401872588	BVP150 LED50/CW PSU 50W SWB G4 MA	110°	865 cool daylight	6500 K	5,000 lm
911401874388	BVP150 LED50/WW PSU 50W SWB MDU G4 MA	110°	830 warm white	3000 K	4,700 lm
911401874488	BVP150 LED50/NW PSU 50W SWB MDU G4 MA	110°	840 neutral white	4000 K	5,000 lm
911401874588	BVP150 LED50/CW PSU 50W SWB MDU G4 MA	110°	865 cool daylight	6500 K	5,000 lm
911401860988	BVP150 LED30/WW PSU 30W SWB G4 CN	110°	830 warm white	3000 K	2,820 lm
911401861088	BVP150 LED30/NW PSU 30W SWB G4 CN	110°	840 neutral white	4000 K	3,000 lm
911401861188	BVP150 LED30/CW PSU 30W SWB G4 CN	110°	865 cool daylight	6500 K	3,000 lm
911401863388	BVP150 LED30/WW PSU 30W SWB G4	110°	830 warm white	3000 K	2,820 lm
911401863488	BVP150 LED30/NW PSU 30W SWB G4	110°	840 neutral white	4000 K	3,000 lm
911401863588	BVP150 LED30/CW PSU 30W SWB G4	110°	865 cool daylight	6500 K	3,000 lm
911401865488	BVP150 LED30/NW PSU 30W SWB MDU G4	110°	840 neutral white	4000 K	3,000 lm
911401865588	BVP150 LED30/CW PSU 30W SWB MDU G4	110°	865 cool daylight	6500 K	3,000 lm
911401872088	BVP150 LED30/WW PSU 30W SWB G4 MA	110°	830 warm white	3000 K	2,820 lm
911401872188	BVP150 LED30/NW PSU 30W SWB G4 MA	110°	840 neutral white	4000 K	3,000 lm
911401872288	BVP150 LED30/CW PSU 30W SWB G4 MA	110°	865 cool daylight	6500 K	3,000 lm
911401874188	BVP150 LED30/NW PSU 30W SWB MDU G4 MA	110°	840 neutral white	4000 K	3,000 lm
911401874288	BVP150 LED30/CW PSU 30W SWB MDU G4 MA	110°	865 cool daylight	6500 K	3,000 lm
911401860688	BVP150 LED20/WW PSU 20W SWB G4 CN	110°	830 warm white	3000 K	1,880 lm

Essential SmartBright G6 LED Floodlight

Order Code	Full Product Name	Luminaire	Light source	Correlated Color	Luminous Flux
		light beam spread	color	Temperature (Nom)	
911401860788	BVP150 LED20/NW PSU 20W SWB G4 CN	110°	840 neutral white	4000 K	2,000 lm
911401860888	BVP150 LED20/CW PSU 20W SWB G4 CN	110°	865 cool daylight	6500 K	2,000 lm
911401863088	BVP150 LED20/WW PSU 20W SWB G4	110°	830 warm white	3000 K	1,880 lm
911401863188	BVP150 LED20/NW PSU 20W SWB G4	110°	840 neutral white	4000 K	2,000 lm
911401863288	BVP150 LED20/CW PSU 20W SWB G4	110°	865 cool daylight	6500 K	2,000 lm
911401865188	BVP150 LED20/WW PSU 20W SWB MDU G4	110°	830 warm white	3000 K	1,880 lm
911401865288	BVP150 LED20/NW PSU 20W SWB MDU G4	110°	840 neutral white	4000 K	2,000 lm
911401865388	BVP150 LED20/CW PSU 20W SWB MDU G4	110°	865 cool daylight	6500 K	2,000 lm
911401871788	BVP150 LED20/WW PSU 20W SWB G4 MA	110°	830 warm white	3000 K	1,880 lm
911401871888	BVP150 LED20/NW PSU 20W SWB G4 MA	110°	840 neutral white	4000 K	2,000 lm
911401871988	BVP150 LED20/CW PSU 20W SWB G4 MA	110°	865 cool daylight	6500 K	2,000 lm
911401873888	BVP150 LED20/WW PSU 20W SWB MDU G4 MA	110°	830 warm white	3000 K	1,880 lm
911401873988	BVP150 LED20/NW PSU 20W SWB MDU G4 MA	110°	840 neutral white	4000 K	2,000 lm
911401874088	BVP150 LED20/CW PSU 20W SWB MDU G4 MA	110°	865 cool daylight	6500 K	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401862488	BVP150 LED200/WW PSU 200W SWB G4 CN	200 W	911401861888	BVP150 LED100/WW PSU 100W SWB G4 CN	100 W
911401862588	BVP150 LED200/NW PSU 200W SWB G4 CN	200 W	911401861988	BVP150 LED100/NW PSU 100W SWB G4 CN	100 W
911401862688	BVP150 LED200/CW PSU 200W SWB G4 CN	200 W	911401862088	BVP150 LED100/CW PSU 100W SWB G4 CN	100 W
911401864888	BVP150 LED200/WW PSU 200W SWB G4	200 W	911401864288	BVP150 LED100/WW PSU 100W SWB G4	100 W
911401864988	BVP150 LED200/NW PSU 200W SWB G4	200 W	911401864388	BVP150 LED100/NW PSU 100W SWB G4	100 W
911401865088	BVP150 LED200/CW PSU 200W SWB G4	200 W	911401864488	BVP150 LED100/CW PSU 100W SWB G4	100 W
911401873588	BVP150 LED200/WW PSU 200W SWB G4 MA	200 W	911401872988	BVP150 LED100/WW PSU 100W SWB G4 MA	100 W
911401873688	BVP150 LED200/NW PSU 200W SWB G4 MA	200 W	911401873088	BVP150 LED100/NW PSU 100W SWB G4 MA	100 W
911401873788	BVP150 LED200/CW PSU 200W SWB G4 MA	200 W	911401873188	BVP150 LED100/CW PSU 100W SWB G4 MA	100 W
911401860388	BVP150 LED10/WW PSU 10W SWB G4 CN	10 W	911401862188	BVP150 LED150/WW PSU 150W SWB G4 CN	150 W
911401860488	BVP150 LED10/NW PSU 10W SWB G4 CN	10 W	911401862288	BVP150 LED150/NW PSU 150W SWB G4 CN	150 W
911401860588	BVP150 LED10/CW PSU 10W SWB G4 CN	10 W	911401862388	BVP150 LED150/CW PSU 150W SWB G4 CN	150 W
911401862788	BVP150 LED10/WW PSU 10W SWB G4	10 W	911401864588	BVP150 LED150/WW PSU 150W SWB G4	150 W
911401862888	BVP150 LED10/NW PSU 10W SWB G4	10 W	911401864688	BVP150 LED150/NW PSU 150W SWB G4	150 W
911401862988	BVP150 LED10/CW PSU 10W SWB G4	10 W	911401864788	BVP150 LED150/CW PSU 150W SWB G4	150 W
911401871488	BVP150 LED10/WW PSU 10W SWB G4 MA	10 W	911401873288	BVP150 LED150/WW PSU 150W SWB G4 MA	150 W
911401871588	BVP150 LED10/NW PSU 10W SWB G4 MA	10 W	911401873388	BVP150 LED150/NW PSU 150W SWB G4 MA	150 W
911401871688	BVP150 LED10/CW PSU 10W SWB G4 MA	10 W	911401873488	BVP150 LED150/CW PSU 150W SWB G4 MA	150 W

Essential SmartBright G6 LED Floodlight

Order Code	Full Product Name	Power Consumption
911401861588	BVP150 LED70/WW PSU 70W SWB G4 CN	70 W
911401861688	BVP150 LED70/NW PSU 70W SWB G4 CN	70 W
911401861788	BVP150 LED70/CW PSU 70W SWB G4 CN	70 W
911401863988	BVP150 LED70/WW PSU 70W SWB G4	70 W
911401864088	BVP150 LED70/NW PSU 70W SWB G4	70 W
911401864188	BVP150 LED70/CW PSU 70W SWB G4	70 W
911401872688	BVP150 LED70/WW PSU 70W SWB G4 MA	70 W
911401872788	BVP150 LED70/NW PSU 70W SWB G4 MA	70 W
911401872888	BVP150 LED70/CW PSU 70W SWB G4 MA	70 W
911401861288	BVP150 LED50/WW PSU 50W SWB G4 CN	50 W
911401861388	BVP150 LED50/NW PSU 50W SWB G4 CN	50 W
911401861488	BVP150 LED50/CW PSU 50W SWB G4 CN	50 W
911401863688	BVP150 LED50/WW PSU 50W SWB G4	50 W
911401863788	BVP150 LED50/NW PSU 50W SWB G4	50 W
911401863888	BVP150 LED50/CW PSU 50W SWB G4	50 W
911401865688	BVP150 LED50/WW PSU 50W SWB MDU G4	50 W
911401865788	BVP150 LED50/NW PSU 50W SWB MDU G4	50 W
911401865888	BVP150 LED50/CW PSU 50W SWB MDU G4	50 W
911401872388	BVP150 LED50/WW PSU 50W SWB G4 MA	50 W
911401872488	BVP150 LED50/NW PSU 50W SWB G4 MA	50 W
911401872588	BVP150 LED50/CW PSU 50W SWB G4 MA	50 W
911401874388	BVP150 LED50/WW PSU 50W SWB MDU G4 MA	50 W
911401874488	BVP150 LED50/NW PSU 50W SWB MDU G4 MA	50 W
911401874588	BVP150 LED50/CW PSU 50W SWB MDU G4 MA	50 W
911401860988	BVP150 LED30/WW PSU 30W SWB G4 CN	30 W
911401861088	BVP150 LED30/NW PSU 30W SWB G4 CN	30 W

Order Code	Full Product Name	Power Consumption
911401861188	BVP150 LED30/CW PSU 30W SWB G4 CN	30 W
911401863388	BVP150 LED30/WW PSU 30W SWB G4	30 W
911401863488	BVP150 LED30/NW PSU 30W SWB G4	30 W
911401863588	BVP150 LED30/CW PSU 30W SWB G4	30 W
911401865488	BVP150 LED30/NW PSU 30W SWB MDU G4	30 W
911401865588	BVP150 LED30/CW PSU 30W SWB MDU G4	30 W
911401872088	BVP150 LED30/WW PSU 30W SWB G4 MA	30 W
911401872188	BVP150 LED30/NW PSU 30W SWB G4 MA	30 W
911401872288	BVP150 LED30/CW PSU 30W SWB G4 MA	30 W
911401874188	BVP150 LED30/NW PSU 30W SWB MDU G4 MA	30 W
911401874288	BVP150 LED30/CW PSU 30W SWB MDU G4 MA	30 W
911401860688	BVP150 LED20/WW PSU 20W SWB G4 CN	20 W
911401860788	BVP150 LED20/NW PSU 20W SWB G4 CN	20 W
911401860888	BVP150 LED20/CW PSU 20W SWB G4 CN	20 W
911401863088	BVP150 LED20/WW PSU 20W SWB G4	20 W
911401863188	BVP150 LED20/NW PSU 20W SWB G4	20 W
911401863288	BVP150 LED20/CW PSU 20W SWB G4	20 W
911401865188	BVP150 LED20/WW PSU 20W SWB MDU G4	20 W
911401865288	BVP150 LED20/NW PSU 20W SWB MDU G4	20 W
911401865388	BVP150 LED20/CW PSU 20W SWB MDU G4	20 W
911401871788	BVP150 LED20/WW PSU 20W SWB G4 MA	20 W
911401871888	BVP150 LED20/NW PSU 20W SWB G4 MA	20 W
911401871988	BVP150 LED20/CW PSU 20W SWB G4 MA	20 W
911401873888	BVP150 LED20/WW PSU 20W SWB MDU G4 MA	20 W
911401873988	BVP150 LED20/NW PSU 20W SWB MDU G4 MA	20 W
911401874088	BVP150 LED20/CW PSU 20W SWB MDU G4 MA	20 W

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
911401862488	BVP150 LED200/WW PSU 200W SWB G4 CN	IK06
911401862588	BVP150 LED200/NW PSU 200W SWB G4 CN	IK06
911401862688	BVP150 LED200/CW PSU 200W SWB G4 CN	IK06
911401864888	BVP150 LED200/WW PSU 200W SWB G4	IK06
911401864988	BVP150 LED200/NW PSU 200W SWB G4	IK06
911401865088	BVP150 LED200/CW PSU 200W SWB G4	IK06
911401873588	BVP150 LED200/WW PSU 200W SWB G4 MA	IK06
911401873688	BVP150 LED200/NW PSU 200W SWB G4 MA	IK06
911401873788	BVP150 LED200/CW PSU 200W SWB G4 MA	IK06
911401860388	BVP150 LED10/WW PSU 10W SWB G4 CN	IK06
911401860488	BVP150 LED10/NW PSU 10W SWB G4 CN	IK06
911401860588	BVP150 LED10/CW PSU 10W SWB G4 CN	IK06
911401862788	BVP150 LED10/WW PSU 10W SWB G4	IK06
911401862888	BVP150 LED10/NW PSU 10W SWB G4	IK06
911401862988	BVP150 LED10/CW PSU 10W SWB G4	IK06
911401871488	BVP150 LED10/WW PSU 10W SWB G4 MA	IK06
911401871588	BVP150 LED10/NW PSU 10W SWB G4 MA	IK06
911401871688	BVP150 LED10/CW PSU 10W SWB G4 MA	IK06
911401861888	BVP150 LED100/WW PSU 100W SWB G4 CN	IK06
911401861988	BVP150 LED100/NW PSU 100W SWB G4 CN	IK06
911401862088	BVP150 LED100/CW PSU 100W SWB G4 CN	IK06

Order Code	Full Product Name	Mech. impact protection code
911401864288	BVP150 LED100/WW PSU 100W SWB G4	IK06
911401864388	BVP150 LED100/NW PSU 100W SWB G4	IK06
911401864488	BVP150 LED100/CW PSU 100W SWB G4	IK06
911401872988	BVP150 LED100/WW PSU 100W SWB G4 MA	IK06
911401873088	BVP150 LED100/NW PSU 100W SWB G4 MA	IK06
911401873188	BVP150 LED100/CW PSU 100W SWB G4 MA	IK06
911401862188	BVP150 LED150/WW PSU 150W SWB G4 CN	IK06
911401862288	BVP150 LED150/NW PSU 150W SWB G4 CN	IK06
911401862388	BVP150 LED150/CW PSU 150W SWB G4 CN	IK06
911401864588	BVP150 LED150/WW PSU 150W SWB G4	IK06
911401864688	BVP150 LED150/NW PSU 150W SWB G4	IK06
911401864788	BVP150 LED150/CW PSU 150W SWB G4	IK06
911401873288	BVP150 LED150/WW PSU 150W SWB G4 MA	IK06
911401873388	BVP150 LED150/NW PSU 150W SWB G4 MA	IK06
911401873488	BVP150 LED150/CW PSU 150W SWB G4 MA	IK06
911401861588	BVP150 LED70/WW PSU 70W SWB G4 CN	IK06
911401861688	BVP150 LED70/NW PSU 70W SWB G4 CN	IK06
911401861788	BVP150 LED70/CW PSU 70W SWB G4 CN	IK06
911401863988	BVP150 LED70/WW PSU 70W SWB G4	IK06
911401864088	BVP150 LED70/NW PSU 70W SWB G4	IK06
911401864188	BVP150 LED70/CW PSU 70W SWB G4	IK06

Essential SmartBright G6 LED Floodlight

Order Code	Full Product Name	Mech. impact protection code
911401872688	BVP150 LED70/WW PSU 70W SWB G4 MA	IK06
911401872788	BVP150 LED70/NW PSU 70W SWB G4 MA	IK06
911401872888	BVP150 LED70/CW PSU 70W SWB G4 MA	IK06
911401861288	BVP150 LED50/WW PSU 50W SWB G4 CN	IK06
911401861388	BVP150 LED50/NW PSU 50W SWB G4 CN	IK06
911401861488	BVP150 LED50/CW PSU 50W SWB G4 CN	IK06
911401863688	BVP150 LED50/WW PSU 50W SWB G4	IK06
911401863788	BVP150 LED50/NW PSU 50W SWB G4	IK06
911401863888	BVP150 LED50/CW PSU 50W SWB G4	IK06
911401865688	BVP150 LED50/WW PSU 50W SWB MDU G4	IK05
911401865788	BVP150 LED50/NW PSU 50W SWB MDU G4	IK05
911401865888	BVP150 LED50/CW PSU 50W SWB MDU G4	IK05
911401872388	BVP150 LED50/WW PSU 50W SWB G4 MA	IK06
911401872488	BVP150 LED50/NW PSU 50W SWB G4 MA	IK06
911401872588	BVP150 LED50/CW PSU 50W SWB G4 MA	IK06
911401874388	BVP150 LED50/WW PSU 50W SWB MDU G4 MA	IK05
911401874488	BVP150 LED50/NW PSU 50W SWB MDU G4 MA	IK05
911401874588	BVP150 LED50/CW PSU 50W SWB MDU G4 MA	IK05
911401860988	BVP150 LED30/WW PSU 30W SWB G4 CN	IK06
911401861088	BVP150 LED30/NW PSU 30W SWB G4 CN	IK06
911401861188	BVP150 LED30/CW PSU 30W SWB G4 CN	IK06
911401863388	BVP150 LED30/WW PSU 30W SWB G4	IK06
911401863488	BVP150 LED30/NW PSU 30W SWB G4	IK06

Order Code	Full Product Name	Mech. impact protection code
911401863588	BVP150 LED30/CW PSU 30W SWB G4	IK06
911401865488	BVP150 LED30/NW PSU 30W SWB MDU G4	IK05
911401865588	BVP150 LED30/CW PSU 30W SWB MDU G4	IK05
911401872088	BVP150 LED30/WW PSU 30W SWB G4 MA	IK06
911401872188	BVP150 LED30/NW PSU 30W SWB G4 MA	IK06
911401872288	BVP150 LED30/CW PSU 30W SWB G4 MA	IK06
911401874188	BVP150 LED30/NW PSU 30W SWB MDU G4 MA	IK05
911401874288	BVP150 LED30/CW PSU 30W SWB MDU G4 MA	IK05
911401860688	BVP150 LED20/WW PSU 20W SWB G4 CN	IK06
911401860788	BVP150 LED20/NW PSU 20W SWB G4 CN	IK06
911401860888	BVP150 LED20/CW PSU 20W SWB G4 CN	IK06
911401863088	BVP150 LED20/WW PSU 20W SWB G4	IK06
911401863188	BVP150 LED20/NW PSU 20W SWB G4	IK06
911401863288	BVP150 LED20/CW PSU 20W SWB G4	IK06
911401865188	BVP150 LED20/WW PSU 20W SWB MDU G4	IK05
911401865288	BVP150 LED20/NW PSU 20W SWB MDU G4	IK05
911401865388	BVP150 LED20/CW PSU 20W SWB MDU G4	IK05
911401871788	BVP150 LED20/WW PSU 20W SWB G4 MA	IK06
911401871888	BVP150 LED20/NW PSU 20W SWB G4 MA	IK06
911401871988	BVP150 LED20/CW PSU 20W SWB G4 MA	IK06
911401873888	BVP150 LED20/WW PSU 20W SWB MDU G4 MA	IK05
911401873988	BVP150 LED20/NW PSU 20W SWB MDU G4 MA	IK05
911401874088	BVP150 LED20/CW PSU 20W SWB MDU G4 MA	IK05

