



Reliable, Energy saving LED Floodlight, CCT Selectable

SmartBright All-in Floodlight

The SmartBright All-in Floodlight comes with a compact and sturdy design. It's a new range with robust die-cast aluminum housing suitable for general outdoor application. CCT selectable is involved that is more convenient for customers' different requirements, saving more time for product selection.

Benefits

- A wide range of applications
- Reliable quality and performance
- Outstanding energy savings
- Easy to install & adjust
- Easier for stock management

Features

- CCT selectable: Warm White (WW), Neutral White (NW) and Cool White (CW) in one package
- Power: 10W, 20W, 30W, 50W, 70W, 100W, 150W and 200W
- Input voltage: 220V-240V
- Lumen efficacy up to 120lm/w
- Working temperature: -25°C to +40°C
- 50khrs life

SmartBright All-in Floodlight

Application

- Warehouses
- Landscape
- Arena and Sports
- Architectural light
- Billboard
- Parking area lighting
- Amenity

Versions



SMARTBRIGHT ALL-IN FLOODLIGHT



SmartBright All-in Floodlight



SmartBright All-in Floodlight



SmartBright All-in Floodlight



SMARTBRIGHT ALL-IN FLOODLIGHT



SmartBright All-in Floodlight



SmartBright All-in Floodlight











SMARTBRIGHT ALL-IN FLOODLIGHT



SMARTBRIGHT ALL-IN FLOODLIGHT









SmartBright All-in Floodlight

Dimensional drawing











SmartBright All-in Floodlight

Dimensional drawing







SmartBright All-in Floodlight

Dimensional drawing



SmartBright All-in Floodlight

Dimensional drawing



Product details



SMARTBRIGHT ALL-IN
FLOODLIGHT



BVP158 CCT switch

SmartBright All-in Floodlight

General Information	
Driver included	Yes
Gear	-
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Mechanical and Housing	
Ingress protection code	IP65
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

General Information

Order Code	Full Product Name	Number of gear units
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	1 unit
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	1 unit
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	1 unit
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	1 unit
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	1 unit
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	1 unit
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	1 unit
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	1 unit
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	-
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	-
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	1 unit
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	1 unit
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	-
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	1 unit
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	1 unit
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	1 unit

Order Code	Full Product Name	Number of gear units
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	1 unit
911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	1 unit
911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	1 unit
911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	1 unit
911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	1 unit
911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	1 unit
911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	1 unit
911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	-
911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	1 unit
911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	1 unit
911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	-
911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	1 unit
911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	1 unit
911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	1 unit
911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	1 unit
911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	1 unit
911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	1 unit

Light Technical

Order Code	Full Product Name	Luminaire light		Color rendering		Number of light sources
		beam spread	Light source color	index (CRI)	Luminous Flux	
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	15,000 lm	1
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	15,000 lm	1
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	110°	3000K/4200K/6500K	80	7,700 lm	1
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	110°	3000K/4200K/6500K	80	7,700 lm	1
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	7,000 lm	1
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	7,000 lm	1
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	110°	3000K/4200K/6500K	80	3,300 lm	1
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	110°	3000K/4200K/6500K	80	3,300 lm	1

SmartBright All-in Floodlight

Order Code	Full Product Name	Luminaire light		Color rendering		Number of light sources
		beam spread	Light source color	index (CRI)	Luminous Flux	
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	-	3000/4000/6500	>80	1,100 lm	-
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	-	3000/4000/6500	>80	2,200 lm	-
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	110°	3000K/4200K/6500K	80	1,100 lm	1
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	110°	3000K/4200K/6500K	80	1,100 lm	1
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	-	3000/4000/6500	>80	3,300 lm	-
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	20,000 lm	1
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	20,000 lm	1
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	3,000 lm	1
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	3,000 lm	1
911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	110°	3000K/4200K/6500K	80	16,500 lm	1
911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	110°	3000K/4200K/6500K	80	16,500 lm	1
911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	110°	3000K/4200K/6500K	80	11,000 lm	1
911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	110°	3000K/4200K/6500K	80	11,000 lm	1
911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	5,000 lm	1
911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	5,000 lm	1
911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	-	3000/4000/6500	>80	7,700 lm	-
911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	92° x 52°	830 warm white and 865 cool daylight	80	10,000 lm	1
911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	92° x 52°	830 warm white and 865 cool daylight	80	10,000 lm	1
911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	-	3000/4000/6500	>80	5,500 lm	-
911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	110°	3000K/4200K/6500K	80	22,000 lm	1
911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	110°	3000K/4200K/6500K	80	22,000 lm	1
911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	110°	3000K/4200K/6500K	80	5,500 lm	1
911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	110°	3000K/4200K/6500K	80	5,500 lm	1
911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	110°	3000K/4200K/6500K	80	2,200 lm	1
911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	110°	3000K/4200K/6500K	80	2,200 lm	1

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	135 W	911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	150 W
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	135 W	911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	150 W
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	70 W	911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	100 W
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	70 W	911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	100 W
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	65 W	911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	45 W
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	65 W	911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	45 W
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	30 W	911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	70 W
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	30 W	911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	90 W
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	10 W	911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	90 W
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	20 W	911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	50 W
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	10 W	911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	200 W
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	10 W	911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	200 W
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	30 W	911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	50 W
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	180 W	911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	50 W
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	180 W	911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	20 W
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	27 W	911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	20 W
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	27 W			

Controls and Dimming

SmartBright All-in Floodlight

Order Code	Full Product Name	Dimmable	Maximum dim level
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	-	Not applicable
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	-	Not applicable
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	No	Not applicable
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	No	Not applicable
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	-	Not applicable
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	-	Not applicable
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	No	Not applicable
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	No	Not applicable
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	No	-
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	No	-
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	No	Not applicable
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	No	Not applicable
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	No	-
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	-	Not applicable
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	-	Not applicable
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	-	Not applicable
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	No	Not applicable
911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	No	Not applicable
911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	No	Not applicable
911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	No	Not applicable
911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	-	Not applicable
911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	-	Not applicable
911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	No	-
911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	-	Not applicable
911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	-	Not applicable
911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	No	-
911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	No	Not applicable
911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	No	Not applicable
911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	No	Not applicable
911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	No	Not applicable
911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	No	Not applicable
911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	Tempered glass	RAL 7043	IK08
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	Tempered glass	RAL 7043	IK08
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	Glass	Grey	IK08
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	Glass	Grey	IK08
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	Tempered glass	RAL 7043	IK08

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	Tempered glass	RAL 7043	IK08
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	Glass	Grey	IK07
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	Glass	Grey	IK07
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	Wide beam	Gray	IK07
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	Wide beam	Gray	IK07

SmartBright All-in Floodlight

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	Glass	Grey	IK07
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	Glass	Grey	IK07
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	Wide beam	Gray	IK07
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	Tempered glass	RAL 7043	IK08
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	Tempered glass	RAL 7043	IK08
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	Tempered glass	RAL 7043	IK07
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	Tempered glass	RAL 7043	IK07
911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	Glass	Grey	IK08
911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	Glass	Grey	IK08
911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	Glass	Grey	IK08
911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	Glass	Grey	IK08
911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	Tempered glass	RAL 7043	IK07

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	Tempered glass	RAL 7043	IK07
911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	Wide beam	Gray	IK08
911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	Tempered glass	RAL 7043	IK08
911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	Tempered glass	RAL 7043	IK08
911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	Wide beam	Gray	IK07
911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	Glass	Grey	IK08
911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	Glass	Grey	IK08
911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	Glass	Grey	IK07
911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	Glass	Grey	IK07
911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	Glass	Grey	IK07
911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	Glass	Grey	IK07

Approval and Application

Order Code	Full Product Name	CE mark	Glow-wire test
911401885186	BVP158 LED157/WW_NW_CW PSU 135W AWB CN	No	Temperature 650 °C, duration 30 s
911401885286	BVP158 LED157/WW_NW_CW PSU 135W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401875186	BVP158 LED84/WW_NW_CW PSU 70W SWB CN	No	Temperature 650 °C, duration 30 s
911401875286	BVP158 LED84/WW_NW_CW PSU 70W SWB GM	No	Temperature 650 °C, duration 30 s
911401883186	BVP158 LED73/WW_NW_CW PSU 65W AWB CN	No	Temperature 650 °C, duration 30 s
911401883286	BVP158 LED73/WW_NW_CW PSU 65W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401873186	BVP158 LED36/WW_NW_CW PSU 30W SWB CN	No	Temperature 650 °C, duration 30 s
911401873286	BVP158 LED36/WW_NW_CW PSU 30W SWB GM	No	Temperature 650 °C, duration 30 s
911401891286	BVP158 LED12/WW_NW_CW PSU 10W SWB MDU GM	No	-
911401892286	BVP158 LED24/WW_NW_CW PSU 20W SWB MDU GM	No	-

Order Code	Full Product Name	CE mark	Glow-wire test
911401871186	BVP158 LED12/WW_NW_CW PSU 10W SWB CN	No	Temperature 650 °C, duration 30 s
911401871286	BVP158 LED12/WW_NW_CW PSU 10W SWB GM	No	Temperature 650 °C, duration 30 s
911401893286	BVP158 LED36/WW_NW_CW PSU 30W SWB MDU GM	No	-
911401886186	BVP158 LED210/WW_NW_CW PSU 180W AWB CN	No	Temperature 650 °C, duration 30 s
911401886286	BVP158 LED210/WW_NW_CW PSU 180W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401881186	BVP158 LED31/WW_NW_CW PSU 27W AWB CN	No	Temperature 650 °C, duration 30 s
911401881286	BVP158 LED31/WW_NW_CW PSU 27W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401877186	BVP158 LED180/WW_NW_CW PSU 150W SWB CN	No	Temperature 650 °C, duration 30 s
911401877286	BVP158 LED180/WW_NW_CW PSU 150W SWB GM	No	Temperature 650 °C, duration 30 s
911401876186	BVP158 LED120/WW_NW_CW PSU 100W SWB CN	No	Temperature 650 °C, duration 30 s

SmartBright All-in Floodlight

Order Code	Full Product Name	CE	
		mark	Glow-wire test
911401876286	BVP158 LED120/WW_NW_CW PSU 100W SWB GM	No	Temperature 650 °C, duration 30 s
911401882186	BVP158 LED52/WW_NW_CW PSU 45W AWB CN	No	Temperature 650 °C, duration 30 s
911401882286	BVP158 LED52/WW_NW_CW PSU 45W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401895286	BVP158 LED84/WW_NW_CW PSU 70W SWB MDU GM	No	-
911401884186	BVP158 LED105/WW_NW_CW PSU 90W AWB CN	No	Temperature 650 °C, duration 30 s
911401884286	BVP158 LED105/WW_NW_CW PSU 90W AWB GM	Yes	Temperature 650 °C, duration 30 s
911401894286	BVP158 LED60/WW_NW_CW PSU 50W SWB MDU GM	No	-

Order Code	Full Product Name	CE	
		mark	Glow-wire test
911401878186	BVP158 LED240/WW_NW_CW PSU 200W SWB CN	No	Temperature 650 °C, duration 30 s
911401878286	BVP158 LED240/WW_NW_CW PSU 200W SWB GM	No	Temperature 650 °C, duration 30 s
911401874186	BVP158 LED60/WW_NW_CW PSU 50W SWB CN	No	Temperature 650 °C, duration 30 s
911401874286	BVP158 LED60/WW_NW_CW PSU 50W SWB GM	No	Temperature 650 °C, duration 30 s
911401872186	BVP158 LED24/WW_NW_CW PSU 20W SWB CN	No	Temperature 650 °C, duration 30 s
911401872286	BVP158 LED24/WW_NW_CW PSU 20W SWB GM	No	Temperature 650 °C, duration 30 s

