



Reliable and high performance LED floodlight

SmartBright LED Floodlight

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards, offering you reliable and long-lasting performance.

Benefits

- Conventional HID floodlight replacement
- Easy to install
- Outstanding energy savings
- High quality and reliability

Features

- Multiple CCT option: 3000K/4000K/5700K
- Multiple power option: 30w/50w/70w/100w/150w/200w
- Long lifetime: 30Khrs(L70B50)
- Wide working temp. range: -40°C ~ +45°C
- High system efficacy: up to 95lm/w

Application

- Architectural lighting
- Landscape lighting
- Billboard lighting
- Parking area lighting
- Amenity
- Security

SmartBright LED Floodlight







Versions



products

products

Dimensional drawing



SmartBright LED Floodlight

General Information

Driver included No

Light Technical

Color rendering index (CRI) >80

Controls and Dimming

Dimmable No

Mechanical and Housing

Optical cover type Polycarbonate
bowl/cover

Housing Color Dark gray

Mech. impact protection code IK07

Ingress protection code IP65

Approval and Application

CE mark Yes

Flammability mark For mounting on
normally
flammable
surfaces

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
911401692907	BVP172 LED43/WW 50W WB GREY CE	730 warm white	3000 K		4,300 lm
911401693207	BVP172 LED43/NW 50W WB GREY CE	740 neutral white	4000 K		4,300 lm
911401693507	BVP172 LED43/CW 50W WB GREY CE	757 cool white	5700 K		4,300 lm
911401693807	BVP171 LED26/WW 30W WB GREY CE	730 warm white	3000 K		2,600 lm
911401694107	BVP171 LED26/NW 30W WB GREY CE	740 neutral white	4000 K		2,600 lm
911401694407	BVP171 LED26/CW 30W WB GREY CE	757 cool white	5700 K		2,600 lm
911401686007	BVP176 LED220/WW 200W WB GREY CE	730 warm white	3000 K		22,000 lm
911401686507	BVP176 LED220/NW 200W WB GREY CE	740 neutral white	4000 K		22,000 lm
911401687007	BVP176 LED220/CW 200W WB GREY CE	757 cool white	5700 K		22,000 lm
911401687507	BVP175 LED170/WW 150W WB GREY CE	730 warm white	3000 K		17,000 lm
911401688007	BVP175 LED170/NW 150W WB GREY CE	740 neutral white	4000 K		17,000 lm
911401688507	BVP175 LED170/CW 150W WB GREY CE	757 cool white	5700 K		17,000 lm
911401689107	BVP174 LED112/WW 100W WB GREY CE	730 warm white	3000 K		11,200 lm
911401689607	BVP174 LED112/NW 100W WB GREY CE	740 neutral white	4000 K		11,200 lm
911401690107	BVP174 LED112/CW 100W WB GREY CE	757 cool white	5700 K		7,800 lm
911401690507	BVP173 LED78/WW 70W WB GREY CE	730 warm white	3000 K		7,800 lm
911401690907	BVP173 LED78/NW 70W WB GREY CE	740 neutral white	4000 K		7,800 lm
911401691307	BVP173 LED78/CW 70W WB GREY CE	757 cool white	5700 K		7,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401692907	BVP172 LED43/WW 50W WB GREY CE	50 W
911401693207	BVP172 LED43/NW 50W WB GREY CE	50 W
911401693507	BVP172 LED43/CW 50W WB GREY CE	50 W
911401693807	BVP171 LED26/WW 30W WB GREY CE	30 W
911401694107	BVP171 LED26/NW 30W WB GREY CE	30 W
911401694407	BVP171 LED26/CW 30W WB GREY CE	30 W
911401686007	BVP176 LED220/WW 200W WB GREY CE	200 W
911401686507	BVP176 LED220/NW 200W WB GREY CE	200 W
911401687007	BVP176 LED220/CW 200W WB GREY CE	200 W

Order Code	Full Product Name	Power Consumption
911401687507	BVP175 LED170/WW 150W WB GREY CE	150 W
911401688007	BVP175 LED170/NW 150W WB GREY CE	150 W
911401688507	BVP175 LED170/CW 150W WB GREY CE	150 W
911401689107	BVP174 LED112/WW 100W WB GREY CE	100 W
911401689607	BVP174 LED112/NW 100W WB GREY CE	100 W
911401690107	BVP174 LED112/CW 100W WB GREY CE	100 W
911401690507	BVP173 LED78/WW 70W WB GREY CE	70 W
911401690907	BVP173 LED78/NW 70W WB GREY CE	70 W
911401691307	BVP173 LED78/CW 70W WB GREY CE	70 W

SmartBright LED Floodlight

