



Architectural LED floodlight for fixed or dynamic lighting.

UniFlood C

UniFlood C is a circular shaped, exterior-rated and cost-effective architectural LED floodlight that is designed for façade, landscape and outdoor flood lighting applications. The robust mechanical design and high-efficiency optical design make it ideal for illuminating multi-story exterior facades, bridges, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Six different spread lenses ranging from narrow spot to wide flood and DMX512/RDM control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Available in White, Monochromatic colors, RGB, RGBW and Tunable White
- Wide Range of Beam Angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design & IP66 for outdoor applications
- Drainage design to reduce dirt and water accumulation
- Available optical distributions: 3.5°, 5°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

UniFlood C

Warnings and Safety

- For outdoor use only

