



Architectural LED floodlight for fixed or dynamic lighting.

UniFlood C

The UniFlood C is a circular, exterior-rated and cost-effective architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting use. The robust mechanical design and high-efficiency optical design make it ideal for illuminating multi-storey exterior facades, bridges, landmarks and monuments. Available in white, monochromatic colours, RGB, RGBW and tunable white. Six different spread lenses ranging from narrow spot to wide flood and a DMX512/RDM control option are available to give architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Wide Range of Beam Angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option
- Compact design

Features

- Robust design and IP66 for outdoor use
- Drainage design to reduce dirt and water accumulation
- Available optical distributions: 3.5°, 5°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for the DMX signal via dedicated cables with IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and squares

UniFlood C

Warnings and Safety

- For outdoor use only

