

UniFlood M G2

BVP353



UniFlood M gen2: A high power floodlight with true modularity

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Applications

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets
- For outdoor use only.

Versions



UniFlood M Gen2



UniFlood M Gen2



UniFlood M Gen2



UniFlood M Gen2



UniFlood M Gen2




UniFlood M Gen2




UniFlood M Gen2


Dimensional drawing




BVP353 12LED 27K 220V L15 45 DMX




BVP353 30LED 30K 220V L30 45




BVP353 48LED 30K 220V L40 45




BVP353 60LED RGBWW 220V L50 15 DMX




UniFlood M Gen2 Dimension Drawing BVP355




BVP353 18LED 40K 220V L21 45 DMX




BVP353 16LED 30K 220V L18 45




UniFlood M Gen2 Dimension Drawing BVP354




BVP353 24LED RGBNW 220V L24 30 DMX




BVP353 36LED 27K 220V L35 15 DMX




UniFlood M Gen2 Dimension Drawing BVP354



UniFlood M Gen2 Dimension Drawing BVP355



BVP353 72LED 27K 220V L57 45



UniFlood M Gen2 Dimension Drawing BVP354

General Information

Driver included Yes

Light Technical

Color rendering index (CRI) >80

Mechanical and Housing

Housing Color Dark gray

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK06 [1 J]

Optical cover type Clear glass

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92607399	BVP353 30LED 27K 220V L30 10	4,515 lm	2700 K	827 warm white
92608099	BVP353 30LED 30K 220V L30 10	4,710 lm	3000 K	830 warm white
92609799	BVP353 30LED 40K 220V L30 10	5,255 lm	4000 K	840 neutral white
92610399	BVP353 30LED 27K 220V L30 10 DMX	4,220 lm	2700 K	827 warm white
92611099	BVP353 30LED 30K 220V L30 10 DMX	4,400 lm	3000 K	830 warm white
92612799	BVP353 30LED 40K 220V L30 10 DMX	4,910 lm	4000 K	840 neutral white
92613499	BVP353 30LED RGB 220V L30 10 DMX	2,495 lm	-	RGB
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	2,855 lm	-	RGBW
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	2,985 lm	-	RGBW
92616599	BVP353 30LED 27K 220V L30 15	4,740 lm	2700 K	827 warm white
92617299	BVP353 30LED 30K 220V L30 15	4,945 lm	3000 K	830 warm white
92618999	BVP353 30LED 40K 220V L30 15	5,520 lm	4000 K	840 neutral white
92619699	BVP353 30LED 27K 220V L30 15 DMX	4,430 lm	2700 K	827 warm white
92620299	BVP353 30LED 30K 220V L30 15 DMX	4,620 lm	3000 K	830 warm white
92621999	BVP353 30LED 40K 220V L30 15 DMX	5,155 lm	4000 K	840 neutral white
92622699	BVP353 30LED RGB 220V L30 15 DMX	2,620 lm	-	RGB
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	3,000 lm	-	RGBW
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	3,130 lm	-	RGBW
92625799	BVP353 30LED 27K 220V L30 30	4,910 lm	2700 K	827 warm white
92626499	BVP353 30LED 30K 220V L30 30	5,125 lm	3000 K	830 warm white
92627199	BVP353 30LED 40K 220V L30 30	5,715 lm	4000 K	840 neutral white
92628899	BVP353 30LED 27K 220V L30 30 DMX	4,585 lm	2700 K	827 warm white
92629599	BVP353 30LED 30K 220V L30 30 DMX	4,785 lm	3000 K	830 warm white
92630199	BVP353 30LED 40K 220V L30 30 DMX	5,340 lm	4000 K	840 neutral white
92631899	BVP353 30LED RGB 220V L30 30 DMX	2,715 lm	-	RGB
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	3,105 lm	-	RGBW
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	3,245 lm	-	RGBW
92634999	BVP353 30LED 27K 220V L30 45	4,740 lm	2700 K	827 warm white
92635699	BVP353 30LED 30K 220V L30 45	4,945 lm	3000 K	830 warm white
92636399	BVP353 30LED 40K 220V L30 45	5,520 lm	4000 K	840 neutral white
92637099	BVP353 30LED 27K 220V L30 45 DMX	4,430 lm	2700 K	827 warm white
92638799	BVP353 30LED 30K 220V L30 45 DMX	4,620 lm	3000 K	830 warm white
92639499	BVP353 30LED 40K 220V L30 45 DMX	5,155 lm	4000 K	840 neutral white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92640099	BVP353 30LED RGB 220V L30 45 DMX	2,620 lm	-	RGB
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	3,000 lm	-	RGBW
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	3,130 lm	-	RGBW
92787200	BVP354 96LED 27K 220V L40 10	15,870 lm	2700 K	827 warm white
92788900	BVP354 96LED 30K 220V L40 10	16,555 lm	3000 K	830 warm white
92789600	BVP354 96LED 40K 220V L40 10	18,470 lm	4000 K	840 neutral white
92790200	BVP354 96LED 27K 220V L40 10 DMX	14,640 lm	2700 K	827 warm white
92791900	BVP354 96LED 30K 220V L40 10 DMX	15,270 lm	3000 K	830 warm white
92792600	BVP354 96LED 40K 220V L40 10 DMX	17,035 lm	4000 K	840 neutral white
92793300	BVP354 96LED RGB 220V L40 10 DMX	8,170 lm	-	RGB
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	10,505 lm	-	RGBW
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	10,975 lm	-	RGBW
92796400	BVP354 96LED 27K 220V L40 15	16,665 lm	2700 K	827 warm white
92797100	BVP354 96LED 30K 220V L40 15	17,385 lm	3000 K	830 warm white
92798800	BVP354 96LED 40K 220V L40 15	19,395 lm	4000 K	840 neutral white
92799500	BVP354 96LED 27K 220V L40 15 DMX	15,370 lm	2700 K	827 warm white
92800800	BVP354 96LED 30K 220V L40 15 DMX	16,035 lm	3000 K	830 warm white
92801500	BVP354 96LED 40K 220V L40 15 DMX	17,890 lm	4000 K	840 neutral white
92802200	BVP354 96LED RGB 220V L40 15 DMX	8,580 lm	-	RGB
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	11,030 lm	-	RGBW
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	11,520 lm	-	RGBW
92805300	BVP354 96LED 27K 220V L40 30	17,260 lm	2700 K	827 warm white
92806000	BVP354 96LED 30K 220V L40 30	18,005 lm	3000 K	830 warm white
92807700	BVP354 96LED 40K 220V L40 30	20,085 lm	4000 K	840 neutral white
92808400	BVP354 96LED 27K 220V L40 30 DMX	15,920 lm	2700 K	827 warm white
92809100	BVP354 96LED 30K 220V L40 30 DMX	16,605 lm	3000 K	830 warm white
92810700	BVP354 96LED 40K 220V L40 30 DMX	18,525 lm	4000 K	840 neutral white
92811400	BVP354 96LED RGB 220V L40 30 DMX	8,885 lm	-	RGB
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	11,425 lm	-	RGBW
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	11,935 lm	-	RGBW
92814500	BVP354 96LED 27K 220V L40 45	16,665 lm	2700 K	827 warm white
92815200	BVP354 96LED 30K 220V L40 45	17,385 lm	3000 K	830 warm white
92816900	BVP354 96LED 40K 220V L40 45	19,395 lm	4000 K	840 neutral white
92817600	BVP354 96LED 27K 220V L40 45 DMX	15,370 lm	2700 K	827 warm white
92818300	BVP354 96LED 30K 220V L40 45 DMX	16,035 lm	3000 K	830 warm white
92819000	BVP354 96LED 40K 220V L40 45 DMX	17,890 lm	4000 K	840 neutral white
92820600	BVP354 96LED RGB 220V L40 45 DMX	8,580 lm	-	RGB
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	11,030 lm	-	RGBW
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	11,520 lm	-	RGBW
92823700	BVP354 120LED 27K 220V L50 10	18,075 lm	2700 K	827 warm white
92824400	BVP354 120LED 30K 220V L50 10	18,850 lm	3000 K	830 warm white
92825100	BVP354 120LED 40K 220V L50 10	21,035 lm	4000 K	840 neutral white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92826800	BVP354 120LED 27K 220V L50 10 DMX	16,880 lm	2700 K	827 warm white
92827500	BVP354 120LED 30K 220V L50 10 DMX	17,605 lm	3000 K	830 warm white
92828200	BVP354 120LED 40K 220V L50 10 DMX	19,645 lm	4000 K	840 neutral white
92829900	BVP354 120LED RGB 220V L50 10 DMX	9,985 lm	-	RGB
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	10,720 lm	-	RGBW
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	11,190 lm	-	RGBW
92832900	BVP354 120LED 27K 220V L50 15	18,975 lm	2700 K	827 warm white
92833600	BVP354 120LED 30K 220V L50 15	19,795 lm	3000 K	830 warm white
92834300	BVP354 120LED 40K 220V L50 15	22,085 lm	4000 K	840 neutral white
92835000	BVP354 120LED 27K 220V L50 15 DMX	17,720 lm	2700 K	827 warm white
92836700	BVP354 120LED 30K 220V L50 15 DMX	18,485 lm	3000 K	830 warm white
92837400	BVP354 120LED 40K 220V L50 15 DMX	20,625 lm	4000 K	840 neutral white
92838100	BVP354 120LED RGB 220V L50 15 DMX	10,485 lm	-	RGB
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	11,255 lm	-	RGBW
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	11,750 lm	-	RGBW
92841100	BVP354 120LED 27K 220V L50 30	19,655 lm	2700 K	827 warm white
92842800	BVP354 120LED 30K 220V L50 30	20,500 lm	3000 K	830 warm white
92843500	BVP354 120LED 40K 220V L50 30	22,875 lm	4000 K	840 neutral white
92844200	BVP354 120LED 27K 220V L50 30 DMX	18,355 lm	2700 K	827 warm white
92845900	BVP354 120LED 30K 220V L50 30 DMX	19,145 lm	3000 K	830 warm white
92846600	BVP354 120LED 40K 220V L50 30 DMX	21,360 lm	4000 K	840 neutral white
92847300	BVP354 120LED RGB 220V L50 30 DMX	10,860 lm	-	RGB
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	11,655 lm	-	RGBW
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	12,170 lm	-	RGBW
92850300	BVP354 120LED 27K 220V L50 45	18,975 lm	2700 K	827 warm white
92851000	BVP354 120LED 30K 220V L50 45	19,795 lm	3000 K	830 warm white
92852700	BVP354 120LED 40K 220V L50 45	22,085 lm	4000 K	840 neutral white
92853400	BVP354 120LED 27K 220V L50 45 DMX	17,720 lm	2700 K	827 warm white
92854100	BVP354 120LED 30K 220V L50 45 DMX	18,485 lm	3000 K	830 warm white
92855800	BVP354 120LED 40K 220V L50 45 DMX	20,625 lm	4000 K	840 neutral white
92856500	BVP354 120LED RGB 220V L50 45 DMX	10,485 lm	-	RGB
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	11,255 lm	-	RGBW
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	11,750 lm	-	RGBW
92859600	BVP354 144LED 27K 220V L57 10	22,765 lm	2700 K	827 warm white
92860200	BVP354 144LED 30K 220V L57 10	23,745 lm	3000 K	830 warm white
92861900	BVP354 144LED 40K 220V L57 10	26,490 lm	4000 K	840 neutral white
92862600	BVP354 144LED 27K 220V L57 10 DMX	21,690 lm	2700 K	827 warm white
92863300	BVP354 144LED 30K 220V L57 10 DMX	22,625 lm	3000 K	830 warm white
92864000	BVP354 144LED 40K 220V L57 10 DMX	25,240 lm	4000 K	840 neutral white
92865700	BVP354 144LED RGB 220V L57 10 DMX	13,410 lm	-	RGB
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	14,395 lm	-	RGBW
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	15,030 lm	-	RGBW

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92868800	BVP354 144LED 27K 220V L57 15	23,900 lm	2700 K	827 warm white
92869500	BVP354 144LED 30K 220V L57 15	24,930 lm	3000 K	830 warm white
92870100	BVP354 144LED 40K 220V L57 15	27,815 lm	4000 K	840 neutral white
92871800	BVP354 144LED 27K 220V L57 15 DMX	22,775 lm	2700 K	827 warm white
92872500	BVP354 144LED 30K 220V L57 15 DMX	23,755 lm	3000 K	830 warm white
92873200	BVP354 144LED 40K 220V L57 15 DMX	26,505 lm	4000 K	840 neutral white
92874900	BVP354 144LED RGB 220V L57 15 DMX	14,080 lm	-	RGB
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	15,115 lm	-	RGBW
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	15,785 lm	-	RGBW
92877000	BVP354 144LED 27K 220V L57 30	24,755 lm	2700 K	827 warm white
92878700	BVP354 144LED 30K 220V L57 30	25,820 lm	3000 K	830 warm white
92879400	BVP354 144LED 40K 220V L57 30	28,810 lm	4000 K	840 neutral white
92880000	BVP354 144LED 27K 220V L57 30 DMX	23,585 lm	2700 K	827 warm white
92881700	BVP354 144LED 30K 220V L57 30 DMX	24,605 lm	3000 K	830 warm white
92882400	BVP354 144LED 40K 220V L57 30 DMX	27,450 lm	4000 K	840 neutral white
92883100	BVP354 144LED RGB 220V L57 30 DMX	14,585 lm	-	RGB
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	15,655 lm	-	RGBW
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	16,345 lm	-	RGBW
92886200	BVP354 144LED 27K 220V L57 45	23,900 lm	2700 K	827 warm white
92887900	BVP354 144LED 30K 220V L57 45	24,930 lm	3000 K	830 warm white
92888600	BVP354 144LED 40K 220V L57 45	27,815 lm	4000 K	840 neutral white
92889300	BVP354 144LED 27K 220V L57 45 DMX	22,775 lm	2700 K	827 warm white
92890900	BVP354 144LED 30K 220V L57 45 DMX	23,755 lm	3000 K	830 warm white
92891600	BVP354 144LED 40K 220V L57 45 DMX	26,505 lm	4000 K	840 neutral white
92892300	BVP354 144LED RGB 220V L57 45 DMX	14,080 lm	-	RGB
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	15,115 lm	-	RGBW
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	15,785 lm	-	RGBW
92751399	BVP353 72LED 27K 220V L57 10	11,380 lm	2700 K	827 warm white
92752099	BVP353 72LED 30K 220V L57 10	11,870 lm	3000 K	830 warm white
92753799	BVP353 72LED 40K 220V L57 10	13,245 lm	4000 K	840 neutral white
92754499	BVP353 72LED 27K 220V L57 10 DMX	10,845 lm	2700 K	827 warm white
92755199	BVP353 72LED 30K 220V L57 10 DMX	11,310 lm	3000 K	830 warm white
92756899	BVP353 72LED 40K 220V L57 10 DMX	12,620 lm	4000 K	840 neutral white
92757599	BVP353 72LED RGB 220V L57 10 DMX	6,705 lm	-	RGB
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	7,195 lm	-	RGBW
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	7,515 lm	-	RGBW
92760599	BVP353 72LED 27K 220V L57 15	11,950 lm	2700 K	827 warm white
92761299	BVP353 72LED 30K 220V L57 15	12,465 lm	3000 K	830 warm white
92762999	BVP353 72LED 40K 220V L57 15	13,905 lm	4000 K	840 neutral white
92763699	BVP353 72LED 27K 220V L57 15 DMX	11,385 lm	2700 K	827 warm white
92764399	BVP353 72LED 30K 220V L57 15 DMX	11,875 lm	3000 K	830 warm white
92765099	BVP353 72LED 40K 220V L57 15 DMX	13,250 lm	4000 K	840 neutral white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92766799	BVP353 72LED RGB 220V L57 15 DMX	7,040 lm	-	RGB
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	7,555 lm	-	RGBW
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	7,890 lm	-	RGBW
92769899	BVP353 72LED 27K 220V L57 30	12,375 lm	2700 K	827 warm white
92770499	BVP353 72LED 30K 220V L57 30	12,910 lm	3000 K	830 warm white
92771199	BVP353 72LED 40K 220V L57 30	14,405 lm	4000 K	840 neutral white
92772899	BVP353 72LED 27K 220V L57 30 DMX	11,790 lm	2700 K	827 warm white
92773599	BVP353 72LED 30K 220V L57 30 DMX	12,300 lm	3000 K	830 warm white
92774299	BVP353 72LED 40K 220V L57 30 DMX	13,725 lm	4000 K	840 neutral white
92775999	BVP353 72LED RGB 220V L57 30 DMX	7,290 lm	-	RGB
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	7,825 lm	-	RGBW
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	8,170 lm	-	RGBW
92778099	BVP353 72LED 27K 220V L57 45	11,950 lm	2700 K	827 warm white
92779799	BVP353 72LED 30K 220V L57 45	12,465 lm	3000 K	830 warm white
92780399	BVP353 72LED 40K 220V L57 45	13,905 lm	4000 K	840 neutral white
92781099	BVP353 72LED 27K 220V L57 45 DMX	11,385 lm	2700 K	827 warm white
92782799	BVP353 72LED 30K 220V L57 45 DMX	11,875 lm	3000 K	830 warm white
92783499	BVP353 72LED 40K 220V L57 45 DMX	13,250 lm	4000 K	840 neutral white
92784199	BVP353 72LED RGB 220V L57 45 DMX	7,040 lm	-	RGB
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	7,555 lm	-	RGBW
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	7,890 lm	-	RGBW
92535999	BVP353 18LED 27K 220V L21 10	2,845 lm	2700 K	827 warm white
92536699	BVP353 18LED 30K 220V L21 10	2,965 lm	3000 K	830 warm white
92537399	BVP353 18LED 40K 220V L21 10	3,310 lm	4000 K	840 neutral white
92538099	BVP353 18LED 27K 220V L21 10 DMX	2,640 lm	2700 K	827 warm white
92539799	BVP353 18LED 30K 220V L21 10 DMX	2,755 lm	3000 K	830 warm white
92540399	BVP353 18LED 40K 220V L21 10 DMX	3,075 lm	4000 K	840 neutral white
92541099	BVP353 18LED RGB 220V L21 10 DMX	1,565 lm	-	RGB
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	1,860 lm	-	RGBW
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	1,945 lm	-	RGBW
92544199	BVP353 18LED 27K 220V L21 15	2,985 lm	2700 K	827 warm white
92545899	BVP353 18LED 30K 220V L21 15	3,115 lm	3000 K	830 warm white
92546599	BVP353 18LED 40K 220V L21 15	3,475 lm	4000 K	840 neutral white
92547299	BVP353 18LED 27K 220V L21 15 DMX	2,770 lm	2700 K	827 warm white
92548999	BVP353 18LED 30K 220V L21 15 DMX	2,890 lm	3000 K	830 warm white
92549699	BVP353 18LED 40K 220V L21 15 DMX	3,225 lm	4000 K	840 neutral white
92550299	BVP353 18LED RGB 220V L21 15 DMX	1,640 lm	-	RGB
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	1,955 lm	-	RGBW
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	2,040 lm	-	RGBW
92553399	BVP353 18LED 27K 220V L21 30	3,090 lm	2700 K	827 warm white
92554099	BVP353 18LED 30K 220V L21 30	3,225 lm	3000 K	830 warm white
92555799	BVP353 18LED 40K 220V L21 30	3,600 lm	4000 K	840 neutral white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92556499	BVP353 18LED 27K 220V L21 30 DMX	2,870 lm	2700 K	827 warm white
92557199	BVP353 18LED 30K 220V L21 30 DMX	2,995 lm	3000 K	830 warm white
92558899	BVP353 18LED 40K 220V L21 30 DMX	3,340 lm	4000 K	840 neutral white
92559599	BVP353 18LED RGB 220V L21 30 DMX	1,700 lm	-	RGB
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	2,025 lm	-	RGBW
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	2,115 lm	-	RGBW
92562599	BVP353 18LED 27K 220V L21 45	2,985 lm	2700 K	827 warm white
92563299	BVP353 18LED 30K 220V L21 45	3,115 lm	3000 K	830 warm white
92564999	BVP353 18LED 40K 220V L21 45	3,475 lm	4000 K	840 neutral white
92565699	BVP353 18LED 27K 220V L21 45 DMX	2,770 lm	2700 K	827 warm white
92566399	BVP353 18LED 30K 220V L21 45 DMX	2,890 lm	3000 K	830 warm white
92567099	BVP353 18LED 40K 220V L21 45 DMX	3,225 lm	4000 K	840 neutral white
92568799	BVP353 18LED RGB 220V L21 45 DMX	1,640 lm	-	RGB
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	1,955 lm	-	RGBW
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	2,040 lm	-	RGBW
92463599	BVP353 12LED 27K 220V L15 10	1,760 lm	2700 K	827 warm white
92464299	BVP353 12LED 30K 220V L15 10	1,835 lm	3000 K	830 warm white
92465999	BVP353 12LED 40K 220V L15 10	2,050 lm	4000 K	840 neutral white
92466699	BVP353 12LED 27K 220V L15 10 DMX	1,615 lm	2700 K	827 warm white
92467399	BVP353 12LED 30K 220V L15 10 DMX	1,685 lm	3000 K	830 warm white
92468099	BVP353 12LED 40K 220V L15 10 DMX	1,880 lm	4000 K	840 neutral white
92469799	BVP353 12LED RGB 220V L15 10 DMX	960 lm	-	RGB
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	1,175 lm	-	RGBW
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	1,225 lm	-	RGBW
92473499	BVP353 12LED 30K 220V L15 15	1,925 lm	3000 K	830 warm white
92481999	BVP353 12LED 27K 220V L15 30	1,915 lm	2700 K	827 warm white
92482699	BVP353 12LED 30K 220V L15 30	1,995 lm	3000 K	830 warm white
92483399	BVP353 12LED 40K 220V L15 30	2,225 lm	4000 K	840 neutral white
92484099	BVP353 12LED 27K 220V L15 30 DMX	1,755 lm	2700 K	827 warm white
92485799	BVP353 12LED 30K 220V L15 30 DMX	1,830 lm	3000 K	830 warm white
92486499	BVP353 12LED 40K 220V L15 30 DMX	2,045 lm	4000 K	840 neutral white
92487199	BVP353 12LED RGB 220V L15 30 DMX	1,045 lm	-	RGB
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	1,275 lm	-	RGBW
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	1,330 lm	-	RGBW
92490199	BVP353 12LED 27K 220V L15 45	1,845 lm	2700 K	827 warm white
92491899	BVP353 12LED 30K 220V L15 45	1,925 lm	3000 K	830 warm white
92492599	BVP353 12LED 40K 220V L15 45	2,150 lm	4000 K	840 neutral white
92493299	BVP353 12LED 27K 220V L15 45 DMX	1,695 lm	2700 K	827 warm white
92494999	BVP353 12LED 30K 220V L15 45 DMX	1,770 lm	3000 K	830 warm white
92495699	BVP353 12LED 40K 220V L15 45 DMX	1,975 lm	4000 K	840 neutral white
92496399	BVP353 12LED RGB 220V L15 45 DMX	1,010 lm	-	RGB
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	1,230 lm	-	RGBW

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	1,285 lm	-	RGBW
92643199	BVP353 36LED 27K 220V L35 10	5,950 lm	2700 K	827 warm white
92644899	BVP353 36LED 30K 220V L35 10	6,205 lm	3000 K	830 warm white
92645599	BVP353 36LED 40K 220V L35 10	6,925 lm	4000 K	840 neutral white
92646299	BVP353 36LED 27K 220V L35 10 DMX	5,350 lm	2700 K	827 warm white
92647999	BVP353 36LED 30K 220V L35 10 DMX	5,585 lm	3000 K	830 warm white
92648699	BVP353 36LED 40K 220V L35 10 DMX	6,230 lm	4000 K	840 neutral white
92649399	BVP353 36LED RGB 220V L35 10 DMX	3,290 lm	-	RGB
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	3,640 lm	-	RGBW
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	3,805 lm	-	RGBW
92652399	BVP353 36LED 27K 220V L35 15	6,245 lm	2700 K	827 warm white
92653099	BVP353 36LED 30K 220V L35 15	6,515 lm	3000 K	830 warm white
92654799	BVP353 36LED 40K 220V L35 15	7,270 lm	4000 K	840 neutral white
92655499	BVP353 36LED 27K 220V L35 15 DMX	5,620 lm	2700 K	827 warm white
92656199	BVP353 36LED 30K 220V L35 15 DMX	5,860 lm	3000 K	830 warm white
92657899	BVP353 36LED 40K 220V L35 15 DMX	6,540 lm	4000 K	840 neutral white
92658599	BVP353 36LED RGB 220V L35 15 DMX	3,455 lm	-	RGB
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	3,825 lm	-	RGBW
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	3,995 lm	-	RGBW
92661599	BVP353 36LED 27K 220V L35 30	6,470 lm	2700 K	827 warm white
92662299	BVP353 36LED 30K 220V L35 30	6,750 lm	3000 K	830 warm white
92663999	BVP353 36LED 40K 220V L35 30	7,530 lm	4000 K	840 neutral white
92664699	BVP353 36LED 27K 220V L35 30 DMX	5,820 lm	2700 K	827 warm white
92665399	BVP353 36LED 30K 220V L35 30 DMX	6,070 lm	3000 K	830 warm white
92666099	BVP353 36LED 40K 220V L35 30 DMX	6,775 lm	4000 K	840 neutral white
92667799	BVP353 36LED RGB 220V L35 30 DMX	3,580 lm	-	RGB
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	3,960 lm	-	RGBW
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	4,135 lm	-	RGBW
92670799	BVP353 36LED 27K 220V L35 45	6,245 lm	2700 K	827 warm white
92671499	BVP353 36LED 30K 220V L35 45	6,515 lm	3000 K	830 warm white
92672199	BVP353 36LED 40K 220V L35 45	7,270 lm	4000 K	840 neutral white
92673899	BVP353 36LED 27K 220V L35 45 DMX	5,620 lm	2700 K	827 warm white
92674599	BVP353 36LED 30K 220V L35 45 DMX	5,860 lm	3000 K	830 warm white
92675299	BVP353 36LED 40K 220V L35 45 DMX	6,540 lm	4000 K	840 neutral white
92676999	BVP353 36LED RGB 220V L35 45 DMX	3,455 lm	-	RGB
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	3,825 lm	-	RGBW
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	3,995 lm	-	RGBW
92571799	BVP353 24LED 27K 220V L24 10	3,615 lm	2700 K	827 warm white
92572499	BVP353 24LED 30K 220V L24 10	3,770 lm	3000 K	830 warm white
92573199	BVP353 24LED 40K 220V L24 10	4,205 lm	4000 K	840 neutral white
92574899	BVP353 24LED 27K 220V L24 10 DMX	3,465 lm	2700 K	827 warm white
92575599	BVP353 24LED 30K 220V L24 10 DMX	3,615 lm	3000 K	830 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92576299	BVP353 24LED 40K 220V L24 10 DMX	4,035 lm	4000 K	840 neutral white
92577999	BVP353 24LED RGB 220V L24 10 DMX	2,085 lm	-	RGB
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	2,350 lm	-	RGBW
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	2,450 lm	-	RGBW
92580999	BVP353 24LED 27K 220V L24 15	3,795 lm	2700 K	827 warm white
92581699	BVP353 24LED 30K 220V L24 15	3,955 lm	3000 K	830 warm white
92582399	BVP353 24LED 40K 220V L24 15	4,415 lm	4000 K	840 neutral white
92583099	BVP353 24LED 27K 220V L24 15 DMX	3,640 lm	2700 K	827 warm white
92584799	BVP353 24LED 30K 220V L24 15 DMX	3,800 lm	3000 K	830 warm white
92585499	BVP353 24LED 40K 220V L24 15 DMX	4,235 lm	4000 K	840 neutral white
92586199	BVP353 24LED RGB 220V L24 15 DMX	2,190 lm	-	RGB
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	2,465 lm	-	RGBW
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	2,575 lm	-	RGBW
92589299	BVP353 24LED 27K 220V L24 30	3,930 lm	2700 K	827 warm white
92590899	BVP353 24LED 30K 220V L24 30	4,100 lm	3000 K	830 warm white
92592299	BVP353 24LED 27K 220V L24 30 DMX	3,770 lm	2700 K	827 warm white
92593999	BVP353 24LED 30K 220V L24 30 DMX	3,935 lm	3000 K	830 warm white
92594699	BVP353 24LED 40K 220V L24 30 DMX	4,390 lm	4000 K	840 neutral white
92595399	BVP353 24LED RGB 220V L24 30 DMX	2,270 lm	-	RGB
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	2,555 lm	-	RGBW
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	2,665 lm	-	RGBW
92598499	BVP353 24LED 27K 220V L24 45	3,795 lm	2700 K	827 warm white
92599199	BVP353 24LED 30K 220V L24 45	3,955 lm	3000 K	830 warm white
92600499	BVP353 24LED 40K 220V L24 45	4,415 lm	4000 K	840 neutral white
92601199	BVP353 24LED 27K 220V L24 45 DMX	3,640 lm	2700 K	827 warm white
92602899	BVP353 24LED 30K 220V L24 45 DMX	3,800 lm	3000 K	830 warm white
92603599	BVP353 24LED 40K 220V L24 45 DMX	4,235 lm	4000 K	840 neutral white
92604299	BVP353 24LED RGB 220V L24 45 DMX	2,190 lm	-	RGB
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	2,465 lm	-	RGBW
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	2,575 lm	-	RGBW
92715599	BVP353 60LED 27K 220V L50 10	9,150 lm	2700 K	827 warm white
92717999	BVP353 60LED 40K 220V L50 10	10,645 lm	4000 K	840 neutral white
92718699	BVP353 60LED 27K 220V L50 10 DMX	8,805 lm	2700 K	827 warm white
92719399	BVP353 60LED 30K 220V L50 10 DMX	9,185 lm	3000 K	830 warm white
92720999	BVP353 60LED 40K 220V L50 10 DMX	10,250 lm	4000 K	840 neutral white
92721699	BVP353 60LED RGB 220V L50 10 DMX	5,215 lm	-	RGB
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	5,995 lm	-	RGBW
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	6,260 lm	-	RGBW
92724799	BVP353 60LED 27K 220V L50 15	9,605 lm	2700 K	827 warm white
92725499	BVP353 60LED 30K 220V L50 15	10,020 lm	3000 K	830 warm white
92726199	BVP353 60LED 40K 220V L50 15	11,180 lm	4000 K	840 neutral white
92727899	BVP353 60LED 27K 220V L50 15 DMX	9,245 lm	2700 K	827 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92728599	BVP353 60LED 30K 220V L50 15 DMX	9,645 lm	3000 K	830 warm white
92729299	BVP353 60LED 40K 220V L50 15 DMX	10,760 lm	4000 K	840 neutral white
92730899	BVP353 60LED RGB 220V L50 15 DMX	5,480 lm	-	RGB
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	6,295 lm	-	RGBW
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	6,575 lm	-	RGBW
92733999	BVP353 60LED 27K 220V L50 30	9,950 lm	2700 K	827 warm white
92734699	BVP353 60LED 30K 220V L50 30	10,380 lm	3000 K	830 warm white
92735399	BVP353 60LED 40K 220V L50 30	11,580 lm	4000 K	840 neutral white
92736099	BVP353 60LED 27K 220V L50 30 DMX	9,575 lm	2700 K	827 warm white
92737799	BVP353 60LED 30K 220V L50 30 DMX	9,990 lm	3000 K	830 warm white
92738499	BVP353 60LED 40K 220V L50 30 DMX	11,145 lm	4000 K	840 neutral white
92739199	BVP353 60LED RGB 220V L50 30 DMX	5,675 lm	-	RGB
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	6,520 lm	-	RGBW
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	6,810 lm	-	RGBW
92742199	BVP353 60LED 27K 220V L50 45	9,605 lm	2700 K	827 warm white
92743899	BVP353 60LED 30K 220V L50 45	10,020 lm	3000 K	830 warm white
92744599	BVP353 60LED 40K 220V L50 45	11,180 lm	4000 K	840 neutral white
92745299	BVP353 60LED 27K 220V L50 45 DMX	9,245 lm	2700 K	827 warm white
92746999	BVP353 60LED 30K 220V L50 45 DMX	9,645 lm	3000 K	830 warm white
92747699	BVP353 60LED 40K 220V L50 45 DMX	10,760 lm	4000 K	840 neutral white
92748399	BVP353 60LED RGB 220V L50 45 DMX	5,480 lm	-	RGB
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	6,295 lm	-	RGBW
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	6,575 lm	-	RGBW
92499499	BVP353 16LED 27K 220V L18 10	2,755 lm	2700 K	827 warm white
92500799	BVP353 16LED 30K 220V L18 10	2,875 lm	3000 K	830 warm white
92501499	BVP353 16LED 40K 220V L18 10	3,205 lm	4000 K	840 neutral white
92502199	BVP353 16LED 27K 220V L18 10 DMX	2,060 lm	2700 K	827 warm white
92503899	BVP353 16LED 30K 220V L18 10 DMX	2,145 lm	3000 K	830 warm white
92504599	BVP353 16LED 40K 220V L18 10 DMX	2,395 lm	4000 K	840 neutral white
92505299	BVP353 15LED RGB 220V L18 10 DMX	1,200 lm	-	RGB
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	1,425 lm	-	RGBW
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	1,490 lm	-	RGBW
92508399	BVP353 16LED 27K 220V L18 15	2,895 lm	2700 K	827 warm white
92509099	BVP353 16LED 30K 220V L18 15	3,020 lm	3000 K	830 warm white
92510699	BVP353 16LED 40K 220V L18 15	3,365 lm	4000 K	840 neutral white
92511399	BVP353 16LED 27K 220V L18 15 DMX	2,160 lm	2700 K	827 warm white
92512099	BVP353 16LED 30K 220V L18 15 DMX	2,255 lm	3000 K	830 warm white
92513799	BVP353 16LED 40K 220V L18 15 DMX	2,515 lm	4000 K	840 neutral white
92514499	BVP353 15LED RGB 220V L18 15 DMX	1,260 lm	-	RGB
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	1,500 lm	-	RGBW
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	1,565 lm	-	RGBW
92517599	BVP353 16LED 27K 220V L18 30	2,995 lm	2700 K	827 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92518299	BVP353 16LED 30K 220V L18 30	3,125 lm	3000 K	830 warm white
92519999	BVP353 16LED 40K 220V L18 30	3,490 lm	4000 K	840 neutral white
92520599	BVP353 16LED 27K 220V L18 30 DMX	2,240 lm	2700 K	827 warm white
92521299	BVP353 16LED 30K 220V L18 30 DMX	2,335 lm	3000 K	830 warm white
92522999	BVP353 16LED 40K 220V L18 30 DMX	2,605 lm	4000 K	840 neutral white
92523699	BVP353 15LED RGB 220V L18 30 DMX	1,305 lm	-	RGB
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	1,550 lm	-	RGBW
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	1,620 lm	-	RGBW
92526799	BVP353 16LED 27K 220V L18 45	2,895 lm	2700 K	827 warm white
92527499	BVP353 16LED 30K 220V L18 45	3,020 lm	3000 K	830 warm white
92528199	BVP353 16LED 40K 220V L18 45	3,365 lm	4000 K	840 neutral white
92529899	BVP353 16LED 27K 220V L18 45 DMX	2,160 lm	2700 K	827 warm white
92530499	BVP353 16LED 30K 220V L18 45 DMX	2,255 lm	3000 K	830 warm white
92531199	BVP353 16LED 40K 220V L18 45 DMX	2,515 lm	4000 K	840 neutral white
92532899	BVP353 15LED RGB 220V L18 45 DMX	1,260 lm	-	RGB
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	1,500 lm	-	RGBW
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	1,565 lm	-	RGBW
92895400	BVP355 216LED 27K 220V L57 10	34,145 lm	2700 K	827 warm white
92896100	BVP355 216LED 30K 220V L57 10	35,615 lm	3000 K	830 warm white
92897800	BVP355 216LED 40K 220V L57 10	39,740 lm	4000 K	840 neutral white
92898500	BVP355 216LED 27K 220V L57 10 DMX	32,535 lm	2700 K	827 warm white
92899200	BVP355 216LED 30K 220V L57 10 DMX	33,935 lm	3000 K	830 warm white
92900500	BVP355 216LED 40K 220V L57 10 DMX	37,860 lm	4000 K	840 neutral white
92901200	BVP355 216LED RGB 220V L57 10 DMX	20,115 lm	-	RGB
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	21,590 lm	-	RGBW
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	22,550 lm	-	RGBW
92904300	BVP355 216LED 27K 220V L57 15	35,850 lm	2700 K	827 warm white
92905000	BVP355 216LED 30K 220V L57 15	37,400 lm	3000 K	830 warm white
92906700	BVP355 216LED 40K 220V L57 15	41,725 lm	4000 K	840 neutral white
92907400	BVP355 216LED 27K 220V L57 15 DMX	34,160 lm	2700 K	827 warm white
92908100	BVP355 216LED 30K 220V L57 15 DMX	35,635 lm	3000 K	830 warm white
92909800	BVP355 216LED 40K 220V L57 15 DMX	39,755 lm	4000 K	840 neutral white
92910400	BVP355 216LED RGB 220V L57 15 DMX	21,120 lm	-	RGB
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	22,670 lm	-	RGBW
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	23,675 lm	-	RGBW
92913500	BVP355 216LED 27K 220V L57 30	37,135 lm	2700 K	827 warm white
92914200	BVP355 216LED 30K 220V L57 30	38,735 lm	3000 K	830 warm white
92915900	BVP355 216LED 40K 220V L57 30	43,215 lm	4000 K	840 neutral white
92916600	BVP355 216LED 27K 220V L57 30 DMX	35,380 lm	2700 K	827 warm white
92917300	BVP355 216LED 30K 220V L57 30 DMX	36,905 lm	3000 K	830 warm white
92918000	BVP355 216LED 40K 220V L57 30 DMX	41,175 lm	4000 K	840 neutral white
92919700	BVP355 216LED RGB 220V L57 30 DMX	21,875 lm	-	RGB

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	23,480 lm	-	RGBW
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	24,520 lm	-	RGBW
92922700	BVP355 216LED 27K 220V L57 45	35,850 lm	2700 K	827 warm white
92923400	BVP355 216LED 30K 220V L57 45	37,400 lm	3000 K	830 warm white
92924100	BVP355 216LED 40K 220V L57 45	41,725 lm	4000 K	840 neutral white
92925800	BVP355 216LED 27K 220V L57 45 DMX	34,160 lm	2700 K	827 warm white
92926500	BVP355 216LED 30K 220V L57 45 DMX	35,635 lm	3000 K	830 warm white
92927200	BVP355 216LED 40K 220V L57 45 DMX	39,755 lm	4000 K	840 neutral white
92928900	BVP355 216LED RGB 220V L57 45 DMX	21,120 lm	-	RGB
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	22,670 lm	-	RGBW
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	23,675 lm	-	RGBW
92931900	BVP355 180LED 27K 220V L50 10	27,450 lm	2700 K	827 warm white
92932600	BVP355 180LED 30K 220V L50 10	28,630 lm	3000 K	830 warm white
92933300	BVP355 180LED 40K 220V L50 10	31,945 lm	4000 K	840 neutral white
92934000	BVP355 180LED 27K 220V L50 10 DMX	26,425 lm	2700 K	827 warm white
92935700	BVP355 180LED 30K 220V L50 10 DMX	27,565 lm	3000 K	830 warm white
92936400	BVP355 180LED 40K 220V L50 10 DMX	30,750 lm	4000 K	840 neutral white
92937100	BVP355 180LED RGB 220V L50 10 DMX	15,655 lm	-	RGB
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	17,990 lm	-	RGBW
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	18,790 lm	-	RGBW
92940100	BVP355 180LED 27K 220V L50 15	28,820 lm	2700 K	827 warm white
92941800	BVP355 180LED 30K 220V L50 15	30,065 lm	3000 K	830 warm white
92942500	BVP355 180LED 40K 220V L50 15	33,540 lm	4000 K	840 neutral white
92943200	BVP355 180LED 27K 220V L50 15 DMX	27,745 lm	2700 K	827 warm white
92944900	BVP355 180LED 30K 220V L50 15 DMX	28,940 lm	3000 K	830 warm white
92945600	BVP355 180LED 40K 220V L50 15 DMX	32,290 lm	4000 K	840 neutral white
92946300	BVP355 180LED RGB 220V L50 15 DMX	16,440 lm	-	RGB
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	18,890 lm	-	RGBW
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	19,730 lm	-	RGBW
92949400	BVP355 180LED 27K 220V L50 30	29,850 lm	2700 K	827 warm white
92950000	BVP355 180LED 30K 220V L50 30	31,140 lm	3000 K	830 warm white
92951700	BVP355 180LED 40K 220V L50 30	34,740 lm	4000 K	840 neutral white
92952400	BVP355 180LED 27K 220V L50 30 DMX	28,735 lm	2700 K	827 warm white
92953100	BVP355 180LED 30K 220V L50 30 DMX	29,975 lm	3000 K	830 warm white
92954800	BVP355 180LED 40K 220V L50 30 DMX	33,445 lm	4000 K	840 neutral white
92955500	BVP355 180LED RGB 220V L50 30 DMX	17,025 lm	-	RGB
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	19,565 lm	-	RGBW
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	20,435 lm	-	RGBW
92958600	BVP355 180LED 27K 220V L50 45	28,820 lm	2700 K	827 warm white
92959300	BVP355 180LED 30K 220V L50 45	30,065 lm	3000 K	830 warm white
92960900	BVP355 180LED 40K 220V L50 45	33,540 lm	4000 K	840 neutral white
92961600	BVP355 180LED 27K 220V L50 45 DMX	27,745 lm	2700 K	827 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
92962300	BVP355 180LED 30K 220V L50 45 DMX	28,940 lm	3000 K	830 warm white
92963000	BVP355 180LED 40K 220V L50 45 DMX	32,290 lm	4000 K	840 neutral white
92964700	BVP355 180LED RGB 220V L50 45 DMX	16,440 lm	-	RGB
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	18,890 lm	-	RGBW
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	19,730 lm	-	RGBW
92679099	BVP353 48LED 27K 220V L40 10	7,440 lm	2700 K	827 warm white
92680699	BVP353 48LED 30K 220V L40 10	7,760 lm	3000 K	830 warm white
92681399	BVP353 48LED 40K 220V L40 10	8,655 lm	4000 K	840 neutral white
92682099	BVP353 48LED 27K 220V L40 10 DMX	6,860 lm	2700 K	827 warm white
92683799	BVP353 48LED 30K 220V L40 10 DMX	7,155 lm	3000 K	830 warm white
92684499	BVP353 48LED 40K 220V L40 10 DMX	7,985 lm	4000 K	840 neutral white
92685199	BVP353 48LED RGB 220V L40 10 DMX	3,830 lm	-	RGB
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	5,250 lm	-	RGBW
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	5,485 lm	-	RGBW
92688299	BVP353 48LED 27K 220V L40 15	7,810 lm	2700 K	827 warm white
92689999	BVP353 48LED 30K 220V L40 15	8,145 lm	3000 K	830 warm white
92690599	BVP353 48LED 40K 220V L40 15	9,090 lm	4000 K	840 neutral white
92691299	BVP353 48LED 27K 220V L40 15 DMX	7,205 lm	2700 K	827 warm white
92692999	BVP353 48LED 30K 220V L40 15 DMX	7,515 lm	3000 K	830 warm white
92693699	BVP353 48LED 40K 220V L40 15 DMX	8,385 lm	4000 K	840 neutral white
92694399	BVP353 48LED RGB 220V L40 15 DMX	4,020 lm	-	RGB
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	5,515 lm	-	RGBW
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	5,760 lm	-	RGBW
92697499	BVP353 48LED 27K 220V L40 30	8,090 lm	2700 K	827 warm white
92698199	BVP353 48LED 30K 220V L40 30	8,440 lm	3000 K	830 warm white
92699899	BVP353 48LED 40K 220V L40 30	9,415 lm	4000 K	840 neutral white
92700199	BVP353 48LED 27K 220V L40 30 DMX	7,460 lm	2700 K	827 warm white
92701899	BVP353 48LED 30K 220V L40 30 DMX	7,785 lm	3000 K	830 warm white
92702599	BVP353 48LED 40K 220V L40 30 DMX	8,685 lm	4000 K	840 neutral white
92703299	BVP353 48LED RGB 220V L40 30 DMX	4,165 lm	-	RGB
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	5,710 lm	-	RGBW
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	5,965 lm	-	RGBW
92706399	BVP353 48LED 27K 220V L40 45	7,810 lm	2700 K	827 warm white
92707099	BVP353 48LED 30K 220V L40 45	8,145 lm	3000 K	830 warm white
92708799	BVP353 48LED 40K 220V L40 45	9,090 lm	4000 K	840 neutral white
92709499	BVP353 48LED 27K 220V L40 45 DMX	7,205 lm	2700 K	827 warm white
92710099	BVP353 48LED 30K 220V L40 45 DMX	7,515 lm	3000 K	830 warm white
92711799	BVP353 48LED 40K 220V L40 45 DMX	8,385 lm	4000 K	840 neutral white
92712499	BVP353 48LED RGB 220V L40 45 DMX	4,020 lm	-	RGB
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	5,515 lm	-	RGBW
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	5,760 lm	-	RGBW

Operating and Electrical

Order Code	Full Product Name	Power Consumption
92607399	BVP353 30LED 27K 220V L30 10	60 W
92608099	BVP353 30LED 30K 220V L30 10	60 W
92609799	BVP353 30LED 40K 220V L30 10	60 W
92610399	BVP353 30LED 27K 220V L30 10 DMX	60 W
92611099	BVP353 30LED 30K 220V L30 10 DMX	60 W
92612799	BVP353 30LED 40K 220V L30 10 DMX	60 W
92613499	BVP353 30LED RGB 220V L30 10 DMX	60 W
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	60 W
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	60 W
92616599	BVP353 30LED 27K 220V L30 15	60 W
92617299	BVP353 30LED 30K 220V L30 15	60 W
92618999	BVP353 30LED 40K 220V L30 15	60 W
92619699	BVP353 30LED 27K 220V L30 15 DMX	60 W
92620299	BVP353 30LED 30K 220V L30 15 DMX	60 W
92621999	BVP353 30LED 40K 220V L30 15 DMX	60 W
92622699	BVP353 30LED RGB 220V L30 15 DMX	60 W
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	60 W
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	60 W
92625799	BVP353 30LED 27K 220V L30 30	60 W
92626499	BVP353 30LED 30K 220V L30 30	60 W
92627199	BVP353 30LED 40K 220V L30 30	60 W
92628899	BVP353 30LED 27K 220V L30 30 DMX	60 W
92629599	BVP353 30LED 30K 220V L30 30 DMX	60 W
92630199	BVP353 30LED 40K 220V L30 30 DMX	60 W
92631899	BVP353 30LED RGB 220V L30 30 DMX	60 W
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	60 W
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	60 W
92634999	BVP353 30LED 27K 220V L30 45	60 W
92635699	BVP353 30LED 30K 220V L30 45	60 W
92636399	BVP353 30LED 40K 220V L30 45	60 W
92637099	BVP353 30LED 27K 220V L30 45 DMX	60 W
92638799	BVP353 30LED 30K 220V L30 45 DMX	60 W
92639499	BVP353 30LED 40K 220V L30 45 DMX	60 W
92640099	BVP353 30LED RGB 220V L30 45 DMX	60 W
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	60 W
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	60 W
92787200	BVP354 96LED 27K 220V L40 10	200 W
92788900	BVP354 96LED 30K 220V L40 10	200 W
92789600	BVP354 96LED 40K 220V L40 10	200 W
92790200	BVP354 96LED 27K 220V L40 10 DMX	200 W
92791900	BVP354 96LED 30K 220V L40 10 DMX	200 W

Order Code	Full Product Name	Power Consumption
92792600	BVP354 96LED 40K 220V L40 10 DMX	200 W
92793300	BVP354 96LED RGB 220V L40 10 DMX	200 W
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	200 W
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	200 W
92796400	BVP354 96LED 27K 220V L40 15	200 W
92797100	BVP354 96LED 30K 220V L40 15	200 W
92798800	BVP354 96LED 40K 220V L40 15	200 W
92799500	BVP354 96LED 27K 220V L40 15 DMX	200 W
92800800	BVP354 96LED 30K 220V L40 15 DMX	200 W
92801500	BVP354 96LED 40K 220V L40 15 DMX	200 W
92802200	BVP354 96LED RGB 220V L40 15 DMX	200 W
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	200 W
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	200 W
92805300	BVP354 96LED 27K 220V L40 30	200 W
92806000	BVP354 96LED 30K 220V L40 30	200 W
92807700	BVP354 96LED 40K 220V L40 30	200 W
92808400	BVP354 96LED 27K 220V L40 30 DMX	200 W
92809100	BVP354 96LED 30K 220V L40 30 DMX	200 W
92810700	BVP354 96LED 40K 220V L40 30 DMX	200 W
92811400	BVP354 96LED RGB 220V L40 30 DMX	200 W
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	200 W
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	200 W
92814500	BVP354 96LED 27K 220V L40 45	200 W
92815200	BVP354 96LED 30K 220V L40 45	200 W
92816900	BVP354 96LED 40K 220V L40 45	200 W
92817600	BVP354 96LED 27K 220V L40 45 DMX	200 W
92818300	BVP354 96LED 30K 220V L40 45 DMX	200 W
92819000	BVP354 96LED 40K 220V L40 45 DMX	200 W
92820600	BVP354 96LED RGB 220V L40 45 DMX	200 W
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	200 W
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
92823700	BVP354 120LED 27K 220V L50 10	240 W
92824400	BVP354 120LED 30K 220V L50 10	240 W
92825100	BVP354 120LED 40K 220V L50 10	240 W
92826800	BVP354 120LED 27K 220V L50 10 DMX	240 W
92827500	BVP354 120LED 30K 220V L50 10 DMX	240 W
92828200	BVP354 120LED 40K 220V L50 10 DMX	240 W
92829900	BVP354 120LED RGB 220V L50 10 DMX	240 W
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	240 W
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	240 W
92832900	BVP354 120LED 27K 220V L50 15	240 W
92833600	BVP354 120LED 30K 220V L50 15	240 W

Order Code	Full Product Name	Power Consumption
92834300	BVP354 120LED 40K 220V L50 15	240 W
92835000	BVP354 120LED 27K 220V L50 15 DMX	240 W
92836700	BVP354 120LED 30K 220V L50 15 DMX	240 W
92837400	BVP354 120LED 40K 220V L50 15 DMX	240 W
92838100	BVP354 120LED RGB 220V L50 15 DMX	240 W
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	240 W
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	240 W
92841100	BVP354 120LED 27K 220V L50 30	240 W
92842800	BVP354 120LED 30K 220V L50 30	240 W
92843500	BVP354 120LED 40K 220V L50 30	240 W
92844200	BVP354 120LED 27K 220V L50 30 DMX	240 W
92845900	BVP354 120LED 30K 220V L50 30 DMX	240 W
92846600	BVP354 120LED 40K 220V L50 30 DMX	240 W
92847300	BVP354 120LED RGB 220V L50 30 DMX	240 W
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	240 W
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	240 W
92850300	BVP354 120LED 27K 220V L50 45	240 W
92851000	BVP354 120LED 30K 220V L50 45	240 W
92852700	BVP354 120LED 40K 220V L50 45	240 W
92853400	BVP354 120LED 27K 220V L50 45 DMX	240 W
92854100	BVP354 120LED 30K 220V L50 45 DMX	240 W
92855800	BVP354 120LED 40K 220V L50 45 DMX	240 W
92856500	BVP354 120LED RGB 220V L50 45 DMX	240 W
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	240 W
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	240 W
92859600	BVP354 144LED 27K 220V L57 10	300 W
92860200	BVP354 144LED 30K 220V L57 10	300 W
92861900	BVP354 144LED 40K 220V L57 10	300 W
92862600	BVP354 144LED 27K 220V L57 10 DMX	300 W
92863300	BVP354 144LED 30K 220V L57 10 DMX	300 W
92864000	BVP354 144LED 40K 220V L57 10 DMX	300 W
92865700	BVP354 144LED RGB 220V L57 10 DMX	300 W
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	300 W
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
92868800	BVP354 144LED 27K 220V L57 15	300 W
92869500	BVP354 144LED 30K 220V L57 15	300 W
92870100	BVP354 144LED 40K 220V L57 15	300 W
92871800	BVP354 144LED 27K 220V L57 15 DMX	300 W
92872500	BVP354 144LED 30K 220V L57 15 DMX	300 W
92873200	BVP354 144LED 40K 220V L57 15 DMX	300 W
92874900	BVP354 144LED RGB 220V L57 15 DMX	300 W
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	300 W

Order Code	Full Product Name	Power Consumption
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	300 W
92877000	BVP354 144LED 27K 220V L57 30	300 W
92878700	BVP354 144LED 30K 220V L57 30	300 W
92879400	BVP354 144LED 40K 220V L57 30	300 W
92880000	BVP354 144LED 27K 220V L57 30 DMX	300 W
92881700	BVP354 144LED 30K 220V L57 30 DMX	300 W
92882400	BVP354 144LED 40K 220V L57 30 DMX	300 W
92883100	BVP354 144LED RGB 220V L57 30 DMX	300 W
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	300 W
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	300 W
92886200	BVP354 144LED 27K 220V L57 45	300 W
92887900	BVP354 144LED 30K 220V L57 45	300 W
92888600	BVP354 144LED 40K 220V L57 45	300 W
92889300	BVP354 144LED 27K 220V L57 45 DMX	300 W
92890900	BVP354 144LED 30K 220V L57 45 DMX	300 W
92891600	BVP354 144LED 40K 220V L57 45 DMX	300 W
92892300	BVP354 144LED RGB 220V L57 45 DMX	300 W
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	300 W
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
92751399	BVP353 72LED 27K 220V L57 10	150 W
92752099	BVP353 72LED 30K 220V L57 10	150 W
92753799	BVP353 72LED 40K 220V L57 10	150 W
92754499	BVP353 72LED 27K 220V L57 10 DMX	150 W
92755199	BVP353 72LED 30K 220V L57 10 DMX	150 W
92756899	BVP353 72LED 40K 220V L57 10 DMX	150 W
92757599	BVP353 72LED RGB 220V L57 10 DMX	150 W
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
92760599	BVP353 72LED 27K 220V L57 15	150 W
92761299	BVP353 72LED 30K 220V L57 15	150 W
92762999	BVP353 72LED 40K 220V L57 15	150 W
92763699	BVP353 72LED 27K 220V L57 15 DMX	150 W
92764399	BVP353 72LED 30K 220V L57 15 DMX	150 W
92765099	BVP353 72LED 40K 220V L57 15 DMX	150 W
92766799	BVP353 72LED RGB 220V L57 15 DMX	150 W
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
92769899	BVP353 72LED 27K 220V L57 30	150 W
92770499	BVP353 72LED 30K 220V L57 30	150 W
92771199	BVP353 72LED 40K 220V L57 30	150 W
92772899	BVP353 72LED 27K 220V L57 30 DMX	150 W
92773599	BVP353 72LED 30K 220V L57 30 DMX	150 W

Order Code	Full Product Name	Power Consumption
92774299	BVP353 72LED 40K 220V L57 30 DMX	150 W
92775999	BVP353 72LED RGB 220V L57 30 DMX	150 W
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
92778099	BVP353 72LED 27K 220V L57 45	150 W
92779799	BVP353 72LED 30K 220V L57 45	150 W
92780399	BVP353 72LED 40K 220V L57 45	150 W
92781099	BVP353 72LED 27K 220V L57 45 DMX	150 W
92782799	BVP353 72LED 30K 220V L57 45 DMX	150 W
92783499	BVP353 72LED 40K 220V L57 45 DMX	150 W
92784199	BVP353 72LED RGB 220V L57 45 DMX	150 W
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
92535999	BVP353 18LED 27K 220V L21 10	40 W
92536699	BVP353 18LED 30K 220V L21 10	40 W
92537399	BVP353 18LED 40K 220V L21 10	40 W
92538099	BVP353 18LED 27K 220V L21 10 DMX	40 W
92539799	BVP353 18LED 30K 220V L21 10 DMX	40 W
92540399	BVP353 18LED 40K 220V L21 10 DMX	40 W
92541099	BVP353 18LED RGB 220V L21 10 DMX	40 W
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	40 W
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
92544199	BVP353 18LED 27K 220V L21 15	40 W
92545899	BVP353 18LED 30K 220V L21 15	40 W
92546599	BVP353 18LED 40K 220V L21 15	40 W
92547299	BVP353 18LED 27K 220V L21 15 DMX	40 W
92548999	BVP353 18LED 30K 220V L21 15 DMX	40 W
92549699	BVP353 18LED 40K 220V L21 15 DMX	40 W
92550299	BVP353 18LED RGB 220V L21 15 DMX	40 W
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	40 W
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
92553399	BVP353 18LED 27K 220V L21 30	40 W
92554099	BVP353 18LED 30K 220V L21 30	40 W
92555799	BVP353 18LED 40K 220V L21 30	40 W
92556499	BVP353 18LED 27K 220V L21 30 DMX	40 W
92557199	BVP353 18LED 30K 220V L21 30 DMX	40 W
92558899	BVP353 18LED 40K 220V L21 30 DMX	40 W
92559599	BVP353 18LED RGB 220V L21 30 DMX	40 W
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	40 W
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
92562599	BVP353 18LED 27K 220V L21 45	40 W
92563299	BVP353 18LED 30K 220V L21 45	40 W

Order Code	Full Product Name	Power Consumption
92564999	BVP353 18LED 40K 220V L21 45	40 W
92565699	BVP353 18LED 27K 220V L21 45 DMX	40 W
92566399	BVP353 18LED 30K 220V L21 45 DMX	40 W
92567099	BVP353 18LED 40K 220V L21 45 DMX	40 W
92568799	BVP353 18LED RGB 220V L21 45 DMX	40 W
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	40 W
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	40 W
92463599	BVP353 12LED 27K 220V L15 10	24 W
92464299	BVP353 12LED 30K 220V L15 10	24 W
92465999	BVP353 12LED 40K 220V L15 10	24 W
92466699	BVP353 12LED 27K 220V L15 10 DMX	24 W
92467399	BVP353 12LED 30K 220V L15 10 DMX	24 W
92468099	BVP353 12LED 40K 220V L15 10 DMX	24 W
92469799	BVP353 12LED RGB 220V L15 10 DMX	24 W
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	24 W
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	24 W
92473499	BVP353 12LED 30K 220V L15 15	24 W
92481999	BVP353 12LED 27K 220V L15 30	24 W
92482699	BVP353 12LED 30K 220V L15 30	24 W
92483399	BVP353 12LED 40K 220V L15 30	24 W
92484099	BVP353 12LED 27K 220V L15 30 DMX	24 W
92485799	BVP353 12LED 30K 220V L15 30 DMX	24 W
92486499	BVP353 12LED 40K 220V L15 30 DMX	24 W
92487199	BVP353 12LED RGB 220V L15 30 DMX	24 W
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	24 W
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	24 W
92490199	BVP353 12LED 27K 220V L15 45	24 W
92491899	BVP353 12LED 30K 220V L15 45	24 W
92492599	BVP353 12LED 40K 220V L15 45	24 W
92493299	BVP353 12LED 27K 220V L15 45 DMX	24 W
92494999	BVP353 12LED 30K 220V L15 45 DMX	24 W
92495699	BVP353 12LED 40K 220V L15 45 DMX	24 W
92496399	BVP353 12LED RGB 220V L15 45 DMX	24 W
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	24 W
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	24 W
92643199	BVP353 36LED 27K 220V L35 10	80 W
92644899	BVP353 36LED 30K 220V L35 10	80 W
92645599	BVP353 36LED 40K 220V L35 10	80 W
92646299	BVP353 36LED 27K 220V L35 10 DMX	80 W
92647999	BVP353 36LED 30K 220V L35 10 DMX	80 W
92648699	BVP353 36LED 40K 220V L35 10 DMX	80 W
92649399	BVP353 36LED RGB 220V L35 10 DMX	80 W

Order Code	Full Product Name	Power Consumption
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	80 W
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	80 W
92652399	BVP353 36LED 27K 220V L35 15	80 W
92653099	BVP353 36LED 30K 220V L35 15	80 W
92654799	BVP353 36LED 40K 220V L35 15	80 W
92655499	BVP353 36LED 27K 220V L35 15 DMX	80 W
92656199	BVP353 36LED 30K 220V L35 15 DMX	80 W
92657899	BVP353 36LED 40K 220V L35 15 DMX	80 W
92658599	BVP353 36LED RGB 220V L35 15 DMX	80 W
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	80 W
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	80 W
92661599	BVP353 36LED 27K 220V L35 30	80 W
92662299	BVP353 36LED 30K 220V L35 30	80 W
92663999	BVP353 36LED 40K 220V L35 30	80 W
92664699	BVP353 36LED 27K 220V L35 30 DMX	80 W
92665399	BVP353 36LED 30K 220V L35 30 DMX	80 W
92666099	BVP353 36LED 40K 220V L35 30 DMX	80 W
92667799	BVP353 36LED RGB 220V L35 30 DMX	80 W
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	80 W
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	80 W
92670799	BVP353 36LED 27K 220V L35 45	80 W
92671499	BVP353 36LED 30K 220V L35 45	80 W
92672199	BVP353 36LED 40K 220V L35 45	80 W
92673899	BVP353 36LED 27K 220V L35 45 DMX	80 W
92674599	BVP353 36LED 30K 220V L35 45 DMX	80 W
92675299	BVP353 36LED 40K 220V L35 45 DMX	80 W
92676999	BVP353 36LED RGB 220V L35 45 DMX	80 W
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	80 W
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
92571799	BVP353 24LED 27K 220V L24 10	50 W
92572499	BVP353 24LED 30K 220V L24 10	50 W
92573199	BVP353 24LED 40K 220V L24 10	50 W
92574899	BVP353 24LED 27K 220V L24 10 DMX	50 W
92575599	BVP353 24LED 30K 220V L24 10 DMX	50 W
92576299	BVP353 24LED 40K 220V L24 10 DMX	50 W
92577999	BVP353 24LED RGB 220V L24 10 DMX	50 W
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	50 W
92580999	BVP353 24LED 27K 220V L24 15	50 W
92581699	BVP353 24LED 30K 220V L24 15	50 W
92582399	BVP353 24LED 40K 220V L24 15	50 W
92583099	BVP353 24LED 27K 220V L24 15 DMX	50 W

Order Code	Full Product Name	Power Consumption
92584799	BVP353 24LED 30K 220V L24 15 DMX	50 W
92585499	BVP353 24LED 40K 220V L24 15 DMX	50 W
92586199	BVP353 24LED RGB 220V L24 15 DMX	50 W
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	50 W
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
92589299	BVP353 24LED 27K 220V L24 30	50 W
92590899	BVP353 24LED 30K 220V L24 30	50 W
92592299	BVP353 24LED 27K 220V L24 30 DMX	50 W
92593999	BVP353 24LED 30K 220V L24 30 DMX	50 W
92594699	BVP353 24LED 40K 220V L24 30 DMX	50 W
92595399	BVP353 24LED RGB 220V L24 30 DMX	50 W
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	50 W
92598499	BVP353 24LED 27K 220V L24 45	50 W
92599199	BVP353 24LED 30K 220V L24 45	50 W
92600499	BVP353 24LED 40K 220V L24 45	50 W
92601199	BVP353 24LED 27K 220V L24 45 DMX	50 W
92602899	BVP353 24LED 30K 220V L24 45 DMX	50 W
92603599	BVP353 24LED 40K 220V L24 45 DMX	50 W
92604299	BVP353 24LED RGB 220V L24 45 DMX	50 W
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	50 W
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	50 W
92715599	BVP353 60LED 27K 220V L50 10	120 W
92717999	BVP353 60LED 40K 220V L50 10	120 W
92718699	BVP353 60LED 27K 220V L50 10 DMX	120 W
92719399	BVP353 60LED 30K 220V L50 10 DMX	120 W
92720999	BVP353 60LED 40K 220V L50 10 DMX	120 W
92721699	BVP353 60LED RGB 220V L50 10 DMX	120 W
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	120 W
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	120 W
92724799	BVP353 60LED 27K 220V L50 15	120 W
92725499	BVP353 60LED 30K 220V L50 15	120 W
92726199	BVP353 60LED 40K 220V L50 15	120 W
92727899	BVP353 60LED 27K 220V L50 15 DMX	120 W
92728599	BVP353 60LED 30K 220V L50 15 DMX	120 W
92729299	BVP353 60LED 40K 220V L50 15 DMX	120 W
92730899	BVP353 60LED RGB 220V L50 15 DMX	120 W
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	120 W
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	120 W
92733999	BVP353 60LED 27K 220V L50 30	120 W
92734699	BVP353 60LED 30K 220V L50 30	120 W
92735399	BVP353 60LED 40K 220V L50 30	120 W

Order Code	Full Product Name	Power Consumption
92736099	BVP353 60LED 27K 220V L50 30 DMX	120 W
92737799	BVP353 60LED 30K 220V L50 30 DMX	120 W
92738499	BVP353 60LED 40K 220V L50 30 DMX	120 W
92739199	BVP353 60LED RGB 220V L50 30 DMX	120 W
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	120 W
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	120 W
92742199	BVP353 60LED 27K 220V L50 45	120 W
92743899	BVP353 60LED 30K 220V L50 45	120 W
92744599	BVP353 60LED 40K 220V L50 45	120 W
92745299	BVP353 60LED 27K 220V L50 45 DMX	120 W
92746999	BVP353 60LED 30K 220V L50 45 DMX	120 W
92747699	BVP353 60LED 40K 220V L50 45 DMX	120 W
92748399	BVP353 60LED RGB 220V L50 45 DMX	120 W
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	120 W
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	120 W
92499499	BVP353 16LED 27K 220V L18 10	30 W
92500799	BVP353 16LED 30K 220V L18 10	30 W
92501499	BVP353 16LED 40K 220V L18 10	30 W
92502199	BVP353 16LED 27K 220V L18 10 DMX	30 W
92503899	BVP353 16LED 30K 220V L18 10 DMX	30 W
92504599	BVP353 16LED 40K 220V L18 10 DMX	30 W
92505299	BVP353 15LED RGB 220V L18 10 DMX	30 W
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	30 W
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	30 W
92508399	BVP353 16LED 27K 220V L18 15	30 W
92509099	BVP353 16LED 30K 220V L18 15	30 W
92510699	BVP353 16LED 40K 220V L18 15	30 W
92511399	BVP353 16LED 27K 220V L18 15 DMX	30 W
92512099	BVP353 16LED 30K 220V L18 15 DMX	30 W
92513799	BVP353 16LED 40K 220V L18 15 DMX	30 W
92514499	BVP353 15LED RGB 220V L18 15 DMX	30 W
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	30 W
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	30 W
92517599	BVP353 16LED 27K 220V L18 30	30 W
92518299	BVP353 16LED 30K 220V L18 30	30 W
92519999	BVP353 16LED 40K 220V L18 30	30 W
92520599	BVP353 16LED 27K 220V L18 30 DMX	30 W
92521299	BVP353 16LED 30K 220V L18 30 DMX	30 W
92522999	BVP353 16LED 40K 220V L18 30 DMX	30 W
92523699	BVP353 15LED RGB 220V L18 30 DMX	30 W
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	30 W

Order Code	Full Product Name	Power Consumption
92526799	BVP353 16LED 27K 220V L18 45	30 W
92527499	BVP353 16LED 30K 220V L18 45	30 W
92528199	BVP353 16LED 40K 220V L18 45	30 W
92529899	BVP353 16LED 27K 220V L18 45 DMX	30 W
92530499	BVP353 16LED 30K 220V L18 45 DMX	30 W
92531199	BVP353 16LED 40K 220V L18 45 DMX	30 W
92532899	BVP353 15LED RGB 220V L18 45 DMX	30 W
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	30 W
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	30 W
92895400	BVP355 216LED 27K 220V L57 10	450 W
92896100	BVP355 216LED 30K 220V L57 10	450 W
92897800	BVP355 216LED 40K 220V L57 10	450 W
92898500	BVP355 216LED 27K 220V L57 10 DMX	450 W
92899200	BVP355 216LED 30K 220V L57 10 DMX	450 W
92900500	BVP355 216LED 40K 220V L57 10 DMX	450 W
92901200	BVP355 216LED RGB 220V L57 10 DMX	450 W
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	450 W
92904300	BVP355 216LED 27K 220V L57 15	450 W
92905000	BVP355 216LED 30K 220V L57 15	450 W
92906700	BVP355 216LED 40K 220V L57 15	450 W
92907400	BVP355 216LED 27K 220V L57 15 DMX	450 W
92908100	BVP355 216LED 30K 220V L57 15 DMX	450 W
92909800	BVP355 216LED 40K 220V L57 15 DMX	450 W
92910400	BVP355 216LED RGB 220V L57 15 DMX	450 W
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	450 W
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
92913500	BVP355 216LED 27K 220V L57 30	450 W
92914200	BVP355 216LED 30K 220V L57 30	450 W
92915900	BVP355 216LED 40K 220V L57 30	450 W
92916600	BVP355 216LED 27K 220V L57 30 DMX	450 W
92917300	BVP355 216LED 30K 220V L57 30 DMX	450 W
92918000	BVP355 216LED 40K 220V L57 30 DMX	450 W
92919700	BVP355 216LED RGB 220V L57 30 DMX	450 W
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	450 W
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	450 W
92922700	BVP355 216LED 27K 220V L57 45	450 W
92923400	BVP355 216LED 30K 220V L57 45	450 W
92924100	BVP355 216LED 40K 220V L57 45	450 W
92925800	BVP355 216LED 27K 220V L57 45 DMX	450 W
92926500	BVP355 216LED 30K 220V L57 45 DMX	450 W
92927200	BVP355 216LED 40K 220V L57 45 DMX	450 W

Order Code	Full Product Name	Power Consumption
92928900	BVP355 216LED RGB 220V L57 45 DMX	450 W
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	450 W
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
92931900	BVP355 180LED 27K 220V L50 10	360 W
92932600	BVP355 180LED 30K 220V L50 10	360 W
92933300	BVP355 180LED 40K 220V L50 10	360 W
92934000	BVP355 180LED 27K 220V L50 10 DMX	360 W
92935700	BVP355 180LED 30K 220V L50 10 DMX	360 W
92936400	BVP355 180LED 40K 220V L50 10 DMX	360 W
92937100	BVP355 180LED RGB 220V L50 10 DMX	360 W
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	360 W
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	360 W
92940100	BVP355 180LED 27K 220V L50 15	360 W
92941800	BVP355 180LED 30K 220V L50 15	360 W
92942500	BVP355 180LED 40K 220V L50 15	360 W
92943200	BVP355 180LED 27K 220V L50 15 DMX	360 W
92944900	BVP355 180LED 30K 220V L50 15 DMX	360 W
92945600	BVP355 180LED 40K 220V L50 15 DMX	360 W
92946300	BVP355 180LED RGB 220V L50 15 DMX	360 W
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	360 W
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	360 W
92949400	BVP355 180LED 27K 220V L50 30	360 W
92950000	BVP355 180LED 30K 220V L50 30	360 W
92951700	BVP355 180LED 40K 220V L50 30	360 W
92952400	BVP355 180LED 27K 220V L50 30 DMX	360 W
92953100	BVP355 180LED 30K 220V L50 30 DMX	360 W
92954800	BVP355 180LED 40K 220V L50 30 DMX	360 W
92955500	BVP355 180LED RGB 220V L50 30 DMX	360 W
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	360 W
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
92958600	BVP355 180LED 27K 220V L50 45	360 W
92959300	BVP355 180LED 30K 220V L50 45	360 W
92960900	BVP355 180LED 40K 220V L50 45	360 W
92961600	BVP355 180LED 27K 220V L50 45 DMX	360 W
92962300	BVP355 180LED 30K 220V L50 45 DMX	360 W
92963000	BVP355 180LED 40K 220V L50 45 DMX	360 W
92964700	BVP355 180LED RGB 220V L50 45 DMX	360 W
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	360 W
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	360 W
92679099	BVP353 48LED 27K 220V L40 10	100 W
92680699	BVP353 48LED 30K 220V L40 10	100 W
92681399	BVP353 48LED 40K 220V L40 10	100 W

Order Code	Full Product Name	Power Consumption
92682099	BVP353 48LED 27K 220V L40 10 DMX	100 W
92683799	BVP353 48LED 30K 220V L40 10 DMX	100 W
92684499	BVP353 48LED 40K 220V L40 10 DMX	100 W
92685199	BVP353 48LED RGB 220V L40 10 DMX	100 W
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
92688299	BVP353 48LED 27K 220V L40 15	100 W
92689999	BVP353 48LED 30K 220V L40 15	100 W
92690599	BVP353 48LED 40K 220V L40 15	100 W
92691299	BVP353 48LED 27K 220V L40 15 DMX	100 W
92692999	BVP353 48LED 30K 220V L40 15 DMX	100 W
92693699	BVP353 48LED 40K 220V L40 15 DMX	100 W
92694399	BVP353 48LED RGB 220V L40 15 DMX	100 W
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	100 W
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	100 W
92697499	BVP353 48LED 27K 220V L40 30	100 W
92698199	BVP353 48LED 30K 220V L40 30	100 W
92699899	BVP353 48LED 40K 220V L40 30	100 W
92700199	BVP353 48LED 27K 220V L40 30 DMX	100 W
92701899	BVP353 48LED 30K 220V L40 30 DMX	100 W
92702599	BVP353 48LED 40K 220V L40 30 DMX	100 W
92703299	BVP353 48LED RGB 220V L40 30 DMX	100 W
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	100 W
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
92706399	BVP353 48LED 27K 220V L40 45	100 W
92707099	BVP353 48LED 30K 220V L40 45	100 W
92708799	BVP353 48LED 40K 220V L40 45	100 W
92709499	BVP353 48LED 27K 220V L40 45 DMX	100 W
92710099	BVP353 48LED 30K 220V L40 45 DMX	100 W
92711799	BVP353 48LED 40K 220V L40 45 DMX	100 W
92712499	BVP353 48LED RGB 220V L40 45 DMX	100 W
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	100 W
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
92607399	BVP353 30LED 27K 220V L30 10	No
92608099	BVP353 30LED 30K 220V L30 10	No
92609799	BVP353 30LED 40K 220V L30 10	No
92610399	BVP353 30LED 27K 220V L30 10 DMX	Yes
92611099	BVP353 30LED 30K 220V L30 10 DMX	Yes

Order Code	Full Product Name	Dimmable
92612799	BVP353 30LED 40K 220V L30 10 DMX	Yes
92613499	BVP353 30LED RGB 220V L30 10 DMX	Yes
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	Yes
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
92616599	BVP353 30LED 27K 220V L30 15	No
92617299	BVP353 30LED 30K 220V L30 15	No
92618999	BVP353 30LED 40K 220V L30 15	No
92619699	BVP353 30LED 27K 220V L30 15 DMX	Yes
92620299	BVP353 30LED 30K 220V L30 15 DMX	Yes
92621999	BVP353 30LED 40K 220V L30 15 DMX	Yes
92622699	BVP353 30LED RGB 220V L30 15 DMX	Yes
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	Yes
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	Yes
92625799	BVP353 30LED 27K 220V L30 30	No
92626499	BVP353 30LED 30K 220V L30 30	No
92627199	BVP353 30LED 40K 220V L30 30	No
92628899	BVP353 30LED 27K 220V L30 30 DMX	Yes
92629599	BVP353 30LED 30K 220V L30 30 DMX	Yes
92630199	BVP353 30LED 40K 220V L30 30 DMX	Yes
92631899	BVP353 30LED RGB 220V L30 30 DMX	Yes
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	Yes
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	Yes
92634999	BVP353 30LED 27K 220V L30 45	No
92635699	BVP353 30LED 30K 220V L30 45	No
92636399	BVP353 30LED 40K 220V L30 45	No
92637099	BVP353 30LED 27K 220V L30 45 DMX	Yes
92638799	BVP353 30LED 30K 220V L30 45 DMX	Yes
92639499	BVP353 30LED 40K 220V L30 45 DMX	Yes
92640099	BVP353 30LED RGB 220V L30 45 DMX	Yes
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	Yes
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	Yes
92787200	BVP354 96LED 27K 220V L40 10	No
92788900	BVP354 96LED 30K 220V L40 10	No
92789600	BVP354 96LED 40K 220V L40 10	No
92790200	BVP354 96LED 27K 220V L40 10 DMX	Yes
92791900	BVP354 96LED 30K 220V L40 10 DMX	Yes
92792600	BVP354 96LED 40K 220V L40 10 DMX	Yes
92793300	BVP354 96LED RGB 220V L40 10 DMX	Yes
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	Yes
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
92796400	BVP354 96LED 27K 220V L40 15	No
92797100	BVP354 96LED 30K 220V L40 15	No

Order Code	Full Product Name	Dimmable
92798800	BVP354 96LED 40K 220V L40 15	No
92799500	BVP354 96LED 27K 220V L40 15 DMX	Yes
92800800	BVP354 96LED 30K 220V L40 15 DMX	Yes
92801500	BVP354 96LED 40K 220V L40 15 DMX	Yes
92802200	BVP354 96LED RGB 220V L40 15 DMX	Yes
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	Yes
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	Yes
92805300	BVP354 96LED 27K 220V L40 30	No
92806000	BVP354 96LED 30K 220V L40 30	No
92807700	BVP354 96LED 40K 220V L40 30	No
92808400	BVP354 96LED 27K 220V L40 30 DMX	Yes
92809100	BVP354 96LED 30K 220V L40 30 DMX	Yes
92810700	BVP354 96LED 40K 220V L40 30 DMX	Yes
92811400	BVP354 96LED RGB 220V L40 30 DMX	Yes
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	Yes
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	Yes
92814500	BVP354 96LED 27K 220V L40 45	No
92815200	BVP354 96LED 30K 220V L40 45	No
92816900	BVP354 96LED 40K 220V L40 45	No
92817600	BVP354 96LED 27K 220V L40 45 DMX	Yes
92818300	BVP354 96LED 30K 220V L40 45 DMX	Yes
92819000	BVP354 96LED 40K 220V L40 45 DMX	Yes
92820600	BVP354 96LED RGB 220V L40 45 DMX	Yes
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	Yes
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
92823700	BVP354 120LED 27K 220V L50 10	No
92824400	BVP354 120LED 30K 220V L50 10	No
92825100	BVP354 120LED 40K 220V L50 10	No
92826800	BVP354 120LED 27K 220V L50 10 DMX	Yes
92827500	BVP354 120LED 30K 220V L50 10 DMX	Yes
92828200	BVP354 120LED 40K 220V L50 10 DMX	Yes
92829900	BVP354 120LED RGB 220V L50 10 DMX	Yes
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	Yes
92832900	BVP354 120LED 27K 220V L50 15	No
92833600	BVP354 120LED 30K 220V L50 15	No
92834300	BVP354 120LED 40K 220V L50 15	No
92835000	BVP354 120LED 27K 220V L50 15 DMX	Yes
92836700	BVP354 120LED 30K 220V L50 15 DMX	Yes
92837400	BVP354 120LED 40K 220V L50 15 DMX	Yes
92838100	BVP354 120LED RGB 220V L50 15 DMX	Yes
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	Yes
92841100	BVP354 120LED 27K 220V L50 30	No
92842800	BVP354 120LED 30K 220V L50 30	No
92843500	BVP354 120LED 40K 220V L50 30	No
92844200	BVP354 120LED 27K 220V L50 30 DMX	Yes
92845900	BVP354 120LED 30K 220V L50 30 DMX	Yes
92846600	BVP354 120LED 40K 220V L50 30 DMX	Yes
92847300	BVP354 120LED RGB 220V L50 30 DMX	Yes
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	Yes
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
92850300	BVP354 120LED 27K 220V L50 45	No
92851000	BVP354 120LED 30K 220V L50 45	No
92852700	BVP354 120LED 40K 220V L50 45	No
92853400	BVP354 120LED 27K 220V L50 45 DMX	Yes
92854100	BVP354 120LED 30K 220V L50 45 DMX	Yes
92855800	BVP354 120LED 40K 220V L50 45 DMX	Yes
92856500	BVP354 120LED RGB 220V L50 45 DMX	Yes
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
92859600	BVP354 144LED 27K 220V L57 10	No
92860200	BVP354 144LED 30K 220V L57 10	No
92861900	BVP354 144LED 40K 220V L57 10	No
92862600	BVP354 144LED 27K 220V L57 10 DMX	Yes
92863300	BVP354 144LED 30K 220V L57 10 DMX	Yes
92864000	BVP354 144LED 40K 220V L57 10 DMX	Yes
92865700	BVP354 144LED RGB 220V L57 10 DMX	Yes
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
92868800	BVP354 144LED 27K 220V L57 15	No
92869500	BVP354 144LED 30K 220V L57 15	No
92870100	BVP354 144LED 40K 220V L57 15	No
92871800	BVP354 144LED 27K 220V L57 15 DMX	Yes
92872500	BVP354 144LED 30K 220V L57 15 DMX	Yes
92873200	BVP354 144LED 40K 220V L57 15 DMX	Yes
92874900	BVP354 144LED RGB 220V L57 15 DMX	Yes
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	Yes
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	Yes
92877000	BVP354 144LED 27K 220V L57 30	No
92878700	BVP354 144LED 30K 220V L57 30	No
92879400	BVP354 144LED 40K 220V L57 30	No
92880000	BVP354 144LED 27K 220V L57 30 DMX	Yes
92881700	BVP354 144LED 30K 220V L57 30 DMX	Yes

Order Code	Full Product Name	Dimmable
92882400	BVP354 144LED 40K 220V L57 30 DMX	Yes
92883100	BVP354 144LED RGB 220V L57 30 DMX	Yes
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	Yes
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	Yes
92886200	BVP354 144LED 27K 220V L57 45	No
92887900	BVP354 144LED 30K 220V L57 45	No
92888600	BVP354 144LED 40K 220V L57 45	No
92889300	BVP354 144LED 27K 220V L57 45 DMX	Yes
92890900	BVP354 144LED 30K 220V L57 45 DMX	Yes
92891600	BVP354 144LED 40K 220V L57 45 DMX	Yes
92892300	BVP354 144LED RGB 220V L57 45 DMX	Yes
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	Yes
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	Yes
92751399	BVP353 72LED 27K 220V L57 10	No
92752099	BVP353 72LED 30K 220V L57 10	No
92753799	BVP353 72LED 40K 220V L57 10	No
92754499	BVP353 72LED 27K 220V L57 10 DMX	Yes
92755199	BVP353 72LED 30K 220V L57 10 DMX	Yes
92756899	BVP353 72LED 40K 220V L57 10 DMX	Yes
92757599	BVP353 72LED RGB 220V L57 10 DMX	Yes
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
92760599	BVP353 72LED 27K 220V L57 15	No
92761299	BVP353 72LED 30K 220V L57 15	No
92762999	BVP353 72LED 40K 220V L57 15	No
92763699	BVP353 72LED 27K 220V L57 15 DMX	Yes
92764399	BVP353 72LED 30K 220V L57 15 DMX	Yes
92765099	BVP353 72LED 40K 220V L57 15 DMX	Yes
92766799	BVP353 72LED RGB 220V L57 15 DMX	Yes
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	Yes
92769899	BVP353 72LED 27K 220V L57 30	No
92770499	BVP353 72LED 30K 220V L57 30	No
92771199	BVP353 72LED 40K 220V L57 30	No
92772899	BVP353 72LED 27K 220V L57 30 DMX	Yes
92773599	BVP353 72LED 30K 220V L57 30 DMX	Yes
92774299	BVP353 72LED 40K 220V L57 30 DMX	Yes
92775999	BVP353 72LED RGB 220V L57 30 DMX	Yes
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
92778099	BVP353 72LED 27K 220V L57 45	No
92779799	BVP353 72LED 30K 220V L57 45	No

Order Code	Full Product Name	Dimmable
92780399	BVP353 72LED 40K 220V L57 45	No
92781099	BVP353 72LED 27K 220V L57 45 DMX	Yes
92782799	BVP353 72LED 30K 220V L57 45 DMX	Yes
92783499	BVP353 72LED 40K 220V L57 45 DMX	Yes
92784199	BVP353 72LED RGB 220V L57 45 DMX	Yes
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
92535999	BVP353 18LED 27K 220V L21 10	No
92536699	BVP353 18LED 30K 220V L21 10	No
92537399	BVP353 18LED 40K 220V L21 10	No
92538099	BVP353 18LED 27K 220V L21 10 DMX	Yes
92539799	BVP353 18LED 30K 220V L21 10 DMX	Yes
92540399	BVP353 18LED 40K 220V L21 10 DMX	Yes
92541099	BVP353 18LED RGB 220V L21 10 DMX	Yes
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	Yes
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
92544199	BVP353 18LED 27K 220V L21 15	No
92545899	BVP353 18LED 30K 220V L21 15	No
92546599	BVP353 18LED 40K 220V L21 15	No
92547299	BVP353 18LED 27K 220V L21 15 DMX	Yes
92548999	BVP353 18LED 30K 220V L21 15 DMX	Yes
92549699	BVP353 18LED 40K 220V L21 15 DMX	Yes
92550299	BVP353 18LED RGB 220V L21 15 DMX	Yes
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	Yes
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
92553399	BVP353 18LED 27K 220V L21 30	No
92554099	BVP353 18LED 30K 220V L21 30	No
92555799	BVP353 18LED 40K 220V L21 30	No
92556499	BVP353 18LED 27K 220V L21 30 DMX	Yes
92557199	BVP353 18LED 30K 220V L21 30 DMX	Yes
92558899	BVP353 18LED 40K 220V L21 30 DMX	Yes
92559599	BVP353 18LED RGB 220V L21 30 DMX	Yes
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	Yes
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
92562599	BVP353 18LED 27K 220V L21 45	No
92563299	BVP353 18LED 30K 220V L21 45	No
92564999	BVP353 18LED 40K 220V L21 45	No
92565699	BVP353 18LED 27K 220V L21 45 DMX	Yes
92566399	BVP353 18LED 30K 220V L21 45 DMX	Yes
92567099	BVP353 18LED 40K 220V L21 45 DMX	Yes
92568799	BVP353 18LED RGB 220V L21 45 DMX	Yes
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	Yes

Order Code	Full Product Name	Dimmable
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	Yes
92463599	BVP353 12LED 27K 220V L15 10	No
92464299	BVP353 12LED 30K 220V L15 10	No
92465999	BVP353 12LED 40K 220V L15 10	No
92466699	BVP353 12LED 27K 220V L15 10 DMX	Yes
92467399	BVP353 12LED 30K 220V L15 10 DMX	Yes
92468099	BVP353 12LED 40K 220V L15 10 DMX	Yes
92469799	BVP353 12LED RGB 220V L15 10 DMX	Yes
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	Yes
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	Yes
92473499	BVP353 12LED 30K 220V L15 15	No
92481999	BVP353 12LED 27K 220V L15 30	No
92482699	BVP353 12LED 30K 220V L15 30	No
92483399	BVP353 12LED 40K 220V L15 30	No
92484099	BVP353 12LED 27K 220V L15 30 DMX	Yes
92485799	BVP353 12LED 30K 220V L15 30 DMX	Yes
92486499	BVP353 12LED 40K 220V L15 30 DMX	Yes
92487199	BVP353 12LED RGB 220V L15 30 DMX	Yes
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	Yes
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	Yes
92490199	BVP353 12LED 27K 220V L15 45	No
92491899	BVP353 12LED 30K 220V L15 45	No
92492599	BVP353 12LED 40K 220V L15 45	No
92493299	BVP353 12LED 27K 220V L15 45 DMX	Yes
92494999	BVP353 12LED 30K 220V L15 45 DMX	Yes
92495699	BVP353 12LED 40K 220V L15 45 DMX	Yes
92496399	BVP353 12LED RGB 220V L15 45 DMX	Yes
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	Yes
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	Yes
92643199	BVP353 36LED 27K 220V L35 10	No
92644899	BVP353 36LED 30K 220V L35 10	No
92645599	BVP353 36LED 40K 220V L35 10	No
92646299	BVP353 36LED 27K 220V L35 10 DMX	Yes
92647999	BVP353 36LED 30K 220V L35 10 DMX	Yes
92648699	BVP353 36LED 40K 220V L35 10 DMX	Yes
92649399	BVP353 36LED RGB 220V L35 10 DMX	Yes
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	Yes
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	Yes
92652399	BVP353 36LED 27K 220V L35 15	No
92653099	BVP353 36LED 30K 220V L35 15	No
92654799	BVP353 36LED 40K 220V L35 15	No
92655499	BVP353 36LED 27K 220V L35 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92656199	BVP353 36LED 30K 220V L35 15 DMX	Yes
92657899	BVP353 36LED 40K 220V L35 15 DMX	Yes
92658599	BVP353 36LED RGB 220V L35 15 DMX	Yes
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	Yes
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	Yes
92661599	BVP353 36LED 27K 220V L35 30	No
92662299	BVP353 36LED 30K 220V L35 30	No
92663999	BVP353 36LED 40K 220V L35 30	No
92664699	BVP353 36LED 27K 220V L35 30 DMX	Yes
92665399	BVP353 36LED 30K 220V L35 30 DMX	Yes
92666099	BVP353 36LED 40K 220V L35 30 DMX	Yes
92667799	BVP353 36LED RGB 220V L35 30 DMX	Yes
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	Yes
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	Yes
92670799	BVP353 36LED 27K 220V L35 45	No
92671499	BVP353 36LED 30K 220V L35 45	No
92672199	BVP353 36LED 40K 220V L35 45	No
92673899	BVP353 36LED 27K 220V L35 45 DMX	Yes
92674599	BVP353 36LED 30K 220V L35 45 DMX	Yes
92675299	BVP353 36LED 40K 220V L35 45 DMX	Yes
92676999	BVP353 36LED RGB 220V L35 45 DMX	Yes
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	Yes
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
92571799	BVP353 24LED 27K 220V L24 10	No
92572499	BVP353 24LED 30K 220V L24 10	No
92573199	BVP353 24LED 40K 220V L24 10	No
92574899	BVP353 24LED 27K 220V L24 10 DMX	Yes
92575599	BVP353 24LED 30K 220V L24 10 DMX	Yes
92576299	BVP353 24LED 40K 220V L24 10 DMX	Yes
92577999	BVP353 24LED RGB 220V L24 10 DMX	Yes
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	Yes
92580999	BVP353 24LED 27K 220V L24 15	No
92581699	BVP353 24LED 30K 220V L24 15	No
92582399	BVP353 24LED 40K 220V L24 15	No
92583099	BVP353 24LED 27K 220V L24 15 DMX	Yes
92584799	BVP353 24LED 30K 220V L24 15 DMX	Yes
92585499	BVP353 24LED 40K 220V L24 15 DMX	Yes
92586199	BVP353 24LED RGB 220V L24 15 DMX	Yes
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	Yes
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
92589299	BVP353 24LED 27K 220V L24 30	No

Order Code	Full Product Name	Dimmable
92590899	BVP353 24LED 30K 220V L24 30	No
92592299	BVP353 24LED 27K 220V L24 30 DMX	Yes
92593999	BVP353 24LED 30K 220V L24 30 DMX	Yes
92594699	BVP353 24LED 40K 220V L24 30 DMX	Yes
92595399	BVP353 24LED RGB 220V L24 30 DMX	Yes
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	Yes
92598499	BVP353 24LED 27K 220V L24 45	No
92599199	BVP353 24LED 30K 220V L24 45	No
92600499	BVP353 24LED 40K 220V L24 45	No
92601199	BVP353 24LED 27K 220V L24 45 DMX	Yes
92602899	BVP353 24LED 30K 220V L24 45 DMX	Yes
92603599	BVP353 24LED 40K 220V L24 45 DMX	Yes
92604299	BVP353 24LED RGB 220V L24 45 DMX	Yes
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	Yes
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	Yes
92715599	BVP353 60LED 27K 220V L50 10	No
92717999	BVP353 60LED 40K 220V L50 10	No
92718699	BVP353 60LED 27K 220V L50 10 DMX	Yes
92719399	BVP353 60LED 30K 220V L50 10 DMX	Yes
92720999	BVP353 60LED 40K 220V L50 10 DMX	Yes
92721699	BVP353 60LED RGB 220V L50 10 DMX	Yes
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	Yes
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	Yes
92724799	BVP353 60LED 27K 220V L50 15	No
92725499	BVP353 60LED 30K 220V L50 15	No
92726199	BVP353 60LED 40K 220V L50 15	No
92727899	BVP353 60LED 27K 220V L50 15 DMX	Yes
92728599	BVP353 60LED 30K 220V L50 15 DMX	Yes
92729299	BVP353 60LED 40K 220V L50 15 DMX	Yes
92730899	BVP353 60LED RGB 220V L50 15 DMX	Yes
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	Yes
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	Yes
92733999	BVP353 60LED 27K 220V L50 30	No
92734699	BVP353 60LED 30K 220V L50 30	No
92735399	BVP353 60LED 40K 220V L50 30	No
92736099	BVP353 60LED 27K 220V L50 30 DMX	Yes
92737799	BVP353 60LED 30K 220V L50 30 DMX	Yes
92738499	BVP353 60LED 40K 220V L50 30 DMX	Yes
92739199	BVP353 60LED RGB 220V L50 30 DMX	Yes
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	Yes
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	Yes

Order Code	Full Product Name	Dimmable
92742199	BVP353 60LED 27K 220V L50 45	No
92743899	BVP353 60LED 30K 220V L50 45	No
92744599	BVP353 60LED 40K 220V L50 45	No
92745299	BVP353 60LED 27K 220V L50 45 DMX	Yes
92746999	BVP353 60LED 30K 220V L50 45 DMX	Yes
92747699	BVP353 60LED 40K 220V L50 45 DMX	Yes
92748399	BVP353 60LED RGB 220V L50 45 DMX	Yes
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	Yes
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	Yes
92499499	BVP353 16LED 27K 220V L18 10	No
92500799	BVP353 16LED 30K 220V L18 10	No
92501499	BVP353 16LED 40K 220V L18 10	No
92502199	BVP353 16LED 27K 220V L18 10 DMX	Yes
92503899	BVP353 16LED 30K 220V L18 10 DMX	Yes
92504599	BVP353 16LED 40K 220V L18 10 DMX	Yes
92505299	BVP353 15LED RGB 220V L18 10 DMX	Yes
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	Yes
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	Yes
92508399	BVP353 16LED 27K 220V L18 15	No
92509099	BVP353 16LED 30K 220V L18 15	No
92510699	BVP353 16LED 40K 220V L18 15	No
92511399	BVP353 16LED 27K 220V L18 15 DMX	Yes
92512099	BVP353 16LED 30K 220V L18 15 DMX	Yes
92513799	BVP353 16LED 40K 220V L18 15 DMX	Yes
92514499	BVP353 15LED RGB 220V L18 15 DMX	Yes
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	Yes
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	Yes
92517599	BVP353 16LED 27K 220V L18 30	No
92518299	BVP353 16LED 30K 220V L18 30	No
92519999	BVP353 16LED 40K 220V L18 30	No
92520599	BVP353 16LED 27K 220V L18 30 DMX	Yes
92521299	BVP353 16LED 30K 220V L18 30 DMX	Yes
92522999	BVP353 16LED 40K 220V L18 30 DMX	Yes
92523699	BVP353 15LED RGB 220V L18 30 DMX	Yes
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	Yes
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	Yes
92526799	BVP353 16LED 27K 220V L18 45	No
92527499	BVP353 16LED 30K 220V L18 45	No
92528199	BVP353 16LED 40K 220V L18 45	No
92529899	BVP353 16LED 27K 220V L18 45 DMX	Yes
92530499	BVP353 16LED 30K 220V L18 45 DMX	Yes
92531199	BVP353 16LED 40K 220V L18 45 DMX	Yes

Order Code	Full Product Name	Dimmable
92532899	BVP353 15LED RGB 220V L18 45 DMX	Yes
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	Yes
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
92895400	BVP355 216LED 27K 220V L57 10	No
92896100	BVP355 216LED 30K 220V L57 10	No
92897800	BVP355 216LED 40K 220V L57 10	No
92898500	BVP355 216LED 27K 220V L57 10 DMX	Yes
92899200	BVP355 216LED 30K 220V L57 10 DMX	Yes
92900500	BVP355 216LED 40K 220V L57 10 DMX	Yes
92901200	BVP355 216LED RGB 220V L57 10 DMX	Yes
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	Yes
92904300	BVP355 216LED 27K 220V L57 15	No
92905000	BVP355 216LED 30K 220V L57 15	No
92906700	BVP355 216LED 40K 220V L57 15	No
92907400	BVP355 216LED 27K 220V L57 15 DMX	Yes
92908100	BVP355 216LED 30K 220V L57 15 DMX	Yes
92909800	BVP355 216LED 40K 220V L57 15 DMX	Yes
92910400	BVP355 216LED RGB 220V L57 15 DMX	Yes
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	Yes
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	Yes
92913500	BVP355 216LED 27K 220V L57 30	No
92914200	BVP355 216LED 30K 220V L57 30	No
92915900	BVP355 216LED 40K 220V L57 30	No
92916600	BVP355 216LED 27K 220V L57 30 DMX	Yes
92917300	BVP355 216LED 30K 220V L57 30 DMX	Yes
92918000	BVP355 216LED 40K 220V L57 30 DMX	Yes
92919700	BVP355 216LED RGB 220V L57 30 DMX	Yes
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	Yes
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	Yes
92922700	BVP355 216LED 27K 220V L57 45	No
92923400	BVP355 216LED 30K 220V L57 45	No
92924100	BVP355 216LED 40K 220V L57 45	No
92925800	BVP355 216LED 27K 220V L57 45 DMX	Yes
92926500	BVP355 216LED 30K 220V L57 45 DMX	Yes
92927200	BVP355 216LED 40K 220V L57 45 DMX	Yes
92928900	BVP355 216LED RGB 220V L57 45 DMX	Yes
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	Yes
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
92931900	BVP355 180LED 27K 220V L50 10	No
92932600	BVP355 180LED 30K 220V L50 10	No
92933300	BVP355 180LED 40K 220V L50 10	No

Order Code	Full Product Name	Dimmable
92934000	BVP355 180LED 27K 220V L50 10 DMX	Yes
92935700	BVP355 180LED 30K 220V L50 10 DMX	Yes
92936400	BVP355 180LED 40K 220V L50 10 DMX	Yes
92937100	BVP355 180LED RGB 220V L50 10 DMX	Yes
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	Yes
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	Yes
92940100	BVP355 180LED 27K 220V L50 15	No
92941800	BVP355 180LED 30K 220V L50 15	No
92942500	BVP355 180LED 40K 220V L50 15	No
92943200	BVP355 180LED 27K 220V L50 15 DMX	Yes
92944900	BVP355 180LED 30K 220V L50 15 DMX	Yes
92945600	BVP355 180LED 40K 220V L50 15 DMX	Yes
92946300	BVP355 180LED RGB 220V L50 15 DMX	Yes
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	Yes
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	Yes
92949400	BVP355 180LED 27K 220V L50 30	No
92950000	BVP355 180LED 30K 220V L50 30	No
92951700	BVP355 180LED 40K 220V L50 30	No
92952400	BVP355 180LED 27K 220V L50 30 DMX	Yes
92953100	BVP355 180LED 30K 220V L50 30 DMX	Yes
92954800	BVP355 180LED 40K 220V L50 30 DMX	Yes
92955500	BVP355 180LED RGB 220V L50 30 DMX	Yes
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	Yes
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	Yes
92958600	BVP355 180LED 27K 220V L50 45	No
92959300	BVP355 180LED 30K 220V L50 45	No
92960900	BVP355 180LED 40K 220V L50 45	No
92961600	BVP355 180LED 27K 220V L50 45 DMX	Yes
92962300	BVP355 180LED 30K 220V L50 45 DMX	Yes
92963000	BVP355 180LED 40K 220V L50 45 DMX	Yes
92964700	BVP355 180LED RGB 220V L50 45 DMX	Yes
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	Yes
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	Yes
92679099	BVP353 48LED 27K 220V L40 10	No
92680699	BVP353 48LED 30K 220V L40 10	No
92681399	BVP353 48LED 40K 220V L40 10	No
92682099	BVP353 48LED 27K 220V L40 10 DMX	Yes
92683799	BVP353 48LED 30K 220V L40 10 DMX	Yes
92684499	BVP353 48LED 40K 220V L40 10 DMX	Yes
92685199	BVP353 48LED RGB 220V L40 10 DMX	Yes
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	Yes

Order Code	Full Product Name	Dimmable
92688299	BVP353 48LED 27K 220V L40 15	No
92689999	BVP353 48LED 30K 220V L40 15	No
92690599	BVP353 48LED 40K 220V L40 15	No
92691299	BVP353 48LED 27K 220V L40 15 DMX	Yes
92692999	BVP353 48LED 30K 220V L40 15 DMX	Yes
92693699	BVP353 48LED 40K 220V L40 15 DMX	Yes
92694399	BVP353 48LED RGB 220V L40 15 DMX	Yes
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	Yes
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	Yes
92697499	BVP353 48LED 27K 220V L40 30	No
92698199	BVP353 48LED 30K 220V L40 30	No
92699899	BVP353 48LED 40K 220V L40 30	No
92700199	BVP353 48LED 27K 220V L40 30 DMX	Yes
92701899	BVP353 48LED 30K 220V L40 30 DMX	Yes
92702599	BVP353 48LED 40K 220V L40 30 DMX	Yes
92703299	BVP353 48LED RGB 220V L40 30 DMX	Yes
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	Yes
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
92706399	BVP353 48LED 27K 220V L40 45	No
92707099	BVP353 48LED 30K 220V L40 45	No
92708799	BVP353 48LED 40K 220V L40 45	No
92709499	BVP353 48LED 27K 220V L40 45 DMX	Yes
92710099	BVP353 48LED 30K 220V L40 45 DMX	Yes
92711799	BVP353 48LED 40K 220V L40 45 DMX	Yes
92712499	BVP353 48LED RGB 220V L40 45 DMX	Yes
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	Yes
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	Yes