



UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2


Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape





Warnings and Safety

- For outdoor use only.









Versions



Dimensional drawing



Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

		Correlated Color		
Order Code	Full Product Name	Light source color	Temperature (Nom)	Luminous Flux
92607399	BVP353 30LED 27K 220V L30 10	827 warm white	2700 K	4,515 lm
92608099	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
92609799	BVP353 30LED 40K 220V L30 10	840 neutral white	4000 K	5,255 lm
92610399	BVP353 30LED 27K 220V L30 10 DMX	827 warm white	2700 K	4,220 lm
92611099	BVP353 30LED 30K 220V L30 10 DMX	830 warm white	3000 K	4,400 lm
92612799	BVP353 30LED 40K 220V L30 10 DMX	840 neutral white	4000 K	4,910 lm
92613499	BVP353 30LED RGB 220V L30 10 DMX	RGB	-	2,495 lm
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	RGBW	-	2,855 lm
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-	2,985 lm
92616599	BVP353 30LED 27K 220V L30 15	827 warm white	2700 K	4,740 lm
92617299	BVP353 30LED 30K 220V L30 15	830 warm white	3000 K	4,945 lm
92618999	BVP353 30LED 40K 220V L30 15	840 neutral white	4000 K	5,520 lm
92619699	BVP353 30LED 27K 220V L30 15 DMX	827 warm white	2700 K	4,430 lm
92620299	BVP353 30LED 30K 220V L30 15 DMX	830 warm white	3000 K	4,620 lm
92621999	BVP353 30LED 40K 220V L30 15 DMX	840 neutral white	4000 K	5,155 lm
92622699	BVP353 30LED RGB 220V L30 15 DMX	RGB	-	2,620 lm
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	RGBW	-	3,000 lm
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	RGBW	-	3,130 lm
92625799	BVP353 30LED 27K 220V L30 30	827 warm white	2700 K	4,910 lm
92626499	BVP353 30LED 30K 220V L30 30	830 warm white	3000 K	5,125 lm
92627199	BVP353 30LED 40K 220V L30 30	840 neutral white	4000 K	5,715 lm
92628899	BVP353 30LED 27K 220V L30 30 DMX	827 warm white	2700 K	4,585 lm
92629599	BVP353 30LED 30K 220V L30 30 DMX	830 warm white	3000 K	4,785 lm
92630199	BVP353 30LED 40K 220V L30 30 DMX	840 neutral white	4000 K	5,340 lm
92631899	BVP353 30LED RGB 220V L30 30 DMX	RGB	-	2,715 lm
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	RGBW	-	3,105 lm
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	RGBW	-	3,245 lm
92634999	BVP353 30LED 27K 220V L30 45	827 warm white	2700 K	4,740 lm
92635699	BVP353 30LED 30K 220V L30 45	830 warm white	3000 K	4,945 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92636399	BVP353 30LED 40K 220V L30 45	840 neutral white	4000 K	5,520 lm
92637099	BVP353 30LED 27K 220V L30 45 DMX	827 warm white	2700 K	4,430 lm
92638799	BVP353 30LED 30K 220V L30 45 DMX	830 warm white	3000 K	4,620 lm
92639499	BVP353 30LED 40K 220V L30 45 DMX	840 neutral white	4000 K	5,155 lm
92640099	BVP353 30LED RGB 220V L30 45 DMX	RGB	-	2,620 lm
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	RGBW	-	3,000 lm
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	RGBW	-	3,130 lm
92787200	BVP354 96LED 27K 220V L40 10	827 warm white	2700 K	15,870 lm
92788900	BVP354 96LED 30K 220V L40 10	830 warm white	3000 K	16,555 lm
92789600	BVP354 96LED 40K 220V L40 10	840 neutral white	4000 K	18,470 lm
92790200	BVP354 96LED 27K 220V L40 10 DMX	827 warm white	2700 K	14,640 lm
92791900	BVP354 96LED 30K 220V L40 10 DMX	830 warm white	3000 K	15,270 lm
92792600	BVP354 96LED 40K 220V L40 10 DMX	840 neutral white	4000 K	17,035 lm
92793300	BVP354 96LED RGB 220V L40 10 DMX	RGB	-	8,170 lm
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	RGBW	-	10,505 lm
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-	10,975 lm
92796400	BVP354 96LED 27K 220V L40 15	827 warm white	2700 K	16,665 lm
92797100	BVP354 96LED 30K 220V L40 15	830 warm white	3000 K	17,385 lm
92798800	BVP354 96LED 40K 220V L40 15	840 neutral white	4000 K	19,395 lm
92799500	BVP354 96LED 27K 220V L40 15 DMX	827 warm white	2700 K	15,370 lm
92800800	BVP354 96LED 30K 220V L40 15 DMX	830 warm white	3000 K	16,035 lm
92801500	BVP354 96LED 40K 220V L40 15 DMX	840 neutral white	4000 K	17,890 lm
92802200	BVP354 96LED RGB 220V L40 15 DMX	RGB	-	8,580 lm
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	RGBW	-	11,030 lm
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	RGBW	-	11,520 lm
92805300	BVP354 96LED 27K 220V L40 30	827 warm white	2700 K	17,260 lm
92806000	BVP354 96LED 30K 220V L40 30	830 warm white	3000 K	18,005 lm
92807700	BVP354 96LED 40K 220V L40 30	840 neutral white	4000 K	20,085 lm
92808400	BVP354 96LED 27K 220V L40 30 DMX	827 warm white	2700 K	15,920 lm
92809100	BVP354 96LED 30K 220V L40 30 DMX	830 warm white	3000 K	16,605 lm
92810700	BVP354 96LED 40K 220V L40 30 DMX	840 neutral white	4000 K	18,525 lm
92811400	BVP354 96LED RGB 220V L40 30 DMX	RGB	-	8,885 lm
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	RGBW	-	11,425 lm
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	RGBW	-	11,935 lm
92814500	BVP354 96LED 27K 220V L40 45	827 warm white	2700 K	16,665 lm
92815200	BVP354 96LED 30K 220V L40 45	830 warm white	3000 K	17,385 lm
92816900	BVP354 96LED 40K 220V L40 45	840 neutral white	4000 K	19,395 lm
92817600	BVP354 96LED 27K 220V L40 45 DMX	827 warm white	2700 K	15,370 lm
92818300	BVP354 96LED 30K 220V L40 45 DMX	830 warm white	3000 K	16,035 lm
92819000	BVP354 96LED 40K 220V L40 45 DMX	840 neutral white	4000 K	17,890 lm
92820600	BVP354 96LED RGB 220V L40 45 DMX	RGB	-	8,580 lm
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	RGBW	-	11,030 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-	11,520 lm
92823700	BVP354 120LED 27K 220V L50 10	827 warm white	2700 K	18,075 lm
92824400	BVP354 120LED 30K 220V L50 10	830 warm white	3000 K	18,850 lm
92825100	BVP354 120LED 40K 220V L50 10	840 neutral white	4000 K	21,035 lm
92826800	BVP354 120LED 27K 220V L50 10 DMX	827 warm white	2700 K	16,880 lm
92827500	BVP354 120LED 30K 220V L50 10 DMX	830 warm white	3000 K	17,605 lm
92828200	BVP354 120LED 40K 220V L50 10 DMX	840 neutral white	4000 K	19,645 lm
92829900	BVP354 120LED RGB 220V L50 10 DMX	RGB	-	9,985 lm
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	RGBW	-	10,720 lm
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	RGBW	-	11,190 lm
92832900	BVP354 120LED 27K 220V L50 15	827 warm white	2700 K	18,975 lm
92833600	BVP354 120LED 30K 220V L50 15	830 warm white	3000 K	19,795 lm
92834300	BVP354 120LED 40K 220V L50 15	840 neutral white	4000 K	22,085 lm
92835000	BVP354 120LED 27K 220V L50 15 DMX	827 warm white	2700 K	17,720 lm
92836700	BVP354 120LED 30K 220V L50 15 DMX	830 warm white	3000 K	18,485 lm
92837400	BVP354 120LED 40K 220V L50 15 DMX	840 neutral white	4000 K	20,625 lm
92838100	BVP354 120LED RGB 220V L50 15 DMX	RGB	-	10,485 lm
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	RGBW	-	11,255 lm
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	RGBW	-	11,750 lm
92841100	BVP354 120LED 27K 220V L50 30	827 warm white	2700 K	19,655 lm
92842800	BVP354 120LED 30K 220V L50 30	830 warm white	3000 K	20,500 lm
92843500	BVP354 120LED 40K 220V L50 30	840 neutral white	4000 K	22,875 lm
92844200	BVP354 120LED 27K 220V L50 30 DMX	827 warm white	2700 K	18,355 lm
92845900	BVP354 120LED 30K 220V L50 30 DMX	830 warm white	3000 K	19,145 lm
92846600	BVP354 120LED 40K 220V L50 30 DMX	840 neutral white	4000 K	21,360 lm
92847300	BVP354 120LED RGB 220V L50 30 DMX	RGB	-	10,860 lm
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	RGBW	-	11,655 lm
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	RGBW	-	12,170 lm
92850300	BVP354 120LED 27K 220V L50 45	827 warm white	2700 K	18,975 lm
92851000	BVP354 120LED 30K 220V L50 45	830 warm white	3000 K	19,795 lm
92852700	BVP354 120LED 40K 220V L50 45	840 neutral white	4000 K	22,085 lm
92853400	BVP354 120LED 27K 220V L50 45 DMX	827 warm white	2700 K	17,720 lm
92854100	BVP354 120LED 30K 220V L50 45 DMX	830 warm white	3000 K	18,485 lm
92855800	BVP354 120LED 40K 220V L50 45 DMX	840 neutral white	4000 K	20,625 lm
92856500	BVP354 120LED RGB 220V L50 45 DMX	RGB	-	10,485 lm
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	RGBW	-	11,255 lm
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	RGBW	-	11,750 lm
92859600	BVP354 144LED 27K 220V L57 10	827 warm white	2700 K	22,765 lm
92860200	BVP354 144LED 30K 220V L57 10	830 warm white	3000 K	23,745 lm
92861900	BVP354 144LED 40K 220V L57 10	840 neutral white	4000 K	26,490 lm
92862600	BVP354 144LED 27K 220V L57 10 DMX	827 warm white	2700 K	21,690 lm
92863300	BVP354 144LED 30K 220V L57 10 DMX	830 warm white	3000 K	22,625 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92864000	BVP354 144LED 40K 220V L57 10 DMX	840 neutral white	4000 K	25,240 lm
92865700	BVP354 144LED RGB 220V L57 10 DMX	RGB	-	13,410 lm
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	RGBW	-	14,395 lm
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
92868800	BVP354 144LED 27K 220V L57 15	827 warm white	2700 K	23,900 lm
92869500	BVP354 144LED 30K 220V L57 15	830 warm white	3000 K	24,930 lm
92870100	BVP354 144LED 40K 220V L57 15	840 neutral white	4000 K	27,815 lm
92871800	BVP354 144LED 27K 220V L57 15 DMX	827 warm white	2700 K	22,775 lm
92872500	BVP354 144LED 30K 220V L57 15 DMX	830 warm white	3000 K	23,755 lm
92873200	BVP354 144LED 40K 220V L57 15 DMX	840 neutral white	4000 K	26,505 lm
92874900	BVP354 144LED RGB 220V L57 15 DMX	RGB	-	14,080 lm
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	RGBW	-	15,115 lm
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	RGBW	-	15,785 lm
92877000	BVP354 144LED 27K 220V L57 30	827 warm white	2700 K	24,755 lm
92878700	BVP354 144LED 30K 220V L57 30	830 warm white	3000 K	25,820 lm
92879400	BVP354 144LED 40K 220V L57 30	840 neutral white	4000 K	28,810 lm
92880000	BVP354 144LED 27K 220V L57 30 DMX	827 warm white	2700 K	23,585 lm
92881700	BVP354 144LED 30K 220V L57 30 DMX	830 warm white	3000 K	24,605 lm
92882400	BVP354 144LED 40K 220V L57 30 DMX	840 neutral white	4000 K	27,450 lm
92883100	BVP354 144LED RGB 220V L57 30 DMX	RGB	-	14,585 lm
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	RGBW	-	15,655 lm
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	RGBW	-	16,345 lm
92886200	BVP354 144LED 27K 220V L57 45	827 warm white	2700 K	23,900 lm
92887900	BVP354 144LED 30K 220V L57 45	830 warm white	3000 K	24,930 lm
92888600	BVP354 144LED 40K 220V L57 45	840 neutral white	4000 K	27,815 lm
92889300	BVP354 144LED 27K 220V L57 45 DMX	827 warm white	2700 K	22,775 lm
92890900	BVP354 144LED 30K 220V L57 45 DMX	830 warm white	3000 K	23,755 lm
92891600	BVP354 144LED 40K 220V L57 45 DMX	840 neutral white	4000 K	26,505 lm
92892300	BVP354 144LED RGB 220V L57 45 DMX	RGB	-	14,080 lm
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	RGBW	-	15,115 lm
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-	15,785 lm
92751399	BVP353 72LED 27K 220V L57 10	827 warm white	2700 K	11,380 lm
92752099	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K	11,870 lm
92753799	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K	13,245 lm
92754499	BVP353 72LED 27K 220V L57 10 DMX	827 warm white	2700 K	10,845 lm
92755199	BVP353 72LED 30K 220V L57 10 DMX	830 warm white	3000 K	11,310 lm
92756899	BVP353 72LED 40K 220V L57 10 DMX	840 neutral white	4000 K	12,620 lm
92757599	BVP353 72LED RGB 220V L57 10 DMX	RGB	-	6,705 lm
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-	7,195 lm
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-	7,515 lm
92760599	BVP353 72LED 27K 220V L57 15	827 warm white	2700 K	11,950 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92761299	BVP353 72LED 30K 220V L57 15	830 warm white	3000 K	12,465 lm
92762999	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K	13,905 lm
92763699	BVP353 72LED 27K 220V L57 15 DMX	827 warm white	2700 K	11,385 lm
92764399	BVP353 72LED 30K 220V L57 15 DMX	830 warm white	3000 K	11,875 lm
92765099	BVP353 72LED 40K 220V L57 15 DMX	840 neutral white	4000 K	13,250 lm
92766799	BVP353 72LED RGB 220V L57 15 DMX	RGB	-	7,040 lm
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	RGBW	-	7,890 lm
92769899	BVP353 72LED 27K 220V L57 30	827 warm white	2700 K	12,375 lm
92770499	BVP353 72LED 30K 220V L57 30	830 warm white	3000 K	12,910 lm
92771199	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K	14,405 lm
92772899	BVP353 72LED 27K 220V L57 30 DMX	827 warm white	2700 K	11,790 lm
92773599	BVP353 72LED 30K 220V L57 30 DMX	830 warm white	3000 K	12,300 lm
92774299	BVP353 72LED 40K 220V L57 30 DMX	840 neutral white	4000 K	13,725 lm
92775999	BVP353 72LED RGB 220V L57 30 DMX	RGB	-	7,290 lm
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-	7,825 lm
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-	8,170 lm
92778099	BVP353 72LED 27K 220V L57 45	827 warm white	2700 K	11,950 lm
92779799	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K	12,465 lm
92780399	BVP353 72LED 40K 220V L57 45	840 neutral white	4000 K	13,905 lm
92781099	BVP353 72LED 27K 220V L57 45 DMX	827 warm white	2700 K	11,385 lm
92782799	BVP353 72LED 30K 220V L57 45 DMX	830 warm white	3000 K	11,875 lm
92783499	BVP353 72LED 40K 220V L57 45 DMX	840 neutral white	4000 K	13,250 lm
92784199	BVP353 72LED RGB 220V L57 45 DMX	RGB	-	7,040 lm
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	RGBW	-	7,555 lm
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-	7,890 lm
92535999	BVP353 18LED 27K 220V L21 10	827 warm white	2700 K	2,845 lm
92536699	BVP353 18LED 30K 220V L21 10	830 warm white	3000 K	2,965 lm
92537399	BVP353 18LED 40K 220V L21 10	840 neutral white	4000 K	3,310 lm
92538099	BVP353 18LED 27K 220V L21 10 DMX	827 warm white	2700 K	2,640 lm
92539799	BVP353 18LED 30K 220V L21 10 DMX	830 warm white	3000 K	2,755 lm
92540399	BVP353 18LED 40K 220V L21 10 DMX	840 neutral white	4000 K	3,075 lm
92541099	BVP353 18LED RGB 220V L21 10 DMX	RGB	-	1,565 lm
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	RGBW	-	1,860 lm
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	RGBW	-	1,945 lm
92544199	BVP353 18LED 27K 220V L21 15	827 warm white	2700 K	2,985 lm
92545899	BVP353 18LED 30K 220V L21 15	830 warm white	3000 K	3,115 lm
92546599	BVP353 18LED 40K 220V L21 15	840 neutral white	4000 K	3,475 lm
92547299	BVP353 18LED 27K 220V L21 15 DMX	827 warm white	2700 K	2,770 lm
92548999	BVP353 18LED 30K 220V L21 15 DMX	830 warm white	3000 K	2,890 lm
92549699	BVP353 18LED 40K 220V L21 15 DMX	840 neutral white	4000 K	3,225 lm
92550299	BVP353 18LED RGB 220V L21 15 DMX	RGB	-	1,640 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	RGBW	-	1,955 lm
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	RGBW	-	2,040 lm
92553399	BVP353 18LED 27K 220V L21 30	827 warm white	2700 K	3,090 lm
92554099	BVP353 18LED 30K 220V L21 30	830 warm white	3000 K	3,225 lm
92555799	BVP353 18LED 40K 220V L21 30	840 neutral white	4000 K	3,600 lm
92556499	BVP353 18LED 27K 220V L21 30 DMX	827 warm white	2700 K	2,870 lm
92557199	BVP353 18LED 30K 220V L21 30 DMX	830 warm white	3000 K	2,995 lm
92558899	BVP353 18LED 40K 220V L21 30 DMX	840 neutral white	4000 K	3,340 lm
92559599	BVP353 18LED RGB 220V L21 30 DMX	RGB	-	1,700 lm
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	RGBW	-	2,025 lm
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	RGBW	-	2,115 lm
92562599	BVP353 18LED 27K 220V L21 45	827 warm white	2700 K	2,985 lm
92563299	BVP353 18LED 30K 220V L21 45	830 warm white	3000 K	3,115 lm
92564999	BVP353 18LED 40K 220V L21 45	840 neutral white	4000 K	3,475 lm
92565699	BVP353 18LED 27K 220V L21 45 DMX	827 warm white	2700 K	2,770 lm
92566399	BVP353 18LED 30K 220V L21 45 DMX	830 warm white	3000 K	2,890 lm
92567099	BVP353 18LED 40K 220V L21 45 DMX	840 neutral white	4000 K	3,225 lm
92568799	BVP353 18LED RGB 220V L21 45 DMX	RGB	-	1,640 lm
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	RGBW	-	1,955 lm
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	RGBW	-	2,040 lm
92463599	BVP353 12LED 27K 220V L15 10	827 warm white	2700 K	1,760 lm
92464299	BVP353 12LED 30K 220V L15 10	830 warm white	3000 K	1,835 lm
92465999	BVP353 12LED 40K 220V L15 10	840 neutral white	4000 K	2,050 lm
92466699	BVP353 12LED 27K 220V L15 10 DMX	827 warm white	2700 K	1,615 lm
92467399	BVP353 12LED 30K 220V L15 10 DMX	830 warm white	3000 K	1,685 lm
92468099	BVP353 12LED 40K 220V L15 10 DMX	840 neutral white	4000 K	1,880 lm
92469799	BVP353 12LED RGB 220V L15 10 DMX	RGB	-	960 lm
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-	1,175 lm
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	RGBW	-	1,225 lm
92473499	BVP353 12LED 30K 220V L15 15	830 warm white	3000 K	1,925 lm
92481999	BVP353 12LED 27K 220V L15 30	827 warm white	2700 K	1,915 lm
92482699	BVP353 12LED 30K 220V L15 30	830 warm white	3000 K	1,995 lm
92483399	BVP353 12LED 40K 220V L15 30	840 neutral white	4000 K	2,225 lm
92484099	BVP353 12LED 27K 220V L15 30 DMX	827 warm white	2700 K	1,755 lm
92485799	BVP353 12LED 30K 220V L15 30 DMX	830 warm white	3000 K	1,830 lm
92486499	BVP353 12LED 40K 220V L15 30 DMX	840 neutral white	4000 K	2,045 lm
92487199	BVP353 12LED RGB 220V L15 30 DMX	RGB	-	1,045 lm
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	RGBW	-	1,275 lm
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	RGBW	-	1,330 lm
92490199	BVP353 12LED 27K 220V L15 45	827 warm white	2700 K	1,845 lm
92491899	BVP353 12LED 30K 220V L15 45	830 warm white	3000 K	1,925 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92492599	BVP353 12LED 40K 220V L15 45	840 neutral white	4000 K	2,150 lm
92493299	BVP353 12LED 27K 220V L15 45 DMX	827 warm white	2700 K	1,695 lm
92494999	BVP353 12LED 30K 220V L15 45 DMX	830 warm white	3000 K	1,770 lm
92495699	BVP353 12LED 40K 220V L15 45 DMX	840 neutral white	4000 K	1,975 lm
92496399	BVP353 12LED RGB 220V L15 45 DMX	RGB	-	1,010 lm
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	RGBW	-	1,230 lm
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	RGBW	-	1,285 lm
92643199	BVP353 36LED 27K 220V L35 10	827 warm white	2700 K	5,950 lm
92644899	BVP353 36LED 30K 220V L35 10	830 warm white	3000 K	6,205 lm
92645599	BVP353 36LED 40K 220V L35 10	840 neutral white	4000 K	6,925 lm
92646299	BVP353 36LED 27K 220V L35 10 DMX	827 warm white	2700 K	5,350 lm
92647999	BVP353 36LED 30K 220V L35 10 DMX	830 warm white	3000 K	5,585 lm
92648699	BVP353 36LED 40K 220V L35 10 DMX	840 neutral white	4000 K	6,230 lm
92649399	BVP353 36LED RGB 220V L35 10 DMX	RGB	-	3,290 lm
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	RGBW	-	3,640 lm
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	RGBW	-	3,805 lm
92652399	BVP353 36LED 27K 220V L35 15	827 warm white	2700 K	6,245 lm
92653099	BVP353 36LED 30K 220V L35 15	830 warm white	3000 K	6,515 lm
92654799	BVP353 36LED 40K 220V L35 15	840 neutral white	4000 K	7,270 lm
92655499	BVP353 36LED 27K 220V L35 15 DMX	827 warm white	2700 K	5,620 lm
92656199	BVP353 36LED 30K 220V L35 15 DMX	830 warm white	3000 K	5,860 lm
92657899	BVP353 36LED 40K 220V L35 15 DMX	840 neutral white	4000 K	6,540 lm
92658599	BVP353 36LED RGB 220V L35 15 DMX	RGB	-	3,455 lm
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	RGBW	-	3,825 lm
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	RGBW	-	3,995 lm
92661599	BVP353 36LED 27K 220V L35 30	827 warm white	2700 K	6,470 lm
92662299	BVP353 36LED 30K 220V L35 30	830 warm white	3000 K	6,750 lm
92663999	BVP353 36LED 40K 220V L35 30	840 neutral white	4000 K	7,530 lm
92664699	BVP353 36LED 27K 220V L35 30 DMX	827 warm white	2700 K	5,820 lm
92665399	BVP353 36LED 30K 220V L35 30 DMX	830 warm white	3000 K	6,070 lm
92666099	BVP353 36LED 40K 220V L35 30 DMX	840 neutral white	4000 K	6,775 lm
92667799	BVP353 36LED RGB 220V L35 30 DMX	RGB	-	3,580 lm
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	RGBW	-	3,960 lm
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	RGBW	-	4,135 lm
92670799	BVP353 36LED 27K 220V L35 45	827 warm white	2700 K	6,245 lm
92671499	BVP353 36LED 30K 220V L35 45	830 warm white	3000 K	6,515 lm
92672199	BVP353 36LED 40K 220V L35 45	840 neutral white	4000 K	7,270 lm
92673899	BVP353 36LED 27K 220V L35 45 DMX	827 warm white	2700 K	5,620 lm
92674599	BVP353 36LED 30K 220V L35 45 DMX	830 warm white	3000 K	5,860 lm
92675299	BVP353 36LED 40K 220V L35 45 DMX	840 neutral white	4000 K	6,540 lm
92676999	BVP353 36LED RGB 220V L35 45 DMX	RGB	-	3,455 lm
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	RGBW	-	3,825 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	RGBW	-	3,995 lm
92571799	BVP353 24LED 27K 220V L24 10	827 warm white	2700 K	3,615 lm
92572499	BVP353 24LED 30K 220V L24 10	830 warm white	3000 K	3,770 lm
92573199	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K	4,205 lm
92574899	BVP353 24LED 27K 220V L24 10 DMX	827 warm white	2700 K	3,465 lm
92575599	BVP353 24LED 30K 220V L24 10 DMX	830 warm white	3000 K	3,615 lm
92576299	BVP353 24LED 40K 220V L24 10 DMX	840 neutral white	4000 K	4,035 lm
92577999	BVP353 24LED RGB 220V L24 10 DMX	RGB	-	2,085 lm
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	RGBW	-	2,350 lm
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	RGBW	-	2,450 lm
92580999	BVP353 24LED 27K 220V L24 15	827 warm white	2700 K	3,795 lm
92581699	BVP353 24LED 30K 220V L24 15	830 warm white	3000 K	3,955 lm
92582399	BVP353 24LED 40K 220V L24 15	840 neutral white	4000 K	4,415 lm
92583099	BVP353 24LED 27K 220V L24 15 DMX	827 warm white	2700 K	3,640 lm
92584799	BVP353 24LED 30K 220V L24 15 DMX	830 warm white	3000 K	3,800 lm
92585499	BVP353 24LED 40K 220V L24 15 DMX	840 neutral white	4000 K	4,235 lm
92586199	BVP353 24LED RGB 220V L24 15 DMX	RGB	-	2,190 lm
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	RGBW	-	2,465 lm
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	RGBW	-	2,575 lm
92589299	BVP353 24LED 27K 220V L24 30	827 warm white	2700 K	3,930 lm
92590899	BVP353 24LED 30K 220V L24 30	830 warm white	3000 K	4,100 lm
92592299	BVP353 24LED 27K 220V L24 30 DMX	827 warm white	2700 K	3,770 lm
92593999	BVP353 24LED 30K 220V L24 30 DMX	830 warm white	3000 K	3,935 lm
92594699	BVP353 24LED 40K 220V L24 30 DMX	840 neutral white	4000 K	4,390 lm
92595399	BVP353 24LED RGB 220V L24 30 DMX	RGB	-	2,270 lm
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-	2,555 lm
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	RGBW	-	2,665 lm
92598499	BVP353 24LED 27K 220V L24 45	827 warm white	2700 K	3,795 lm
92599199	BVP353 24LED 30K 220V L24 45	830 warm white	3000 K	3,955 lm
92600499	BVP353 24LED 40K 220V L24 45	840 neutral white	4000 K	4,415 lm
92601199	BVP353 24LED 27K 220V L24 45 DMX	827 warm white	2700 K	3,640 lm
92602899	BVP353 24LED 30K 220V L24 45 DMX	830 warm white	3000 K	3,800 lm
92603599	BVP353 24LED 40K 220V L24 45 DMX	840 neutral white	4000 K	4,235 lm
92604299	BVP353 24LED RGB 220V L24 45 DMX	RGB	-	2,190 lm
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	RGBW	-	2,465 lm
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	RGBW	-	2,575 lm
92715599	BVP353 60LED 27K 220V L50 10	827 warm white	2700 K	9,150 lm
92717999	BVP353 60LED 40K 220V L50 10	840 neutral white	4000 K	10,645 lm
92718699	BVP353 60LED 27K 220V L50 10 DMX	827 warm white	2700 K	8,805 lm
92719399	BVP353 60LED 30K 220V L50 10 DMX	830 warm white	3000 K	9,185 lm
92720999	BVP353 60LED 40K 220V L50 10 DMX	840 neutral white	4000 K	10,250 lm
92721699	BVP353 60LED RGB 220V L50 10 DMX	RGB	-	5,215 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	RGBW	-	5,995 lm
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	RGBW	-	6,260 lm
92724799	BVP353 60LED 27K 220V L50 15	827 warm white	2700 K	9,605 lm
92725499	BVP353 60LED 30K 220V L50 15	830 warm white	3000 K	10,020 lm
92726199	BVP353 60LED 40K 220V L50 15	840 neutral white	4000 K	11,180 lm
92727899	BVP353 60LED 27K 220V L50 15 DMX	827 warm white	2700 K	9,245 lm
92728599	BVP353 60LED 30K 220V L50 15 DMX	830 warm white	3000 K	9,645 lm
92729299	BVP353 60LED 40K 220V L50 15 DMX	840 neutral white	4000 K	10,760 lm
92730899	BVP353 60LED RGB 220V L50 15 DMX	RGB	-	5,480 lm
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	RGBW	-	6,295 lm
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	RGBW	-	6,575 lm
92733999	BVP353 60LED 27K 220V L50 30	827 warm white	2700 K	9,950 lm
92734699	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K	10,380 lm
92735399	BVP353 60LED 40K 220V L50 30	840 neutral white	4000 K	11,580 lm
92736099	BVP353 60LED 27K 220V L50 30 DMX	827 warm white	2700 K	9,575 lm
92737799	BVP353 60LED 30K 220V L50 30 DMX	830 warm white	3000 K	9,990 lm
92738499	BVP353 60LED 40K 220V L50 30 DMX	840 neutral white	4000 K	11,145 lm
92739199	BVP353 60LED RGB 220V L50 30 DMX	RGB	-	5,675 lm
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	RGBW	-	6,520 lm
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	RGBW	-	6,810 lm
92742199	BVP353 60LED 27K 220V L50 45	827 warm white	2700 K	9,605 lm
92743899	BVP353 60LED 30K 220V L50 45	830 warm white	3000 K	10,020 lm
92744599	BVP353 60LED 40K 220V L50 45	840 neutral white	4000 K	11,180 lm
92745299	BVP353 60LED 27K 220V L50 45 DMX	827 warm white	2700 K	9,245 lm
92746999	BVP353 60LED 30K 220V L50 45 DMX	830 warm white	3000 K	9,645 lm
92747699	BVP353 60LED 40K 220V L50 45 DMX	840 neutral white	4000 K	10,760 lm
92748399	BVP353 60LED RGB 220V L50 45 DMX	RGB	-	5,480 lm
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	RGBW	-	6,295 lm
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	RGBW	-	6,575 lm
92499499	BVP353 16LED 27K 220V L18 10	827 warm white	2700 K	2,755 lm
92500799	BVP353 16LED 30K 220V L18 10	830 warm white	3000 K	2,875 lm
92501499	BVP353 16LED 40K 220V L18 10	840 neutral white	4000 K	3,205 lm
92502199	BVP353 16LED 27K 220V L18 10 DMX	827 warm white	2700 K	2,060 lm
92503899	BVP353 16LED 30K 220V L18 10 DMX	830 warm white	3000 K	2,145 lm
92504599	BVP353 16LED 40K 220V L18 10 DMX	840 neutral white	4000 K	2,395 lm
92505299	BVP353 15LED RGB 220V L18 10 DMX	RGB	-	1,200 lm
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	RGBW	-	1,425 lm
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	RGBW	-	1,490 lm
92508399	BVP353 16LED 27K 220V L18 15	827 warm white	2700 K	2,895 lm
92509099	BVP353 16LED 30K 220V L18 15	830 warm white	3000 K	3,020 lm
92510699	BVP353 16LED 40K 220V L18 15	840 neutral white	4000 K	3,365 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92511399	BVP353 16LED 27K 220V L18 15 DMX	827 warm white	2700 K	2,160 lm
92512099	BVP353 16LED 30K 220V L18 15 DMX	830 warm white	3000 K	2,255 lm
92513799	BVP353 16LED 40K 220V L18 15 DMX	840 neutral white	4000 K	2,515 lm
92514499	BVP353 15LED RGB 220V L18 15 DMX	RGB	-	1,260 lm
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	RGBW	-	1,500 lm
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	RGBW	-	1,565 lm
92517599	BVP353 16LED 27K 220V L18 30	827 warm white	2700 K	2,995 lm
92518299	BVP353 16LED 30K 220V L18 30	830 warm white	3000 K	3,125 lm
92519999	BVP353 16LED 40K 220V L18 30	840 neutral white	4000 K	3,490 lm
92520599	BVP353 16LED 27K 220V L18 30 DMX	827 warm white	2700 K	2,240 lm
92521299	BVP353 16LED 30K 220V L18 30 DMX	830 warm white	3000 K	2,335 lm
92522999	BVP353 16LED 40K 220V L18 30 DMX	840 neutral white	4000 K	2,605 lm
92523699	BVP353 15LED RGB 220V L18 30 DMX	RGB	-	1,305 lm
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	RGBW	-	1,550 lm
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	RGBW	-	1,620 lm
92526799	BVP353 16LED 27K 220V L18 45	827 warm white	2700 K	2,895 lm
92527499	BVP353 16LED 30K 220V L18 45	830 warm white	3000 K	3,020 lm
92528199	BVP353 16LED 40K 220V L18 45	840 neutral white	4000 K	3,365 lm
92529899	BVP353 16LED 27K 220V L18 45 DMX	827 warm white	2700 K	2,160 lm
92530499	BVP353 16LED 30K 220V L18 45 DMX	830 warm white	3000 K	2,255 lm
92531199	BVP353 16LED 40K 220V L18 45 DMX	840 neutral white	4000 K	2,515 lm
92532899	BVP353 15LED RGB 220V L18 45 DMX	RGB	-	1,260 lm
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	RGBW	-	1,500 lm
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	RGBW	-	1,565 lm
92895400	BVP355 216LED 27K 220V L57 10	827 warm white	2700 K	34,145 lm
92896100	BVP355 216LED 30K 220V L57 10	830 warm white	3000 K	35,615 lm
92897800	BVP355 216LED 40K 220V L57 10	840 neutral white	4000 K	39,740 lm
92898500	BVP355 216LED 27K 220V L57 10 DMX	827 warm white	2700 K	32,535 lm
92899200	BVP355 216LED 30K 220V L57 10 DMX	830 warm white	3000 K	33,935 lm
92900500	BVP355 216LED 40K 220V L57 10 DMX	840 neutral white	4000 K	37,860 lm
92901200	BVP355 216LED RGB 220V L57 10 DMX	RGB	-	20,115 lm
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	RGBW	-	21,590 lm
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	RGBW	-	22,550 lm
92904300	BVP355 216LED 27K 220V L57 15	827 warm white	2700 K	35,850 lm
92905000	BVP355 216LED 30K 220V L57 15	830 warm white	3000 K	37,400 lm
92906700	BVP355 216LED 40K 220V L57 15	840 neutral white	4000 K	41,725 lm
92907400	BVP355 216LED 27K 220V L57 15 DMX	827 warm white	2700 K	34,160 lm
92908100	BVP355 216LED 30K 220V L57 15 DMX	830 warm white	3000 K	35,635 lm
92909800	BVP355 216LED 40K 220V L57 15 DMX	840 neutral white	4000 K	39,755 lm
92910400	BVP355 216LED RGB 220V L57 15 DMX	RGB	-	21,120 lm
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	RGBW	-	22,670 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	RGBW	-	23,675 lm
92913500	BVP355 216LED 27K 220V L57 30	827 warm white	2700 K	37,135 lm
92914200	BVP355 216LED 30K 220V L57 30	830 warm white	3000 K	38,735 lm
92915900	BVP355 216LED 40K 220V L57 30	840 neutral white	4000 K	43,215 lm
92916600	BVP355 216LED 27K 220V L57 30 DMX	827 warm white	2700 K	35,380 lm
92917300	BVP355 216LED 30K 220V L57 30 DMX	830 warm white	3000 K	36,905 lm
92918000	BVP355 216LED 40K 220V L57 30 DMX	840 neutral white	4000 K	41,175 lm
92919700	BVP355 216LED RGB 220V L57 30 DMX	RGB	-	21,875 lm
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	RGBW	-	23,480 lm
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	RGBW	-	24,520 lm
92922700	BVP355 216LED 27K 220V L57 45	827 warm white	2700 K	35,850 lm
92923400	BVP355 216LED 30K 220V L57 45	830 warm white	3000 K	37,400 lm
92924100	BVP355 216LED 40K 220V L57 45	840 neutral white	4000 K	41,725 lm
92925800	BVP355 216LED 27K 220V L57 45 DMX	827 warm white	2700 K	34,160 lm
92926500	BVP355 216LED 30K 220V L57 45 DMX	830 warm white	3000 K	35,635 lm
92927200	BVP355 216LED 40K 220V L57 45 DMX	840 neutral white	4000 K	39,755 lm
92928900	BVP355 216LED RGB 220V L57 45 DMX	RGB	-	21,120 lm
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	RGBW	-	22,670 lm
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	RGBW	-	23,675 lm
92931900	BVP355 180LED 27K 220V L50 10	827 warm white	2700 K	27,450 lm
92932600	BVP355 180LED 30K 220V L50 10	830 warm white	3000 K	28,630 lm
92933300	BVP355 180LED 40K 220V L50 10	840 neutral white	4000 K	31,945 lm
92934000	BVP355 180LED 27K 220V L50 10 DMX	827 warm white	2700 K	26,425 lm
92935700	BVP355 180LED 30K 220V L50 10 DMX	830 warm white	3000 K	27,565 lm
92936400	BVP355 180LED 40K 220V L50 10 DMX	840 neutral white	4000 K	30,750 lm
92937100	BVP355 180LED RGB 220V L50 10 DMX	RGB	-	15,655 lm
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	RGBW	-	17,990 lm
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	RGBW	-	18,790 lm
92940100	BVP355 180LED 27K 220V L50 15	827 warm white	2700 K	28,820 lm
92941800	BVP355 180LED 30K 220V L50 15	830 warm white	3000 K	30,065 lm
92942500	BVP355 180LED 40K 220V L50 15	840 neutral white	4000 K	33,540 lm
92943200	BVP355 180LED 27K 220V L50 15 DMX	827 warm white	2700 K	27,745 lm
92944900	BVP355 180LED 30K 220V L50 15 DMX	830 warm white	3000 K	28,940 lm
92945600	BVP355 180LED 40K 220V L50 15 DMX	840 neutral white	4000 K	32,290 lm
92946300	BVP355 180LED RGB 220V L50 15 DMX	RGB	-	16,440 lm
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	RGBW	-	18,890 lm
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	RGBW	-	19,730 lm
92949400	BVP355 180LED 27K 220V L50 30	827 warm white	2700 K	29,850 lm
92950000	BVP355 180LED 30K 220V L50 30	830 warm white	3000 K	31,140 lm
92951700	BVP355 180LED 40K 220V L50 30	840 neutral white	4000 K	34,740 lm
92952400	BVP355 180LED 27K 220V L50 30 DMX	827 warm white	2700 K	28,735 lm
92953100	BVP355 180LED 30K 220V L50 30 DMX	830 warm white	3000 K	29,975 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92954800	BVP355 180LED 40K 220V L50 30 DMX	840 neutral white	4000 K	33,445 lm
92955500	BVP355 180LED RGB 220V L50 30 DMX	RGB	-	17,025 lm
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	RGBW	-	19,565 lm
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	RGBW	-	20,435 lm
92958600	BVP355 180LED 27K 220V L50 45	827 warm white	2700 K	28,820 lm
92959300	BVP355 180LED 30K 220V L50 45	830 warm white	3000 K	30,065 lm
92960900	BVP355 180LED 40K 220V L50 45	840 neutral white	4000 K	33,540 lm
92961600	BVP355 180LED 27K 220V L50 45 DMX	827 warm white	2700 K	27,745 lm
92962300	BVP355 180LED 30K 220V L50 45 DMX	830 warm white	3000 K	28,940 lm
92963000	BVP355 180LED 40K 220V L50 45 DMX	840 neutral white	4000 K	32,290 lm
92964700	BVP355 180LED RGB 220V L50 45 DMX	RGB	-	16,440 lm
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	RGBW	-	18,890 lm
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	RGBW	-	19,730 lm
92679099	BVP353 48LED 27K 220V L40 10	827 warm white	2700 K	7,440 lm
92680699	BVP353 48LED 30K 220V L40 10	830 warm white	3000 K	7,760 lm
92681399	BVP353 48LED 40K 220V L40 10	840 neutral white	4000 K	8,655 lm
92682099	BVP353 48LED 27K 220V L40 10 DMX	827 warm white	2700 K	6,860 lm
92683799	BVP353 48LED 30K 220V L40 10 DMX	830 warm white	3000 K	7,155 lm
92684499	BVP353 48LED 40K 220V L40 10 DMX	840 neutral white	4000 K	7,985 lm
92685199	BVP353 48LED RGB 220V L40 10 DMX	RGB	-	3,830 lm
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	RGBW	-	5,250 lm
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	RGBW	-	5,485 lm
92688299	BVP353 48LED 27K 220V L40 15	827 warm white	2700 K	7,810 lm
92689999	BVP353 48LED 30K 220V L40 15	830 warm white	3000 K	8,145 lm
92690599	BVP353 48LED 40K 220V L40 15	840 neutral white	4000 K	9,090 lm
92691299	BVP353 48LED 27K 220V L40 15 DMX	827 warm white	2700 K	7,205 lm
92692999	BVP353 48LED 30K 220V L40 15 DMX	830 warm white	3000 K	7,515 lm
92693699	BVP353 48LED 40K 220V L40 15 DMX	840 neutral white	4000 K	8,385 lm
92694399	BVP353 48LED RGB 220V L40 15 DMX	RGB	-	4,020 lm
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	RGBW	-	5,515 lm
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	RGBW	-	5,760 lm
92697499	BVP353 48LED 27K 220V L40 30	827 warm white	2700 K	8,090 lm
92698199	BVP353 48LED 30K 220V L40 30	830 warm white	3000 K	8,440 lm
92699899	BVP353 48LED 40K 220V L40 30	840 neutral white	4000 K	9,415 lm
92700199	BVP353 48LED 27K 220V L40 30 DMX	827 warm white	2700 K	7,460 lm
92701899	BVP353 48LED 30K 220V L40 30 DMX	830 warm white	3000 K	7,785 lm
92702599	BVP353 48LED 40K 220V L40 30 DMX	840 neutral white	4000 K	8,685 lm
92703299	BVP353 48LED RGB 220V L40 30 DMX	RGB	-	4,165 lm
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	RGBW	-	5,710 lm
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	RGBW	-	5,965 lm
92706399	BVP353 48LED 27K 220V L40 45	827 warm white	2700 K	7,810 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
92707099	BVP353 48LED 30K 220V L40 45	830 warm white	3000 K	8,145 lm
92708799	BVP353 48LED 40K 220V L40 45	840 neutral white	4000 K	9,090 lm
92709499	BVP353 48LED 27K 220V L40 45 DMX	827 warm white	2700 K	7,205 lm
92710099	BVP353 48LED 30K 220V L40 45 DMX	830 warm white	3000 K	7,515 lm
92711799	BVP353 48LED 40K 220V L40 45 DMX	840 neutral white	4000 K	8,385 lm
92712499	BVP353 48LED RGB 220V L40 45 DMX	RGB	-	4,020 lm
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	RGBW	-	5,515 lm
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	RGBW	-	5,760 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92607399	BVP353 30LED 27K 220V L30 10	60 W	92788900	BVP354 96LED 30K 220V L40 10	200 W
92608099	BVP353 30LED 30K 220V L30 10	60 W	92789600	BVP354 96LED 40K 220V L40 10	200 W
92609799	BVP353 30LED 40K 220V L30 10	60 W	92790200	BVP354 96LED 27K 220V L40 10 DMX	200 W
92610399	BVP353 30LED 27K 220V L30 10 DMX	60 W	92791900	BVP354 96LED 30K 220V L40 10 DMX	200 W
92611099	BVP353 30LED 30K 220V L30 10 DMX	60 W	92792600	BVP354 96LED 40K 220V L40 10 DMX	200 W
92612799	BVP353 30LED 40K 220V L30 10 DMX	60 W	92793300	BVP354 96LED RGB 220V L40 10 DMX	200 W
92613499	BVP353 30LED RGB 220V L30 10 DMX	60 W	92794000	BVP354 96LED RGBWW 220V L40 10 DMX	200 W
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	60 W	92795700	BVP354 96LED RGBNW 220V L40 10 DMX	200 W
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	60 W	92796400	BVP354 96LED 27K 220V L40 15	200 W
92616599	BVP353 30LED 27K 220V L30 15	60 W	92797100	BVP354 96LED 30K 220V L40 15	200 W
92617299	BVP353 30LED 30K 220V L30 15	60 W	92798800	BVP354 96LED 40K 220V L40 15	200 W
92618999	BVP353 30LED 40K 220V L30 15	60 W	92799500	BVP354 96LED 27K 220V L40 15 DMX	200 W
92619699	BVP353 30LED 27K 220V L30 15 DMX	60 W	92800800	BVP354 96LED 30K 220V L40 15 DMX	200 W
92620299	BVP353 30LED 30K 220V L30 15 DMX	60 W	92801500	BVP354 96LED 40K 220V L40 15 DMX	200 W
92621999	BVP353 30LED 40K 220V L30 15 DMX	60 W	92802200	BVP354 96LED RGB 220V L40 15 DMX	200 W
92622699	BVP353 30LED RGB 220V L30 15 DMX	60 W	92803900	BVP354 96LED RGBWW 220V L40 15 DMX	200 W
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	60 W	92804600	BVP354 96LED RGBNW 220V L40 15 DMX	200 W
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	60 W	92805300	BVP354 96LED 27K 220V L40 30	200 W
92625799	BVP353 30LED 27K 220V L30 30	60 W	92806000	BVP354 96LED 30K 220V L40 30	200 W
92626499	BVP353 30LED 30K 220V L30 30	60 W	92807700	BVP354 96LED 40K 220V L40 30	200 W
92627199	BVP353 30LED 40K 220V L30 30	60 W	92808400	BVP354 96LED 27K 220V L40 30 DMX	200 W
92628899	BVP353 30LED 27K 220V L30 30 DMX	60 W	92809100	BVP354 96LED 30K 220V L40 30 DMX	200 W
92629599	BVP353 30LED 30K 220V L30 30 DMX	60 W	92810700	BVP354 96LED 40K 220V L40 30 DMX	200 W
92630199	BVP353 30LED 40K 220V L30 30 DMX	60 W	92811400	BVP354 96LED RGB 220V L40 30 DMX	200 W
92631899	BVP353 30LED RGB 220V L30 30 DMX	60 W	92812100	BVP354 96LED RGBWW 220V L40 30 DMX	200 W
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	60 W	92813800	BVP354 96LED RGBNW 220V L40 30 DMX	200 W
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	60 W	92814500	BVP354 96LED 27K 220V L40 45	200 W
92634999	BVP353 30LED 27K 220V L30 45	60 W	92815200	BVP354 96LED 30K 220V L40 45	200 W
92635699	BVP353 30LED 30K 220V L30 45	60 W	92816900	BVP354 96LED 40K 220V L40 45	200 W
92636399	BVP353 30LED 40K 220V L30 45	60 W	92817600	BVP354 96LED 27K 220V L40 45 DMX	200 W
92637099	BVP353 30LED 27K 220V L30 45 DMX	60 W	92818300	BVP354 96LED 30K 220V L40 45 DMX	200 W
92638799	BVP353 30LED 30K 220V L30 45 DMX	60 W	92819000	BVP354 96LED 40K 220V L40 45 DMX	200 W
92639499	BVP353 30LED 40K 220V L30 45 DMX	60 W	92820600	BVP354 96LED RGB 220V L40 45 DMX	200 W
92640099	BVP353 30LED RGB 220V L30 45 DMX	60 W	92821300	BVP354 96LED RGBWW 220V L40 45 DMX	200 W
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	60 W	92822000	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	60 W	92823700	BVP354 120LED 27K 220V L50 10	240 W
92787200	BVP354 96LED 27K 220V L40 10	200 W	92824400	BVP354 120LED 30K 220V L50 10	240 W

Order Code	Full Product Name	Power Consumption
92825100	BVP354 120LED 40K 220V L50 10	240 W
92826800	BVP354 120LED 27K 220V L50 10 DMX	240 W
92827500	BVP354 120LED 30K 220V L50 10 DMX	240 W
92828200	BVP354 120LED 40K 220V L50 10 DMX	240 W
92829900	BVP354 120LED RGB 220V L50 10 DMX	240 W
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	240 W
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	240 W
92832900	BVP354 120LED 27K 220V L50 15	240 W
92833600	BVP354 120LED 30K 220V L50 15	240 W
92834300	BVP354 120LED 40K 220V L50 15	240 W
92835000	BVP354 120LED 27K 220V L50 15 DMX	240 W
92836700	BVP354 120LED 30K 220V L50 15 DMX	240 W
92837400	BVP354 120LED 40K 220V L50 15 DMX	240 W
92838100	BVP354 120LED RGB 220V L50 15 DMX	240 W
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	240 W
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	240 W
92841100	BVP354 120LED 27K 220V L50 30	240 W
92842800	BVP354 120LED 30K 220V L50 30	240 W
92843500	BVP354 120LED 40K 220V L50 30	240 W
92844200	BVP354 120LED 27K 220V L50 30 DMX	240 W
92845900	BVP354 120LED 30K 220V L50 30 DMX	240 W
92846600	BVP354 120LED 40K 220V L50 30 DMX	240 W
92847300	BVP354 120LED RGB 220V L50 30 DMX	240 W
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	240 W
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	240 W
92850300	BVP354 120LED 27K 220V L50 45	240 W
92851000	BVP354 120LED 30K 220V L50 45	240 W
92852700	BVP354 120LED 40K 220V L50 45	240 W
92853400	BVP354 120LED 27K 220V L50 45 DMX	240 W
92854100	BVP354 120LED 30K 220V L50 45 DMX	240 W
92855800	BVP354 120LED 40K 220V L50 45 DMX	240 W
92856500	BVP354 120LED RGB 220V L50 45 DMX	240 W
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	240 W
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	240 W
92859600	BVP354 144LED 27K 220V L57 10	300 W
92860200	BVP354 144LED 30K 220V L57 10	300 W
92861900	BVP354 144LED 40K 220V L57 10	300 W
92862600	BVP354 144LED 27K 220V L57 10 DMX	300 W
92863300	BVP354 144LED 30K 220V L57 10 DMX	300 W
92864000	BVP354 144LED 40K 220V L57 10 DMX	300 W
92865700	BVP354 144LED RGB 220V L57 10 DMX	300 W
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	300 W
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
92868800	BVP354 144LED 27K 220V L57 15	300 W
92869500	BVP354 144LED 30K 220V L57 15	300 W
92870100	BVP354 144LED 40K 220V L57 15	300 W
92871800	BVP354 144LED 27K 220V L57 15 DMX	300 W
92872500	BVP354 144LED 30K 220V L57 15 DMX	300 W
92873200	BVP354 144LED 40K 220V L57 15 DMX	300 W
92874900	BVP354 144LED RGB 220V L57 15 DMX	300 W
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	300 W
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	300 W

Order Code	Full Product Name	Power Consumption
92877000	BVP354 144LED 27K 220V L57 30	300 W
92878700	BVP354 144LED 30K 220V L57 30	300 W
92879400	BVP354 144LED 40K 220V L57 30	300 W
92880000	BVP354 144LED 27K 220V L57 30 DMX	300 W
92881700	BVP354 144LED 30K 220V L57 30 DMX	300 W
92882400	BVP354 144LED 40K 220V L57 30 DMX	300 W
92883100	BVP354 144LED RGB 220V L57 30 DMX	300 W
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	300 W
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	300 W
92886200	BVP354 144LED 27K 220V L57 45	300 W
92887900	BVP354 144LED 30K 220V L57 45	300 W
92888600	BVP354 144LED 40K 220V L57 45	300 W
92889300	BVP354 144LED 27K 220V L57 45 DMX	300 W
92890900	BVP354 144LED 30K 220V L57 45 DMX	300 W
92891600	BVP354 144LED 40K 220V L57 45 DMX	300 W
92892300	BVP354 144LED RGB 220V L57 45 DMX	300 W
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	300 W
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
92751399	BVP353 72LED 27K 220V L57 10	150 W
92752099	BVP353 72LED 30K 220V L57 10	150 W
92753799	BVP353 72LED 40K 220V L57 10	150 W
92754499	BVP353 72LED 27K 220V L57 10 DMX	150 W
92755199	BVP353 72LED 30K 220V L57 10 DMX	150 W
92756899	BVP353 72LED 40K 220V L57 10 DMX	150 W
92757599	BVP353 72LED RGB 220V L57 10 DMX	150 W
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
92760599	BVP353 72LED 27K 220V L57 15	150 W
92761299	BVP353 72LED 30K 220V L57 15	150 W
92762999	BVP353 72LED 40K 220V L57 15	150 W
92763699	BVP353 72LED 27K 220V L57 15 DMX	150 W
92764399	BVP353 72LED 30K 220V L57 15 DMX	150 W
92765099	BVP353 72LED 40K 220V L57 15 DMX	150 W
92766799	BVP353 72LED RGB 220V L57 15 DMX	150 W
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
92769899	BVP353 72LED 27K 220V L57 30	150 W
92770499	BVP353 72LED 30K 220V L57 30	150 W
92771199	BVP353 72LED 40K 220V L57 30	150 W
92772899	BVP353 72LED 27K 220V L57 30 DMX	150 W
92773599	BVP353 72LED 30K 220V L57 30 DMX	150 W
92774299	BVP353 72LED 40K 220V L57 30 DMX	150 W
92775999	BVP353 72LED RGB 220V L57 30 DMX	150 W
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
92778099	BVP353 72LED 27K 220V L57 45	150 W
92779799	BVP353 72LED 30K 220V L57 45	150 W
92780399	BVP353 72LED 40K 220V L57 45	150 W
92781099	BVP353 72LED 27K 220V L57 45 DMX	150 W
92782799	BVP353 72LED 30K 220V L57 45 DMX	150 W
92783499	BVP353 72LED 40K 220V L57 45 DMX	150 W
92784199	BVP353 72LED RGB 220V L57 45 DMX	150 W

Order Code	Full Product Name	Power Consumption
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
92535999	BVP353 18LED 27K 220V L21 10	40 W
92536699	BVP353 18LED 30K 220V L21 10	40 W
92537399	BVP353 18LED 40K 220V L21 10	40 W
92538099	BVP353 18LED 27K 220V L21 10 DMX	40 W
92539799	BVP353 18LED 30K 220V L21 10 DMX	40 W
92540399	BVP353 18LED 40K 220V L21 10 DMX	40 W
92541099	BVP353 18LED RGB 220V L21 10 DMX	40 W
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	40 W
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
92544199	BVP353 18LED 27K 220V L21 15	40 W
92545899	BVP353 18LED 30K 220V L21 15	40 W
92546599	BVP353 18LED 40K 220V L21 15	40 W
92547299	BVP353 18LED 27K 220V L21 15 DMX	40 W
92548999	BVP353 18LED 30K 220V L21 15 DMX	40 W
92549699	BVP353 18LED 40K 220V L21 15 DMX	40 W
92550299	BVP353 18LED RGB 220V L21 15 DMX	40 W
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	40 W
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
92553399	BVP353 18LED 27K 220V L21 30	40 W
92554099	BVP353 18LED 30K 220V L21 30	40 W
92555799	BVP353 18LED 40K 220V L21 30	40 W
92556499	BVP353 18LED 27K 220V L21 30 DMX	40 W
92557199	BVP353 18LED 30K 220V L21 30 DMX	40 W
92558899	BVP353 18LED 40K 220V L21 30 DMX	40 W
92559599	BVP353 18LED RGB 220V L21 30 DMX	40 W
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	40 W
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
92562599	BVP353 18LED 27K 220V L21 45	40 W
92563299	BVP353 18LED 30K 220V L21 45	40 W
92564999	BVP353 18LED 40K 220V L21 45	40 W
92565699	BVP353 18LED 27K 220V L21 45 DMX	40 W
92566399	BVP353 18LED 30K 220V L21 45 DMX	40 W
92567099	BVP353 18LED 40K 220V L21 45 DMX	40 W
92568799	BVP353 18LED RGB 220V L21 45 DMX	40 W
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	40 W
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	40 W
92463599	BVP353 12LED 27K 220V L15 10	24 W
92464299	BVP353 12LED 30K 220V L15 10	24 W
92465999	BVP353 12LED 40K 220V L15 10	24 W
92466699	BVP353 12LED 27K 220V L15 10 DMX	24 W
92467399	BVP353 12LED 30K 220V L15 10 DMX	24 W
92468099	BVP353 12LED 40K 220V L15 10 DMX	24 W
92469799	BVP353 12LED RGB 220V L15 10 DMX	24 W
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	24 W
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	24 W
92473499	BVP353 12LED 30K 220V L15 15	24 W
92481999	BVP353 12LED 27K 220V L15 30	24 W
92482699	BVP353 12LED 30K 220V L15 30	24 W
92483399	BVP353 12LED 40K 220V L15 30	24 W
92484099	BVP353 12LED 27K 220V L15 30 DMX	24 W

Order Code	Full Product Name	Power Consumption
92485799	BVP353 12LED 30K 220V L15 30 DMX	24 W
92486499	BVP353 12LED 40K 220V L15 30 DMX	24 W
92487199	BVP353 12LED RGB 220V L15 30 DMX	24 W
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	24 W
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	24 W
92490199	BVP353 12LED 27K 220V L15 45	24 W
92491899	BVP353 12LED 30K 220V L15 45	24 W
92492599	BVP353 12LED 40K 220V L15 45	24 W
92493299	BVP353 12LED 27K 220V L15 45 DMX	24 W
92494999	BVP353 12LED 30K 220V L15 45 DMX	24 W
92495699	BVP353 12LED 40K 220V L15 45 DMX	24 W
92496399	BVP353 12LED RGB 220V L15 45 DMX	24 W
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	24 W
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	24 W
92643199	BVP353 36LED 27K 220V L35 10	80 W
92644899	BVP353 36LED 30K 220V L35 10	80 W
92645599	BVP353 36LED 40K 220V L35 10	80 W
92646299	BVP353 36LED 27K 220V L35 10 DMX	80 W
92647999	BVP353 36LED 30K 220V L35 10 DMX	80 W
92648699	BVP353 36LED 40K 220V L35 10 DMX	80 W
92649399	BVP353 36LED RGB 220V L35 10 DMX	80 W
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	80 W
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	80 W
92652399	BVP353 36LED 27K 220V L35 15	80 W
92653099	BVP353 36LED 30K 220V L35 15	80 W
92654799	BVP353 36LED 40K 220V L35 15	80 W
92655499	BVP353 36LED 27K 220V L35 15 DMX	80 W
92656199	BVP353 36LED 30K 220V L35 15 DMX	80 W
92657899	BVP353 36LED 40K 220V L35 15 DMX	80 W
92658599	BVP353 36LED RGB 220V L35 15 DMX	80 W
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	80 W
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	80 W
92661599	BVP353 36LED 27K 220V L35 30	80 W
92662299	BVP353 36LED 30K 220V L35 30	80 W
92663999	BVP353 36LED 40K 220V L35 30	80 W
92664699	BVP353 36LED 27K 220V L35 30 DMX	80 W
92665399	BVP353 36LED 30K 220V L35 30 DMX	80 W
92666099	BVP353 36LED 40K 220V L35 30 DMX	80 W
92667799	BVP353 36LED RGB 220V L35 30 DMX	80 W
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	80 W
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	80 W
92670799	BVP353 36LED 27K 220V L35 45	80 W
92671499	BVP353 36LED 30K 220V L35 45	80 W
92672199	BVP353 36LED 40K 220V L35 45	80 W
92673899	BVP353 36LED 27K 220V L35 45 DMX	80 W
92674599	BVP353 36LED 30K 220V L35 45 DMX	80 W
92675299	BVP353 36LED 40K 220V L35 45 DMX	80 W
92676999	BVP353 36LED RGB 220V L35 45 DMX	80 W
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	80 W
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
92571799	BVP353 24LED 27K 220V L24 10	50 W
92572499	BVP353 24LED 30K 220V L24 10	50 W

Order Code	Full Product Name	Power Consumption
92573199	BVP353 24LED 40K 220V L24 10	50 W
92574899	BVP353 24LED 27K 220V L24 10 DMX	50 W
92575599	BVP353 24LED 30K 220V L24 10 DMX	50 W
92576299	BVP353 24LED 40K 220V L24 10 DMX	50 W
92577999	BVP353 24LED RGB 220V L24 10 DMX	50 W
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	50 W
92580999	BVP353 24LED 27K 220V L24 15	50 W
92581699	BVP353 24LED 30K 220V L24 15	50 W
92582399	BVP353 24LED 40K 220V L24 15	50 W
92583099	BVP353 24LED 27K 220V L24 15 DMX	50 W
92584799	BVP353 24LED 30K 220V L24 15 DMX	50 W
92585499	BVP353 24LED 40K 220V L24 15 DMX	50 W
92586199	BVP353 24LED RGB 220V L24 15 DMX	50 W
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	50 W
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
92589299	BVP353 24LED 27K 220V L24 30	50 W
92590899	BVP353 24LED 30K 220V L24 30	50 W
92592299	BVP353 24LED 27K 220V L24 30 DMX	50 W
92593999	BVP353 24LED 30K 220V L24 30 DMX	50 W
92594699	BVP353 24LED 40K 220V L24 30 DMX	50 W
92595399	BVP353 24LED RGB 220V L24 30 DMX	50 W
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	50 W
92598499	BVP353 24LED 27K 220V L24 45	50 W
92599199	BVP353 24LED 30K 220V L24 45	50 W
92600499	BVP353 24LED 40K 220V L24 45	50 W
92601199	BVP353 24LED 27K 220V L24 45 DMX	50 W
92602899	BVP353 24LED 30K 220V L24 45 DMX	50 W
92603599	BVP353 24LED 40K 220V L24 45 DMX	50 W
92604299	BVP353 24LED RGB 220V L24 45 DMX	50 W
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	50 W
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	50 W
92715599	BVP353 60LED 27K 220V L50 10	120 W
92717999	BVP353 60LED 40K 220V L50 10	120 W
92718699	BVP353 60LED 27K 220V L50 10 DMX	120 W
92719399	BVP353 60LED 30K 220V L50 10 DMX	120 W
92720999	BVP353 60LED 40K 220V L50 10 DMX	120 W
92721699	BVP353 60LED RGB 220V L50 10 DMX	120 W
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	120 W
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	120 W
92724799	BVP353 60LED 27K 220V L50 15	120 W
92725499	BVP353 60LED 30K 220V L50 15	120 W
92726199	BVP353 60LED 40K 220V L50 15	120 W
92727899	BVP353 60LED 27K 220V L50 15 DMX	120 W
92728599	BVP353 60LED 30K 220V L50 15 DMX	120 W
92729299	BVP353 60LED 40K 220V L50 15 DMX	120 W
92730899	BVP353 60LED RGB 220V L50 15 DMX	120 W
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	120 W
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	120 W
92733999	BVP353 60LED 27K 220V L50 30	120 W
92734699	BVP353 60LED 30K 220V L50 30	120 W

Order Code	Full Product Name	Power Consumption
92735399	BVP353 60LED 40K 220V L50 30	120 W
92736099	BVP353 60LED 27K 220V L50 30 DMX	120 W
92737799	BVP353 60LED 30K 220V L50 30 DMX	120 W
92738499	BVP353 60LED 40K 220V L50 30 DMX	120 W
92739199	BVP353 60LED RGB 220V L50 30 DMX	120 W
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	120 W
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	120 W
92742199	BVP353 60LED 27K 220V L50 45	120 W
92743899	BVP353 60LED 30K 220V L50 45	120 W
92744599	BVP353 60LED 40K 220V L50 45	120 W
92745299	BVP353 60LED 27K 220V L50 45 DMX	120 W
92746999	BVP353 60LED 30K 220V L50 45 DMX	120 W
92747699	BVP353 60LED 40K 220V L50 45 DMX	120 W
92748399	BVP353 60LED RGB 220V L50 45 DMX	120 W
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	120 W
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	120 W
92499499	BVP353 16LED 27K 220V L18 10	30 W
92500799	BVP353 16LED 30K 220V L18 10	30 W
92501499	BVP353 16LED 40K 220V L18 10	30 W
92502199	BVP353 16LED 27K 220V L18 10 DMX	30 W
92503899	BVP353 16LED 30K 220V L18 10 DMX	30 W
92504599	BVP353 16LED 40K 220V L18 10 DMX	30 W
92505299	BVP353 15LED RGB 220V L18 10 DMX	30 W
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	30 W
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	30 W
92508399	BVP353 16LED 27K 220V L18 15	30 W
92509099	BVP353 16LED 30K 220V L18 15	30 W
92510699	BVP353 16LED 40K 220V L18 15	30 W
92511399	BVP353 16LED 27K 220V L18 15 DMX	30 W
92512099	BVP353 16LED 30K 220V L18 15 DMX	30 W
92513799	BVP353 16LED 40K 220V L18 15 DMX	30 W
92514499	BVP353 15LED RGB 220V L18 15 DMX	30 W
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	30 W
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	30 W
92517599	BVP353 16LED 27K 220V L18 30	30 W
92518299	BVP353 16LED 30K 220V L18 30	30 W
92519999	BVP353 16LED 40K 220V L18 30	30 W
92520599	BVP353 16LED 27K 220V L18 30 DMX	30 W
92521299	BVP353 16LED 30K 220V L18 30 DMX	30 W
92522999	BVP353 16LED 40K 220V L18 30 DMX	30 W
92523699	BVP353 15LED RGB 220V L18 30 DMX	30 W
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	30 W
92526799	BVP353 16LED 27K 220V L18 45	30 W
92527499	BVP353 16LED 30K 220V L18 45	30 W
92528199	BVP353 16LED 40K 220V L18 45	30 W
92529899	BVP353 16LED 27K 220V L18 45 DMX	30 W
92530499	BVP353 16LED 30K 220V L18 45 DMX	30 W
92531199	BVP353 16LED 40K 220V L18 45 DMX	30 W
92532899	BVP353 15LED RGB 220V L18 45 DMX	30 W
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	30 W
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	30 W

Order Code	Full Product Name	Power Consumption
92895400	BVP355 216LED 27K 220V L57 10	450 W
92896100	BVP355 216LED 30K 220V L57 10	450 W
92897800	BVP355 216LED 40K 220V L57 10	450 W
92898500	BVP355 216LED 27K 220V L57 10 DMX	450 W
92899200	BVP355 216LED 30K 220V L57 10 DMX	450 W
92900500	BVP355 216LED 40K 220V L57 10 DMX	450 W
92901200	BVP355 216LED RGB 220V L57 10 DMX	450 W
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	450 W
92904300	BVP355 216LED 27K 220V L57 15	450 W
92905000	BVP355 216LED 30K 220V L57 15	450 W
92906700	BVP355 216LED 40K 220V L57 15	450 W
92907400	BVP355 216LED 27K 220V L57 15 DMX	450 W
92908100	BVP355 216LED 30K 220V L57 15 DMX	450 W
92909800	BVP355 216LED 40K 220V L57 15 DMX	450 W
92910400	BVP355 216LED RGB 220V L57 15 DMX	450 W
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	450 W
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
92913500	BVP355 216LED 27K 220V L57 30	450 W
92914200	BVP355 216LED 30K 220V L57 30	450 W
92915900	BVP355 216LED 40K 220V L57 30	450 W
92916600	BVP355 216LED 27K 220V L57 30 DMX	450 W
92917300	BVP355 216LED 30K 220V L57 30 DMX	450 W
92918000	BVP355 216LED 40K 220V L57 30 DMX	450 W
92919700	BVP355 216LED RGB 220V L57 30 DMX	450 W
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	450 W
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	450 W
92922700	BVP355 216LED 27K 220V L57 45	450 W
92923400	BVP355 216LED 30K 220V L57 45	450 W
92924100	BVP355 216LED 40K 220V L57 45	450 W
92925800	BVP355 216LED 27K 220V L57 45 DMX	450 W
92926500	BVP355 216LED 30K 220V L57 45 DMX	450 W
92927200	BVP355 216LED 40K 220V L57 45 DMX	450 W
92928900	BVP355 216LED RGB 220V L57 45 DMX	450 W
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	450 W
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
92931900	BVP355 180LED 27K 220V L50 10	360 W
92932600	BVP355 180LED 30K 220V L50 10	360 W
92933300	BVP355 180LED 40K 220V L50 10	360 W
92934000	BVP355 180LED 27K 220V L50 10 DMX	360 W
92935700	BVP355 180LED 30K 220V L50 10 DMX	360 W
92936400	BVP355 180LED 40K 220V L50 10 DMX	360 W
92937100	BVP355 180LED RGB 220V L50 10 DMX	360 W
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	360 W
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	360 W
92940100	BVP355 180LED 27K 220V L50 15	360 W
92941800	BVP355 180LED 30K 220V L50 15	360 W
92942500	BVP355 180LED 40K 220V L50 15	360 W
92943200	BVP355 180LED 27K 220V L50 15 DMX	360 W
92944900	BVP355 180LED 30K 220V L50 15 DMX	360 W
92945600	BVP355 180LED 40K 220V L50 15 DMX	360 W
92946300	BVP355 180LED RGB 220V L50 15 DMX	360 W

Order Code	Full Product Name	Power Consumption
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	360 W
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	360 W
92949400	BVP355 180LED 27K 220V L50 30	360 W
92950000	BVP355 180LED 30K 220V L50 30	360 W
92951700	BVP355 180LED 40K 220V L50 30	360 W
92952400	BVP355 180LED 27K 220V L50 30 DMX	360 W
92953100	BVP355 180LED 30K 220V L50 30 DMX	360 W
92954800	BVP355 180LED 40K 220V L50 30 DMX	360 W
92955500	BVP355 180LED RGB 220V L50 30 DMX	360 W
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	360 W
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
92958600	BVP355 180LED 27K 220V L50 45	360 W
92959300	BVP355 180LED 30K 220V L50 45	360 W
92960900	BVP355 180LED 40K 220V L50 45	360 W
92961600	BVP355 180LED 27K 220V L50 45 DMX	360 W
92962300	BVP355 180LED 30K 220V L50 45 DMX	360 W
92963000	BVP355 180LED 40K 220V L50 45 DMX	360 W
92964700	BVP355 180LED RGB 220V L50 45 DMX	360 W
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	360 W
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	360 W
92679099	BVP353 48LED 27K 220V L40 10	100 W
92680699	BVP353 48LED 30K 220V L40 10	100 W
92681399	BVP353 48LED 40K 220V L40 10	100 W
92682099	BVP353 48LED 27K 220V L40 10 DMX	100 W
92683799	BVP353 48LED 30K 220V L40 10 DMX	100 W
92684499	BVP353 48LED 40K 220V L40 10 DMX	100 W
92685199	BVP353 48LED RGB 220V L40 10 DMX	100 W
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
92688299	BVP353 48LED 27K 220V L40 15	100 W
92689999	BVP353 48LED 30K 220V L40 15	100 W
92690599	BVP353 48LED 40K 220V L40 15	100 W
92691299	BVP353 48LED 27K 220V L40 15 DMX	100 W
92692999	BVP353 48LED 30K 220V L40 15 DMX	100 W
92693699	BVP353 48LED 40K 220V L40 15 DMX	100 W
92694399	BVP353 48LED RGB 220V L40 15 DMX	100 W
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	100 W
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	100 W
92697499	BVP353 48LED 27K 220V L40 30	100 W
92698199	BVP353 48LED 30K 220V L40 30	100 W
92699899	BVP353 48LED 40K 220V L40 30	100 W
92700199	BVP353 48LED 27K 220V L40 30 DMX	100 W
92701899	BVP353 48LED 30K 220V L40 30 DMX	100 W
92702599	BVP353 48LED 40K 220V L40 30 DMX	100 W
92703299	BVP353 48LED RGB 220V L40 30 DMX	100 W
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	100 W
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
92706399	BVP353 48LED 27K 220V L40 45	100 W
92707099	BVP353 48LED 30K 220V L40 45	100 W
92708799	BVP353 48LED 40K 220V L40 45	100 W
92709499	BVP353 48LED 27K 220V L40 45 DMX	100 W
92710099	BVP353 48LED 30K 220V L40 45 DMX	100 W

Order Code	Full Product Name	Power Consumption
92711799	BVP353 48LED 40K 220V L40 45 DMX	100 W
92712499	BVP353 48LED RGB 220V L40 45 DMX	100 W

Order Code	Full Product Name	Power Consumption
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	100 W
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
92607399	BVP353 30LED 27K 220V L30 10	No
92608099	BVP353 30LED 30K 220V L30 10	No
92609799	BVP353 30LED 40K 220V L30 10	No
92610399	BVP353 30LED 27K 220V L30 10 DMX	Yes
92611099	BVP353 30LED 30K 220V L30 10 DMX	Yes
92612799	BVP353 30LED 40K 220V L30 10 DMX	Yes
92613499	BVP353 30LED RGB 220V L30 10 DMX	Yes
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	Yes
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
92616599	BVP353 30LED 27K 220V L30 15	No
92617299	BVP353 30LED 30K 220V L30 15	No
92618999	BVP353 30LED 40K 220V L30 15	No
92619699	BVP353 30LED 27K 220V L30 15 DMX	Yes
92620299	BVP353 30LED 30K 220V L30 15 DMX	Yes
92621999	BVP353 30LED 40K 220V L30 15 DMX	Yes
92622699	BVP353 30LED RGB 220V L30 15 DMX	Yes
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	Yes
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	Yes
92625799	BVP353 30LED 27K 220V L30 30	No
92626499	BVP353 30LED 30K 220V L30 30	No
92627199	BVP353 30LED 40K 220V L30 30	No
92628899	BVP353 30LED 27K 220V L30 30 DMX	Yes
92629599	BVP353 30LED 30K 220V L30 30 DMX	Yes
92630199	BVP353 30LED 40K 220V L30 30 DMX	Yes
92631899	BVP353 30LED RGB 220V L30 30 DMX	Yes
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	Yes
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	Yes
92634999	BVP353 30LED 27K 220V L30 45	No
92635699	BVP353 30LED 30K 220V L30 45	No
92636399	BVP353 30LED 40K 220V L30 45	No
92637099	BVP353 30LED 27K 220V L30 45 DMX	Yes
92638799	BVP353 30LED 30K 220V L30 45 DMX	Yes
92639499	BVP353 30LED 40K 220V L30 45 DMX	Yes
92640099	BVP353 30LED RGB 220V L30 45 DMX	Yes
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	Yes
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	Yes
92787200	BVP354 96LED 27K 220V L40 10	No
92788900	BVP354 96LED 30K 220V L40 10	No
92789600	BVP354 96LED 40K 220V L40 10	No
92790200	BVP354 96LED 27K 220V L40 10 DMX	Yes
92791900	BVP354 96LED 30K 220V L40 10 DMX	Yes
92792600	BVP354 96LED 40K 220V L40 10 DMX	Yes
92793300	BVP354 96LED RGB 220V L40 10 DMX	Yes
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	Yes
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
92796400	BVP354 96LED 27K 220V L40 15	No

Order Code	Full Product Name	Dimmable
92797100	BVP354 96LED 30K 220V L40 15	No
92798800	BVP354 96LED 40K 220V L40 15	No
92799500	BVP354 96LED 27K 220V L40 15 DMX	Yes
92800800	BVP354 96LED 30K 220V L40 15 DMX	Yes
92801500	BVP354 96LED 40K 220V L40 15 DMX	Yes
92802200	BVP354 96LED RGB 220V L40 15 DMX	Yes
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	Yes
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	Yes
92805300	BVP354 96LED 27K 220V L40 30	No
92806000	BVP354 96LED 30K 220V L40 30	No
92807700	BVP354 96LED 40K 220V L40 30	No
92808400	BVP354 96LED 27K 220V L40 30 DMX	Yes
92809100	BVP354 96LED 30K 220V L40 30 DMX	Yes
92810700	BVP354 96LED 40K 220V L40 30 DMX	Yes
92811400	BVP354 96LED RGB 220V L40 30 DMX	Yes
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	Yes
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	Yes
92814500	BVP354 96LED 27K 220V L40 45	No
92815200	BVP354 96LED 30K 220V L40 45	No
92816900	BVP354 96LED 40K 220V L40 45	No
92817600	BVP354 96LED 27K 220V L40 45 DMX	Yes
92818300	BVP354 96LED 30K 220V L40 45 DMX	Yes
92819000	BVP354 96LED 40K 220V L40 45 DMX	Yes
92820600	BVP354 96LED RGB 220V L40 45 DMX	Yes
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	Yes
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
92823700	BVP354 120LED 27K 220V L50 10	No
92824400	BVP354 120LED 30K 220V L50 10	No
92825100	BVP354 120LED 40K 220V L50 10	No
92826800	BVP354 120LED 27K 220V L50 10 DMX	Yes
92827500	BVP354 120LED 30K 220V L50 10 DMX	Yes
92828200	BVP354 120LED 40K 220V L50 10 DMX	Yes
92829900	BVP354 120LED RGB 220V L50 10 DMX	Yes
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	Yes
92832900	BVP354 120LED 27K 220V L50 15	No
92833600	BVP354 120LED 30K 220V L50 15	No
92834300	BVP354 120LED 40K 220V L50 15	No
92835000	BVP354 120LED 27K 220V L50 15 DMX	Yes
92836700	BVP354 120LED 30K 220V L50 15 DMX	Yes
92837400	BVP354 120LED 40K 220V L50 15 DMX	Yes
92838100	BVP354 120LED RGB 220V L50 15 DMX	Yes
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	Yes
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	Yes
92841100	BVP354 120LED 27K 220V L50 30	No
92842800	BVP354 120LED 30K 220V L50 30	No

Order Code	Full Product Name	Dimmable
92843500	BVP354 120LED 40K 220V L50 30	No
92844200	BVP354 120LED 27K 220V L50 30 DMX	Yes
92845900	BVP354 120LED 30K 220V L50 30 DMX	Yes
92846600	BVP354 120LED 40K 220V L50 30 DMX	Yes
92847300	BVP354 120LED RGB 220V L50 30 DMX	Yes
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	Yes
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
92850300	BVP354 120LED 27K 220V L50 45	No
92851000	BVP354 120LED 30K 220V L50 45	No
92852700	BVP354 120LED 40K 220V L50 45	No
92853400	BVP354 120LED 27K 220V L50 45 DMX	Yes
92854100	BVP354 120LED 30K 220V L50 45 DMX	Yes
92855800	BVP354 120LED 40K 220V L50 45 DMX	Yes
92856500	BVP354 120LED RGB 220V L50 45 DMX	Yes
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
92859600	BVP354 144LED 27K 220V L57 10	No
92860200	BVP354 144LED 30K 220V L57 10	No
92861900	BVP354 144LED 40K 220V L57 10	No
92862600	BVP354 144LED 27K 220V L57 10 DMX	Yes
92863300	BVP354 144LED 30K 220V L57 10 DMX	Yes
92864000	BVP354 144LED 40K 220V L57 10 DMX	Yes
92865700	BVP354 144LED RGB 220V L57 10 DMX	Yes
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
92868800	BVP354 144LED 27K 220V L57 15	No
92869500	BVP354 144LED 30K 220V L57 15	No
92870100	BVP354 144LED 40K 220V L57 15	No
92871800	BVP354 144LED 27K 220V L57 15 DMX	Yes
92872500	BVP354 144LED 30K 220V L57 15 DMX	Yes
92873200	BVP354 144LED 40K 220V L57 15 DMX	Yes
92874900	BVP354 144LED RGB 220V L57 15 DMX	Yes
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	Yes
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	Yes
92877000	BVP354 144LED 27K 220V L57 30	No
92878700	BVP354 144LED 30K 220V L57 30	No
92879400	BVP354 144LED 40K 220V L57 30	No
92880000	BVP354 144LED 27K 220V L57 30 DMX	Yes
92881700	BVP354 144LED 30K 220V L57 30 DMX	Yes
92882400	BVP354 144LED 40K 220V L57 30 DMX	Yes
92883100	BVP354 144LED RGB 220V L57 30 DMX	Yes
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	Yes
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	Yes
92886200	BVP354 144LED 27K 220V L57 45	No
92887900	BVP354 144LED 30K 220V L57 45	No
92888600	BVP354 144LED 40K 220V L57 45	No
92889300	BVP354 144LED 27K 220V L57 45 DMX	Yes
92890900	BVP354 144LED 30K 220V L57 45 DMX	Yes
92891600	BVP354 144LED 40K 220V L57 45 DMX	Yes
92892300	BVP354 144LED RGB 220V L57 45 DMX	Yes
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	Yes
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	Yes

Order Code	Full Product Name	Dimmable
92751399	BVP353 72LED 27K 220V L57 10	No
92752099	BVP353 72LED 30K 220V L57 10	No
92753799	BVP353 72LED 40K 220V L57 10	No
92754499	BVP353 72LED 27K 220V L57 10 DMX	Yes
92755199	BVP353 72LED 30K 220V L57 10 DMX	Yes
92756899	BVP353 72LED 40K 220V L57 10 DMX	Yes
92757599	BVP353 72LED RGB 220V L57 10 DMX	Yes
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
92760599	BVP353 72LED 27K 220V L57 15	No
92761299	BVP353 72LED 30K 220V L57 15	No
92762999	BVP353 72LED 40K 220V L57 15	No
92763699	BVP353 72LED 27K 220V L57 15 DMX	Yes
92764399	BVP353 72LED 30K 220V L57 15 DMX	Yes
92765099	BVP353 72LED 40K 220V L57 15 DMX	Yes
92766799	BVP353 72LED RGB 220V L57 15 DMX	Yes
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	Yes
92769899	BVP353 72LED 27K 220V L57 30	No
92770499	BVP353 72LED 30K 220V L57 30	No
92771199	BVP353 72LED 40K 220V L57 30	No
92772899	BVP353 72LED 27K 220V L57 30 DMX	Yes
92773599	BVP353 72LED 30K 220V L57 30 DMX	Yes
92774299	BVP353 72LED 40K 220V L57 30 DMX	Yes
92775999	BVP353 72LED RGB 220V L57 30 DMX	Yes
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
92778099	BVP353 72LED 27K 220V L57 45	No
92779799	BVP353 72LED 30K 220V L57 45	No
92780399	BVP353 72LED 40K 220V L57 45	No
92781099	BVP353 72LED 27K 220V L57 45 DMX	Yes
92782799	BVP353 72LED 30K 220V L57 45 DMX	Yes
92783499	BVP353 72LED 40K 220V L57 45 DMX	Yes
92784199	BVP353 72LED RGB 220V L57 45 DMX	Yes
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
92535999	BVP353 18LED 27K 220V L21 10	No
92536699	BVP353 18LED 30K 220V L21 10	No
92537399	BVP353 18LED 40K 220V L21 10	No
92538099	BVP353 18LED 27K 220V L21 10 DMX	Yes
92539799	BVP353 18LED 30K 220V L21 10 DMX	Yes
92540399	BVP353 18LED 40K 220V L21 10 DMX	Yes
92541099	BVP353 18LED RGB 220V L21 10 DMX	Yes
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	Yes
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
92544199	BVP353 18LED 27K 220V L21 15	No
92545899	BVP353 18LED 30K 220V L21 15	No
92546599	BVP353 18LED 40K 220V L21 15	No
92547299	BVP353 18LED 27K 220V L21 15 DMX	Yes
92548999	BVP353 18LED 30K 220V L21 15 DMX	Yes
92549699	BVP353 18LED 40K 220V L21 15 DMX	Yes
92550299	BVP353 18LED RGB 220V L21 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	Yes
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
92553399	BVP353 18LED 27K 220V L21 30	No
92554099	BVP353 18LED 30K 220V L21 30	No
92555799	BVP353 18LED 40K 220V L21 30	No
92556499	BVP353 18LED 27K 220V L21 30 DMX	Yes
92557199	BVP353 18LED 30K 220V L21 30 DMX	Yes
92558899	BVP353 18LED 40K 220V L21 30 DMX	Yes
92559599	BVP353 18LED RGB 220V L21 30 DMX	Yes
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	Yes
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
92562599	BVP353 18LED 27K 220V L21 45	No
92563299	BVP353 18LED 30K 220V L21 45	No
92564999	BVP353 18LED 40K 220V L21 45	No
92565699	BVP353 18LED 27K 220V L21 45 DMX	Yes
92566399	BVP353 18LED 30K 220V L21 45 DMX	Yes
92567099	BVP353 18LED 40K 220V L21 45 DMX	Yes
92568799	BVP353 18LED RGB 220V L21 45 DMX	Yes
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	Yes
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	Yes
92463599	BVP353 12LED 27K 220V L15 10	No
92464299	BVP353 12LED 30K 220V L15 10	No
92465999	BVP353 12LED 40K 220V L15 10	No
92466699	BVP353 12LED 27K 220V L15 10 DMX	Yes
92467399	BVP353 12LED 30K 220V L15 10 DMX	Yes
92468099	BVP353 12LED 40K 220V L15 10 DMX	Yes
92469799	BVP353 12LED RGB 220V L15 10 DMX	Yes
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	Yes
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	Yes
92473499	BVP353 12LED 30K 220V L15 15	No
92481999	BVP353 12LED 27K 220V L15 30	No
92482699	BVP353 12LED 30K 220V L15 30	No
92483399	BVP353 12LED 40K 220V L15 30	No
92484099	BVP353 12LED 27K 220V L15 30 DMX	Yes
92485799	BVP353 12LED 30K 220V L15 30 DMX	Yes
92486499	BVP353 12LED 40K 220V L15 30 DMX	Yes
92487199	BVP353 12LED RGB 220V L15 30 DMX	Yes
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	Yes
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	Yes
92490199	BVP353 12LED 27K 220V L15 45	No
92491899	BVP353 12LED 30K 220V L15 45	No
92492599	BVP353 12LED 40K 220V L15 45	No
92493299	BVP353 12LED 27K 220V L15 45 DMX	Yes
92494999	BVP353 12LED 30K 220V L15 45 DMX	Yes
92495699	BVP353 12LED 40K 220V L15 45 DMX	Yes
92496399	BVP353 12LED RGB 220V L15 45 DMX	Yes
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	Yes
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	Yes
92643199	BVP353 36LED 27K 220V L35 10	No
92644899	BVP353 36LED 30K 220V L35 10	No
92645599	BVP353 36LED 40K 220V L35 10	No
92646299	BVP353 36LED 27K 220V L35 10 DMX	Yes

Order Code	Full Product Name	Dimmable
92647999	BVP353 36LED 30K 220V L35 10 DMX	Yes
92648699	BVP353 36LED 40K 220V L35 10 DMX	Yes
92649399	BVP353 36LED RGB 220V L35 10 DMX	Yes
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	Yes
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	Yes
92652399	BVP353 36LED 27K 220V L35 15	No
92653099	BVP353 36LED 30K 220V L35 15	No
92654799	BVP353 36LED 40K 220V L35 15	No
92655499	BVP353 36LED 27K 220V L35 15 DMX	Yes
92656199	BVP353 36LED 30K 220V L35 15 DMX	Yes
92657899	BVP353 36LED 40K 220V L35 15 DMX	Yes
92658599	BVP353 36LED RGB 220V L35 15 DMX	Yes
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	Yes
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	Yes
92661599	BVP353 36LED 27K 220V L35 30	No
92662299	BVP353 36LED 30K 220V L35 30	No
92663999	BVP353 36LED 40K 220V L35 30	No
92664699	BVP353 36LED 27K 220V L35 30 DMX	Yes
92665399	BVP353 36LED 30K 220V L35 30 DMX	Yes
92666099	BVP353 36LED 40K 220V L35 30 DMX	Yes
92667799	BVP353 36LED RGB 220V L35 30 DMX	Yes
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	Yes
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	Yes
92670799	BVP353 36LED 27K 220V L35 45	No
92671499	BVP353 36LED 30K 220V L35 45	No
92672199	BVP353 36LED 40K 220V L35 45	No
92673899	BVP353 36LED 27K 220V L35 45 DMX	Yes
92674599	BVP353 36LED 30K 220V L35 45 DMX	Yes
92675299	BVP353 36LED 40K 220V L35 45 DMX	Yes
92676999	BVP353 36LED RGB 220V L35 45 DMX	Yes
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	Yes
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
92571799	BVP353 24LED 27K 220V L24 10	No
92572499	BVP353 24LED 30K 220V L24 10	No
92573199	BVP353 24LED 40K 220V L24 10	No
92574899	BVP353 24LED 27K 220V L24 10 DMX	Yes
92575599	BVP353 24LED 30K 220V L24 10 DMX	Yes
92576299	BVP353 24LED 40K 220V L24 10 DMX	Yes
92577999	BVP353 24LED RGB 220V L24 10 DMX	Yes
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	Yes
92580999	BVP353 24LED 27K 220V L24 15	No
92581699	BVP353 24LED 30K 220V L24 15	No
92582399	BVP353 24LED 40K 220V L24 15	No
92583099	BVP353 24LED 27K 220V L24 15 DMX	Yes
92584799	BVP353 24LED 30K 220V L24 15 DMX	Yes
92585499	BVP353 24LED 40K 220V L24 15 DMX	Yes
92586199	BVP353 24LED RGB 220V L24 15 DMX	Yes
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	Yes
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
92589299	BVP353 24LED 27K 220V L24 30	No
92590899	BVP353 24LED 30K 220V L24 30	No

Order Code	Full Product Name	Dimmable
92592299	BVP353 24LED 27K 220V L24 30 DMX	Yes
92593999	BVP353 24LED 30K 220V L24 30 DMX	Yes
92594699	BVP353 24LED 40K 220V L24 30 DMX	Yes
92595399	BVP353 24LED RGB 220V L24 30 DMX	Yes
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	Yes
92598499	BVP353 24LED 27K 220V L24 45	No
92599199	BVP353 24LED 30K 220V L24 45	No
92600499	BVP353 24LED 40K 220V L24 45	No
92601199	BVP353 24LED 27K 220V L24 45 DMX	Yes
92602899	BVP353 24LED 30K 220V L24 45 DMX	Yes
92603599	BVP353 24LED 40K 220V L24 45 DMX	Yes
92604299	BVP353 24LED RGB 220V L24 45 DMX	Yes
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	Yes
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	Yes
92715599	BVP353 60LED 27K 220V L50 10	No
92717999	BVP353 60LED 40K 220V L50 10	No
92718699	BVP353 60LED 27K 220V L50 10 DMX	Yes
92719399	BVP353 60LED 30K 220V L50 10 DMX	Yes
92720999	BVP353 60LED 40K 220V L50 10 DMX	Yes
92721699	BVP353 60LED RGB 220V L50 10 DMX	Yes
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	Yes
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	Yes
92724799	BVP353 60LED 27K 220V L50 15	No
92725499	BVP353 60LED 30K 220V L50 15	No
92726199	BVP353 60LED 40K 220V L50 15	No
92727899	BVP353 60LED 27K 220V L50 15 DMX	Yes
92728599	BVP353 60LED 30K 220V L50 15 DMX	Yes
92729299	BVP353 60LED 40K 220V L50 15 DMX	Yes
92730899	BVP353 60LED RGB 220V L50 15 DMX	Yes
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	Yes
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	Yes
92733999	BVP353 60LED 27K 220V L50 30	No
92734699	BVP353 60LED 30K 220V L50 30	No
92735399	BVP353 60LED 40K 220V L50 30	No
92736099	BVP353 60LED 27K 220V L50 30 DMX	Yes
92737799	BVP353 60LED 30K 220V L50 30 DMX	Yes
92738499	BVP353 60LED 40K 220V L50 30 DMX	Yes
92739199	BVP353 60LED RGB 220V L50 30 DMX	Yes
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	Yes
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	Yes
92742199	BVP353 60LED 27K 220V L50 45	No
92743899	BVP353 60LED 30K 220V L50 45	No
92744599	BVP353 60LED 40K 220V L50 45	No
92745299	BVP353 60LED 27K 220V L50 45 DMX	Yes
92746999	BVP353 60LED 30K 220V L50 45 DMX	Yes
92747699	BVP353 60LED 40K 220V L50 45 DMX	Yes
92748399	BVP353 60LED RGB 220V L50 45 DMX	Yes
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	Yes
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	Yes
92499499	BVP353 16LED 27K 220V L18 10	No
92500799	BVP353 16LED 30K 220V L18 10	No

Order Code	Full Product Name	Dimmable
92501499	BVP353 16LED 40K 220V L18 10	No
92502199	BVP353 16LED 27K 220V L18 10 DMX	Yes
92503899	BVP353 16LED 30K 220V L18 10 DMX	Yes
92504599	BVP353 16LED 40K 220V L18 10 DMX	Yes
92505299	BVP353 15LED RGB 220V L18 10 DMX	Yes
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	Yes
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	Yes
92508399	BVP353 16LED 27K 220V L18 15	No
92509099	BVP353 16LED 30K 220V L18 15	No
92510699	BVP353 16LED 40K 220V L18 15	No
92511399	BVP353 16LED 27K 220V L18 15 DMX	Yes
92512099	BVP353 16LED 30K 220V L18 15 DMX	Yes
92513799	BVP353 16LED 40K 220V L18 15 DMX	Yes
92514499	BVP353 15LED RGB 220V L18 15 DMX	Yes
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	Yes
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	Yes
92517599	BVP353 16LED 27K 220V L18 30	No
92518299	BVP353 16LED 30K 220V L18 30	No
92519999	BVP353 16LED 40K 220V L18 30	No
92520599	BVP353 16LED 27K 220V L18 30 DMX	Yes
92521299	BVP353 16LED 30K 220V L18 30 DMX	Yes
92522999	BVP353 16LED 40K 220V L18 30 DMX	Yes
92523699	BVP353 15LED RGB 220V L18 30 DMX	Yes
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	Yes
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	Yes
92526799	BVP353 16LED 27K 220V L18 45	No
92527499	BVP353 16LED 30K 220V L18 45	No
92528199	BVP353 16LED 40K 220V L18 45	No
92529899	BVP353 16LED 27K 220V L18 45 DMX	Yes
92530499	BVP353 16LED 30K 220V L18 45 DMX	Yes
92531199	BVP353 16LED 40K 220V L18 45 DMX	Yes
92532899	BVP353 15LED RGB 220V L18 45 DMX	Yes
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	Yes
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
92895400	BVP355 216LED 27K 220V L57 10	No
92896100	BVP355 216LED 30K 220V L57 10	No
92897800	BVP355 216LED 40K 220V L57 10	No
92898500	BVP355 216LED 27K 220V L57 10 DMX	Yes
92899200	BVP355 216LED 30K 220V L57 10 DMX	Yes
92900500	BVP355 216LED 40K 220V L57 10 DMX	Yes
92901200	BVP355 216LED RGB 220V L57 10 DMX	Yes
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	Yes
92904300	BVP355 216LED 27K 220V L57 15	No
92905000	BVP355 216LED 30K 220V L57 15	No
92906700	BVP355 216LED 40K 220V L57 15	No
92907400	BVP355 216LED 27K 220V L57 15 DMX	Yes
92908100	BVP355 216LED 30K 220V L57 15 DMX	Yes
92909800	BVP355 216LED 40K 220V L57 15 DMX	Yes
92910400	BVP355 216LED RGB 220V L57 15 DMX	Yes
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	Yes
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92913500	BVP355 216LED 27K 220V L57 30	No
92914200	BVP355 216LED 30K 220V L57 30	No
92915900	BVP355 216LED 40K 220V L57 30	No
92916600	BVP355 216LED 27K 220V L57 30 DMX	Yes
92917300	BVP355 216LED 30K 220V L57 30 DMX	Yes
92918000	BVP355 216LED 40K 220V L57 30 DMX	Yes
92919700	BVP355 216LED RGB 220V L57 30 DMX	Yes
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	Yes
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	Yes
92922700	BVP355 216LED 27K 220V L57 45	No
92923400	BVP355 216LED 30K 220V L57 45	No
92924100	BVP355 216LED 40K 220V L57 45	No
92925800	BVP355 216LED 27K 220V L57 45 DMX	Yes
92926500	BVP355 216LED 30K 220V L57 45 DMX	Yes
92927200	BVP355 216LED 40K 220V L57 45 DMX	Yes
92928900	BVP355 216LED RGB 220V L57 45 DMX	Yes
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	Yes
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
92931900	BVP355 180LED 27K 220V L50 10	No
92932600	BVP355 180LED 30K 220V L50 10	No
92933300	BVP355 180LED 40K 220V L50 10	No
92934000	BVP355 180LED 27K 220V L50 10 DMX	Yes
92935700	BVP355 180LED 30K 220V L50 10 DMX	Yes
92936400	BVP355 180LED 40K 220V L50 10 DMX	Yes
92937100	BVP355 180LED RGB 220V L50 10 DMX	Yes
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	Yes
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	Yes
92940100	BVP355 180LED 27K 220V L50 15	No
92941800	BVP355 180LED 30K 220V L50 15	No
92942500	BVP355 180LED 40K 220V L50 15	No
92943200	BVP355 180LED 27K 220V L50 15 DMX	Yes
92944900	BVP355 180LED 30K 220V L50 15 DMX	Yes
92945600	BVP355 180LED 40K 220V L50 15 DMX	Yes
92946300	BVP355 180LED RGB 220V L50 15 DMX	Yes
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	Yes
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	Yes
92949400	BVP355 180LED 27K 220V L50 30	No
92950000	BVP355 180LED 30K 220V L50 30	No
92951700	BVP355 180LED 40K 220V L50 30	No
92952400	BVP355 180LED 27K 220V L50 30 DMX	Yes
92953100	BVP355 180LED 30K 220V L50 30 DMX	Yes
92954800	BVP355 180LED 40K 220V L50 30 DMX	Yes
92955500	BVP355 180LED RGB 220V L50 30 DMX	Yes
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	Yes
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	Yes

Order Code	Full Product Name	Dimmable
92958600	BVP355 180LED 27K 220V L50 45	No
92959300	BVP355 180LED 30K 220V L50 45	No
92960900	BVP355 180LED 40K 220V L50 45	No
92961600	BVP355 180LED 27K 220V L50 45 DMX	Yes
92962300	BVP355 180LED 30K 220V L50 45 DMX	Yes
92963000	BVP355 180LED 40K 220V L50 45 DMX	Yes
92964700	BVP355 180LED RGB 220V L50 45 DMX	Yes
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	Yes
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	Yes
92679099	BVP353 48LED 27K 220V L40 10	No
92680699	BVP353 48LED 30K 220V L40 10	No
92681399	BVP353 48LED 40K 220V L40 10	No
92682099	BVP353 48LED 27K 220V L40 10 DMX	Yes
92683799	BVP353 48LED 30K 220V L40 10 DMX	Yes
92684499	BVP353 48LED 40K 220V L40 10 DMX	Yes
92685199	BVP353 48LED RGB 220V L40 10 DMX	Yes
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	Yes
92688299	BVP353 48LED 27K 220V L40 15	No
92689999	BVP353 48LED 30K 220V L40 15	No
92690599	BVP353 48LED 40K 220V L40 15	No
92691299	BVP353 48LED 27K 220V L40 15 DMX	Yes
92692999	BVP353 48LED 30K 220V L40 15 DMX	Yes
92693699	BVP353 48LED 40K 220V L40 15 DMX	Yes
92694399	BVP353 48LED RGB 220V L40 15 DMX	Yes
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	Yes
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	Yes
92697499	BVP353 48LED 27K 220V L40 30	No
92698199	BVP353 48LED 30K 220V L40 30	No
92699899	BVP353 48LED 40K 220V L40 30	No
92700199	BVP353 48LED 27K 220V L40 30 DMX	Yes
92701899	BVP353 48LED 30K 220V L40 30 DMX	Yes
92702599	BVP353 48LED 40K 220V L40 30 DMX	Yes
92703299	BVP353 48LED RGB 220V L40 30 DMX	Yes
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	Yes
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
92706399	BVP353 48LED 27K 220V L40 45	No
92707099	BVP353 48LED 30K 220V L40 45	No
92708799	BVP353 48LED 40K 220V L40 45	No
92709499	BVP353 48LED 27K 220V L40 45 DMX	Yes
92710099	BVP353 48LED 30K 220V L40 45 DMX	Yes
92711799	BVP353 48LED 40K 220V L40 45 DMX	Yes
92712499	BVP353 48LED RGB 220V L40 45 DMX	Yes
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	Yes
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	Yes

