



UniFlood M gen2: A high power floodlight with true modularity

UniFlood M G2

The Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor floodlighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colours, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

Features

- Standard: RGBW, RGB, 2,700 K, 3,000 K and 4,000 K
- Optional 5,000 K, monochromatic colours and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

UniFlood M G2







Application

- Bridges, Monuments, Facades
- Parks and squares
- Landscape









Warnings and Safety

- For outdoor use only.

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Colour rendering index (CRI)	>80
Mechanical and Housing	
Optical cover type	Clear glass
Housing Colour	Dark grey
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Light source colour	Correlated Colour	
			Temperature (Nom)	Luminous Flux
92608099	BVP353 30LED 30K 220V L30 10	830 warm white	3000 K	4,710 lm
92609799	BVP353 30LED 40K 220V L30 10	840 neutral white	4000 K	5,255 lm
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	RGBW	-	2,855 lm
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	RGBW	-	2,985 lm
92617299	BVP353 30LED 30K 220V L30 15	830 warm white	3000 K	4,945 lm
92618999	BVP353 30LED 40K 220V L30 15	840 neutral white	4000 K	5,520 lm
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	RGBW	-	3,000 lm
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	RGBW	-	3,130 lm
92626499	BVP353 30LED 30K 220V L30 30	830 warm white	3000 K	5,125 lm
92627199	BVP353 30LED 40K 220V L30 30	840 neutral white	4000 K	5,715 lm
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	RGBW	-	3,105 lm
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	RGBW	-	3,245 lm
92635699	BVP353 30LED 30K 220V L30 45	830 warm white	3000 K	4,945 lm
92636399	BVP353 30LED 40K 220V L30 45	840 neutral white	4000 K	5,520 lm
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	RGBW	-	3,000 lm
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	RGBW	-	3,130 lm
92788900	BVP354 96LED 30K 220V L40 10	830 warm white	3000 K	16,555 lm
92789600	BVP354 96LED 40K 220V L40 10	840 neutral white	4000 K	18,470 lm
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	RGBW	-	10,505 lm
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	RGBW	-	10,975 lm
92797100	BVP354 96LED 30K 220V L40 15	830 warm white	3000 K	17,385 lm
92798800	BVP354 96LED 40K 220V L40 15	840 neutral white	4000 K	19,395 lm
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	RGBW	-	11,030 lm
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	RGBW	-	11,520 lm
92806000	BVP354 96LED 30K 220V L40 30	830 warm white	3000 K	18,005 lm
92807700	BVP354 96LED 40K 220V L40 30	840 neutral white	4000 K	20,085 lm
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	RGBW	-	11,425 lm
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	RGBW	-	11,935 lm
92815200	BVP354 96LED 30K 220V L40 45	830 warm white	3000 K	17,385 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92816900	BVP354 96LED 40K 220V L40 45	840 neutral white	4000 K	19,395 lm
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	RGBW	-	11,030 lm
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	RGBW	-	11,520 lm
92824400	BVP354 120LED 30K 220V L50 10	830 warm white	3000 K	18,850 lm
92825100	BVP354 120LED 40K 220V L50 10	840 neutral white	4000 K	21,035 lm
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	RGBW	-	10,720 lm
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	RGBW	-	11,190 lm
92833600	BVP354 120LED 30K 220V L50 15	830 warm white	3000 K	19,795 lm
92834300	BVP354 120LED 40K 220V L50 15	840 neutral white	4000 K	22,085 lm
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	RGBW	-	11,255 lm
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	RGBW	-	11,750 lm
92842800	BVP354 120LED 30K 220V L50 30	830 warm white	3000 K	20,500 lm
92843500	BVP354 120LED 40K 220V L50 30	840 neutral white	4000 K	22,875 lm
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	RGBW	-	11,655 lm
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	RGBW	-	12,170 lm
92851000	BVP354 120LED 30K 220V L50 45	830 warm white	3000 K	19,795 lm
92852700	BVP354 120LED 40K 220V L50 45	840 neutral white	4000 K	22,085 lm
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	RGBW	-	11,255 lm
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	RGBW	-	11,750 lm
92860200	BVP354 144LED 30K 220V L57 10	830 warm white	3000 K	23,745 lm
92861900	BVP354 144LED 40K 220V L57 10	840 neutral white	4000 K	26,490 lm
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	RGBW	-	14,395 lm
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	RGBW	-	15,030 lm
92869500	BVP354 144LED 30K 220V L57 15	830 warm white	3000 K	24,930 lm
92870100	BVP354 144LED 40K 220V L57 15	840 neutral white	4000 K	27,815 lm
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	RGBW	-	15,115 lm
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	RGBW	-	15,785 lm
92878700	BVP354 144LED 30K 220V L57 30	830 warm white	3000 K	25,820 lm
92879400	BVP354 144LED 40K 220V L57 30	840 neutral white	4000 K	28,810 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	RGBW	-	15,655 lm
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	RGBW	-	16,345 lm
92888600	BVP354 144LED 40K 220V L57 45	840 neutral white	4000 K	27,815 lm
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	RGBW	-	15,115 lm
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	RGBW	-	15,785 lm
92752099	BVP353 72LED 30K 220V L57 10	830 warm white	3000 K	11,870 lm
92753799	BVP353 72LED 40K 220V L57 10	840 neutral white	4000 K	13,245 lm
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	RGBW	-	7,195 lm
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	RGBW	-	7,515 lm
92761299	BVP353 72LED 30K 220V L57 15	830 warm white	3000 K	12,465 lm
92762999	BVP353 72LED 40K 220V L57 15	840 neutral white	4000 K	13,905 lm
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	RGBW	-	7,555 lm
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	RGBW	-	7,890 lm
92770499	BVP353 72LED 30K 220V L57 30	830 warm white	3000 K	12,910 lm
92771199	BVP353 72LED 40K 220V L57 30	840 neutral white	4000 K	14,405 lm
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	RGBW	-	7,825 lm
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	RGBW	-	8,170 lm
92779799	BVP353 72LED 30K 220V L57 45	830 warm white	3000 K	12,465 lm
92780399	BVP353 72LED 40K 220V L57 45	840 neutral white	4000 K	13,905 lm
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	RGBW	-	7,555 lm
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	RGBW	-	7,890 lm
92536699	BVP353 18LED 30K 220V L21 10	830 warm white	3000 K	2,965 lm
92537399	BVP353 18LED 40K 220V L21 10	840 neutral white	4000 K	3,310 lm
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	RGBW	-	1,860 lm
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	RGBW	-	1,945 lm
92545899	BVP353 18LED 30K 220V L21 15	830 warm white	3000 K	3,115 lm
92546599	BVP353 18LED 40K 220V L21 15	840 neutral white	4000 K	3,475 lm
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	RGBW	-	1,955 lm
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	RGBW	-	2,040 lm
92554099	BVP353 18LED 30K 220V L21 30	830 warm white	3000 K	3,225 lm
92555799	BVP353 18LED 40K 220V L21 30	840 neutral white	4000 K	3,600 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	RGBW	-	2,025 lm
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	RGBW	-	2,115 lm
92563299	BVP353 18LED 30K 220V L21 45	830 warm white	3000 K	3,115 lm
92564999	BVP353 18LED 40K 220V L21 45	840 neutral white	4000 K	3,475 lm
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	RGBW	-	1,955 lm
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	RGBW	-	2,040 lm
92464299	BVP353 12LED 30K 220V L15 10	830 warm white	3000 K	1,835 lm
92465999	BVP353 12LED 40K 220V L15 10	840 neutral white	4000 K	2,050 lm
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	RGBW	-	1,175 lm
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	RGBW	-	1,225 lm
92473499	BVP353 12LED 30K 220V L15 15	830 warm white	3000 K	1,925 lm
92474199	BVP353 12LED 40K 220V L15 15	840 neutral white	4000 K	2,150 lm
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	RGBW	-	1,230 lm
92480299	BVP353 12LED RGBNW 220V L15 15 DMX	RGBW	-	1,285 lm
92482699	BVP353 12LED 30K 220V L15 30	830 warm white	3000 K	1,995 lm
92483399	BVP353 12LED 40K 220V L15 30	840 neutral white	4000 K	2,225 lm
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	RGBW	-	1,275 lm
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	RGBW	-	1,330 lm
92491899	BVP353 12LED 30K 220V L15 45	830 warm white	3000 K	1,925 lm
92492599	BVP353 12LED 40K 220V L15 45	840 neutral white	4000 K	2,150 lm
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	RGBW	-	1,230 lm
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	RGBW	-	1,285 lm
92644899	BVP353 36LED 30K 220V L35 10	830 warm white	3000 K	6,205 lm
92645599	BVP353 36LED 40K 220V L35 10	840 neutral white	4000 K	6,925 lm
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	RGBW	-	3,640 lm
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	RGBW	-	3,805 lm
92653099	BVP353 36LED 30K 220V L35 15	830 warm white	3000 K	6,515 lm
92654799	BVP353 36LED 40K 220V L35 15	840 neutral white	4000 K	7,270 lm
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	RGBW	-	3,825 lm
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	RGBW	-	3,995 lm
92662299	BVP353 36LED 30K 220V L35 30	830 warm white	3000 K	6,750 lm
92663999	BVP353 36LED 40K 220V L35 30	840 neutral white	4000 K	7,530 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	RGBW	-	3,960 lm
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	RGBW	-	4,135 lm
92671499	BVP353 36LED 30K 220V L35 45	830 warm white	3000 K	6,515 lm
92672199	BVP353 36LED 40K 220V L35 45	840 neutral white	4000 K	7,270 lm
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	RGBW	-	3,825 lm
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	RGBW	-	3,995 lm
92572499	BVP353 24LED 30K 220V L24 10	830 warm white	3000 K	3,770 lm
92573199	BVP353 24LED 40K 220V L24 10	840 neutral white	4000 K	4,205 lm
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	RGBW	-	2,350 lm
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	RGBW	-	2,450 lm
92581699	BVP353 24LED 30K 220V L24 15	830 warm white	3000 K	3,955 lm
92582399	BVP353 24LED 40K 220V L24 15	840 neutral white	4000 K	4,415 lm
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	RGBW	-	2,465 lm
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	RGBW	-	2,575 lm
92590899	BVP353 24LED 30K 220V L24 30	830 warm white	3000 K	4,100 lm
92591599	BVP353 24LED 40K 220V L24 30	840 neutral white	4000 K	4,575 lm
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	RGBW	-	2,555 lm
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	RGBW	-	2,665 lm
92599199	BVP353 24LED 30K 220V L24 45	830 warm white	3000 K	3,955 lm
92600499	BVP353 24LED 40K 220V L24 45	840 neutral white	4000 K	4,415 lm
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	RGBW	-	2,465 lm
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	RGBW	-	2,575 lm
92716299	BVP353 60LED 30K 220V L50 10	830 warm white	3000 K	9,540 lm
92717999	BVP353 60LED 40K 220V L50 10	840 neutral white	4000 K	10,645 lm
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	RGBW	-	5,995 lm
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	RGBW	-	6,260 lm
92725499	BVP353 60LED 30K 220V L50 15	830 warm white	3000 K	10,020 lm
92726199	BVP353 60LED 40K 220V L50 15	840 neutral white	4000 K	11,180 lm
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	RGBW	-	6,295 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	RGBW	-	6,575 lm
92734699	BVP353 60LED 30K 220V L50 30	830 warm white	3000 K	10,380 lm
92735399	BVP353 60LED 40K 220V L50 30	840 neutral white	4000 K	11,580 lm
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	RGBW	-	6,520 lm
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	RGBW	-	6,810 lm
92743899	BVP353 60LED 30K 220V L50 45	830 warm white	3000 K	10,020 lm
92744599	BVP353 60LED 40K 220V L50 45	840 neutral white	4000 K	11,180 lm
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	RGBW	-	6,295 lm
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	RGBW	-	6,575 lm
92500799	BVP353 16LED 30K 220V L18 10	830 warm white	3000 K	2,875 lm
92501499	BVP353 16LED 40K 220V L18 10	840 neutral white	4000 K	3,205 lm
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	RGBW	-	1,425 lm
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	RGBW	-	1,490 lm
92509099	BVP353 16LED 30K 220V L18 15	830 warm white	3000 K	3,020 lm
92510699	BVP353 16LED 40K 220V L18 15	840 neutral white	4000 K	3,365 lm
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	RGBW	-	1,500 lm
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	RGBW	-	1,565 lm
92518299	BVP353 16LED 30K 220V L18 30	830 warm white	3000 K	3,125 lm
92519999	BVP353 16LED 40K 220V L18 30	840 neutral white	4000 K	3,490 lm
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	RGBW	-	1,550 lm
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	RGBW	-	1,620 lm
92527499	BVP353 16LED 30K 220V L18 45	830 warm white	3000 K	3,020 lm
92528199	BVP353 16LED 40K 220V L18 45	840 neutral white	4000 K	3,365 lm
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	RGBW	-	1,500 lm
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	RGBW	-	1,565 lm
92896100	BVP355 216LED 30K 220V L57 10	830 warm white	3000 K	35,615 lm
92897800	BVP355 216LED 40K 220V L57 10	840 neutral white	4000 K	39,740 lm
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	RGBW	-	21,590 lm
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	RGBW	-	22,550 lm
92905000	BVP355 216LED 30K 220V L57 15	830 warm white	3000 K	37,400 lm
92906700	BVP355 216LED 40K 220V L57 15	840 neutral white	4000 K	41,725 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	RGBW	-	22,670 lm
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	RGBW	-	23,675 lm
92914200	BVP355 216LED 30K 220V L57 30	830 warm white	3000 K	38,735 lm
92915900	BVP355 216LED 40K 220V L57 30	840 neutral white	4000 K	43,215 lm
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	RGBW	-	23,480 lm
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	RGBW	-	24,520 lm
92923400	BVP355 216LED 30K 220V L57 45	830 warm white	3000 K	37,400 lm
92924100	BVP355 216LED 40K 220V L57 45	840 neutral white	4000 K	41,725 lm
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	RGBW	-	22,670 lm
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	RGBW	-	23,675 lm
92932600	BVP355 180LED 30K 220V L50 10	830 warm white	3000 K	28,630 lm
92933300	BVP355 180LED 40K 220V L50 10	840 neutral white	4000 K	31,945 lm
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	RGBW	-	17,990 lm
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	RGBW	-	18,790 lm
92941800	BVP355 180LED 30K 220V L50 15	830 warm white	3000 K	30,065 lm
92942500	BVP355 180LED 40K 220V L50 15	840 neutral white	4000 K	33,540 lm
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	RGBW	-	18,890 lm
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	RGBW	-	19,730 lm
92950000	BVP355 180LED 30K 220V L50 30	830 warm white	3000 K	31,140 lm
92951700	BVP355 180LED 40K 220V L50 30	840 neutral white	4000 K	34,740 lm
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	RGBW	-	19,565 lm
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	RGBW	-	20,435 lm
92959300	BVP355 180LED 30K 220V L50 45	830 warm white	3000 K	30,065 lm
92960900	BVP355 180LED 40K 220V L50 45	840 neutral white	4000 K	33,540 lm
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	RGBW	-	18,890 lm
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	RGBW	-	19,730 lm
92680699	BVP353 48LED 30K 220V L40 10	830 warm white	3000 K	7,760 lm
92681399	BVP353 48LED 40K 220V L40 10	840 neutral white	4000 K	8,655 lm
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	RGBW	-	5,250 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Luminous Flux
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	RGBW	-	5,485 lm
92689999	BVP353 48LED 30K 220V L40 15	830 warm white	3000 K	8,145 lm
92690599	BVP353 48LED 40K 220V L40 15	840 neutral white	4000 K	9,090 lm
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	RGBW	-	5,515 lm
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	RGBW	-	5,760 lm
92698199	BVP353 48LED 30K 220V L40 30	830 warm white	3000 K	8,440 lm
92699899	BVP353 48LED 40K 220V L40 30	840 neutral white	4000 K	9,415 lm
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	RGBW	-	5,710 lm
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	RGBW	-	5,965 lm
92707099	BVP353 48LED 30K 220V L40 45	830 warm white	3000 K	8,145 lm
92708799	BVP353 48LED 40K 220V L40 45	840 neutral white	4000 K	9,090 lm
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	RGBW	-	5,515 lm
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	RGBW	-	5,760 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
92608099	BVP353 30LED 30K 220V L30 10	60 W	92806000	BVP354 96LED 30K 220V L40 30	200 W
92609799	BVP353 30LED 40K 220V L30 10	60 W	92807700	BVP354 96LED 40K 220V L40 30	200 W
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	60 W	92812100	BVP354 96LED RGBWW 220V L40 30 DMX	200 W
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	60 W	92813800	BVP354 96LED RGBNW 220V L40 30 DMX	200 W
92617299	BVP353 30LED 30K 220V L30 15	60 W	92815200	BVP354 96LED 30K 220V L40 45	200 W
92618999	BVP353 30LED 40K 220V L30 15	60 W	92816900	BVP354 96LED 40K 220V L40 45	200 W
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	60 W	92821300	BVP354 96LED RGBWW 220V L40 45 DMX	200 W
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	60 W	92822000	BVP354 96LED RGBNW 220V L40 45 DMX	200 W
92626499	BVP353 30LED 30K 220V L30 30	60 W	92824400	BVP354 120LED 30K 220V L50 10	240 W
92627199	BVP353 30LED 40K 220V L30 30	60 W	92825100	BVP354 120LED 40K 220V L50 10	240 W
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	60 W	92830500	BVP354 120LED RGBWW 220V L50 10 DMX	240 W
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	60 W	92831200	BVP354 120LED RGBNW 220V L50 10 DMX	240 W
92635699	BVP353 30LED 30K 220V L30 45	60 W	92833600	BVP354 120LED 30K 220V L50 15	240 W
92636399	BVP353 30LED 40K 220V L30 45	60 W	92834300	BVP354 120LED 40K 220V L50 15	240 W
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	60 W	92839800	BVP354 120LED RGBWW 220V L50 15 DMX	240 W
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	60 W	92840400	BVP354 120LED RGBNW 220V L50 15 DMX	240 W
92788900	BVP354 96LED 30K 220V L40 10	200 W	92842800	BVP354 120LED 30K 220V L50 30	240 W
92789600	BVP354 96LED 40K 220V L40 10	200 W	92843500	BVP354 120LED 40K 220V L50 30	240 W
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	200 W	92848000	BVP354 120LED RGBWW 220V L50 30 DMX	240 W
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	200 W	92849700	BVP354 120LED RGBNW 220V L50 30 DMX	240 W
92797100	BVP354 96LED 30K 220V L40 15	200 W	92851000	BVP354 120LED 30K 220V L50 45	240 W
92798800	BVP354 96LED 40K 220V L40 15	200 W	92852700	BVP354 120LED 40K 220V L50 45	240 W
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	200 W	92857200	BVP354 120LED RGBWW 220V L50 45 DMX	240 W
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	200 W	92858900	BVP354 120LED RGBNW 220V L50 45 DMX	240 W

Order Code	Full Product Name	Power Consumption
92860200	BVP354 144LED 30K 220V L57 10	300 W
92861900	BVP354 144LED 40K 220V L57 10	300 W
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	300 W
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	300 W
92869500	BVP354 144LED 30K 220V L57 15	300 W
92870100	BVP354 144LED 40K 220V L57 15	300 W
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	300 W
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	300 W
92878700	BVP354 144LED 30K 220V L57 30	300 W
92879400	BVP354 144LED 40K 220V L57 30	300 W
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	300 W
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	300 W
92888600	BVP354 144LED 40K 220V L57 45	300 W
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	300 W
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	300 W
92752099	BVP353 72LED 30K 220V L57 10	150 W
92753799	BVP353 72LED 40K 220V L57 10	150 W
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	150 W
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	150 W
92761299	BVP353 72LED 30K 220V L57 15	150 W
92762999	BVP353 72LED 40K 220V L57 15	150 W
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	150 W
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	150 W
92770499	BVP353 72LED 30K 220V L57 30	150 W
92771199	BVP353 72LED 40K 220V L57 30	150 W
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	150 W
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	150 W
92779799	BVP353 72LED 30K 220V L57 45	150 W
92780399	BVP353 72LED 40K 220V L57 45	150 W
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	150 W
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	150 W
92536699	BVP353 18LED 30K 220V L21 10	40 W
92537399	BVP353 18LED 40K 220V L21 10	40 W
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	40 W
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	40 W
92545899	BVP353 18LED 30K 220V L21 15	40 W
92546599	BVP353 18LED 40K 220V L21 15	40 W
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	40 W
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	40 W
92554099	BVP353 18LED 30K 220V L21 30	40 W
92555799	BVP353 18LED 40K 220V L21 30	40 W
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	40 W
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	40 W
92563299	BVP353 18LED 30K 220V L21 45	40 W
92564999	BVP353 18LED 40K 220V L21 45	40 W
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	40 W
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	40 W
92464299	BVP353 12LED 30K 220V L15 10	24 W
92465999	BVP353 12LED 40K 220V L15 10	24 W
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	24 W
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	24 W
92473499	BVP353 12LED 30K 220V L15 15	24 W

Order Code	Full Product Name	Power Consumption
92474199	BVP353 12LED 40K 220V L15 15	24 W
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	24 W
92480299	BVP353 12LED RGBNW 220V L15 15 DMX	24 W
92482699	BVP353 12LED 30K 220V L15 30	24 W
92483399	BVP353 12LED 40K 220V L15 30	24 W
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	24 W
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	24 W
92491899	BVP353 12LED 30K 220V L15 45	24 W
92492599	BVP353 12LED 40K 220V L15 45	24 W
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	24 W
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	24 W
92644899	BVP353 36LED 30K 220V L35 10	80 W
92645599	BVP353 36LED 40K 220V L35 10	80 W
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	80 W
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	80 W
92653099	BVP353 36LED 30K 220V L35 15	80 W
92654799	BVP353 36LED 40K 220V L35 15	80 W
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	80 W
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	80 W
92662299	BVP353 36LED 30K 220V L35 30	80 W
92663999	BVP353 36LED 40K 220V L35 30	80 W
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	80 W
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	80 W
92671499	BVP353 36LED 30K 220V L35 45	80 W
92672199	BVP353 36LED 40K 220V L35 45	80 W
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	80 W
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	80 W
92572499	BVP353 24LED 30K 220V L24 10	50 W
92573199	BVP353 24LED 40K 220V L24 10	50 W
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	50 W
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	50 W
92581699	BVP353 24LED 30K 220V L24 15	50 W
92582399	BVP353 24LED 40K 220V L24 15	50 W
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	50 W
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	50 W
92590899	BVP353 24LED 30K 220V L24 30	50 W
92591599	BVP353 24LED 40K 220V L24 30	50 W
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	50 W
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	50 W
92599199	BVP353 24LED 30K 220V L24 45	50 W
92600499	BVP353 24LED 40K 220V L24 45	50 W
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	50 W
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	50 W
92716299	BVP353 60LED 30K 220V L50 10	120 W
92717999	BVP353 60LED 40K 220V L50 10	120 W
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	120 W
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	120 W
92725499	BVP353 60LED 30K 220V L50 15	120 W
92726199	BVP353 60LED 40K 220V L50 15	120 W
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	120 W
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	120 W
92734699	BVP353 60LED 30K 220V L50 30	120 W

Order Code	Full Product Name	Power Consumption
92735399	BVP353 60LED 40K 220V L50 30	120 W
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	120 W
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	120 W
92743899	BVP353 60LED 30K 220V L50 45	120 W
92744599	BVP353 60LED 40K 220V L50 45	120 W
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	120 W
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	120 W
92500799	BVP353 16LED 30K 220V L18 10	30 W
92501499	BVP353 16LED 40K 220V L18 10	30 W
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	30 W
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	30 W
92509099	BVP353 16LED 30K 220V L18 15	30 W
92510699	BVP353 16LED 40K 220V L18 15	30 W
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	30 W
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	30 W
92518299	BVP353 16LED 30K 220V L18 30	30 W
92519999	BVP353 16LED 40K 220V L18 30	30 W
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	30 W
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	30 W
92527499	BVP353 16LED 30K 220V L18 45	30 W
92528199	BVP353 16LED 40K 220V L18 45	30 W
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	30 W
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	30 W
92896100	BVP355 216LED 30K 220V L57 10	450 W
92897800	BVP355 216LED 40K 220V L57 10	450 W
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	450 W
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	450 W
92905000	BVP355 216LED 30K 220V L57 15	450 W
92906700	BVP355 216LED 40K 220V L57 15	450 W
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	450 W
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	450 W
92914200	BVP355 216LED 30K 220V L57 30	450 W
92915900	BVP355 216LED 40K 220V L57 30	450 W
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	450 W
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	450 W
92923400	BVP355 216LED 30K 220V L57 45	450 W

Order Code	Full Product Name	Power Consumption
92924100	BVP355 216LED 40K 220V L57 45	450 W
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	450 W
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	450 W
92932600	BVP355 180LED 30K 220V L50 10	360 W
92933300	BVP355 180LED 40K 220V L50 10	360 W
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	360 W
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	360 W
92941800	BVP355 180LED 30K 220V L50 15	360 W
92942500	BVP355 180LED 40K 220V L50 15	360 W
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	360 W
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	360 W
92950000	BVP355 180LED 30K 220V L50 30	360 W
92951700	BVP355 180LED 40K 220V L50 30	360 W
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	360 W
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	360 W
92959300	BVP355 180LED 30K 220V L50 45	360 W
92960900	BVP355 180LED 40K 220V L50 45	360 W
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	360 W
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	360 W
92680699	BVP353 48LED 30K 220V L40 10	100 W
92681399	BVP353 48LED 40K 220V L40 10	100 W
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	100 W
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	100 W
92689999	BVP353 48LED 30K 220V L40 15	100 W
92690599	BVP353 48LED 40K 220V L40 15	100 W
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	100 W
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	100 W
92698199	BVP353 48LED 30K 220V L40 30	100 W
92699899	BVP353 48LED 40K 220V L40 30	100 W
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	100 W
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	100 W
92707099	BVP353 48LED 30K 220V L40 45	100 W
92708799	BVP353 48LED 40K 220V L40 45	100 W
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	100 W
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	100 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
92608099	BVP353 30LED 30K 220V L30 10	No
92609799	BVP353 30LED 40K 220V L30 10	No
92614199	BVP353 32LED RGBWW 220V L30 10 DMX	Yes
92615899	BVP353 32LED RGBNW 220V L30 10 DMX	Yes
92617299	BVP353 30LED 30K 220V L30 15	No
92618999	BVP353 30LED 40K 220V L30 15	No
92623399	BVP353 32LED RGBWW 220V L30 15 DMX	Yes
92624099	BVP353 32LED RGBNW 220V L30 15 DMX	Yes
92626499	BVP353 30LED 30K 220V L30 30	No
92627199	BVP353 30LED 40K 220V L30 30	No
92632599	BVP353 32LED RGBWW 220V L30 30 DMX	Yes
92633299	BVP353 32LED RGBNW 220V L30 30 DMX	Yes

Order Code	Full Product Name	Dimmable
92635699	BVP353 30LED 30K 220V L30 45	No
92636399	BVP353 30LED 40K 220V L30 45	No
92641799	BVP353 32LED RGBWW 220V L30 45 DMX	Yes
92642499	BVP353 32LED RGBNW 220V L30 45 DMX	Yes
92788900	BVP354 96LED 30K 220V L40 10	No
92789600	BVP354 96LED 40K 220V L40 10	No
92794000	BVP354 96LED RGBWW 220V L40 10 DMX	Yes
92795700	BVP354 96LED RGBNW 220V L40 10 DMX	Yes
92797100	BVP354 96LED 30K 220V L40 15	No
92798800	BVP354 96LED 40K 220V L40 15	No
92803900	BVP354 96LED RGBWW 220V L40 15 DMX	Yes
92804600	BVP354 96LED RGBNW 220V L40 15 DMX	Yes

Order Code	Full Product Name	Dimmable
92806000	BVP354 96LED 30K 220V L40 30	No
92807700	BVP354 96LED 40K 220V L40 30	No
92812100	BVP354 96LED RGBWW 220V L40 30 DMX	Yes
92813800	BVP354 96LED RGBNW 220V L40 30 DMX	Yes
92815200	BVP354 96LED 30K 220V L40 45	No
92816900	BVP354 96LED 40K 220V L40 45	No
92821300	BVP354 96LED RGBWW 220V L40 45 DMX	Yes
92822000	BVP354 96LED RGBNW 220V L40 45 DMX	Yes
92824400	BVP354 120LED 30K 220V L50 10	No
92825100	BVP354 120LED 40K 220V L50 10	No
92830500	BVP354 120LED RGBWW 220V L50 10 DMX	Yes
92831200	BVP354 120LED RGBNW 220V L50 10 DMX	Yes
92833600	BVP354 120LED 30K 220V L50 15	No
92834300	BVP354 120LED 40K 220V L50 15	No
92839800	BVP354 120LED RGBWW 220V L50 15 DMX	Yes
92840400	BVP354 120LED RGBNW 220V L50 15 DMX	Yes
92842800	BVP354 120LED 30K 220V L50 30	No
92843500	BVP354 120LED 40K 220V L50 30	No
92848000	BVP354 120LED RGBWW 220V L50 30 DMX	Yes
92849700	BVP354 120LED RGBNW 220V L50 30 DMX	Yes
92851000	BVP354 120LED 30K 220V L50 45	No
92852700	BVP354 120LED 40K 220V L50 45	No
92857200	BVP354 120LED RGBWW 220V L50 45 DMX	Yes
92858900	BVP354 120LED RGBNW 220V L50 45 DMX	Yes
92860200	BVP354 144LED 30K 220V L57 10	No
92861900	BVP354 144LED 40K 220V L57 10	No
92866400	BVP354 144LED RGBWW 220V L57 10 DMX	Yes
92867100	BVP354 144LED RGBNW 220V L57 10 DMX	Yes
92869500	BVP354 144LED 30K 220V L57 15	No
92870100	BVP354 144LED 40K 220V L57 15	No
92875600	BVP354 144LED RGBWW 220V L57 15 DMX	Yes
92876300	BVP354 144LED RGBNW 220V L57 15 DMX	Yes
92878700	BVP354 144LED 30K 220V L57 30	No
92879400	BVP354 144LED 40K 220V L57 30	No
92884800	BVP354 144LED RGBWW 220V L57 30 DMX	Yes
92885500	BVP354 144LED RGBNW 220V L57 30 DMX	Yes
92888600	BVP354 144LED 40K 220V L57 45	No
92893000	BVP354 144LED RGBWW 220V L57 45 DMX	Yes
92894700	BVP354 144LED RGBNW 220V L57 45 DMX	Yes
92752099	BVP353 72LED 30K 220V L57 10	No
92753799	BVP353 72LED 40K 220V L57 10	No
92758299	BVP353 72LED RGBWW 220V L57 10 DMX	Yes
92759999	BVP353 72LED RGBNW 220V L57 10 DMX	Yes
92761299	BVP353 72LED 30K 220V L57 15	No
92762999	BVP353 72LED 40K 220V L57 15	No
92767499	BVP353 72LED RGBWW 220V L57 15 DMX	Yes
92768199	BVP353 72LED RGBNW 220V L57 15 DMX	Yes
92770499	BVP353 72LED 30K 220V L57 30	No
92771199	BVP353 72LED 40K 220V L57 30	No
92776699	BVP353 72LED RGBWW 220V L57 30 DMX	Yes
92777399	BVP353 72LED RGBNW 220V L57 30 DMX	Yes
92779799	BVP353 72LED 30K 220V L57 45	No

Order Code	Full Product Name	Dimmable
92780399	BVP353 72LED 40K 220V L57 45	No
92785899	BVP353 72LED RGBWW 220V L57 45 DMX	Yes
92786599	BVP353 72LED RGBNW 220V L57 45 DMX	Yes
92536699	BVP353 18LED 30K 220V L21 10	No
92537399	BVP353 18LED 40K 220V L21 10	No
92542799	BVP353 20LED RGBWW 220V L21 10 DMX	Yes
92543499	BVP353 20LED RGBNW 220V L21 10 DMX	Yes
92545899	BVP353 18LED 30K 220V L21 15	No
92546599	BVP353 18LED 40K 220V L21 15	No
92551999	BVP353 20LED RGBWW 220V L21 15 DMX	Yes
92552699	BVP353 20LED RGBNW 220V L21 15 DMX	Yes
92554099	BVP353 18LED 30K 220V L21 30	No
92555799	BVP353 18LED 40K 220V L21 30	No
92560199	BVP353 20LED RGBWW 220V L21 30 DMX	Yes
92561899	BVP353 20LED RGBNW 220V L21 30 DMX	Yes
92563299	BVP353 18LED 30K 220V L21 45	No
92564999	BVP353 18LED 40K 220V L21 45	No
92569499	BVP353 20LED RGBWW 220V L21 45 DMX	Yes
92570099	BVP353 20LED RGBNW 220V L21 45 DMX	Yes
92464299	BVP353 12LED 30K 220V L15 10	No
92465999	BVP353 12LED 40K 220V L15 10	No
92470399	BVP353 12LED RGBWW 220V L15 10 DMX	Yes
92471099	BVP353 12LED RGBNW 220V L15 10 DMX	Yes
92473499	BVP353 12LED 30K 220V L15 15	No
92474199	BVP353 12LED 40K 220V L15 15	No
92479699	BVP353 12LED RGBWW 220V L15 15 DMX	Yes
92480299	BVP353 12LED RGBNW 220V L15 15 DMX	Yes
92482699	BVP353 12LED 30K 220V L15 30	No
92483399	BVP353 12LED 40K 220V L15 30	No
92488899	BVP353 12LED RGBWW 220V L15 30 DMX	Yes
92489599	BVP353 12LED RGBNW 220V L15 30 DMX	Yes
92491899	BVP353 12LED 30K 220V L15 45	No
92492599	BVP353 12LED 40K 220V L15 45	No
92497099	BVP353 12LED RGBWW 220V L15 45 DMX	Yes
92498799	BVP353 12LED RGBNW 220V L15 45 DMX	Yes
92644899	BVP353 36LED 30K 220V L35 10	No
92645599	BVP353 36LED 40K 220V L35 10	No
92650999	BVP353 36LED RGBWW 220V L35 10 DMX	Yes
92651699	BVP353 36LED RGBNW 220V L35 10 DMX	Yes
92653099	BVP353 36LED 30K 220V L35 15	No
92654799	BVP353 36LED 40K 220V L35 15	No
92659299	BVP353 36LED RGBWW 220V L35 15 DMX	Yes
92660899	BVP353 36LED RGBNW 220V L35 15 DMX	Yes
92662299	BVP353 36LED 30K 220V L35 30	No
92663999	BVP353 36LED 40K 220V L35 30	No
92668499	BVP353 36LED RGBWW 220V L35 30 DMX	Yes
92669199	BVP353 36LED RGBNW 220V L35 30 DMX	Yes
92671499	BVP353 36LED 30K 220V L35 45	No
92672199	BVP353 36LED 40K 220V L35 45	No
92677699	BVP353 36LED RGBWW 220V L35 45 DMX	Yes
92678399	BVP353 36LED RGBNW 220V L35 45 DMX	Yes
92572499	BVP353 24LED 30K 220V L24 10	No

Order Code	Full Product Name	Dimmable
92573199	BVP353 24LED 40K 220V L24 10	No
92578699	BVP353 24LED RGBWW 220V L24 10 DMX	Yes
92579399	BVP353 24LED RGBNW 220V L24 10 DMX	Yes
92581699	BVP353 24LED 30K 220V L24 15	No
92582399	BVP353 24LED 40K 220V L24 15	No
92587899	BVP353 24LED RGBWW 220V L24 15 DMX	Yes
92588599	BVP353 24LED RGBNW 220V L24 15 DMX	Yes
92590899	BVP353 24LED 30K 220V L24 30	No
92591599	BVP353 24LED 40K 220V L24 30	No
92596099	BVP353 24LED RGBWW 220V L24 30 DMX	Yes
92597799	BVP353 24LED RGBNW 220V L24 30 DMX	Yes
92599199	BVP353 24LED 30K 220V L24 45	No
92600499	BVP353 24LED 40K 220V L24 45	No
92605999	BVP353 24LED RGBWW 220V L24 45 DMX	Yes
92606699	BVP353 24LED RGBNW 220V L24 45 DMX	Yes
92716299	BVP353 60LED 30K 220V L50 10	No
92717999	BVP353 60LED 40K 220V L50 10	No
92722399	BVP353 60LED RGBWW 220V L50 10 DMX	Yes
92723099	BVP353 60LED RGBNW 220V L50 10 DMX	Yes
92725499	BVP353 60LED 30K 220V L50 15	No
92726199	BVP353 60LED 40K 220V L50 15	No
92731599	BVP353 60LED RGBWW 220V L50 15 DMX	Yes
92732299	BVP353 60LED RGBNW 220V L50 15 DMX	Yes
92734699	BVP353 60LED 30K 220V L50 30	No
92735399	BVP353 60LED 40K 220V L50 30	No
92740799	BVP353 60LED RGBWW 220V L50 30 DMX	Yes
92741499	BVP353 60LED RGBNW 220V L50 30 DMX	Yes
92743899	BVP353 60LED 30K 220V L50 45	No
92744599	BVP353 60LED 40K 220V L50 45	No
92749099	BVP353 60LED RGBWW 220V L50 45 DMX	Yes
92750699	BVP353 60LED RGBNW 220V L50 45 DMX	Yes
92500799	BVP353 16LED 30K 220V L18 10	No
92501499	BVP353 16LED 40K 220V L18 10	No
92506999	BVP353 16LED RGBWW 220V L18 10 DMX	Yes
92507699	BVP353 16LED RGBNW 220V L18 10 DMX	Yes
92509099	BVP353 16LED 30K 220V L18 15	No
92510699	BVP353 16LED 40K 220V L18 15	No
92515199	BVP353 16LED RGBWW 220V L18 15 DMX	Yes
92516899	BVP353 16LED RGBNW 220V L18 15 DMX	Yes
92518299	BVP353 16LED 30K 220V L18 30	No
92519999	BVP353 16LED 40K 220V L18 30	No
92524399	BVP353 16LED RGBWW 220V L18 30 DMX	Yes
92525099	BVP353 16LED RGBNW 220V L18 30 DMX	Yes
92527499	BVP353 16LED 30K 220V L18 45	No
92528199	BVP353 16LED 40K 220V L18 45	No
92533599	BVP353 16LED RGBWW 220V L18 45 DMX	Yes
92534299	BVP353 16LED RGBNW 220V L18 45 DMX	Yes
92896100	BVP355 216LED 30K 220V L57 10	No

Order Code	Full Product Name	Dimmable
92897800	BVP355 216LED 40K 220V L57 10	No
92902900	BVP355 216LED RGBWW 220V L57 10 DMX	Yes
92903600	BVP355 216LED RGBNW 220V L57 10 DMX	Yes
92905000	BVP355 216LED 30K 220V L57 15	No
92906700	BVP355 216LED 40K 220V L57 15	No
92911100	BVP355 216LED RGBWW 220V L57 15 DMX	Yes
92912800	BVP355 216LED RGBNW 220V L57 15 DMX	Yes
92914200	BVP355 216LED 30K 220V L57 30	No
92915900	BVP355 216LED 40K 220V L57 30	No
92920300	BVP355 216LED RGBWW 220V L57 30 DMX	Yes
92921000	BVP355 216LED RGBNW 220V L57 30 DMX	Yes
92923400	BVP355 216LED 30K 220V L57 45	No
92924100	BVP355 216LED 40K 220V L57 45	No
92929600	BVP355 216LED RGBWW 220V L57 45 DMX	Yes
92930200	BVP355 216LED RGBNW 220V L57 45 DMX	Yes
92932600	BVP355 180LED 30K 220V L50 10	No
92933300	BVP355 180LED 40K 220V L50 10	No
92938800	BVP355 180LED RGBWW 220V L50 10 DMX	Yes
92939500	BVP355 180LED RGBNW 220V L50 10 DMX	Yes
92941800	BVP355 180LED 30K 220V L50 15	No
92942500	BVP355 180LED 40K 220V L50 15	No
92947000	BVP355 180LED RGBWW 220V L50 15 DMX	Yes
92948700	BVP355 180LED RGBNW 220V L50 15 DMX	Yes
92950000	BVP355 180LED 30K 220V L50 30	No
92951700	BVP355 180LED 40K 220V L50 30	No
92956200	BVP355 180LED RGBWW 220V L50 30 DMX	Yes
92957900	BVP355 180LED RGBNW 220V L50 30 DMX	Yes
92959300	BVP355 180LED 30K 220V L50 45	No
92960900	BVP355 180LED 40K 220V L50 45	No
92965400	BVP355 180LED RGBWW 220V L50 45 DMX	Yes
92966100	BVP355 180LED RGBNW 220V L50 45 DMX	Yes
92680699	BVP353 48LED 30K 220V L40 10	No
92681399	BVP353 48LED 40K 220V L40 10	No
92686899	BVP353 48LED RGBWW 220V L40 10 DMX	Yes
92687599	BVP353 48LED RGBNW 220V L40 10 DMX	Yes
92689999	BVP353 48LED 30K 220V L40 15	No
92690599	BVP353 48LED 40K 220V L40 15	No
92695099	BVP353 48LED RGBWW 220V L40 15 DMX	Yes
92696799	BVP353 48LED RGBNW 220V L40 15 DMX	Yes
92698199	BVP353 48LED 30K 220V L40 30	No
92699899	BVP353 48LED 40K 220V L40 30	No
92704999	BVP353 48LED RGBWW 220V L40 30 DMX	Yes
92705699	BVP353 48LED RGBNW 220V L40 30 DMX	Yes
92707099	BVP353 48LED 30K 220V L40 45	No
92708799	BVP353 48LED 40K 220V L40 45	No
92713199	BVP353 48LED RGBWW 220V L40 45 DMX	Yes
92714899	BVP353 48LED RGBNW 220V L40 45 DMX	Yes

