



# UniFlood M gen2: A high power floodlight with true modularity

## UniFlood M G2

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Benefits

- Great design flexibility with individually tilting heads and controls
- Create the right lighting effect with six different spread lenses (narrow spot to wide flood)
- Easy to control with DMX512/RDM
- A robust choice that's IP66-rated for outdoor use

### Features

- Standard: RGBW, RGB, 2700K, 3000K and 4000K
- Optional 5000K, monochromatic colors and tunable white
- Flexible lengths from 155 to 569 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

# UniFlood M G2







## Application

- Bridges, Monuments, Facades
- Parks and Plazas
- Landscape









## Warnings and Safety

- For outdoor use only.

## Dimensional drawing



## Dimensional drawing



| General Information          |                                             |
|------------------------------|---------------------------------------------|
| Driver included              | Yes                                         |
| Light Technical              |                                             |
| Color rendering index (CRI)  | >80                                         |
| Mechanical and Housing       |                                             |
| Optical cover type           | Clear glass                                 |
| Housing Color                | Dark gray                                   |
| Mech. impact protection code | IK06                                        |
| Ingress protection code      | IP66                                        |
| Approval and Application     |                                             |
| CE mark                      | Yes                                         |
| Flammability mark            | For mounting on normally flammable surfaces |

Light Technical

| Order Code   | Full Product Name                   | Light source color | Correlated Color  |               |
|--------------|-------------------------------------|--------------------|-------------------|---------------|
|              |                                     |                    | Temperature (Nom) | Luminous Flux |
| 911401746873 | BVP353 30LED 30K 220V L30 10        | 830 warm white     | 3000 K            | 4,710 lm      |
| 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX  | RGBW               | -                 | 2,855 lm      |
| 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX  | RGBW               | -                 | 2,985 lm      |
| 911401746973 | BVP353 30LED 40K 220V L30 15        | 840 neutral white  | 4000 K            | 5,520 lm      |
| 911401746983 | BVP353 30LED 27K 220V L30 15 DMX    | 827 warm white     | 2700 K            | 4,430 lm      |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX    | RGB                | -                 | 2,620 lm      |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX  | RGBW               | -                 | 3,000 lm      |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX  | RGBW               | -                 | 3,130 lm      |
| 911401747053 | BVP353 30LED 30K 220V L30 30        | 830 warm white     | 3000 K            | 5,125 lm      |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX    | RGB                | -                 | 2,715 lm      |
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX  | RGBW               | -                 | 3,105 lm      |
| 911401747133 | BVP353 30LED 27K 220V L30 45        | 827 warm white     | 2700 K            | 4,740 lm      |
| 911401747143 | BVP353 30LED 30K 220V L30 45        | 830 warm white     | 3000 K            | 4,945 lm      |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX  | RGBW               | -                 | 3,000 lm      |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX  | RGBW               | -                 | 3,130 lm      |
| 911401748673 | BVP354 96LED 30K 220V L40 10        | 830 warm white     | 3000 K            | 16,555 lm     |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX  | RGBW               | -                 | 10,505 lm     |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX  | RGBW               | -                 | 10,975 lm     |
| 911401748853 | BVP354 96LED 30K 220V L40 30        | 830 warm white     | 3000 K            | 18,005 lm     |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX  | RGBW               | -                 | 11,425 lm     |
| 911401748943 | BVP354 96LED 30K 220V L40 45        | 830 warm white     | 3000 K            | 17,385 lm     |
| 911401749013 | BVP354 96LED RGBNW 220V L40 45 DMX  | RGBW               | -                 | 11,520 lm     |
| 911401749103 | BVP354 120LED RGBNW 220V L50 10 DMX | RGBW               | -                 | 11,190 lm     |
| 911401749123 | BVP354 120LED 30K 220V L50 15       | 830 warm white     | 3000 K            | 19,795 lm     |
| 911401749223 | BVP354 120LED 40K 220V L50 30       | 840 neutral white  | 4000 K            | 22,875 lm     |
| 911401749283 | BVP354 120LED RGBNW 220V L50 30 DMX | RGBW               | -                 | 12,170 lm     |
| 911401749303 | BVP354 120LED 30K 220V L50 45       | 830 warm white     | 3000 K            | 19,795 lm     |
| 911401749363 | BVP354 120LED RGBWW 220V L50 45 DMX | RGBW               | -                 | 11,255 lm     |
| 911401749373 | BVP354 120LED RGBNW 220V L50 45 DMX | RGBW               | -                 | 11,750 lm     |
| 911401749453 | BVP354 144LED RGBWW 220V L57 10 DMX | RGBW               | -                 | 14,395 lm     |
| 911401749463 | BVP354 144LED RGBNW 220V L57 10 DMX | RGBW               | -                 | 15,030 lm     |

| Order Code   | Full Product Name                   | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401749483 | BVP354 144LED 30K 220V L57 15       | 830 warm white     | 3000 K                             | 24,930 lm     |
| 911401749553 | BVP354 144LED RGBNW 220V L57 15 DMX | RGBW               | -                                  | 15,785 lm     |
| 911401749573 | BVP354 144LED 30K 220V L57 30       | 830 warm white     | 3000 K                             | 25,820 lm     |
| 911401749643 | BVP354 144LED RGBNW 220V L57 30 DMX | RGBW               | -                                  | 16,345 lm     |
| 911401749653 | BVP354 144LED 27K 220V L57 45       | 827 warm white     | 2700 K                             | 23,900 lm     |
| 911401749693 | BVP354 144LED 30K 220V L57 45 DMX   | 830 warm white     | 3000 K                             | 23,755 lm     |
| 911401749723 | BVP354 144LED RGBWW 220V L57 45 DMX | RGBW               | -                                  | 15,115 lm     |
| 911401749733 | BVP354 144LED RGBNW 220V L57 45 DMX | RGBW               | -                                  | 15,785 lm     |
| 911401748313 | BVP353 72LED 30K 220V L57 10        | 830 warm white     | 3000 K                             | 11,870 lm     |
| 911401748323 | BVP353 72LED 40K 220V L57 10        | 840 neutral white  | 4000 K                             | 13,245 lm     |
| 911401748373 | BVP353 72LED RGBWW 220V L57 10 DMX  | RGBW               | -                                  | 7,195 lm      |
| 911401748383 | BVP353 72LED RGBNW 220V L57 10 DMX  | RGBW               | -                                  | 7,515 lm      |
| 911401748393 | BVP353 72LED 27K 220V L57 15        | 827 warm white     | 2700 K                             | 11,950 lm     |
| 911401748413 | BVP353 72LED 40K 220V L57 15        | 840 neutral white  | 4000 K                             | 13,905 lm     |
| 911401748463 | BVP353 72LED RGBWW 220V L57 15 DMX  | RGBW               | -                                  | 7,555 lm      |
| 911401748473 | BVP353 72LED RGBNW 220V L57 15 DMX  | RGBW               | -                                  | 7,890 lm      |
| 911401748483 | BVP353 72LED 27K 220V L57 30        | 827 warm white     | 2700 K                             | 12,375 lm     |
| 911401748493 | BVP353 72LED 30K 220V L57 30        | 830 warm white     | 3000 K                             | 12,910 lm     |
| 911401748503 | BVP353 72LED 40K 220V L57 30        | 840 neutral white  | 4000 K                             | 14,405 lm     |
| 911401748553 | BVP353 72LED RGBWW 220V L57 30 DMX  | RGBW               | -                                  | 7,825 lm      |
| 911401748563 | BVP353 72LED RGBNW 220V L57 30 DMX  | RGBW               | -                                  | 8,170 lm      |
| 911401748573 | BVP353 72LED 27K 220V L57 45        | 827 warm white     | 2700 K                             | 11,950 lm     |
| 911401748583 | BVP353 72LED 30K 220V L57 45        | 830 warm white     | 3000 K                             | 12,465 lm     |
| 911401748643 | BVP353 72LED RGBWW 220V L57 45 DMX  | RGBW               | -                                  | 7,555 lm      |
| 911401748653 | BVP353 72LED RGBNW 220V L57 45 DMX  | RGBW               | -                                  | 7,890 lm      |
| 911401746223 | BVP353 20LED RGBNW 220V L21 10 DMX  | RGBW               | -                                  | 1,945 lm      |
| 911401746303 | BVP353 20LED RGBWW 220V L21 15 DMX  | RGBW               | -                                  | 1,955 lm      |
| 911401746313 | BVP353 20LED RGBNW 220V L21 15 DMX  | RGBW               | -                                  | 2,040 lm      |
| 911401746333 | BVP353 18LED 30K 220V L21 30        | 830 warm white     | 3000 K                             | 3,225 lm      |
| 911401746343 | BVP353 18LED 40K 220V L21 30        | 840 neutral white  | 4000 K                             | 3,600 lm      |
| 911401746403 | BVP353 20LED RGBNW 220V L21 30 DMX  | RGBW               | -                                  | 2,115 lm      |

| Order Code   | Full Product Name                  | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401746413 | BVP353 18LED 27K 220V L21 45       | 827 warm white     | 2700 K                             | 2,985 lm      |
| 911401746423 | BVP353 18LED 30K 220V L21 45       | 830 warm white     | 3000 K                             | 3,115 lm      |
| 911401746473 | BVP353 18LED RGB 220V L21 45 DMX   | RGB                | -                                  | 1,640 lm      |
| 911401746483 | BVP353 20LED RGBWW 220V L21 45 DMX | RGBW               | -                                  | 1,955 lm      |
| 911401746493 | BVP353 20LED RGBNW 220V L21 45 DMX | RGBW               | -                                  | 2,040 lm      |
| 911401745423 | BVP353 12LED 27K 220V L15 10       | 827 warm white     | 2700 K                             | 1,760 lm      |
| 911401745433 | BVP353 12LED 30K 220V L15 10       | 830 warm white     | 3000 K                             | 1,835 lm      |
| 911401745443 | BVP353 12LED 40K 220V L15 10       | 840 neutral white  | 4000 K                             | 2,050 lm      |
| 911401745453 | BVP353 12LED 27K 220V L15 10 DMX   | 827 warm white     | 2700 K                             | 1,615 lm      |
| 911401745463 | BVP353 12LED 30K 220V L15 10 DMX   | 830 warm white     | 3000 K                             | 1,685 lm      |
| 911401745483 | BVP353 12LED RGB 220V L15 10 DMX   | RGB                | -                                  | 960 lm        |
| 911401745493 | BVP353 12LED RGBWW 220V L15 10 DMX | RGBW               | -                                  | 1,175 lm      |
| 911401745503 | BVP353 12LED RGBNW 220V L15 10 DMX | RGBW               | -                                  | 1,225 lm      |
| 911401745523 | BVP353 12LED 30K 220V L15 15       | 830 warm white     | 3000 K                             | 1,925 lm      |
| 911401745533 | BVP353 12LED 40K 220V L15 15       | 840 neutral white  | 4000 K                             | 2,150 lm      |
| 911401745553 | BVP353 12LED 30K 220V L15 15 DMX   | 830 warm white     | 3000 K                             | 1,770 lm      |
| 911401745583 | BVP353 12LED RGBWW 220V L15 15 DMX | RGBW               | -                                  | 1,230 lm      |
| 911401745593 | BVP353 12LED RGBNW 220V L15 15 DMX | RGBW               | -                                  | 1,285 lm      |
| 911401745603 | BVP353 12LED 27K 220V L15 30       | 827 warm white     | 2700 K                             | 1,915 lm      |
| 911401745613 | BVP353 12LED 30K 220V L15 30       | 830 warm white     | 3000 K                             | 1,995 lm      |
| 911401745623 | BVP353 12LED 40K 220V L15 30       | 840 neutral white  | 4000 K                             | 2,225 lm      |
| 911401745693 | BVP353 12LED 27K 220V L15 45       | 827 warm white     | 2700 K                             | 1,845 lm      |
| 911401745703 | BVP353 12LED 30K 220V L15 45       | 830 warm white     | 3000 K                             | 1,925 lm      |
| 911401745713 | BVP353 12LED 40K 220V L15 45       | 840 neutral white  | 4000 K                             | 2,150 lm      |
| 911401745753 | BVP353 12LED RGB 220V L15 45 DMX   | RGB                | -                                  | 1,010 lm      |
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | RGBW               | -                                  | 1,230 lm      |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | RGBW               | -                                  | 1,285 lm      |
| 911401747233 | BVP353 36LED 30K 220V L35 10       | 830 warm white     | 3000 K                             | 6,205 lm      |
| 911401747243 | BVP353 36LED 40K 220V L35 10       | 840 neutral white  | 4000 K                             | 6,925 lm      |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX   | RGB                | -                                  | 3,290 lm      |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | RGBW               | -                                  | 3,805 lm      |
| 911401747333 | BVP353 36LED 40K 220V L35 15       | 840 neutral white  | 4000 K                             | 7,270 lm      |
| 911401747403 | BVP353 36LED 27K 220V L35 30       | 827 warm white     | 2700 K                             | 6,470 lm      |
| 911401747423 | BVP353 36LED 40K 220V L35 30       | 840 neutral white  | 4000 K                             | 7,530 lm      |
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX   | 830 warm white     | 3000 K                             | 6,070 lm      |

| Order Code   | Full Product Name                  | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|------------------------------------|--------------------|------------------------------------|---------------|
| 911401747493 | BVP353 36LED 27K 220V L35 45       | 827 warm white     | 2700 K                             | 6,245 lm      |
| 911401747503 | BVP353 36LED 30K 220V L35 45       | 830 warm white     | 3000 K                             | 6,515 lm      |
| 911401747513 | BVP353 36LED 40K 220V L35 45       | 840 neutral white  | 4000 K                             | 7,270 lm      |
| 911401747533 | BVP353 36LED 30K 220V L35 45 DMX   | 830 warm white     | 3000 K                             | 5,860 lm      |
| 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | RGBW               | -                                  | 3,995 lm      |
| 911401746513 | BVP353 24LED 30K 220V L24 10       | 830 warm white     | 3000 K                             | 3,770 lm      |
| 911401746523 | BVP353 24LED 40K 220V L24 10       | 840 neutral white  | 4000 K                             | 4,205 lm      |
| 911401746563 | BVP353 24LED RGB 220V L24 10 DMX   | RGB                | -                                  | 2,085 lm      |
| 911401746593 | BVP353 24LED 27K 220V L24 15       | 827 warm white     | 2700 K                             | 3,795 lm      |
| 911401746603 | BVP353 24LED 30K 220V L24 15       | 830 warm white     | 3000 K                             | 3,955 lm      |
| 911401746613 | BVP353 24LED 40K 220V L24 15       | 840 neutral white  | 4000 K                             | 4,415 lm      |
| 911401746693 | BVP353 24LED 30K 220V L24 30       | 830 warm white     | 3000 K                             | 4,100 lm      |
| 911401746743 | BVP353 24LED RGB 220V L24 30 DMX   | RGB                | -                                  | 2,270 lm      |
| 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | RGBW               | -                                  | 2,555 lm      |
| 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | RGBW               | -                                  | 2,665 lm      |
| 911401746773 | BVP353 24LED 27K 220V L24 45       | 827 warm white     | 2700 K                             | 3,795 lm      |
| 911401746783 | BVP353 24LED 30K 220V L24 45       | 830 warm white     | 3000 K                             | 3,955 lm      |
| 911401746793 | BVP353 24LED 40K 220V L24 45       | 840 neutral white  | 4000 K                             | 4,415 lm      |
| 911401747943 | BVP353 60LED 27K 220V L50 10       | 827 warm white     | 2700 K                             | 9,150 lm      |
| 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | RGBW               | -                                  | 5,995 lm      |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX   | RGB                | -                                  | 5,480 lm      |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | RGBW               | -                                  | 6,575 lm      |
| 911401748123 | BVP353 60LED 27K 220V L50 30       | 827 warm white     | 2700 K                             | 9,950 lm      |
| 911401748133 | BVP353 60LED 30K 220V L50 30       | 830 warm white     | 3000 K                             | 10,380 lm     |
| 911401748143 | BVP353 60LED 40K 220V L50 30       | 840 neutral white  | 4000 K                             | 11,580 lm     |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | RGBW               | -                                  | 6,810 lm      |
| 911401748213 | BVP353 60LED 27K 220V L50 45       | 827 warm white     | 2700 K                             | 9,605 lm      |
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX | RGBW               | -                                  | 6,295 lm      |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX | RGBW               | -                                  | 6,575 lm      |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX   | 830 warm white     | 3000 K                             | 2,145 lm      |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX | RGBW               | -                                  | 1,425 lm      |
| 911401745883 | BVP353 16LED 30K 220V L18 15       | 830 warm white     | 3000 K                             | 3,020 lm      |
| 911401745893 | BVP353 16LED 40K 220V L18 15       | 840 neutral white  | 4000 K                             | 3,365 lm      |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX   | RGB                | -                                  | 1,260 lm      |

| Order Code   | Full Product Name                   | Light source color | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|-------------------------------------|--------------------|------------------------------------|---------------|
| 911401745973 | BVP353 16LED 30K 220V L18 30        | 830 warm white     | 3000 K                             | 3,125 lm      |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX    | RGB                | -                                  | 1,305 lm      |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX  | RGBW               | -                                  | 1,550 lm      |
| 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX  | RGBW               | -                                  | 1,620 lm      |
| 911401746113 | BVP353 15LED RGB 220V L18 45 DMX    | RGB                | -                                  | 1,260 lm      |
| 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX  | RGBW               | -                                  | 1,565 lm      |
| 911401749753 | BVP355 216LED 30K 220V L57 10       | 830 warm white     | 3000 K                             | 35,615 lm     |
| 911401749763 | BVP355 216LED 40K 220V L57 10       | 840 neutral white  | 4000 K                             | 39,740 lm     |
| 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | RGBW               | -                                  | 21,590 lm     |
| 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | RGBW               | -                                  | 22,550 lm     |
| 911401749913 | BVP355 216LED RGBNW 220V L57 15 DMX | RGBW               | -                                  | 23,675 lm     |
| 911401750003 | BVP355 216LED RGBNW 220V L57 30 DMX | RGBW               | -                                  | 24,520 lm     |
| 911401750023 | BVP355 216LED 30K 220V L57 45       | 830 warm white     | 3000 K                             | 37,400 lm     |
| 911401750093 | BVP355 216LED RGBNW 220V L57 45 DMX | RGBW               | -                                  | 23,675 lm     |
| 911401750123 | BVP355 180LED 40K 220V L50 10       | 840 neutral white  | 4000 K                             | 31,945 lm     |
| 911401750213 | BVP355 180LED 40K 220V L50 15       | 840 neutral white  | 4000 K                             | 33,540 lm     |
| 911401750303 | BVP355 180LED 40K 220V L50 30       | 840 neutral white  | 4000 K                             | 34,740 lm     |
| 911401750363 | BVP355 180LED RGBNW 220V L50 30 DMX | RGBW               | -                                  | 20,435 lm     |
| 911401750393 | BVP355 180LED 40K 220V L50 45       | 840 neutral white  | 4000 K                             | 33,540 lm     |
| 911401750433 | BVP355 180LED RGB 220V L50 45 DMX   | RGB                | -                                  | 16,440 lm     |
| 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX  | RGBW               | -                                  | 5,250 lm      |
| 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX  | RGBW               | -                                  | 5,485 lm      |
| 911401747693 | BVP353 48LED 40K 220V L40 15        | 840 neutral white  | 4000 K                             | 9,090 lm      |
| 911401747723 | BVP353 48LED 40K 220V L40 15 DMX    | 840 neutral white  | 4000 K                             | 8,385 lm      |
| 911401747733 | BVP353 48LED RGB 220V L40 15 DMX    | RGB                | -                                  | 4,020 lm      |
| 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX  | RGBW               | -                                  | 5,515 lm      |
| 911401747783 | BVP353 48LED 40K 220V L40 30        | 840 neutral white  | 4000 K                             | 9,415 lm      |
| 911401747823 | BVP353 48LED RGB 220V L40 30 DMX    | RGB                | -                                  | 4,165 lm      |
| 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX  | RGBW               | -                                  | 5,965 lm      |



| Order Code   | Full Product Name                     | Light source         | Correlated Color  |               |
|--------------|---------------------------------------|----------------------|-------------------|---------------|
|              |                                       | color                | Temperature (Nom) | Luminous Flux |
| 911401746873 | BVP353 48LED 40K 220V L40 45          | 840 neutral<br>white | 4000 K            | 9,090 lm      |
| 911401747933 | BVP353 48LED RGBNW 220V L40 45<br>DMX | RGBW                 | -                 | 5,760 lm      |

Operating and Electrical

| Order Code   | Full Product Name                   | Power Consumption | Order Code   | Full Product Name                  | Power Consumption |
|--------------|-------------------------------------|-------------------|--------------|------------------------------------|-------------------|
| 911401746873 | BVP353 30LED 30K 220V L30 10        | 60 W              | 911401748393 | BVP353 72LED 27K 220V L57 15       | 150 W             |
| 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX  | 60 W              | 911401748413 | BVP353 72LED 40K 220V L57 15       | 150 W             |
| 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX  | 60 W              | 911401748463 | BVP353 72LED RGBWW 220V L57 15 DMX | 150 W             |
| 911401746973 | BVP353 30LED 40K 220V L30 15        | 60 W              | 911401748473 | BVP353 72LED RGBNW 220V L57 15 DMX | 150 W             |
| 911401746983 | BVP353 30LED 27K 220V L30 15 DMX    | 60 W              | 911401748483 | BVP353 72LED 27K 220V L57 30       | 150 W             |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX    | 60 W              | 911401748493 | BVP353 72LED 30K 220V L57 30       | 150 W             |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX  | 60 W              | 911401748503 | BVP353 72LED 40K 220V L57 30       | 150 W             |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX  | 60 W              | 911401748553 | BVP353 72LED RGBWW 220V L57 30 DMX | 150 W             |
| 911401747053 | BVP353 30LED 30K 220V L30 30        | 60 W              | 911401748563 | BVP353 72LED RGBNW 220V L57 30 DMX | 150 W             |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX    | 60 W              | 911401748573 | BVP353 72LED 27K 220V L57 45       | 150 W             |
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX  | 60 W              | 911401748583 | BVP353 72LED 30K 220V L57 45       | 150 W             |
| 911401747133 | BVP353 30LED 27K 220V L30 45        | 60 W              | 911401748643 | BVP353 72LED RGBWW 220V L57 45 DMX | 150 W             |
| 911401747143 | BVP353 30LED 30K 220V L30 45        | 60 W              | 911401748653 | BVP353 72LED RGBNW 220V L57 45 DMX | 150 W             |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX  | 60 W              | 911401746223 | BVP353 20LED RGBNW 220V L21 10 DMX | 40 W              |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX  | 60 W              | 911401746303 | BVP353 20LED RGBWW 220V L21 15 DMX | 40 W              |
| 911401748673 | BVP354 96LED 30K 220V L40 10        | 200 W             | 911401746313 | BVP353 20LED RGBNW 220V L21 15 DMX | 40 W              |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX  | 200 W             | 911401746333 | BVP353 18LED 30K 220V L21 30       | 40 W              |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX  | 200 W             | 911401746343 | BVP353 18LED 40K 220V L21 30       | 40 W              |
| 911401748853 | BVP354 96LED 30K 220V L40 30        | 200 W             | 911401746403 | BVP353 20LED RGBNW 220V L21 30 DMX | 40 W              |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX  | 200 W             | 911401746413 | BVP353 18LED 27K 220V L21 45       | 40 W              |
| 911401748943 | BVP354 96LED 30K 220V L40 45        | 200 W             | 911401746423 | BVP353 18LED 30K 220V L21 45       | 40 W              |
| 911401749013 | BVP354 96LED RGBNW 220V L40 45 DMX  | 200 W             | 911401746473 | BVP353 18LED RGB 220V L21 45 DMX   | 40 W              |
| 911401749103 | BVP354 120LED RGBNW 220V L50 10 DMX | 240 W             | 911401746483 | BVP353 20LED RGBWW 220V L21 45 DMX | 40 W              |
| 911401749123 | BVP354 120LED 30K 220V L50 15       | 240 W             | 911401746493 | BVP353 20LED RGBNW 220V L21 45 DMX | 40 W              |
| 911401749223 | BVP354 120LED 40K 220V L50 30       | 240 W             | 911401745423 | BVP353 12LED 27K 220V L15 10       | 24 W              |
| 911401749283 | BVP354 120LED RGBNW 220V L50 30 DMX | 240 W             | 911401745433 | BVP353 12LED 30K 220V L15 10       | 24 W              |
| 911401749303 | BVP354 120LED 30K 220V L50 45       | 240 W             | 911401745443 | BVP353 12LED 40K 220V L15 10       | 24 W              |
| 911401749363 | BVP354 120LED RGBWW 220V L50 45 DMX | 240 W             | 911401745453 | BVP353 12LED 27K 220V L15 10 DMX   | 24 W              |
| 911401749373 | BVP354 120LED RGBNW 220V L50 45 DMX | 240 W             | 911401745463 | BVP353 12LED 30K 220V L15 10 DMX   | 24 W              |
| 911401749453 | BVP354 144LED RGBWW 220V L57 10 DMX | 300 W             | 911401745483 | BVP353 12LED RGB 220V L15 10 DMX   | 24 W              |
| 911401749463 | BVP354 144LED RGBNW 220V L57 10 DMX | 300 W             | 911401745493 | BVP353 12LED RGBWW 220V L15 10 DMX | 24 W              |
| 911401749483 | BVP354 144LED 30K 220V L57 15       | 300 W             | 911401745503 | BVP353 12LED RGBNW 220V L15 10 DMX | 24 W              |
| 911401749553 | BVP354 144LED RGBNW 220V L57 15 DMX | 300 W             | 911401745523 | BVP353 12LED 30K 220V L15 15       | 24 W              |
| 911401749573 | BVP354 144LED 30K 220V L57 30       | 300 W             | 911401745533 | BVP353 12LED 40K 220V L15 15       | 24 W              |
| 911401749643 | BVP354 144LED RGBNW 220V L57 30 DMX | 300 W             | 911401745553 | BVP353 12LED 30K 220V L15 15 DMX   | 24 W              |
| 911401749653 | BVP354 144LED 27K 220V L57 45       | 300 W             | 911401745583 | BVP353 12LED RGBWW 220V L15 15 DMX | 24 W              |
| 911401749693 | BVP354 144LED 30K 220V L57 45 DMX   | 300 W             | 911401745593 | BVP353 12LED RGBNW 220V L15 15 DMX | 24 W              |
| 911401749723 | BVP354 144LED RGBWW 220V L57 45 DMX | 300 W             | 911401745603 | BVP353 12LED 27K 220V L15 30       | 24 W              |
| 911401749733 | BVP354 144LED RGBNW 220V L57 45 DMX | 300 W             | 911401745613 | BVP353 12LED 30K 220V L15 30       | 24 W              |
| 911401748313 | BVP353 72LED 30K 220V L57 10        | 150 W             | 911401745623 | BVP353 12LED 40K 220V L15 30       | 24 W              |
| 911401748323 | BVP353 72LED 40K 220V L57 10        | 150 W             | 911401745693 | BVP353 12LED 27K 220V L15 45       | 24 W              |
| 911401748373 | BVP353 72LED RGBWW 220V L57 10 DMX  | 150 W             | 911401745703 | BVP353 12LED 30K 220V L15 45       | 24 W              |
| 911401748383 | BVP353 72LED RGBNW 220V L57 10 DMX  | 150 W             | 911401745713 | BVP353 12LED 40K 220V L15 45       | 24 W              |

| Order Code   | Full Product Name                  | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401745753 | BVP353 12LED RGB 220V L15 45 DMX   | 24 W              |
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | 24 W              |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | 24 W              |
| 911401747233 | BVP353 36LED 30K 220V L35 10       | 80 W              |
| 911401747243 | BVP353 36LED 40K 220V L35 10       | 80 W              |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX   | 80 W              |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | 80 W              |
| 911401747333 | BVP353 36LED 40K 220V L35 15       | 80 W              |
| 911401747403 | BVP353 36LED 27K 220V L35 30       | 80 W              |
| 911401747423 | BVP353 36LED 40K 220V L35 30       | 80 W              |
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX   | 80 W              |
| 911401747493 | BVP353 36LED 27K 220V L35 45       | 80 W              |
| 911401747503 | BVP353 36LED 30K 220V L35 45       | 80 W              |
| 911401747513 | BVP353 36LED 40K 220V L35 45       | 80 W              |
| 911401747533 | BVP353 36LED 30K 220V L35 45 DMX   | 80 W              |
| 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | 80 W              |
| 911401746513 | BVP353 24LED 30K 220V L24 10       | 50 W              |
| 911401746523 | BVP353 24LED 40K 220V L24 10       | 50 W              |
| 911401746563 | BVP353 24LED RGB 220V L24 10 DMX   | 50 W              |
| 911401746593 | BVP353 24LED 27K 220V L24 15       | 50 W              |
| 911401746603 | BVP353 24LED 30K 220V L24 15       | 50 W              |
| 911401746613 | BVP353 24LED 40K 220V L24 15       | 50 W              |
| 911401746693 | BVP353 24LED 30K 220V L24 30       | 50 W              |
| 911401746743 | BVP353 24LED RGB 220V L24 30 DMX   | 50 W              |
| 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | 50 W              |
| 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | 50 W              |
| 911401746773 | BVP353 24LED 27K 220V L24 45       | 50 W              |
| 911401746783 | BVP353 24LED 30K 220V L24 45       | 50 W              |
| 911401746793 | BVP353 24LED 40K 220V L24 45       | 50 W              |
| 911401747943 | BVP353 60LED 27K 220V L50 10       | 120 W             |
| 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | 120 W             |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX   | 120 W             |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | 120 W             |
| 911401748123 | BVP353 60LED 27K 220V L50 30       | 120 W             |
| 911401748133 | BVP353 60LED 30K 220V L50 30       | 120 W             |
| 911401748143 | BVP353 60LED 40K 220V L50 30       | 120 W             |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | 120 W             |
| 911401748213 | BVP353 60LED 27K 220V L50 45       | 120 W             |

| Order Code   | Full Product Name                   | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX  | 120 W             |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX  | 120 W             |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX    | 30 W              |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX  | 30 W              |
| 911401745883 | BVP353 16LED 30K 220V L18 15        | 30 W              |
| 911401745893 | BVP353 16LED 40K 220V L18 15        | 30 W              |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX    | 30 W              |
| 911401745973 | BVP353 16LED 30K 220V L18 30        | 30 W              |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX    | 30 W              |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX  | 30 W              |
| 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX  | 30 W              |
| 911401746113 | BVP353 15LED RGB 220V L18 45 DMX    | 30 W              |
| 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX  | 30 W              |
| 911401749753 | BVP355 216LED 30K 220V L57 10       | 450 W             |
| 911401749763 | BVP355 216LED 40K 220V L57 10       | 450 W             |
| 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | 450 W             |
| 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | 450 W             |
| 911401749913 | BVP355 216LED RGBNW 220V L57 15 DMX | 450 W             |
| 911401750003 | BVP355 216LED RGBNW 220V L57 30 DMX | 450 W             |
| 911401750023 | BVP355 216LED 30K 220V L57 45       | 450 W             |
| 911401750093 | BVP355 216LED RGBNW 220V L57 45 DMX | 450 W             |
| 911401750123 | BVP355 180LED 40K 220V L50 10       | 360 W             |
| 911401750213 | BVP355 180LED 40K 220V L50 15       | 360 W             |
| 911401750303 | BVP355 180LED 40K 220V L50 30       | 360 W             |
| 911401750363 | BVP355 180LED RGBNW 220V L50 30 DMX | 360 W             |
| 911401750393 | BVP355 180LED 40K 220V L50 45       | 360 W             |
| 911401750433 | BVP355 180LED RGB 220V L50 45 DMX   | 360 W             |
| 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX  | 100 W             |
| 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX  | 100 W             |
| 911401747693 | BVP353 48LED 40K 220V L40 15        | 100 W             |
| 911401747723 | BVP353 48LED 40K 220V L40 15 DMX    | 100 W             |
| 911401747733 | BVP353 48LED RGB 220V L40 15 DMX    | 100 W             |
| 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX  | 100 W             |
| 911401747783 | BVP353 48LED 40K 220V L40 30        | 100 W             |
| 911401747823 | BVP353 48LED RGB 220V L40 30 DMX    | 100 W             |
| 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX  | 100 W             |
| 911401747873 | BVP353 48LED 40K 220V L40 45        | 100 W             |
| 911401747933 | BVP353 48LED RGBNW 220V L40 45 DMX  | 100 W             |

Controls and Dimming

| Order Code   | Full Product Name                  | Dimmable |
|--------------|------------------------------------|----------|
| 911401746873 | BVP353 30LED 30K 220V L30 10       | No       |
| 911401746933 | BVP353 32LED RGBWW 220V L30 10 DMX | Yes      |
| 911401746943 | BVP353 32LED RGBNW 220V L30 10 DMX | Yes      |
| 911401746973 | BVP353 30LED 40K 220V L30 15       | No       |
| 911401746983 | BVP353 30LED 27K 220V L30 15 DMX   | Yes      |
| 911401747013 | BVP353 30LED RGB 220V L30 15 DMX   | Yes      |
| 911401747023 | BVP353 32LED RGBWW 220V L30 15 DMX | Yes      |
| 911401747033 | BVP353 32LED RGBNW 220V L30 15 DMX | Yes      |
| 911401747053 | BVP353 30LED 30K 220V L30 30       | No       |
| 911401747103 | BVP353 30LED RGB 220V L30 30 DMX   | Yes      |

| Order Code   | Full Product Name                  | Dimmable |
|--------------|------------------------------------|----------|
| 911401747113 | BVP353 32LED RGBWW 220V L30 30 DMX | Yes      |
| 911401747133 | BVP353 30LED 27K 220V L30 45       | No       |
| 911401747143 | BVP353 30LED 30K 220V L30 45       | No       |
| 911401747203 | BVP353 32LED RGBWW 220V L30 45 DMX | Yes      |
| 911401747213 | BVP353 32LED RGBNW 220V L30 45 DMX | Yes      |
| 911401748673 | BVP354 96LED 30K 220V L40 10       | No       |
| 911401748733 | BVP354 96LED RGBWW 220V L40 10 DMX | Yes      |
| 911401748743 | BVP354 96LED RGBNW 220V L40 10 DMX | Yes      |
| 911401748853 | BVP354 96LED 30K 220V L40 30       | No       |
| 911401748913 | BVP354 96LED RGBWW 220V L40 30 DMX | Yes      |

| Order Code   | Full Product Name                   | Dimmable |
|--------------|-------------------------------------|----------|
| 911401748943 | BVP354 96LED 30K 220V L40 45        | No       |
| 911401749013 | BVP354 96LED RGBNW 220V L40 45 DMX  | Yes      |
| 911401749103 | BVP354 120LED RGBNW 220V L50 10 DMX | Yes      |
| 911401749123 | BVP354 120LED 30K 220V L50 15       | No       |
| 911401749223 | BVP354 120LED 40K 220V L50 30       | No       |
| 911401749283 | BVP354 120LED RGBNW 220V L50 30 DMX | Yes      |
| 911401749303 | BVP354 120LED 30K 220V L50 45       | No       |
| 911401749363 | BVP354 120LED RGBWW 220V L50 45 DMX | Yes      |
| 911401749373 | BVP354 120LED RGBNW 220V L50 45 DMX | Yes      |
| 911401749453 | BVP354 144LED RGBWW 220V L57 10 DMX | Yes      |
| 911401749463 | BVP354 144LED RGBNW 220V L57 10 DMX | Yes      |
| 911401749483 | BVP354 144LED 30K 220V L57 15       | No       |
| 911401749553 | BVP354 144LED RGBNW 220V L57 15 DMX | Yes      |
| 911401749573 | BVP354 144LED 30K 220V L57 30       | No       |
| 911401749643 | BVP354 144LED RGBNW 220V L57 30 DMX | Yes      |
| 911401749653 | BVP354 144LED 27K 220V L57 45       | No       |
| 911401749693 | BVP354 144LED 30K 220V L57 45 DMX   | Yes      |
| 911401749723 | BVP354 144LED RGBWW 220V L57 45 DMX | Yes      |
| 911401749733 | BVP354 144LED RGBNW 220V L57 45 DMX | Yes      |
| 911401748313 | BVP353 72LED 30K 220V L57 10        | No       |
| 911401748323 | BVP353 72LED 40K 220V L57 10        | No       |
| 911401748373 | BVP353 72LED RGBWW 220V L57 10 DMX  | Yes      |
| 911401748383 | BVP353 72LED RGBNW 220V L57 10 DMX  | Yes      |
| 911401748393 | BVP353 72LED 27K 220V L57 15        | No       |
| 911401748413 | BVP353 72LED 40K 220V L57 15        | No       |
| 911401748463 | BVP353 72LED RGBWW 220V L57 15 DMX  | Yes      |
| 911401748473 | BVP353 72LED RGBNW 220V L57 15 DMX  | Yes      |
| 911401748483 | BVP353 72LED 27K 220V L57 30        | No       |
| 911401748493 | BVP353 72LED 30K 220V L57 30        | No       |
| 911401748503 | BVP353 72LED 40K 220V L57 30        | No       |
| 911401748553 | BVP353 72LED RGBWW 220V L57 30 DMX  | Yes      |
| 911401748563 | BVP353 72LED RGBNW 220V L57 30 DMX  | Yes      |
| 911401748573 | BVP353 72LED 27K 220V L57 45        | No       |
| 911401748583 | BVP353 72LED 30K 220V L57 45        | No       |
| 911401748643 | BVP353 72LED RGBWW 220V L57 45 DMX  | Yes      |
| 911401748653 | BVP353 72LED RGBNW 220V L57 45 DMX  | Yes      |
| 911401746223 | BVP353 20LED RGBNW 220V L21 10 DMX  | Yes      |
| 911401746303 | BVP353 20LED RGBWW 220V L21 15 DMX  | Yes      |
| 911401746313 | BVP353 20LED RGBNW 220V L21 15 DMX  | Yes      |
| 911401746333 | BVP353 18LED 30K 220V L21 30        | No       |
| 911401746343 | BVP353 18LED 40K 220V L21 30        | No       |
| 911401746403 | BVP353 20LED RGBNW 220V L21 30 DMX  | Yes      |
| 911401746413 | BVP353 18LED 27K 220V L21 45        | No       |
| 911401746423 | BVP353 18LED 30K 220V L21 45        | No       |
| 911401746473 | BVP353 18LED RGB 220V L21 45 DMX    | Yes      |
| 911401746483 | BVP353 20LED RGBWW 220V L21 45 DMX  | Yes      |
| 911401746493 | BVP353 20LED RGBNW 220V L21 45 DMX  | Yes      |
| 911401745423 | BVP353 12LED 27K 220V L15 10        | No       |
| 911401745433 | BVP353 12LED 30K 220V L15 10        | No       |
| 911401745443 | BVP353 12LED 40K 220V L15 10        | No       |
| 911401745453 | BVP353 12LED 27K 220V L15 10 DMX    | Yes      |
| 911401745463 | BVP353 12LED 30K 220V L15 10 DMX    | Yes      |

| Order Code   | Full Product Name                  | Dimmable |
|--------------|------------------------------------|----------|
| 911401745483 | BVP353 12LED RGB 220V L15 10 DMX   | Yes      |
| 911401745493 | BVP353 12LED RGBWW 220V L15 10 DMX | Yes      |
| 911401745503 | BVP353 12LED RGBNW 220V L15 10 DMX | Yes      |
| 911401745523 | BVP353 12LED 30K 220V L15 15       | No       |
| 911401745533 | BVP353 12LED 40K 220V L15 15       | No       |
| 911401745553 | BVP353 12LED 30K 220V L15 15 DMX   | Yes      |
| 911401745583 | BVP353 12LED RGBWW 220V L15 15 DMX | Yes      |
| 911401745593 | BVP353 12LED RGBNW 220V L15 15 DMX | Yes      |
| 911401745603 | BVP353 12LED 27K 220V L15 30       | No       |
| 911401745613 | BVP353 12LED 30K 220V L15 30       | No       |
| 911401745623 | BVP353 12LED 40K 220V L15 30       | No       |
| 911401745693 | BVP353 12LED 27K 220V L15 45       | No       |
| 911401745703 | BVP353 12LED 30K 220V L15 45       | No       |
| 911401745713 | BVP353 12LED 40K 220V L15 45       | No       |
| 911401745753 | BVP353 12LED RGB 220V L15 45 DMX   | Yes      |
| 911401745763 | BVP353 12LED RGBWW 220V L15 45 DMX | Yes      |
| 911401745773 | BVP353 12LED RGBNW 220V L15 45 DMX | Yes      |
| 911401747233 | BVP353 36LED 30K 220V L35 10       | No       |
| 911401747243 | BVP353 36LED 40K 220V L35 10       | No       |
| 911401747283 | BVP353 36LED RGB 220V L35 10 DMX   | Yes      |
| 911401747303 | BVP353 36LED RGBNW 220V L35 10 DMX | Yes      |
| 911401747333 | BVP353 36LED 40K 220V L35 15       | No       |
| 911401747403 | BVP353 36LED 27K 220V L35 30       | No       |
| 911401747423 | BVP353 36LED 40K 220V L35 30       | No       |
| 911401747443 | BVP353 36LED 30K 220V L35 30 DMX   | Yes      |
| 911401747493 | BVP353 36LED 27K 220V L35 45       | No       |
| 911401747503 | BVP353 36LED 30K 220V L35 45       | No       |
| 911401747513 | BVP353 36LED 40K 220V L35 45       | No       |
| 911401747533 | BVP353 36LED 30K 220V L35 45 DMX   | Yes      |
| 911401747573 | BVP353 36LED RGBNW 220V L35 45 DMX | Yes      |
| 911401746513 | BVP353 24LED 30K 220V L24 10       | No       |
| 911401746523 | BVP353 24LED 40K 220V L24 10       | No       |
| 911401746563 | BVP353 24LED RGB 220V L24 10 DMX   | Yes      |
| 911401746593 | BVP353 24LED 27K 220V L24 15       | No       |
| 911401746603 | BVP353 24LED 30K 220V L24 15       | No       |
| 911401746613 | BVP353 24LED 40K 220V L24 15       | No       |
| 911401746693 | BVP353 24LED 30K 220V L24 30       | No       |
| 911401746743 | BVP353 24LED RGB 220V L24 30 DMX   | Yes      |
| 911401746753 | BVP353 24LED RGBWW 220V L24 30 DMX | Yes      |
| 911401746763 | BVP353 24LED RGBNW 220V L24 30 DMX | Yes      |
| 911401746773 | BVP353 24LED 27K 220V L24 45       | No       |
| 911401746783 | BVP353 24LED 30K 220V L24 45       | No       |
| 911401746793 | BVP353 24LED 40K 220V L24 45       | No       |
| 911401747943 | BVP353 60LED 27K 220V L50 10       | No       |
| 911401748013 | BVP353 60LED RGBWW 220V L50 10 DMX | Yes      |
| 911401748093 | BVP353 60LED RGB 220V L50 15 DMX   | Yes      |
| 911401748113 | BVP353 60LED RGBNW 220V L50 15 DMX | Yes      |
| 911401748123 | BVP353 60LED 27K 220V L50 30       | No       |
| 911401748133 | BVP353 60LED 30K 220V L50 30       | No       |
| 911401748143 | BVP353 60LED 40K 220V L50 30       | No       |
| 911401748203 | BVP353 60LED RGBNW 220V L50 30 DMX | Yes      |
| 911401748213 | BVP353 60LED 27K 220V L50 45       | No       |

| Order Code   | Full Product Name                   | Dimmable |
|--------------|-------------------------------------|----------|
| 911401748283 | BVP353 60LED RGBWW 220V L50 45 DMX  | Yes      |
| 911401748293 | BVP353 60LED RGBNW 220V L50 45 DMX  | Yes      |
| 911401745823 | BVP353 16LED 30K 220V L18 10 DMX    | Yes      |
| 911401745853 | BVP353 16LED RGBWW 220V L18 10 DMX  | Yes      |
| 911401745883 | BVP353 16LED 30K 220V L18 15        | No       |
| 911401745893 | BVP353 16LED 40K 220V L18 15        | No       |
| 911401745933 | BVP353 15LED RGB 220V L18 15 DMX    | Yes      |
| 911401745973 | BVP353 16LED 30K 220V L18 30        | No       |
| 911401746023 | BVP353 15LED RGB 220V L18 30 DMX    | Yes      |
| 911401746033 | BVP353 16LED RGBWW 220V L18 30 DMX  | Yes      |
| 911401746043 | BVP353 16LED RGBNW 220V L18 30 DMX  | Yes      |
| 911401746113 | BVP353 15LED RGB 220V L18 45 DMX    | Yes      |
| 911401746133 | BVP353 16LED RGBNW 220V L18 45 DMX  | Yes      |
| 911401749753 | BVP355 216LED 30K 220V L57 10       | No       |
| 911401749763 | BVP355 216LED 40K 220V L57 10       | No       |
| 911401749813 | BVP355 216LED RGBWW 220V L57 10 DMX | Yes      |
| 911401749823 | BVP355 216LED RGBNW 220V L57 10 DMX | Yes      |
| 911401749913 | BVP355 216LED RGBNW 220V L57 15 DMX | Yes      |
| 911401750003 | BVP355 216LED RGBNW 220V L57 30 DMX | Yes      |

| Order Code   | Full Product Name                   | Dimmable |
|--------------|-------------------------------------|----------|
| 911401750023 | BVP355 216LED 30K 220V L57 45       | No       |
| 911401750093 | BVP355 216LED RGBNW 220V L57 45 DMX | Yes      |
| 911401750123 | BVP355 180LED 40K 220V L50 10       | No       |
| 911401750213 | BVP355 180LED 40K 220V L50 15       | No       |
| 911401750303 | BVP355 180LED 40K 220V L50 30       | No       |
| 911401750363 | BVP355 180LED RGBNW 220V L50 30 DMX | Yes      |
| 911401750393 | BVP355 180LED 40K 220V L50 45       | No       |
| 911401750433 | BVP355 180LED RGB 220V L50 45 DMX   | Yes      |
| 911401747653 | BVP353 48LED RGBWW 220V L40 10 DMX  | Yes      |
| 911401747663 | BVP353 48LED RGBNW 220V L40 10 DMX  | Yes      |
| 911401747693 | BVP353 48LED 40K 220V L40 15        | No       |
| 911401747723 | BVP353 48LED 40K 220V L40 15 DMX    | Yes      |
| 911401747733 | BVP353 48LED RGB 220V L40 15 DMX    | Yes      |
| 911401747743 | BVP353 48LED RGBWW 220V L40 15 DMX  | Yes      |
| 911401747783 | BVP353 48LED 40K 220V L40 30        | No       |
| 911401747823 | BVP353 48LED RGB 220V L40 30 DMX    | Yes      |
| 911401747843 | BVP353 48LED RGBNW 220V L40 30 DMX  | Yes      |
| 911401747873 | BVP353 48LED 40K 220V L40 45        | No       |
| 911401747933 | BVP353 48LED RGBNW 220V L40 45 DMX  | Yes      |

