

UniFlood C Pro

BVP371



Architectural LED floodlight for fixed or dynamic lighting

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Applications

- Bridges, Monuments, Façades
- Landscape
- Parks and Plazas

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°

- Adjustable $\pm 90^\circ$ tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors
- For outdoor use only

Versions

UniFlood C Pro



UniFlood C Pro




UniFlood C Pro



UniFlood C Pro





Dimensional drawing



UniFlood C Pro - 100 W - 4000 K



UniFlood C Pro - 24 W - - K



Driver included	Yes
-----------------	-----

Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass

CE mark	Yes
---------	-----

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50342799	BVP371 12LED 27K 220V 10 24W HE	1,570 lm	2700 K	>80	827 warm white
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	1,440 lm	2700 K	>80	827 warm white
50344199	BVP371 12LED 27K 220V 15 24W HE	1,635 lm	2700 K	>80	827 warm white
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	1,500 lm	2700 K	>80	827 warm white
50346599	BVP371 12LED 27K 220V 30 24W HE	1,855 lm	2700 K	>80	827 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	1,705 lm	2700 K	>80	827 warm white
50348999	BVP371 12LED 27K 220V 45 24W HE	1,390 lm	2700 K	>80	827 warm white
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	1,280 lm	2700 K	>80	827 warm white
50350299	BVP371 12LED 27K 220V 60 24W HE	1,345 lm	2700 K	>80	827 warm white
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	1,235 lm	2700 K	>80	827 warm white
50352699	BVP371 12LED 30K 220V 10 24W HE	1,635 lm	3000 K	>80	830 warm white
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	1,505 lm	3000 K	>80	830 warm white
50354099	BVP371 12LED 30K 220V 15 24W HE	1,705 lm	3000 K	>80	830 warm white
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	1,565 lm	3000 K	>80	830 warm white
50356499	BVP371 12LED 30K 220V 30 24W HE	1,935 lm	3000 K	>80	830 warm white
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	1,780 lm	3000 K	>80	830 warm white
50358899	BVP371 12LED 30K 220V 45 24W HE	1,450 lm	3000 K	>80	830 warm white
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	1,335 lm	3000 K	>80	830 warm white
50360199	BVP371 12LED 30K 220V 60 24W HE	1,405 lm	3000 K	>80	830 warm white
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	1,290 lm	3000 K	>80	830 warm white
50362599	BVP371 12LED 40K 220V 10 24W HE	1,825 lm	4000 K	>80	840 neutral white
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	1,675 lm	4000 K	>80	840 neutral white
50364999	BVP371 12LED 40K 220V 15 24W HE	1,905 lm	4000 K	>80	840 neutral white
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	1,750 lm	4000 K	>80	840 neutral white
50366399	BVP371 12LED 40K 220V 30 24W HE	2,160 lm	4000 K	>80	840 neutral white
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	1,985 lm	4000 K	>80	840 neutral white
50368799	BVP371 12LED 40K 220V 45 24W HE	1,620 lm	4000 K	>80	840 neutral white
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	1,485 lm	4000 K	>80	840 neutral white
50370099	BVP371 12LED 40K 220V 60 24W HE	1,570 lm	4000 K	>80	840 neutral white
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	1,440 lm	4000 K	>80	840 neutral white
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	880 lm	-	N.A.	RGB
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	920 lm	-	N.A.	RGB
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	1,040 lm	-	N.A.	RGB
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	780 lm	-	N.A.	RGB
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	755 lm	-	N.A.	RGB
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	1,090 lm	-	N.A.	RGBW
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	1,140 lm	-	N.A.	RGBW
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	1,290 lm	-	N.A.	RGBW
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	970 lm	-	N.A.	RGBW
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	940 lm	-	N.A.	RGBW
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	1,045 lm	-	N.A.	RGBW
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	1,090 lm	-	N.A.	RGBW
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	1,235 lm	-	N.A.	RGBW
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	925 lm	-	N.A.	RGBW
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	900 lm	-	N.A.	RGBW
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	1,295 lm	-	N.A.	RGB
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	1,350 lm	-	N.A.	RGB

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	1,530 lm	-	N.A.	RGB
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	1,150 lm	-	N.A.	RGB
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	1,110 lm	-	N.A.	RGB
50392299	BVP372 16LED 27K 220V 10 40W HP	2,465 lm	2700 K	>80	827 warm white
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	2,240 lm	2700 K	>80	827 warm white
50394699	BVP372 16LED 27K 220V 15 40W HP	2,570 lm	2700 K	>80	827 warm white
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	2,335 lm	2700 K	>80	827 warm white
50396099	BVP372 16LED 27K 220V 30 40W HP	2,915 lm	2700 K	>80	827 warm white
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	2,650 lm	2700 K	>80	827 warm white
50398499	BVP372 16LED 27K 220V 45 40W HP	2,185 lm	2700 K	>80	827 warm white
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	1,990 lm	2700 K	>80	827 warm white
50400499	BVP372 16LED 27K 220V 60 40W HP	2,115 lm	2700 K	>80	827 warm white
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	1,925 lm	2700 K	>80	827 warm white
50402899	BVP372 16LED 30K 220V 10 40W HP	2,570 lm	3000 K	>80	830 warm white
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	2,340 lm	3000 K	>80	830 warm white
50404299	BVP372 16LED 30K 220V 15 40W HP	2,680 lm	3000 K	>80	830 warm white
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	2,435 lm	3000 K	>80	830 warm white
50406699	BVP372 16LED 30K 220V 30 40W HP	3,040 lm	3000 K	>80	830 warm white
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	2,765 lm	3000 K	>80	830 warm white
50408099	BVP372 16LED 30K 220V 45 40W HP	2,280 lm	3000 K	>80	830 warm white
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	2,075 lm	3000 K	>80	830 warm white
50410399	BVP372 16LED 30K 220V 60 40W HP	2,210 lm	3000 K	>80	830 warm white
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	2,010 lm	3000 K	>80	830 warm white
50412799	BVP372 16LED 40K 220V 10 40W HP	2,870 lm	4000 K	>80	840 neutral white
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	2,610 lm	4000 K	>80	840 neutral white
50414199	BVP372 16LED 40K 220V 15 40W HP	2,990 lm	4000 K	>80	840 neutral white
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	2,720 lm	4000 K	>80	840 neutral white
50416599	BVP372 16LED 40K 220V 30 40W HP	3,395 lm	4000 K	>80	840 neutral white
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	3,085 lm	4000 K	>80	840 neutral white
50418999	BVP372 16LED 40K 220V 45 40W HP	2,545 lm	4000 K	>80	840 neutral white
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	2,315 lm	4000 K	>80	840 neutral white
50420299	BVP372 16LED 40K 220V 60 40W HP	2,465 lm	4000 K	>80	840 neutral white
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	2,240 lm	4000 K	>80	840 neutral white
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	1,580 lm	-	N.A.	RGBW
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	1,650 lm	-	N.A.	RGBW
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	1,870 lm	-	N.A.	RGBW
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	1,400 lm	-	N.A.	RGBW
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	1,360 lm	-	N.A.	RGBW
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	1,515 lm	-	N.A.	RGBW
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	1,575 lm	-	N.A.	RGBW
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	1,790 lm	-	N.A.	RGBW
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	1,340 lm	-	N.A.	RGBW

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	1,300 lm	-	N.A.	RGBW
50432599	BVP372 18LED 27K 220V 10 50W HP	2,945 lm	2700 K	>80	827 warm white
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	2,745 lm	2700 K	>80	827 warm white
50434999	BVP372 18LED 27K 220V 15 50W HP	3,070 lm	2700 K	>80	827 warm white
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	2,860 lm	2700 K	>80	827 warm white
50436399	BVP372 18LED 27K 220V 30 50W HP	3,485 lm	2700 K	>80	827 warm white
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	3,250 lm	2700 K	>80	827 warm white
50438799	BVP372 18LED 27K 220V 45 50W HP	2,615 lm	2700 K	>80	827 warm white
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	2,435 lm	2700 K	>80	827 warm white
50440099	BVP372 18LED 27K 220V 60 50W HP	2,530 lm	2700 K	>80	827 warm white
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	2,360 lm	2700 K	>80	827 warm white
50442499	BVP372 18LED 30K 220V 10 50W HP	3,070 lm	3000 K	>80	830 warm white
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	2,865 lm	3000 K	>80	830 warm white
50444899	BVP372 18LED 30K 220V 15 50W HP	3,200 lm	3000 K	>80	830 warm white
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	2,985 lm	3000 K	>80	830 warm white
50446299	BVP372 18LED 30K 220V 30 50W HP	3,635 lm	3000 K	>80	830 warm white
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	3,390 lm	3000 K	>80	830 warm white
50448699	BVP372 18LED 30K 220V 45 50W HP	2,725 lm	3000 K	>80	830 warm white
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	2,540 lm	3000 K	>80	830 warm white
50450999	BVP372 18LED 30K 220V 60 50W HP	2,640 lm	3000 K	>80	830 warm white
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	2,460 lm	3000 K	>80	830 warm white
50452399	BVP372 18LED 40K 220V 10 50W HP	3,430 lm	4000 K	>80	840 neutral white
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	3,195 lm	4000 K	>80	840 neutral white
50454799	BVP372 18LED 40K 220V 15 50W HP	3,575 lm	4000 K	>80	840 neutral white
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	3,330 lm	4000 K	>80	840 neutral white
50456199	BVP372 18LED 40K 220V 30 50W HP	4,055 lm	4000 K	>80	840 neutral white
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	3,780 lm	4000 K	>80	840 neutral white
50458599	BVP372 18LED 40K 220V 45 50W HP	3,040 lm	4000 K	>80	840 neutral white
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	2,835 lm	4000 K	>80	840 neutral white
50460899	BVP372 18LED 40K 220V 60 50W HP	2,945 lm	4000 K	>80	840 neutral white
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	2,745 lm	4000 K	>80	840 neutral white
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	1,570 lm	-	N.A.	RGB
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	1,635 lm	-	N.A.	RGB
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	1,855 lm	-	N.A.	RGB
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	1,390 lm	-	N.A.	RGB
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	1,345 lm	-	N.A.	RGB
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	2,140 lm	-	N.A.	RGBW
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	2,230 lm	-	N.A.	RGBW
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	2,530 lm	-	N.A.	RGBW
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	1,895 lm	-	N.A.	RGBW
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	1,835 lm	-	N.A.	RGBW
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	2,045 lm	-	N.A.	RGBW

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	2,130 lm	-	N.A.	RGBW
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	2,420 lm	-	N.A.	RGBW
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	1,815 lm	-	N.A.	RGBW
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	1,755 lm	-	N.A.	RGBW
50477699	BVP373 30LED 27K 220V 10 80W HP	4,945 lm	2700 K	>80	827 warm white
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	4,640 lm	2700 K	>80	827 warm white
50479099	BVP373 30LED 27K 220V 15 80W HP	5,155 lm	2700 K	>80	827 warm white
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	4,835 lm	2700 K	>80	827 warm white
50481399	BVP373 30LED 27K 220V 30 80W HP	5,850 lm	2700 K	>80	827 warm white
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	5,490 lm	2700 K	>80	827 warm white
50483799	BVP373 30LED 27K 220V 45 80W HP	4,385 lm	2700 K	>80	827 warm white
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	4,115 lm	2700 K	>80	827 warm white
50485199	BVP373 30LED 27K 220V 60 80W HP	4,250 lm	2700 K	>80	827 warm white
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	3,985 lm	2700 K	>80	827 warm white
50487599	BVP373 30LED 30K 220V 10 80W HP	5,160 lm	3000 K	>80	830 warm white
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	4,840 lm	3000 K	>80	830 warm white
50489999	BVP373 30LED 30K 220V 15 80W HP	5,375 lm	3000 K	>80	830 warm white
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	5,045 lm	3000 K	>80	830 warm white
50491299	BVP373 30LED 30K 220V 30 80W HP	6,100 lm	3000 K	>80	830 warm white
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	5,725 lm	3000 K	>80	830 warm white
50493699	BVP373 30LED 30K 220V 45 80W HP	4,575 lm	3000 K	>80	830 warm white
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	4,295 lm	3000 K	>80	830 warm white
50495099	BVP373 30LED 30K 220V 60 80W HP	4,430 lm	3000 K	>80	830 warm white
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	4,155 lm	3000 K	>80	830 warm white
50497499	BVP373 30LED 40K 220V 10 80W HP	5,755 lm	4000 K	>80	840 neutral white
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	5,400 lm	4000 K	>80	840 neutral white
50499899	BVP373 30LED 40K 220V 15 80W HP	6,000 lm	4000 K	>80	840 neutral white
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	5,625 lm	4000 K	>80	840 neutral white
50501899	BVP373 30LED 40K 220V 30 80W HP	6,810 lm	4000 K	>80	840 neutral white
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	6,385 lm	4000 K	>80	840 neutral white
50503299	BVP373 30LED 40K 220V 45 80W HP	5,105 lm	4000 K	>80	840 neutral white
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	4,790 lm	4000 K	>80	840 neutral white
50505699	BVP373 30LED 40K 220V 60 80W HP	4,945 lm	4000 K	>80	840 neutral white
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	4,640 lm	4000 K	>80	840 neutral white
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	2,695 lm	-	N.A.	RGB
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	2,810 lm	-	N.A.	RGB
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	3,190 lm	-	N.A.	RGB
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	2,390 lm	-	N.A.	RGB
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	2,315 lm	-	N.A.	RGB
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	3,520 lm	-	N.A.	RGBW
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	3,670 lm	-	N.A.	RGBW
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	4,170 lm	-	N.A.	RGBW

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	3,125 lm	-	N.A.	RGBW
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	3,025 lm	-	N.A.	RGBW
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	3,370 lm	-	N.A.	RGBW
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	3,515 lm	-	N.A.	RGBW
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	3,990 lm	-	N.A.	RGBW
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	2,990 lm	-	N.A.	RGBW
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	2,895 lm	-	N.A.	RGBW
50522399	BVP373 36LED 27K 220V 10 100W HP	6,175 lm	2700 K	>80	827 warm white
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	5,720 lm	2700 K	>80	827 warm white
50524799	BVP373 36LED 27K 220V 15 100W HP	6,440 lm	2700 K	>80	827 warm white
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	5,965 lm	2700 K	>80	827 warm white
50526199	BVP373 36LED 27K 220V 30 100W HP	7,310 lm	2700 K	>80	827 warm white
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	6,770 lm	2700 K	>80	827 warm white
50528599	BVP373 36LED 27K 220V 45 100W HP	5,480 lm	2700 K	>80	827 warm white
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	5,075 lm	2700 K	>80	827 warm white
50530899	BVP373 36LED 27K 220V 60 100W HP	5,305 lm	2700 K	>80	827 warm white
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	4,915 lm	2700 K	>80	827 warm white
50532299	BVP373 36LED 30K 220V 10 100W HP	6,445 lm	3000 K	>80	830 warm white
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	5,970 lm	3000 K	>80	830 warm white
50534699	BVP373 36LED 30K 220V 15 100W HP	6,715 lm	3000 K	>80	830 warm white
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	6,220 lm	3000 K	>80	830 warm white
50536099	BVP373 36LED 30K 220V 30 100W HP	7,625 lm	3000 K	>80	830 warm white
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	7,060 lm	3000 K	>80	830 warm white
50538499	BVP373 36LED 30K 220V 45 100W HP	5,715 lm	3000 K	>80	830 warm white
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	5,295 lm	3000 K	>80	830 warm white
50540799	BVP373 36LED 30K 220V 60 100W HP	5,535 lm	3000 K	>80	830 warm white
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	5,125 lm	3000 K	>80	830 warm white
50542199	BVP373 36LED 40K 220V 10 100W HP	7,190 lm	4000 K	>80	840 neutral white
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	6,660 lm	4000 K	>80	840 neutral white
50544599	BVP373 36LED 40K 220V 15 100W HP	7,495 lm	4000 K	>80	840 neutral white
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	6,940 lm	4000 K	>80	840 neutral white
50546999	BVP373 36LED 40K 220V 30 100W HP	8,505 lm	4000 K	>80	840 neutral white
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	7,880 lm	4000 K	>80	840 neutral white
50548399	BVP373 36LED 40K 220V 45 100W HP	6,380 lm	4000 K	>80	840 neutral white
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	5,910 lm	4000 K	>80	840 neutral white
50550699	BVP373 36LED 40K 220V 60 100W HP	6,175 lm	4000 K	>80	840 neutral white
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	5,720 lm	4000 K	>80	840 neutral white
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	3,300 lm	-	N.A.	RGB
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	3,440 lm	-	N.A.	RGB
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	3,905 lm	-	N.A.	RGB
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	2,930 lm	-	N.A.	RGB
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	2,835 lm	-	N.A.	RGB

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	4,175 lm	-	N.A.	RGBW
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	4,355 lm	-	N.A.	RGBW
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	4,945 lm	-	N.A.	RGBW
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	3,705 lm	-	N.A.	RGBW
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	3,590 lm	-	N.A.	RGBW
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	3,995 lm	-	N.A.	RGBW
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	4,165 lm	-	N.A.	RGBW
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	4,730 lm	-	N.A.	RGBW
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	3,545 lm	-	N.A.	RGBW
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	3,435 lm	-	N.A.	RGBW
50567499	BVP374 48LED 27K 220V 10 120W HP	7,540 lm	2700 K	>80	827 warm white
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	7,040 lm	2700 K	>80	827 warm white
50569899	BVP374 48LED 27K 220V 15 120W HP	7,855 lm	2700 K	>80	827 warm white
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	7,340 lm	2700 K	>80	827 warm white
50571199	BVP374 48LED 27K 220V 30 120W HP	8,920 lm	2700 K	>80	827 warm white
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	8,330 lm	2700 K	>80	827 warm white
50573599	BVP374 48LED 27K 220V 45 120W HP	6,690 lm	2700 K	>80	827 warm white
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	6,245 lm	2700 K	>80	827 warm white
50575999	BVP374 48LED 27K 220V 60 120W HP	6,475 lm	2700 K	>80	827 warm white
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	6,050 lm	2700 K	>80	827 warm white
50577399	BVP374 48LED 30K 220V 10 120W HP	7,865 lm	3000 K	>80	830 warm white
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	7,345 lm	3000 K	>80	830 warm white
50579799	BVP374 48LED 30K 220V 15 120W HP	8,195 lm	3000 K	>80	830 warm white
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	7,655 lm	3000 K	>80	830 warm white
50581099	BVP374 48LED 30K 220V 30 120W HP	9,305 lm	3000 K	>80	830 warm white
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	8,690 lm	3000 K	>80	830 warm white
50583499	BVP374 48LED 30K 220V 45 120W HP	6,975 lm	3000 K	>80	830 warm white
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	6,515 lm	3000 K	>80	830 warm white
50585899	BVP374 48LED 30K 220V 60 120W HP	6,755 lm	3000 K	>80	830 warm white
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	6,310 lm	3000 K	>80	830 warm white
50587299	BVP374 48LED 40K 220V 10 120W HP	8,775 lm	4000 K	>80	840 neutral white
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	8,195 lm	4000 K	>80	840 neutral white
50589699	BVP374 48LED 40K 220V 15 120W HP	9,145 lm	4000 K	>80	840 neutral white
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	8,540 lm	4000 K	>80	840 neutral white
50591999	BVP374 48LED 40K 220V 30 120W HP	10,380 lm	4000 K	>80	840 neutral white
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	9,695 lm	4000 K	>80	840 neutral white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50593399	BVP374 48LED 40K 220V 45 120W HP	7,785 lm	4000 K	>80	840 neutral white
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	7,270 lm	4000 K	>80	840 neutral white
50595799	BVP374 48LED 40K 220V 60 120W HP	7,535 lm	4000 K	>80	840 neutral white
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	7,040 lm	4000 K	>80	840 neutral white
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	4,035 lm	-	N.A.	RGB
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	4,205 lm	-	N.A.	RGB
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	4,775 lm	-	N.A.	RGB
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	3,580 lm	-	N.A.	RGB
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	3,465 lm	-	N.A.	RGB
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	5,165 lm	-	N.A.	RGBW
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	5,380 lm	-	N.A.	RGBW
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	6,110 lm	-	N.A.	RGBW
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	4,580 lm	-	N.A.	RGBW
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	4,435 lm	-	N.A.	RGBW
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	4,940 lm	-	N.A.	RGBW
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	5,150 lm	-	N.A.	RGBW
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	5,845 lm	-	N.A.	RGBW
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	4,385 lm	-	N.A.	RGBW
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	4,245 lm	-	N.A.	RGBW
50612199	BVP374 60LED 27K 220V 10 150W HP	9,425 lm	2700 K	>80	827 warm white
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	9,065 lm	2700 K	>80	827 warm white
50614599	BVP374 60LED 27K 220V 15 150W HP	9,820 lm	2700 K	>80	827 warm white
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	9,450 lm	2700 K	>80	827 warm white
50616999	BVP374 60LED 27K 220V 30 150W HP	11,150 lm	2700 K	>80	827 warm white
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	10,725 lm	2700 K	>80	827 warm white
50618399	BVP374 60LED 27K 220V 45 150W HP	8,360 lm	2700 K	>80	827 warm white
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	8,045 lm	2700 K	>80	827 warm white
50620699	BVP374 60LED 27K 220V 60 150W HP	8,095 lm	2700 K	>80	827 warm white
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	7,790 lm	2700 K	>80	827 warm white
50622099	BVP374 60LED 30K 220V 10 150W HP	9,830 lm	3000 K	>80	830 warm white
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	9,455 lm	3000 K	>80	830 warm white
50624499	BVP374 60LED 30K 220V 15 150W HP	10,245 lm	3000 K	>80	830 warm white
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	9,855 lm	3000 K	>80	830 warm white
50626899	BVP374 60LED 30K 220V 30 150W HP	11,630 lm	3000 K	>80	830 warm white
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	11,190 lm	3000 K	>80	830 warm white
50628299	BVP374 60LED 30K 220V 45 150W HP	8,720 lm	3000 K	>80	830 warm white

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	8,390 lm	3000 K	>80	830 warm white
50630599	BVP374 60LED 30K 220V 60 150W HP	8,445 lm	3000 K	>80	830 warm white
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	8,125 lm	3000 K	>80	830 warm white
50632999	BVP374 60LED 40K 220V 10 150W HP	10,965 lm	4000 K	>80	840 neutral white
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	10,550 lm	4000 K	>80	840 neutral white
50634399	BVP374 60LED 40K 220V 15 150W HP	11,430 lm	4000 K	>80	840 neutral white
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	10,995 lm	4000 K	>80	840 neutral white
50636799	BVP374 60LED 40K 220V 30 150W HP	12,975 lm	4000 K	>80	840 neutral white
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	12,485 lm	4000 K	>80	840 neutral white
50638199	BVP374 60LED 40K 220V 45 150W HP	9,730 lm	4000 K	>80	840 neutral white
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	9,360 lm	4000 K	>80	840 neutral white
50640499	BVP374 60LED 40K 220V 60 150W HP	9,420 lm	4000 K	>80	840 neutral white
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	9,065 lm	4000 K	>80	840 neutral white
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	5,185 lm	-	N.A.	RGB
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	5,405 lm	-	N.A.	RGB
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	6,135 lm	-	N.A.	RGB
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	4,600 lm	-	N.A.	RGB
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	4,455 lm	-	N.A.	RGB
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	6,635 lm	-	N.A.	RGBW
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	6,920 lm	-	N.A.	RGBW
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	7,855 lm	-	N.A.	RGBW
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	5,890 lm	-	N.A.	RGBW
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	5,700 lm	-	N.A.	RGBW
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	6,370 lm	-	N.A.	RGBW
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	6,640 lm	-	N.A.	RGBW
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	7,535 lm	-	N.A.	RGBW
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	5,650 lm	-	N.A.	RGBW
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	5,470 lm	-	N.A.	RGBW

Operating and Electrical

Order Code	Full Product Name	Power Consumption
50342799	BVP371 12LED 27K 220V 10 24W HE	24 W
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	24 W
50344199	BVP371 12LED 27K 220V 15 24W HE	24 W

Order Code	Full Product Name	Power Consumption
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	24 W
50346599	BVP371 12LED 27K 220V 30 24W HE	24 W
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	24 W
50348999	BVP371 12LED 27K 220V 45 24W HE	24 W
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	24 W
50350299	BVP371 12LED 27K 220V 60 24W HE	24 W
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	24 W
50352699	BVP371 12LED 30K 220V 10 24W HE	24 W
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	24 W
50354099	BVP371 12LED 30K 220V 15 24W HE	24 W
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	24 W
50356499	BVP371 12LED 30K 220V 30 24W HE	24 W
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	24 W
50358899	BVP371 12LED 30K 220V 45 24W HE	24 W
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	24 W
50360199	BVP371 12LED 30K 220V 60 24W HE	24 W
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	24 W
50362599	BVP371 12LED 40K 220V 10 24W HE	24 W
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	24 W
50364999	BVP371 12LED 40K 220V 15 24W HE	24 W
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	24 W
50366399	BVP371 12LED 40K 220V 30 24W HE	24 W
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	24 W
50368799	BVP371 12LED 40K 220V 45 24W HE	24 W
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	24 W
50370099	BVP371 12LED 40K 220V 60 24W HE	24 W
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	24 W
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	24 W
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	24 W
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	24 W
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	24 W
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	24 W
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	24 W
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	24 W
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	24 W
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	24 W
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	24 W
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	24 W
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	24 W
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	24 W
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	24 W
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	24 W

Order Code	Full Product Name	Power Consumption
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	40 W
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	40 W
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	40 W
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	40 W
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	40 W
50392299	BVP372 16LED 27K 220V 10 40W HP	40 W
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	40 W
50394699	BVP372 16LED 27K 220V 15 40W HP	40 W
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	40 W
50396099	BVP372 16LED 27K 220V 30 40W HP	40 W
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	40 W
50398499	BVP372 16LED 27K 220V 45 40W HP	40 W
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	40 W
50400499	BVP372 16LED 27K 220V 60 40W HP	40 W
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	40 W
50402899	BVP372 16LED 30K 220V 10 40W HP	40 W
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	40 W
50404299	BVP372 16LED 30K 220V 15 40W HP	40 W
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	40 W
50406699	BVP372 16LED 30K 220V 30 40W HP	40 W
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	40 W
50408099	BVP372 16LED 30K 220V 45 40W HP	40 W
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	40 W
50410399	BVP372 16LED 30K 220V 60 40W HP	40 W
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	40 W
50412799	BVP372 16LED 40K 220V 10 40W HP	40 W
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	40 W
50414199	BVP372 16LED 40K 220V 15 40W HP	40 W
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	40 W
50416599	BVP372 16LED 40K 220V 30 40W HP	40 W
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	40 W
50418999	BVP372 16LED 40K 220V 45 40W HP	40 W
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	40 W
50420299	BVP372 16LED 40K 220V 60 40W HP	40 W
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	40 W
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	40 W
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	40 W
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	40 W
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	40 W
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	40 W
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	40 W
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	40 W

Order Code	Full Product Name	Power Consumption
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	40 W
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	40 W
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	40 W
50432599	BVP372 18LED 27K 220V 10 50W HP	50 W
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	50 W
50434999	BVP372 18LED 27K 220V 15 50W HP	50 W
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	50 W
50436399	BVP372 18LED 27K 220V 30 50W HP	50 W
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	50 W
50438799	BVP372 18LED 27K 220V 45 50W HP	50 W
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	50 W
50440099	BVP372 18LED 27K 220V 60 50W HP	50 W
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	50 W
50442499	BVP372 18LED 30K 220V 10 50W HP	50 W
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	50 W
50444899	BVP372 18LED 30K 220V 15 50W HP	50 W
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	50 W
50446299	BVP372 18LED 30K 220V 30 50W HP	50 W
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	50 W
50448699	BVP372 18LED 30K 220V 45 50W HP	50 W
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	50 W
50450999	BVP372 18LED 30K 220V 60 50W HP	50 W
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	50 W
50452399	BVP372 18LED 40K 220V 10 50W HP	50 W
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	50 W
50454799	BVP372 18LED 40K 220V 15 50W HP	50 W
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	50 W
50456199	BVP372 18LED 40K 220V 30 50W HP	50 W
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	50 W
50458599	BVP372 18LED 40K 220V 45 50W HP	50 W
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	50 W
50460899	BVP372 18LED 40K 220V 60 50W HP	50 W
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	50 W
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	50 W
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	50 W
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	50 W
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	50 W
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	50 W
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	50 W
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	50 W
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	50 W

Order Code	Full Product Name	Power Consumption
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	50 W
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	50 W
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	50 W
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	50 W
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	50 W
50477699	BVP373 30LED 27K 220V 10 80W HP	80 W
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	80 W
50479099	BVP373 30LED 27K 220V 15 80W HP	80 W
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	80 W
50481399	BVP373 30LED 27K 220V 30 80W HP	80 W
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	80 W
50483799	BVP373 30LED 27K 220V 45 80W HP	80 W
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	80 W
50485199	BVP373 30LED 27K 220V 60 80W HP	80 W
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	80 W
50487599	BVP373 30LED 30K 220V 10 80W HP	80 W
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	80 W
50489999	BVP373 30LED 30K 220V 15 80W HP	80 W
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	80 W
50491299	BVP373 30LED 30K 220V 30 80W HP	80 W
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	80 W
50493699	BVP373 30LED 30K 220V 45 80W HP	80 W
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	80 W
50495099	BVP373 30LED 30K 220V 60 80W HP	80 W
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	80 W
50497499	BVP373 30LED 40K 220V 10 80W HP	80 W
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	80 W
50499899	BVP373 30LED 40K 220V 15 80W HP	80 W
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	80 W
50501899	BVP373 30LED 40K 220V 30 80W HP	80 W
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	80 W
50503299	BVP373 30LED 40K 220V 45 80W HP	80 W
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	80 W
50505699	BVP373 30LED 40K 220V 60 80W HP	80 W
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	80 W
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	80 W
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	80 W
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	80 W
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	80 W
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	80 W
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	80 W

Order Code	Full Product Name	Power Consumption
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	80 W
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	80 W
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	80 W
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	80 W
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	80 W
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	80 W
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	80 W
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	80 W
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	80 W
50522399	BVP373 36LED 27K 220V 10 100W HP	100 W
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	100 W
50524799	BVP373 36LED 27K 220V 15 100W HP	100 W
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	100 W
50526199	BVP373 36LED 27K 220V 30 100W HP	100 W
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	100 W
50528599	BVP373 36LED 27K 220V 45 100W HP	100 W
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	100 W
50530899	BVP373 36LED 27K 220V 60 100W HP	100 W
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	100 W
50532299	BVP373 36LED 30K 220V 10 100W HP	100 W
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	100 W
50534699	BVP373 36LED 30K 220V 15 100W HP	100 W
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	100 W
50536099	BVP373 36LED 30K 220V 30 100W HP	100 W
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	100 W
50538499	BVP373 36LED 30K 220V 45 100W HP	100 W
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	100 W
50540799	BVP373 36LED 30K 220V 60 100W HP	100 W
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	100 W
50542199	BVP373 36LED 40K 220V 10 100W HP	100 W
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	100 W
50544599	BVP373 36LED 40K 220V 15 100W HP	100 W
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	100 W
50546999	BVP373 36LED 40K 220V 30 100W HP	100 W
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	100 W
50548399	BVP373 36LED 40K 220V 45 100W HP	100 W
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	100 W
50550699	BVP373 36LED 40K 220V 60 100W HP	100 W
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	100 W
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	100 W
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	100 W
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	100 W

Order Code	Full Product Name	Power Consumption
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	100 W
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	100 W
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	100 W
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	100 W
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	100 W
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	100 W
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	100 W
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	100 W
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	100 W
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	100 W
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	100 W
50567499	BVP374 48LED 27K 220V 10 120W HP	120 W
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	120 W
50569899	BVP374 48LED 27K 220V 15 120W HP	120 W
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	120 W
50571199	BVP374 48LED 27K 220V 30 120W HP	120 W
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	120 W
50573599	BVP374 48LED 27K 220V 45 120W HP	120 W
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	120 W
50575999	BVP374 48LED 27K 220V 60 120W HP	120 W
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	120 W
50577399	BVP374 48LED 30K 220V 10 120W HP	120 W
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	120 W
50579799	BVP374 48LED 30K 220V 15 120W HP	120 W
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	120 W
50581099	BVP374 48LED 30K 220V 30 120W HP	120 W
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	120 W
50583499	BVP374 48LED 30K 220V 45 120W HP	120 W
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	120 W
50585899	BVP374 48LED 30K 220V 60 120W HP	120 W
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	120 W
50587299	BVP374 48LED 40K 220V 10 120W HP	120 W
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	120 W
50589699	BVP374 48LED 40K 220V 15 120W HP	120 W
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	120 W
50591999	BVP374 48LED 40K 220V 30 120W HP	120 W
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	120 W
50593399	BVP374 48LED 40K 220V 45 120W HP	120 W
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	120 W
50595799	BVP374 48LED 40K 220V 60 120W HP	120 W
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	120 W

Order Code	Full Product Name	Power Consumption
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	120 W
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	120 W
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	120 W
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	120 W
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	120 W
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	120 W
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	120 W
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	120 W
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	120 W
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	120 W
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	120 W
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	120 W
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	120 W
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	120 W
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	120 W
50612199	BVP374 60LED 27K 220V 10 150W HP	150 W
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	150 W
50614599	BVP374 60LED 27K 220V 15 150W HP	150 W
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	150 W
50616999	BVP374 60LED 27K 220V 30 150W HP	150 W
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	150 W
50618399	BVP374 60LED 27K 220V 45 150W HP	150 W
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	150 W
50620699	BVP374 60LED 27K 220V 60 150W HP	150 W
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	150 W
50622099	BVP374 60LED 30K 220V 10 150W HP	150 W
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	150 W
50624499	BVP374 60LED 30K 220V 15 150W HP	150 W
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	150 W
50626899	BVP374 60LED 30K 220V 30 150W HP	150 W
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	150 W
50628299	BVP374 60LED 30K 220V 45 150W HP	150 W
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	150 W
50630599	BVP374 60LED 30K 220V 60 150W HP	150 W
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	150 W
50632999	BVP374 60LED 40K 220V 10 150W HP	150 W
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	150 W
50634399	BVP374 60LED 40K 220V 15 150W HP	150 W
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	150 W
50636799	BVP374 60LED 40K 220V 30 150W HP	150 W
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	150 W
50638199	BVP374 60LED 40K 220V 45 150W HP	150 W

Order Code	Full Product Name	Power Consumption
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	150 W
50640499	BVP374 60LED 40K 220V 60 150W HP	150 W
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	150 W
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	150 W
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	150 W
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	150 W
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	150 W
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	150 W
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	150 W
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	150 W
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	150 W
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	150 W
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	150 W
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	150 W
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	150 W
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	150 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
50342799	BVP371 12LED 27K 220V 10 24W HE	No
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	Yes
50344199	BVP371 12LED 27K 220V 15 24W HE	No
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	Yes
50346599	BVP371 12LED 27K 220V 30 24W HE	No
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	Yes
50348999	BVP371 12LED 27K 220V 45 24W HE	No
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	Yes
50350299	BVP371 12LED 27K 220V 60 24W HE	No
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	Yes
50352699	BVP371 12LED 30K 220V 10 24W HE	No
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	Yes
50354099	BVP371 12LED 30K 220V 15 24W HE	No
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	Yes
50356499	BVP371 12LED 30K 220V 30 24W HE	No
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	Yes
50358899	BVP371 12LED 30K 220V 45 24W HE	No
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	Yes
50360199	BVP371 12LED 30K 220V 60 24W HE	No
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	Yes
50362599	BVP371 12LED 40K 220V 10 24W HE	No

Order Code	Full Product Name	Dimmable
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	Yes
50364999	BVP371 12LED 40K 220V 15 24W HE	No
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	Yes
50366399	BVP371 12LED 40K 220V 30 24W HE	No
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	Yes
50368799	BVP371 12LED 40K 220V 45 24W HE	No
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	Yes
50370099	BVP371 12LED 40K 220V 60 24W HE	No
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	Yes
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	Yes
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	Yes
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	Yes
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	Yes
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	Yes
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	Yes
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	Yes
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	Yes
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	Yes
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	Yes
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	Yes
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	Yes
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	Yes
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	Yes
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	Yes
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	Yes
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	Yes
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	Yes
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	Yes
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	Yes
50392299	BVP372 16LED 27K 220V 10 40W HP	No
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	Yes
50394699	BVP372 16LED 27K 220V 15 40W HP	No
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	Yes
50396099	BVP372 16LED 27K 220V 30 40W HP	No
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	Yes
50398499	BVP372 16LED 27K 220V 45 40W HP	No
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	Yes
50400499	BVP372 16LED 27K 220V 60 40W HP	No
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	Yes
50402899	BVP372 16LED 30K 220V 10 40W HP	No
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	Yes
50404299	BVP372 16LED 30K 220V 15 40W HP	No

Order Code	Full Product Name	Dimmable
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	Yes
50406699	BVP372 16LED 30K 220V 30 40W HP	No
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	Yes
50408099	BVP372 16LED 30K 220V 45 40W HP	No
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	Yes
50410399	BVP372 16LED 30K 220V 60 40W HP	No
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	Yes
50412799	BVP372 16LED 40K 220V 10 40W HP	No
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	Yes
50414199	BVP372 16LED 40K 220V 15 40W HP	No
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	Yes
50416599	BVP372 16LED 40K 220V 30 40W HP	No
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	Yes
50418999	BVP372 16LED 40K 220V 45 40W HP	No
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	Yes
50420299	BVP372 16LED 40K 220V 60 40W HP	No
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	Yes
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	Yes
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	Yes
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	Yes
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	Yes
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	Yes
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	Yes
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	Yes
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	Yes
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	Yes
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	Yes
50432599	BVP372 18LED 27K 220V 10 50W HP	No
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	Yes
50434999	BVP372 18LED 27K 220V 15 50W HP	No
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	Yes
50436399	BVP372 18LED 27K 220V 30 50W HP	No
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	Yes
50438799	BVP372 18LED 27K 220V 45 50W HP	No
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	Yes
50440099	BVP372 18LED 27K 220V 60 50W HP	No
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	Yes
50442499	BVP372 18LED 30K 220V 10 50W HP	No
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	Yes
50444899	BVP372 18LED 30K 220V 15 50W HP	No
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	Yes
50446299	BVP372 18LED 30K 220V 30 50W HP	No

Order Code	Full Product Name	Dimmable
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	Yes
50448699	BVP372 18LED 30K 220V 45 50W HP	No
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	Yes
50450999	BVP372 18LED 30K 220V 60 50W HP	No
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	Yes
50452399	BVP372 18LED 40K 220V 10 50W HP	No
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	Yes
50454799	BVP372 18LED 40K 220V 15 50W HP	No
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	Yes
50456199	BVP372 18LED 40K 220V 30 50W HP	No
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	Yes
50458599	BVP372 18LED 40K 220V 45 50W HP	No
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	Yes
50460899	BVP372 18LED 40K 220V 60 50W HP	No
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	Yes
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	Yes
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	Yes
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	Yes
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	Yes
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	Yes
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	Yes
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	Yes
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	Yes
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	Yes
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	Yes
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	Yes
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	Yes
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	Yes
50477699	BVP373 30LED 27K 220V 10 80W HP	No
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	Yes
50479099	BVP373 30LED 27K 220V 15 80W HP	No
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	Yes
50481399	BVP373 30LED 27K 220V 30 80W HP	No
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	Yes
50483799	BVP373 30LED 27K 220V 45 80W HP	No
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	Yes
50485199	BVP373 30LED 27K 220V 60 80W HP	No
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	Yes
50487599	BVP373 30LED 30K 220V 10 80W HP	No
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	Yes

Order Code	Full Product Name	Dimmable
50489999	BVP373 30LED 30K 220V 15 80W HP	No
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	Yes
50491299	BVP373 30LED 30K 220V 30 80W HP	No
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	Yes
50493699	BVP373 30LED 30K 220V 45 80W HP	No
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	Yes
50495099	BVP373 30LED 30K 220V 60 80W HP	No
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	Yes
50497499	BVP373 30LED 40K 220V 10 80W HP	No
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	Yes
50499899	BVP373 30LED 40K 220V 15 80W HP	No
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	Yes
50501899	BVP373 30LED 40K 220V 30 80W HP	No
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	Yes
50503299	BVP373 30LED 40K 220V 45 80W HP	No
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	Yes
50505699	BVP373 30LED 40K 220V 60 80W HP	No
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	Yes
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	Yes
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	Yes
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	Yes
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	Yes
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	Yes
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	Yes
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	Yes
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	Yes
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	Yes
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	Yes
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	Yes
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	Yes
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	Yes
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	Yes
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	Yes
50522399	BVP373 36LED 27K 220V 10 100W HP	No
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	Yes
50524799	BVP373 36LED 27K 220V 15 100W HP	No
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	Yes
50526199	BVP373 36LED 27K 220V 30 100W HP	No
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	Yes
50528599	BVP373 36LED 27K 220V 45 100W HP	No
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	Yes
50530899	BVP373 36LED 27K 220V 60 100W HP	No

Order Code	Full Product Name	Dimmable
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	Yes
50532299	BVP373 36LED 30K 220V 10 100W HP	No
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	Yes
50534699	BVP373 36LED 30K 220V 15 100W HP	No
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	Yes
50536099	BVP373 36LED 30K 220V 30 100W HP	No
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	Yes
50538499	BVP373 36LED 30K 220V 45 100W HP	No
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	Yes
50540799	BVP373 36LED 30K 220V 60 100W HP	No
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	Yes
50542199	BVP373 36LED 40K 220V 10 100W HP	No
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	Yes
50544599	BVP373 36LED 40K 220V 15 100W HP	No
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	Yes
50546999	BVP373 36LED 40K 220V 30 100W HP	No
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	Yes
50548399	BVP373 36LED 40K 220V 45 100W HP	No
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	Yes
50550699	BVP373 36LED 40K 220V 60 100W HP	No
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	Yes
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	Yes
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	Yes
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	Yes
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	Yes
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	Yes
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	Yes
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	Yes
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	Yes
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	Yes
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	Yes
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	Yes
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	Yes
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	Yes
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	Yes
50567499	BVP374 48LED 27K 220V 10 120W HP	No
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	Yes
50569899	BVP374 48LED 27K 220V 15 120W HP	No
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	Yes
50571199	BVP374 48LED 27K 220V 30 120W HP	No
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	Yes

Order Code	Full Product Name	Dimmable
50573599	BVP374 48LED 27K 220V 45 120W HP	No
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	Yes
50575999	BVP374 48LED 27K 220V 60 120W HP	No
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	Yes
50577399	BVP374 48LED 30K 220V 10 120W HP	No
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	Yes
50579799	BVP374 48LED 30K 220V 15 120W HP	No
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	Yes
50581099	BVP374 48LED 30K 220V 30 120W HP	No
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	Yes
50583499	BVP374 48LED 30K 220V 45 120W HP	No
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	Yes
50585899	BVP374 48LED 30K 220V 60 120W HP	No
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	Yes
50587299	BVP374 48LED 40K 220V 10 120W HP	No
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	Yes
50589699	BVP374 48LED 40K 220V 15 120W HP	No
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	Yes
50591999	BVP374 48LED 40K 220V 30 120W HP	No
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	Yes
50593399	BVP374 48LED 40K 220V 45 120W HP	No
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	Yes
50595799	BVP374 48LED 40K 220V 60 120W HP	No
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	Yes
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	Yes
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	Yes
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	Yes
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	Yes
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	Yes
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	Yes
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	Yes
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	Yes
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	Yes
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	Yes
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	Yes
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	Yes
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	Yes
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	Yes
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	Yes
50612199	BVP374 60LED 27K 220V 10 150W HP	No
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	Yes
50614599	BVP374 60LED 27K 220V 15 150W HP	No

Order Code	Full Product Name	Dimmable
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	Yes
50616999	BVP374 60LED 27K 220V 30 150W HP	No
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	Yes
50618399	BVP374 60LED 27K 220V 45 150W HP	No
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	Yes
50620699	BVP374 60LED 27K 220V 60 150W HP	No
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	Yes
50622099	BVP374 60LED 30K 220V 10 150W HP	No
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	Yes
50624499	BVP374 60LED 30K 220V 15 150W HP	No
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	Yes
50626899	BVP374 60LED 30K 220V 30 150W HP	No
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	Yes
50628299	BVP374 60LED 30K 220V 45 150W HP	No
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	Yes
50630599	BVP374 60LED 30K 220V 60 150W HP	No
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	Yes
50632999	BVP374 60LED 40K 220V 10 150W HP	No
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	Yes
50634399	BVP374 60LED 40K 220V 15 150W HP	No
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	Yes
50636799	BVP374 60LED 40K 220V 30 150W HP	No
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	Yes
50638199	BVP374 60LED 40K 220V 45 150W HP	No
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	Yes
50640499	BVP374 60LED 40K 220V 60 150W HP	No
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	Yes
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	Yes
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	Yes
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	Yes
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	Yes
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	Yes
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	Yes
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	Yes
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	Yes
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	Yes
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	Yes
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	Yes
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	Yes
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	Yes

