



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro


Application

- Bridges, Monuments, Façades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information	
Driver included	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

Light Technical

UniFlood C Pro

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50342799	BVP371 12LED 27K 220V 10 24W HE	827 warm white	2700 K	>80	1,570 lm
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	827 warm white	2700 K	>80	1,440 lm
50344199	BVP371 12LED 27K 220V 15 24W HE	827 warm white	2700 K	>80	1,635 lm
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	827 warm white	2700 K	>80	1,500 lm
50346599	BVP371 12LED 27K 220V 30 24W HE	827 warm white	2700 K	>80	1,855 lm
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	827 warm white	2700 K	>80	1,705 lm
50348999	BVP371 12LED 27K 220V 45 24W HE	827 warm white	2700 K	>80	1,390 lm
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	827 warm white	2700 K	>80	1,280 lm
50350299	BVP371 12LED 27K 220V 60 24W HE	827 warm white	2700 K	>80	1,345 lm
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	827 warm white	2700 K	>80	1,235 lm
50352699	BVP371 12LED 30K 220V 10 24W HE	830 warm white	3000 K	>80	1,635 lm
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	830 warm white	3000 K	>80	1,505 lm
50354099	BVP371 12LED 30K 220V 15 24W HE	830 warm white	3000 K	>80	1,705 lm
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	830 warm white	3000 K	>80	1,565 lm
50356499	BVP371 12LED 30K 220V 30 24W HE	830 warm white	3000 K	>80	1,935 lm
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	830 warm white	3000 K	>80	1,780 lm
50358899	BVP371 12LED 30K 220V 45 24W HE	830 warm white	3000 K	>80	1,450 lm
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	830 warm white	3000 K	>80	1,335 lm
50360199	BVP371 12LED 30K 220V 60 24W HE	830 warm white	3000 K	>80	1,405 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	830 warm white	3000 K	>80	1,290 lm
50362599	BVP371 12LED 40K 220V 10 24W HE	840 neutral white	4000 K	>80	1,825 lm
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	840 neutral white	4000 K	>80	1,675 lm
50364999	BVP371 12LED 40K 220V 15 24W HE	840 neutral white	4000 K	>80	1,905 lm
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	840 neutral white	4000 K	>80	1,750 lm
50366399	BVP371 12LED 40K 220V 30 24W HE	840 neutral white	4000 K	>80	2,160 lm
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	840 neutral white	4000 K	>80	1,985 lm
50368799	BVP371 12LED 40K 220V 45 24W HE	840 neutral white	4000 K	>80	1,620 lm
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	840 neutral white	4000 K	>80	1,485 lm
50370099	BVP371 12LED 40K 220V 60 24W HE	840 neutral white	4000 K	>80	1,570 lm
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	840 neutral white	4000 K	>80	1,440 lm
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	RGB	-	N.A.	880 lm
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	RGB	-	N.A.	920 lm
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	RGB	-	N.A.	1,040 lm
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	RGB	-	N.A.	780 lm
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	RGB	-	N.A.	755 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,090 lm
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,140 lm
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,290 lm
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	RGBW	-	N.A.	970 lm
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	RGBW	-	N.A.	940 lm
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,045 lm
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,090 lm
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,235 lm
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	RGBW	-	N.A.	925 lm
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	RGBW	-	N.A.	900 lm
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	RGB	-	N.A.	1,295 lm
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	RGB	-	N.A.	1,350 lm
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	RGB	-	N.A.	1,530 lm
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	RGB	-	N.A.	1,150 lm
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	RGB	-	N.A.	1,110 lm
50392299	BVP372 16LED 27K 220V 10 40W HP	827 warm white	2700 K	>80	2,465 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	827 warm white	2700 K	>80	2,240 lm
50394699	BVP372 16LED 27K 220V 15 40W HP	827 warm white	2700 K	>80	2,570 lm
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	827 warm white	2700 K	>80	2,335 lm
50396099	BVP372 16LED 27K 220V 30 40W HP	827 warm white	2700 K	>80	2,915 lm
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	827 warm white	2700 K	>80	2,650 lm
50398499	BVP372 16LED 27K 220V 45 40W HP	827 warm white	2700 K	>80	2,185 lm
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	827 warm white	2700 K	>80	1,990 lm
50400499	BVP372 16LED 27K 220V 60 40W HP	827 warm white	2700 K	>80	2,115 lm
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	827 warm white	2700 K	>80	1,925 lm
50402899	BVP372 16LED 30K 220V 10 40W HP	830 warm white	3000 K	>80	2,570 lm
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	830 warm white	3000 K	>80	2,340 lm
50404299	BVP372 16LED 30K 220V 15 40W HP	830 warm white	3000 K	>80	2,680 lm
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	830 warm white	3000 K	>80	2,435 lm
50406699	BVP372 16LED 30K 220V 30 40W HP	830 warm white	3000 K	>80	3,040 lm
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	830 warm white	3000 K	>80	2,765 lm
50408099	BVP372 16LED 30K 220V 45 40W HP	830 warm white	3000 K	>80	2,280 lm
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	830 warm white	3000 K	>80	2,075 lm
50410399	BVP372 16LED 30K 220V 60 40W HP	830 warm white	3000 K	>80	2,210 lm
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	830 warm white	3000 K	>80	2,010 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50412799	BVP372 16LED 40K 220V 10 40W HP	840 neutral white	4000 K	>80	2,870 lm
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	840 neutral white	4000 K	>80	2,610 lm
50414199	BVP372 16LED 40K 220V 15 40W HP	840 neutral white	4000 K	>80	2,990 lm
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	840 neutral white	4000 K	>80	2,720 lm
50416599	BVP372 16LED 40K 220V 30 40W HP	840 neutral white	4000 K	>80	3,395 lm
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	840 neutral white	4000 K	>80	3,085 lm
50418999	BVP372 16LED 40K 220V 45 40W HP	840 neutral white	4000 K	>80	2,545 lm
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	840 neutral white	4000 K	>80	2,315 lm
50420299	BVP372 16LED 40K 220V 60 40W HP	840 neutral white	4000 K	>80	2,465 lm
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	840 neutral white	4000 K	>80	2,240 lm
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,580 lm
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,650 lm
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,870 lm
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,400 lm
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,360 lm
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,515 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,575 lm
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,790 lm
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,340 lm
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,300 lm
50432599	BVP372 18LED 27K 220V 10 50W HP	827 warm white	2700 K	>80	2,945 lm
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	827 warm white	2700 K	>80	2,745 lm
50434999	BVP372 18LED 27K 220V 15 50W HP	827 warm white	2700 K	>80	3,070 lm
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	827 warm white	2700 K	>80	2,860 lm
50436399	BVP372 18LED 27K 220V 30 50W HP	827 warm white	2700 K	>80	3,485 lm
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	827 warm white	2700 K	>80	3,250 lm
50438799	BVP372 18LED 27K 220V 45 50W HP	827 warm white	2700 K	>80	2,615 lm
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	827 warm white	2700 K	>80	2,435 lm
50440099	BVP372 18LED 27K 220V 60 50W HP	827 warm white	2700 K	>80	2,530 lm
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	827 warm white	2700 K	>80	2,360 lm
50442499	BVP372 18LED 30K 220V 10 50W HP	830 warm white	3000 K	>80	3,070 lm
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	830 warm white	3000 K	>80	2,865 lm
50444899	BVP372 18LED 30K 220V 15 50W HP	830 warm white	3000 K	>80	3,200 lm
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	830 warm white	3000 K	>80	2,985 lm
50446299	BVP372 18LED 30K 220V 30 50W HP	830 warm white	3000 K	>80	3,635 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	830 warm white	3000 K	>80	3,390 lm
50448699	BVP372 18LED 30K 220V 45 50W HP	830 warm white	3000 K	>80	2,725 lm
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	830 warm white	3000 K	>80	2,540 lm
50450999	BVP372 18LED 30K 220V 60 50W HP	830 warm white	3000 K	>80	2,640 lm
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	830 warm white	3000 K	>80	2,460 lm
50452399	BVP372 18LED 40K 220V 10 50W HP	840 neutral white	4000 K	>80	3,430 lm
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	840 neutral white	4000 K	>80	3,195 lm
50454799	BVP372 18LED 40K 220V 15 50W HP	840 neutral white	4000 K	>80	3,575 lm
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	840 neutral white	4000 K	>80	3,330 lm
50456199	BVP372 18LED 40K 220V 30 50W HP	840 neutral white	4000 K	>80	4,055 lm
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	840 neutral white	4000 K	>80	3,780 lm
50458599	BVP372 18LED 40K 220V 45 50W HP	840 neutral white	4000 K	>80	3,040 lm
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	840 neutral white	4000 K	>80	2,835 lm
50460899	BVP372 18LED 40K 220V 60 50W HP	840 neutral white	4000 K	>80	2,945 lm
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	840 neutral white	4000 K	>80	2,745 lm
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	RGB	-	N.A.	1,570 lm
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	RGB	-	N.A.	1,635 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	RGB	-	N.A.	1,855 lm
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	RGB	-	N.A.	1,390 lm
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	RGB	-	N.A.	1,345 lm
50467799	BVP372 20LED RGBW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,140 lm
50468499	BVP372 20LED RGBW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,230 lm
50469199	BVP372 20LED RGBW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,530 lm
50470799	BVP372 20LED RGBW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,895 lm
50471499	BVP372 20LED RGBW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,835 lm
50472199	BVP372 20LED RGBW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,045 lm
50473899	BVP372 20LED RGBW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,130 lm
50474599	BVP372 20LED RGBW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,420 lm
50475299	BVP372 20LED RGBW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,815 lm
50476999	BVP372 20LED RGBW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,755 lm
50477699	BVP373 30LED 27K 220V 10 80W HP	827 warm white	2700 K	>80	4,945 lm
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	827 warm white	2700 K	>80	4,640 lm
50479099	BVP373 30LED 27K 220V 15 80W HP	827 warm white	2700 K	>80	5,155 lm
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	827 warm white	2700 K	>80	4,835 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50481399	BVP373 30LED 27K 220V 30 80W HP	827 warm white	2700 K	>80	5,850 lm
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	827 warm white	2700 K	>80	5,490 lm
50483799	BVP373 30LED 27K 220V 45 80W HP	827 warm white	2700 K	>80	4,385 lm
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	827 warm white	2700 K	>80	4,115 lm
50485199	BVP373 30LED 27K 220V 60 80W HP	827 warm white	2700 K	>80	4,250 lm
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	827 warm white	2700 K	>80	3,985 lm
50487599	BVP373 30LED 30K 220V 10 80W HP	830 warm white	3000 K	>80	5,160 lm
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	830 warm white	3000 K	>80	4,840 lm
50489999	BVP373 30LED 30K 220V 15 80W HP	830 warm white	3000 K	>80	5,375 lm
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	830 warm white	3000 K	>80	5,045 lm
50491299	BVP373 30LED 30K 220V 30 80W HP	830 warm white	3000 K	>80	6,100 lm
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	830 warm white	3000 K	>80	5,725 lm
50493699	BVP373 30LED 30K 220V 45 80W HP	830 warm white	3000 K	>80	4,575 lm
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	830 warm white	3000 K	>80	4,295 lm
50495099	BVP373 30LED 30K 220V 60 80W HP	830 warm white	3000 K	>80	4,430 lm
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	830 warm white	3000 K	>80	4,155 lm
50497499	BVP373 30LED 40K 220V 10 80W HP	840 neutral white	4000 K	>80	5,755 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	840 neutral white	4000 K	>80	5,400 lm
50499899	BVP373 30LED 40K 220V 15 80W HP	840 neutral white	4000 K	>80	6,000 lm
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	840 neutral white	4000 K	>80	5,625 lm
50501899	BVP373 30LED 40K 220V 30 80W HP	840 neutral white	4000 K	>80	6,810 lm
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	840 neutral white	4000 K	>80	6,385 lm
50503299	BVP373 30LED 40K 220V 45 80W HP	840 neutral white	4000 K	>80	5,105 lm
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	840 neutral white	4000 K	>80	4,790 lm
50505699	BVP373 30LED 40K 220V 60 80W HP	840 neutral white	4000 K	>80	4,945 lm
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	840 neutral white	4000 K	>80	4,640 lm
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	RGB	-	N.A.	2,695 lm
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	RGB	-	N.A.	2,810 lm
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	RGB	-	N.A.	3,190 lm
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	RGB	-	N.A.	2,390 lm
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	RGB	-	N.A.	2,315 lm
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,520 lm
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,670 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	RGBW	-	N.A.	4,170 lm
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	RGBW	-	N.A.	3,125 lm
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	RGBW	-	N.A.	3,025 lm
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,370 lm
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,515 lm
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	RGBW	-	N.A.	3,990 lm
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	RGBW	-	N.A.	2,990 lm
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	RGBW	-	N.A.	2,895 lm
50522399	BVP373 36LED 27K 220V 10 100W HP	827 warm white	2700 K	>80	6,175 lm
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	827 warm white	2700 K	>80	5,720 lm
50524799	BVP373 36LED 27K 220V 15 100W HP	827 warm white	2700 K	>80	6,440 lm
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	827 warm white	2700 K	>80	5,965 lm
50526199	BVP373 36LED 27K 220V 30 100W HP	827 warm white	2700 K	>80	7,310 lm
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	827 warm white	2700 K	>80	6,770 lm
50528599	BVP373 36LED 27K 220V 45 100W HP	827 warm white	2700 K	>80	5,480 lm
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	827 warm white	2700 K	>80	5,075 lm
50530899	BVP373 36LED 27K 220V 60 100W HP	827 warm white	2700 K	>80	5,305 lm
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	827 warm white	2700 K	>80	4,915 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50532299	BVP373 36LED 30K 220V 10 100W HP	830 warm white	3000 K	>80	6,445 lm
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	830 warm white	3000 K	>80	5,970 lm
50534699	BVP373 36LED 30K 220V 15 100W HP	830 warm white	3000 K	>80	6,715 lm
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	830 warm white	3000 K	>80	6,220 lm
50536099	BVP373 36LED 30K 220V 30 100W HP	830 warm white	3000 K	>80	7,625 lm
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	830 warm white	3000 K	>80	7,060 lm
50538499	BVP373 36LED 30K 220V 45 100W HP	830 warm white	3000 K	>80	5,715 lm
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	830 warm white	3000 K	>80	5,295 lm
50540799	BVP373 36LED 30K 220V 60 100W HP	830 warm white	3000 K	>80	5,535 lm
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	830 warm white	3000 K	>80	5,125 lm
50542199	BVP373 36LED 40K 220V 10 100W HP	840 neutral white	4000 K	>80	7,190 lm
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	840 neutral white	4000 K	>80	6,660 lm
50544599	BVP373 36LED 40K 220V 15 100W HP	840 neutral white	4000 K	>80	7,495 lm
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	840 neutral white	4000 K	>80	6,940 lm
50546999	BVP373 36LED 40K 220V 30 100W HP	840 neutral white	4000 K	>80	8,505 lm
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	840 neutral white	4000 K	>80	7,880 lm

UniFlood C Pro

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50548399	BVP373 36LED 40K 220V 45 100W HP	840 neutral white	4000 K	>80	6,380 lm
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	840 neutral white	4000 K	>80	5,910 lm
50550699	BVP373 36LED 40K 220V 60 100W HP	840 neutral white	4000 K	>80	6,175 lm
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	840 neutral white	4000 K	>80	5,720 lm
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	RGB	-	N.A.	3,300 lm
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	RGB	-	N.A.	3,440 lm
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	RGB	-	N.A.	3,905 lm
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	RGB	-	N.A.	2,930 lm
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	RGB	-	N.A.	2,835 lm
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	RGBW	-	N.A.	4,175 lm
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,355 lm
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,945 lm
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,705 lm
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,590 lm
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	RGBW	-	N.A.	3,995 lm
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,165 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,730 lm
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,545 lm
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,435 lm
50567499	BVP374 48LED 27K 220V 10 120W HP	827 warm white	2700 K	>80	7,540 lm
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	827 warm white	2700 K	>80	7,040 lm
50569899	BVP374 48LED 27K 220V 15 120W HP	827 warm white	2700 K	>80	7,855 lm
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	827 warm white	2700 K	>80	7,340 lm
50571199	BVP374 48LED 27K 220V 30 120W HP	827 warm white	2700 K	>80	8,920 lm
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	827 warm white	2700 K	>80	8,330 lm
50573599	BVP374 48LED 27K 220V 45 120W HP	827 warm white	2700 K	>80	6,690 lm
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	827 warm white	2700 K	>80	6,245 lm
50575999	BVP374 48LED 27K 220V 60 120W HP	827 warm white	2700 K	>80	6,475 lm
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	827 warm white	2700 K	>80	6,050 lm
50577399	BVP374 48LED 30K 220V 10 120W HP	830 warm white	3000 K	>80	7,865 lm
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	830 warm white	3000 K	>80	7,345 lm
50579799	BVP374 48LED 30K 220V 15 120W HP	830 warm white	3000 K	>80	8,195 lm
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	830 warm white	3000 K	>80	7,655 lm
50581099	BVP374 48LED 30K 220V 30 120W HP	830 warm white	3000 K	>80	9,305 lm

UniFlood C Pro

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	830 warm white	3000 K	>80	8,690 lm
50583499	BVP374 48LED 30K 220V 45 120W HP	830 warm white	3000 K	>80	6,975 lm
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	830 warm white	3000 K	>80	6,515 lm
50585899	BVP374 48LED 30K 220V 60 120W HP	830 warm white	3000 K	>80	6,755 lm
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	830 warm white	3000 K	>80	6,310 lm
50587299	BVP374 48LED 40K 220V 10 120W HP	840 neutral white	4000 K	>80	8,775 lm
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	840 neutral white	4000 K	>80	8,195 lm
50589699	BVP374 48LED 40K 220V 15 120W HP	840 neutral white	4000 K	>80	9,145 lm
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	840 neutral white	4000 K	>80	8,540 lm
50591999	BVP374 48LED 40K 220V 30 120W HP	840 neutral white	4000 K	>80	10,380 lm
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	840 neutral white	4000 K	>80	9,695 lm
50593399	BVP374 48LED 40K 220V 45 120W HP	840 neutral white	4000 K	>80	7,785 lm
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	840 neutral white	4000 K	>80	7,270 lm
50595799	BVP374 48LED 40K 220V 60 120W HP	840 neutral white	4000 K	>80	7,535 lm
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	840 neutral white	4000 K	>80	7,040 lm
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	RGB	-	N.A.	4,035 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	RGB	-	N.A.	4,205 lm
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	RGB	-	N.A.	4,775 lm
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	RGB	-	N.A.	3,580 lm
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	RGB	-	N.A.	3,465 lm
50602299	BVP374 48LED RGBW 220V 10 DMX 120W HP	RGBW	-	N.A.	5,165 lm
50603999	BVP374 48LED RGBW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,380 lm
50604699	BVP374 48LED RGBW 220V 30 DMX 120W HP	RGBW	-	N.A.	6,110 lm
50605399	BVP374 48LED RGBW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,580 lm
50606099	BVP374 48LED RGBW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,435 lm
50607799	BVP374 48LED RGBW 220V 10 DMX 120W HP	RGBW	-	N.A.	4,940 lm
50608499	BVP374 48LED RGBW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,150 lm
50609199	BVP374 48LED RGBW 220V 30 DMX 120W HP	RGBW	-	N.A.	5,845 lm
50610799	BVP374 48LED RGBW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,385 lm
50611499	BVP374 48LED RGBW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,245 lm
50612199	BVP374 60LED 27K 220V 10 150W HP	827 warm white	2700 K	>80	9,425 lm
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	827 warm white	2700 K	>80	9,065 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50614599	BVP374 60LED 27K 220V 15 150W HP	827 warm white	2700 K	>80	9,820 lm
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	827 warm white	2700 K	>80	9,450 lm
50616999	BVP374 60LED 27K 220V 30 150W HP	827 warm white	2700 K	>80	11,150 lm
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	827 warm white	2700 K	>80	10,725 lm
50618399	BVP374 60LED 27K 220V 45 150W HP	827 warm white	2700 K	>80	8,360 lm
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	827 warm white	2700 K	>80	8,045 lm
50620699	BVP374 60LED 27K 220V 60 150W HP	827 warm white	2700 K	>80	8,095 lm
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	827 warm white	2700 K	>80	7,790 lm
50622099	BVP374 60LED 30K 220V 10 150W HP	830 warm white	3000 K	>80	9,830 lm
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	830 warm white	3000 K	>80	9,455 lm
50624499	BVP374 60LED 30K 220V 15 150W HP	830 warm white	3000 K	>80	10,245 lm
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	830 warm white	3000 K	>80	9,855 lm
50626899	BVP374 60LED 30K 220V 30 150W HP	830 warm white	3000 K	>80	11,630 lm
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	830 warm white	3000 K	>80	11,190 lm
50628299	BVP374 60LED 30K 220V 45 150W HP	830 warm white	3000 K	>80	8,720 lm
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	830 warm white	3000 K	>80	8,390 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
50630599	BVP374 60LED 30K 220V 60 150W HP	830 warm white	3000 K	>80	8,445 lm
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	830 warm white	3000 K	>80	8,125 lm
50632999	BVP374 60LED 40K 220V 10 150W HP	840 neutral white	4000 K	>80	10,965 lm
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	840 neutral white	4000 K	>80	10,550 lm
50634399	BVP374 60LED 40K 220V 15 150W HP	840 neutral white	4000 K	>80	11,430 lm
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	840 neutral white	4000 K	>80	10,995 lm
50636799	BVP374 60LED 40K 220V 30 150W HP	840 neutral white	4000 K	>80	12,975 lm
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	840 neutral white	4000 K	>80	12,485 lm
50638199	BVP374 60LED 40K 220V 45 150W HP	840 neutral white	4000 K	>80	9,730 lm
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	840 neutral white	4000 K	>80	9,360 lm
50640499	BVP374 60LED 40K 220V 60 150W HP	840 neutral white	4000 K	>80	9,420 lm
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	840 neutral white	4000 K	>80	9,065 lm
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	RGB	-	N.A.	5,185 lm
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	RGB	-	N.A.	5,405 lm
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	RGB	-	N.A.	6,135 lm
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	RGB	-	N.A.	4,600 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	RGB	-	N.A.	4,455 lm
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,635 lm
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,920 lm
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,855 lm
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,890 lm
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,700 lm

Order Code	Full Product Name	Light	Correlated	Color rendering index (CRI)	Luminous Flux
		source color	Color Temperature (Nom)		
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,370 lm
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,640 lm
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,535 lm
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,650 lm
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
50342799	BVP371 12LED 27K 220V 10 24W HE	24 W
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	24 W
50344199	BVP371 12LED 27K 220V 15 24W HE	24 W
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	24 W
50346599	BVP371 12LED 27K 220V 30 24W HE	24 W
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	24 W
50348999	BVP371 12LED 27K 220V 45 24W HE	24 W
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	24 W
50350299	BVP371 12LED 27K 220V 60 24W HE	24 W
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	24 W
50352699	BVP371 12LED 30K 220V 10 24W HE	24 W
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	24 W
50354099	BVP371 12LED 30K 220V 15 24W HE	24 W
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	24 W
50356499	BVP371 12LED 30K 220V 30 24W HE	24 W
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	24 W
50358899	BVP371 12LED 30K 220V 45 24W HE	24 W
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	24 W
50360199	BVP371 12LED 30K 220V 60 24W HE	24 W
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	24 W
50362599	BVP371 12LED 40K 220V 10 24W HE	24 W
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	24 W
50364999	BVP371 12LED 40K 220V 15 24W HE	24 W
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	24 W
50366399	BVP371 12LED 40K 220V 30 24W HE	24 W
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	24 W
50368799	BVP371 12LED 40K 220V 45 24W HE	24 W

Order Code	Full Product Name	Power Consumption
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	24 W
50370099	BVP371 12LED 40K 220V 60 24W HE	24 W
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	24 W
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	24 W
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	24 W
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	24 W
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	24 W
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	24 W
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	24 W
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	24 W
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	24 W
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	24 W
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	24 W
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	24 W
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	24 W
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	24 W
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	24 W
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	24 W
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	40 W
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	40 W
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	40 W
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	40 W
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	40 W
50392299	BVP372 16LED 27K 220V 10 40W HP	40 W
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	40 W
50394699	BVP372 16LED 27K 220V 15 40W HP	40 W
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	40 W

Order Code	Full Product Name	Power Consumption
50396099	BVP372 16LED 27K 220V 30 40W HP	40 W
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	40 W
50398499	BVP372 16LED 27K 220V 45 40W HP	40 W
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	40 W
50400499	BVP372 16LED 27K 220V 60 40W HP	40 W
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	40 W
50402899	BVP372 16LED 30K 220V 10 40W HP	40 W
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	40 W
50404299	BVP372 16LED 30K 220V 15 40W HP	40 W
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	40 W
50406699	BVP372 16LED 30K 220V 30 40W HP	40 W
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	40 W
50408099	BVP372 16LED 30K 220V 45 40W HP	40 W
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	40 W
50410399	BVP372 16LED 30K 220V 60 40W HP	40 W
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	40 W
50412799	BVP372 16LED 40K 220V 10 40W HP	40 W
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	40 W
50414199	BVP372 16LED 40K 220V 15 40W HP	40 W
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	40 W
50416599	BVP372 16LED 40K 220V 30 40W HP	40 W
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	40 W
50418999	BVP372 16LED 40K 220V 45 40W HP	40 W
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	40 W
50420299	BVP372 16LED 40K 220V 60 40W HP	40 W
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	40 W
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	40 W
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	40 W
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	40 W
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	40 W
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	40 W
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	40 W
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	40 W
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	40 W
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	40 W
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	40 W
50432599	BVP372 18LED 27K 220V 10 50W HP	50 W
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	50 W
50434999	BVP372 18LED 27K 220V 15 50W HP	50 W
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	50 W
50436399	BVP372 18LED 27K 220V 30 50W HP	50 W
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	50 W
50438799	BVP372 18LED 27K 220V 45 50W HP	50 W
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	50 W
50440099	BVP372 18LED 27K 220V 60 50W HP	50 W
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	50 W
50442499	BVP372 18LED 30K 220V 10 50W HP	50 W
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	50 W
50444899	BVP372 18LED 30K 220V 15 50W HP	50 W
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	50 W
50446299	BVP372 18LED 30K 220V 30 50W HP	50 W
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	50 W

Order Code	Full Product Name	Power Consumption
50448699	BVP372 18LED 30K 220V 45 50W HP	50 W
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	50 W
50450999	BVP372 18LED 30K 220V 60 50W HP	50 W
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	50 W
50452399	BVP372 18LED 40K 220V 10 50W HP	50 W
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	50 W
50454799	BVP372 18LED 40K 220V 15 50W HP	50 W
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	50 W
50456199	BVP372 18LED 40K 220V 30 50W HP	50 W
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	50 W
50458599	BVP372 18LED 40K 220V 45 50W HP	50 W
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	50 W
50460899	BVP372 18LED 40K 220V 60 50W HP	50 W
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	50 W
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	50 W
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	50 W
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	50 W
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	50 W
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	50 W
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	50 W
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	50 W
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	50 W
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	50 W
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	50 W
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	50 W
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	50 W
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	50 W
50477699	BVP373 30LED 27K 220V 10 80W HP	80 W
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	80 W
50479099	BVP373 30LED 27K 220V 15 80W HP	80 W
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	80 W
50481399	BVP373 30LED 27K 220V 30 80W HP	80 W
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	80 W
50483799	BVP373 30LED 27K 220V 45 80W HP	80 W
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	80 W
50485199	BVP373 30LED 27K 220V 60 80W HP	80 W
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	80 W
50487599	BVP373 30LED 30K 220V 10 80W HP	80 W
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	80 W
50489999	BVP373 30LED 30K 220V 15 80W HP	80 W
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	80 W
50491299	BVP373 30LED 30K 220V 30 80W HP	80 W
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	80 W
50493699	BVP373 30LED 30K 220V 45 80W HP	80 W
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	80 W
50495099	BVP373 30LED 30K 220V 60 80W HP	80 W
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	80 W
50497499	BVP373 30LED 40K 220V 10 80W HP	80 W
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	80 W
50499899	BVP373 30LED 40K 220V 15 80W HP	80 W

Order Code	Full Product Name	Power Consumption
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	80 W
50501899	BVP373 30LED 40K 220V 30 80W HP	80 W
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	80 W
50503299	BVP373 30LED 40K 220V 45 80W HP	80 W
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	80 W
50505699	BVP373 30LED 40K 220V 60 80W HP	80 W
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	80 W
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	80 W
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	80 W
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	80 W
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	80 W
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	80 W
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	80 W
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	80 W
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	80 W
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	80 W
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	80 W
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	80 W
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	80 W
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	80 W
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	80 W
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	80 W
50522399	BVP373 36LED 27K 220V 10 100W HP	100 W
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	100 W
50524799	BVP373 36LED 27K 220V 15 100W HP	100 W
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	100 W
50526199	BVP373 36LED 27K 220V 30 100W HP	100 W
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	100 W
50528599	BVP373 36LED 27K 220V 45 100W HP	100 W
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	100 W
50530899	BVP373 36LED 27K 220V 60 100W HP	100 W
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	100 W
50532299	BVP373 36LED 30K 220V 10 100W HP	100 W
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	100 W
50534699	BVP373 36LED 30K 220V 15 100W HP	100 W
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	100 W
50536099	BVP373 36LED 30K 220V 30 100W HP	100 W
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	100 W
50538499	BVP373 36LED 30K 220V 45 100W HP	100 W
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	100 W
50540799	BVP373 36LED 30K 220V 60 100W HP	100 W
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	100 W
50542199	BVP373 36LED 40K 220V 10 100W HP	100 W
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	100 W
50544599	BVP373 36LED 40K 220V 15 100W HP	100 W
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	100 W
50546999	BVP373 36LED 40K 220V 30 100W HP	100 W
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	100 W
50548399	BVP373 36LED 40K 220V 45 100W HP	100 W
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	100 W
50550699	BVP373 36LED 40K 220V 60 100W HP	100 W
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	100 W

Order Code	Full Product Name	Power Consumption
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	100 W
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	100 W
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	100 W
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	100 W
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	100 W
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	100 W
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	100 W
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	100 W
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	100 W
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	100 W
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	100 W
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	100 W
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	100 W
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	100 W
50567499	BVP374 48LED 27K 220V 10 120W HP	120 W
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	120 W
50569899	BVP374 48LED 27K 220V 15 120W HP	120 W
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	120 W
50571199	BVP374 48LED 27K 220V 30 120W HP	120 W
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	120 W
50573599	BVP374 48LED 27K 220V 45 120W HP	120 W
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	120 W
50575999	BVP374 48LED 27K 220V 60 120W HP	120 W
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	120 W
50577399	BVP374 48LED 30K 220V 10 120W HP	120 W
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	120 W
50579799	BVP374 48LED 30K 220V 15 120W HP	120 W
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	120 W
50581099	BVP374 48LED 30K 220V 30 120W HP	120 W
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	120 W
50583499	BVP374 48LED 30K 220V 45 120W HP	120 W
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	120 W
50585899	BVP374 48LED 30K 220V 60 120W HP	120 W
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	120 W
50587299	BVP374 48LED 40K 220V 10 120W HP	120 W
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	120 W
50589699	BVP374 48LED 40K 220V 15 120W HP	120 W
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	120 W
50591999	BVP374 48LED 40K 220V 30 120W HP	120 W
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	120 W
50593399	BVP374 48LED 40K 220V 45 120W HP	120 W
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	120 W
50595799	BVP374 48LED 40K 220V 60 120W HP	120 W
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	120 W
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	120 W
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	120 W
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	120 W
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	120 W
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	120 W
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	120 W
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	120 W

Order Code	Full Product Name	Power Consumption
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	120 W
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	120 W
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	120 W
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	120 W
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	120 W
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	120 W
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	120 W
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	120 W
50612199	BVP374 60LED 27K 220V 10 150W HP	150 W
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	150 W
50614599	BVP374 60LED 27K 220V 15 150W HP	150 W
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	150 W
50616999	BVP374 60LED 27K 220V 30 150W HP	150 W
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	150 W
50618399	BVP374 60LED 27K 220V 45 150W HP	150 W
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	150 W
50620699	BVP374 60LED 27K 220V 60 150W HP	150 W
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	150 W
50622099	BVP374 60LED 30K 220V 10 150W HP	150 W
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	150 W
50624499	BVP374 60LED 30K 220V 15 150W HP	150 W
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	150 W
50626899	BVP374 60LED 30K 220V 30 150W HP	150 W
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	150 W
50628299	BVP374 60LED 30K 220V 45 150W HP	150 W
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	150 W
50630599	BVP374 60LED 30K 220V 60 150W HP	150 W

Order Code	Full Product Name	Power Consumption
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	150 W
50632999	BVP374 60LED 40K 220V 10 150W HP	150 W
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	150 W
50634399	BVP374 60LED 40K 220V 15 150W HP	150 W
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	150 W
50636799	BVP374 60LED 40K 220V 30 150W HP	150 W
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	150 W
50638199	BVP374 60LED 40K 220V 45 150W HP	150 W
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	150 W
50640499	BVP374 60LED 40K 220V 60 150W HP	150 W
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	150 W
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	150 W
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	150 W
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	150 W
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	150 W
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	150 W
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	150 W
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	150 W
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	150 W
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	150 W
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	150 W
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	150 W
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	150 W
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	150 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
50342799	BVP371 12LED 27K 220V 10 24W HE	No
50343499	BVP371 12LED 27K 220V 10 DMX 24W HE	Yes
50344199	BVP371 12LED 27K 220V 15 24W HE	No
50345899	BVP371 12LED 27K 220V 15 DMX 24W HE	Yes
50346599	BVP371 12LED 27K 220V 30 24W HE	No
50347299	BVP371 12LED 27K 220V 30 DMX 24W HE	Yes
50348999	BVP371 12LED 27K 220V 45 24W HE	No
50349699	BVP371 12LED 27K 220V 45 DMX 24W HE	Yes
50350299	BVP371 12LED 27K 220V 60 24W HE	No
50351999	BVP371 12LED 27K 220V 60 DMX 24W HE	Yes
50352699	BVP371 12LED 30K 220V 10 24W HE	No
50353399	BVP371 12LED 30K 220V 10 DMX 24W HE	Yes
50354099	BVP371 12LED 30K 220V 15 24W HE	No
50355799	BVP371 12LED 30K 220V 15 DMX 24W HE	Yes
50356499	BVP371 12LED 30K 220V 30 24W HE	No
50357199	BVP371 12LED 30K 220V 30 DMX 24W HE	Yes
50358899	BVP371 12LED 30K 220V 45 24W HE	No
50359599	BVP371 12LED 30K 220V 45 DMX 24W HE	Yes
50360199	BVP371 12LED 30K 220V 60 24W HE	No
50361899	BVP371 12LED 30K 220V 60 DMX 24W HE	Yes
50362599	BVP371 12LED 40K 220V 10 24W HE	No

Order Code	Full Product Name	Dimmable
50363299	BVP371 12LED 40K 220V 10 DMX 24W HE	Yes
50364999	BVP371 12LED 40K 220V 15 24W HE	No
50365699	BVP371 12LED 40K 220V 15 DMX 24W HE	Yes
50366399	BVP371 12LED 40K 220V 30 24W HE	No
50367099	BVP371 12LED 40K 220V 30 DMX 24W HE	Yes
50368799	BVP371 12LED 40K 220V 45 24W HE	No
50369499	BVP371 12LED 40K 220V 45 DMX 24W HE	Yes
50370099	BVP371 12LED 40K 220V 60 24W HE	No
50371799	BVP371 12LED 40K 220V 60 DMX 24W HE	Yes
50372499	BVP371 12LED RGB 220V 10 DMX 24W HE	Yes
50373199	BVP371 12LED RGB 220V 15 DMX 24W HE	Yes
50374899	BVP371 12LED RGB 220V 30 DMX 24W HE	Yes
50375599	BVP371 12LED RGB 220V 45 DMX 24W HE	Yes
50376299	BVP371 12LED RGB 220V 60 DMX 24W HE	Yes
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	Yes
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	Yes
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	Yes
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	Yes
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	Yes
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	Yes
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	Yes

Order Code	Full Product Name	Dimmable
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	Yes
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	Yes
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	Yes
50387899	BVP372 15LED RGB 220V 10 DMX 40W HP	Yes
50388599	BVP372 15LED RGB 220V 15 DMX 40W HP	Yes
50389299	BVP372 15LED RGB 220V 30 DMX 40W HP	Yes
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	Yes
50391599	BVP372 15LED RGB 220V 60 DMX 40W HP	Yes
50392299	BVP372 16LED 27K 220V 10 40W HP	No
50393999	BVP372 16LED 27K 220V 10 DMX 40W HP	Yes
50394699	BVP372 16LED 27K 220V 15 40W HP	No
50395399	BVP372 16LED 27K 220V 15 DMX 40W HP	Yes
50396099	BVP372 16LED 27K 220V 30 40W HP	No
50397799	BVP372 16LED 27K 220V 30 DMX 40W HP	Yes
50398499	BVP372 16LED 27K 220V 45 40W HP	No
50399199	BVP372 16LED 27K 220V 45 DMX 40W HP	Yes
50400499	BVP372 16LED 27K 220V 60 40W HP	No
50401199	BVP372 16LED 27K 220V 60 DMX 40W HP	Yes
50402899	BVP372 16LED 30K 220V 10 40W HP	No
50403599	BVP372 16LED 30K 220V 10 DMX 40W HP	Yes
50404299	BVP372 16LED 30K 220V 15 40W HP	No
50405999	BVP372 16LED 30K 220V 15 DMX 40W HP	Yes
50406699	BVP372 16LED 30K 220V 30 40W HP	No
50407399	BVP372 16LED 30K 220V 30 DMX 40W HP	Yes
50408099	BVP372 16LED 30K 220V 45 40W HP	No
50409799	BVP372 16LED 30K 220V 45 DMX 40W HP	Yes
50410399	BVP372 16LED 30K 220V 60 40W HP	No
50411099	BVP372 16LED 30K 220V 60 DMX 40W HP	Yes
50412799	BVP372 16LED 40K 220V 10 40W HP	No
50413499	BVP372 16LED 40K 220V 10 DMX 40W HP	Yes
50414199	BVP372 16LED 40K 220V 15 40W HP	No
50415899	BVP372 16LED 40K 220V 15 DMX 40W HP	Yes
50416599	BVP372 16LED 40K 220V 30 40W HP	No
50417299	BVP372 16LED 40K 220V 30 DMX 40W HP	Yes
50418999	BVP372 16LED 40K 220V 45 40W HP	No
50419699	BVP372 16LED 40K 220V 45 DMX 40W HP	Yes
50420299	BVP372 16LED 40K 220V 60 40W HP	No
50421999	BVP372 16LED 40K 220V 60 DMX 40W HP	Yes
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	Yes
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	Yes
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	Yes
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	Yes
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	Yes
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	Yes
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	Yes
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	Yes
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	Yes
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	Yes
50432599	BVP372 18LED 27K 220V 10 50W HP	No
50433299	BVP372 18LED 27K 220V 10 DMX 50W HP	Yes
50434999	BVP372 18LED 27K 220V 15 50W HP	No
50435699	BVP372 18LED 27K 220V 15 DMX 50W HP	Yes

Order Code	Full Product Name	Dimmable
50436399	BVP372 18LED 27K 220V 30 50W HP	No
50437099	BVP372 18LED 27K 220V 30 DMX 50W HP	Yes
50438799	BVP372 18LED 27K 220V 45 50W HP	No
50439499	BVP372 18LED 27K 220V 45 DMX 50W HP	Yes
50440099	BVP372 18LED 27K 220V 60 50W HP	No
50441799	BVP372 18LED 27K 220V 60 DMX 50W HP	Yes
50442499	BVP372 18LED 30K 220V 10 50W HP	No
50443199	BVP372 18LED 30K 220V 10 DMX 50W HP	Yes
50444899	BVP372 18LED 30K 220V 15 50W HP	No
50445599	BVP372 18LED 30K 220V 15 DMX 50W HP	Yes
50446299	BVP372 18LED 30K 220V 30 50W HP	No
50447999	BVP372 18LED 30K 220V 30 DMX 50W HP	Yes
50448699	BVP372 18LED 30K 220V 45 50W HP	No
50449399	BVP372 18LED 30K 220V 45 DMX 50W HP	Yes
50450999	BVP372 18LED 30K 220V 60 50W HP	No
50451699	BVP372 18LED 30K 220V 60 DMX 50W HP	Yes
50452399	BVP372 18LED 40K 220V 10 50W HP	No
50453099	BVP372 18LED 40K 220V 10 DMX 50W HP	Yes
50454799	BVP372 18LED 40K 220V 15 50W HP	No
50455499	BVP372 18LED 40K 220V 15 DMX 50W HP	Yes
50456199	BVP372 18LED 40K 220V 30 50W HP	No
50457899	BVP372 18LED 40K 220V 30 DMX 50W HP	Yes
50458599	BVP372 18LED 40K 220V 45 50W HP	No
50459299	BVP372 18LED 40K 220V 45 DMX 50W HP	Yes
50460899	BVP372 18LED 40K 220V 60 50W HP	No
50461599	BVP372 18LED 40K 220V 60 DMX 50W HP	Yes
50462299	BVP372 18LED RGB 220V 10 DMX 50W HP	Yes
50463999	BVP372 18LED RGB 220V 15 DMX 50W HP	Yes
50464699	BVP372 18LED RGB 220V 30 DMX 50W HP	Yes
50465399	BVP372 18LED RGB 220V 45 DMX 50W HP	Yes
50466099	BVP372 18LED RGB 220V 60 DMX 50W HP	Yes
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	Yes
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	Yes
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	Yes
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	Yes
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	Yes
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	Yes
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	Yes
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	Yes
50477699	BVP373 30LED 27K 220V 10 80W HP	No
50478399	BVP373 30LED 27K 220V 10 DMX 80W HP	Yes
50479099	BVP373 30LED 27K 220V 15 80W HP	No
50480699	BVP373 30LED 27K 220V 15 DMX 80W HP	Yes
50481399	BVP373 30LED 27K 220V 30 80W HP	No
50482099	BVP373 30LED 27K 220V 30 DMX 80W HP	Yes
50483799	BVP373 30LED 27K 220V 45 80W HP	No
50484499	BVP373 30LED 27K 220V 45 DMX 80W HP	Yes
50485199	BVP373 30LED 27K 220V 60 80W HP	No
50486899	BVP373 30LED 27K 220V 60 DMX 80W HP	Yes
50487599	BVP373 30LED 30K 220V 10 80W HP	No

Order Code	Full Product Name	Dimmable
50488299	BVP373 30LED 30K 220V 10 DMX 80W HP	Yes
50489999	BVP373 30LED 30K 220V 15 80W HP	No
50490599	BVP373 30LED 30K 220V 15 DMX 80W HP	Yes
50491299	BVP373 30LED 30K 220V 30 80W HP	No
50492999	BVP373 30LED 30K 220V 30 DMX 80W HP	Yes
50493699	BVP373 30LED 30K 220V 45 80W HP	No
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	Yes
50495099	BVP373 30LED 30K 220V 60 80W HP	No
50496799	BVP373 30LED 30K 220V 60 DMX 80W HP	Yes
50497499	BVP373 30LED 40K 220V 10 80W HP	No
50498199	BVP373 30LED 40K 220V 10 DMX 80W HP	Yes
50499899	BVP373 30LED 40K 220V 15 80W HP	No
50500199	BVP373 30LED 40K 220V 15 DMX 80W HP	Yes
50501899	BVP373 30LED 40K 220V 30 80W HP	No
50502599	BVP373 30LED 40K 220V 30 DMX 80W HP	Yes
50503299	BVP373 30LED 40K 220V 45 80W HP	No
50504999	BVP373 30LED 40K 220V 45 DMX 80W HP	Yes
50505699	BVP373 30LED 40K 220V 60 80W HP	No
50506399	BVP373 30LED 40K 220V 60 DMX 80W HP	Yes
50507099	BVP373 30LED RGB 220V 10 DMX 80W HP	Yes
50508799	BVP373 30LED RGB 220V 15 DMX 80W HP	Yes
50509499	BVP373 30LED RGB 220V 30 DMX 80W HP	Yes
50510099	BVP373 30LED RGB 220V 45 DMX 80W HP	Yes
50511799	BVP373 30LED RGB 220V 60 DMX 80W HP	Yes
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	Yes
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	Yes
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	Yes
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	Yes
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	Yes
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	Yes
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	Yes
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	Yes
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	Yes
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	Yes
50522399	BVP373 36LED 27K 220V 10 100W HP	No
50523099	BVP373 36LED 27K 220V 10 DMX 100W HP	Yes
50524799	BVP373 36LED 27K 220V 15 100W HP	No
50525499	BVP373 36LED 27K 220V 15 DMX 100W HP	Yes
50526199	BVP373 36LED 27K 220V 30 100W HP	No
50527899	BVP373 36LED 27K 220V 30 DMX 100W HP	Yes
50528599	BVP373 36LED 27K 220V 45 100W HP	No
50529299	BVP373 36LED 27K 220V 45 DMX 100W HP	Yes
50530899	BVP373 36LED 27K 220V 60 100W HP	No
50531599	BVP373 36LED 27K 220V 60 DMX 100W HP	Yes
50532299	BVP373 36LED 30K 220V 10 100W HP	No
50533999	BVP373 36LED 30K 220V 10 DMX 100W HP	Yes
50534699	BVP373 36LED 30K 220V 15 100W HP	No
50535399	BVP373 36LED 30K 220V 15 DMX 100W HP	Yes
50536099	BVP373 36LED 30K 220V 30 100W HP	No
50537799	BVP373 36LED 30K 220V 30 DMX 100W HP	Yes
50538499	BVP373 36LED 30K 220V 45 100W HP	No
50539199	BVP373 36LED 30K 220V 45 DMX 100W HP	Yes

Order Code	Full Product Name	Dimmable
50540799	BVP373 36LED 30K 220V 60 100W HP	No
50541499	BVP373 36LED 30K 220V 60 DMX 100W HP	Yes
50542199	BVP373 36LED 40K 220V 10 100W HP	No
50543899	BVP373 36LED 40K 220V 10 DMX 100W HP	Yes
50544599	BVP373 36LED 40K 220V 15 100W HP	No
50545299	BVP373 36LED 40K 220V 15 DMX 100W HP	Yes
50546999	BVP373 36LED 40K 220V 30 100W HP	No
50547699	BVP373 36LED 40K 220V 30 DMX 100W HP	Yes
50548399	BVP373 36LED 40K 220V 45 100W HP	No
50549099	BVP373 36LED 40K 220V 45 DMX 100W HP	Yes
50550699	BVP373 36LED 40K 220V 60 100W HP	No
50551399	BVP373 36LED 40K 220V 60 DMX 100W HP	Yes
50552099	BVP373 36LED RGB 220V 10 DMX 100W HP	Yes
50553799	BVP373 36LED RGB 220V 15 DMX 100W HP	Yes
50554499	BVP373 36LED RGB 220V 30 DMX 100W HP	Yes
50555199	BVP373 36LED RGB 220V 45 DMX 100W HP	Yes
50556899	BVP373 36LED RGB 220V 60 DMX 100W HP	Yes
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	Yes
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	Yes
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	Yes
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	Yes
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	Yes
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	Yes
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	Yes
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	Yes
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	Yes
50567499	BVP374 48LED 27K 220V 10 120W HP	No
50568199	BVP374 48LED 27K 220V 10 DMX 120W HP	Yes
50569899	BVP374 48LED 27K 220V 15 120W HP	No
50570499	BVP374 48LED 27K 220V 15 DMX 120W HP	Yes
50571199	BVP374 48LED 27K 220V 30 120W HP	No
50572899	BVP374 48LED 27K 220V 30 DMX 120W HP	Yes
50573599	BVP374 48LED 27K 220V 45 120W HP	No
50574299	BVP374 48LED 27K 220V 45 DMX 120W HP	Yes
50575999	BVP374 48LED 27K 220V 60 120W HP	No
50576699	BVP374 48LED 27K 220V 60 DMX 120W HP	Yes
50577399	BVP374 48LED 30K 220V 10 120W HP	No
50578099	BVP374 48LED 30K 220V 10 DMX 120W HP	Yes
50579799	BVP374 48LED 30K 220V 15 120W HP	No
50580399	BVP374 48LED 30K 220V 15 DMX 120W HP	Yes
50581099	BVP374 48LED 30K 220V 30 120W HP	No
50582799	BVP374 48LED 30K 220V 30 DMX 120W HP	Yes
50583499	BVP374 48LED 30K 220V 45 120W HP	No
50584199	BVP374 48LED 30K 220V 45 DMX 120W HP	Yes
50585899	BVP374 48LED 30K 220V 60 120W HP	No
50586599	BVP374 48LED 30K 220V 60 DMX 120W HP	Yes
50587299	BVP374 48LED 40K 220V 10 120W HP	No
50588999	BVP374 48LED 40K 220V 10 DMX 120W HP	Yes
50589699	BVP374 48LED 40K 220V 15 120W HP	No
50590299	BVP374 48LED 40K 220V 15 DMX 120W HP	Yes
50591999	BVP374 48LED 40K 220V 30 120W HP	No

Order Code	Full Product Name	Dimmable
50592699	BVP374 48LED 40K 220V 30 DMX 120W HP	Yes
50593399	BVP374 48LED 40K 220V 45 120W HP	No
50594099	BVP374 48LED 40K 220V 45 DMX 120W HP	Yes
50595799	BVP374 48LED 40K 220V 60 120W HP	No
50596499	BVP374 48LED 40K 220V 60 DMX 120W HP	Yes
50597199	BVP374 48LED RGB 220V 10 DMX 120W HP	Yes
50598899	BVP374 48LED RGB 220V 15 DMX 120W HP	Yes
50599599	BVP374 48LED RGB 220V 30 DMX 120W HP	Yes
50600899	BVP374 48LED RGB 220V 45 DMX 120W HP	Yes
50601599	BVP374 48LED RGB 220V 60 DMX 120W HP	Yes
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	Yes
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	Yes
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	Yes
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	Yes
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	Yes
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	Yes
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	Yes
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	Yes
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	Yes
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	Yes
50612199	BVP374 60LED 27K 220V 10 150W HP	No
50613899	BVP374 60LED 27K 220V 10 DMX 150W HP	Yes
50614599	BVP374 60LED 27K 220V 15 150W HP	No
50615299	BVP374 60LED 27K 220V 15 DMX 150W HP	Yes
50616999	BVP374 60LED 27K 220V 30 150W HP	No
50617699	BVP374 60LED 27K 220V 30 DMX 150W HP	Yes
50618399	BVP374 60LED 27K 220V 45 150W HP	No
50619099	BVP374 60LED 27K 220V 45 DMX 150W HP	Yes
50620699	BVP374 60LED 27K 220V 60 150W HP	No
50621399	BVP374 60LED 27K 220V 60 DMX 150W HP	Yes
50622099	BVP374 60LED 30K 220V 10 150W HP	No
50623799	BVP374 60LED 30K 220V 10 DMX 150W HP	Yes
50624499	BVP374 60LED 30K 220V 15 150W HP	No

Order Code	Full Product Name	Dimmable
50625199	BVP374 60LED 30K 220V 15 DMX 150W HP	Yes
50626899	BVP374 60LED 30K 220V 30 150W HP	No
50627599	BVP374 60LED 30K 220V 30 DMX 150W HP	Yes
50628299	BVP374 60LED 30K 220V 45 150W HP	No
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	Yes
50630599	BVP374 60LED 30K 220V 60 150W HP	No
50631299	BVP374 60LED 30K 220V 60 DMX 150W HP	Yes
50632999	BVP374 60LED 40K 220V 10 150W HP	No
50633699	BVP374 60LED 40K 220V 10 DMX 150W HP	Yes
50634399	BVP374 60LED 40K 220V 15 150W HP	No
50635099	BVP374 60LED 40K 220V 15 DMX 150W HP	Yes
50636799	BVP374 60LED 40K 220V 30 150W HP	No
50637499	BVP374 60LED 40K 220V 30 DMX 150W HP	Yes
50638199	BVP374 60LED 40K 220V 45 150W HP	No
50639899	BVP374 60LED 40K 220V 45 DMX 150W HP	Yes
50640499	BVP374 60LED 40K 220V 60 150W HP	No
50641199	BVP374 60LED 40K 220V 60 DMX 150W HP	Yes
50642899	BVP374 60LED RGB 220V 10 DMX 150W HP	Yes
50643599	BVP374 60LED RGB 220V 15 DMX 150W HP	Yes
50644299	BVP374 60LED RGB 220V 30 DMX 150W HP	Yes
50645999	BVP374 60LED RGB 220V 45 DMX 150W HP	Yes
50646699	BVP374 60LED RGB 220V 60 DMX 150W HP	Yes
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	Yes
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	Yes
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	Yes
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	Yes
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	Yes
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	Yes
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	Yes
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	Yes

