



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

The Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is a compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, the Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-storey exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colours, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for the DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro




Application

- Bridges, Monuments, Façades
- Landscape
- Parks and squares

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information

Driver included Yes

Mechanical and Housing

Optical cover type Clear glass

Housing Colour Dark grey

Mech. impact protection code IK06

Ingress protection code IP66

Approval and Application

CE mark Yes

Light Technical

UniFlood C Pro

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401773703	BVP371 12LED 30K 220V 10 24W HE	830 warm white	3000 K	>80	1,635 lm
911401773723	BVP371 12LED 30K 220V 15 24W HE	830 warm white	3000 K	>80	1,705 lm
911401773743	BVP371 12LED 30K 220V 30 24W HE	830 warm white	3000 K	>80	1,935 lm
911401773763	BVP371 12LED 30K 220V 45 24W HE	830 warm white	3000 K	>80	1,450 lm
911401773783	BVP371 12LED 30K 220V 60 24W HE	830 warm white	3000 K	>80	1,405 lm
911401773803	BVP371 12LED 40K 220V 10 24W HE	840 neutral white	4000 K	>80	1,825 lm
911401773823	BVP371 12LED 40K 220V 15 24W HE	840 neutral white	4000 K	>80	1,905 lm
911401773843	BVP371 12LED 40K 220V 30 24W HE	840 neutral white	4000 K	>80	2,160 lm
911401773863	BVP371 12LED 40K 220V 45 24W HE	840 neutral white	4000 K	>80	1,620 lm
911401773883	BVP371 12LED 40K 220V 60 24W HE	840 neutral white	4000 K	>80	1,570 lm
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,090 lm
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,140 lm
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,290 lm
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	RGBW	-	N.A.	970 lm
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	RGBW	-	N.A.	940 lm
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,045 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,090 lm
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,235 lm
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	RGBW	-	N.A.	925 lm
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	RGBW	-	N.A.	900 lm
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	RGB	-	N.A.	1,150 lm
911401774203	BVP372 16LED 30K 220V 10 40W HP	830 warm white	3000 K	>80	2,570 lm
911401774223	BVP372 16LED 30K 220V 15 40W HP	830 warm white	3000 K	>80	2,680 lm
911401774243	BVP372 16LED 30K 220V 30 40W HP	830 warm white	3000 K	>80	3,040 lm
911401774263	BVP372 16LED 30K 220V 45 40W HP	830 warm white	3000 K	>80	2,280 lm
911401774283	BVP372 16LED 30K 220V 60 40W HP	830 warm white	3000 K	>80	2,210 lm
911401774303	BVP372 16LED 40K 220V 10 40W HP	840 neutral white	4000 K	>80	2,870 lm
911401774323	BVP372 16LED 40K 220V 15 40W HP	840 neutral white	4000 K	>80	2,990 lm
911401774343	BVP372 16LED 40K 220V 30 40W HP	840 neutral white	4000 K	>80	3,395 lm
911401774363	BVP372 16LED 40K 220V 45 40W HP	840 neutral white	4000 K	>80	2,545 lm
911401774383	BVP372 16LED 40K 220V 60 40W HP	840 neutral white	4000 K	>80	2,465 lm
911401774403	BVP372 16LED RGBNW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,580 lm

UniFlood C Pro

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401774413	BVP372 16LED RGBNW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,650 lm
911401774423	BVP372 16LED RGBNW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,870 lm
911401774433	BVP372 16LED RGBNW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,400 lm
911401774443	BVP372 16LED RGBNW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,360 lm
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,515 lm
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,575 lm
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,790 lm
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,340 lm
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,300 lm
911401774603	BVP372 18LED 30K 220V 10 50W HP	830 warm white	3000 K	>80	3,070 lm
911401774623	BVP372 18LED 30K 220V 15 50W HP	830 warm white	3000 K	>80	3,200 lm
911401774643	BVP372 18LED 30K 220V 30 50W HP	830 warm white	3000 K	>80	3,635 lm
911401774663	BVP372 18LED 30K 220V 45 50W HP	830 warm white	3000 K	>80	2,725 lm
911401774683	BVP372 18LED 30K 220V 60 50W HP	830 warm white	3000 K	>80	2,640 lm
911401774703	BVP372 18LED 40K 220V 10 50W HP	840 neutral white	4000 K	>80	3,430 lm
911401774723	BVP372 18LED 40K 220V 15 50W HP	840 neutral white	4000 K	>80	3,575 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401774743	BVP372 18LED 40K 220V 30 50W HP	840 neutral white	4000 K	>80	4,055 lm
911401774763	BVP372 18LED 40K 220V 45 50W HP	840 neutral white	4000 K	>80	3,040 lm
911401774783	BVP372 18LED 40K 220V 60 50W HP	840 neutral white	4000 K	>80	2,945 lm
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,140 lm
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,230 lm
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,530 lm
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,895 lm
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,835 lm
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,045 lm
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,130 lm
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,420 lm
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,815 lm
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,755 lm
911401775053	BVP373 30LED 30K 220V 10 80W HP	830 warm white	3000 K	>80	5,160 lm
911401775073	BVP373 30LED 30K 220V 15 80W HP	830 warm white	3000 K	>80	5,375 lm
911401775093	BVP373 30LED 30K 220V 30 80W HP	830 warm white	3000 K	>80	6,100 lm

UniFlood C Pro

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401775113	BVP373 30LED 30K 220V 45 80W HP	830 warm white	3000 K	>80	4,575 lm
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	830 warm white	3000 K	>80	4,295 lm
911401775133	BVP373 30LED 30K 220V 60 80W HP	830 warm white	3000 K	>80	4,430 lm
911401775153	BVP373 30LED 40K 220V 10 80W HP	840 neutral white	4000 K	>80	5,755 lm
911401775173	BVP373 30LED 40K 220V 15 80W HP	840 neutral white	4000 K	>80	6,000 lm
911401775193	BVP373 30LED 40K 220V 30 80W HP	840 neutral white	4000 K	>80	6,810 lm
911401775213	BVP373 30LED 40K 220V 45 80W HP	840 neutral white	4000 K	>80	5,105 lm
911401775233	BVP373 30LED 40K 220V 60 80W HP	840 neutral white	4000 K	>80	4,945 lm
911401775303	BVP373 32LED RGBNW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,520 lm
911401775313	BVP373 32LED RGBNW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,670 lm
911401775323	BVP373 32LED RGBNW 220V 30 DMX 80W HP	RGBW	-	N.A.	4,170 lm
911401775333	BVP373 32LED RGBNW 220V 45 DMX 80W HP	RGBW	-	N.A.	3,125 lm
911401775343	BVP373 32LED RGBNW 220V 60 DMX 80W HP	RGBW	-	N.A.	3,025 lm
911401775353	BVP373 32LED RGBWW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,370 lm
911401775363	BVP373 32LED RGBWW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,515 lm
911401775373	BVP373 32LED RGBWW 220V 30 DMX 80W HP	RGBW	-	N.A.	3,990 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401775383	BVP373 32LED RGBWW 220V 45 DMX 80W HP	RGBW	-	N.A.	2,990 lm
911401775393	BVP373 32LED RGBWW 220V 60 DMX 80W HP	RGBW	-	N.A.	2,895 lm
911401775503	BVP373 36LED 30K 220V 10 100W HP	830 warm white	3000 K	>80	6,445 lm
911401775523	BVP373 36LED 30K 220V 15 100W HP	830 warm white	3000 K	>80	6,715 lm
911401775543	BVP373 36LED 30K 220V 30 100W HP	830 warm white	3000 K	>80	7,625 lm
911401775563	BVP373 36LED 30K 220V 45 100W HP	830 warm white	3000 K	>80	5,715 lm
911401775583	BVP373 36LED 30K 220V 60 100W HP	830 warm white	3000 K	>80	5,535 lm
911401775603	BVP373 36LED 40K 220V 10 100W HP	840 neutral white	4000 K	>80	7,190 lm
911401775623	BVP373 36LED 40K 220V 15 100W HP	840 neutral white	4000 K	>80	7,495 lm
911401775643	BVP373 36LED 40K 220V 30 100W HP	840 neutral white	4000 K	>80	8,505 lm
911401775663	BVP373 36LED 40K 220V 45 100W HP	840 neutral white	4000 K	>80	6,380 lm
911401775683	BVP373 36LED 40K 220V 60 100W HP	840 neutral white	4000 K	>80	6,175 lm
911401775753	BVP373 36LED RGBNW 220V 10 DMX 100W HP	RGBW	-	N.A.	4,175 lm
911401775763	BVP373 36LED RGBNW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,355 lm
911401775773	BVP373 36LED RGBNW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,945 lm
911401775783	BVP373 36LED RGBNW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,705 lm

UniFlood C Pro

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401775793	BVP373 36LED RGBNW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,590 lm
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	RGBW	-	N.A.	3,995 lm
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,165 lm
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,730 lm
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,545 lm
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,435 lm
911401775953	BVP374 48LED 30K 220V 10 120W HP	830 warm white	3000 K	>80	7,865 lm
911401775973	BVP374 48LED 30K 220V 15 120W HP	830 warm white	3000 K	>80	8,195 lm
911401775993	BVP374 48LED 30K 220V 30 120W HP	830 warm white	3000 K	>80	9,305 lm
911401776013	BVP374 48LED 30K 220V 45 120W HP	830 warm white	3000 K	>80	6,975 lm
911401776033	BVP374 48LED 30K 220V 60 120W HP	830 warm white	3000 K	>80	6,755 lm
911401776053	BVP374 48LED 40K 220V 10 120W HP	840 neutral white	4000 K	>80	8,775 lm
911401776073	BVP374 48LED 40K 220V 15 120W HP	840 neutral white	4000 K	>80	9,145 lm
911401776093	BVP374 48LED 40K 220V 30 120W HP	840 neutral white	4000 K	>80	10,380 lm
911401776113	BVP374 48LED 40K 220V 45 120W HP	840 neutral white	4000 K	>80	7,785 lm
911401776133	BVP374 48LED 40K 220V 60 120W HP	840 neutral white	4000 K	>80	7,535 lm

Order Code	Full Product Name	Light source colour	Correlated Colour Temperature (Nom)	Colour rendering index (CRI)	Luminous Flux
911401776203	BVP374 48LED RGBNW 220V 10 DMX 120W HP	RGBW	-	N.A.	5,165 lm
911401776213	BVP374 48LED RGBNW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,380 lm
911401776223	BVP374 48LED RGBNW 220V 30 DMX 120W HP	RGBW	-	N.A.	6,110 lm
911401776233	BVP374 48LED RGBNW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,580 lm
911401776243	BVP374 48LED RGBNW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,435 lm
911401776253	BVP374 48LED RGBWW 220V 10 DMX 120W HP	RGBW	-	N.A.	4,940 lm
911401776263	BVP374 48LED RGBWW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,150 lm
911401776273	BVP374 48LED RGBWW 220V 30 DMX 120W HP	RGBW	-	N.A.	5,845 lm
911401776283	BVP374 48LED RGBWW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,385 lm
911401776293	BVP374 48LED RGBWW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,245 lm
911401776403	BVP374 60LED 30K 220V 10 150W HP	830 warm white	3000 K	>80	9,830 lm
911401776423	BVP374 60LED 30K 220V 15 150W HP	830 warm white	3000 K	>80	10,245 lm
911401776443	BVP374 60LED 30K 220V 30 150W HP	830 warm white	3000 K	>80	11,630 lm
911401776463	BVP374 60LED 30K 220V 45 150W HP	830 warm white	3000 K	>80	8,720 lm
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	830 warm white	3000 K	>80	8,390 lm
911401776483	BVP374 60LED 30K 220V 60 150W HP	830 warm white	3000 K	>80	8,445 lm

UniFlood C Pro

Order Code	Full Product Name	Light source colour	Correlated	Colour	Luminous Flux
			Colour Temperature (Nom)	rendering index (CRI)	
911401776503	BVP374 60LED	840	4000 K	>80	10,965 lm
	40K 220V 10	neutral			
	150W HP	white			
911401776523	BVP374 60LED	840	4000 K	>80	11,430 lm
	40K 220V 15	neutral			
	150W HP	white			
911401776543	BVP374 60LED	840	4000 K	>80	12,975 lm
	40K 220V 30	neutral			
	150W HP	white			
911401776563	BVP374 60LED	840	4000 K	>80	9,730 lm
	40K 220V 45	neutral			
	150W HP	white			
911401776583	BVP374 60LED	840	4000 K	>80	9,420 lm
	40K 220V 60	neutral			
	150W HP	white			
911401776653	BVP374 60LED	RGBW	-	N.A.	6,635 lm
	RGBNW 220V 10				
	DMX 150W HP				
911401776663	BVP374 60LED	RGBW	-	N.A.	6,920 lm
	RGBNW 220V 15				
	DMX 150W HP				
911401776673	BVP374 60LED	RGBW	-	N.A.	7,855 lm
	RGBNW 220V 30				
	DMX 150W HP				

Order Code	Full Product Name	Light source colour	Correlated	Colour	Luminous Flux
			Colour Temperature (Nom)	rendering index (CRI)	
911401776683	BVP374 60LED	RGBW	-	N.A.	5,890 lm
	RGBNW 220V 45				
	DMX 150W HP				
911401776693	BVP374 60LED	RGBW	-	N.A.	5,700 lm
	RGBNW 220V 60				
	DMX 150W HP				
911401776703	BVP374 60LED	RGBW	-	N.A.	6,370 lm
	RGBWW 220V 10				
	DMX 150W HP				
911401776713	BVP374 60LED	RGBW	-	N.A.	6,640 lm
	RGBWW 220V 15				
	DMX 150W HP				
911401776723	BVP374 60LED	RGBW	-	N.A.	7,535 lm
	RGBWW 220V 30				
	DMX 150W HP				
911401776733	BVP374 60LED	RGBW	-	N.A.	5,650 lm
	RGBWW 220V 45				
	DMX 150W HP				
911401776743	BVP374 60LED	RGBW	-	N.A.	5,470 lm
	RGBWW 220V 60				
	DMX 150W HP				

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401773703	BVP371 12LED 30K 220V 10 24W HE	24 W
911401773723	BVP371 12LED 30K 220V 15 24W HE	24 W
911401773743	BVP371 12LED 30K 220V 30 24W HE	24 W
911401773763	BVP371 12LED 30K 220V 45 24W HE	24 W
911401773783	BVP371 12LED 30K 220V 60 24W HE	24 W
911401773803	BVP371 12LED 40K 220V 10 24W HE	24 W
911401773823	BVP371 12LED 40K 220V 15 24W HE	24 W
911401773843	BVP371 12LED 40K 220V 30 24W HE	24 W
911401773863	BVP371 12LED 40K 220V 45 24W HE	24 W
911401773883	BVP371 12LED 40K 220V 60 24W HE	24 W
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	24 W
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	24 W
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	24 W
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	24 W
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	24 W
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	24 W
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	24 W
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	24 W
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	24 W
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	24 W
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	40 W

Order Code	Full Product Name	Power Consumption
911401774203	BVP372 16LED 30K 220V 10 40W HP	40 W
911401774223	BVP372 16LED 30K 220V 15 40W HP	40 W
911401774243	BVP372 16LED 30K 220V 30 40W HP	40 W
911401774263	BVP372 16LED 30K 220V 45 40W HP	40 W
911401774283	BVP372 16LED 30K 220V 60 40W HP	40 W
911401774303	BVP372 16LED 40K 220V 10 40W HP	40 W
911401774323	BVP372 16LED 40K 220V 15 40W HP	40 W
911401774343	BVP372 16LED 40K 220V 30 40W HP	40 W
911401774363	BVP372 16LED 40K 220V 45 40W HP	40 W
911401774383	BVP372 16LED 40K 220V 60 40W HP	40 W
911401774403	BVP372 16LED RGBNW 220V 10 DMX 40W HP	40 W
911401774413	BVP372 16LED RGBNW 220V 15 DMX 40W HP	40 W
911401774423	BVP372 16LED RGBNW 220V 30 DMX 40W HP	40 W
911401774433	BVP372 16LED RGBNW 220V 45 DMX 40W HP	40 W
911401774443	BVP372 16LED RGBNW 220V 60 DMX 40W HP	40 W
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	40 W
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	40 W
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	40 W
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	40 W
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	40 W
911401774603	BVP372 18LED 30K 220V 10 50W HP	50 W

UniFlood C Pro

Order Code	Full Product Name	Power Consumption
911401774623	BVP372 18LED 30K 220V 15 50W HP	50 W
911401774643	BVP372 18LED 30K 220V 30 50W HP	50 W
911401774663	BVP372 18LED 30K 220V 45 50W HP	50 W
911401774683	BVP372 18LED 30K 220V 60 50W HP	50 W
911401774703	BVP372 18LED 40K 220V 10 50W HP	50 W
911401774723	BVP372 18LED 40K 220V 15 50W HP	50 W
911401774743	BVP372 18LED 40K 220V 30 50W HP	50 W
911401774763	BVP372 18LED 40K 220V 45 50W HP	50 W
911401774783	BVP372 18LED 40K 220V 60 50W HP	50 W
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	50 W
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	50 W
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	50 W
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	50 W
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	50 W
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	50 W
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	50 W
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	50 W
911401775053	BVP373 30LED 30K 220V 10 80W HP	80 W
911401775073	BVP373 30LED 30K 220V 15 80W HP	80 W
911401775093	BVP373 30LED 30K 220V 30 80W HP	80 W
911401775113	BVP373 30LED 30K 220V 45 80W HP	80 W
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	80 W
911401775133	BVP373 30LED 30K 220V 60 80W HP	80 W
911401775153	BVP373 30LED 40K 220V 10 80W HP	80 W
911401775173	BVP373 30LED 40K 220V 15 80W HP	80 W
911401775193	BVP373 30LED 40K 220V 30 80W HP	80 W
911401775213	BVP373 30LED 40K 220V 45 80W HP	80 W
911401775233	BVP373 30LED 40K 220V 60 80W HP	80 W
911401775303	BVP373 32LED RGBNW 220V 10 DMX 80W HP	80 W
911401775313	BVP373 32LED RGBNW 220V 15 DMX 80W HP	80 W
911401775323	BVP373 32LED RGBNW 220V 30 DMX 80W HP	80 W
911401775333	BVP373 32LED RGBNW 220V 45 DMX 80W HP	80 W
911401775343	BVP373 32LED RGBNW 220V 60 DMX 80W HP	80 W
911401775353	BVP373 32LED RGBWW 220V 10 DMX 80W HP	80 W
911401775363	BVP373 32LED RGBWW 220V 15 DMX 80W HP	80 W
911401775373	BVP373 32LED RGBWW 220V 30 DMX 80W HP	80 W
911401775383	BVP373 32LED RGBWW 220V 45 DMX 80W HP	80 W
911401775393	BVP373 32LED RGBWW 220V 60 DMX 80W HP	80 W
911401775503	BVP373 36LED 30K 220V 10 100W HP	100 W
911401775523	BVP373 36LED 30K 220V 15 100W HP	100 W
911401775543	BVP373 36LED 30K 220V 30 100W HP	100 W
911401775563	BVP373 36LED 30K 220V 45 100W HP	100 W
911401775583	BVP373 36LED 30K 220V 60 100W HP	100 W
911401775603	BVP373 36LED 40K 220V 10 100W HP	100 W
911401775623	BVP373 36LED 40K 220V 15 100W HP	100 W
911401775643	BVP373 36LED 40K 220V 30 100W HP	100 W
911401775663	BVP373 36LED 40K 220V 45 100W HP	100 W
911401775683	BVP373 36LED 40K 220V 60 100W HP	100 W
911401775753	BVP373 36LED RGBNW 220V 10 DMX 100W HP	100 W

Order Code	Full Product Name	Power Consumption
911401775763	BVP373 36LED RGBNW 220V 15 DMX 100W HP	100 W
911401775773	BVP373 36LED RGBNW 220V 30 DMX 100W HP	100 W
911401775783	BVP373 36LED RGBNW 220V 45 DMX 100W HP	100 W
911401775793	BVP373 36LED RGBNW 220V 60 DMX 100W HP	100 W
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	100 W
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	100 W
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	100 W
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	100 W
911401775953	BVP374 48LED 30K 220V 10 120W HP	120 W
911401775973	BVP374 48LED 30K 220V 15 120W HP	120 W
911401775993	BVP374 48LED 30K 220V 30 120W HP	120 W
911401776013	BVP374 48LED 30K 220V 45 120W HP	120 W
911401776033	BVP374 48LED 30K 220V 60 120W HP	120 W
911401776053	BVP374 48LED 40K 220V 10 120W HP	120 W
911401776073	BVP374 48LED 40K 220V 15 120W HP	120 W
911401776093	BVP374 48LED 40K 220V 30 120W HP	120 W
911401776113	BVP374 48LED 40K 220V 45 120W HP	120 W
911401776133	BVP374 48LED 40K 220V 60 120W HP	120 W
911401776203	BVP374 48LED RGBNW 220V 10 DMX 120W HP	120 W
911401776213	BVP374 48LED RGBNW 220V 15 DMX 120W HP	120 W
911401776223	BVP374 48LED RGBNW 220V 30 DMX 120W HP	120 W
911401776233	BVP374 48LED RGBNW 220V 45 DMX 120W HP	120 W
911401776243	BVP374 48LED RGBNW 220V 60 DMX 120W HP	120 W
911401776253	BVP374 48LED RGBWW 220V 10 DMX 120W HP	120 W
911401776263	BVP374 48LED RGBWW 220V 15 DMX 120W HP	120 W
911401776273	BVP374 48LED RGBWW 220V 30 DMX 120W HP	120 W
911401776283	BVP374 48LED RGBWW 220V 45 DMX 120W HP	120 W
911401776293	BVP374 48LED RGBWW 220V 60 DMX 120W HP	120 W
911401776403	BVP374 60LED 30K 220V 10 150W HP	150 W
911401776423	BVP374 60LED 30K 220V 15 150W HP	150 W
911401776443	BVP374 60LED 30K 220V 30 150W HP	150 W
911401776463	BVP374 60LED 30K 220V 45 150W HP	150 W
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	150 W
911401776483	BVP374 60LED 30K 220V 60 150W HP	150 W
911401776503	BVP374 60LED 40K 220V 10 150W HP	150 W
911401776523	BVP374 60LED 40K 220V 15 150W HP	150 W
911401776543	BVP374 60LED 40K 220V 30 150W HP	150 W
911401776563	BVP374 60LED 40K 220V 45 150W HP	150 W
911401776583	BVP374 60LED 40K 220V 60 150W HP	150 W
911401776653	BVP374 60LED RGBNW 220V 10 DMX 150W HP	150 W
911401776663	BVP374 60LED RGBNW 220V 15 DMX 150W HP	150 W
911401776673	BVP374 60LED RGBNW 220V 30 DMX 150W HP	150 W
911401776683	BVP374 60LED RGBNW 220V 45 DMX 150W HP	150 W
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
911401776703	BVP374 60LED RGBWW 220V 10 DMX 150W HP	150 W
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W
911401776723	BVP374 60LED RGBWW 220V 30 DMX 150W HP	150 W
911401776733	BVP374 60LED RGBWW 220V 45 DMX 150W HP	150 W
911401776743	BVP374 60LED RGBWW 220V 60 DMX 150W HP	150 W

Controls and Dimming

UniFlood C Pro

Order Code	Full Product Name	Dimmable
911401773703	BVP371 12LED 30K 220V 10 24W HE	No
911401773723	BVP371 12LED 30K 220V 15 24W HE	No
911401773743	BVP371 12LED 30K 220V 30 24W HE	No
911401773763	BVP371 12LED 30K 220V 45 24W HE	No
911401773783	BVP371 12LED 30K 220V 60 24W HE	No
911401773803	BVP371 12LED 40K 220V 10 24W HE	No
911401773823	BVP371 12LED 40K 220V 15 24W HE	No
911401773843	BVP371 12LED 40K 220V 30 24W HE	No
911401773863	BVP371 12LED 40K 220V 45 24W HE	No
911401773883	BVP371 12LED 40K 220V 60 24W HE	No
911401773953	BVP371 12LED RGBNW 220V 10 DMX 24W HE	Yes
911401773963	BVP371 12LED RGBNW 220V 15 DMX 24W HE	Yes
911401773973	BVP371 12LED RGBNW 220V 30 DMX 24W HE	Yes
911401773983	BVP371 12LED RGBNW 220V 45 DMX 24W HE	Yes
911401773993	BVP371 12LED RGBNW 220V 60 DMX 24W HE	Yes
911401774003	BVP371 12LED RGBWW 220V 10 DMX 24W HE	Yes
911401774013	BVP371 12LED RGBWW 220V 15 DMX 24W HE	Yes
911401774023	BVP371 12LED RGBWW 220V 30 DMX 24W HE	Yes
911401774033	BVP371 12LED RGBWW 220V 45 DMX 24W HE	Yes
911401774043	BVP371 12LED RGBWW 220V 60 DMX 24W HE	Yes
911401774083	BVP372 15LED RGB 220V 45 DMX 40W HP	Yes
911401774203	BVP372 16LED 30K 220V 10 40W HP	No
911401774223	BVP372 16LED 30K 220V 15 40W HP	No
911401774243	BVP372 16LED 30K 220V 30 40W HP	No
911401774263	BVP372 16LED 30K 220V 45 40W HP	No
911401774283	BVP372 16LED 30K 220V 60 40W HP	No
911401774303	BVP372 16LED 40K 220V 10 40W HP	No
911401774323	BVP372 16LED 40K 220V 15 40W HP	No
911401774343	BVP372 16LED 40K 220V 30 40W HP	No
911401774363	BVP372 16LED 40K 220V 45 40W HP	No
911401774383	BVP372 16LED 40K 220V 60 40W HP	No
911401774403	BVP372 16LED RGBNW 220V 10 DMX 40W HP	Yes
911401774413	BVP372 16LED RGBNW 220V 15 DMX 40W HP	Yes
911401774423	BVP372 16LED RGBNW 220V 30 DMX 40W HP	Yes
911401774433	BVP372 16LED RGBNW 220V 45 DMX 40W HP	Yes
911401774443	BVP372 16LED RGBNW 220V 60 DMX 40W HP	Yes
911401774453	BVP372 16LED RGBWW 220V 10 DMX 40W HP	Yes
911401774463	BVP372 16LED RGBWW 220V 15 DMX 40W HP	Yes
911401774473	BVP372 16LED RGBWW 220V 30 DMX 40W HP	Yes
911401774483	BVP372 16LED RGBWW 220V 45 DMX 40W HP	Yes
911401774493	BVP372 16LED RGBWW 220V 60 DMX 40W HP	Yes
911401774603	BVP372 18LED 30K 220V 10 50W HP	No
911401774623	BVP372 18LED 30K 220V 15 50W HP	No
911401774643	BVP372 18LED 30K 220V 30 50W HP	No
911401774663	BVP372 18LED 30K 220V 45 50W HP	No
911401774683	BVP372 18LED 30K 220V 60 50W HP	No
911401774703	BVP372 18LED 40K 220V 10 50W HP	No
911401774723	BVP372 18LED 40K 220V 15 50W HP	No
911401774743	BVP372 18LED 40K 220V 30 50W HP	No
911401774763	BVP372 18LED 40K 220V 45 50W HP	No
911401774783	BVP372 18LED 40K 220V 60 50W HP	No
911401774853	BVP372 20LED RGBNW 220V 10 DMX 50W HP	Yes

Order Code	Full Product Name	Dimmable
911401774863	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
911401774873	BVP372 20LED RGBNW 220V 30 DMX 50W HP	Yes
911401774883	BVP372 20LED RGBNW 220V 45 DMX 50W HP	Yes
911401774893	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes
911401774903	BVP372 20LED RGBWW 220V 10 DMX 50W HP	Yes
911401774913	BVP372 20LED RGBWW 220V 15 DMX 50W HP	Yes
911401774923	BVP372 20LED RGBWW 220V 30 DMX 50W HP	Yes
911401774933	BVP372 20LED RGBWW 220V 45 DMX 50W HP	Yes
911401774943	BVP372 20LED RGBWW 220V 60 DMX 50W HP	Yes
911401775053	BVP373 30LED 30K 220V 10 80W HP	No
911401775073	BVP373 30LED 30K 220V 15 80W HP	No
911401775093	BVP373 30LED 30K 220V 30 80W HP	No
911401775113	BVP373 30LED 30K 220V 45 80W HP	No
911401775123	BVP373 30LED 30K 220V 45 DMX 80W HP	Yes
911401775133	BVP373 30LED 30K 220V 60 80W HP	No
911401775153	BVP373 30LED 40K 220V 10 80W HP	No
911401775173	BVP373 30LED 40K 220V 15 80W HP	No
911401775193	BVP373 30LED 40K 220V 30 80W HP	No
911401775213	BVP373 30LED 40K 220V 45 80W HP	No
911401775233	BVP373 30LED 40K 220V 60 80W HP	No
911401775303	BVP373 32LED RGBNW 220V 10 DMX 80W HP	Yes
911401775313	BVP373 32LED RGBNW 220V 15 DMX 80W HP	Yes
911401775323	BVP373 32LED RGBNW 220V 30 DMX 80W HP	Yes
911401775333	BVP373 32LED RGBNW 220V 45 DMX 80W HP	Yes
911401775343	BVP373 32LED RGBNW 220V 60 DMX 80W HP	Yes
911401775353	BVP373 32LED RGBWW 220V 10 DMX 80W HP	Yes
911401775363	BVP373 32LED RGBWW 220V 15 DMX 80W HP	Yes
911401775373	BVP373 32LED RGBWW 220V 30 DMX 80W HP	Yes
911401775383	BVP373 32LED RGBWW 220V 45 DMX 80W HP	Yes
911401775393	BVP373 32LED RGBWW 220V 60 DMX 80W HP	Yes
911401775503	BVP373 36LED 30K 220V 10 100W HP	No
911401775523	BVP373 36LED 30K 220V 15 100W HP	No
911401775543	BVP373 36LED 30K 220V 30 100W HP	No
911401775563	BVP373 36LED 30K 220V 45 100W HP	No
911401775583	BVP373 36LED 30K 220V 60 100W HP	No
911401775603	BVP373 36LED 40K 220V 10 100W HP	No
911401775623	BVP373 36LED 40K 220V 15 100W HP	No
911401775643	BVP373 36LED 40K 220V 30 100W HP	No
911401775663	BVP373 36LED 40K 220V 45 100W HP	No
911401775683	BVP373 36LED 40K 220V 60 100W HP	No
911401775753	BVP373 36LED RGBNW 220V 10 DMX 100W HP	Yes
911401775763	BVP373 36LED RGBNW 220V 15 DMX 100W HP	Yes
911401775773	BVP373 36LED RGBNW 220V 30 DMX 100W HP	Yes
911401775783	BVP373 36LED RGBNW 220V 45 DMX 100W HP	Yes
911401775793	BVP373 36LED RGBNW 220V 60 DMX 100W HP	Yes
911401775803	BVP373 36LED RGBWW 220V 10 DMX 100W HP	Yes
911401775813	BVP373 36LED RGBWW 220V 15 DMX 100W HP	Yes
911401775823	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
911401775833	BVP373 36LED RGBWW 220V 45 DMX 100W HP	Yes
911401775843	BVP373 36LED RGBWW 220V 60 DMX 100W HP	Yes
911401775953	BVP374 48LED 30K 220V 10 120W HP	No
911401775973	BVP374 48LED 30K 220V 15 120W HP	No

UniFlood C Pro

Order Code	Full Product Name	Dimmable
911401775993	BVP374 48LED 30K 220V 30 120W HP	No
911401776013	BVP374 48LED 30K 220V 45 120W HP	No
911401776033	BVP374 48LED 30K 220V 60 120W HP	No
911401776053	BVP374 48LED 40K 220V 10 120W HP	No
911401776073	BVP374 48LED 40K 220V 15 120W HP	No
911401776093	BVP374 48LED 40K 220V 30 120W HP	No
911401776113	BVP374 48LED 40K 220V 45 120W HP	No
911401776133	BVP374 48LED 40K 220V 60 120W HP	No
911401776203	BVP374 48LED RGBNW 220V 10 DMX 120W HP	Yes
911401776213	BVP374 48LED RGBNW 220V 15 DMX 120W HP	Yes
911401776223	BVP374 48LED RGBNW 220V 30 DMX 120W HP	Yes
911401776233	BVP374 48LED RGBNW 220V 45 DMX 120W HP	Yes
911401776243	BVP374 48LED RGBNW 220V 60 DMX 120W HP	Yes
911401776253	BVP374 48LED RGBWW 220V 10 DMX 120W HP	Yes
911401776263	BVP374 48LED RGBWW 220V 15 DMX 120W HP	Yes
911401776273	BVP374 48LED RGBWW 220V 30 DMX 120W HP	Yes
911401776283	BVP374 48LED RGBWW 220V 45 DMX 120W HP	Yes
911401776293	BVP374 48LED RGBWW 220V 60 DMX 120W HP	Yes
911401776403	BVP374 60LED 30K 220V 10 150W HP	No
911401776423	BVP374 60LED 30K 220V 15 150W HP	No

Order Code	Full Product Name	Dimmable
911401776443	BVP374 60LED 30K 220V 30 150W HP	No
911401776463	BVP374 60LED 30K 220V 45 150W HP	No
911401776473	BVP374 60LED 30K 220V 45 DMX 150W HP	Yes
911401776483	BVP374 60LED 30K 220V 60 150W HP	No
911401776503	BVP374 60LED 40K 220V 10 150W HP	No
911401776523	BVP374 60LED 40K 220V 15 150W HP	No
911401776543	BVP374 60LED 40K 220V 30 150W HP	No
911401776563	BVP374 60LED 40K 220V 45 150W HP	No
911401776583	BVP374 60LED 40K 220V 60 150W HP	No
911401776653	BVP374 60LED RGBNW 220V 10 DMX 150W HP	Yes
911401776663	BVP374 60LED RGBNW 220V 15 DMX 150W HP	Yes
911401776673	BVP374 60LED RGBNW 220V 30 DMX 150W HP	Yes
911401776683	BVP374 60LED RGBNW 220V 45 DMX 150W HP	Yes
911401776693	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
911401776703	BVP374 60LED RGBWW 220V 10 DMX 150W HP	Yes
911401776713	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes
911401776723	BVP374 60LED RGBWW 220V 30 DMX 150W HP	Yes
911401776733	BVP374 60LED RGBWW 220V 45 DMX 150W HP	Yes
911401776743	BVP374 60LED RGBWW 220V 60 DMX 150W HP	Yes

