



Architectural LED floodlight for fixed or dynamic lighting

UniFlood C Pro

The Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is a compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, the Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-storey exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colours, multiple spread lenses and a DMX512/RDM control option.

Benefits

- Available in white, monochromatic colors, RGB, RGBW and tunable white
- Wide range of beam angles from Narrow Spot to Wide Flood
- Available in DMX512/RDM control interface option

Features

- Robust design, IP66 rated for outdoor use
- Optical distributions: 3.5°, 10°, 15°, 30°, 45° and 60°
- Adjustable ±90° tilting angle
- Through wiring for the DMX signal via dedicated cables with IP67 connectors

UniFlood C Pro


Application

- Bridges, Monuments, Façades
- Landscape
- Parks and squares

Warnings and Safety

- For outdoor use only

Dimensional drawing



General Information	
Driver included	Yes
Mechanical and Housing	
Optical cover type	Clear glass
Housing Colour	Dark grey
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50352699	BVP371 12LED 30K 220V 10 24W HE	830 warm white	3000 K	>80	1,635 lm
50354099	BVP371 12LED 30K 220V 15 24W HE	830 warm white	3000 K	>80	1,705 lm
50356499	BVP371 12LED 30K 220V 30 24W HE	830 warm white	3000 K	>80	1,935 lm
50358899	BVP371 12LED 30K 220V 45 24W HE	830 warm white	3000 K	>80	1,450 lm
50360199	BVP371 12LED 30K 220V 60 24W HE	830 warm white	3000 K	>80	1,405 lm
50362599	BVP371 12LED 40K 220V 10 24W HE	840 neutral white	4000 K	>80	1,825 lm
50364999	BVP371 12LED 40K 220V 15 24W HE	840 neutral white	4000 K	>80	1,905 lm
50366399	BVP371 12LED 40K 220V 30 24W HE	840 neutral white	4000 K	>80	2,160 lm
50368799	BVP371 12LED 40K 220V 45 24W HE	840 neutral white	4000 K	>80	1,620 lm
50370099	BVP371 12LED 40K 220V 60 24W HE	840 neutral white	4000 K	>80	1,570 lm
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,090 lm
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,140 lm
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,290 lm
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	RGBW	-	N.A.	970 lm
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	RGBW	-	N.A.	940 lm
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	RGBW	-	N.A.	1,045 lm
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	RGBW	-	N.A.	1,090 lm
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	RGBW	-	N.A.	1,235 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	RGBW	-	N.A.	925 lm
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	RGBW	-	N.A.	900 lm
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	RGB	-	N.A.	1,150 lm
50402899	BVP372 16LED 30K 220V 10 40W HP	830 warm white	3000 K	>80	2,570 lm
50404299	BVP372 16LED 30K 220V 15 40W HP	830 warm white	3000 K	>80	2,680 lm
50406699	BVP372 16LED 30K 220V 30 40W HP	830 warm white	3000 K	>80	3,040 lm
50408099	BVP372 16LED 30K 220V 45 40W HP	830 warm white	3000 K	>80	2,280 lm
50410399	BVP372 16LED 30K 220V 60 40W HP	830 warm white	3000 K	>80	2,210 lm
50412799	BVP372 16LED 40K 220V 10 40W HP	840 neutral white	4000 K	>80	2,870 lm
50414199	BVP372 16LED 40K 220V 15 40W HP	840 neutral white	4000 K	>80	2,990 lm
50416599	BVP372 16LED 40K 220V 30 40W HP	840 neutral white	4000 K	>80	3,395 lm
50418999	BVP372 16LED 40K 220V 45 40W HP	840 neutral white	4000 K	>80	2,545 lm
50420299	BVP372 16LED 40K 220V 60 40W HP	840 neutral white	4000 K	>80	2,465 lm
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,580 lm
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,650 lm
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,870 lm
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,400 lm
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,360 lm

Order Code	Full Product Name	Light	Correlated	Colour	Luminous
		source	Colour	rendering	
		colour	Temperature	index (CRI)	Flux
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	RGBW	-	N.A.	1,515 lm
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	RGBW	-	N.A.	1,575 lm
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	RGBW	-	N.A.	1,790 lm
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	RGBW	-	N.A.	1,340 lm
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	RGBW	-	N.A.	1,300 lm
50442499	BVP372 18LED 30K 220V 10 50W HP	830 warm white	3000 K	>80	3,070 lm
50444899	BVP372 18LED 30K 220V 15 50W HP	830 warm white	3000 K	>80	3,200 lm
50446299	BVP372 18LED 30K 220V 30 50W HP	830 warm white	3000 K	>80	3,635 lm
50448699	BVP372 18LED 30K 220V 45 50W HP	830 warm white	3000 K	>80	2,725 lm
50450999	BVP372 18LED 30K 220V 60 50W HP	830 warm white	3000 K	>80	2,640 lm
50452399	BVP372 18LED 40K 220V 10 50W HP	840 neutral white	4000 K	>80	3,430 lm
50454799	BVP372 18LED 40K 220V 15 50W HP	840 neutral white	4000 K	>80	3,575 lm
50456199	BVP372 18LED 40K 220V 30 50W HP	840 neutral white	4000 K	>80	4,055 lm
50458599	BVP372 18LED 40K 220V 45 50W HP	840 neutral white	4000 K	>80	3,040 lm
50460899	BVP372 18LED 40K 220V 60 50W HP	840 neutral white	4000 K	>80	2,945 lm
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,140 lm
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,230 lm
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,530 lm

Order Code	Full Product Name	Light	Correlated	Colour	Luminous
		source	Colour	rendering	
		colour	Temperature	index (CRI)	Flux
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,895 lm
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,835 lm
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	RGBW	-	N.A.	2,045 lm
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	RGBW	-	N.A.	2,130 lm
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	RGBW	-	N.A.	2,420 lm
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	RGBW	-	N.A.	1,815 lm
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	RGBW	-	N.A.	1,755 lm
50487599	BVP373 30LED 30K 220V 10 80W HP	830 warm white	3000 K	>80	5,160 lm
50489999	BVP373 30LED 30K 220V 15 80W HP	830 warm white	3000 K	>80	5,375 lm
50491299	BVP373 30LED 30K 220V 30 80W HP	830 warm white	3000 K	>80	6,100 lm
50493699	BVP373 30LED 30K 220V 45 80W HP	830 warm white	3000 K	>80	4,575 lm
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	830 warm white	3000 K	>80	4,295 lm
50495099	BVP373 30LED 30K 220V 60 80W HP	830 warm white	3000 K	>80	4,430 lm
50497499	BVP373 30LED 40K 220V 10 80W HP	840 neutral white	4000 K	>80	5,755 lm
50499899	BVP373 30LED 40K 220V 15 80W HP	840 neutral white	4000 K	>80	6,000 lm
50501899	BVP373 30LED 40K 220V 30 80W HP	840 neutral white	4000 K	>80	6,810 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50503299	BVP373 30LED 40K 220V 45 80W HP	840 neutral white	4000 K	>80	5,105 lm
50505699	BVP373 30LED 40K 220V 60 80W HP	840 neutral white	4000 K	>80	4,945 lm
50512499	BVP373 32LED RGBW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,520 lm
50513199	BVP373 32LED RGBW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,670 lm
50514899	BVP373 32LED RGBW 220V 30 DMX 80W HP	RGBW	-	N.A.	4,170 lm
50515599	BVP373 32LED RGBW 220V 45 DMX 80W HP	RGBW	-	N.A.	3,125 lm
50516299	BVP373 32LED RGBW 220V 60 DMX 80W HP	RGBW	-	N.A.	3,025 lm
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	RGBW	-	N.A.	3,370 lm
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	RGBW	-	N.A.	3,515 lm
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	RGBW	-	N.A.	3,990 lm
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	RGBW	-	N.A.	2,990 lm
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	RGBW	-	N.A.	2,895 lm
50532299	BVP373 36LED 30K 220V 10 100W HP	830 warm white	3000 K	>80	6,445 lm
50534699	BVP373 36LED 30K 220V 15 100W HP	830 warm white	3000 K	>80	6,715 lm
50536099	BVP373 36LED 30K 220V 30 100W HP	830 warm white	3000 K	>80	7,625 lm
50538499	BVP373 36LED 30K 220V 45 100W HP	830 warm white	3000 K	>80	5,715 lm
50540799	BVP373 36LED 30K 220V 60 100W HP	830 warm white	3000 K	>80	5,535 lm
50542199	BVP373 36LED 40K 220V 10 100W HP	840 neutral white	4000 K	>80	7,190 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50544599	BVP373 36LED 40K 220V 15 100W HP	840 neutral white	4000 K	>80	7,495 lm
50546999	BVP373 36LED 40K 220V 30 100W HP	840 neutral white	4000 K	>80	8,505 lm
50548399	BVP373 36LED 40K 220V 45 100W HP	840 neutral white	4000 K	>80	6,380 lm
50550699	BVP373 36LED 40K 220V 60 100W HP	840 neutral white	4000 K	>80	6,175 lm
50557599	BVP373 36LED RGBW 220V 10 DMX 100W HP	RGBW	-	N.A.	4,175 lm
50558299	BVP373 36LED RGBW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,355 lm
50559999	BVP373 36LED RGBW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,945 lm
50560599	BVP373 36LED RGBW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,705 lm
50561299	BVP373 36LED RGBW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,590 lm
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	RGBW	-	N.A.	3,995 lm
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	RGBW	-	N.A.	4,165 lm
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	RGBW	-	N.A.	4,730 lm
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	RGBW	-	N.A.	3,545 lm
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	RGBW	-	N.A.	3,435 lm
50577399	BVP374 48LED 30K 220V 10 120W HP	830 warm white	3000 K	>80	7,865 lm
50579799	BVP374 48LED 30K 220V 15 120W HP	830 warm white	3000 K	>80	8,195 lm
50581099	BVP374 48LED 30K 220V 30 120W HP	830 warm white	3000 K	>80	9,305 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50583499	BVP374 48LED 30K 220V 45 120W HP	830 warm white	3000 K	>80	6,975 lm
50585899	BVP374 48LED 30K 220V 60 120W HP	830 warm white	3000 K	>80	6,755 lm
50587299	BVP374 48LED 40K 220V 10 120W HP	840 neutral white	4000 K	>80	8,775 lm
50589699	BVP374 48LED 40K 220V 15 120W HP	840 neutral white	4000 K	>80	9,145 lm
50591999	BVP374 48LED 40K 220V 30 120W HP	840 neutral white	4000 K	>80	10,380 lm
50593399	BVP374 48LED 40K 220V 45 120W HP	840 neutral white	4000 K	>80	7,785 lm
50595799	BVP374 48LED 40K 220V 60 120W HP	840 neutral white	4000 K	>80	7,535 lm
50602299	BVP374 48LED RGBW RGBNW 220V 10 DMX 120W HP	RGBW	-	N.A.	5,165 lm
50603999	BVP374 48LED RGBW RGBNW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,380 lm
50604699	BVP374 48LED RGBW RGBNW 220V 30 DMX 120W HP	RGBW	-	N.A.	6,110 lm
50605399	BVP374 48LED RGBW RGBNW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,580 lm
50606099	BVP374 48LED RGBW RGBNW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,435 lm
50607799	BVP374 48LED RGBW RGBWW 220V 10 DMX 120W HP	RGBW	-	N.A.	4,940 lm
50608499	BVP374 48LED RGBW RGBWW 220V 15 DMX 120W HP	RGBW	-	N.A.	5,150 lm
50609199	BVP374 48LED RGBW RGBWW 220V 30 DMX 120W HP	RGBW	-	N.A.	5,845 lm
50610799	BVP374 48LED RGBW RGBWW 220V 45 DMX 120W HP	RGBW	-	N.A.	4,385 lm
50611499	BVP374 48LED RGBW RGBWW 220V 60 DMX 120W HP	RGBW	-	N.A.	4,245 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50622099	BVP374 60LED 30K 220V 10 150W HP	830 warm white	3000 K	>80	9,830 lm
50624499	BVP374 60LED 30K 220V 15 150W HP	830 warm white	3000 K	>80	10,245 lm
50626899	BVP374 60LED 30K 220V 30 150W HP	830 warm white	3000 K	>80	11,630 lm
50628299	BVP374 60LED 30K 220V 45 150W HP	830 warm white	3000 K	>80	8,720 lm
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	830 warm white	3000 K	>80	8,390 lm
50630599	BVP374 60LED 30K 220V 60 150W HP	830 warm white	3000 K	>80	8,445 lm
50632999	BVP374 60LED 40K 220V 10 150W HP	840 neutral white	4000 K	>80	10,965 lm
50634399	BVP374 60LED 40K 220V 15 150W HP	840 neutral white	4000 K	>80	11,430 lm
50636799	BVP374 60LED 40K 220V 30 150W HP	840 neutral white	4000 K	>80	12,975 lm
50638199	BVP374 60LED 40K 220V 45 150W HP	840 neutral white	4000 K	>80	9,730 lm
50640499	BVP374 60LED 40K 220V 60 150W HP	840 neutral white	4000 K	>80	9,420 lm
50647399	BVP374 60LED RGBW RGBNW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,635 lm
50648099	BVP374 60LED RGBW RGBNW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,920 lm
50649799	BVP374 60LED RGBW RGBNW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,855 lm
50650399	BVP374 60LED RGBW RGBNW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,890 lm
50651099	BVP374 60LED RGBW RGBNW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,700 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	RGBW	-	N.A.	6,370 lm
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	RGBW	-	N.A.	6,640 lm
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	RGBW	-	N.A.	7,535 lm

Order Code	Full Product Name	Light	Correlated	Colour rendering index (CRI)	Luminous Flux
		source colour	Colour Temperature (Nom)		
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	RGBW	-	N.A.	5,650 lm
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	RGBW	-	N.A.	5,470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
50352699	BVP371 12LED 30K 220V 10 24W HE	24 W
50354099	BVP371 12LED 30K 220V 15 24W HE	24 W
50356499	BVP371 12LED 30K 220V 30 24W HE	24 W
50358899	BVP371 12LED 30K 220V 45 24W HE	24 W
50360199	BVP371 12LED 30K 220V 60 24W HE	24 W
50362599	BVP371 12LED 40K 220V 10 24W HE	24 W
50364999	BVP371 12LED 40K 220V 15 24W HE	24 W
50366399	BVP371 12LED 40K 220V 30 24W HE	24 W
50368799	BVP371 12LED 40K 220V 45 24W HE	24 W
50370099	BVP371 12LED 40K 220V 60 24W HE	24 W
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	24 W
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	24 W
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	24 W
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	24 W
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	24 W
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	24 W
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	24 W
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	24 W
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	24 W
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	24 W
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	40 W
50402899	BVP372 16LED 30K 220V 10 40W HP	40 W
50404299	BVP372 16LED 30K 220V 15 40W HP	40 W
50406699	BVP372 16LED 30K 220V 30 40W HP	40 W
50408099	BVP372 16LED 30K 220V 45 40W HP	40 W
50410399	BVP372 16LED 30K 220V 60 40W HP	40 W
50412799	BVP372 16LED 40K 220V 10 40W HP	40 W
50414199	BVP372 16LED 40K 220V 15 40W HP	40 W
50416599	BVP372 16LED 40K 220V 30 40W HP	40 W
50418999	BVP372 16LED 40K 220V 45 40W HP	40 W
50420299	BVP372 16LED 40K 220V 60 40W HP	40 W
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	40 W
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	40 W
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	40 W
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	40 W
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	40 W

Order Code	Full Product Name	Power Consumption
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	40 W
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	40 W
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	40 W
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	40 W
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	40 W
50442499	BVP372 18LED 30K 220V 10 50W HP	50 W
50444899	BVP372 18LED 30K 220V 15 50W HP	50 W
50446299	BVP372 18LED 30K 220V 30 50W HP	50 W
50448699	BVP372 18LED 30K 220V 45 50W HP	50 W
50450999	BVP372 18LED 30K 220V 60 50W HP	50 W
50452399	BVP372 18LED 40K 220V 10 50W HP	50 W
50454799	BVP372 18LED 40K 220V 15 50W HP	50 W
50456199	BVP372 18LED 40K 220V 30 50W HP	50 W
50458599	BVP372 18LED 40K 220V 45 50W HP	50 W
50460899	BVP372 18LED 40K 220V 60 50W HP	50 W
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	50 W
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	50 W
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	50 W
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	50 W
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	50 W
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	50 W
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	50 W
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	50 W
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	50 W
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	50 W
50487599	BVP373 30LED 30K 220V 10 80W HP	80 W
50489999	BVP373 30LED 30K 220V 15 80W HP	80 W
50491299	BVP373 30LED 30K 220V 30 80W HP	80 W
50493699	BVP373 30LED 30K 220V 45 80W HP	80 W
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	80 W
50495099	BVP373 30LED 30K 220V 60 80W HP	80 W
50497499	BVP373 30LED 40K 220V 10 80W HP	80 W
50499899	BVP373 30LED 40K 220V 15 80W HP	80 W
50501899	BVP373 30LED 40K 220V 30 80W HP	80 W
50503299	BVP373 30LED 40K 220V 45 80W HP	80 W
50505699	BVP373 30LED 40K 220V 60 80W HP	80 W

Order Code	Full Product Name	Power Consumption
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	80 W
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	80 W
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	80 W
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	80 W
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	80 W
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	80 W
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	80 W
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	80 W
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	80 W
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	80 W
50532299	BVP373 36LED 30K 220V 10 100W HP	100 W
50534699	BVP373 36LED 30K 220V 15 100W HP	100 W
50536099	BVP373 36LED 30K 220V 30 100W HP	100 W
50538499	BVP373 36LED 30K 220V 45 100W HP	100 W
50540799	BVP373 36LED 30K 220V 60 100W HP	100 W
50542199	BVP373 36LED 40K 220V 10 100W HP	100 W
50544599	BVP373 36LED 40K 220V 15 100W HP	100 W
50546999	BVP373 36LED 40K 220V 30 100W HP	100 W
50548399	BVP373 36LED 40K 220V 45 100W HP	100 W
50550699	BVP373 36LED 40K 220V 60 100W HP	100 W
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	100 W
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	100 W
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	100 W
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	100 W
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	100 W
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	100 W
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	100 W
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	100 W
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	100 W
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	100 W
50577399	BVP374 48LED 30K 220V 10 120W HP	120 W
50579799	BVP374 48LED 30K 220V 15 120W HP	120 W
50581099	BVP374 48LED 30K 220V 30 120W HP	120 W
50583499	BVP374 48LED 30K 220V 45 120W HP	120 W
50585899	BVP374 48LED 30K 220V 60 120W HP	120 W
50587299	BVP374 48LED 40K 220V 10 120W HP	120 W

Order Code	Full Product Name	Power Consumption
50589699	BVP374 48LED 40K 220V 15 120W HP	120 W
50591999	BVP374 48LED 40K 220V 30 120W HP	120 W
50593399	BVP374 48LED 40K 220V 45 120W HP	120 W
50595799	BVP374 48LED 40K 220V 60 120W HP	120 W
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	120 W
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	120 W
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	120 W
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	120 W
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	120 W
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	120 W
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	120 W
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	120 W
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	120 W
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	120 W
50622099	BVP374 60LED 30K 220V 10 150W HP	150 W
50624499	BVP374 60LED 30K 220V 15 150W HP	150 W
50626899	BVP374 60LED 30K 220V 30 150W HP	150 W
50628299	BVP374 60LED 30K 220V 45 150W HP	150 W
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	150 W
50630599	BVP374 60LED 30K 220V 60 150W HP	150 W
50632999	BVP374 60LED 40K 220V 10 150W HP	150 W
50634399	BVP374 60LED 40K 220V 15 150W HP	150 W
50636799	BVP374 60LED 40K 220V 30 150W HP	150 W
50638199	BVP374 60LED 40K 220V 45 150W HP	150 W
50640499	BVP374 60LED 40K 220V 60 150W HP	150 W
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	150 W
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	150 W
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	150 W
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	150 W
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	150 W
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	150 W
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	150 W
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	150 W
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	150 W
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	150 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
50352699	BVP371 12LED 30K 220V 10 24W HE	No
50354099	BVP371 12LED 30K 220V 15 24W HE	No
50356499	BVP371 12LED 30K 220V 30 24W HE	No
50358899	BVP371 12LED 30K 220V 45 24W HE	No
50360199	BVP371 12LED 30K 220V 60 24W HE	No
50362599	BVP371 12LED 40K 220V 10 24W HE	No
50364999	BVP371 12LED 40K 220V 15 24W HE	No
50366399	BVP371 12LED 40K 220V 30 24W HE	No
50368799	BVP371 12LED 40K 220V 45 24W HE	No
50370099	BVP371 12LED 40K 220V 60 24W HE	No
50377999	BVP371 12LED RGBNW 220V 10 DMX 24W HE	Yes
50378699	BVP371 12LED RGBNW 220V 15 DMX 24W HE	Yes

Order Code	Full Product Name	Dimmable
50379399	BVP371 12LED RGBNW 220V 30 DMX 24W HE	Yes
50380999	BVP371 12LED RGBNW 220V 45 DMX 24W HE	Yes
50381699	BVP371 12LED RGBNW 220V 60 DMX 24W HE	Yes
50382399	BVP371 12LED RGBWW 220V 10 DMX 24W HE	Yes
50383099	BVP371 12LED RGBWW 220V 15 DMX 24W HE	Yes
50384799	BVP371 12LED RGBWW 220V 30 DMX 24W HE	Yes
50385499	BVP371 12LED RGBWW 220V 45 DMX 24W HE	Yes
50386199	BVP371 12LED RGBWW 220V 60 DMX 24W HE	Yes
50390899	BVP372 15LED RGB 220V 45 DMX 40W HP	Yes
50402899	BVP372 16LED 30K 220V 10 40W HP	No
50404299	BVP372 16LED 30K 220V 15 40W HP	No
50406699	BVP372 16LED 30K 220V 30 40W HP	No

Order Code	Full Product Name	Dimmable
50408099	BVP372 16LED 30K 220V 45 40W HP	No
50410399	BVP372 16LED 30K 220V 60 40W HP	No
50412799	BVP372 16LED 40K 220V 10 40W HP	No
50414199	BVP372 16LED 40K 220V 15 40W HP	No
50416599	BVP372 16LED 40K 220V 30 40W HP	No
50418999	BVP372 16LED 40K 220V 45 40W HP	No
50420299	BVP372 16LED 40K 220V 60 40W HP	No
50422699	BVP372 16LED RGBNW 220V 10 DMX 40W HP	Yes
50423399	BVP372 16LED RGBNW 220V 15 DMX 40W HP	Yes
50424099	BVP372 16LED RGBNW 220V 30 DMX 40W HP	Yes
50425799	BVP372 16LED RGBNW 220V 45 DMX 40W HP	Yes
50426499	BVP372 16LED RGBNW 220V 60 DMX 40W HP	Yes
50427199	BVP372 16LED RGBWW 220V 10 DMX 40W HP	Yes
50428899	BVP372 16LED RGBWW 220V 15 DMX 40W HP	Yes
50429599	BVP372 16LED RGBWW 220V 30 DMX 40W HP	Yes
50430199	BVP372 16LED RGBWW 220V 45 DMX 40W HP	Yes
50431899	BVP372 16LED RGBWW 220V 60 DMX 40W HP	Yes
50442499	BVP372 18LED 30K 220V 10 50W HP	No
50444899	BVP372 18LED 30K 220V 15 50W HP	No
50446299	BVP372 18LED 30K 220V 30 50W HP	No
50448699	BVP372 18LED 30K 220V 45 50W HP	No
50450999	BVP372 18LED 30K 220V 60 50W HP	No
50452399	BVP372 18LED 40K 220V 10 50W HP	No
50454799	BVP372 18LED 40K 220V 15 50W HP	No
50456199	BVP372 18LED 40K 220V 30 50W HP	No
50458599	BVP372 18LED 40K 220V 45 50W HP	No
50460899	BVP372 18LED 40K 220V 60 50W HP	No
50467799	BVP372 20LED RGBNW 220V 10 DMX 50W HP	Yes
50468499	BVP372 20LED RGBNW 220V 15 DMX 50W HP	Yes
50469199	BVP372 20LED RGBNW 220V 30 DMX 50W HP	Yes
50470799	BVP372 20LED RGBNW 220V 45 DMX 50W HP	Yes
50471499	BVP372 20LED RGBNW 220V 60 DMX 50W HP	Yes
50472199	BVP372 20LED RGBWW 220V 10 DMX 50W HP	Yes
50473899	BVP372 20LED RGBWW 220V 15 DMX 50W HP	Yes
50474599	BVP372 20LED RGBWW 220V 30 DMX 50W HP	Yes
50475299	BVP372 20LED RGBWW 220V 45 DMX 50W HP	Yes
50476999	BVP372 20LED RGBWW 220V 60 DMX 50W HP	Yes
50487599	BVP373 30LED 30K 220V 10 80W HP	No
50489999	BVP373 30LED 30K 220V 15 80W HP	No
50491299	BVP373 30LED 30K 220V 30 80W HP	No
50493699	BVP373 30LED 30K 220V 45 80W HP	No
50494399	BVP373 30LED 30K 220V 45 DMX 80W HP	Yes
50495099	BVP373 30LED 30K 220V 60 80W HP	No
50497499	BVP373 30LED 40K 220V 10 80W HP	No
50499899	BVP373 30LED 40K 220V 15 80W HP	No
50501899	BVP373 30LED 40K 220V 30 80W HP	No
50503299	BVP373 30LED 40K 220V 45 80W HP	No
50505699	BVP373 30LED 40K 220V 60 80W HP	No
50512499	BVP373 32LED RGBNW 220V 10 DMX 80W HP	Yes
50513199	BVP373 32LED RGBNW 220V 15 DMX 80W HP	Yes
50514899	BVP373 32LED RGBNW 220V 30 DMX 80W HP	Yes
50515599	BVP373 32LED RGBNW 220V 45 DMX 80W HP	Yes

Order Code	Full Product Name	Dimmable
50516299	BVP373 32LED RGBNW 220V 60 DMX 80W HP	Yes
50517999	BVP373 32LED RGBWW 220V 10 DMX 80W HP	Yes
50518699	BVP373 32LED RGBWW 220V 15 DMX 80W HP	Yes
50519399	BVP373 32LED RGBWW 220V 30 DMX 80W HP	Yes
50520999	BVP373 32LED RGBWW 220V 45 DMX 80W HP	Yes
50521699	BVP373 32LED RGBWW 220V 60 DMX 80W HP	Yes
50532299	BVP373 36LED 30K 220V 10 100W HP	No
50534699	BVP373 36LED 30K 220V 15 100W HP	No
50536099	BVP373 36LED 30K 220V 30 100W HP	No
50538499	BVP373 36LED 30K 220V 45 100W HP	No
50540799	BVP373 36LED 30K 220V 60 100W HP	No
50542199	BVP373 36LED 40K 220V 10 100W HP	No
50544599	BVP373 36LED 40K 220V 15 100W HP	No
50546999	BVP373 36LED 40K 220V 30 100W HP	No
50548399	BVP373 36LED 40K 220V 45 100W HP	No
50550699	BVP373 36LED 40K 220V 60 100W HP	No
50557599	BVP373 36LED RGBNW 220V 10 DMX 100W HP	Yes
50558299	BVP373 36LED RGBNW 220V 15 DMX 100W HP	Yes
50559999	BVP373 36LED RGBNW 220V 30 DMX 100W HP	Yes
50560599	BVP373 36LED RGBNW 220V 45 DMX 100W HP	Yes
50561299	BVP373 36LED RGBNW 220V 60 DMX 100W HP	Yes
50562999	BVP373 36LED RGBWW 220V 10 DMX 100W HP	Yes
50563699	BVP373 36LED RGBWW 220V 15 DMX 100W HP	Yes
50564399	BVP373 36LED RGBWW 220V 30 DMX 100W HP	Yes
50565099	BVP373 36LED RGBWW 220V 45 DMX 100W HP	Yes
50566799	BVP373 36LED RGBWW 220V 60 DMX 100W HP	Yes
50577399	BVP374 48LED 30K 220V 10 120W HP	No
50579799	BVP374 48LED 30K 220V 15 120W HP	No
50581099	BVP374 48LED 30K 220V 30 120W HP	No
50583499	BVP374 48LED 30K 220V 45 120W HP	No
50585899	BVP374 48LED 30K 220V 60 120W HP	No
50587299	BVP374 48LED 40K 220V 10 120W HP	No
50589699	BVP374 48LED 40K 220V 15 120W HP	No
50591999	BVP374 48LED 40K 220V 30 120W HP	No
50593399	BVP374 48LED 40K 220V 45 120W HP	No
50595799	BVP374 48LED 40K 220V 60 120W HP	No
50602299	BVP374 48LED RGBNW 220V 10 DMX 120W HP	Yes
50603999	BVP374 48LED RGBNW 220V 15 DMX 120W HP	Yes
50604699	BVP374 48LED RGBNW 220V 30 DMX 120W HP	Yes
50605399	BVP374 48LED RGBNW 220V 45 DMX 120W HP	Yes
50606099	BVP374 48LED RGBNW 220V 60 DMX 120W HP	Yes
50607799	BVP374 48LED RGBWW 220V 10 DMX 120W HP	Yes
50608499	BVP374 48LED RGBWW 220V 15 DMX 120W HP	Yes
50609199	BVP374 48LED RGBWW 220V 30 DMX 120W HP	Yes
50610799	BVP374 48LED RGBWW 220V 45 DMX 120W HP	Yes
50611499	BVP374 48LED RGBWW 220V 60 DMX 120W HP	Yes
50622099	BVP374 60LED 30K 220V 10 150W HP	No
50624499	BVP374 60LED 30K 220V 15 150W HP	No
50626899	BVP374 60LED 30K 220V 30 150W HP	No
50628299	BVP374 60LED 30K 220V 45 150W HP	No
50629999	BVP374 60LED 30K 220V 45 DMX 150W HP	Yes
50630599	BVP374 60LED 30K 220V 60 150W HP	No

UniFlood C Pro

Order Code	Full Product Name	Dimmable
50632999	BVP374 60LED 40K 220V 10 150W HP	No
50634399	BVP374 60LED 40K 220V 15 150W HP	No
50636799	BVP374 60LED 40K 220V 30 150W HP	No
50638199	BVP374 60LED 40K 220V 45 150W HP	No
50640499	BVP374 60LED 40K 220V 60 150W HP	No
50647399	BVP374 60LED RGBNW 220V 10 DMX 150W HP	Yes
50648099	BVP374 60LED RGBNW 220V 15 DMX 150W HP	Yes
50649799	BVP374 60LED RGBNW 220V 30 DMX 150W HP	Yes

Order Code	Full Product Name	Dimmable
50650399	BVP374 60LED RGBNW 220V 45 DMX 150W HP	Yes
50651099	BVP374 60LED RGBNW 220V 60 DMX 150W HP	Yes
50652799	BVP374 60LED RGBWW 220V 10 DMX 150W HP	Yes
50653499	BVP374 60LED RGBWW 220V 15 DMX 150W HP	Yes
50654199	BVP374 60LED RGBWW 220V 30 DMX 150W HP	Yes
50655899	BVP374 60LED RGBWW 220V 45 DMX 150W HP	Yes
50656599	BVP374 60LED RGBWW 220V 60 DMX 150W HP	Yes

