



Sophisticated and compact outdoor spotlight

UniSpot

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Benefits

- Sleek and minimalist design, suitable for diverse application scenarios
- A variety of optics and color selections
- Multiple mounting methods suitable for different lighting applications





Features

- Standard: RGB+3000K, RGB+4000K, RGB, 3000K, and 4000K
- Optional 2200K, 2700K, 3500K, 5000K, 5700K, 6500K, monochrome, and RGB +5700K,
- Wide range of beam angles, from narrow spot to wide flood
- Robust design with IP66 rating for outdoor use
- Adjustable vertical 130° and horizontal 340° tilting angle range

Application

- Bridges, Monuments, Facades
- Municipal Buildings
- Parks and Plazas

Dimensional drawing



Light Technical

Color rendering index (CRI) >80

Mechanical and Housing

Optical cover type Clear glass

Housing Color Dark gray

Mech. impact protection code IK06

Ingress protection code IP66

Approval and Application

CE mark Yes

General Information

Order Code	Full Product Name	Driver included
911401733424	BVP378 4LED 30K 220V 20 50W COB	Yes
911401733434	BVP378 4LED 40K 220V 20 50W COB	Yes
911401733444	BVP378 4LED 30K 220V 25 50W COB	Yes
911401733454	BVP378 4LED 40K 220V 25 50W COB	Yes
911401733464	BVP378 4LED 30K 220V 35 50W COB	Yes
911401733474	BVP378 4LED 40K 220V 35 50W COB	Yes
911401733524	BVP378 4LED 30K 220V 20 RDM 50W COB	Yes
911401733534	BVP378 4LED 40K 220V 20 RDM 50W COB	Yes
911401733544	BVP378 4LED 30K 220V 25 RDM 50W COB	Yes
911401733554	BVP378 4LED 40K 220V 25 RDM 50W COB	Yes
911401733564	BVP378 4LED 30K 220V 35 RDM 50W COB	Yes
911401733574	BVP378 4LED 40K 220V 35 RDM 50W COB	Yes

Order Code	Full Product Name	Driver included
911401733584	BVP378 4LED RGB30K 220V 10 RDM 50W	Yes
911401733594	BVP378 4LED RGB40K 220V 10 RDM 50W	Yes
911401733604	BVP378 4LED RGB 220V 10 RDM 50W	Yes
911401733614	BVP378 4LED RGB30K 220V 15 RDM 50W	Yes
911401733624	BVP378 4LED RGB40K 220V 15 RDM 50W	Yes
911401733634	BVP378 4LED RGB 220V 15 RDM 50W	Yes
911401733644	BVP378 4LED RGB30K 220V 30 RDM 50W	Yes
911401733654	BVP378 4LED RGB40K 220V 30 RDM 50W	Yes
911401733664	BVP378 4LED RGB 220V 30 RDM 50W	Yes
911401733674	BVP378 4LED RGB30K 220V 55 RDM 50W	Yes
911401733684	BVP378 4LED RGB40K 220V 55 RDM 50W	Yes
911401733694	BVP378 4LED RGB 220V 55 RDM 50W	Yes

Order Code	Full Product Name	Driver included
911401734544	BVP377 3LED RGB30K 24V 10 DMX 30W	No
911401734554	BVP377 3LED RGB40K 24V 10 DMX 30W	No
911401734564	BVP377 3LED RGB 24V 10 DMX 30W	No
911401734574	BVP377 3LED RGB30K 24V 15 DMX 30W	No
911401734584	BVP377 3LED RGB40K 24V 15 DMX 30W	No
911401734594	BVP377 3LED RGB 24V 15 DMX 30W	No
911401734604	BVP377 3LED RGB30K 24V 30 DMX 30W	No
911401734614	BVP377 3LED RGB40K 24V 30 DMX 30W	No
911401734624	BVP377 3LED RGB 24V 30 DMX 30W	No
911401734634	BVP377 3LED RGB30K 24V 55 DMX 30W	No
911401734644	BVP377 3LED RGB40K 24V 55 DMX 30W	No
911401734654	BVP377 3LED RGB 24V 55 DMX 30W	No
911401734384	BVP377 1LED 30K 24V 15 30W COB	No
911401734394	BVP377 1LED 40K 24V 15 30W COB	No
911401734404	BVP377 1LED 30K 24V 20 30W COB	No
911401734414	BVP377 1LED 40K 24V 20 30W COB	No
911401734424	BVP377 1LED 30K 24V 35 30W COB	No
911401734434	BVP377 1LED 40K 24V 35 30W COB	No
911401734484	BVP377 1LED 30K 24V 15 DMX 30W COB	No
911401734494	BVP377 1LED 40K 24V 15 DMX 30W COB	No
911401734504	BVP377 1LED 30K 24V 20 DMX 30W COB	No
911401734514	BVP377 1LED 40K 24V 20 DMX 30W COB	No
911401734524	BVP377 1LED 30K 24V 35 DMX 30W COB	No
911401734534	BVP377 1LED 40K 24V 35 DMX 30W COB	No
911401733744	BVP375 1LED 30K 24V 20 10W COB	No
911401733754	BVP375 1LED 40K 24V 20 10W COB	No
911401733764	BVP375 1LED 30K 24V 25 10W COB	No
911401733774	BVP375 1LED 40K 24V 25 10W COB	No
911401733784	BVP375 1LED 30K 24V 35 10W COB	No
911401733794	BVP375 1LED 40K 24V 35 10W COB	No
911401733844	BVP375 1LED 30K 24V 20 DMX 10W COB	No
911401733854	BVP375 1LED 40K 24V 20 DMX 10W COB	No
911401733864	BVP375 1LED 30K 24V 25 DMX 10W COB	No
911401733874	BVP375 1LED 40K 24V 25 DMX 10W COB	No
911401733884	BVP375 1LED 30K 24V 35 DMX 10W COB	No
911401733894	BVP375 1LED 40K 24V 35 DMX 10W COB	No

Order Code	Full Product Name	Driver included
911401733904	BVP375 1LED RGB30K 24V 10 DMX 10W	No
911401733914	BVP375 1LED RGB40K 24V 10 DMX 10W	No
911401733924	BVP375 1LED RGB30K 24V 15 DMX 10W	No
911401733934	BVP375 1LED RGB40K 24V 15 DMX 10W	No
911401733944	BVP375 1LED RGB30K 24V 30 DMX 10W	No
911401733954	BVP375 1LED RGB40K 24V 30 DMX 10W	No
911401733964	BVP375 1LED RGB30K 24V 55 DMX 10W	No
911401733974	BVP375 1LED RGB40K 24V 55 DMX 10W	No
911401733984	BVP375 1LED RGB 24V 10 DMX 10W	No
911401733994	BVP375 1LED RGB 24V 15 DMX 10W	No
911401734004	BVP375 1LED RGB 24V 30 DMX 10W	No
911401734014	BVP375 1LED RGB 24V 55 DMX 10W	No
911401734064	BVP376 1LED 30K 24V 20 20W COB	No
911401734074	BVP376 1LED 40K 24V 20 20W COB	No
911401734084	BVP376 1LED 30K 24V 25 20W COB	No
911401734094	BVP376 1LED 40K 24V 25 20W COB	No
911401734104	BVP376 1LED 30K 24V 35 20W COB	No
911401734114	BVP376 1LED 40K 24V 35 20W COB	No
911401734164	BVP376 1LED 30K 24V 20 DMX 20W COB	No
911401734174	BVP376 1LED 40K 24V 20 DMX 20W COB	No
911401734184	BVP376 1LED 30K 24V 25 DMX 20W COB	No
911401734194	BVP376 1LED 40K 24V 25 DMX 20W COB	No
911401734204	BVP376 1LED 30K 24V 35 DMX 20W COB	No
911401734214	BVP376 1LED 40K 24V 35 DMX 20W COB	No
911401734224	BVP376 1LED RGB30K 24V 10 DMX 16W	No
911401734234	BVP376 1LED RGB40K 24V 10 DMX 16W	No
911401734244	BVP376 1LED RGB 24V 10 DMX 12W	No
911401734254	BVP376 1LED RGB30K 24V 15 DMX 16W	No
911401734264	BVP376 1LED RGB40K 24V 15 DMX 16W	No
911401734274	BVP376 1LED RGB 24V 15 DMX 12W	No
911401734284	BVP376 1LED RGB30K 24V 30 DMX 16W	No
911401734294	BVP376 1LED RGB40K 24V 30 DMX 16W	No
911401734304	BVP376 1LED RGB 24V 30 DMX 12W	No
911401734314	BVP376 1LED RGB30K 24V 55 DMX 16W	No
911401734324	BVP376 1LED RGB40K 24V 55 DMX 16W	No
911401734334	BVP376 1LED RGB 24V 55 DMX 12W	No

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401733424	BVP378 4LED 30K 220V 20 50W COB	830 warm white	3000 K	3,805 lm
911401733434	BVP378 4LED 40K 220V 20 50W COB	840 neutral white	4000 K	3,925 lm
911401733444	BVP378 4LED 30K 220V 25 50W COB	830 warm white	3000 K	3,780 lm
911401733454	BVP378 4LED 40K 220V 25 50W COB	840 neutral white	4000 K	3,900 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401733464	BVP378 4LED 30K 220V 35 50W COB	830 warm white	4000 K	3,885 lm
911401733474	BVP378 4LED 40K 220V 35 50W COB	840 neutral white	4000 K	4,005 lm
911401733524	BVP378 4LED 30K 220V 20 RDM 50W COB	830 warm white	3000 K	3,805 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401733534	BVP378 4LED 40K 220V 20 RDM 50W COB	840 neutral white	4000 K	3,925 lm
911401733544	BVP378 4LED 30K 220V 25 RDM 50W COB	830 warm white	3000 K	3,780 lm
911401733554	BVP378 4LED 40K 220V 25 RDM 50W COB	840 neutral white	4000 K	3,900 lm
911401733564	BVP378 4LED 30K 220V 35 RDM 50W COB	830 warm white	3000 K	3,885 lm
911401733574	BVP378 4LED 40K 220V 35 RDM 50W COB	840 neutral white	4000 K	4,005 lm
911401733584	BVP378 4LED RGB30K 220V 10 RDM 50W	Red, green, blue and white	RGBW	1,550 lm
911401733594	BVP378 4LED RGB40K 220V 10 RDM 50W	Red, green, blue and white	RGBW	1,630 lm
911401733604	BVP378 4LED RGB 220V 10 RDM 50W	Red, green and blue	-	1,155 lm
911401733614	BVP378 4LED RGB30K 220V 15 RDM 50W	Red, green, blue and white	RGBW	1,520 lm
911401733624	BVP378 4LED RGB40K 220V 15 RDM 50W	Red, green, blue and white	RGBW	1,600 lm
911401733634	BVP378 4LED RGB 220V 15 RDM 50W	Red, green and blue	-	1,090 lm
911401733644	BVP378 4LED RGB30K 220V 30 RDM 50W	Red, green, blue and white	RGBW	1,335 lm
911401733654	BVP378 4LED RGB40K 220V 30 RDM 50W	Red, green, blue and white	RGBW	1,405 lm
911401733664	BVP378 4LED RGB 220V 30 RDM 50W	Red, green and blue	-	1,025 lm
911401733674	BVP378 4LED RGB30K 220V 55 RDM 50W	Red, green, blue and white	RGBW	1,140 lm
911401733684	BVP378 4LED RGB40K 220V 55 RDM 50W	Red, green, blue and white	RGBW	1,200 lm
911401733694	BVP378 4LED RGB 220V 55 RDM 50W	Red, green and blue	-	910 lm
911401734544	BVP377 3LED RGB30K 24V 10 DMX 30W	Red, green, blue and white	RGBW	1,170 lm
911401734554	BVP377 3LED RGB40K 24V 10 DMX 30W	Red, green, blue and white	RGBW	1,235 lm
911401734564	BVP377 3LED RGB 24V 10 DMX 30W	Red, green and blue	-	835 lm
911401734574	BVP377 3LED RGB30K 24V 15 DMX 30W	Red, green, blue and white	RGBW	1,110 lm
911401734584	BVP377 3LED RGB40K 24V 15 DMX 30W	Red, green, blue and white	RGBW	1,170 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401734594	BVP377 3LED RGB 24V 15 DMX 30W	Red, green and blue	-	785 lm
911401734604	BVP377 3LED RGB30K 24V 30 DMX 30W	Red, green, blue and white	RGBW	1,040 lm
911401734614	BVP377 3LED RGB40K 24V 30 DMX 30W	Red, green, blue and white	RGBW	1,095 lm
911401734624	BVP377 3LED RGB 24V 30 DMX 30W	Red, green and blue	-	740 lm
911401734634	BVP377 3LED RGB30K 24V 55 DMX 30W	Red, green, blue and white	RGBW	925 lm
911401734644	BVP377 3LED RGB40K 24V 55 DMX 30W	Red, green, blue and white	RGBW	975 lm
911401734654	BVP377 3LED RGB 24V 55 DMX 30W	Red, green and blue	-	655 lm
911401734384	BVP377 1LED 30K 24V 15 30W COB	830 warm white	3000 K	2,230 lm
911401734394	BVP377 1LED 40K 24V 15 30W COB	840 neutral white	4000 K	2,230 lm
911401734404	BVP377 1LED 30K 24V 20 30W COB	830 warm white	3000 K	2,230 lm
911401734414	BVP377 1LED 40K 24V 20 30W COB	840 neutral white	4000 K	2,230 lm
911401734424	BVP377 1LED 30K 24V 35 30W COB	830 warm white	3000 K	2,365 lm
911401734434	BVP377 1LED 40K 24V 35 30W COB	840 neutral white	4000 K	2,365 lm
911401734484	BVP377 1LED 30K 24V 15 DMX 30W COB	830 warm white	3000 K	2,230 lm
911401734494	BVP377 1LED 40K 24V 15 DMX 30W COB	840 neutral white	4000 K	2,230 lm
911401734504	BVP377 1LED 30K 24V 20 DMX 30W COB	830 warm white	3000 K	2,230 lm
911401734514	BVP377 1LED 40K 24V 20 DMX 30W COB	840 neutral white	4000 K	2,230 lm
911401734524	BVP377 1LED 30K 24V 35 DMX 30W COB	830 warm white	3000 K	2,365 lm
911401734534	BVP377 1LED 40K 24V 35 DMX 30W COB	840 neutral white	4000 K	2,365 lm
911401733744	BVP375 1LED 30K 24V 20 10W COB	830 warm white	3000 K	895 lm
911401733754	BVP375 1LED 40K 24V 20 10W COB	840 neutral white	4000 K	895 lm
911401733764	BVP375 1LED 30K 24V 25 10W COB	830 warm white	3000 K	880 lm
911401733774	BVP375 1LED 40K 24V 25 10W COB	840 neutral white	4000 K	880 lm
911401733784	BVP375 1LED 30K 24V 35 10W COB	830 warm white	3000 K	890 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401733794	BVP375 1LED 40K 24V 35 10W COB	840 neutral white	4000 K	890 lm
911401733844	BVP375 1LED 30K 24V 20 DMX 10W COB	830 warm white	3000 K	895 lm
911401733854	BVP375 1LED 40K 24V 20 DMX 10W COB	840 neutral white	4000 K	895 lm
911401733864	BVP375 1LED 30K 24V 25 DMX 10W COB	830 warm white	3000 K	880 lm
911401733874	BVP375 1LED 40K 24V 25 DMX 10W COB	840 neutral white	4000 K	880 lm
911401733884	BVP375 1LED 30K 24V 35 DMX 10W COB	830 warm white	3000 K	890 lm
911401733894	BVP375 1LED 40K 24V 35 DMX 10W COB	840 neutral white	4000 K	890 lm
911401733904	BVP375 1LED RGB30K 24V 10 DMX 10W	Red, green, blue and white	RGBW	215 lm
911401733914	BVP375 1LED RGB40K 24V 10 DMX 10W	Red, green, blue and white	RGBW	215 lm
911401733924	BVP375 1LED RGB30K 24V 15 DMX 10W	Red, green, blue and white	RGBW	215 lm
911401733934	BVP375 1LED RGB40K 24V 15 DMX 10W	Red, green, blue and white	RGBW	215 lm
911401733944	BVP375 1LED RGB30K 24V 30 DMX 10W	Red, green, blue and white	RGBW	180 lm
911401733954	BVP375 1LED RGB40K 24V 30 DMX 10W	Red, green, blue and white	RGBW	180 lm
911401733964	BVP375 1LED RGB30K 24V 55 DMX 10W	Red, green, blue and white	RGBW	185 lm
911401733974	BVP375 1LED RGB40K 24V 55 DMX 10W	Red, green, blue and white	RGBW	185 lm
911401733984	BVP375 1LED RGB 24V 10 DMX 10W	Red, green and blue	-	240 lm
911401733994	BVP375 1LED RGB 24V 15 DMX 10W	Red, green and blue	-	225 lm
911401734004	BVP375 1LED RGB 24V 30 DMX 10W	Red, green and blue	-	210 lm
911401734014	BVP375 1LED RGB 24V 55 DMX 10W	Red, green and blue	-	185 lm
911401734064	BVP376 1LED 30K 24V 20 20W COB	830 warm white	3000 K	1,730 lm
911401734074	BVP376 1LED 40K 24V 20 20W COB	840 neutral white	4000 K	1,730 lm
911401734084	BVP376 1LED 30K 24V 25 20W COB	830 warm white	3000 K	1,675 lm

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401734094	BVP376 1LED 40K 24V 25 20W COB	840 neutral white	4000 K	1,675 lm
911401734104	BVP376 1LED 30K 24V 35 20W COB	830 warm white	3000 K	1,695 lm
911401734114	BVP376 1LED 40K 24V 35 20W COB	840 neutral white	4000 K	1,695 lm
911401734164	BVP376 1LED 30K 24V 20 DMX 20W COB	830 warm white	3000 K	1,730 lm
911401734174	BVP376 1LED 40K 24V 20 DMX 20W COB	840 neutral white	4000 K	1,730 lm
911401734184	BVP376 1LED 30K 24V 25 DMX 20W COB	830 warm white	3000 K	1,675 lm
911401734194	BVP376 1LED 40K 24V 25 DMX 20W COB	840 neutral white	4000 K	1,675 lm
911401734204	BVP376 1LED 30K 24V 35 DMX 20W COB	830 warm white	3000 K	1,695 lm
911401734214	BVP376 1LED 40K 24V 35 DMX 20W COB	840 neutral white	4000 K	1,695 lm
911401734224	BVP376 1LED RGB30K 24V 10 DMX 16W	Red, green, blue and white	RGBW	540 lm
911401734234	BVP376 1LED RGB40K 24V 10 DMX 16W	Red, green, blue and white	RGBW	570 lm
911401734244	BVP376 1LED RGB 24V 10 DMX 12W	Red, green and blue	-	310 lm
911401734254	BVP376 1LED RGB30K 24V 15 DMX 16W	Red, green, blue and white	RGBW	510 lm
911401734264	BVP376 1LED RGB40K 24V 15 DMX 16W	Red, green, blue and white	RGBW	535 lm
911401734274	BVP376 1LED RGB 24V 15 DMX 12W	Red, green and blue	-	295 lm
911401734284	BVP376 1LED RGB30K 24V 30 DMX 16W	Red, green, blue and white	RGBW	480 lm
911401734294	BVP376 1LED RGB40K 24V 30 DMX 16W	Red, green, blue and white	RGBW	505 lm
911401734304	BVP376 1LED RGB 24V 30 DMX 12W	Red, green and blue	-	275 lm
911401734314	BVP376 1LED RGB30K 24V 55 DMX 16W	Red, green, blue and white	RGBW	425 lm
911401734324	BVP376 1LED RGB40K 24V 55 DMX 16W	Red, green, blue and white	RGBW	445 lm
911401734334	BVP376 1LED RGB 24V 55 DMX 12W	Red, green and blue	-	245 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401733424	BVP378 4LED 30K 220V 20 50W COB	50 W

Order Code	Full Product Name	Power Consumption
911401733434	BVP378 4LED 40K 220V 20 50W COB	50 W

Order Code	Full Product Name	Power Consumption
911401733444	BVP378 4LED 30K 220V 25 50W COB	50 W
911401733454	BVP378 4LED 40K 220V 25 50W COB	50 W
911401733464	BVP378 4LED 30K 220V 35 50W COB	50 W
911401733474	BVP378 4LED 40K 220V 35 50W COB	50 W
911401733524	BVP378 4LED 30K 220V 20 RDM 50W COB	50 W
911401733534	BVP378 4LED 40K 220V 20 RDM 50W COB	50 W
911401733544	BVP378 4LED 30K 220V 25 RDM 50W COB	50 W
911401733554	BVP378 4LED 40K 220V 25 RDM 50W COB	50 W
911401733564	BVP378 4LED 30K 220V 35 RDM 50W COB	50 W
911401733574	BVP378 4LED 40K 220V 35 RDM 50W COB	50 W
911401733584	BVP378 4LED RGB30K 220V 10 RDM 50W	50 W
911401733594	BVP378 4LED RGB40K 220V 10 RDM 50W	50 W
911401733604	BVP378 4LED RGB 220V 10 RDM 50W	50 W
911401733614	BVP378 4LED RGB30K 220V 15 RDM 50W	50 W
911401733624	BVP378 4LED RGB40K 220V 15 RDM 50W	50 W
911401733634	BVP378 4LED RGB 220V 15 RDM 50W	50 W
911401733644	BVP378 4LED RGB30K 220V 30 RDM 50W	50 W
911401733654	BVP378 4LED RGB40K 220V 30 RDM 50W	50 W
911401733664	BVP378 4LED RGB 220V 30 RDM 50W	50 W
911401733674	BVP378 4LED RGB30K 220V 55 RDM 50W	50 W
911401733684	BVP378 4LED RGB40K 220V 55 RDM 50W	50 W
911401733694	BVP378 4LED RGB 220V 55 RDM 50W	50 W
911401734544	BVP377 3LED RGB30K 24V 10 DMX 30W	30 W
911401734554	BVP377 3LED RGB40K 24V 10 DMX 30W	30 W
911401734564	BVP377 3LED RGB 24V 10 DMX 30W	30 W
911401734574	BVP377 3LED RGB30K 24V 15 DMX 30W	30 W
911401734584	BVP377 3LED RGB40K 24V 15 DMX 30W	30 W
911401734594	BVP377 3LED RGB 24V 15 DMX 30W	30 W
911401734604	BVP377 3LED RGB30K 24V 30 DMX 30W	30 W
911401734614	BVP377 3LED RGB40K 24V 30 DMX 30W	30 W
911401734624	BVP377 3LED RGB 24V 30 DMX 30W	30 W
911401734634	BVP377 3LED RGB30K 24V 55 DMX 30W	30 W
911401734644	BVP377 3LED RGB40K 24V 55 DMX 30W	30 W
911401734654	BVP377 3LED RGB 24V 55 DMX 30W	30 W
911401734384	BVP377 1LED 30K 24V 15 30W COB	30 W
911401734394	BVP377 1LED 40K 24V 15 30W COB	30 W
911401734404	BVP377 1LED 30K 24V 20 30W COB	30 W
911401734414	BVP377 1LED 40K 24V 20 30W COB	30 W
911401734424	BVP377 1LED 30K 24V 35 30W COB	30 W
911401734434	BVP377 1LED 40K 24V 35 30W COB	30 W
911401734484	BVP377 1LED 30K 24V 15 DMX 30W COB	30 W
911401734494	BVP377 1LED 40K 24V 15 DMX 30W COB	30 W
911401734504	BVP377 1LED 30K 24V 20 DMX 30W COB	30 W
911401734514	BVP377 1LED 40K 24V 20 DMX 30W COB	30 W
911401734524	BVP377 1LED 30K 24V 35 DMX 30W COB	30 W
911401734534	BVP377 1LED 40K 24V 35 DMX 30W COB	30 W
911401733744	BVP375 1LED 30K 24V 20 10W COB	10 W

Order Code	Full Product Name	Power Consumption
911401733754	BVP375 1LED 40K 24V 20 10W COB	10 W
911401733764	BVP375 1LED 30K 24V 25 10W COB	10 W
911401733774	BVP375 1LED 40K 24V 25 10W COB	10 W
911401733784	BVP375 1LED 30K 24V 35 10W COB	10 W
911401733794	BVP375 1LED 40K 24V 35 10W COB	10 W
911401733844	BVP375 1LED 30K 24V 20 DMX 10W COB	10 W
911401733854	BVP375 1LED 40K 24V 20 DMX 10W COB	10 W
911401733864	BVP375 1LED 30K 24V 25 DMX 10W COB	10 W
911401733874	BVP375 1LED 40K 24V 25 DMX 10W COB	10 W
911401733884	BVP375 1LED 30K 24V 35 DMX 10W COB	10 W
911401733894	BVP375 1LED 40K 24V 35 DMX 10W COB	10 W
911401733904	BVP375 1LED RGB30K 24V 10 DMX 10W	10 W
911401733914	BVP375 1LED RGB40K 24V 10 DMX 10W	10 W
911401733924	BVP375 1LED RGB30K 24V 15 DMX 10W	10 W
911401733934	BVP375 1LED RGB40K 24V 15 DMX 10W	10 W
911401733944	BVP375 1LED RGB30K 24V 30 DMX 10W	10 W
911401733954	BVP375 1LED RGB40K 24V 30 DMX 10W	10 W
911401733964	BVP375 1LED RGB30K 24V 55 DMX 10W	10 W
911401733974	BVP375 1LED RGB40K 24V 55 DMX 10W	10 W
911401733984	BVP375 1LED RGB 24V 10 DMX 10W	10 W
911401733994	BVP375 1LED RGB 24V 15 DMX 10W	10 W
911401734004	BVP375 1LED RGB 24V 30 DMX 10W	10 W
911401734014	BVP375 1LED RGB 24V 55 DMX 10W	10 W
911401734064	BVP376 1LED 30K 24V 20 20W COB	20 W
911401734074	BVP376 1LED 40K 24V 20 20W COB	20 W
911401734084	BVP376 1LED 30K 24V 25 20W COB	20 W
911401734094	BVP376 1LED 40K 24V 25 20W COB	20 W
911401734104	BVP376 1LED 30K 24V 35 20W COB	20 W
911401734114	BVP376 1LED 40K 24V 35 20W COB	20 W
911401734164	BVP376 1LED 30K 24V 20 DMX 20W COB	20 W
911401734174	BVP376 1LED 40K 24V 20 DMX 20W COB	20 W
911401734184	BVP376 1LED 30K 24V 25 DMX 20W COB	20 W
911401734194	BVP376 1LED 40K 24V 25 DMX 20W COB	20 W
911401734204	BVP376 1LED 30K 24V 35 DMX 20W COB	20 W
911401734214	BVP376 1LED 40K 24V 35 DMX 20W COB	20 W
911401734224	BVP376 1LED RGB30K 24V 10 DMX 16W	16 W
911401734234	BVP376 1LED RGB40K 24V 10 DMX 16W	16 W
911401734244	BVP376 1LED RGB 24V 10 DMX 12W	12 W
911401734254	BVP376 1LED RGB30K 24V 15 DMX 16W	16 W
911401734264	BVP376 1LED RGB40K 24V 15 DMX 16W	16 W
911401734274	BVP376 1LED RGB 24V 15 DMX 12W	12 W
911401734284	BVP376 1LED RGB30K 24V 30 DMX 16W	16 W
911401734294	BVP376 1LED RGB40K 24V 30 DMX 16W	16 W
911401734304	BVP376 1LED RGB 24V 30 DMX 12W	12 W
911401734314	BVP376 1LED RGB30K 24V 55 DMX 16W	16 W
911401734324	BVP376 1LED RGB40K 24V 55 DMX 16W	16 W
911401734334	BVP376 1LED RGB 24V 55 DMX 12W	12 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401733424	BVP378 4LED 30K 220V 20 50W COB	No

Order Code	Full Product Name	Dimmable
911401733434	BVP378 4LED 40K 220V 20 50W COB	No

Order Code	Full Product Name	Dimmable
911401733444	BVP378 4LED 30K 220V 25 50W COB	No
911401733454	BVP378 4LED 40K 220V 25 50W COB	No
911401733464	BVP378 4LED 30K 220V 35 50W COB	No
911401733474	BVP378 4LED 40K 220V 35 50W COB	No
911401733524	BVP378 4LED 30K 220V 20 RDM 50W COB	Yes
911401733534	BVP378 4LED 40K 220V 20 RDM 50W COB	Yes
911401733544	BVP378 4LED 30K 220V 25 RDM 50W COB	Yes
911401733554	BVP378 4LED 40K 220V 25 RDM 50W COB	Yes
911401733564	BVP378 4LED 30K 220V 35 RDM 50W COB	Yes
911401733574	BVP378 4LED 40K 220V 35 RDM 50W COB	Yes
911401733584	BVP378 4LED RGB30K 220V 10 RDM 50W	Yes
911401733594	BVP378 4LED RGB40K 220V 10 RDM 50W	Yes
911401733604	BVP378 4LED RGB 220V 10 RDM 50W	Yes
911401733614	BVP378 4LED RGB30K 220V 15 RDM 50W	Yes
911401733624	BVP378 4LED RGB40K 220V 15 RDM 50W	Yes
911401733634	BVP378 4LED RGB 220V 15 RDM 50W	Yes
911401733644	BVP378 4LED RGB30K 220V 30 RDM 50W	Yes
911401733654	BVP378 4LED RGB40K 220V 30 RDM 50W	Yes
911401733664	BVP378 4LED RGB 220V 30 RDM 50W	Yes
911401733674	BVP378 4LED RGB30K 220V 55 RDM 50W	Yes
911401733684	BVP378 4LED RGB40K 220V 55 RDM 50W	Yes
911401733694	BVP378 4LED RGB 220V 55 RDM 50W	Yes
911401734544	BVP377 3LED RGB30K 24V 10 DMX 30W	Yes
911401734554	BVP377 3LED RGB40K 24V 10 DMX 30W	Yes
911401734564	BVP377 3LED RGB 24V 10 DMX 30W	Yes
911401734574	BVP377 3LED RGB30K 24V 15 DMX 30W	Yes
911401734584	BVP377 3LED RGB40K 24V 15 DMX 30W	Yes
911401734594	BVP377 3LED RGB 24V 15 DMX 30W	Yes
911401734604	BVP377 3LED RGB30K 24V 30 DMX 30W	Yes
911401734614	BVP377 3LED RGB40K 24V 30 DMX 30W	Yes
911401734624	BVP377 3LED RGB 24V 30 DMX 30W	Yes
911401734634	BVP377 3LED RGB30K 24V 55 DMX 30W	Yes
911401734644	BVP377 3LED RGB40K 24V 55 DMX 30W	Yes
911401734654	BVP377 3LED RGB 24V 55 DMX 30W	Yes
911401734384	BVP377 1LED 30K 24V 15 30W COB	No
911401734394	BVP377 1LED 40K 24V 15 30W COB	No
911401734404	BVP377 1LED 30K 24V 20 30W COB	No
911401734414	BVP377 1LED 40K 24V 20 30W COB	No
911401734424	BVP377 1LED 30K 24V 35 30W COB	No
911401734434	BVP377 1LED 40K 24V 35 30W COB	No
911401734484	BVP377 1LED 30K 24V 15 DMX 30W COB	Yes
911401734494	BVP377 1LED 40K 24V 15 DMX 30W COB	Yes
911401734504	BVP377 1LED 30K 24V 20 DMX 30W COB	Yes
911401734514	BVP377 1LED 40K 24V 20 DMX 30W COB	Yes
911401734524	BVP377 1LED 30K 24V 35 DMX 30W COB	Yes
911401734534	BVP377 1LED 40K 24V 35 DMX 30W COB	Yes
911401733744	BVP375 1LED 30K 24V 20 10W COB	No

Order Code	Full Product Name	Dimmable
911401733754	BVP375 1LED 40K 24V 20 10W COB	No
911401733764	BVP375 1LED 30K 24V 25 10W COB	No
911401733774	BVP375 1LED 40K 24V 25 10W COB	No
911401733784	BVP375 1LED 30K 24V 35 10W COB	No
911401733794	BVP375 1LED 40K 24V 35 10W COB	No
911401733844	BVP375 1LED 30K 24V 20 DMX 10W COB	Yes
911401733854	BVP375 1LED 40K 24V 20 DMX 10W COB	Yes
911401733864	BVP375 1LED 30K 24V 25 DMX 10W COB	Yes
911401733874	BVP375 1LED 40K 24V 25 DMX 10W COB	Yes
911401733884	BVP375 1LED 30K 24V 35 DMX 10W COB	Yes
911401733894	BVP375 1LED 40K 24V 35 DMX 10W COB	Yes
911401733904	BVP375 1LED RGB30K 24V 10 DMX 10W	Yes
911401733914	BVP375 1LED RGB40K 24V 10 DMX 10W	Yes
911401733924	BVP375 1LED RGB30K 24V 15 DMX 10W	Yes
911401733934	BVP375 1LED RGB40K 24V 15 DMX 10W	Yes
911401733944	BVP375 1LED RGB30K 24V 30 DMX 10W	Yes
911401733954	BVP375 1LED RGB40K 24V 30 DMX 10W	Yes
911401733964	BVP375 1LED RGB30K 24V 55 DMX 10W	Yes
911401733974	BVP375 1LED RGB40K 24V 55 DMX 10W	Yes
911401733984	BVP375 1LED RGB 24V 10 DMX 10W	Yes
911401733994	BVP375 1LED RGB 24V 15 DMX 10W	Yes
911401734004	BVP375 1LED RGB 24V 30 DMX 10W	Yes
911401734014	BVP375 1LED RGB 24V 55 DMX 10W	Yes
911401734064	BVP376 1LED 30K 24V 20 20W COB	No
911401734074	BVP376 1LED 40K 24V 20 20W COB	No
911401734084	BVP376 1LED 30K 24V 25 20W COB	No
911401734094	BVP376 1LED 40K 24V 25 20W COB	No
911401734104	BVP376 1LED 30K 24V 35 20W COB	No
911401734114	BVP376 1LED 40K 24V 35 20W COB	No
911401734164	BVP376 1LED 30K 24V 20 DMX 20W COB	Yes
911401734174	BVP376 1LED 40K 24V 20 DMX 20W COB	Yes
911401734184	BVP376 1LED 30K 24V 25 DMX 20W COB	Yes
911401734194	BVP376 1LED 40K 24V 25 DMX 20W COB	Yes
911401734204	BVP376 1LED 30K 24V 35 DMX 20W COB	Yes
911401734214	BVP376 1LED 40K 24V 35 DMX 20W COB	Yes
911401734224	BVP376 1LED RGB30K 24V 10 DMX 16W	Yes
911401734234	BVP376 1LED RGB40K 24V 10 DMX 16W	Yes
911401734244	BVP376 1LED RGB 24V 10 DMX 12W	Yes
911401734254	BVP376 1LED RGB30K 24V 15 DMX 16W	Yes
911401734264	BVP376 1LED RGB40K 24V 15 DMX 16W	Yes
911401734274	BVP376 1LED RGB 24V 15 DMX 12W	Yes
911401734284	BVP376 1LED RGB30K 24V 30 DMX 16W	Yes
911401734294	BVP376 1LED RGB40K 24V 30 DMX 16W	Yes
911401734304	BVP376 1LED RGB 24V 30 DMX 12W	Yes
911401734314	BVP376 1LED RGB30K 24V 55 DMX 16W	Yes
911401734324	BVP376 1LED RGB40K 24V 55 DMX 16W	Yes
911401734334	BVP376 1LED RGB 24V 55 DMX 12W	Yes

