



Sophisticated and compact outdoor spotlight

UniSpot

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Benefits

- Sleek and minimalist design, suitable for diverse application scenarios
- A variety of optics and color selections
- Multiple mounting methods suitable for different lighting applications

Features

- Standard: RGB+3000K, RGB+4000K, RGB, 3000K, and 4000K
- Optional 2200K, 2700K, 3500K, 5000K, 5700K, 6500K, monochrome, and RGB +5700K,
- Wide range of beam angles, from narrow spot to wide flood
- Robust design with IP66 rating for outdoor use
- Adjustable vertical 130° and horizontal 340° tilting angle range

Application





- Bridges, Monuments, Facades
- Municipal Buildings
- Parks and Plazas

Versions



RTP-OF-UniSpot

Dimensional drawing



Light Technical

Color rendering index (CRI) >80

Mechanical and Housing

Optical cover type Clear glass

Housing Color Dark gray

Mech. impact protection code IK06

Ingress protection code IP66

Approval and Application

CE mark Yes

General Information

Order Code	Full Product Name	Driver included
70296899	BVP378 4LED 30K 220V 35 50W COB	Yes
70297599	BVP378 4LED 40K 220V 35 50W COB	Yes
70302699	BVP378 4LED 30K 220V 35 RDM 50W COB	Yes
70303399	BVP378 4LED 40K 220V 35 RDM 50W COB	Yes
70310199	BVP378 4LED RGB30K 220V 30 RDM 50W	Yes
70311899	BVP378 4LED RGB40K 220V 30 RDM 50W	Yes
70312599	BVP378 4LED RGB 220V 30 RDM 50W	Yes
70286999	BVP377 3LED RGB30K 24V 30 DMX 30W	No
70287699	BVP377 3LED RGB40K 24V 30 DMX 30W	No
70288399	BVP377 3LED RGB 24V 30 DMX 30W	No
70272299	BVP377 1LED 30K 24V 35 30W COB	No
70273999	BVP377 1LED 40K 24V 35 30W COB	No
70278499	BVP377 1LED 30K 24V 35 DMX 30W COB	No
70279199	BVP377 1LED 40K 24V 35 DMX 30W COB	No

Order Code	Full Product Name	Driver included
70224199	BVP375 1LED 30K 24V 35 10W COB	No
70225899	BVP375 1LED 40K 24V 35 10W COB	No
70230299	BVP375 1LED 30K 24V 35 DMX 10W COB	No
70231999	BVP375 1LED 40K 24V 35 DMX 10W COB	No
70236499	BVP375 1LED RGB30K 24V 30 DMX 10W	No
70237199	BVP375 1LED RGB40K 24V 30 DMX 10W	No
70242599	BVP375 1LED RGB 24V 30 DMX 10W	No
70248799	BVP376 1LED 30K 24V 35 20W COB	No
70249499	BVP376 1LED 40K 24V 35 20W COB	No
70254899	BVP376 1LED 30K 24V 35 DMX 20W COB	No
70255599	BVP376 1LED 40K 24V 35 DMX 20W COB	No
70262399	BVP376 1LED RGB30K 24V 30 DMX 16W	No
70263099	BVP376 1LED RGB40K 24V 30 DMX 16W	No
70264799	BVP376 1LED RGB 24V 30 DMX 12W	No

Light Technical

Order Code	Full Product Name	Correlated Color		
		Light source color	Temperature (Nom)	Luminous Flux
70296899	BVP378 4LED 30K 220V 35 50W COB	830 warm white	4000 K	3,885 lm
70297599	BVP378 4LED 40K 220V 35 50W COB	840 neutral white	4000 K	4,005 lm
70302699	BVP378 4LED 30K 220V 35 RDM 50W COB	830 warm white	3000 K	3,885 lm
70303399	BVP378 4LED 40K 220V 35 RDM 50W COB	840 neutral white	4000 K	4,005 lm
70310199	BVP378 4LED RGB30K 220V 30 RDM 50W	Red, green, blue and white	RGBW	1,335 lm
70311899	BVP378 4LED RGB40K 220V 30 RDM 50W	Red, green, blue and white	RGBW	1,405 lm
70312599	BVP378 4LED RGB 220V 30 RDM 50W	Red, green and blue	-	1,025 lm
70286999	BVP377 3LED RGB30K 24V 30 DMX 30W	Red, green, blue and white	RGBW	1,040 lm
70287699	BVP377 3LED RGB40K 24V 30 DMX 30W	Red, green, blue and white	RGBW	1,095 lm
70288399	BVP377 3LED RGB 24V 30 DMX 30W	Red, green and blue	-	740 lm
70272299	BVP377 1LED 30K 24V 35 30W COB	830 warm white	3000 K	2,365 lm
70273999	BVP377 1LED 40K 24V 35 30W COB	840 neutral white	4000 K	2,365 lm
70278499	BVP377 1LED 30K 24V 35 DMX 30W COB	830 warm white	3000 K	2,365 lm
70279199	BVP377 1LED 40K 24V 35 DMX 30W COB	840 neutral white	4000 K	2,365 lm

Order Code	Full Product Name	Correlated Color		
		Light source color	Temperature (Nom)	Luminous Flux
70224199	BVP375 1LED 30K 24V 35 10W COB	830 warm white	3000 K	890 lm
70225899	BVP375 1LED 40K 24V 35 10W COB	840 neutral white	4000 K	890 lm
70230299	BVP375 1LED 30K 24V 35 DMX 10W COB	830 warm white	3000 K	890 lm
70231999	BVP375 1LED 40K 24V 35 DMX 10W COB	840 neutral white	4000 K	890 lm
70236499	BVP375 1LED RGB30K 24V 30 DMX 10W	Red, green, blue and white	RGBW	180 lm
70237199	BVP375 1LED RGB40K 24V 30 DMX 10W	Red, green, blue and white	RGBW	180 lm
70242599	BVP375 1LED RGB 24V 30 DMX 10W	Red, green and blue	-	210 lm
70248799	BVP376 1LED 30K 24V 35 20W COB	830 warm white	3000 K	1,695 lm
70249499	BVP376 1LED 40K 24V 35 20W COB	840 neutral white	4000 K	1,695 lm
70254899	BVP376 1LED 30K 24V 35 DMX 20W COB	830 warm white	3000 K	1,695 lm
70255599	BVP376 1LED 40K 24V 35 DMX 20W COB	840 neutral white	4000 K	1,695 lm
70262399	BVP376 1LED RGB30K 24V 30 DMX 16W	Red, green, blue and white	RGBW	480 lm
70263099	BVP376 1LED RGB40K 24V 30 DMX 16W	Red, green, blue and white	RGBW	505 lm
70264799	BVP376 1LED RGB 24V 30 DMX 12W	Red, green and blue	-	275 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
70296899	BVP378 4LED 30K 220V 35 50W COB	50 W
70297599	BVP378 4LED 40K 220V 35 50W COB	50 W
70302699	BVP378 4LED 30K 220V 35 RDM 50W COB	50 W
70303399	BVP378 4LED 40K 220V 35 RDM 50W COB	50 W
70310199	BVP378 4LED RGB30K 220V 30 RDM 50W	50 W
70311899	BVP378 4LED RGB40K 220V 30 RDM 50W	50 W
70312599	BVP378 4LED RGB 220V 30 RDM 50W	50 W
70286999	BVP377 3LED RGB30K 24V 30 DMX 30W	30 W
70287699	BVP377 3LED RGB40K 24V 30 DMX 30W	30 W
70288399	BVP377 3LED RGB 24V 30 DMX 30W	30 W
70272299	BVP377 1LED 30K 24V 35 30W COB	30 W
70273999	BVP377 1LED 40K 24V 35 30W COB	30 W
70278499	BVP377 1LED 30K 24V 35 DMX 30W COB	30 W
70279199	BVP377 1LED 40K 24V 35 DMX 30W COB	30 W

Order Code	Full Product Name	Power Consumption
70224199	BVP375 1LED 30K 24V 35 10W COB	10 W
70225899	BVP375 1LED 40K 24V 35 10W COB	10 W
70230299	BVP375 1LED 30K 24V 35 DMX 10W COB	10 W
70231999	BVP375 1LED 40K 24V 35 DMX 10W COB	10 W
70236499	BVP375 1LED RGB30K 24V 30 DMX 10W	10 W
70237199	BVP375 1LED RGB40K 24V 30 DMX 10W	10 W
70242599	BVP375 1LED RGB 24V 30 DMX 10W	10 W
70248799	BVP376 1LED 30K 24V 35 20W COB	20 W
70249499	BVP376 1LED 40K 24V 35 20W COB	20 W
70254899	BVP376 1LED 30K 24V 35 DMX 20W COB	20 W
70255599	BVP376 1LED 40K 24V 35 DMX 20W COB	20 W
70262399	BVP376 1LED RGB30K 24V 30 DMX 16W	16 W
70263099	BVP376 1LED RGB40K 24V 30 DMX 16W	16 W
70264799	BVP376 1LED RGB 24V 30 DMX 12W	12 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
70296899	BVP378 4LED 30K 220V 35 50W COB	No
70297599	BVP378 4LED 40K 220V 35 50W COB	No
70302699	BVP378 4LED 30K 220V 35 RDM 50W COB	Yes
70303399	BVP378 4LED 40K 220V 35 RDM 50W COB	Yes
70310199	BVP378 4LED RGB30K 220V 30 RDM 50W	Yes
70311899	BVP378 4LED RGB40K 220V 30 RDM 50W	Yes
70312599	BVP378 4LED RGB 220V 30 RDM 50W	Yes
70286999	BVP377 3LED RGB30K 24V 30 DMX 30W	Yes
70287699	BVP377 3LED RGB40K 24V 30 DMX 30W	Yes
70288399	BVP377 3LED RGB 24V 30 DMX 30W	Yes
70272299	BVP377 1LED 30K 24V 35 30W COB	No
70273999	BVP377 1LED 40K 24V 35 30W COB	No
70278499	BVP377 1LED 30K 24V 35 DMX 30W COB	Yes
70279199	BVP377 1LED 40K 24V 35 DMX 30W COB	Yes

Order Code	Full Product Name	Dimmable
70224199	BVP375 1LED 30K 24V 35 10W COB	No
70225899	BVP375 1LED 40K 24V 35 10W COB	No
70230299	BVP375 1LED 30K 24V 35 DMX 10W COB	Yes
70231999	BVP375 1LED 40K 24V 35 DMX 10W COB	Yes
70236499	BVP375 1LED RGB30K 24V 30 DMX 10W	Yes
70237199	BVP375 1LED RGB40K 24V 30 DMX 10W	Yes
70242599	BVP375 1LED RGB 24V 30 DMX 10W	Yes
70248799	BVP376 1LED 30K 24V 35 20W COB	No
70249499	BVP376 1LED 40K 24V 35 20W COB	No
70254899	BVP376 1LED 30K 24V 35 DMX 20W COB	Yes
70255599	BVP376 1LED 40K 24V 35 DMX 20W COB	Yes
70262399	BVP376 1LED RGB30K 24V 30 DMX 16W	Yes
70263099	BVP376 1LED RGB40K 24V 30 DMX 16W	Yes
70264799	BVP376 1LED RGB 24V 30 DMX 12W	Yes

