



Sophisticated and compact outdoor spotlight

UniSpot

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Benefits

- Sleek and minimalist design, suitable for diverse application scenarios
- A variety of optics and color selections
- Multiple mounting methods suitable for different lighting applications

Features

- Standard: RGB+3000K, RGB+4000K, RGB, 3000K, and 4000K
- Optional 2200K, 2700K, 3500K, 5000K, 5700K, 6500K, monochrome, and RGB +5700K,
- Wide range of beam angles, from narrow spot to wide flood
- Robust design with IP66 rating for outdoor use
- Adjustable vertical 130° and horizontal 340° tilting angle range

Application

- Bridges, Monuments, Facades
- Municipal Buildings
- Parks and Plazas

UniSpot

Versions



RTP-OF-UniSpot

Dimensional drawing

