



UltraEfficient and Versatile LED Floodlight

Tango Pro LED floodlight is the fifth generation of the Tango LED floodlight. Tango Pro takes efficiency to the next level, delivering industry-best efficiency in a compact but elegant design. The luminaire can be applied in a versatile range of applications, from area lighting to recreational sports facilities. The LED driver comes in compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. The modular, streamlined luminaire silhouette offers a visually balanced design. Tango Pro LED floodlight is engineered to create brighter and safer environments. Powered by the latest LED technology, Tango Pro delivers superior performance in both light distribution and UltraEfficiency 170lm/W and up to 200lm/W. The long luminaire lifetime and recyclable materials supports your efforts to meet sustainability targets.

Benefits

- Product comes in High Efficiency and UltraEfficient versions for low carbon emissions and energy savings.
- 6 optics, 12 driver options and accessories (external louvers, safety chain, aiming device) allow you to meet a wide range of application requirements.
- Connected and system-ready (ready for interact and ZD4i) to be compatible with Interact platform.
- Appealing and sustainable design, and robust materials provide durability, robust quality and reliability against harsh environments.

Applications

- Airports
- Arena and sports
- Parking garages
- Buildings, monuments, and façades
- Transportation terminals and tollways
- Billboard
- Ports and container yard
- Large industrial areas

Features

- UltraEfficiency version offers 170lm/W and system efficacy up to 200lm/W.
- Lumen packages ranging from 8,500 lumens to 85,000 lumens.
- High quality ADC1 diecast aluminum housing and stainless-steel bracket.
- 1,000 hrs/2,000 hrs marine salt protection (MSP) for coastline applications.
- IP66 ingress protection rating and IK08 impact protection rating.
- 100K cycles vibration tests at 3G in X, Y, and Z axis directions and 6G for crane version.
- Withstand 150km/h+ typhoon.
- 75K hours lifetime (L70, @ta=50°C).
- Certified operation at ambient temperature of 50°C.
- 5-year warranty.
- For coastline applications, 2,000 hours (or above) MSP recommended (liability for wear-and-tear damages exempted)
- Not suitable for chemical industrial areas
- Not suitable for installation on moving objects

Versions



Tango-pro-standard-picture



Tango-pro-standard-picture




Tango-pro-standard-picture




Tango-pro-standard-picture




Dimensional drawing




BVP564 LED555/740 380W EP S6





BVP563 LED336/750 220W EP SWB



BVP561 LED135/740 78W PSU SWBC



BVP565 LED672/757 430W EP SWB



Product details



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight



Tango-pro-detail-picture



Tango Pro, floodlight



Tango Pro, floodlight



Tango Pro, floodlight

General Information

Driver included	Yes
Service tag	Yes

Mechanical and Housing

Housing Color	RAL7040
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate

Approval and Application

Flammability mark	-
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401630510	BVP565 LED672/740 430W EP SWB	67,200 lm	4000 K	70	750 neutral white	-
911401630810	BVP565 LED672/750 430W EP SWB	67,200 lm	5000 K	70	750 neutral white	-
911401631110	BVP565 LED672/757 430W EP SWB	67,200 lm	5700 K	70	757 cool white	-
911401631210	BVP565 LED577/730 430W EP SAWB P7	57,700 lm	3000 K	70	730 warm white	-
911401631310	BVP565 LED577/730 430W EP SAWB	57,700 lm	3000 K	70	730 warm white	-
911401631410	BVP565 LED672/740 430W EP NB	67,200 lm	4000 K	70	740 neutral white	-
911401631510	BVP565 LED672/740 430W EP S6	67,200 lm	4000 K	70	740 neutral white	-
911401631610	BVP565 LED672/750 430W EP NB	67,200 lm	5000 K	70	750 neutral white	-
911401631710	BVP565 LED672/750 430W EP S6	67,200 lm	5000 K	70	750 neutral white	-
911401631810	BVP565 LED672/757 430W EP NB	67,200 lm	5700 K	70	757 cool white	-
911401632010	BVP565 LED672/757 430W EP S6	67,200 lm	5700 K	70	757 cool white	-
911401632810	BVP565 LED558/730 370W FP SWB	55,800 lm	3000 K	70	730 warm white	-
911401633010	BVP565 LED601/740 370W FP SWB	60,100 lm	4000 K	70	740 neutral white	-
911401633610	BVP565 LED601/750 370W FP SWB	60,100 lm	5000 K	70	750 neutral white	-
911401634010	BVP565 LED601/757 370W FP SWB	60,100 lm	5700 K	70	757 cool white	-
911401634210	BVP565 LED601/740 370W FP NB	60,100 lm	4000 K	70	740 neutral white	-
911401634410	BVP565 LED601/740 370W FP S6	60,100 lm	4000 K	70	740 neutral white	-

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401634610	BVP565 LED601/750 370W FP NB	60,100 lm	5000 K	70	750 neutral white	-
911401634810	BVP565 LED601/750 370W FP S6	60,100 lm	5000 K	70	750 neutral white	-
911401635010	BVP565 LED601/757 370W FP NB	60,100 lm	5700 K	70	757 cool white	-
911401635210	BVP565 LED601/757 370W FP S6	60,100 lm	5700 K	70	757 cool white	-
911401645310	BVP565 LED800/740 470W EP AMB	80,000 lm	4000 K	70	740 neutral white	-
911401645410	BVP565 LED800/740 470W EP SMB	80,000 lm	4000 K	70	740 neutral white	-
911401649710	BVP564 LED530/740 310W PSU AMB	53,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401649810	BVP564 LED530/757 310W PSU AMB	53,000 lm	5700 K	70	757 cool white	91.6° x 55.1° x 34°
911401649910	BVP564 LED530/740 310W PSU SMB	53,000 lm	4000 K	70	740 neutral white	55°
911401650010	BVP564 LED530/757 310W PSU SMB	53,000 lm	5700 K	70	757 cool white	55°
911401650110	BVP564 LED410/740 240W EP AMB	41,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401650210	BVP564 LED410/757 240W EP AMB	41,000 lm	5700 K	70	757 cool white	91.6° x 55.1° x 34°
911401650310	BVP564 LED410/740 240W EP SMB	41,000 lm	4000 K	70	740 neutral white	55°
911401650410	BVP564 LED410/757 240W EP SMB	41,000 lm	5700 K	70	757 cool white	55°
911401650510	BVP564 LED470/740 275W EP AMB	47,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401650610	BVP564 LED470/757 275W EP AMB	47,000 lm	5700 K	70	757 cool white	91.6° x 55.1° x 34°
911401650710	BVP564 LED470/740 275W EP SMB	47,000 lm	4000 K	70	740 neutral white	55°
911401650810	BVP564 LED470/757 275W EP SMB	47,000 lm	5700 K	70	757 cool white	55°
911401650910	BVP564 LED530/740 310W EP AMB	53,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401651010	BVP564 LED530/757 310W EP AMB	53,000 lm	5700 K	70	757 cool white	91.6° x 55.1° x 34°
911401651210	BVP564 LED530/740 310W EP SMB	53,000 lm	4000 K	70	740 neutral white	55°
911401651410	BVP564 LED530/757 310W EP SMB	53,000 lm	5700 K	70	757 cool white	55°
911401651510	BVP564 LED625/740 380W EP AMB	62,500 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401651610	BVP564 LED625/740 380W EP SMB	62,500 lm	4000 K	70	740 neutral white	55°
911401652210	BVP564 LED520/740 350W EP NB	52,000 lm	4000 K	70	740 neutral white	12°
911401652410	BVP564 LED555/740 380W EP NB	55,500 lm	4000 K	70	740 neutral white	12°
911401652610	BVP564 LED555/740 380W EP S6	55,500 lm	4000 K	70	740 neutral white	23°
911401652810	BVP564 LED516/740 380W EP SAWB	51,600 lm	4000 K	70	740 neutral white	116° x 15.7° x 65°
911401653010	BVP564 LED555/740 380W EP SWB	55,500 lm	4000 K	70	740 neutral white	73° x 26°
911401654410	BVP564 LED750/740 470W EP AMB	75,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401654610	BVP564 LED750/740 470W EP SMB	75,000 lm	4000 K	70	740 neutral white	55°
911401654810	BVP564 LED750/740 470W WLP AMB	75,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401655010	BVP564 LED720/740 450W GL AMB	72,000 lm	4000 K	70	740 neutral white	91.6° x 55.1° x 34°
911401655210	BVP564 LED720/740 450W GL SMB	72,000 lm	4000 K	70	740 neutral white	55°
911401655410	BVP564 LED612/740 440W EP NB	61,200 lm	4000 K	70	740 neutral white	12°
911401655610	BVP564 LED612/740 440W EP S6	61,200 lm	4000 K	70	740 neutral white	23°
911401655810	BVP564 LED567/740 440W EP SAWB	56,700 lm	4000 K	70	740 neutral white	116° x 15.7° x 65°
911401656010	BVP564 LED612/740 440W EP SWB	61,200 lm	4000 K	70	740 neutral white	73° x 26°
911401656210	BVP564 LED590/740 410W WLP NB	59,000 lm	4000 K	70	740 neutral white	12°
911401656410	BVP564 LED590/740 410W GL NB	59,000 lm	4000 K	70	740 neutral white	12°
911401656610	BVP564 LED590/740 410W GL S6	59,000 lm	4000 K	70	740 neutral white	23°
911401656810	BVP564 LED546/740 410W GL SAWB	54,600 lm	4000 K	70	740 neutral white	116° x 15.7° x 65°
911401657010	BVP564 LED590/740 410W GL SWB	59,000 lm	4000 K	70	740 neutral white	73° x 26°
911401666610	BVP561 LED68/740 40W PSU SMB	6,800 lm	4000 K	70	740 neutral white	89°
911401666810	BVP561 LED68/740 40W PSU AMB	6,800 lm	4000 K	70	740 neutral white	55°
911401667010	BVP561 LED68/740 40W PSU SWBC	6,800 lm	4000 K	70	740 neutral white	55°
911401667210	BVP561 LED102/740 60W PSU SMB	10,200 lm	4000 K	70	740 neutral white	55°
911401667410	BVP561 LED102/740 60W PSU AMB	10,200 lm	4000 K	70	740 neutral white	89°
911401667610	BVP561 LED102/740 60W PSU SWBC	10,200 lm	4000 K	70	740 neutral white	92° x 55°
911401667810	BVP561 LED135/740 78W PSU SMB	13,500 lm	4000 K	70	740 neutral white	55°
911401668010	BVP561 LED135/740 78W PSU AMB	13,500 lm	4000 K	70	740 neutral white	89°
911401668210	BVP561 LED135/740 78W PSU SWBC	13,500 lm	4000 K	70	740 neutral white	92° x 55°
911401668410	BVP561 LED40/740 20W WLP SMB	4,000 lm	4000 K	70	740 neutral white	55°
911401668610	BVP561 LED40/740 20W WLP AMB	4,000 lm	4000 K	70	740 neutral white	55°
911401668810	BVP561 LED40/740 20W WLP SWBC	4,000 lm	4000 K	70	740 neutral white	55°
911401669010	BVP561 LED187/740 120W EP SMB	18,714 lm	4000 K	70	740 neutral white	55°
911401669210	BVP561 LED187/740 120W EP AMB	18,714 lm	4000 K	70	740 neutral white	55°
911401669410	BVP561 LED187/740 120W EP SWBC	18,714 lm	4000 K	70	740 neutral white	89°
911401669610	BVP561 LED187/740 120W WLP SMB	18,714 lm	4000 K	70	740 neutral white	55°
911401669810	BVP561 LED187/740 120W WLP AMB	18,714 lm	4000 K	70	740 neutral white	89°
911401670010	BVP561 LED187/740 120W WLP SWBC	18,714 lm	4000 K	70	740 neutral white	92° x 55°
911401687610	BVP561 LED163/740 100W WLP SMB P7	16,277 lm	4000 K	70	740 neutral white	55°

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Light source color	Luminaire light beam spread
911401687710	BVP561 LED163/740 100W GL SMB	16,277 lm	4000 K	70	740 neutral white	92° x 55°
911401687810	BVP561 LED163/740 100W GL SMB P7	16,277 lm	4000 K	70	740 neutral white	89°
911401626510	BVP563 LED336/740 220W EP SWB	33,600 lm	4000 K	70	740 neutral white	-
911401626910	BVP563 LED336/750 220W EP SWB	33,600 lm	5000 K	70	750 neutral white	-
911401627210	BVP563 LED336/757 220W EP SWB	33,600 lm	5700 K	70	757 cool white	-
911401627310	BVP563 LED288/730 220W EP SAWB	28,800 lm	3000 K	70	730 warm white	-
911401629810	BVP563 LED288/730 220W EP SAWB P7	28,800 lm	3000 K	70	730 warm white	-
911401644910	BVP563 LED375/740 220W EP AMB	37,500 lm	4000 K	70	740 neutral white	-
911401645010	BVP563 LED375/740 220W EP SMB	37,500 lm	4000 K	70	740 neutral white	-
911401645110	BVP563 LED355/840 220W EP SMB	35,500 lm	4000 K	80	840 neutral white	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401630510	BVP565 LED672/740 430W EP SWB	470 W
911401630810	BVP565 LED672/750 430W EP SWB	430 W
911401631110	BVP565 LED672/757 430W EP SWB	430 W
911401631210	BVP565 LED577/730 430W EP SAWB P7	430 W
911401631310	BVP565 LED577/730 430W EP SAWB	430 W
911401631410	BVP565 LED672/740 430W EP NB	430 W
911401631510	BVP565 LED672/740 430W EP S6	430 W
911401631610	BVP565 LED672/750 430W EP NB	430 W
911401631710	BVP565 LED672/750 430W EP S6	430 W
911401631810	BVP565 LED672/757 430W EP NB	430 W
911401632010	BVP565 LED672/757 430W EP S6	430 W
911401632810	BVP565 LED558/730 370W FP SWB	370 W
911401633010	BVP565 LED601/740 370W FP SWB	370 W
911401633610	BVP565 LED601/750 370W FP SWB	370 W
911401634010	BVP565 LED601/757 370W FP SWB	370 W
911401634210	BVP565 LED601/740 370W FP NB	370 W
911401634410	BVP565 LED601/740 370W FP S6	370 W
911401634610	BVP565 LED601/750 370W FP NB	370 W
911401634810	BVP565 LED601/750 370W FP S6	370 W
911401635010	BVP565 LED601/757 370W FP NB	370 W
911401635210	BVP565 LED601/757 370W FP S6	370 W
911401645310	BVP565 LED800/740 470W EP AMB	470 W
911401645410	BVP565 LED800/740 470W EP SMB	470 W

Order Code	Full Product Name	Power Consumption
911401649710	BVP564 LED530/740 310W PSU AMB	310 W
911401649810	BVP564 LED530/757 310W PSU AMB	310 W
911401649910	BVP564 LED530/740 310W PSU SMB	310 W
911401650010	BVP564 LED530/757 310W PSU SMB	310 W
911401650110	BVP564 LED410/740 240W EP AMB	240 W
911401650210	BVP564 LED410/757 240W EP AMB	240 W
911401650310	BVP564 LED410/740 240W EP SMB	240 W
911401650410	BVP564 LED410/757 240W EP SMB	240 W
911401650510	BVP564 LED470/740 275W EP AMB	275 W
911401650610	BVP564 LED470/757 275W EP AMB	275 W
911401650710	BVP564 LED470/740 275W EP SMB	275 W
911401650810	BVP564 LED470/757 275W EP SMB	275 W
911401650910	BVP564 LED530/740 310W EP AMB	310 W
911401651010	BVP564 LED530/757 310W EP AMB	310 W
911401651210	BVP564 LED530/740 310W EP SMB	310 W
911401651410	BVP564 LED530/757 310W EP SMB	310 W
911401651510	BVP564 LED625/740 380W EP AMB	380 W
911401651610	BVP564 LED625/740 380W EP SMB	380 W
911401652210	BVP564 LED520/740 350W EP NB	350 W
911401652410	BVP564 LED555/740 380W EP NB	380 W
911401652610	BVP564 LED555/740 380W EP S6	380 W
911401652810	BVP564 LED516/740 380W EP SAWB	380 W
911401653010	BVP564 LED555/740 380W EP SWB	380 W
911401654410	BVP564 LED750/740 470W EP AMB	470 W
911401654610	BVP564 LED750/740 470W EP SMB	470 W
911401654810	BVP564 LED750/740 470W WLP AMB	470 W
911401655010	BVP564 LED720/740 450W GL AMB	450 W
911401655210	BVP564 LED720/740 450W GL SMB	450 W
911401655410	BVP564 LED612/740 440W EP NB	440 W
911401655610	BVP564 LED612/740 440W EP S6	440 W
911401655810	BVP564 LED567/740 440W EP SAWB	440 W
911401656010	BVP564 LED612/740 440W EP SWB	440 W
911401656210	BVP564 LED590/740 410W WLP NB	410 W
911401656410	BVP564 LED590/740 410W GL NB	410 W
911401656610	BVP564 LED590/740 410W GL S6	410 W
911401656810	BVP564 LED546/740 410W GL SAWB	410 W
911401657010	BVP564 LED590/740 410W GL SWB	410 W
911401666610	BVP561 LED68/740 40W PSU SMB	40 W
911401666810	BVP561 LED68/740 40W PSU AMB	40 W
911401667010	BVP561 LED68/740 40W PSU SWBC	40 W

Order Code	Full Product Name	Power Consumption
911401667210	BVP561 LED102/740 60W PSU SMB	60 W
911401667410	BVP561 LED102/740 60W PSU AMB	60 W
911401667610	BVP561 LED102/740 60W PSU SWBC	60 W
911401667810	BVP561 LED135/740 78W PSU SMB	78 W
911401668010	BVP561 LED135/740 78W PSU AMB	78 W
911401668210	BVP561 LED135/740 78W PSU SWBC	78 W
911401668410	BVP561 LED40/740 20W WLP SMB	20 W
911401668610	BVP561 LED40/740 20W WLP AMB	20 W
911401668810	BVP561 LED40/740 20W WLP SWBC	20 W
911401669010	BVP561 LED187/740 120W EP SMB	120 W
911401669210	BVP561 LED187/740 120W EP AMB	120 W
911401669410	BVP561 LED187/740 120W EP SWBC	120 W
911401669610	BVP561 LED187/740 120W WLP SMB	120 W
911401669810	BVP561 LED187/740 120W WLP AMB	120 W
911401670010	BVP561 LED187/740 120W WLP SWBC	120 W
911401687610	BVP561 LED163/740 100W WLP SMB P7	100 W
911401687710	BVP561 LED163/740 100W GL SMB	100 W
911401687810	BVP561 LED163/740 100W GL SMB P7	100 W
911401626510	BVP563 LED336/740 220W EP SWB	220 W
911401626910	BVP563 LED336/750 220W EP SWB	220 W
911401627210	BVP563 LED336/757 220W EP SWB	220 W
911401627310	BVP563 LED288/730 220W EP SAWB	220 W
911401629810	BVP563 LED288/730 220W EP SAWB P7	220 W
911401644910	BVP563 LED375/740 220W EP AMB	220 W
911401645010	BVP563 LED375/740 220W EP SMB	220 W
911401645110	BVP563 LED355/840 220W EP SMB	220 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401630510	BVP565 LED672/740 430W EP SWB	1-10V	-
911401630810	BVP565 LED672/750 430W EP SWB	1-10V	-
911401631110	BVP565 LED672/757 430W EP SWB	1-10V	-
911401631210	BVP565 LED577/730 430W EP SAWB P7	1-10V	-
911401631310	BVP565 LED577/730 430W EP SAWB	1-10V	-
911401631410	BVP565 LED672/740 430W EP NB	1-10V	-
911401631510	BVP565 LED672/740 430W EP S6	1-10V	-
911401631610	BVP565 LED672/750 430W EP NB	1-10V	-
911401631710	BVP565 LED672/750 430W EP S6	1-10V	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401631810	BVP565 LED672/757 430W EP NB	1-10V	-
911401632010	BVP565 LED672/757 430W EP S6	1-10V	-
911401632810	BVP565 LED558/730 370W FP SWB	DALI	-
911401633010	BVP565 LED601/740 370W FP SWB	DALI	-
911401633610	BVP565 LED601/750 370W FP SWB	DALI	-
911401634010	BVP565 LED601/757 370W FP SWB	DALI	-
911401634210	BVP565 LED601/740 370W FP NB	DALI	-
911401634410	BVP565 LED601/740 370W FP S6	DALI	-
911401634610	BVP565 LED601/750 370W FP NB	DALI	-
911401634810	BVP565 LED601/750 370W FP S6	DALI	-
911401635010	BVP565 LED601/757 370W FP NB	DALI	-
911401635210	BVP565 LED601/757 370W FP S6	DALI	-
911401645310	BVP565 LED800/740 470W EP AMB	1-10V	-
911401645410	BVP565 LED800/740 470W EP SMB	1-10V	-
911401649710	BVP564 LED530/740 310W PSU AMB	-	Not applicable
911401649810	BVP564 LED530/757 310W PSU AMB	-	Not applicable
911401649910	BVP564 LED530/740 310W PSU SMB	-	Not applicable
911401650010	BVP564 LED530/757 310W PSU SMB	-	Not applicable
911401650110	BVP564 LED410/740 240W EP AMB	1-10V	10%
911401650210	BVP564 LED410/757 240W EP AMB	1-10V	10%
911401650310	BVP564 LED410/740 240W EP SMB	1-10V	10%
911401650410	BVP564 LED410/757 240W EP SMB	1-10V	10%
911401650510	BVP564 LED470/740 275W EP AMB	1-10V	10%
911401650610	BVP564 LED470/757 275W EP AMB	1-10V	10%
911401650710	BVP564 LED470/740 275W EP SMB	1-10V	10%
911401650810	BVP564 LED470/757 275W EP SMB	1-10V	10%
911401650910	BVP564 LED530/740 310W EP AMB	1-10V	10%
911401651010	BVP564 LED530/757 310W EP AMB	1-10V	10%
911401651210	BVP564 LED530/740 310W EP SMB	1-10V	10%
911401651410	BVP564 LED530/757 310W EP SMB	1-10V	10%
911401651510	BVP564 LED625/740 380W EP AMB	1-10V	10%
911401651610	BVP564 LED625/740 380W EP SMB	1-10V	10%
911401652210	BVP564 LED520/740 350W EP NB	1-10V	10%
911401652410	BVP564 LED555/740 380W EP NB	1-10V	10%
911401652610	BVP564 LED555/740 380W EP S6	1-10V	10%
911401652810	BVP564 LED516/740 380W EP SAWB	1-10V	10%
911401653010	BVP564 LED555/740 380W EP SWB	1-10V	10%
911401654410	BVP564 LED750/740 470W EP AMB	1-10V	10%
911401654610	BVP564 LED750/740 470W EP SMB	1-10V	10%
911401654810	BVP564 LED750/740 470W WLP AMB	1-10V	10%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401655010	BVP564 LED720/740 450W GL AMB	1-10V	10%
911401655210	BVP564 LED720/740 450W GL SMB	1-10V	10%
911401655410	BVP564 LED612/740 440W EP NB	1-10V	10%
911401655610	BVP564 LED612/740 440W EP S6	1-10V	10%
911401655810	BVP564 LED567/740 440W EP SAWB	1-10V	10%
911401656010	BVP564 LED612/740 440W EP SWB	1-10V	10%
911401656210	BVP564 LED590/740 410W WLP NB	1-10V	10%
911401656410	BVP564 LED590/740 410W GL NB	1-10V	10%
911401656610	BVP564 LED590/740 410W GL S6	1-10V	10%
911401656810	BVP564 LED546/740 410W GL SAWB	1-10V	10%
911401657010	BVP564 LED590/740 410W GL SWB	1-10V	10%
911401666610	BVP561 LED68/740 40W PSU SMB	-	-
911401666810	BVP561 LED68/740 40W PSU AMB	-	-
911401667010	BVP561 LED68/740 40W PSU SWBC	-	-
911401667210	BVP561 LED102/740 60W PSU SMB	-	-
911401667410	BVP561 LED102/740 60W PSU AMB	-	-
911401667610	BVP561 LED102/740 60W PSU SWBC	-	-
911401667810	BVP561 LED135/740 78W PSU SMB	-	-
911401668010	BVP561 LED135/740 78W PSU AMB	-	-
911401668210	BVP561 LED135/740 78W PSU SWBC	-	-
911401668410	BVP561 LED40/740 20W WLP SMB	1-10V	-
911401668610	BVP561 LED40/740 20W WLP AMB	1-10V	-
911401668810	BVP561 LED40/740 20W WLP SWBC	1-10V	-
911401669010	BVP561 LED187/740 120W EP SMB	1-10V	-
911401669210	BVP561 LED187/740 120W EP AMB	1-10V	-
911401669410	BVP561 LED187/740 120W EP SWBC	1-10V	-
911401669610	BVP561 LED187/740 120W WLP SMB	1-10V	-
911401669810	BVP561 LED187/740 120W WLP AMB	1-10V	-
911401670010	BVP561 LED187/740 120W WLP SWBC	1-10V	-
911401687610	BVP561 LED163/740 100W WLP SMB P7	1-10V	-
911401687710	BVP561 LED163/740 100W GL SMB	1-10V	-
911401687810	BVP561 LED163/740 100W GL SMB P7	1-10V	-
911401626510	BVP563 LED336/740 220W EP SWB	1-10V	-
911401626910	BVP563 LED336/750 220W EP SWB	1-10V	-
911401627210	BVP563 LED336/757 220W EP SWB	1-10V	-
911401627310	BVP563 LED288/730 220W EP SAWB	1-10V	-
911401629810	BVP563 LED288/730 220W EP SAWB P7	1-10V	-
911401644910	BVP563 LED375/740 220W EP AMB	1-10V	-
911401645010	BVP563 LED375/740 220W EP SMB	1-10V	-
911401645110	BVP563 LED355/840 220W EP SMB	1-10V	-

