



ArenaX

BVP571



Where champions shine

ArenaX is a high-performance, intelligent lighting solution engineered for professional sports venues, delivering exceptional light quality, precision, and significant operational and environmental benefits. It provides an immersive viewer experience while prioritizing engineering convenience, minimizing spill light pollution for neighboring environments, and reducing its carbon footprint. The system delivers up to 198,000 lumens with a high color rendering index CRI90 and features a long lifetime exceeding 100,000 hours, ensuring reliable performance in harsh conditions. Its superior light quality is achieved through advanced LEDs and breakthrough thermal management technology, which also reduces the luminaire's weight and dimensions. Equipped with specialized optics and an innovative beam control system, ArenaX fully complies with global sports association lighting standards while effectively containing spill light. The lightweight, compact design facilitates easier installation, lowers structural load costs, and reduces wind load pressure. A horizontally rotatable

bracket allows for flexible physical installation and simplified aiming for optimal field illumination, while a beam tracking system streamlines maintenance by identifying individual fixture optics. An all-in-one driver integrates DMX/RDM, DALI, and D4i protocols and is compatible with the Interact system for comprehensive point control, operational scheduling, and asset management.

Benefits

- System lumen output up to 198,900lm and 171,100lm (without visor) based on CRI90 at 110lm/W reduces the number of fixtures by 20% and therefore lowers TCO per area.
- The light weight (3Kg by 12% reduced compared to typical floodlight) and compact size will result in convenience of installation, lower structural load cost and lower wind loading pressure (SCx).
- Innovative beam control system – proven optics in ArenaVision and specialized designed visors, ensuring arena lighting fully complying with global sports lighting standards and minimize glare and spill light sharp cut-off at 10.7° towards neighbor environment.
- Versatile mounting system with horizontally rotatable ($\pm 75^\circ$) bracket will enable installation with less constraints physically and easy aiming for optimal field illumination.
- Beam easy tracking system (color coded cap) give more convenience on maintenance to track and identify optics of each lighting fixture.
- All-in-one driver of the luminaire integrate DMX/ RDM, complying to DALI and D4i which are compatible with Interact system to control lighting points, set operation scheme and asset-management.

Applications

- Arenas
- Outdoor stadiums
- Indoor stadiums

Features

- System lumen output up to 198,900lm and 171,100lm (without visor) based on CRI90 at 110lm/W
- Specialized designed dual-layer visor to cut spill light
- Color caps for easy identification of optic type at installation site
- Both symmetric and asymmetric optics for better lighting performance given far distance light distribution and reduce quantity on project
- PC and glass front face cover optional
- Horizontally rotatable ($\pm 75^\circ$) U bracket for easing aiming and commissioning
- Breather on each LED module and 3-in-1 seamless cable for wiring, bird-proof conduit
- Unique adjustable module design to lower wind loading pressure (SCx).
- Not suitable for industry area where chemical stuff exists. Application in corrosion environment like swimming pool, coastline outdoors, please consult local sales team for special painting before order. Product has be installed on fixed objects.

Versions



ArenaX sports area




ArenaX sports area


ArenaX sports area




Dimensional drawing




BVP572 LED916/957 900W S3 VOR35BV




BVP573 LED1989/957 1800W S3 ROHB




BVP571 LED663/957 600W S5 ROBV



BVP572 LED1141/957 1200W S3 VOR35HB



BVP573 LED1989/957 1800W S6 ROHB



BVP571 LED663/957 600W S3 ROHB

Product details

ArenaX sports area



ArenaX sports area



ArenaX sports area



General Information

Driver included Yes

Light Technical

Correlated Color Temperature (Nom) 5700 K

Color rendering index (CRI) 90

Mechanical and Housing

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [6 J]

Optical cover type Polycarbonate

Approval and Application

Flammability mark -

CE mark Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Light source color
911401600010	BVP573 LED1412/957 1400W S3 VOR35BV	141,200 lm	957 cool white
911401600110	BVP573 LED1491/957 1500W S3 VOR35BV	149,100 lm	957 cool white
911401600210	BVP573 LED1571/957 1600W S3 VOR35BV	157,100 lm	957 cool white
911401600310	BVP573 LED1722/957 1800W S2 VOR35BV	172,200 lm	957 cool white
911401600410	BVP573 LED1711/957 1800W S3 VOR35BV	171,100 lm	957 cool white
911401600510	BVP573 LED1705/957 1800W S4 VOR35BV	170,500 lm	957 cool white
911401600610	BVP573 LED1679/957 1800W S5 VOR35BV	167,900 lm	957 cool white
911401600710	BVP573 LED1628/957 1800W S6 VOR35BV	162,800 lm	957 cool white
911401600810	BVP573 LED1551/957 1800W S7 VOR35BV	155,100 lm	957 cool white
911401600910	BVP573 LED1497/957 1800W S8 VOR35BV	149,700 lm	957 cool white
911401601010	BVP573 LED1497/957 1800W S9 VOR35BV	149,700 lm	957 cool white
911401601310	BVP573 LED1989/957 1800W S3 ROHB	198,900 lm	957 cool white
911401601610	BVP573 LED1711/957 1800W S3 VOR35HB	171,100 lm	957 cool white
911401695409	BVP573 LED1989/957 1800W S4 ROBV	198,900 lm	957 cool white
911401697409	BVP573 LED1641/957 1400W S3 ROBV	164,100 lm	957 cool white
911401697509	BVP573 LED1734/957 1500W S3 ROBV	173,400 lm	957 cool white
911401697609	BVP573 LED1826/957 1600W S3 ROBV	182,600 lm	957 cool white
911401697709	BVP573 LED1989/957 1800W S2 ROBV	198,900 lm	957 cool white
911401697809	BVP573 LED1989/957 1800W S3 ROBV	198,900 lm	957 cool white

Order Code	Full Product Name	Luminous Flux	Light source color
911401697909	BVP573 LED1989/957 1800W S5 ROBV	198,900 lm	957 cool white
911401698009	BVP573 LED1989/957 1800W S6 ROBV	198,900 lm	957 cool white
911401698109	BVP573 LED1989/957 1800W S7 ROBV	198,900 lm	957 cool white
911401698209	BVP573 LED1989/957 1800W S8 ROBV	198,900 lm	957 cool white
911401698309	BVP573 LED1989/957 1800W S9 ROBV	198,900 lm	957 cool white
911401601210	BVP572 LED1326/957 1200W S3 ROHB	132,600 lm	957 cool white
911401601510	BVP572 LED1141/957 1200W S3 VOR35HB	114,100 lm	957 cool white
911401613110	BVP572 LED1681/757 1200W S9 ROBV	168,100 lm	757 cool white
911401695009	BVP572 LED1326/957 1200W S3 ROBV	132,600 lm	957 cool white
911401695109	BVP572 LED1326/957 1200W S5 ROBV	132,600 lm	957 cool white
911401695209	BVP572 LED1326/957 1200W S7 ROBV	132,600 lm	957 cool white
911401695309	BVP572 LED1326/957 1200W S9 ROBV	132,600 lm	957 cool white
911401696809	BVP572 LED1065/957 900W S3 ROBV	106,500 lm	957 cool white
911401696909	BVP572 LED1161/957 1000W S3 ROBV	116,100 lm	957 cool white
911401697009	BVP572 LED1326/957 1200W S2 ROBV	132,600 lm	957 cool white
911401697109	BVP572 LED1326/957 1200W S4 ROBV	132,600 lm	957 cool white
911401697209	BVP572 LED1326/957 1200W S6 ROBV	132,600 lm	957 cool white
911401697309	BVP572 LED1326/957 1200W S8 ROBV	132,600 lm	957 cool white
911401699009	BVP572 LED916/957 900W S3 VOR35BV	91,600 lm	957 cool white
911401699109	BVP572 LED999/957 1000W S3 VOR35BV	99,900 lm	957 cool white
911401699209	BVP572 LED1148/957 1200W S2 VOR35BV	114,800 lm	957 cool white
911401699309	BVP572 LED1141/957 1200W S3 VOR35BV	114,100 lm	957 cool white
911401699409	BVP572 LED1136/957 1200W S4 VOR35BV	113,600 lm	957 cool white
911401699509	BVP572 LED1119/957 1200W S5 VOR35BV	111,900 lm	957 cool white
911401699609	BVP572 LED1085/957 1200W S6 VOR35BV	108,500 lm	957 cool white
911401699709	BVP572 LED1034/957 1200W S7 VOR35BV	103,400 lm	957 cool white
911401699809	BVP572 LED998/957 1200W S8 VOR35BV	99,800 lm	957 cool white
911401699909	BVP572 LED998/957 1200W S9 VOR35BV	99,800 lm	957 cool white
911401601110	BVP571 LED663/957 600W S3 ROHB	66,300 lm	957 cool white
911401601410	BVP571 LED552/957 600W S3 VOROHB	55,200 lm	957 cool white
911401694909	BVP571 LED663/957 600W S6 ROBV	66,300 lm	957 cool white
911401695509	BVP571 LED538/957 600W S5 VOROVB	53,800 lm	957 cool white
911401695609	BVP571 LED499/957 600W S8 VOROVB	49,900 lm	957 cool white
911401696109	BVP571 LED663/957 600W S2 ROBV	66,300 lm	957 cool white
911401696209	BVP571 LED663/957 600W S3 ROBV	66,300 lm	957 cool white
911401696309	BVP571 LED663/957 600W S4 ROBV	66,300 lm	957 cool white
911401696409	BVP571 LED663/957 600W S5 ROBV	66,300 lm	957 cool white
911401696509	BVP571 LED663/957 600W S7 ROBV	66,300 lm	957 cool white
911401696609	BVP571 LED663/957 600W S8 ROBV	66,300 lm	957 cool white
911401696709	BVP571 LED663/957 600W S9 ROBV	66,300 lm	957 cool white

Order Code	Full Product Name	Luminous Flux	Light source color
911401698409	BVP571 LED555/957 600W S2 VOR0BV	55,500 lm	957 cool white
911401698509	BVP571 LED552/957 600W S3 VOR0BV	55,200 lm	957 cool white
911401698609	BVP571 LED547/957 600W S4 VOR0BV	54,700 lm	957 cool white
911401698709	BVP571 LED528/957 600W S6 VOR0BV	52,800 lm	957 cool white
911401698809	BVP571 LED502/957 600W S7 VOR0BV	50,200 lm	957 cool white
911401698909	BVP571 LED499/957 600W S9 VOR0BV	49,900 lm	957 cool white

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401600010	BVP573 LED1412/957 1400W S3 VOR35BV	1,400 W
911401600110	BVP573 LED1491/957 1500W S3 VOR35BV	1,500 W
911401600210	BVP573 LED1571/957 1600W S3 VOR35BV	1,600 W
911401600310	BVP573 LED1722/957 1800W S2 VOR35BV	1,800 W
911401600410	BVP573 LED1711/957 1800W S3 VOR35BV	1,800 W
911401600510	BVP573 LED1705/957 1800W S4 VOR35BV	1,800 W
911401600610	BVP573 LED1679/957 1800W S5 VOR35BV	1,800 W
911401600710	BVP573 LED1628/957 1800W S6 VOR35BV	1,800 W
911401600810	BVP573 LED1551/957 1800W S7 VOR35BV	1,800 W
911401600910	BVP573 LED1497/957 1800W S8 VOR35BV	1,800 W
911401601010	BVP573 LED1497/957 1800W S9 VOR35BV	1,800 W
911401601310	BVP573 LED1989/957 1800W S3 ROHB	1,800 W
911401601610	BVP573 LED1711/957 1800W S3 VOR35HB	1,800 W
911401695409	BVP573 LED1989/957 1800W S4 ROBV	1,800 W
911401697409	BVP573 LED1641/957 1400W S3 ROBV	1,400 W
911401697509	BVP573 LED1734/957 1500W S3 ROBV	1,500 W
911401697609	BVP573 LED1826/957 1600W S3 ROBV	1,600 W
911401697709	BVP573 LED1989/957 1800W S2 ROBV	1,800 W
911401697809	BVP573 LED1989/957 1800W S3 ROBV	1,800 W
911401697909	BVP573 LED1989/957 1800W S5 ROBV	1,800 W
911401698009	BVP573 LED1989/957 1800W S6 ROBV	1,800 W
911401698109	BVP573 LED1989/957 1800W S7 ROBV	1,800 W
911401698209	BVP573 LED1989/957 1800W S8 ROBV	1,800 W
911401698309	BVP573 LED1989/957 1800W S9 ROBV	1,800 W
911401601210	BVP572 LED1326/957 1200W S3 ROHB	1,200 W
911401601510	BVP572 LED1141/957 1200W S3 VOR35HB	1,200 W
911401613110	BVP572 LED1681/757 1200W S9 ROBV	1,200 W
911401695009	BVP572 LED1326/957 1200W S3 ROBV	1,200 W
911401695109	BVP572 LED1326/957 1200W S5 ROBV	1,200 W

Order Code	Full Product Name	Power Consumption
911401695209	BVP572 LED1326/957 1200W S7 ROBV	1,200 W
911401695309	BVP572 LED1326/957 1200W S9 ROBV	1,200 W
911401696809	BVP572 LED1065/957 900W S3 ROBV	900 W
911401696909	BVP572 LED1161/957 1000W S3 ROBV	1,000 W
911401697009	BVP572 LED1326/957 1200W S2 ROBV	1,200 W
911401697109	BVP572 LED1326/957 1200W S4 ROBV	1,200 W
911401697209	BVP572 LED1326/957 1200W S6 ROBV	1,200 W
911401697309	BVP572 LED1326/957 1200W S8 ROBV	1,200 W
911401699009	BVP572 LED916/957 900W S3 VOR35BV	900 W
911401699109	BVP572 LED999/957 1000W S3 VOR35BV	1,000 W
911401699209	BVP572 LED1148/957 1200W S2 VOR35BV	1,200 W
911401699309	BVP572 LED1141/957 1200W S3 VOR35BV	1,200 W
911401699409	BVP572 LED1136/957 1200W S4 VOR35BV	1,200 W
911401699509	BVP572 LED1119/957 1200W S5 VOR35BV	1,200 W
911401699609	BVP572 LED1085/957 1200W S6 VOR35BV	1,200 W
911401699709	BVP572 LED1034/957 1200W S7 VOR35BV	1,200 W
911401699809	BVP572 LED998/957 1200W S8 VOR35BV	1,200 W
911401699909	BVP572 LED998/957 1200W S9 VOR35BV	1,200 W
911401601110	BVP571 LED663/957 600W S3 ROHB	600 W
911401601410	BVP571 LED552/957 600W S3 VOR0HB	600 W
911401694909	BVP571 LED663/957 600W S6 ROBV	600 W
911401695509	BVP571 LED538/957 600W S5 VOR0BV	600 W
911401695609	BVP571 LED499/957 600W S8 VOR0BV	600 W
911401696109	BVP571 LED663/957 600W S2 ROBV	600 W
911401696209	BVP571 LED663/957 600W S3 ROBV	600 W
911401696309	BVP571 LED663/957 600W S4 ROBV	600 W
911401696409	BVP571 LED663/957 600W S5 ROBV	600 W
911401696509	BVP571 LED663/957 600W S7 ROBV	600 W
911401696609	BVP571 LED663/957 600W S8 ROBV	600 W
911401696709	BVP571 LED663/957 600W S9 ROBV	600 W
911401698409	BVP571 LED555/957 600W S2 VOR0BV	600 W
911401698509	BVP571 LED552/957 600W S3 VOR0BV	600 W
911401698609	BVP571 LED547/957 600W S4 VOR0BV	600 W
911401698709	BVP571 LED528/957 600W S6 VOR0BV	600 W
911401698809	BVP571 LED502/957 600W S7 VOR0BV	600 W
911401698909	BVP571 LED499/957 600W S9 VOR0BV	600 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401600010	BVP573 LED1412/957 1400W S3 VOR35BV	DMX
911401600110	BVP573 LED1491/957 1500W S3 VOR35BV	DMX
911401600210	BVP573 LED1571/957 1600W S3 VOR35BV	DMX
911401600310	BVP573 LED1722/957 1800W S2 VOR35BV	DMX
911401600410	BVP573 LED1711/957 1800W S3 VOR35BV	DMX
911401600510	BVP573 LED1705/957 1800W S4 VOR35BV	DMX
911401600610	BVP573 LED1679/957 1800W S5 VOR35BV	DMX
911401600710	BVP573 LED1628/957 1800W S6 VOR35BV	DMX
911401600810	BVP573 LED1551/957 1800W S7 VOR35BV	DMX
911401600910	BVP573 LED1497/957 1800W S8 VOR35BV	DMX
911401601010	BVP573 LED1497/957 1800W S9 VOR35BV	DMX
911401601310	BVP573 LED1989/957 1800W S3 ROHB	DMX
911401601610	BVP573 LED1711/957 1800W S3 VOR35HB	DMX
911401695409	BVP573 LED1989/957 1800W S4 ROBV	DMX
911401697409	BVP573 LED1641/957 1400W S3 ROBV	DMX
911401697509	BVP573 LED1734/957 1500W S3 ROBV	DMX
911401697609	BVP573 LED1826/957 1600W S3 ROBV	DMX
911401697709	BVP573 LED1989/957 1800W S2 ROBV	DMX
911401697809	BVP573 LED1989/957 1800W S3 ROBV	DMX
911401697909	BVP573 LED1989/957 1800W S5 ROBV	DMX
911401698009	BVP573 LED1989/957 1800W S6 ROBV	DMX
911401698109	BVP573 LED1989/957 1800W S7 ROBV	DMX
911401698209	BVP573 LED1989/957 1800W S8 ROBV	DMX
911401698309	BVP573 LED1989/957 1800W S9 ROBV	DMX
911401601210	BVP572 LED1326/957 1200W S3 ROHB	DMX
911401601510	BVP572 LED1141/957 1200W S3 VOR35HB	DMX
911401613110	BVP572 LED1681/757 1200W S9 ROBV	DALI
911401695009	BVP572 LED1326/957 1200W S3 ROBV	DMX
911401695109	BVP572 LED1326/957 1200W S5 ROBV	DMX
911401695209	BVP572 LED1326/957 1200W S7 ROBV	DMX
911401695309	BVP572 LED1326/957 1200W S9 ROBV	DMX
911401696809	BVP572 LED1065/957 900W S3 ROBV	DMX
911401696909	BVP572 LED1161/957 1000W S3 ROBV	DMX
911401697009	BVP572 LED1326/957 1200W S2 ROBV	DMX
911401697109	BVP572 LED1326/957 1200W S4 ROBV	DMX
911401697209	BVP572 LED1326/957 1200W S6 ROBV	DMX
911401697309	BVP572 LED1326/957 1200W S8 ROBV	DMX

Order Code	Full Product Name	Dimmable
911401699009	BVP572 LED916/957 900W S3 VOR35BV	DMX
911401699109	BVP572 LED999/957 1000W S3 VOR35BV	DMX
911401699209	BVP572 LED1148/957 1200W S2 VOR35BV	DMX
911401699309	BVP572 LED1141/957 1200W S3 VOR35BV	DMX
911401699409	BVP572 LED1136/957 1200W S4 VOR35BV	DMX
911401699509	BVP572 LED1119/957 1200W S5 VOR35BV	DMX
911401699609	BVP572 LED1085/957 1200W S6 VOR35BV	DMX
911401699709	BVP572 LED1034/957 1200W S7 VOR35BV	DMX
911401699809	BVP572 LED998/957 1200W S8 VOR35BV	DMX
911401699909	BVP572 LED998/957 1200W S9 VOR35BV	DMX
911401601110	BVP571 LED663/957 600W S3 ROHB	DMX
911401601410	BVP571 LED552/957 600W S3 VOROHB	DMX
911401694909	BVP571 LED663/957 600W S6 ROBV	DMX
911401695509	BVP571 LED538/957 600W S5 VOROBV	DMX
911401695609	BVP571 LED499/957 600W S8 VOROBV	DMX
911401696109	BVP571 LED663/957 600W S2 ROBV	DMX
911401696209	BVP571 LED663/957 600W S3 ROBV	DMX
911401696309	BVP571 LED663/957 600W S4 ROBV	DMX
911401696409	BVP571 LED663/957 600W S5 ROBV	DMX
911401696509	BVP571 LED663/957 600W S7 ROBV	DMX
911401696609	BVP571 LED663/957 600W S8 ROBV	DMX
911401696709	BVP571 LED663/957 600W S9 ROBV	DMX
911401698409	BVP571 LED555/957 600W S2 VOROBV	DMX
911401698509	BVP571 LED552/957 600W S3 VOROBV	DMX
911401698609	BVP571 LED547/957 600W S4 VOROBV	DMX
911401698709	BVP571 LED528/957 600W S6 VOROBV	DMX
911401698809	BVP571 LED502/957 600W S7 VOROBV	DMX
911401698909	BVP571 LED499/957 600W S9 VOROBV	DMX

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401600010	BVP573 LED1412/957 1400W S3 VOR35BV	RAL 9007
911401600110	BVP573 LED1491/957 1500W S3 VOR35BV	RAL 9007
911401600210	BVP573 LED1571/957 1600W S3 VOR35BV	RAL 9007
911401600310	BVP573 LED1722/957 1800W S2 VOR35BV	RAL 9007
911401600410	BVP573 LED1711/957 1800W S3 VOR35BV	RAL 9007
911401600510	BVP573 LED1705/957 1800W S4 VOR35BV	RAL 9007
911401600610	BVP573 LED1679/957 1800W S5 VOR35BV	RAL 9007

Order Code	Full Product Name	Housing Color
911401600710	BVP573 LED1628/957 1800W S6 VOR35BV	RAL 9007
911401600810	BVP573 LED1551/957 1800W S7 VOR35BV	RAL 9007
911401600910	BVP573 LED1497/957 1800W S8 VOR35BV	RAL 9007
911401601010	BVP573 LED1497/957 1800W S9 VOR35BV	RAL 9007
911401601310	BVP573 LED1989/957 1800W S3 ROHB	RAL 9007
911401601610	BVP573 LED1711/957 1800W S3 VOR35HB	RAL 9007
911401695409	BVP573 LED1989/957 1800W S4 ROBV	RAL 9007
911401697409	BVP573 LED1641/957 1400W S3 ROBV	RAL 9007
911401697509	BVP573 LED1734/957 1500W S3 ROBV	RAL 9007
911401697609	BVP573 LED1826/957 1600W S3 ROBV	RAL 9007
911401697709	BVP573 LED1989/957 1800W S2 ROBV	RAL 9007
911401697809	BVP573 LED1989/957 1800W S3 ROBV	RAL 9007
911401697909	BVP573 LED1989/957 1800W S5 ROBV	RAL 9007
911401698009	BVP573 LED1989/957 1800W S6 ROBV	RAL 9007
911401698109	BVP573 LED1989/957 1800W S7 ROBV	RAL 9007
911401698209	BVP573 LED1989/957 1800W S8 ROBV	RAL 9007
911401698309	BVP573 LED1989/957 1800W S9 ROBV	RAL 9007
911401601210	BVP572 LED1326/957 1200W S3 ROHB	RAL 9007
911401601510	BVP572 LED1141/957 1200W S3 VOR35HB	RAL 9007
911401613110	BVP572 LED1681/757 1200W S9 ROBV	Dark gray
911401695009	BVP572 LED1326/957 1200W S3 ROBV	RAL 9007
911401695109	BVP572 LED1326/957 1200W S5 ROBV	RAL 9007
911401695209	BVP572 LED1326/957 1200W S7 ROBV	RAL 9007
911401695309	BVP572 LED1326/957 1200W S9 ROBV	RAL 9007
911401696809	BVP572 LED1065/957 900W S3 ROBV	RAL 9007
911401696909	BVP572 LED1161/957 1000W S3 ROBV	RAL 9007
911401697009	BVP572 LED1326/957 1200W S2 ROBV	RAL 9007
911401697109	BVP572 LED1326/957 1200W S4 ROBV	RAL 9007
911401697209	BVP572 LED1326/957 1200W S6 ROBV	RAL 9007
911401697309	BVP572 LED1326/957 1200W S8 ROBV	RAL 9007
911401699009	BVP572 LED916/957 900W S3 VOR35BV	RAL 9007
911401699109	BVP572 LED999/957 1000W S3 VOR35BV	RAL 9007
911401699209	BVP572 LED1148/957 1200W S2 VOR35BV	RAL 9007
911401699309	BVP572 LED1141/957 1200W S3 VOR35BV	RAL 9007
911401699409	BVP572 LED1136/957 1200W S4 VOR35BV	RAL 9007
911401699509	BVP572 LED1119/957 1200W S5 VOR35BV	RAL 9007
911401699609	BVP572 LED1085/957 1200W S6 VOR35BV	RAL 9007
911401699709	BVP572 LED1034/957 1200W S7 VOR35BV	RAL 9007
911401699809	BVP572 LED998/957 1200W S8 VOR35BV	RAL 9007
911401699909	BVP572 LED998/957 1200W S9 VOR35BV	RAL 9007

Order Code	Full Product Name	Housing Color
911401601110	BVP571 LED663/957 600W S3 ROHB	RAL 9007
911401601410	BVP571 LED552/957 600W S3 VOR0HB	RAL 9007
911401694909	BVP571 LED663/957 600W S6 ROBV	RAL 9007
911401695509	BVP571 LED538/957 600W S5 VOR0BV	RAL 9007
911401695609	BVP571 LED499/957 600W S8 VOR0BV	RAL 9007
911401696109	BVP571 LED663/957 600W S2 ROBV	RAL 9007
911401696209	BVP571 LED663/957 600W S3 ROBV	RAL 9007
911401696309	BVP571 LED663/957 600W S4 ROBV	RAL 9007
911401696409	BVP571 LED663/957 600W S5 ROBV	RAL 9007
911401696509	BVP571 LED663/957 600W S7 ROBV	RAL 9007
911401696609	BVP571 LED663/957 600W S8 ROBV	RAL 9007
911401696709	BVP571 LED663/957 600W S9 ROBV	RAL 9007
911401698409	BVP571 LED555/957 600W S2 VOR0BV	RAL 9007
911401698509	BVP571 LED552/957 600W S3 VOR0BV	RAL 9007
911401698609	BVP571 LED547/957 600W S4 VOR0BV	RAL 9007
911401698709	BVP571 LED528/957 600W S6 VOR0BV	RAL 9007
911401698809	BVP571 LED502/957 600W S7 VOR0BV	RAL 9007
911401698909	BVP571 LED499/957 600W S9 VOR0BV	RAL 9007