



# GreenPerform Canopy Mini500 Gen4: A high-performance, versatile, energy- saving LED

## GreenPerform Canopy Mini500 G4

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

### Benefits

- Excellent energy savings
- Long-term quality and reliability
- Choice of optics
- Flexible installation options
- Range of control and connectivity platforms

# GreenPerform Canopy Mini500 G4

## Features

- Up to 160 lm/W system efficacy
- 60,000 hours lifetime @Ta 35°C
- Outdoor and edge area (Asymmetry WB), general area (WB), emphasizing and limited area (NB)
- Recessed (BBP), Surface & frame (BCP), Pole (BGP)
- DALI control, GU5.3 for emergency lighting, EcoSet sensor

## Application

- Petrol and Convenience
- Parking Garages
- Food Processing

## Specifications

<b>Mounting type</b>	Recessed
	Surface
	Pole
<b>Operating Temperature range</b>	- 40 to +50 °C
<b>Light Source</b>	LED
<b>Mains Voltage</b>	2320-240V / 50-60Hz
<b>Mains connection</b>	Flying cable
<b>Mechanical Accessories</b>	Clamp
<b>Dimming</b>	PSU: non-dimmable PSD: Dimmable via Dali-broadcasting
<b>Control system input</b>	DALI
<b>Material</b>	Housing: die-cast aluminium
<b>Main color of the luminaire</b>	RAL9003
<b>Flicker / Pst / SVM</b>	<3.2% / 0.5 / 0.4
<b>Luminous flux</b>	8.5klm - 18klm
<b>Power consumption</b>	53W - 128W
<b>Luminaire efficacy</b>	Up to 160lm/W
<b>Correlated color temperature - CCT</b>	4000K 6000K

<b>Color Rendering index - CRI</b>	80
<b>Beam angle</b>	S-WB: 115° S-MB: 90° A-WB: 110°*80°
<b>Optical cover/lens material</b>	Lens: PC Cover: Glass
<b>Optical cover/lens finish</b>	Clear
<b>Protection Class IEC61140</b>	Class I
<b>Mechanical impact protection</b>	IK07
<b>Ingress protection</b>	IP65
<b>Driver replaceable</b>	Yes
<b>Installation</b>	Recessed Surface Pole








## Versions



### GreenPerform Canopy Mini500 G9

# GreenPerform Canopy Mini500 G4

## Dimensional drawing



# GreenPerform Canopy Mini500 G4

General Information	
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Color	White
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401502742	BCP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
911401502842	BCP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
911401502942	BCP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401503042	BCP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
911401503142	BCP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
911401503242	BCP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401503342	BCP500 G4 LED125/NW PSU S-WB	4000 K	159 lm/W	12,638 lm
911401503442	BCP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
911401503542	BCP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
911401503642	BCP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
911401503742	BCP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
911401503842	BCP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
911401503942	BCP500 G4 LED140/NW PSU S-WB	4000 K	155 lm/W	14,079 lm
911401504042	BCP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
911401504142	BCP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401504242	BCP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
911401504342	BCP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
911401504442	BCP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401504542	BCP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm
911401504642	BCP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
911401504742	BCP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401504842	BCP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
911401504942	BCP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
911401505042	BCP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	4000 K	157 lm/W	8,313 lm
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	4000 K	157 lm/W	8,313 lm
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	4000 K	157 lm/W	8,313 lm
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	6500 K	157 lm/W	8,313 lm
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	6500 K	157 lm/W	8,313 lm

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	6500 K	157 lm/W	8,313 lm
911401510542	BCP500 G4 LED125/NW PSU S- WB PC	4000 K	156 lm/W	12,366 lm
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	4000 K	156 lm/W	12,366 lm
911401510742	BCP500 G4 LED125/NW PSU A- WB PC	4000 K	156 lm/W	12,366 lm
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	6500 K	156 lm/W	12,366 lm
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	6500 K	156 lm/W	12,366 lm
911401511042	BCP500 G4 LED125/CW PSU A- WB PC	6500 K	156 lm/W	12,366 lm
911401511142	BCP500 G4 LED140/NW PSU S- WB PC	4000 K	152 lm/W	13,777 lm
911401511242	BCP500 G4 LED140/NW PSU S- MB PC	4000 K	152 lm/W	13,777 lm
911401511342	BCP500 G4 LED140/NW PSU A- WB PC	4000 K	152 lm/W	13,777 lm
911401511442	BCP500 G4 LED140/CW PSU S- WB PC	6500 K	152 lm/W	13,777 lm
911401511542	BCP500 G4 LED140/CW PSU S- MB PC	6500 K	152 lm/W	13,777 lm
911401511642	BCP500 G4 LED140/CW PSU A- WB PC	6500 K	152 lm/W	13,777 lm
911401511742	BCP500 G4 LED180/NW PSU S- WB PC	4000 K	145 lm/W	17,677 lm
911401511842	BCP500 G4 LED180/NW PSU S- MB PC	4000 K	145 lm/W	17,677 lm
911401511942	BCP500 G4 LED180/NW PSU A- WB PC	4000 K	145 lm/W	17,677 lm
911401512042	BCP500 G4 LED180/CW PSU S- WB PC	6500 K	145 lm/W	17,677 lm
911401512142	BCP500 G4 LED180/CW PSU S- MB PC	6500 K	145 lm/W	17,677 lm
911401512242	BCP500 G4 LED180/CW PSU A- WB PC	6500 K	145 lm/W	17,677 lm
911401507542	BCP500 G4 LED85/NW GU5.3 S- WB	4000 K	160 lm/W	8,496 lm
911401507642	BCP500 G4 LED85/NW GU5.3 S- MB	4000 K	160 lm/W	8,496 lm
911401507742	BCP500 G4 LED85/NW GU5.3 A- WB	4000 K	160 lm/W	8,496 lm
911401507842	BCP500 G4 LED85/CW GU5.3 S- WB	6500 K	160 lm/W	8,496 lm
911401507942	BCP500 G4 LED85/CW GU5.3 S- MB	6500 K	160 lm/W	8,496 lm
911401508042	BCP500 G4 LED85/CW GU5.3 A- WB	6500 K	160 lm/W	8,496 lm

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	4000 K	160 lm/W	8,496 lm
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	4000 K	160 lm/W	8,496 lm
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	4000 K	160 lm/W	8,496 lm
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	6500 K	160 lm/W	8,496 lm

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	6500 K	160 lm/W	8,496 lm
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	6500 K	160 lm/W	8,496 lm
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
911401512342	BGP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401512442	BGP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401512542	BGP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
911401512642	BGP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
911401512742	BGP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401512842	BGP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401512942	BGP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401513042	BGP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401505142	BCP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
911401505242	BCP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
911401505342	BCP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401505442	BCP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
911401505542	BCP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
911401505642	BCP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
911401505742	BCP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
911401505842	BCP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
911401505942	BCP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
911401506042	BCP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
911401506142	BCP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
911401506242	BCP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
911401506342	BCP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
911401506442	BCP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
911401506542	BCP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
911401506642	BCP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
911401506742	BCP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
911401506842	BCP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm
911401506942	BCP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
911401507042	BCP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
911401507142	BCP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
911401507242	BCP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
911401507342	BCP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
911401507442	BCP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	4000 K	157 lm/W	8,313 lm
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	4000 K	157 lm/W	8,313 lm
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	4000 K	157 lm/W	8,313 lm
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	6500 K	157 lm/W	8,313 lm
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	6500 K	157 lm/W	8,313 lm
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	6500 K	157 lm/W	8,313 lm
911401500942	BBP500 G4 LED125/NW PSU S-WB WB PC	4000 K	156 lm/W	12,366 lm

# GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	4000 K	156 lm/W	12,366 lm
911401501142	BBP500 G4 LED125/NW PSU A- WB PC	4000 K	156 lm/W	12,366 lm
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	6500 K	156 lm/W	12,366 lm
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	6500 K	156 lm/W	12,366 lm
911401501442	BBP500 G4 LED125/CW PSU A- WB PC	6500 K	156 lm/W	12,366 lm
911401501542	BBP500 G4 LED140/NW PSU S- WB PC	4000 K	152 lm/W	13,777 lm
911401501642	BBP500 G4 LED140/NW PSU S- MB PC	4000 K	152 lm/W	13,777 lm
911401501742	BBP500 G4 LED140/NW PSU A- WB PC	4000 K	152 lm/W	13,777 lm
911401501842	BBP500 G4 LED140/CW PSU S- WB PC	6500 K	152 lm/W	13,777 lm
911401501942	BBP500 G4 LED140/CW PSU S- MB PC	6500 K	152 lm/W	13,777 lm
911401502042	BBP500 G4 LED140/CW PSU A- WB PC	6500 K	152 lm/W	13,777 lm
911401502142	BBP500 G4 LED180/NW PSU S- WB PC	4000 K	145 lm/W	17,677 lm
911401502242	BBP500 G4 LED180/NW PSU S- MB PC	4000 K	145 lm/W	17,677 lm
911401502342	BBP500 G4 LED180/NW PSU A- WB PC	4000 K	145 lm/W	17,677 lm
911401502442	BBP500 G4 LED180/CW PSU S- WB PC	6500 K	145 lm/W	17,677 lm
911401502542	BBP500 G4 LED180/CW PSU S- MB PC	6500 K	145 lm/W	17,677 lm
911401502642	BBP500 G4 LED180/CW PSU A- WB PC	6500 K	145 lm/W	17,677 lm
911401593132	BBP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
911401593232	BBP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
911401593332	BBP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401593432	BBP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
911401593532	BBP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
911401593632	BBP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401593732	BBP500 G4 LED125/NW PSU S- WB	4000 K	159 lm/W	12,638 lm
911401593832	BBP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
911401593932	BBP500 G4 LED125/NW PSU A- WB	4000 K	159 lm/W	12,638 lm
911401594032	BBP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
911401594132	BBP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
911401594232	BBP500 G4 LED125/CW PSU A- WB	6500 K	159 lm/W	12,638 lm
911401594332	BBP500 G4 LED140/NW PSU S- WB	4000 K	155 lm/W	14,079 lm

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401594432	BBP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
911401594532	BBP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401594632	BBP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
911401594732	BBP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
911401594832	BBP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401594932	BBP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm
911401595032	BBP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
911401595132	BBP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401595232	BBP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
911401595332	BBP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
911401595432	BBP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401595532	BBP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
911401595632	BBP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
911401595732	BBP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm
911401595832	BBP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
911401595932	BBP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
911401596032	BBP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
911401596132	BBP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
911401596232	BBP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
911401596332	BBP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
911401596432	BBP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
911401596532	BBP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
911401596632	BBP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
911401596732	BBP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
911401596832	BBP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
911401596932	BBP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
911401597032	BBP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
911401597132	BBP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
911401597232	BBP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm

# GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401597332	BBP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
911401597432	BBP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
911401597532	BBP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
911401597632	BBP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
911401597732	BBP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
911401597832	BBP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401502742	BCP500 G4 LED85/NW PSU S-WB	53 W	911401511042	BCP500 G4 LED125/CW PSU A-WB PC	79 W
911401502842	BCP500 G4 LED85/NW PSU S-MB	53 W	911401511142	BCP500 G4 LED140/NW PSU S-WB PC	91 W
911401502942	BCP500 G4 LED85/NW PSU A-WB	53 W	911401511242	BCP500 G4 LED140/NW PSU S-MB PC	91 W
911401503042	BCP500 G4 LED85/CW PSU S-WB	53 W	911401511342	BCP500 G4 LED140/NW PSU A-WB PC	91 W
911401503142	BCP500 G4 LED85/CW PSU S-MB	53 W	911401511442	BCP500 G4 LED140/CW PSU S-WB PC	91 W
911401503242	BCP500 G4 LED85/CW PSU A-WB	53 W	911401511542	BCP500 G4 LED140/CW PSU S-MB PC	91 W
911401503342	BCP500 G4 LED125/NW PSU S-WB	79 W	911401511642	BCP500 G4 LED140/CW PSU A-WB PC	91 W
911401503442	BCP500 G4 LED125/NW PSU S-MB	79 W	911401511742	BCP500 G4 LED180/NW PSU S-WB PC	122 W
911401503542	BCP500 G4 LED125/NW PSU A-WB	79 W	911401511842	BCP500 G4 LED180/NW PSU S-MB PC	122 W
911401503642	BCP500 G4 LED125/CW PSU S-WB	79 W	911401511942	BCP500 G4 LED180/NW PSU A-WB PC	122 W
911401503742	BCP500 G4 LED125/CW PSU S-MB	79 W	911401512042	BCP500 G4 LED180/CW PSU S-WB PC	122 W
911401503842	BCP500 G4 LED125/CW PSU A-WB	79 W	911401512142	BCP500 G4 LED180/CW PSU S-MB PC	122 W
911401503942	BCP500 G4 LED140/NW PSU S-WB	91 W	911401512242	BCP500 G4 LED180/CW PSU A-WB PC	122 W
911401504042	BCP500 G4 LED140/NW PSU S-MB	91 W	911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	53 W
911401504142	BCP500 G4 LED140/NW PSU A-WB	91 W	911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	53 W
911401504242	BCP500 G4 LED140/CW PSU S-WB	91 W	911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	53 W
911401504342	BCP500 G4 LED140/CW PSU S-MB	91 W	911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	53 W
911401504442	BCP500 G4 LED140/CW PSU A-WB	91 W	911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	53 W
911401504542	BCP500 G4 LED180/NW PSU S-WB	122 W	911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	53 W
911401504642	BCP500 G4 LED180/NW PSU S-MB	122 W	911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	79 W
911401504742	BCP500 G4 LED180/NW PSU A-WB	122 W	911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	79 W
911401504842	BCP500 G4 LED180/CW PSU S-WB	122 W	911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	79 W
911401504942	BCP500 G4 LED180/CW PSU S-MB	122 W	911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	79 W
911401505042	BCP500 G4 LED180/CW PSU A-WB	122 W	911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	79 W
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	53 W	911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	79 W
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	53 W	911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	91 W
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	53 W	911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	91 W
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	53 W	911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	91 W
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	53 W	911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	91 W
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	53 W	911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	91 W
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	79 W	911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	91 W
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	79 W	911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	122 W
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	79 W	911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	122 W
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	79 W	911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	122 W
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	79 W	911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	122 W

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	122 W	911401506942	BCP500 G4 LED180/NW PSD S-WB	128 W
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	122 W	911401507042	BCP500 G4 LED180/NW PSD S-MB	128 W
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	122 W	911401507142	BCP500 G4 LED180/NW PSD A-WB	128 W
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	122 W	911401507242	BCP500 G4 LED180/CW PSD S-WB	128 W
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	122 W	911401507342	BCP500 G4 LED180/CW PSD S-MB	128 W
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	53 W	911401507442	BCP500 G4 LED180/CW PSD A-WB	128 W
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	53 W	911401500342	BBP500 G4 LED85/NW PSU S-WB PC	53 W
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	53 W	911401500442	BBP500 G4 LED85/NW PSU S-MB PC	53 W
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	53 W	911401500542	BBP500 G4 LED85/NW PSU A-WB PC	53 W
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	53 W	911401500642	BBP500 G4 LED85/CW PSU S-WB PC	53 W
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	53 W	911401500742	BBP500 G4 LED85/CW PSU S-MB PC	53 W
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	79 W	911401500842	BBP500 G4 LED85/CW PSU A-WB PC	53 W
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	79 W	911401500942	BBP500 G4 LED125/NW PSU S-WB PC	79 W
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	79 W	911401501042	BBP500 G4 LED125/NW PSU S-MB PC	79 W
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	79 W	911401501142	BBP500 G4 LED125/NW PSU A-WB PC	79 W
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	79 W	911401501242	BBP500 G4 LED125/CW PSU S-WB PC	79 W
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	79 W	911401501342	BBP500 G4 LED125/CW PSU S-MB PC	79 W
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	91 W	911401501442	BBP500 G4 LED125/CW PSU A-WB PC	79 W
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	91 W	911401501542	BBP500 G4 LED140/NW PSU S-WB PC	91 W
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	91 W	911401501642	BBP500 G4 LED140/NW PSU S-MB PC	91 W
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	91 W	911401501742	BBP500 G4 LED140/NW PSU A-WB PC	91 W
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	91 W	911401501842	BBP500 G4 LED140/CW PSU S-WB PC	91 W
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	91 W	911401501942	BBP500 G4 LED140/CW PSU S-MB PC	91 W
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	122 W	911401502042	BBP500 G4 LED140/CW PSU A-WB PC	91 W
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	122 W	911401502142	BBP500 G4 LED180/NW PSU S-WB PC	122 W
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	122 W	911401502242	BBP500 G4 LED180/NW PSU S-MB PC	122 W
911401512342	BGP500 G4 LED85/NW PSU A-WB	53 W	911401502342	BBP500 G4 LED180/NW PSU A-WB PC	122 W
911401512442	BGP500 G4 LED85/CW PSU A-WB	53 W	911401502442	BBP500 G4 LED180/CW PSU S-WB PC	122 W
911401512542	BGP500 G4 LED125/NW PSU A-WB	79 W	911401502542	BBP500 G4 LED180/CW PSU S-MB PC	122 W
911401512642	BGP500 G4 LED125/CW PSU A-WB	79 W	911401502642	BBP500 G4 LED180/CW PSU A-WB PC	122 W
911401512742	BGP500 G4 LED140/NW PSU A-WB	91 W	911401593132	BBP500 G4 LED85/NW PSU S-WB	53 W
911401512842	BGP500 G4 LED140/CW PSU A-WB	91 W	911401593232	BBP500 G4 LED85/NW PSU S-MB	53 W
911401512942	BGP500 G4 LED180/NW PSU A-WB	122 W	911401593332	BBP500 G4 LED85/NW PSU A-WB	53 W
911401513042	BGP500 G4 LED180/CW PSU A-WB	122 W	911401593432	BBP500 G4 LED85/CW PSU S-WB	53 W
911401505142	BCP500 G4 LED85/NW PSD S-WB	58 W	911401593532	BBP500 G4 LED85/CW PSU S-MB	53 W
911401505242	BCP500 G4 LED85/NW PSD S-MB	58 W	911401593632	BBP500 G4 LED85/CW PSU A-WB	53 W
911401505342	BCP500 G4 LED85/NW PSD A-WB	58 W	911401593732	BBP500 G4 LED125/NW PSU S-WB	79 W
911401505442	BCP500 G4 LED85/CW PSD S-WB	58 W	911401593832	BBP500 G4 LED125/NW PSU S-MB	79 W
911401505542	BCP500 G4 LED85/CW PSD S-MB	58 W	911401593932	BBP500 G4 LED125/NW PSU A-WB	79 W
911401505642	BCP500 G4 LED85/CW PSD A-WB	58 W	911401594032	BBP500 G4 LED125/CW PSU S-WB	79 W
911401505742	BCP500 G4 LED125/NW PSD S-WB	85 W	911401594132	BBP500 G4 LED125/CW PSU S-MB	79 W
911401505842	BCP500 G4 LED125/NW PSD S-MB	85 W	911401594232	BBP500 G4 LED125/CW PSU A-WB	79 W
911401505942	BCP500 G4 LED125/NW PSD A-WB	85 W	911401594332	BBP500 G4 LED140/NW PSU S-WB	91 W
911401506042	BCP500 G4 LED125/CW PSD S-WB	85 W	911401594432	BBP500 G4 LED140/NW PSU S-MB	91 W
911401506142	BCP500 G4 LED125/CW PSD S-MB	85 W	911401594532	BBP500 G4 LED140/NW PSU A-WB	91 W
911401506242	BCP500 G4 LED125/CW PSD A-WB	85 W	911401594632	BBP500 G4 LED140/CW PSU S-WB	91 W
911401506342	BCP500 G4 LED140/NW PSD S-WB	96 W	911401594732	BBP500 G4 LED140/CW PSU S-MB	91 W
911401506442	BCP500 G4 LED140/NW PSD S-MB	96 W	911401594832	BBP500 G4 LED140/CW PSU A-WB	91 W
911401506542	BCP500 G4 LED140/NW PSD A-WB	96 W	911401594932	BBP500 G4 LED180/NW PSU S-WB	122 W
911401506642	BCP500 G4 LED140/CW PSD S-WB	96 W	911401595032	BBP500 G4 LED180/NW PSU S-MB	122 W
911401506742	BCP500 G4 LED140/CW PSD S-MB	96 W	911401595132	BBP500 G4 LED180/NW PSU A-WB	122 W
911401506842	BCP500 G4 LED140/CW PSD A-WB	96 W	911401595232	BBP500 G4 LED180/CW PSU S-WB	122 W

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption
911401595332	BBP500 G4 LED180/CW PSU S-MB	122 W
911401595432	BBP500 G4 LED180/CW PSU A-WB	122 W
911401595532	BBP500 G4 LED85/NW PSD S-WB	58 W
911401595632	BBP500 G4 LED85/NW PSD S-MB	58 W
911401595732	BBP500 G4 LED85/NW PSD A-WB	58 W
911401595832	BBP500 G4 LED85/CW PSD S-WB	58 W
911401595932	BBP500 G4 LED85/CW PSD S-MB	58 W
911401596032	BBP500 G4 LED85/CW PSD A-WB	58 W
911401596132	BBP500 G4 LED125/NW PSD S-WB	85 W
911401596232	BBP500 G4 LED125/NW PSD S-MB	85 W
911401596332	BBP500 G4 LED125/NW PSD A-WB	85 W
911401596432	BBP500 G4 LED125/CW PSD S-WB	85 W
911401596532	BBP500 G4 LED125/CW PSD S-MB	85 W

Order Code	Full Product Name	Power Consumption
911401596632	BBP500 G4 LED125/CW PSD A-WB	85 W
911401596732	BBP500 G4 LED140/NW PSD S-WB	96 W
911401596832	BBP500 G4 LED140/NW PSD S-MB	96 W
911401596932	BBP500 G4 LED140/NW PSD A-WB	96 W
911401597032	BBP500 G4 LED140/CW PSD S-WB	96 W
911401597132	BBP500 G4 LED140/CW PSD S-MB	96 W
911401597232	BBP500 G4 LED140/CW PSD A-WB	96 W
911401597332	BBP500 G4 LED180/NW PSD S-WB	128 W
911401597432	BBP500 G4 LED180/NW PSD S-MB	128 W
911401597532	BBP500 G4 LED180/NW PSD A-WB	128 W
911401597632	BBP500 G4 LED180/CW PSD S-WB	128 W
911401597732	BBP500 G4 LED180/CW PSD S-MB	128 W
911401597832	BBP500 G4 LED180/CW PSD A-WB	128 W

### Controls and Dimming

Order Code	Full Product Name	Dimmable
911401502742	BCP500 G4 LED85/NW PSU S-WB	No
911401502842	BCP500 G4 LED85/NW PSU S-MB	No
911401502942	BCP500 G4 LED85/NW PSU A-WB	No
911401503042	BCP500 G4 LED85/CW PSU S-WB	No
911401503142	BCP500 G4 LED85/CW PSU S-MB	No
911401503242	BCP500 G4 LED85/CW PSU A-WB	No
911401503342	BCP500 G4 LED125/NW PSU S-WB	No
911401503442	BCP500 G4 LED125/NW PSU S-MB	No
911401503542	BCP500 G4 LED125/NW PSU A-WB	No
911401503642	BCP500 G4 LED125/CW PSU S-WB	No
911401503742	BCP500 G4 LED125/CW PSU S-MB	No
911401503842	BCP500 G4 LED125/CW PSU A-WB	No
911401503942	BCP500 G4 LED140/NW PSU S-WB	No
911401504042	BCP500 G4 LED140/NW PSU S-MB	No
911401504142	BCP500 G4 LED140/NW PSU A-WB	No
911401504242	BCP500 G4 LED140/CW PSU S-WB	No
911401504342	BCP500 G4 LED140/CW PSU S-MB	No
911401504442	BCP500 G4 LED140/CW PSU A-WB	No
911401504542	BCP500 G4 LED180/NW PSU S-WB	No
911401504642	BCP500 G4 LED180/NW PSU S-MB	No
911401504742	BCP500 G4 LED180/NW PSU A-WB	No
911401504842	BCP500 G4 LED180/CW PSU S-WB	No
911401504942	BCP500 G4 LED180/CW PSU S-MB	No
911401505042	BCP500 G4 LED180/CW PSU A-WB	No
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	No
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	No
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	No
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	No
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	No
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	No
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	No
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	No
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	No
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	No
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	No

Order Code	Full Product Name	Dimmable
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	No
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	No
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	No
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	No
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	No
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	No
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	No
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	No
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	No
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	No
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	No
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	No
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	No
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	No
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	No
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	No
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	No
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	No
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	No
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	No
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	No
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	No
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	No
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	No
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	No
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	No
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	No
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	No
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	No
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	No
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	No
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	No
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	No
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	No
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	No

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	No	911401506942	BCP500 G4 LED180/NW PSD S-WB	DALI
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	No	911401507042	BCP500 G4 LED180/NW PSD S-MB	DALI
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	No	911401507142	BCP500 G4 LED180/NW PSD A-WB	DALI
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	No	911401507242	BCP500 G4 LED180/CW PSD S-WB	DALI
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	No	911401507342	BCP500 G4 LED180/CW PSD S-MB	DALI
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	No	911401507442	BCP500 G4 LED180/CW PSD A-WB	DALI
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	No	911401500342	BBP500 G4 LED85/NW PSU S-WB PC	No
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	No	911401500442	BBP500 G4 LED85/NW PSU S-MB PC	No
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	No	911401500542	BBP500 G4 LED85/NW PSU A-WB PC	No
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	No	911401500642	BBP500 G4 LED85/CW PSU S-WB PC	No
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	No	911401500742	BBP500 G4 LED85/CW PSU S-MB PC	No
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	No	911401500842	BBP500 G4 LED85/CW PSU A-WB PC	No
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	No	911401500942	BBP500 G4 LED125/NW PSU S-WB PC	No
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	No	911401501042	BBP500 G4 LED125/NW PSU S-MB PC	No
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	No	911401501142	BBP500 G4 LED125/NW PSU A-WB PC	No
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	No	911401501242	BBP500 G4 LED125/CW PSU S-WB PC	No
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	No	911401501342	BBP500 G4 LED125/CW PSU S-MB PC	No
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	No	911401501442	BBP500 G4 LED125/CW PSU A-WB PC	No
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	No	911401501542	BBP500 G4 LED140/NW PSU S-WB PC	No
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	No	911401501642	BBP500 G4 LED140/NW PSU S-MB PC	No
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	No	911401501742	BBP500 G4 LED140/NW PSU A-WB PC	No
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	No	911401501842	BBP500 G4 LED140/CW PSU S-WB PC	No
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	No	911401501942	BBP500 G4 LED140/CW PSU S-MB PC	No
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	No	911401502042	BBP500 G4 LED140/CW PSU A-WB PC	No
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	No	911401502142	BBP500 G4 LED180/NW PSU S-WB PC	No
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	No	911401502242	BBP500 G4 LED180/NW PSU S-MB PC	No
911401512342	BGP500 G4 LED85/NW PSU A-WB	No	911401502342	BBP500 G4 LED180/NW PSU A-WB PC	No
911401512442	BGP500 G4 LED85/CW PSU A-WB	No	911401502442	BBP500 G4 LED180/CW PSU S-WB PC	No
911401512542	BGP500 G4 LED125/NW PSU A-WB	No	911401502542	BBP500 G4 LED180/CW PSU S-MB PC	No
911401512642	BGP500 G4 LED125/CW PSU A-WB	No	911401502642	BBP500 G4 LED180/CW PSU A-WB PC	No
911401512742	BGP500 G4 LED140/NW PSU A-WB	No	911401593132	BBP500 G4 LED85/NW PSU S-WB	No
911401512842	BGP500 G4 LED140/CW PSU A-WB	No	911401593232	BBP500 G4 LED85/NW PSU S-MB	No
911401512942	BGP500 G4 LED180/NW PSU A-WB	No	911401593332	BBP500 G4 LED85/NW PSU A-WB	No
911401513042	BGP500 G4 LED180/CW PSU A-WB	No	911401593432	BBP500 G4 LED85/CW PSU S-WB	No
911401505142	BCP500 G4 LED85/NW PSD S-WB	DALI	911401593532	BBP500 G4 LED85/CW PSU S-MB	No
911401505242	BCP500 G4 LED85/NW PSD S-MB	DALI	911401593632	BBP500 G4 LED85/CW PSU A-WB	No
911401505342	BCP500 G4 LED85/NW PSD A-WB	DALI	911401593732	BBP500 G4 LED125/NW PSU S-WB	No
911401505442	BCP500 G4 LED85/CW PSD S-WB	DALI	911401593832	BBP500 G4 LED125/NW PSU S-MB	No
911401505542	BCP500 G4 LED85/CW PSD S-MB	DALI	911401593932	BBP500 G4 LED125/NW PSU A-WB	No
911401505642	BCP500 G4 LED85/CW PSD A-WB	DALI	911401594032	BBP500 G4 LED125/CW PSU S-WB	No
911401505742	BCP500 G4 LED125/NW PSD S-WB	DALI	911401594132	BBP500 G4 LED125/CW PSU S-MB	No
911401505842	BCP500 G4 LED125/NW PSD S-MB	DALI	911401594232	BBP500 G4 LED125/CW PSU A-WB	No
911401505942	BCP500 G4 LED125/NW PSD A-WB	DALI	911401594332	BBP500 G4 LED140/NW PSU S-WB	No
911401506042	BCP500 G4 LED125/CW PSD S-WB	DALI	911401594432	BBP500 G4 LED140/NW PSU S-MB	No
911401506142	BCP500 G4 LED125/CW PSD S-MB	DALI	911401594532	BBP500 G4 LED140/NW PSU A-WB	No
911401506242	BCP500 G4 LED125/CW PSD A-WB	DALI	911401594632	BBP500 G4 LED140/CW PSU S-WB	No
911401506342	BCP500 G4 LED140/NW PSD S-WB	DALI	911401594732	BBP500 G4 LED140/CW PSU S-MB	No
911401506442	BCP500 G4 LED140/NW PSD S-MB	DALI	911401594832	BBP500 G4 LED140/CW PSU A-WB	No
911401506542	BCP500 G4 LED140/NW PSD A-WB	DALI	911401594932	BBP500 G4 LED180/NW PSU S-WB	No
911401506642	BCP500 G4 LED140/CW PSD S-WB	DALI	911401595032	BBP500 G4 LED180/NW PSU S-MB	No
911401506742	BCP500 G4 LED140/CW PSD S-MB	DALI	911401595132	BBP500 G4 LED180/NW PSU A-WB	No
911401506842	BCP500 G4 LED140/CW PSD A-WB	DALI	911401595232	BBP500 G4 LED180/CW PSU S-WB	No

# GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable
911401595332	BBP500 G4 LED180/CW PSU S-MB	No
911401595432	BBP500 G4 LED180/CW PSU A-WB	No
911401595532	BBP500 G4 LED85/NW PSD S-WB	DALI
911401595632	BBP500 G4 LED85/NW PSD S-MB	DALI
911401595732	BBP500 G4 LED85/NW PSD A-WB	DALI
911401595832	BBP500 G4 LED85/CW PSD S-WB	DALI
911401595932	BBP500 G4 LED85/CW PSD S-MB	DALI
911401596032	BBP500 G4 LED85/CW PSD A-WB	DALI
911401596132	BBP500 G4 LED125/NW PSD S-WB	DALI
911401596232	BBP500 G4 LED125/NW PSD S-MB	DALI
911401596332	BBP500 G4 LED125/NW PSD A-WB	DALI
911401596432	BBP500 G4 LED125/CW PSD S-WB	DALI
911401596532	BBP500 G4 LED125/CW PSD S-MB	DALI

Order Code	Full Product Name	Dimmable
911401596632	BBP500 G4 LED125/CW PSD A-WB	DALI
911401596732	BBP500 G4 LED140/NW PSD S-WB	DALI
911401596832	BBP500 G4 LED140/NW PSD S-MB	DALI
911401596932	BBP500 G4 LED140/NW PSD A-WB	DALI
911401597032	BBP500 G4 LED140/CW PSD S-WB	DALI
911401597132	BBP500 G4 LED140/CW PSD S-MB	DALI
911401597232	BBP500 G4 LED140/CW PSD A-WB	DALI
911401597332	BBP500 G4 LED180/NW PSD S-WB	DALI
911401597432	BBP500 G4 LED180/NW PSD S-MB	DALI
911401597532	BBP500 G4 LED180/NW PSD A-WB	DALI
911401597632	BBP500 G4 LED180/CW PSD S-WB	DALI
911401597732	BBP500 G4 LED180/CW PSD S-MB	DALI
911401597832	BBP500 G4 LED180/CW PSD A-WB	DALI

## Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401502742	BCP500 G4 LED85/NW PSU S-WB	Clear glass	IK07
911401502842	BCP500 G4 LED85/NW PSU S-MB	Clear glass	IK07
911401502942	BCP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401503042	BCP500 G4 LED85/CW PSU S-WB	Clear glass	IK07
911401503142	BCP500 G4 LED85/CW PSU S-MB	Clear glass	IK07
911401503242	BCP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401503342	BCP500 G4 LED125/NW PSU S-WB	Clear glass	IK07
911401503442	BCP500 G4 LED125/NW PSU S-MB	Clear glass	IK07
911401503542	BCP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
911401503642	BCP500 G4 LED125/CW PSU S-WB	Clear glass	IK07
911401503742	BCP500 G4 LED125/CW PSU S-MB	Clear glass	IK07
911401503842	BCP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401503942	BCP500 G4 LED140/NW PSU S-WB	Clear glass	IK07
911401504042	BCP500 G4 LED140/NW PSU S-MB	Clear glass	IK07
911401504142	BCP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401504242	BCP500 G4 LED140/CW PSU S-WB	Clear glass	IK07
911401504342	BCP500 G4 LED140/CW PSU S-MB	Clear glass	IK07
911401504442	BCP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401504542	BCP500 G4 LED180/NW PSU S-WB	Clear glass	IK07
911401504642	BCP500 G4 LED180/NW PSU S-MB	Clear glass	IK07
911401504742	BCP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401504842	BCP500 G4 LED180/CW PSU S-WB	Clear glass	IK07
911401504942	BCP500 G4 LED180/CW PSU S-MB	Clear glass	IK07
911401505042	BCP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401509942	BCP500 G4 LED85/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401510042	BCP500 G4 LED85/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401510142	BCP500 G4 LED85/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401510242	BCP500 G4 LED85/CW PSU S-WB	Polycarbonate	IK08
	PC		

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401510342	BCP500 G4 LED85/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401510442	BCP500 G4 LED85/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401510542	BCP500 G4 LED125/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401510642	BCP500 G4 LED125/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401510742	BCP500 G4 LED125/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401510842	BCP500 G4 LED125/CW PSU S-WB	Polycarbonate	IK08
	PC		
911401510942	BCP500 G4 LED125/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401511042	BCP500 G4 LED125/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401511142	BCP500 G4 LED140/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401511242	BCP500 G4 LED140/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401511342	BCP500 G4 LED140/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401511442	BCP500 G4 LED140/CW PSU S-WB	Polycarbonate	IK08
	PC		
911401511542	BCP500 G4 LED140/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401511642	BCP500 G4 LED140/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401511742	BCP500 G4 LED180/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401511842	BCP500 G4 LED180/NW PSU S-MB	Polycarbonate	IK08
	PC		

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
911401509732	BBP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
9114015098032	BBP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
9114015098132	BBP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
9114015098232	BBP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
9114015098332	BBP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
9114015098432	BBP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
9114015098532	BBP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
9114015098632	BBP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
9114015098732	BBP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
9114015098832	BBP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
9114015098932	BBP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
9114015099032	BBP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
9114015099132	BBP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
9114015099232	BBP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
9114015099332	BBP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
9114015099432	BBP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
9114015099532	BBP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
9114015099632	BBP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
9114015099732	BBP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
9114015099832	BBP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
9114015099932	BBP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
911401512342	BGP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401512442	BGP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401512542	BGP500 G4 LED125/NW PSU A-WB	Clear glass	IK07

# GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401512642	BGP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401512742	BGP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401512842	BGP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401512942	BGP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401513042	BGP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401505142	BCP500 G4 LED85/NW PSD S-WB	Clear glass	IK07
911401505242	BCP500 G4 LED85/NW PSD S-MB	Clear glass	IK07
911401505342	BCP500 G4 LED85/NW PSD A-WB	Clear glass	IK07
911401505442	BCP500 G4 LED85/CW PSD S-WB	Clear glass	IK07
911401505542	BCP500 G4 LED85/CW PSD S-MB	Clear glass	IK07
911401505642	BCP500 G4 LED85/CW PSD A-WB	Clear glass	IK07
911401505742	BCP500 G4 LED125/NW PSD S-WB	Clear glass	IK07
911401505842	BCP500 G4 LED125/NW PSD S-MB	Clear glass	IK07
911401505942	BCP500 G4 LED125/NW PSD A-WB	Clear glass	IK07
911401506042	BCP500 G4 LED125/CW PSD S-WB	Clear glass	IK07
911401506142	BCP500 G4 LED125/CW PSD S-MB	Clear glass	IK07
911401506242	BCP500 G4 LED125/CW PSD A-WB	Clear glass	IK07
911401506342	BCP500 G4 LED140/NW PSD S-WB	Clear glass	IK07
911401506442	BCP500 G4 LED140/NW PSD S-MB	Clear glass	IK07
911401506542	BCP500 G4 LED140/NW PSD A-WB	Clear glass	IK07
911401506642	BCP500 G4 LED140/CW PSD S-WB	Clear glass	IK07
911401506742	BCP500 G4 LED140/CW PSD S-MB	Clear glass	IK07
911401506842	BCP500 G4 LED140/CW PSD A-WB	Clear glass	IK07
911401506942	BCP500 G4 LED180/NW PSD S-WB	Clear glass	IK07
911401507042	BCP500 G4 LED180/NW PSD S-MB	Clear glass	IK07
911401507142	BCP500 G4 LED180/NW PSD A-WB	Clear glass	IK07
911401507242	BCP500 G4 LED180/CW PSD S-WB	Clear glass	IK07
911401507342	BCP500 G4 LED180/CW PSD S-MB	Clear glass	IK07
911401507442	BCP500 G4 LED180/CW PSD A-WB	Clear glass	IK07
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	IK08
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	IK08
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	IK08
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	IK08
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	IK08
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	IK08
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	IK08
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	IK08
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	IK08
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	IK08

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	IK08
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	IK08
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	IK08
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	IK08
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	IK08
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	IK08
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	IK08
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	IK08
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	IK08
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	IK08
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08
911401593132	BBP500 G4 LED85/NW PSU S-WB	Clear glass	IK07
911401593232	BBP500 G4 LED85/NW PSU S-MB	Clear glass	IK07
911401593332	BBP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401593432	BBP500 G4 LED85/CW PSU S-WB	Clear glass	IK07
911401593532	BBP500 G4 LED85/CW PSU S-MB	Clear glass	IK07
911401593632	BBP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401593732	BBP500 G4 LED125/NW PSU S-WB	Clear glass	IK07
911401593832	BBP500 G4 LED125/NW PSU S-MB	Clear glass	IK07
911401593932	BBP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
911401594032	BBP500 G4 LED125/CW PSU S-WB	Clear glass	IK07
911401594132	BBP500 G4 LED125/CW PSU S-MB	Clear glass	IK07
911401594232	BBP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401594332	BBP500 G4 LED140/NW PSU S-WB	Clear glass	IK07
911401594432	BBP500 G4 LED140/NW PSU S-MB	Clear glass	IK07
911401594532	BBP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401594632	BBP500 G4 LED140/CW PSU S-WB	Clear glass	IK07
911401594732	BBP500 G4 LED140/CW PSU S-MB	Clear glass	IK07
911401594832	BBP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401594932	BBP500 G4 LED180/NW PSU S-WB	Clear glass	IK07
911401595032	BBP500 G4 LED180/NW PSU S-MB	Clear glass	IK07
911401595132	BBP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401595232	BBP500 G4 LED180/CW PSU S-WB	Clear glass	IK07

# GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401595332	BBP500 G4 LED180/CW PSU S-MB	Clear glass	IK07
911401595432	BBP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401595532	BBP500 G4 LED85/NW PSD S-WB	Clear glass	IK07
911401595632	BBP500 G4 LED85/NW PSD S-MB	Clear glass	IK07
911401595732	BBP500 G4 LED85/NW PSD A-WB	Clear glass	IK07
911401595832	BBP500 G4 LED85/CW PSD S-WB	Clear glass	IK07
911401595932	BBP500 G4 LED85/CW PSD S-MB	Clear glass	IK07
911401596032	BBP500 G4 LED85/CW PSD A-WB	Clear glass	IK07
911401596132	BBP500 G4 LED125/NW PSD S-WB	Clear glass	IK07
911401596232	BBP500 G4 LED125/NW PSD S-MB	Clear glass	IK07
911401596332	BBP500 G4 LED125/NW PSD A-WB	Clear glass	IK07
911401596432	BBP500 G4 LED125/CW PSD S-WB	Clear glass	IK07
911401596532	BBP500 G4 LED125/CW PSD S-MB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401596632	BBP500 G4 LED125/CW PSD A-WB	Clear glass	IK07
911401596732	BBP500 G4 LED140/NW PSD S-WB	Clear glass	IK07
911401596832	BBP500 G4 LED140/NW PSD S-MB	Clear glass	IK07
911401596932	BBP500 G4 LED140/NW PSD A-WB	Clear glass	IK07
911401597032	BBP500 G4 LED140/CW PSD S-WB	Clear glass	IK07
911401597132	BBP500 G4 LED140/CW PSD S-MB	Clear glass	IK07
911401597232	BBP500 G4 LED140/CW PSD A-WB	Clear glass	IK07
911401597332	BBP500 G4 LED180/NW PSD S-WB	Clear glass	IK07
911401597432	BBP500 G4 LED180/NW PSD S-MB	Clear glass	IK07
911401597532	BBP500 G4 LED180/NW PSD A-WB	Clear glass	IK07
911401597632	BBP500 G4 LED180/CW PSD S-WB	Clear glass	IK07
911401597732	BBP500 G4 LED180/CW PSD S-MB	Clear glass	IK07
911401597832	BBP500 G4 LED180/CW PSD A-WB	Clear glass	IK07

## Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401502742	BCP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401502842	BCP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401502942	BCP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503042	BCP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503142	BCP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503242	BCP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503342	BCP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503442	BCP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503542	BCP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503642	BCP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401503742	BCP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503842	BCP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503942	BCP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504042	BCP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504142	BCP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504242	BCP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504342	BCP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504442	BCP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504542	BCP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504642	BCP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401504742	BCP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504842	BCP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504942	BCP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
911401505042	BCP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511942	BCP500 G4 LED180/NW PSU A-WB WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401512342	BGP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-40 to +50 °C	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-40 to +50 °C	-
911401505142	BCP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505242	BCP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505342	BCP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401505442	BCP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505542	BCP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505642	BCP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505742	BCP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505842	BCP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505942	BCP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506042	BCP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506142	BCP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506242	BCP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506342	BCP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506442	BCP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506542	BCP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506642	BCP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506742	BCP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506842	BCP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506942	BCP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507042	BCP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401507142	BCP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507242	BCP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507342	BCP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507442	BCP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502342	BBP500 G4 LED180/NW PSU A-WB WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401593132	BBP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593232	BBP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593332	BBP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593432	BBP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593532	BBP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593632	BBP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401593732	BBP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593832	BBP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593932	BBP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594032	BBP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594132	BBP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594232	BBP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594332	BBP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594432	BBP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594532	BBP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594632	BBP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594732	BBP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594832	BBP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594932	BBP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595032	BBP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595132	BBP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595232	BBP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595332	BBP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401595432	BBP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595532	BBP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595632	BBP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595732	BBP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595832	BBP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595932	BBP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596032	BBP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596132	BBP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596232	BBP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596332	BBP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596432	BBP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596532	BBP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596632	BBP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596732	BBP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596832	BBP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596932	BBP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597032	BBP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

## GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401597132	BBP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597232	BBP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597332	BBP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597432	BBP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401597532	BBP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597632	BBP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597732	BBP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597832	BBP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

