



GreenPerform Canopy Mini500 Gen4: A high-performance, versatile, energy- saving LED

GreenPerform Canopy Mini500 G4

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Choice of optics
- Flexible installation options
- Range of control and connectivity platforms

GreenPerform Canopy Mini500 G4

Features

- Up to 160 lm/W system efficacy
- 60,000 hours lifetime @Ta 35°C
- Outdoor and edge area (Asymmetry WB), general area (WB), emphasizing and limited area (NB)
- Recessed (BBP), Surface & frame (BCP), Pole (BGP)
- DALI control, GU5.3 for emergency lighting, EcoSet sensor

Application

- Petrol and Convenience
- Parking Garages
- Food Processing

Specifications

Mounting type	Recessed
	Surface
	Pole
Operating Temperature range	- 40 to +50 °C
Light Source	LED
Mains Voltage	2320-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Clamp
Dimming	PSU: non-dimmable PSD: Dimmable via Dali-broadcasting
Control system input	DALI
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL9003
Flicker / Pst / SVM	<3.2% / 0.5 / 0.4
Luminous flux	8.5klm - 18klm
Power consumption	53W - 128W
Luminaire efficacy	Up to 160lm/W
Correlated color temperature - CCT	4000K 6000K

Color Rendering index - CRI	80
Beam angle	S-WB: 115° S-MB: 90° A-WB: 110°*80°
Optical cover/lens material	Lens: PC Cover: Glass
Optical cover/lens finish	Clear
Protection Class IEC61140	Class I
Mechanical impact protection	IK07
Ingress protection	IP65
Driver replaceable	Yes
Installation	Recessed Surface Pole








Versions



GreenPerform Canopy Mini500 G7

GreenPerform Canopy Mini500 G4

Dimensional drawing



GreenPerform Canopy Mini500 G4

General Information

Service tag Yes

Light Technical

Color rendering index (CRI) >80

Operating and Electrical

Protection class IEC Safety class I

Input Voltage 220-240 V

Line Frequency 50 to 60 Hz

Mechanical and Housing

Housing Color White

Ingress protection code IP65

Approval and Application

CE mark Yes

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401502742	BCP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
911401502842	BCP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
911401502942	BCP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401503042	BCP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
911401503142	BCP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
911401503242	BCP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401503342	BCP500 G4 LED125/NW PSU S-WB	4000 K	159 lm/W	12,638 lm
911401503442	BCP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
911401503542	BCP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
911401503642	BCP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
911401503742	BCP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
911401503842	BCP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
911401503942	BCP500 G4 LED140/NW PSU S-WB	4000 K	155 lm/W	14,079 lm
911401504042	BCP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
911401504142	BCP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401504242	BCP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
911401504342	BCP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
911401504442	BCP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401504542	BCP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm
911401504642	BCP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
911401504742	BCP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401504842	BCP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
911401504942	BCP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
911401505042	BCP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	4000 K	157 lm/W	8,313 lm
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	4000 K	157 lm/W	8,313 lm
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	4000 K	157 lm/W	8,313 lm
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	6500 K	157 lm/W	8,313 lm
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	6500 K	157 lm/W	8,313 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	6500 K	157 lm/W	8,313 lm
911401510542	BCP500 G4 LED125/NW PSU S- WB PC	4000 K	156 lm/W	12,366 lm
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	4000 K	156 lm/W	12,366 lm
911401510742	BCP500 G4 LED125/NW PSU A- WB PC	4000 K	156 lm/W	12,366 lm
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	6500 K	156 lm/W	12,366 lm
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	6500 K	156 lm/W	12,366 lm
911401511042	BCP500 G4 LED125/CW PSU A- WB PC	6500 K	156 lm/W	12,366 lm
911401511142	BCP500 G4 LED140/NW PSU S- WB PC	4000 K	152 lm/W	13,777 lm
911401511242	BCP500 G4 LED140/NW PSU S- MB PC	4000 K	152 lm/W	13,777 lm
911401511342	BCP500 G4 LED140/NW PSU A- WB PC	4000 K	152 lm/W	13,777 lm
911401511442	BCP500 G4 LED140/CW PSU S- WB PC	6500 K	152 lm/W	13,777 lm
911401511542	BCP500 G4 LED140/CW PSU S- MB PC	6500 K	152 lm/W	13,777 lm
911401511642	BCP500 G4 LED140/CW PSU A- WB PC	6500 K	152 lm/W	13,777 lm
911401511742	BCP500 G4 LED180/NW PSU S- WB PC	4000 K	145 lm/W	17,677 lm
911401511842	BCP500 G4 LED180/NW PSU S- MB PC	4000 K	145 lm/W	17,677 lm
911401511942	BCP500 G4 LED180/NW PSU A- WB PC	4000 K	145 lm/W	17,677 lm
911401512042	BCP500 G4 LED180/CW PSU S- WB PC	6500 K	145 lm/W	17,677 lm
911401512142	BCP500 G4 LED180/CW PSU S- MB PC	6500 K	145 lm/W	17,677 lm
911401512242	BCP500 G4 LED180/CW PSU A- WB PC	6500 K	145 lm/W	17,677 lm
911401507542	BCP500 G4 LED85/NW GU5.3 S- WB	4000 K	160 lm/W	8,496 lm
911401507642	BCP500 G4 LED85/NW GU5.3 S- MB	4000 K	160 lm/W	8,496 lm
911401507742	BCP500 G4 LED85/NW GU5.3 A- WB	4000 K	160 lm/W	8,496 lm
911401507842	BCP500 G4 LED85/CW GU5.3 S- WB	6500 K	160 lm/W	8,496 lm
911401507942	BCP500 G4 LED85/CW GU5.3 S- MB	6500 K	160 lm/W	8,496 lm
911401508042	BCP500 G4 LED85/CW GU5.3 A- WB	6500 K	160 lm/W	8,496 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	6500 K	148 lm/W	18,066 lm
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	6500 K	148 lm/W	18,066 lm
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	6500 K	148 lm/W	18,066 lm
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	4000 K	160 lm/W	8,496 lm
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	4000 K	160 lm/W	8,496 lm
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	4000 K	160 lm/W	8,496 lm
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	6500 K	160 lm/W	8,496 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	6500 K	160 lm/W	8,496 lm
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	6500 K	160 lm/W	8,496 lm
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	4000 K	159 lm/W	12,638 lm
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	4000 K	159 lm/W	12,638 lm
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	4000 K	159 lm/W	12,638 lm
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	6500 K	159 lm/W	12,638 lm
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	6500 K	159 lm/W	12,638 lm
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	6500 K	159 lm/W	12,638 lm
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	4000 K	155 lm/W	14,079 lm
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	4000 K	155 lm/W	14,079 lm
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	4000 K	155 lm/W	14,079 lm
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	6500 K	155 lm/W	14,079 lm
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	6500 K	155 lm/W	14,079 lm
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	6500 K	155 lm/W	14,079 lm
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	4000 K	148 lm/W	18,066 lm
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	4000 K	148 lm/W	18,066 lm
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	4000 K	148 lm/W	18,066 lm
911401512342	BGP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401512442	BGP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401512542	BGP500 G4 LED125/NW PSU A-WB	4000 K	159 lm/W	12,638 lm
911401512642	BGP500 G4 LED125/CW PSU A-WB	6500 K	159 lm/W	12,638 lm
911401512742	BGP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401512842	BGP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401512942	BGP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401513042	BGP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401505142	BCP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
911401505242	BCP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
911401505342	BCP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401505442	BCP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
911401505542	BCP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
911401505642	BCP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
911401505742	BCP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
911401505842	BCP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
911401505942	BCP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
911401506042	BCP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
911401506142	BCP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
911401506242	BCP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
911401506342	BCP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
911401506442	BCP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
911401506542	BCP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
911401506642	BCP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
911401506742	BCP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
911401506842	BCP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm
911401506942	BCP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
911401507042	BCP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
911401507142	BCP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
911401507242	BCP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
911401507342	BCP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
911401507442	BCP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	4000 K	157 lm/W	8,313 lm
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	4000 K	157 lm/W	8,313 lm
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	4000 K	157 lm/W	8,313 lm
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	6500 K	157 lm/W	8,313 lm
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	6500 K	157 lm/W	8,313 lm
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	6500 K	157 lm/W	8,313 lm
911401500942	BBP500 G4 LED125/NW PSU S-WB WB PC	4000 K	156 lm/W	12,366 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	4000 K	156 lm/W	12,366 lm
911401501142	BBP500 G4 LED125/NW PSU A- WB PC	4000 K	156 lm/W	12,366 lm
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	6500 K	156 lm/W	12,366 lm
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	6500 K	156 lm/W	12,366 lm
911401501442	BBP500 G4 LED125/CW PSU A- WB PC	6500 K	156 lm/W	12,366 lm
911401501542	BBP500 G4 LED140/NW PSU S- WB PC	4000 K	152 lm/W	13,777 lm
911401501642	BBP500 G4 LED140/NW PSU S- MB PC	4000 K	152 lm/W	13,777 lm
911401501742	BBP500 G4 LED140/NW PSU A- WB PC	4000 K	152 lm/W	13,777 lm
911401501842	BBP500 G4 LED140/CW PSU S- WB PC	6500 K	152 lm/W	13,777 lm
911401501942	BBP500 G4 LED140/CW PSU S- MB PC	6500 K	152 lm/W	13,777 lm
911401502042	BBP500 G4 LED140/CW PSU A- WB PC	6500 K	152 lm/W	13,777 lm
911401502142	BBP500 G4 LED180/NW PSU S- WB PC	4000 K	145 lm/W	17,677 lm
911401502242	BBP500 G4 LED180/NW PSU S- MB PC	4000 K	145 lm/W	17,677 lm
911401502342	BBP500 G4 LED180/NW PSU A- WB PC	4000 K	145 lm/W	17,677 lm
911401502442	BBP500 G4 LED180/CW PSU S- WB PC	6500 K	145 lm/W	17,677 lm
911401502542	BBP500 G4 LED180/CW PSU S- MB PC	6500 K	145 lm/W	17,677 lm
911401502642	BBP500 G4 LED180/CW PSU A- WB PC	6500 K	145 lm/W	17,677 lm
911401593132	BBP500 G4 LED85/NW PSU S-WB	4000 K	160 lm/W	8,496 lm
911401593232	BBP500 G4 LED85/NW PSU S-MB	4000 K	160 lm/W	8,496 lm
911401593332	BBP500 G4 LED85/NW PSU A-WB	4000 K	160 lm/W	8,496 lm
911401593432	BBP500 G4 LED85/CW PSU S-WB	6500 K	160 lm/W	8,496 lm
911401593532	BBP500 G4 LED85/CW PSU S-MB	6500 K	160 lm/W	8,496 lm
911401593632	BBP500 G4 LED85/CW PSU A-WB	6500 K	160 lm/W	8,496 lm
911401593732	BBP500 G4 LED125/NW PSU S- WB	4000 K	159 lm/W	12,638 lm
911401593832	BBP500 G4 LED125/NW PSU S-MB	4000 K	159 lm/W	12,638 lm
911401593932	BBP500 G4 LED125/NW PSU A- WB	4000 K	159 lm/W	12,638 lm
911401594032	BBP500 G4 LED125/CW PSU S-WB	6500 K	159 lm/W	12,638 lm
911401594132	BBP500 G4 LED125/CW PSU S-MB	6500 K	159 lm/W	12,638 lm
911401594232	BBP500 G4 LED125/CW PSU A- WB	6500 K	159 lm/W	12,638 lm
911401594332	BBP500 G4 LED140/NW PSU S- WB	4000 K	155 lm/W	14,079 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401594432	BBP500 G4 LED140/NW PSU S-MB	4000 K	155 lm/W	14,079 lm
911401594532	BBP500 G4 LED140/NW PSU A-WB	4000 K	155 lm/W	14,079 lm
911401594632	BBP500 G4 LED140/CW PSU S-WB	6500 K	155 lm/W	14,079 lm
911401594732	BBP500 G4 LED140/CW PSU S-MB	6500 K	155 lm/W	14,079 lm
911401594832	BBP500 G4 LED140/CW PSU A-WB	6500 K	155 lm/W	14,079 lm
911401594932	BBP500 G4 LED180/NW PSU S-WB	4000 K	148 lm/W	18,066 lm
911401595032	BBP500 G4 LED180/NW PSU S-MB	4000 K	148 lm/W	18,066 lm
911401595132	BBP500 G4 LED180/NW PSU A-WB	4000 K	148 lm/W	18,066 lm
911401595232	BBP500 G4 LED180/CW PSU S-WB	6500 K	148 lm/W	18,066 lm
911401595332	BBP500 G4 LED180/CW PSU S-MB	6500 K	148 lm/W	18,066 lm
911401595432	BBP500 G4 LED180/CW PSU A-WB	6500 K	148 lm/W	18,066 lm
911401595532	BBP500 G4 LED85/NW PSD S-WB	4000 K	147 lm/W	8,496 lm
911401595632	BBP500 G4 LED85/NW PSD S-MB	4000 K	147 lm/W	8,496 lm
911401595732	BBP500 G4 LED85/NW PSD A-WB	4000 K	147 lm/W	8,496 lm
911401595832	BBP500 G4 LED85/CW PSD S-WB	6500 K	147 lm/W	8,496 lm
911401595932	BBP500 G4 LED85/CW PSD S-MB	6500 K	147 lm/W	8,496 lm
911401596032	BBP500 G4 LED85/CW PSD A-WB	6500 K	147 lm/W	8,496 lm
911401596132	BBP500 G4 LED125/NW PSD S-WB	4000 K	149 lm/W	12,638 lm
911401596232	BBP500 G4 LED125/NW PSD S-MB	4000 K	149 lm/W	12,638 lm
911401596332	BBP500 G4 LED125/NW PSD A-WB	4000 K	149 lm/W	12,638 lm
911401596432	BBP500 G4 LED125/CW PSD S-WB	6500 K	149 lm/W	12,638 lm
911401596532	BBP500 G4 LED125/CW PSD S-MB	6500 K	149 lm/W	12,638 lm
911401596632	BBP500 G4 LED125/CW PSD A-WB	6500 K	149 lm/W	12,638 lm
911401596732	BBP500 G4 LED140/NW PSD S-WB	4000 K	147 lm/W	14,079 lm
911401596832	BBP500 G4 LED140/NW PSD S-MB	4000 K	147 lm/W	14,079 lm
911401596932	BBP500 G4 LED140/NW PSD A-WB	4000 K	147 lm/W	14,079 lm
911401597032	BBP500 G4 LED140/CW PSD S-WB	6500 K	147 lm/W	14,079 lm
911401597132	BBP500 G4 LED140/CW PSD S-MB	6500 K	147 lm/W	14,079 lm
911401597232	BBP500 G4 LED140/CW PSD A-WB	6500 K	147 lm/W	14,079 lm

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401597332	BBP500 G4 LED180/NW PSD S-WB	4000 K	142 lm/W	18,066 lm
911401597432	BBP500 G4 LED180/NW PSD S-MB	4000 K	142 lm/W	18,066 lm
911401597532	BBP500 G4 LED180/NW PSD A-WB	4000 K	142 lm/W	18,066 lm
911401597632	BBP500 G4 LED180/CW PSD S-WB	6500 K	142 lm/W	18,066 lm
911401597732	BBP500 G4 LED180/CW PSD S-MB	6500 K	142 lm/W	18,066 lm
911401597832	BBP500 G4 LED180/CW PSD A-WB	6500 K	142 lm/W	18,066 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401502742	BCP500 G4 LED85/NW PSU S-WB	53 W	911401511042	BCP500 G4 LED125/CW PSU A-WB PC	79 W
911401502842	BCP500 G4 LED85/NW PSU S-MB	53 W	911401511142	BCP500 G4 LED140/NW PSU S-WB PC	91 W
911401502942	BCP500 G4 LED85/NW PSU A-WB	53 W	911401511242	BCP500 G4 LED140/NW PSU S-MB PC	91 W
911401503042	BCP500 G4 LED85/CW PSU S-WB	53 W	911401511342	BCP500 G4 LED140/NW PSU A-WB PC	91 W
911401503142	BCP500 G4 LED85/CW PSU S-MB	53 W	911401511442	BCP500 G4 LED140/CW PSU S-WB PC	91 W
911401503242	BCP500 G4 LED85/CW PSU A-WB	53 W	911401511542	BCP500 G4 LED140/CW PSU S-MB PC	91 W
911401503342	BCP500 G4 LED125/NW PSU S-WB	79 W	911401511642	BCP500 G4 LED140/CW PSU A-WB PC	91 W
911401503442	BCP500 G4 LED125/NW PSU S-MB	79 W	911401511742	BCP500 G4 LED180/NW PSU S-WB PC	122 W
911401503542	BCP500 G4 LED125/NW PSU A-WB	79 W	911401511842	BCP500 G4 LED180/NW PSU S-MB PC	122 W
911401503642	BCP500 G4 LED125/CW PSU S-WB	79 W	911401511942	BCP500 G4 LED180/NW PSU A-WB PC	122 W
911401503742	BCP500 G4 LED125/CW PSU S-MB	79 W	911401512042	BCP500 G4 LED180/CW PSU S-WB PC	122 W
911401503842	BCP500 G4 LED125/CW PSU A-WB	79 W	911401512142	BCP500 G4 LED180/CW PSU S-MB PC	122 W
911401503942	BCP500 G4 LED140/NW PSU S-WB	91 W	911401512242	BCP500 G4 LED180/CW PSU A-WB PC	122 W
911401504042	BCP500 G4 LED140/NW PSU S-MB	91 W	911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	53 W
911401504142	BCP500 G4 LED140/NW PSU A-WB	91 W	911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	53 W
911401504242	BCP500 G4 LED140/CW PSU S-WB	91 W	911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	53 W
911401504342	BCP500 G4 LED140/CW PSU S-MB	91 W	911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	53 W
911401504442	BCP500 G4 LED140/CW PSU A-WB	91 W	911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	53 W
911401504542	BCP500 G4 LED180/NW PSU S-WB	122 W	911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	53 W
911401504642	BCP500 G4 LED180/NW PSU S-MB	122 W	911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	79 W
911401504742	BCP500 G4 LED180/NW PSU A-WB	122 W	911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	79 W
911401504842	BCP500 G4 LED180/CW PSU S-WB	122 W	911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	79 W
911401504942	BCP500 G4 LED180/CW PSU S-MB	122 W	911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	79 W
911401505042	BCP500 G4 LED180/CW PSU A-WB	122 W	911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	79 W
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	53 W	911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	79 W
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	53 W	911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	91 W
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	53 W	911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	91 W
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	53 W	911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	91 W
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	53 W	911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	91 W
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	53 W	911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	91 W
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	79 W	911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	91 W
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	79 W	911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	122 W
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	79 W	911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	122 W
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	79 W	911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	122 W
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	79 W	911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	122 W

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	122 W
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	122 W
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	122 W
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	122 W
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	122 W
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	53 W
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	53 W
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	53 W
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	53 W
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	53 W
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	53 W
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	79 W
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	79 W
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	79 W
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	79 W
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	79 W
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	79 W
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	91 W
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	91 W
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	91 W
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	91 W
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	91 W
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	91 W
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	122 W
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	122 W
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	122 W
911401512342	BGP500 G4 LED85/NW PSU A-WB	53 W
911401512442	BGP500 G4 LED85/CW PSU A-WB	53 W
911401512542	BGP500 G4 LED125/NW PSU A-WB	79 W
911401512642	BGP500 G4 LED125/CW PSU A-WB	79 W
911401512742	BGP500 G4 LED140/NW PSU A-WB	91 W
911401512842	BGP500 G4 LED140/CW PSU A-WB	91 W
911401512942	BGP500 G4 LED180/NW PSU A-WB	122 W
911401513042	BGP500 G4 LED180/CW PSU A-WB	122 W
911401505142	BCP500 G4 LED85/NW PSD S-WB	58 W
911401505242	BCP500 G4 LED85/NW PSD S-MB	58 W
911401505342	BCP500 G4 LED85/NW PSD A-WB	58 W
911401505442	BCP500 G4 LED85/CW PSD S-WB	58 W
911401505542	BCP500 G4 LED85/CW PSD S-MB	58 W
911401505642	BCP500 G4 LED85/CW PSD A-WB	58 W
911401505742	BCP500 G4 LED125/NW PSD S-WB	85 W
911401505842	BCP500 G4 LED125/NW PSD S-MB	85 W
911401505942	BCP500 G4 LED125/NW PSD A-WB	85 W
911401506042	BCP500 G4 LED125/CW PSD S-WB	85 W
911401506142	BCP500 G4 LED125/CW PSD S-MB	85 W
911401506242	BCP500 G4 LED125/CW PSD A-WB	85 W
911401506342	BCP500 G4 LED140/NW PSD S-WB	96 W
911401506442	BCP500 G4 LED140/NW PSD S-MB	96 W
911401506542	BCP500 G4 LED140/NW PSD A-WB	96 W
911401506642	BCP500 G4 LED140/CW PSD S-WB	96 W
911401506742	BCP500 G4 LED140/CW PSD S-MB	96 W
911401506842	BCP500 G4 LED140/CW PSD A-WB	96 W

Order Code	Full Product Name	Power Consumption
911401506942	BCP500 G4 LED180/NW PSD S-WB	128 W
911401507042	BCP500 G4 LED180/NW PSD S-MB	128 W
911401507142	BCP500 G4 LED180/NW PSD A-WB	128 W
911401507242	BCP500 G4 LED180/CW PSD S-WB	128 W
911401507342	BCP500 G4 LED180/CW PSD S-MB	128 W
911401507442	BCP500 G4 LED180/CW PSD A-WB	128 W
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	53 W
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	53 W
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	53 W
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	53 W
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	53 W
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	53 W
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	79 W
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	79 W
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	79 W
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	79 W
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	79 W
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	79 W
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	91 W
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	91 W
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	91 W
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	91 W
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	91 W
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	91 W
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	122 W
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	122 W
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	122 W
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	122 W
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	122 W
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	122 W
911401593132	BBP500 G4 LED85/NW PSU S-WB	53 W
911401593232	BBP500 G4 LED85/NW PSU S-MB	53 W
911401593332	BBP500 G4 LED85/NW PSU A-WB	53 W
911401593432	BBP500 G4 LED85/CW PSU S-WB	53 W
911401593532	BBP500 G4 LED85/CW PSU S-MB	53 W
911401593632	BBP500 G4 LED85/CW PSU A-WB	53 W
911401593732	BBP500 G4 LED125/NW PSU S-WB	79 W
911401593832	BBP500 G4 LED125/NW PSU S-MB	79 W
911401593932	BBP500 G4 LED125/NW PSU A-WB	79 W
911401594032	BBP500 G4 LED125/CW PSU S-WB	79 W
911401594132	BBP500 G4 LED125/CW PSU S-MB	79 W
911401594232	BBP500 G4 LED125/CW PSU A-WB	79 W
911401594332	BBP500 G4 LED140/NW PSU S-WB	91 W
911401594432	BBP500 G4 LED140/NW PSU S-MB	91 W
911401594532	BBP500 G4 LED140/NW PSU A-WB	91 W
911401594632	BBP500 G4 LED140/CW PSU S-WB	91 W
911401594732	BBP500 G4 LED140/CW PSU S-MB	91 W
911401594832	BBP500 G4 LED140/CW PSU A-WB	91 W
911401594932	BBP500 G4 LED180/NW PSU S-WB	122 W
911401595032	BBP500 G4 LED180/NW PSU S-MB	122 W
911401595132	BBP500 G4 LED180/NW PSU A-WB	122 W
911401595232	BBP500 G4 LED180/CW PSU S-WB	122 W

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Power Consumption
911401595332	BBP500 G4 LED180/CW PSU S-MB	122 W
911401595432	BBP500 G4 LED180/CW PSU A-WB	122 W
911401595532	BBP500 G4 LED85/NW PSD S-WB	58 W
911401595632	BBP500 G4 LED85/NW PSD S-MB	58 W
911401595732	BBP500 G4 LED85/NW PSD A-WB	58 W
911401595832	BBP500 G4 LED85/CW PSD S-WB	58 W
911401595932	BBP500 G4 LED85/CW PSD S-MB	58 W
911401596032	BBP500 G4 LED85/CW PSD A-WB	58 W
911401596132	BBP500 G4 LED125/NW PSD S-WB	85 W
911401596232	BBP500 G4 LED125/NW PSD S-MB	85 W
911401596332	BBP500 G4 LED125/NW PSD A-WB	85 W
911401596432	BBP500 G4 LED125/CW PSD S-WB	85 W
911401596532	BBP500 G4 LED125/CW PSD S-MB	85 W

Order Code	Full Product Name	Power Consumption
911401596632	BBP500 G4 LED125/CW PSD A-WB	85 W
911401596732	BBP500 G4 LED140/NW PSD S-WB	96 W
911401596832	BBP500 G4 LED140/NW PSD S-MB	96 W
911401596932	BBP500 G4 LED140/NW PSD A-WB	96 W
911401597032	BBP500 G4 LED140/CW PSD S-WB	96 W
911401597132	BBP500 G4 LED140/CW PSD S-MB	96 W
911401597232	BBP500 G4 LED140/CW PSD A-WB	96 W
911401597332	BBP500 G4 LED180/NW PSD S-WB	128 W
911401597432	BBP500 G4 LED180/NW PSD S-MB	128 W
911401597532	BBP500 G4 LED180/NW PSD A-WB	128 W
911401597632	BBP500 G4 LED180/CW PSD S-WB	128 W
911401597732	BBP500 G4 LED180/CW PSD S-MB	128 W
911401597832	BBP500 G4 LED180/CW PSD A-WB	128 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401502742	BCP500 G4 LED85/NW PSU S-WB	No
911401502842	BCP500 G4 LED85/NW PSU S-MB	No
911401502942	BCP500 G4 LED85/NW PSU A-WB	No
911401503042	BCP500 G4 LED85/CW PSU S-WB	No
911401503142	BCP500 G4 LED85/CW PSU S-MB	No
911401503242	BCP500 G4 LED85/CW PSU A-WB	No
911401503342	BCP500 G4 LED125/NW PSU S-WB	No
911401503442	BCP500 G4 LED125/NW PSU S-MB	No
911401503542	BCP500 G4 LED125/NW PSU A-WB	No
911401503642	BCP500 G4 LED125/CW PSU S-WB	No
911401503742	BCP500 G4 LED125/CW PSU S-MB	No
911401503842	BCP500 G4 LED125/CW PSU A-WB	No
911401503942	BCP500 G4 LED140/NW PSU S-WB	No
911401504042	BCP500 G4 LED140/NW PSU S-MB	No
911401504142	BCP500 G4 LED140/NW PSU A-WB	No
911401504242	BCP500 G4 LED140/CW PSU S-WB	No
911401504342	BCP500 G4 LED140/CW PSU S-MB	No
911401504442	BCP500 G4 LED140/CW PSU A-WB	No
911401504542	BCP500 G4 LED180/NW PSU S-WB	No
911401504642	BCP500 G4 LED180/NW PSU S-MB	No
911401504742	BCP500 G4 LED180/NW PSU A-WB	No
911401504842	BCP500 G4 LED180/CW PSU S-WB	No
911401504942	BCP500 G4 LED180/CW PSU S-MB	No
911401505042	BCP500 G4 LED180/CW PSU A-WB	No
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	No
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	No
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	No
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	No
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	No
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	No
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	No
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	No
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	No
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	No
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	No

Order Code	Full Product Name	Dimmable
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	No
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	No
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	No
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	No
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	No
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	No
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	No
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	No
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	No
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	No
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	No
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	No
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	No
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	No
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	No
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	No
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	No
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	No
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	No
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	No
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	No
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	No
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	No
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	No
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	No
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	No
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	No
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	No
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	No
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	No
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	No
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	No
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	No
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	No
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	No

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	No	911401506942	BCP500 G4 LED180/NW PSD S-WB	DALI
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	No	911401507042	BCP500 G4 LED180/NW PSD S-MB	DALI
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	No	911401507142	BCP500 G4 LED180/NW PSD A-WB	DALI
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	No	911401507242	BCP500 G4 LED180/CW PSD S-WB	DALI
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	No	911401507342	BCP500 G4 LED180/CW PSD S-MB	DALI
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	No	911401507442	BCP500 G4 LED180/CW PSD A-WB	DALI
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	No	911401500342	BBP500 G4 LED85/NW PSU S-WB PC	No
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	No	911401500442	BBP500 G4 LED85/NW PSU S-MB PC	No
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	No	911401500542	BBP500 G4 LED85/NW PSU A-WB PC	No
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	No	911401500642	BBP500 G4 LED85/CW PSU S-WB PC	No
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	No	911401500742	BBP500 G4 LED85/CW PSU S-MB PC	No
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	No	911401500842	BBP500 G4 LED85/CW PSU A-WB PC	No
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	No	911401500942	BBP500 G4 LED125/NW PSU S-WB PC	No
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	No	911401501042	BBP500 G4 LED125/NW PSU S-MB PC	No
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	No	911401501142	BBP500 G4 LED125/NW PSU A-WB PC	No
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	No	911401501242	BBP500 G4 LED125/CW PSU S-WB PC	No
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	No	911401501342	BBP500 G4 LED125/CW PSU S-MB PC	No
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	No	911401501442	BBP500 G4 LED125/CW PSU A-WB PC	No
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	No	911401501542	BBP500 G4 LED140/NW PSU S-WB PC	No
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	No	911401501642	BBP500 G4 LED140/NW PSU S-MB PC	No
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	No	911401501742	BBP500 G4 LED140/NW PSU A-WB PC	No
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	No	911401501842	BBP500 G4 LED140/CW PSU S-WB PC	No
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	No	911401501942	BBP500 G4 LED140/CW PSU S-MB PC	No
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	No	911401502042	BBP500 G4 LED140/CW PSU A-WB PC	No
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	No	911401502142	BBP500 G4 LED180/NW PSU S-WB PC	No
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	No	911401502242	BBP500 G4 LED180/NW PSU S-MB PC	No
911401512342	BGP500 G4 LED85/NW PSU A-WB	No	911401502342	BBP500 G4 LED180/NW PSU A-WB PC	No
911401512442	BGP500 G4 LED85/CW PSU A-WB	No	911401502442	BBP500 G4 LED180/CW PSU S-WB PC	No
911401512542	BGP500 G4 LED125/NW PSU A-WB	No	911401502542	BBP500 G4 LED180/CW PSU S-MB PC	No
911401512642	BGP500 G4 LED125/CW PSU A-WB	No	911401502642	BBP500 G4 LED180/CW PSU A-WB PC	No
911401512742	BGP500 G4 LED140/NW PSU A-WB	No	911401593132	BBP500 G4 LED85/NW PSU S-WB	No
911401512842	BGP500 G4 LED140/CW PSU A-WB	No	911401593232	BBP500 G4 LED85/NW PSU S-MB	No
911401512942	BGP500 G4 LED180/NW PSU A-WB	No	911401593332	BBP500 G4 LED85/NW PSU A-WB	No
911401513042	BGP500 G4 LED180/CW PSU A-WB	No	911401593432	BBP500 G4 LED85/CW PSU S-WB	No
911401505142	BCP500 G4 LED85/NW PSD S-WB	DALI	911401593532	BBP500 G4 LED85/CW PSU S-MB	No
911401505242	BCP500 G4 LED85/NW PSD S-MB	DALI	911401593632	BBP500 G4 LED85/CW PSU A-WB	No
911401505342	BCP500 G4 LED85/NW PSD A-WB	DALI	911401593732	BBP500 G4 LED125/NW PSU S-WB	No
911401505442	BCP500 G4 LED85/CW PSD S-WB	DALI	911401593832	BBP500 G4 LED125/NW PSU S-MB	No
911401505542	BCP500 G4 LED85/CW PSD S-MB	DALI	911401593932	BBP500 G4 LED125/NW PSU A-WB	No
911401505642	BCP500 G4 LED85/CW PSD A-WB	DALI	911401594032	BBP500 G4 LED125/CW PSU S-WB	No
911401505742	BCP500 G4 LED125/NW PSD S-WB	DALI	911401594132	BBP500 G4 LED125/CW PSU S-MB	No
911401505842	BCP500 G4 LED125/NW PSD S-MB	DALI	911401594232	BBP500 G4 LED125/CW PSU A-WB	No
911401505942	BCP500 G4 LED125/NW PSD A-WB	DALI	911401594332	BBP500 G4 LED140/NW PSU S-WB	No
911401506042	BCP500 G4 LED125/CW PSD S-WB	DALI	911401594432	BBP500 G4 LED140/NW PSU S-MB	No
911401506142	BCP500 G4 LED125/CW PSD S-MB	DALI	911401594532	BBP500 G4 LED140/NW PSU A-WB	No
911401506242	BCP500 G4 LED125/CW PSD A-WB	DALI	911401594632	BBP500 G4 LED140/CW PSU S-WB	No
911401506342	BCP500 G4 LED140/NW PSD S-WB	DALI	911401594732	BBP500 G4 LED140/CW PSU S-MB	No
911401506442	BCP500 G4 LED140/NW PSD S-MB	DALI	911401594832	BBP500 G4 LED140/CW PSU A-WB	No
911401506542	BCP500 G4 LED140/NW PSD A-WB	DALI	911401594932	BBP500 G4 LED180/NW PSU S-WB	No
911401506642	BCP500 G4 LED140/CW PSD S-WB	DALI	911401595032	BBP500 G4 LED180/NW PSU S-MB	No
911401506742	BCP500 G4 LED140/CW PSD S-MB	DALI	911401595132	BBP500 G4 LED180/NW PSU A-WB	No
911401506842	BCP500 G4 LED140/CW PSD A-WB	DALI	911401595232	BBP500 G4 LED180/CW PSU S-WB	No

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Dimmable
911401595332	BBP500 G4 LED180/CW PSU S-MB	No
911401595432	BBP500 G4 LED180/CW PSU A-WB	No
911401595532	BBP500 G4 LED85/NW PSD S-WB	DALI
911401595632	BBP500 G4 LED85/NW PSD S-MB	DALI
911401595732	BBP500 G4 LED85/NW PSD A-WB	DALI
911401595832	BBP500 G4 LED85/CW PSD S-WB	DALI
911401595932	BBP500 G4 LED85/CW PSD S-MB	DALI
911401596032	BBP500 G4 LED85/CW PSD A-WB	DALI
911401596132	BBP500 G4 LED125/NW PSD S-WB	DALI
911401596232	BBP500 G4 LED125/NW PSD S-MB	DALI
911401596332	BBP500 G4 LED125/NW PSD A-WB	DALI
911401596432	BBP500 G4 LED125/CW PSD S-WB	DALI
911401596532	BBP500 G4 LED125/CW PSD S-MB	DALI

Order Code	Full Product Name	Dimmable
911401596632	BBP500 G4 LED125/CW PSD A-WB	DALI
911401596732	BBP500 G4 LED140/NW PSD S-WB	DALI
911401596832	BBP500 G4 LED140/NW PSD S-MB	DALI
911401596932	BBP500 G4 LED140/NW PSD A-WB	DALI
911401597032	BBP500 G4 LED140/CW PSD S-WB	DALI
911401597132	BBP500 G4 LED140/CW PSD S-MB	DALI
911401597232	BBP500 G4 LED140/CW PSD A-WB	DALI
911401597332	BBP500 G4 LED180/NW PSD S-WB	DALI
911401597432	BBP500 G4 LED180/NW PSD S-MB	DALI
911401597532	BBP500 G4 LED180/NW PSD A-WB	DALI
911401597632	BBP500 G4 LED180/CW PSD S-WB	DALI
911401597732	BBP500 G4 LED180/CW PSD S-MB	DALI
911401597832	BBP500 G4 LED180/CW PSD A-WB	DALI

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401502742	BCP500 G4 LED85/NW PSU S-WB	Clear glass	IK07
911401502842	BCP500 G4 LED85/NW PSU S-MB	Clear glass	IK07
911401502942	BCP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401503042	BCP500 G4 LED85/CW PSU S-WB	Clear glass	IK07
911401503142	BCP500 G4 LED85/CW PSU S-MB	Clear glass	IK07
911401503242	BCP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401503342	BCP500 G4 LED125/NW PSU S-WB	Clear glass	IK07
911401503442	BCP500 G4 LED125/NW PSU S-MB	Clear glass	IK07
911401503542	BCP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
911401503642	BCP500 G4 LED125/CW PSU S-WB	Clear glass	IK07
911401503742	BCP500 G4 LED125/CW PSU S-MB	Clear glass	IK07
911401503842	BCP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401503942	BCP500 G4 LED140/NW PSU S-WB	Clear glass	IK07
911401504042	BCP500 G4 LED140/NW PSU S-MB	Clear glass	IK07
911401504142	BCP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401504242	BCP500 G4 LED140/CW PSU S-WB	Clear glass	IK07
911401504342	BCP500 G4 LED140/CW PSU S-MB	Clear glass	IK07
911401504442	BCP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401504542	BCP500 G4 LED180/NW PSU S-WB	Clear glass	IK07
911401504642	BCP500 G4 LED180/NW PSU S-MB	Clear glass	IK07
911401504742	BCP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401504842	BCP500 G4 LED180/CW PSU S-WB	Clear glass	IK07
911401504942	BCP500 G4 LED180/CW PSU S-MB	Clear glass	IK07
911401505042	BCP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401509942	BCP500 G4 LED85/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401510042	BCP500 G4 LED85/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401510142	BCP500 G4 LED85/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401510242	BCP500 G4 LED85/CW PSU S-WB	Polycarbonate	IK08
	PC		

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401510342	BCP500 G4 LED85/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401510442	BCP500 G4 LED85/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401510542	BCP500 G4 LED125/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401510642	BCP500 G4 LED125/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401510742	BCP500 G4 LED125/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401510842	BCP500 G4 LED125/CW PSU S-WB	Polycarbonate	IK08
	PC		
911401510942	BCP500 G4 LED125/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401511042	BCP500 G4 LED125/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401511142	BCP500 G4 LED140/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401511242	BCP500 G4 LED140/NW PSU S-MB	Polycarbonate	IK08
	PC		
911401511342	BCP500 G4 LED140/NW PSU A-WB	Polycarbonate	IK08
	PC		
911401511442	BCP500 G4 LED140/CW PSU S-WB	Polycarbonate	IK08
	PC		
911401511542	BCP500 G4 LED140/CW PSU S-MB	Polycarbonate	IK08
	PC		
911401511642	BCP500 G4 LED140/CW PSU A-WB	Polycarbonate	IK08
	PC		
911401511742	BCP500 G4 LED180/NW PSU S-WB	Polycarbonate	IK08
	PC		
911401511842	BCP500 G4 LED180/NW PSU S-MB	Polycarbonate	IK08
	PC		

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401511942	BCP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	Clear glass	IK07
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	Clear glass	IK07
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	Clear glass	IK07
911401509732	BBP500 G4 LED85/NW GU5.3 S-WB	Clear glass	IK07
9114015098032	BBP500 G4 LED85/NW GU5.3 S-MB	Clear glass	IK07
9114015098132	BBP500 G4 LED85/NW GU5.3 A-WB	Clear glass	IK07
9114015098232	BBP500 G4 LED85/CW GU5.3 S-WB	Clear glass	IK07
9114015098332	BBP500 G4 LED85/CW GU5.3 S-MB	Clear glass	IK07
9114015098432	BBP500 G4 LED85/CW GU5.3 A-WB	Clear glass	IK07
9114015098532	BBP500 G4 LED125/NW GU5.3 S-WB	Clear glass	IK07
9114015098632	BBP500 G4 LED125/NW GU5.3 S-MB	Clear glass	IK07
9114015098732	BBP500 G4 LED125/NW GU5.3 A-WB	Clear glass	IK07
9114015098832	BBP500 G4 LED125/CW GU5.3 S-WB	Clear glass	IK07
9114015098932	BBP500 G4 LED125/CW GU5.3 S-MB	Clear glass	IK07
9114015099032	BBP500 G4 LED125/CW GU5.3 A-WB	Clear glass	IK07
9114015099132	BBP500 G4 LED140/NW GU5.3 S-WB	Clear glass	IK07
9114015099232	BBP500 G4 LED140/NW GU5.3 S-MB	Clear glass	IK07
9114015099332	BBP500 G4 LED140/NW GU5.3 A-WB	Clear glass	IK07
9114015099432	BBP500 G4 LED140/CW GU5.3 S-WB	Clear glass	IK07
9114015099532	BBP500 G4 LED140/CW GU5.3 S-MB	Clear glass	IK07
9114015099632	BBP500 G4 LED140/CW GU5.3 A-WB	Clear glass	IK07
9114015099732	BBP500 G4 LED180/NW GU5.3 S-WB	Clear glass	IK07
9114015099832	BBP500 G4 LED180/NW GU5.3 S-MB	Clear glass	IK07
9114015099932	BBP500 G4 LED180/NW GU5.3 A-WB	Clear glass	IK07
911401512342	BGP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401512442	BGP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401512542	BGP500 G4 LED125/NW PSU A-WB	Clear glass	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401512642	BGP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401512742	BGP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401512842	BGP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401512942	BGP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401513042	BGP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401505142	BCP500 G4 LED85/NW PSD S-WB	Clear glass	IK07
911401505242	BCP500 G4 LED85/NW PSD S-MB	Clear glass	IK07
911401505342	BCP500 G4 LED85/NW PSD A-WB	Clear glass	IK07
911401505442	BCP500 G4 LED85/CW PSD S-WB	Clear glass	IK07
911401505542	BCP500 G4 LED85/CW PSD S-MB	Clear glass	IK07
911401505642	BCP500 G4 LED85/CW PSD A-WB	Clear glass	IK07
911401505742	BCP500 G4 LED125/NW PSD S-WB	Clear glass	IK07
911401505842	BCP500 G4 LED125/NW PSD S-MB	Clear glass	IK07
911401505942	BCP500 G4 LED125/NW PSD A-WB	Clear glass	IK07
911401506042	BCP500 G4 LED125/CW PSD S-WB	Clear glass	IK07
911401506142	BCP500 G4 LED125/CW PSD S-MB	Clear glass	IK07
911401506242	BCP500 G4 LED125/CW PSD A-WB	Clear glass	IK07
911401506342	BCP500 G4 LED140/NW PSD S-WB	Clear glass	IK07
911401506442	BCP500 G4 LED140/NW PSD S-MB	Clear glass	IK07
911401506542	BCP500 G4 LED140/NW PSD A-WB	Clear glass	IK07
911401506642	BCP500 G4 LED140/CW PSD S-WB	Clear glass	IK07
911401506742	BCP500 G4 LED140/CW PSD S-MB	Clear glass	IK07
911401506842	BCP500 G4 LED140/CW PSD A-WB	Clear glass	IK07
911401506942	BCP500 G4 LED180/NW PSD S-WB	Clear glass	IK07
911401507042	BCP500 G4 LED180/NW PSD S-MB	Clear glass	IK07
911401507142	BCP500 G4 LED180/NW PSD A-WB	Clear glass	IK07
911401507242	BCP500 G4 LED180/CW PSD S-WB	Clear glass	IK07
911401507342	BCP500 G4 LED180/CW PSD S-MB	Clear glass	IK07
911401507442	BCP500 G4 LED180/CW PSD A-WB	Clear glass	IK07
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	Polycarbonate	IK08
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	Polycarbonate	IK08
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	Polycarbonate	IK08
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	Polycarbonate	IK08
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	Polycarbonate	IK08
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	Polycarbonate	IK08
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	Polycarbonate	IK08
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	Polycarbonate	IK08
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	Polycarbonate	IK08
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	Polycarbonate	IK08

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	Polycarbonate	IK08
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	Polycarbonate	IK08
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	Polycarbonate	IK08
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	Polycarbonate	IK08
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	Polycarbonate	IK08
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	Polycarbonate	IK08
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	Polycarbonate	IK08
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	Polycarbonate	IK08
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	Polycarbonate	IK08
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	Polycarbonate	IK08
911401502342	BBP500 G4 LED180/NW PSU A-WB PC	Polycarbonate	IK08
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	Polycarbonate	IK08
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	Polycarbonate	IK08
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	Polycarbonate	IK08
911401593132	BBP500 G4 LED85/NW PSU S-WB	Clear glass	IK07
911401593232	BBP500 G4 LED85/NW PSU S-MB	Clear glass	IK07
911401593332	BBP500 G4 LED85/NW PSU A-WB	Clear glass	IK07
911401593432	BBP500 G4 LED85/CW PSU S-WB	Clear glass	IK07
911401593532	BBP500 G4 LED85/CW PSU S-MB	Clear glass	IK07
911401593632	BBP500 G4 LED85/CW PSU A-WB	Clear glass	IK07
911401593732	BBP500 G4 LED125/NW PSU S-WB	Clear glass	IK07
911401593832	BBP500 G4 LED125/NW PSU S-MB	Clear glass	IK07
911401593932	BBP500 G4 LED125/NW PSU A-WB	Clear glass	IK07
911401594032	BBP500 G4 LED125/CW PSU S-WB	Clear glass	IK07
911401594132	BBP500 G4 LED125/CW PSU S-MB	Clear glass	IK07
911401594232	BBP500 G4 LED125/CW PSU A-WB	Clear glass	IK07
911401594332	BBP500 G4 LED140/NW PSU S-WB	Clear glass	IK07
911401594432	BBP500 G4 LED140/NW PSU S-MB	Clear glass	IK07
911401594532	BBP500 G4 LED140/NW PSU A-WB	Clear glass	IK07
911401594632	BBP500 G4 LED140/CW PSU S-WB	Clear glass	IK07
911401594732	BBP500 G4 LED140/CW PSU S-MB	Clear glass	IK07
911401594832	BBP500 G4 LED140/CW PSU A-WB	Clear glass	IK07
911401594932	BBP500 G4 LED180/NW PSU S-WB	Clear glass	IK07
911401595032	BBP500 G4 LED180/NW PSU S-MB	Clear glass	IK07
911401595132	BBP500 G4 LED180/NW PSU A-WB	Clear glass	IK07
911401595232	BBP500 G4 LED180/CW PSU S-WB	Clear glass	IK07

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401595332	BBP500 G4 LED180/CW PSU S-MB	Clear glass	IK07
911401595432	BBP500 G4 LED180/CW PSU A-WB	Clear glass	IK07
911401595532	BBP500 G4 LED85/NW PSD S-WB	Clear glass	IK07
911401595632	BBP500 G4 LED85/NW PSD S-MB	Clear glass	IK07
911401595732	BBP500 G4 LED85/NW PSD A-WB	Clear glass	IK07
911401595832	BBP500 G4 LED85/CW PSD S-WB	Clear glass	IK07
911401595932	BBP500 G4 LED85/CW PSD S-MB	Clear glass	IK07
911401596032	BBP500 G4 LED85/CW PSD A-WB	Clear glass	IK07
911401596132	BBP500 G4 LED125/NW PSD S-WB	Clear glass	IK07
911401596232	BBP500 G4 LED125/NW PSD S-MB	Clear glass	IK07
911401596332	BBP500 G4 LED125/NW PSD A-WB	Clear glass	IK07
911401596432	BBP500 G4 LED125/CW PSD S-WB	Clear glass	IK07
911401596532	BBP500 G4 LED125/CW PSD S-MB	Clear glass	IK07

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401596632	BBP500 G4 LED125/CW PSD A-WB	Clear glass	IK07
911401596732	BBP500 G4 LED140/NW PSD S-WB	Clear glass	IK07
911401596832	BBP500 G4 LED140/NW PSD S-MB	Clear glass	IK07
911401596932	BBP500 G4 LED140/NW PSD A-WB	Clear glass	IK07
911401597032	BBP500 G4 LED140/CW PSD S-WB	Clear glass	IK07
911401597132	BBP500 G4 LED140/CW PSD S-MB	Clear glass	IK07
911401597232	BBP500 G4 LED140/CW PSD A-WB	Clear glass	IK07
911401597332	BBP500 G4 LED180/NW PSD S-WB	Clear glass	IK07
911401597432	BBP500 G4 LED180/NW PSD S-MB	Clear glass	IK07
911401597532	BBP500 G4 LED180/NW PSD A-WB	Clear glass	IK07
911401597632	BBP500 G4 LED180/CW PSD S-WB	Clear glass	IK07
911401597732	BBP500 G4 LED180/CW PSD S-MB	Clear glass	IK07
911401597832	BBP500 G4 LED180/CW PSD A-WB	Clear glass	IK07

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401502742	BCP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401502842	BCP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401502942	BCP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503042	BCP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503142	BCP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503242	BCP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503342	BCP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503442	BCP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503542	BCP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503642	BCP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401503742	BCP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503842	BCP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401503942	BCP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504042	BCP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504142	BCP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504242	BCP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504342	BCP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504442	BCP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401504542	BCP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504642	BCP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401504742	BCP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504842	BCP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401504942	BCP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
911401505042	BCP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401509942	BCP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510042	BCP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510142	BCP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510242	BCP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510342	BCP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510442	BCP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510542	BCP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510642	BCP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510742	BCP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510842	BCP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401510942	BCP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511042	BCP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511142	BCP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401511242	BCP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511342	BCP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511442	BCP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511542	BCP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511642	BCP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511742	BCP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511842	BCP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401511942	BCP500 G4 LED180/NW PSU A-WB WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512042	BCP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512142	BCP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401512242	BCP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401507542	BCP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507642	BCP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507742	BCP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507842	BCP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507942	BCP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508042	BCP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401508142	BCP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508242	BCP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508342	BCP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508442	BCP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508542	BCP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508642	BCP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508742	BCP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508842	BCP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401508942	BCP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509042	BCP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509142	BCP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509242	BCP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509342	BCP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509442	BCP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509542	BCP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509642	BCP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401509742	BCP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401509842	BCP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500042	BBP500 G4 LED180/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500142	BBP500 G4 LED180/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500242	BBP500 G4 LED180/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597932	BBP500 G4 LED85/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598032	BBP500 G4 LED85/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598132	BBP500 G4 LED85/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598232	BBP500 G4 LED85/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598332	BBP500 G4 LED85/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598432	BBP500 G4 LED85/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598532	BBP500 G4 LED125/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598632	BBP500 G4 LED125/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598732	BBP500 G4 LED125/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598832	BBP500 G4 LED125/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401598932	BBP500 G4 LED125/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599032	BBP500 G4 LED125/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599132	BBP500 G4 LED140/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401599232	BBP500 G4 LED140/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599332	BBP500 G4 LED140/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599432	BBP500 G4 LED140/CW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599532	BBP500 G4 LED140/CW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599632	BBP500 G4 LED140/CW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599732	BBP500 G4 LED180/NW GU5.3 S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599832	BBP500 G4 LED180/NW GU5.3 S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401599932	BBP500 G4 LED180/NW GU5.3 A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401512342	BGP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	-
911401512442	BGP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	-
911401512542	BGP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	-
911401512642	BGP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	-
911401512742	BGP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	-
911401512842	BGP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	-
911401512942	BGP500 G4 LED180/NW PSU A-WB	-40 to +50 °C	-
911401513042	BGP500 G4 LED180/CW PSU A-WB	-40 to +50 °C	-
911401505142	BCP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505242	BCP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505342	BCP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401505442	BCP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505542	BCP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505642	BCP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505742	BCP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505842	BCP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401505942	BCP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506042	BCP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506142	BCP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506242	BCP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506342	BCP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506442	BCP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506542	BCP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506642	BCP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506742	BCP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506842	BCP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401506942	BCP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507042	BCP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401507142	BCP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507242	BCP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507342	BCP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401507442	BCP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401500342	BBP500 G4 LED85/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500442	BBP500 G4 LED85/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500542	BBP500 G4 LED85/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500642	BBP500 G4 LED85/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500742	BBP500 G4 LED85/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500842	BBP500 G4 LED85/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401500942	BBP500 G4 LED125/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501042	BBP500 G4 LED125/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501142	BBP500 G4 LED125/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501242	BBP500 G4 LED125/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501342	BBP500 G4 LED125/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501442	BBP500 G4 LED125/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501542	BBP500 G4 LED140/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401501642	BBP500 G4 LED140/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501742	BBP500 G4 LED140/NW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501842	BBP500 G4 LED140/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401501942	BBP500 G4 LED140/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502042	BBP500 G4 LED140/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502142	BBP500 G4 LED180/NW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502242	BBP500 G4 LED180/NW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502342	BBP500 G4 LED180/NW PSU A-WB WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502442	BBP500 G4 LED180/CW PSU S-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502542	BBP500 G4 LED180/CW PSU S-MB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401502642	BBP500 G4 LED180/CW PSU A-WB PC	-20 to +40 °C	For mounting on normally flammable surfaces
911401593132	BBP500 G4 LED85/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593232	BBP500 G4 LED85/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593332	BBP500 G4 LED85/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593432	BBP500 G4 LED85/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593532	BBP500 G4 LED85/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593632	BBP500 G4 LED85/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401593732	BBP500 G4 LED125/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593832	BBP500 G4 LED125/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401593932	BBP500 G4 LED125/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594032	BBP500 G4 LED125/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594132	BBP500 G4 LED125/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594232	BBP500 G4 LED125/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594332	BBP500 G4 LED140/NW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594432	BBP500 G4 LED140/NW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594532	BBP500 G4 LED140/NW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594632	BBP500 G4 LED140/CW PSU S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594732	BBP500 G4 LED140/CW PSU S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594832	BBP500 G4 LED140/CW PSU A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401594932	BBP500 G4 LED180/NW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595032	BBP500 G4 LED180/NW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595132	BBP500 G4 LED180/NW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595232	BBP500 G4 LED180/CW PSU S-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595332	BBP500 G4 LED180/CW PSU S-MB	-40 to +45 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401595432	BBP500 G4 LED180/CW PSU A-WB	-40 to +45 °C	For mounting on normally flammable surfaces
911401595532	BBP500 G4 LED85/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595632	BBP500 G4 LED85/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595732	BBP500 G4 LED85/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595832	BBP500 G4 LED85/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401595932	BBP500 G4 LED85/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596032	BBP500 G4 LED85/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596132	BBP500 G4 LED125/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596232	BBP500 G4 LED125/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596332	BBP500 G4 LED125/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596432	BBP500 G4 LED125/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596532	BBP500 G4 LED125/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596632	BBP500 G4 LED125/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596732	BBP500 G4 LED140/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596832	BBP500 G4 LED140/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401596932	BBP500 G4 LED140/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597032	BBP500 G4 LED140/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces

GreenPerform Canopy Mini500 G4

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401597132	BBP500 G4 LED140/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597232	BBP500 G4 LED140/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597332	BBP500 G4 LED180/NW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597432	BBP500 G4 LED180/NW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces

Order Code	Full Product Name	Ambient temperature range	Flammability mark
911401597532	BBP500 G4 LED180/NW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597632	BBP500 G4 LED180/CW PSD S-WB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597732	BBP500 G4 LED180/CW PSD S-MB	-40 to +50 °C	For mounting on normally flammable surfaces
911401597832	BBP500 G4 LED180/CW PSD A-WB	-40 to +50 °C	For mounting on normally flammable surfaces

