



Ledinaire highbay – For your everyday lighting jobs, easy to simply select and install.

Ledinaire High-bay

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that come with Philips high-quality at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables simple and flexible installation, either on a hook or an optional bracket. Products can be installed with optional reflectors for lower glare.

Benefits

- Philips quality and reliability
- Energy savings
- Easy and quick installation
- Wide application coverage

Features

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000lm with 24cm diameter, 20,000lm with 34cm diameter
- The IP65 rating is perfect for any application
- Including IP65 connector
- Single suspension with installation hook(included) or pipe mounting(not included)
- Optional reflector accessory for medium beam
- Non-dimming with driver on board

Ledinaire High-bay

Application

- Warehouses & Logistic centres
- General Manufacturing
- Exhibition halls & high ceiling lounges


Versions



Ledinaire Highbay All-in BY30P

Dimensional drawing

BY030P LED150_220_280S/840_50_65 PSU WB



Product details



Ledinaire BY030P CCT swtch
DDP3



Ledinaire BY030P sensor install
DPP

Ledinaire High-bay



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2025, August 26 - data subject to change