



Ledinaire highbay – For your everyday lighting jobs, easy to simply select and install.

Ledinaire High-bay

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that come with Philips high-quality at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables simple and flexible installation, either on a hook or an optional bracket. Products can be installed with optional reflectors for lower glare.

Benefits

- Philips quality and reliability
- Energy savings
- Easy and quick installation
- Wide application coverage

Features

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000lm with 24cm diameter, 20,000lm with 34cm diameter
- The IP65 rating is perfect for any application
- Including IP65 connector
- Single suspension with installation hook(included) or pipe mounting(not included)
- Optional reflector accessory for medium beam
- Non-dimming with driver on board

Ledinaire High-bay

Application

- Warehouses & Logistic centres
- General Manufacturing
- Exhibition halls & high celing lounges


Versions



Ledinaire Highbay All-in BY30P

Dimensional drawing

BY030P LED150_220_2805/840_50_65 PSU WB



Product details



Ledinaire BY030P CCT swtch
DDP3



Ledinaire BY030P sensor install
DPP

Ledinaire High-bay

