



**Proven quality.
Effortless installation.
Your dependable and
affordable choice for
every job, every time.**

Ledinaire High-bay

The Ledinaire high-bay range includes a selection of off-the-shelf high-bay LED luminaires offering Philips's renowned quality at a competitive price. Reliable, energy efficient and affordable. Ledinaire high-bay enables simple and flexible installation, either on a hook or on an optional bracket. Products can be installed with optional reflectors for lower glare.

Benefits

- Philips quality and reliability
- Energy savings
- Easy and quick installation
- Wide application coverage

Features

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000 lm 24 cm (BY020P), 20,000 lm 34 cm (BY021P)
- High protection rates (IP65) that are perfect for any application
- Including IP65 connector
- Single suspension with installation hook

Ledinaire High-bay

Application

- Warehouses
- Manufacturing


Versions



Ledinaire Highbay All-in BY30P

Dimensional drawing

BY030P LED150_220_2805/840_50_65 PSU WB



Product details



Ledinaire BY030P CCT swtch
DDP3



Ledinaire BY030P sensor install
DPP

Ledinaire High-bay

