



GreenPerform Highbay G5: a versatile LED highbay with optimized performance and future-proof control system

GreenPerform Highbay G5

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Visual comfort
- Wide range of applications
- Connected ready for cloud-based IoT software applications

GreenPerform Highbay G5

Features

- 170 lm/W system efficacy
- 75,000 hours L70B50 lifetime @Ta 35°
- Glare control (Narrow Beam), uniform illuminance (Wide Beam)
- Works seamlessly with the Interact IoT software and platform
- Cold room application support

Application



- Manufacturing
- Warehouses
- Logistic center
- Exhibition hall

Specifications

| | |
|------------------------------------|--|
| Mounting type | Suspended |
| | Pipe |
| | Surface |
| Operating Temperature range | -30 to +50 °C |
| Light Source | LED |
| Mains Voltage | 220-240V / 50-60Hz |
| Mains connection | Flying cable |
| Mechanical Accessories | Hook for suspension |
| | Mounting bracket for surface |
| Dimming | PSU: non-dimmable |
| | PSD: Dimmable via Dali-broadcasting |
| | Connected: Wireless control, compatible with SNH210 sensor |
| Control system input | DALI/Wireless |
| Integrated sensors | SNH210 |
| Material | Housing: die-cast aluminium |
| Main color of the luminaire | RAL7012 |
| Flicker / Pst / SVM | PSU: <30% |
| | PSD/Connected: <3.2% |
| Luminous flux | 10klm-30klm |
| Power consumption | 67W-205W |


| | |
|---|---------------|
| Luminaire efficacy | Up to 160lm/W |
| Correlated color temperature - CCT | 4000K |
| Color Rendering index - CRI | 6500K |
| Color Rendering index - CRI | 80 |
| Beam angle | WB: 85° |
| | NB: 55° |
| Optical cover/lens material | PC |
| Optical cover/lens finish | Clear |
| Protection Class | Class I |
| IEC61140 | |
| Mechanical impact protection | IK08 |
| Ingress protection | IP65 |
| Driver replaceable | Yes |
| UGR | WB: 25 |
| | NB: 22 |
| Installation | Suspended |
| | Pipe |
| | Surface |

Dimensional drawing






GreenPerform Highbay G5

Dimensional drawing



GreenPerform Highbay G5

Dimensional drawing



Product details



GreenPerform Highbay G5



GreenPerform Highbay G5

GreenPerform Highbay G5

General Information

| | |
|----------------------|--------|
| Driver included | Yes |
| Gear | - |
| Number of gear units | 1 unit |

Light Technical

| | |
|-----------------------------|---------------|
| Beam angle of light source | 115 degree(s) |
| Color rendering index (CRI) | 80 |
| Number of light sources | 1 |

Operating and Electrical

| | |
|-------------------------------|----------------|
| Protection class IEC | Safety class I |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Suitable for random switching | Yes |

Mechanical and Housing

| | |
|--------------------|------------|
| Optical cover type | Clear dome |
| Housing Color | Grey |

Approval and Application

| | |
|-------------------|---|
| CE mark | Yes |
| ENEC mark | - |
| Flammability mark | For mounting on normally flammable surfaces |

Light Technical

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous Flux | Optic type |
|--------------|--|-------------------|------------------------|---------------|------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | | |
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | 4000 K | 173 lm/W | 25,000 lm | Wide beam |

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous Flux | Optic type |
|--------------|--|-------------------|------------------------|---------------|-------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | | |
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401528245 | BY698P G5 LED105/NW PSU WB GM | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401528345 | BY698P G5 LED105/NW PSU NB GM | 4000 K | 166 lm/W | 10,500 lm | Narrow beam |
| 911401528445 | BY698P G5 LED105/CW PSU WB GM | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401528545 | BY698P G5 LED105/CW PSU NB GM | 6500 K | 166 lm/W | 10,500 lm | Narrow beam |
| 911401528645 | BY698P G5 LED150/NW PSU WB GM | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401528745 | BY698P G5 LED150/NW PSU NB GM | 4000 K | 170 lm/W | 15,000 lm | Narrow beam |
| 911401528845 | BY698P G5 LED150/CW PSU WB GM | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401528945 | BY698P G5 LED150/CW PSU NB GM | 6500 K | 170 lm/W | 15,000 lm | Narrow beam |
| 911401529045 | BY698P G5 LED200/NW PSU WB GM | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401529145 | BY698P G5 LED200/NW PSU NB GM | 4000 K | 169 lm/W | 20,500 lm | Narrow beam |
| 911401529245 | BY698P G5 LED200/CW PSU WB GM | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401529345 | BY698P G5 LED200/CW PSU NB GM | 6500 K | 169 lm/W | 20,500 lm | Narrow beam |
| 911401529445 | BY698P G5 LED250/NW PSU WB GM | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401529545 | BY698P G5 LED250/NW PSU NB GM | 4000 K | 173 lm/W | 25,000 lm | Narrow beam |

GreenPerform Highbay G5

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous Flux | Optic type |
|--------------|-------------------------------|-------------------|------------------------|---------------|-------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | | |
| 911401529645 | BY698P G5 LED250/CW PSU WB GM | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401529745 | BY698P G5 LED250/CW PSU NB GM | 6500 K | 173 lm/W | 25,000 lm | Narrow beam |
| 911401529845 | BY698P G5 LED300/NW PSU WB GM | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | 4000 K | 171 lm/W | 31,000 lm | Narrow beam |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | 6500 K | 171 lm/W | 31,000 lm | Narrow beam |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | 4000 K | 152 lm/W | 10,500 lm | Wide beam |
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | 4000 K | 152 lm/W | 10,500 lm | Narrow beam |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | 6500 K | 152 lm/W | 10,500 lm | Wide beam |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | 6500 K | 152 lm/W | 10,500 lm | Narrow beam |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | 4000 K | 161 lm/W | 15,000 lm | Wide beam |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | 4000 K | 161 lm/W | 15,000 lm | Narrow beam |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | 6500 K | 161 lm/W | 15,000 lm | Wide beam |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | 6500 K | 161 lm/W | 15,000 lm | Narrow beam |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | 4000 K | 162 lm/W | 20,500 lm | Wide beam |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | 4000 K | 162 lm/W | 20,500 lm | Narrow beam |
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | 6500 K | 162 lm/W | 20,500 lm | Wide beam |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | 6500 K | 162 lm/W | 20,500 lm | Narrow beam |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | 4000 K | 162 lm/W | 25,000 lm | Wide beam |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | 4000 K | 162 lm/W | 25,000 lm | Narrow beam |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | 6500 K | 162 lm/W | 25,000 lm | Wide beam |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | 6500 K | 162 lm/W | 25,000 lm | Narrow beam |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | 4000 K | 163 lm/W | 31,000 lm | Wide beam |
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | 4000 K | 163 lm/W | 31,000 lm | Narrow beam |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | 6500 K | 163 lm/W | 31,000 lm | Wide beam |

GreenPerform Highbay G5

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous Flux | Optic type |
|--------------|-----------------------------------|-------------------|------------------------|---------------|-------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | | |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | 6500 K | 163 lm/W | 31,000 lm | Narrow beam |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | 4000 K | 166 lm/W | 10,500 lm | Narrow beam |
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | 6500 K | 166 lm/W | 10,500 lm | Narrow beam |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | 4000 K | 170 lm/W | 15,000 lm | Narrow beam |
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | 6500 K | 170 lm/W | 15,000 lm | Narrow beam |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | 4000 K | 169 lm/W | 20,500 lm | Narrow beam |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | 6500 K | 169 lm/W | 20,500 lm | Narrow beam |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | 4000 K | 173 lm/W | 25,000 lm | Narrow beam |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | 6500 K | 173 lm/W | 25,000 lm | Narrow beam |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | 4000 K | 171 lm/W | 31,000 lm | Narrow beam |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | 6500 K | 171 lm/W | 31,000 lm | Narrow beam |
| 911401541745 | BY690P LED105/NW PSU WB GM | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401541845 | BY690P LED105/CW PSU WB GM | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401541945 | BY690P LED150/NW PSU WB GM | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401542045 | BY690P LED150/CW PSU WB GM | 6500 K | 170 lm/W | 15,000 lm | Wide beam |

GreenPerform Highbay G5

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous | Optic type |
|--------------|--|-------------------|------------------------|-----------|-------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | Flux | |
| 911401542145 | BY690P LED200/NW PSU WB GM | 4000 K | 181 lm/W | 20,000 lm | Wide beam |
| 911401542245 | BY690P LED200/CW PSU WB GM | 6500 K | 181 lm/W | 20,000 lm | Wide beam |
| 911401542345 | BY690P LED250/NW PSU WB GM | 4000 K | 177 lm/W | 25,500 lm | Wide beam |
| 911401542445 | BY690P LED250/CW PSU WB GM | 6500 K | 177 lm/W | 25,500 lm | Wide beam |
| 911401542545 | BY690P LED300/NW PSU WB GM | 4000 K | 176 lm/W | 30,000 lm | Wide beam |
| 911401542645 | BY690P LED300/CW PSU WB GM | 6500 K | 176 lm/W | 30,000 lm | Wide beam |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | 4000 K | 174 lm/W | 15,000 lm | Wide beam |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | 4000 K | 174 lm/W | 15,000 lm | Narrow beam |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | 6500 K | 174 lm/W | 15,000 lm | Wide beam |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | 6500 K | 174 lm/W | 15,000 lm | Narrow beam |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | 4000 K | 168 lm/W | 20,500 lm | Wide beam |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | 4000 K | 168 lm/W | 20,500 lm | Narrow beam |
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | 6500 K | 168 lm/W | 20,500 lm | Wide beam |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | 6500 K | 168 lm/W | 20,500 lm | Narrow beam |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | 4000 K | 170 lm/W | 25,000 lm | Wide beam |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | 4000 K | 170 lm/W | 25,000 lm | Narrow beam |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | 6500 K | 170 lm/W | 25,000 lm | Wide beam |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | 6500 K | 170 lm/W | 25,000 lm | Narrow beam |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | 4000 K | 170 lm/W | 31,000 lm | Wide beam |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | 4000 K | 170 lm/W | 31,000 lm | Narrow beam |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | 6500 K | 170 lm/W | 31,000 lm | Wide beam |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | 6500 K | 170 lm/W | 31,000 lm | Narrow beam |
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | 4000 K | 170 lm/W | 15,000 lm | Wide beam |

GreenPerform Highbay G5

| Order Code | Full Product Name | Correlated Color | Luminous | Luminous Flux | Optic type |
|--------------|--------------------------------------|-------------------|------------------------|---------------|------------|
| | | Temperature (Nom) | Efficacy (rated) (Nom) | | |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | 6500 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | 4000 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | 6500 K | 166 lm/W | 10,500 lm | Wide beam |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | 4000 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | 6500 K | 170 lm/W | 15,000 lm | Wide beam |
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | 4000 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | 6500 K | 169 lm/W | 20,500 lm | Wide beam |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | 4000 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | 6500 K | 173 lm/W | 25,000 lm | Wide beam |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | 4000 K | 171 lm/W | 31,000 lm | Wide beam |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | 6500 K | 171 lm/W | 31,000 lm | Wide beam |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|-----------------------------------|-------------------|--------------|-------------------------------------|-------------------|
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | 63 W | 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | 88 W |
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | 63 W | 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | 88 W |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | 88 W | 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | 121 W |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | 88 W | 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | 121 W |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | 121 W | 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | 144 W |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | 121 W | 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | 144 W |
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | 144 W | 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | 181 W |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | 144 W | 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | 181 W |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | 181 W | 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | 63 W |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | 181 W | 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | 88 W |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | 63 W | 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | 121 W |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | 63 W | 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | 144 W |

GreenPerform Highbay G5

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | 181 W |
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | 63 W |
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | 63 W |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | 88 W |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | 88 W |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | 121 W |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | 121 W |
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | 144 W |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | 144 W |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | 181 W |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | 181 W |
| 911401528245 | BY698P G5 LED105/NW PSU WB GM | 63 W |
| 911401528345 | BY698P G5 LED105/NW PSU NB GM | 63 W |
| 911401528445 | BY698P G5 LED105/CW PSU WB GM | 63 W |
| 911401528545 | BY698P G5 LED105/CW PSU NB GM | 63 W |
| 911401528645 | BY698P G5 LED150/NW PSU WB GM | 88 W |
| 911401528745 | BY698P G5 LED150/NW PSU NB GM | 88 W |
| 911401528845 | BY698P G5 LED150/CW PSU WB GM | 88 W |
| 911401528945 | BY698P G5 LED150/CW PSU NB GM | 88 W |
| 911401529045 | BY698P G5 LED200/NW PSU WB GM | 121 W |
| 911401529145 | BY698P G5 LED200/NW PSU NB GM | 121 W |
| 911401529245 | BY698P G5 LED200/CW PSU WB GM | 121 W |
| 911401529345 | BY698P G5 LED200/CW PSU NB GM | 121 W |
| 911401529445 | BY698P G5 LED250/NW PSU WB GM | 144 W |
| 911401529545 | BY698P G5 LED250/NW PSU NB GM | 144 W |
| 911401529645 | BY698P G5 LED250/CW PSU WB GM | 144 W |
| 911401529745 | BY698P G5 LED250/CW PSU NB GM | 144 W |
| 911401529845 | BY698P G5 LED300/NW PSU WB GM | 181 W |
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | 181 W |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | 181 W |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | 181 W |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | 69 W |
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | 69 W |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | 69 W |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | 69 W |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | 93 W |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | 93 W |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | 93 W |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | 93 W |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | 126 W |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | 126 W |
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | 126 W |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | 126 W |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | 154 W |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | 154 W |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | 154 W |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | 154 W |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | 190 W |
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | 190 W |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | 190 W |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | 190 W |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | 63 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | 63 W |
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | 63 W |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | 63 W |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | 88 W |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | 88 W |
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | 88 W |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | 88 W |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | 121 W |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | 121 W |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | 121 W |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | 121 W |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | 144 W |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | 144 W |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | 144 W |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | 144 W |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | 181 W |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | 181 W |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | 181 W |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | 181 W |
| 911401541745 | BY690P LED105/NW PSU WB GM | 63 W |
| 911401541845 | BY690P LED105/CW PSU WB GM | 63 W |
| 911401541945 | BY690P LED150/NW PSU WB GM | 88 W |
| 911401542045 | BY690P LED150/CW PSU WB GM | 88 W |
| 911401542145 | BY690P LED200/NW PSU WB GM | 110 W |
| 911401542245 | BY690P LED200/CW PSU WB GM | 110 W |
| 911401542345 | BY690P LED250/NW PSU WB GM | 144 W |
| 911401542445 | BY690P LED250/CW PSU WB GM | 144 W |
| 911401542545 | BY690P LED300/NW PSU WB GM | 170 W |
| 911401542645 | BY690P LED300/CW PSU WB GM | 170 W |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | 86 W |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | 86 W |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | 86 W |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | 86 W |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | 122 W |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | 122 W |
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | 122 W |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | 122 W |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | 147 W |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | 147 W |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | 147 W |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | 147 W |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | 182 W |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | 182 W |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | 182 W |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | 182 W |
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | 63 W |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | 63 W |
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | 88 W |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | 88 W |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | 121 W |
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | 121 W |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | 144 W |

GreenPerform Highbay G5

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------------|-------------------|
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | 144 W |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | 181 W |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | 181 W |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | 63 W |
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | 63 W |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | 88 W |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | 88 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------------|-------------------|
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | 121 W |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | 121 W |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | 144 W |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | 144 W |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | 181 W |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | 181 W |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--------------------------------------|---|-------------------|
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--|---|-------------------|
| 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |

GreenPerform Highbay G5

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|---------------------------------------|---------------------------------------|-------------------|
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401528245 | BY698P G5 LED105/NW PSU WB GM | - | Not applicable |
| 911401528345 | BY698P G5 LED105/NW PSU NB GM | - | Not applicable |
| 911401528445 | BY698P G5 LED105/CW PSU WB GM | - | Not applicable |
| 911401528545 | BY698P G5 LED105/CW PSU NB GM | - | Not applicable |
| 911401528645 | BY698P G5 LED150/NW PSU WB GM | - | Not applicable |
| 911401528745 | BY698P G5 LED150/NW PSU NB GM | - | Not applicable |
| 911401528845 | BY698P G5 LED150/CW PSU WB GM | - | Not applicable |
| 911401528945 | BY698P G5 LED150/CW PSU NB GM | - | Not applicable |
| 911401529045 | BY698P G5 LED200/NW PSU WB GM | - | Not applicable |
| 911401529145 | BY698P G5 LED200/NW PSU NB GM | - | Not applicable |
| 911401529245 | BY698P G5 LED200/CW PSU WB GM | - | Not applicable |
| 911401529345 | BY698P G5 LED200/CW PSU NB GM | - | Not applicable |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|-------------------------------|----------|-------------------|
| 911401529445 | BY698P G5 LED250/NW PSU WB GM | - | Not applicable |
| 911401529545 | BY698P G5 LED250/NW PSU NB GM | - | Not applicable |
| 911401529645 | BY698P G5 LED250/CW PSU WB GM | - | Not applicable |
| 911401529745 | BY698P G5 LED250/CW PSU NB GM | - | Not applicable |
| 911401529845 | BY698P G5 LED300/NW PSU WB GM | - | Not applicable |
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | - | Not applicable |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | - | Not applicable |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | - | Not applicable |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | DALI | 20% |
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | DALI | 20% |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | DALI | 20% |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | DALI | 20% |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | DALI | 20% |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | DALI | 20% |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | DALI | 20% |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | DALI | 20% |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | DALI | 10% |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | DALI | 10% |
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | DALI | 10% |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | DALI | 10% |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | DALI | 20% |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | DALI | 20% |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | DALI | 20% |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | DALI | 20% |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | DALI | 20% |

GreenPerform Highbay G5

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|-----------------------------------|----------|-------------------|
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | DALI | 20% |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | DALI | 20% |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | DALI | 20% |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | - | Not applicable |
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | - | Not applicable |
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | - | Not applicable |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | - | Not applicable |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | - | Not applicable |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | - | Not applicable |
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | - | Not applicable |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | - | Not applicable |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | - | Not applicable |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | - | Not applicable |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | - | Not applicable |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | - | Not applicable |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | - | Not applicable |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | - | Not applicable |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | - | Not applicable |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | - | Not applicable |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | - | Not applicable |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | - | Not applicable |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | - | Not applicable |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | - | Not applicable |
| 911401541745 | BY690P LED105/NW PSU WB GM | - | Not applicable |
| 911401541845 | BY690P LED105/CW PSU WB GM | - | Not applicable |
| 911401541945 | BY690P LED150/NW PSU WB GM | - | Not applicable |
| 911401542045 | BY690P LED150/CW PSU WB GM | - | Not applicable |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|-------------------------------------|---------------------------------------|-------------------|
| 911401542145 | BY690P LED200/NW PSU WB GM | - | Not applicable |
| 911401542245 | BY690P LED200/CW PSU WB GM | - | Not applicable |
| 911401542345 | BY690P LED250/NW PSU WB GM | - | Not applicable |
| 911401542445 | BY690P LED250/CW PSU WB GM | - | Not applicable |
| 911401542545 | BY690P LED300/NW PSU WB GM | - | Not applicable |
| 911401542645 | BY690P LED300/CW PSU WB GM | - | Not applicable |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | - | 3% |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | - | 3% |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | - | 3% |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | - | 3% |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | - | 1% |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | - | 1% |
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | - | 1% |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | - | 1% |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | - | 3% |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | - | 3% |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | - | 3% |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | - | 3% |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | - | 3% |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | - | 3% |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | - | 3% |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | - | 3% |
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |

GreenPerform Highbay G5

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--------------------------------------|---------------------------------------|-------------------|
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |

| Order Code | Full Product Name | Dimmable | Maximum dim level |
|--------------|--------------------------------------|---------------------------------------|-------------------|
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | Wireless Dim - Do not use with dimmer | 0% (digital) |

Mechanical and Housing

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-----------------------------------|------------------------------|-------------------------|
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | IK03 | IP65 |
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | IK03 | IP65 |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | IK03 | IP65 |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | IK03 | IP65 |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | IK03 | IP65 |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | IK03 | IP65 |
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | IK03 | IP65 |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | IK03 | IP65 |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | IK03 | IP65 |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | IK03 | IP65 |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | IK03 | IP65 |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | IK03 | IP65 |
| 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | IK03 | IP65 |
| 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | IK03 | IP65 |
| 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | IK03 | IP65 |
| 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | IK03 | IP65 |

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-------------------------------------|------------------------------|-------------------------|
| 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | IK03 | IP65 |
| 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | IK03 | IP65 |
| 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | IK03 | IP65 |
| 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | IK03 | IP65 |
| 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | IK03 | IP65 |
| 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | IK03 | IP65 |
| 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | IK03 | IP65 |
| 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | IK03 | IP65 |
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | IK03 | IP65 |

GreenPerform Highbay G5

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|---------------------------------------|------------------------------|-------------------------|
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | IK03 | IP65 |
| 911401528245 | BY698P G5 LED105/NW PSU WB GM | IK08 | IP65 |
| 911401528345 | BY698P G5 LED105/NW PSU NB GM | IK08 | IP65 |
| 911401528445 | BY698P G5 LED105/CW PSU WB GM | IK08 | IP65 |
| 911401528545 | BY698P G5 LED105/CW PSU NB GM | IK08 | IP65 |
| 911401528645 | BY698P G5 LED150/NW PSU WB GM | IK08 | IP65 |
| 911401528745 | BY698P G5 LED150/NW PSU NB GM | IK08 | IP65 |
| 911401528845 | BY698P G5 LED150/CW PSU WB GM | IK08 | IP65 |
| 911401528945 | BY698P G5 LED150/CW PSU NB GM | IK08 | IP65 |
| 911401529045 | BY698P G5 LED200/NW PSU WB GM | IK08 | IP65 |
| 911401529145 | BY698P G5 LED200/NW PSU NB GM | IK08 | IP65 |
| 911401529245 | BY698P G5 LED200/CW PSU WB GM | IK08 | IP65 |
| 911401529345 | BY698P G5 LED200/CW PSU NB GM | IK08 | IP65 |
| 911401529445 | BY698P G5 LED250/NW PSU WB GM | IK08 | IP65 |
| 911401529545 | BY698P G5 LED250/NW PSU NB GM | IK08 | IP65 |
| 911401529645 | BY698P G5 LED250/CW PSU WB GM | IK08 | IP65 |
| 911401529745 | BY698P G5 LED250/CW PSU NB GM | IK08 | IP65 |
| 911401529845 | BY698P G5 LED300/NW PSU WB GM | IK08 | IP65 |
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | IK08 | IP65 |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | IK08 | IP65 |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | IK08 | IP65 |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | IK08 | IP65 |
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | IK08 | IP65 |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | IK08 | IP65 |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | IK08 | IP65 |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | IK08 | IP65 |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | IK08 | IP65 |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | IK08 | IP65 |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | IK08 | IP65 |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | IK08 | IP65 |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | IK08 | IP65 |

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-----------------------------------|------------------------------|-------------------------|
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | IK08 | IP65 |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | IK08 | IP65 |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | IK08 | IP65 |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | IK08 | IP65 |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | IK08 | IP65 |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | IK08 | IP65 |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | IK08 | IP65 |
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | IK08 | IP65 |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | IK08 | IP65 |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | IK08 | IP65 |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | IK08 | IP65 |
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | IK08 | IP65 |
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | IK08 | IP65 |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | IK08 | IP65 |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | IK08 | IP65 |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | IK08 | IP65 |
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | IK08 | IP65 |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | IK08 | IP65 |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | IK08 | IP65 |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | IK08 | IP65 |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | IK08 | IP65 |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | IK08 | IP65 |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | IK08 | IP65 |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | IK08 | IP65 |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | IK08 | IP65 |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | IK08 | IP65 |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | IK08 | IP65 |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | IK08 | IP65 |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | IK08 | IP65 |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | IK08 | IP65 |

GreenPerform Highbay G5

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|-------------------------------------|------------------------------|-------------------------|
| 911401541745 | BY690P LED105/NW PSU WB GM | IK08 | IP66 |
| 911401541845 | BY690P LED105/CW PSU WB GM | IK08 | IP66 |
| 911401541945 | BY690P LED150/NW PSU WB GM | IK08 | IP66 |
| 911401542045 | BY690P LED150/CW PSU WB GM | IK08 | IP66 |
| 911401542145 | BY690P LED200/NW PSU WB GM | IK08 | IP66 |
| 911401542245 | BY690P LED200/CW PSU WB GM | IK08 | IP66 |
| 911401542345 | BY690P LED250/NW PSU WB GM | IK08 | IP66 |
| 911401542445 | BY690P LED250/CW PSU WB GM | IK08 | IP66 |
| 911401542545 | BY690P LED300/NW PSU WB GM | IK08 | IP66 |
| 911401542645 | BY690P LED300/CW PSU WB GM | IK08 | IP66 |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | IK05 | IP65 |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | IK05 | IP65 |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | IK05 | IP65 |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | IK05 | IP65 |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | IK05 | IP65 |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | IK05 | IP65 |
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | IK05 | IP65 |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | IK05 | IP65 |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | IK05 | IP65 |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | IK05 | IP65 |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | IK05 | IP65 |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | IK05 | IP65 |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | IK05 | IP65 |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | IK05 | IP65 |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | IK05 | IP65 |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | IK05 | IP65 |

| Order Code | Full Product Name | Mech. impact protection code | Ingress protection code |
|--------------|--------------------------------------|------------------------------|-------------------------|
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | IK06 | IP65 |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | IK06 | IP65 |
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | IK06 | IP65 |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | IK06 | IP65 |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | IK06 | IP65 |
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | IK06 | IP65 |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | IK06 | IP65 |
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | IK06 | IP65 |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | IK06 | IP65 |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | IK06 | IP65 |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | IK06 | IP65 |
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | IK06 | IP65 |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | IK06 | IP65 |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | IK06 | IP65 |
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | IK06 | IP65 |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | IK06 | IP65 |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | IK06 | IP65 |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | IK06 | IP65 |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | IK06 | IP65 |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | IK06 | IP65 |

Approval and Application

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test |
|--------------|-----------------------------------|---------------------------|-----------------------------------|
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test |
|--------------|-----------------------------------|---------------------------|-----------------------------------|
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |

GreenPerform Highbay G5

| Order Code | Full Product Name | Ambient | |
|--------------|--|-------------------|--------------------------------------|
| | | temperature range | Glow-wire test |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |

| Order Code | Full Product Name | Ambient | |
|---------------|--|-------------------|--------------------------------------|
| | | temperature range | Glow-wire test |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 9114015528245 | BY698P G5 LED105/NW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528345 | BY698P G5 LED105/NW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528445 | BY698P G5 LED105/CW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528545 | BY698P G5 LED105/CW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528645 | BY698P G5 LED150/NW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528745 | BY698P G5 LED150/NW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528845 | BY698P G5 LED150/CW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015528945 | BY698P G5 LED150/CW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529045 | BY698P G5 LED200/NW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529145 | BY698P G5 LED200/NW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529245 | BY698P G5 LED200/CW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529345 | BY698P G5 LED200/CW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529445 | BY698P G5 LED250/NW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529545 | BY698P G5 LED250/NW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529645 | BY698P G5 LED250/CW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529745 | BY698P G5 LED250/CW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 9114015529845 | BY698P G5 LED300/NW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |

GreenPerform Highbay G5

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test |
|--------------|-----------------------------------|---------------------------|-----------------------------------|
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test |
|--------------|-----------------------------------|---------------------------|-----------------------------------|
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401541745 | BY690P LED105/NW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401541845 | BY690P LED105/CW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401541945 | BY690P LED150/NW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542045 | BY690P LED150/CW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542145 | BY690P LED200/NW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542245 | BY690P LED200/CW PSU WB GM | -40 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542345 | BY690P LED250/NW PSU WB GM | -35 °C to 50 °C | Temperature 650 °C, duration 30 s |

GreenPerform Highbay G5

| Order Code | Full Product Name | Ambient | |
|--------------|-------------------------------------|-------------------|-----------------------------------|
| | | temperature range | Glow-wire test |
| 911401542445 | BY690P LED250/CW PSU WB GM | -35 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542545 | BY690P LED300/NW PSU WB GM | -35 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401542645 | BY690P LED300/CW PSU WB GM | -35 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | -30 °C to 50 °C | Temperature 650 °C, duration 30 s |
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |

| Order Code | Full Product Name | Ambient | |
|--------------|--------------------------------------|-------------------|-----------------------------------|
| | | temperature range | Glow-wire test |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | -30 to +50 °C | Temperature 750 °C, duration 30 s |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial chromaticity | Luminous flux |
|--------------|-----------------------------------|--------------------------|---------------|
| | | | tolerance |
| 911401549545 | BY698X G5 LED105/NW L1W PIR WB GC | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401549645 | BY698X G5 LED105/CW L1W PIR WB GC | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401549745 | BY698X G5 LED150/NW L1W PIR WB GC | (0.386, 0.384) SDCM<5 | +/-10% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux |
|--------------|-----------------------------------|--------------------------|---------------|
| | | | tolerance |
| 911401549845 | BY698X G5 LED150/CW L1W PIR WB GC | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401549945 | BY698X G5 LED200/NW L1W PIR WB GC | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401550045 | BY698X G5 LED200/CW L1W PIR WB GC | (0.317, 0.338) SDCM<5 | +/-10% |

GreenPerform Highbay G5

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|--|--------------------------|-------------------------|
| 911401550145 | BY698X G5 LED250/NW L1W PIR WB GC | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401550245 | BY698X G5 LED250/CW L1W PIR WB GC | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401550345 | BY698X G5 LED300/NW L1W PIR WB GC | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401550445 | BY698X G5 LED300/CW L1W PIR WB GC | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401550545 | BY698X G5 LED105/NW L1W PIR WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401550645 | BY698X G5 LED105/CW L1W PIR WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401550745 | BY698X G5 LED150/NW L1W PIR WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401550845 | BY698X G5 LED150/CW L1W PIR WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401550945 | BY698X G5 LED200/NW L1W PIR WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401551045 | BY698X G5 LED200/CW L1W PIR WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401551145 | BY698X G5 LED250/NW L1W PIR WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401551245 | BY698X G5 LED250/CW L1W PIR WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401551345 | BY698X G5 LED300/NW L1W PIR WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401551445 | BY698X G5 LED300/CW L1W PIR WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401551545 | BY698X G5 LED105/840 L1W PIR WB CAU | - | +/-10% |
| 911401551645 | BY698X G5 LED150/840 L1W PIR WB CAU | - | +/-10% |
| 911401551745 | BY698X G5 LED200/840 L1W PIR WB CAU | - | +/-10% |
| 911401551845 | BY698X G5 LED250/840 L1W PIR WB CAU | - | +/-10% |
| 911401551945 | BY698X G5 LED300/840 L1W PIR WB CAU | - | +/-10% |
| 911401552045 | BY698X G5 LED105/NW L1W PIR WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401552145 | BY698X G5 LED105/CW L1W PIR WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401552245 | BY698X G5 LED150/NW L1W PIR WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401552345 | BY698X G5 LED150/CW L1W PIR WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401552445 | BY698X G5 LED200/NW L1W PIR WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401552545 | BY698X G5 LED200/CW L1W PIR WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|--|--------------------------|-------------------------|
| 911401552645 | BY698X G5 LED250/NW L1W PIR WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401552745 | BY698X G5 LED250/CW L1W PIR WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401552845 | BY698X G5 LED300/NW L1W PIR WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401552945 | BY698X G5 LED300/CW L1W PIR WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401528245 | BY698P G5 LED105/NW PSU WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401528345 | BY698P G5 LED105/NW PSU NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401528445 | BY698P G5 LED105/CW PSU WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401528545 | BY698P G5 LED105/CW PSU NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401528645 | BY698P G5 LED150/NW PSU WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401528745 | BY698P G5 LED150/NW PSU NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401528845 | BY698P G5 LED150/CW PSU WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401528945 | BY698P G5 LED150/CW PSU NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401529045 | BY698P G5 LED200/NW PSU WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401529145 | BY698P G5 LED200/NW PSU NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401529245 | BY698P G5 LED200/CW PSU WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401529345 | BY698P G5 LED200/CW PSU NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401529445 | BY698P G5 LED250/NW PSU WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401529545 | BY698P G5 LED250/NW PSU NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401529645 | BY698P G5 LED250/CW PSU WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401529745 | BY698P G5 LED250/CW PSU NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401529845 | BY698P G5 LED300/NW PSU WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401529945 | BY698P G5 LED300/NW PSU NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401530045 | BY698P G5 LED300/CW PSU WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401530145 | BY698P G5 LED300/CW PSU NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401533145 | BY698P G5 LED105/NW PSD WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |

GreenPerform Highbay G5

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|-----------------------------------|--------------------------|-------------------------|
| 911401533245 | BY698P G5 LED105/NW PSD NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401533345 | BY698P G5 LED105/CW PSD WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401533445 | BY698P G5 LED105/CW PSD NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401533545 | BY698P G5 LED150/NW PSD WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401533645 | BY698P G5 LED150/NW PSD NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401533745 | BY698P G5 LED150/CW PSD WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401533845 | BY698P G5 LED150/CW PSD NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401533945 | BY698P G5 LED200/NW PSD WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534045 | BY698P G5 LED200/NW PSD NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534145 | BY698P G5 LED200/CW PSD WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401534245 | BY698P G5 LED200/CW PSD NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401534345 | BY698P G5 LED250/NW PSD WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534445 | BY698P G5 LED250/NW PSD NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534545 | BY698P G5 LED250/CW PSD WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401534645 | BY698P G5 LED250/CW PSD NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401534745 | BY698P G5 LED300/NW PSD WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534845 | BY698P G5 LED300/NW PSD NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401534945 | BY698P G5 LED300/CW PSD WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401535045 | BY698P G5 LED300/CW PSD NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401538745 | BY698P G5 LED105/NW PSU WB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401538845 | BY698P G5 LED105/NW PSU NB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401538945 | BY698P G5 LED105/CW PSU WB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539045 | BY698P G5 LED105/CW PSU NB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539145 | BY698P G5 LED150/NW PSU WB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401539245 | BY698P G5 LED150/NW PSU NB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|-------------------------------------|--------------------------|-------------------------|
| 911401539345 | BY698P G5 LED150/CW PSU WB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539445 | BY698P G5 LED150/CW PSU NB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539545 | BY698P G5 LED200/NW PSU WB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401539645 | BY698P G5 LED200/NW PSU NB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401539745 | BY698P G5 LED200/CW PSU WB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539845 | BY698P G5 LED200/CW PSU NB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401539945 | BY698P G5 LED250/NW PSU WB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401540045 | BY698P G5 LED250/NW PSU NB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401540145 | BY698P G5 LED250/CW PSU WB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401540245 | BY698P G5 LED250/CW PSU NB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401540345 | BY698P G5 LED300/NW PSU WB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401540445 | BY698P G5 LED300/NW PSU NB GM L3m | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401540545 | BY698P G5 LED300/CW PSU WB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401540645 | BY698P G5 LED300/CW PSU NB GM L3m | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401541745 | BY690P LED105/NW PSU WB GM | - | -10% / +10% |
| 911401541845 | BY690P LED105/CW PSU WB GM | - | -10% / +10% |
| 911401541945 | BY690P LED150/NW PSU WB GM | - | -10% / +10% |
| 911401542045 | BY690P LED150/CW PSU WB GM | - | -10% / +10% |
| 911401542145 | BY690P LED200/NW PSU WB GM | - | -10% / +10% |
| 911401542245 | BY690P LED200/CW PSU WB GM | - | -10% / +10% |
| 911401542345 | BY690P LED250/NW PSU WB GM | - | -10% / +10% |
| 911401542445 | BY690P LED250/CW PSU WB GM | - | -10% / +10% |
| 911401542545 | BY690P LED300/NW PSU WB GM | - | -10% / +10% |
| 911401542645 | BY690P LED300/CW PSU WB GM | - | -10% / +10% |
| 911401544245 | BY698X G5 LED150/NW Connected WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401544345 | BY698X G5 LED150/NW Connected NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401544445 | BY698X G5 LED150/CW Connected WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401544545 | BY698X G5 LED150/CW Connected NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401544645 | BY698X G5 LED200/NW Connected WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401544745 | BY698X G5 LED200/NW Connected NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |

GreenPerform Highbay G5

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|--|--------------------------|-------------------------|
| 911401544845 | BY698X G5 LED200/CW Connected WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401544945 | BY698X G5 LED200/CW Connected NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401545045 | BY698X G5 LED250/NW Connected WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401545145 | BY698X G5 LED250/NW Connected NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401545245 | BY698X G5 LED250/CW Connected WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401545345 | BY698X G5 LED250/CW Connected NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401545445 | BY698X G5 LED300/NW Connected WB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401545545 | BY698X G5 LED300/NW Connected NB GM | (0.386, 0.384) SDCM<5 | -10% / +10% |
| 911401545645 | BY698X G5 LED300/CW Connected WB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401545745 | BY698X G5 LED300/CW Connected NB GM | (0.317, 0.338) SDCM<5 | -10% / +10% |
| 911401547545 | BY698X G5 LED105/NW L1W MW WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401547645 | BY698X G5 LED105/CW L1W MW WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401547745 | BY698X G5 LED150/NW L1W MW WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401547845 | BY698X G5 LED150/CW L1W MW WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401547945 | BY698X G5 LED200/NW L1W MW WB GM | (0.386, 0.384) SDCM<5 | +/-10% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|--------------|---|--------------------------|-------------------------|
| 911401548045 | BY698X G5 LED200/CW L1W MW WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401548145 | BY698X G5 LED250/NW L1W MW WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401548245 | BY698X G5 LED250/CW L1W MW WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401548345 | BY698X G5 LED300/NW L1W MW WB GM | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401548445 | BY698X G5 LED300/CW L1W MW WB GM | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401548545 | BY698X G5 LED105/NW L1W MW WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401548645 | BY698X G5 LED105/CW L1W MW WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401548745 | BY698X G5 LED150/NW L1W MW WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401548845 | BY698X G5 LED150/CW L1W MW WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401548945 | BY698X G5 LED200/NW L1W MW WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401549045 | BY698X G5 LED200/CW L1W MW WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401549145 | BY698X G5 LED250/NW L1W MW WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401549245 | BY698X G5 LED250/CW L1W MW WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |
| 911401549345 | BY698X G5 LED300/NW L1W MW WB GM L3m | (0.386, 0.384) SDCM<5 | +/-10% |
| 911401549445 | BY698X G5 LED300/CW L1W MW WB GM L3m | (0.317, 0.338) SDCM<5 | +/-10% |

