



Pengontrol beban melakukan pekerjaan berat dalam sistem kontrol

Pengontrol Beban Dynalite

Pengendali beban menerima instruksi dari jaringan dan menyesuaikan keluaran yang dikontrol sebagaimana diperlukan. Mereka berisi semua elemen – catu daya, port jaringan, sirkuit keluaran, dan manajemen mikroprosesor – yang diperlukan untuk mengoperasikan kelompok pencahayaan yang menjadi tanggung jawabnya. Semua informasi penamaan saluran, pengalamatan saluran, pengalamatan area, dan tingkat adegan saluran disimpan dalam memori pengontrol beban. Dynalite memiliki berbagai pengontrol beban yang dapat dicampur dan disesuaikan untuk mendukung berbagai persyaratan proyek dan berbagai jenis lumener. Rangkaian pengontrol beban dilengkapi berbagai jenis sirkuit keluaran untuk pengalihan, peredupan tepi depan/belakang, peredupan PWM, DALI, dan kontrol 0-10 V. Pengontrol menawarkan berbagai kapasitas saluran dari 2-20A, serta pilihan pemasangan di dinding atau rel DIN.

Application

- Industri
- Fasilitas pendidikan
- Layanan kesehatan
- Retail
- Hospitality (hotel, restoran, kafe)

Pengontrol Beban Dynalite

Versions



DDLEDC605GL Product Image



DDBC516FR Product Image



DMBC110 Product Image



DDBC120-DALI Product Image



DDMC802 Product Image



DBC905W Product Image




DMC4 Product Image









DMC2 Product Image

Dimensional drawing



Pengontrol Beban Dynalite


Dimensional drawing



Product details




Front of the DBC905 9 x 5A
EcoLinux Signal Dimmer Controller



DDBC516FR 5 x 16A Signal Dimmer
Controller front

Pengontrol Beban Dynalite

Product details



DMC2 Multipurpose Modular
Controller - Front



DMC2 Multipurpose Modular
Controller - exploded view



DMC2 Multipurpose Modular
Controller - open



DMC4-CE Multipurpose Modular
Controller - exploded view



DMC4-CE Multipurpose Modular
Controller - front



DMC4 Complete BottomOpen
Front



DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 BottomClose




DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 BottomOpen

Pengontrol Beban Dynalite

Product details




DMC4 DSM4 DMR316 DMD316
DMR610 DMP603




DMC4 DSM4 DMR316 DMD316
DMR610 DMP603 Front



DMC4 DSM4 DMR316 DMD316
DMR610 Front



DMC4 DSM4 DMR316 DMD316



DMC4 DSM4 DMR316



DMC4 DSM4 DMR316 Front



DMC4 DSM4 Front



DMC4 Empty BottomOpen

Pengontrol Beban Dynalite

Product details

DMC4 UL BS



DMC4 UL Empty



DMC4 UL Empty Front




DDBC120-DALI MultiMaster DALI Driver Controller



Detail photo of the DDLEDC605-GL



DDMC802 front detail



Detail photo of the DMBC110



Pengontrol Beban Dynalite

