



Low mercury, energy savings.

PL-T Triple 4-Pin Base

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Benefits

- Extend your relamp cycles and reduce your maintenance costs with 12,000 hours rated average life (3 hrs per start) and 20,000 hours rated average life (12 hrs per start).
- Better for the environment - only 1.4 mg of mercury per lamp.
- More design flexibility - 25% shorter than PL-C lamps.

Features

- Temperature-independent lamp
- Extended relamping cycles
- Dimmable for application flexibility and energy savings
- More design flexibility
- Better for the environment
- Available in 18,26,32,42, and 57 watts with 2700,3000,3500,and 4100 color temperatures

Application

- Ideal for downlights in offices, hotels and retail environments

PL-T Triple 4-Pin Base

Versions






LPPR PLTTOP4P 57W



LPPR PLTTOP4P 18W

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 18W/835/A/4P 1CT/5X10BOX ALTO	41 mm	71.7 mm	96.0 mm	111.7 mm

Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/827/A/4P 1CT/5X10BOX ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm
PL-T 26W/830/A/4P 1CT/5X10BOX ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm
PL-T 26W/835/A/4P 1CT/5X10BOX ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm
PL-T 26W/841/A/4P 1CT/5X10BOX ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm
PL-T 32W/830/A/4P 1CT/5X10BOX ALTO	41 mm	98.7 mm	123.0 mm	138.7 mm
PL-T 32W/835/A/4P 1CT/5X10BOX ALTO	41 mm	98.7 mm	123.0 mm	138.7 mm
PL-T 32W/841/A/4P 1CT/5X10BOX ALTO	41 mm	98.7 mm	123.0 mm	138.7 mm

Product	D (max)	A (max)	B (max)	C (max)
PL-T 42W/830/A/4P 1CT/5X10BOX ALTO	41 mm	120.7 mm	145.0 mm	160.7 mm
PL-T 42W/835/A/4P 1CT/5X10BOX ALTO	41 mm	120.7 mm	145.0 mm	160.7 mm
PL-T 42W/841/A/4P 1CT/5X10BOX ALTO	41 mm	120.7 mm	145.0 mm	160.7 mm

PL-T Triple 4-Pin Base

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
PL-T 57W/835/A/4P 1CT/5X10BOX ALTO	41 mm	157.7 mm	182.0 mm	197.7 mm
PL-T 57W/841/A/4P 1CT/5X10BOX ALTO	41 mm	157.7 mm	182.0 mm	197.7 mm

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Mercury (Hg) Content (Nom)	1.4 mg
----------------------------	--------

General Information

Order Code	Full Product Name	Cap-Base	Order Code	Full Product Name	Cap-Base
927911083050	PL-T 32W/830/A/4P 1CT/5X10BOX ALTO	GX24q-3	927914084020	PL-T 57W/841/A/4P 1CT/5X10BOX ALTO	GX24q-5
927911083550	PL-T 32W/835/A/4P 1CT/5X10BOX ALTO	GX24q-3	927910583550	PL-T 18W/835/A/4P 1CT/5X10BOX ALTO	GX24q-2
927911084150	PL-T 32W/841/A/4P 1CT/5X10BOX ALTO	GX24q-3	927910982750	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO	GX24q-3
927911483020	PL-T 42W/830/A/4P 1CT/5X10BOX ALTO	GX24q-4	927910983050	PL-T 26W/830/A/4P 1CT/5X10BOX ALTO	GX24q-3
927911483520	PL-T 42W/835/A/4P 1CT/5X10BOX ALTO	GX24q-4	927910983550	PL-T 26W/835/A/4P 1CT/5X10BOX ALTO	GX24q-3
927911484120	PL-T 42W/841/A/4P 1CT/5X10BOX ALTO	GX24q-4	927910984150	PL-T 26W/841/A/4P 1CT/5X10BOX ALTO	GX24q-3
927914083520	PL-T 57W/835/A/4P 1CT/5X10BOX ALTO	GX24q-5			

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (Rated) (Min)	Luminous Efficacy (rated) (Nom)	Luminous Flux
927911083050	PL-T 32W/830/A/4P 1CT/5X10BOX ALTO	Warm White (WW)	3000 K	>80	-	68.2 lm/W	2,250 lm
927911083550	PL-T 32W/835/A/4P 1CT/5X10BOX ALTO	White (WH)	3500 K	82	-	68.2 lm/W	2,250 lm
927911084150	PL-T 32W/841/A/4P 1CT/5X10BOX ALTO	Cool White (CW)	4100 K	80	-	68.2 lm/W	2,250 lm
927911483020	PL-T 42W/830/A/4P 1CT/5X10BOX ALTO	Warm White (WW)	3000 K	>80	80 lm/W	-	3,200 lm
927911483520	PL-T 42W/835/A/4P 1CT/5X10BOX ALTO	White (WH)	3500 K	82	80 lm/W	-	3,200 lm
927911484120	PL-T 42W/841/A/4P 1CT/5X10BOX ALTO	Cool White (CW)	4100 K	82	80 lm/W	-	3,200 lm
927914083520	PL-T 57W/835/A/4P 1CT/5X10BOX ALTO	White (WH)	3500 K	82	76 lm/W	-	4,300 lm
927914084020	PL-T 57W/841/A/4P 1CT/5X10BOX ALTO	Cool White (CW)	4100 K	82	76 lm/W	-	4,300 lm
927910583550	PL-T 18W/835/A/4P 1CT/5X10BOX ALTO	White (WH)	3500 K	82	-	65.3 lm/W	1,175 lm
927910982750	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO	Incandescent White	2700 K	82	-	64.8 lm/W	1,750 lm
927910983050	PL-T 26W/830/A/4P 1CT/5X10BOX ALTO	Warm White (WW)	3000 K	>80	-	64.8 lm/W	1,750 lm
927910983550	PL-T 26W/835/A/4P 1CT/5X10BOX ALTO	White (WH)	3500 K	82	-	64.8 lm/W	1,750 lm
927910984150	PL-T 26W/841/A/4P 1CT/5X10BOX ALTO	Cool White (CW)	4100 K	80	-	64.8 lm/W	1,750 lm

Operating and Electrical

PL-T Triple 4-Pin Base

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927911083050	PL-T 32W/830/A/4P 1CT/5X10BOX ALTO	0.320 A	33.0 W
927911083550	PL-T 32W/835/A/4P 1CT/5X10BOX ALTO	0.320 A	33.0 W
927911084150	PL-T 32W/841/A/4P 1CT/5X10BOX ALTO	0.320 A	32 W
927911483020	PL-T 42W/830/A/4P 1CT/5X10BOX ALTO	0.320 A	38.0 W
927911483520	PL-T 42W/835/A/4P 1CT/5X10BOX ALTO	0.320 A	38.0 W
927911484120	PL-T 42W/841/A/4P 1CT/5X10BOX ALTO	0.320 A	38.0 W
927914083520	PL-T 57W/835/A/4P 1CT/5X10BOX ALTO	0.320 A	51.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927914084020	PL-T 57W/841/A/4P 1CT/5X10BOX ALTO	0.320 A	51.0 W
927910583550	PL-T 18W/835/A/4P 1CT/5X10BOX ALTO	0.225 A	18.0 W
927910982750	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO	0.335 A	27.0 W
927910983050	PL-T 26W/830/A/4P 1CT/ 5X10BOX ALTO	0.335 A	26 W
927910983550	PL-T 26W/835/A/4P 1CT/5X10BOX ALTO	0.335 A	27.0 W
927910984150	PL-T 26W/841/A/4P 1CT/5X10BOX ALTO	0.335 A	27.0 W

