



For your everyday lighting jobs, CorePro LEDspot mv is the perfect fit for spot lighting GU10 and deliver warm halogen-like light

CorePro LED spot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs

CorePro LED spot MV

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Contain no mercury and hazardous materials – RoHS compliant

Application

- Hospitality
- Retail
- Residential

Versions



CLA LEDspotMV ND 5W PAR16 GU10




LEDspot 50W GU10 PAR16 827-865 36D ND




LEDspots switch EU PAR16 GU11

CorePro LED spot MV

Dimensional drawing






Product	D	C
CorePro LEDspot 3-35W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 mm	54 mm
CoreProLEDspot 4-50W GU10 827 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 830 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 840 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 865 36D DIM UK	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 827 36D	50 mm	53 mm
Corepro LEDspot 2.7-25W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D UK	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D UK	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D UK	50 mm	54 mm
Essential LED 4.6-50W GU10 865 36D	50 mm	54 mm



Product	D	C
LEDspot GU10 50W 830 36D 6CT	50 mm	54 mm

CorePro LED spot MV

Dimensional drawing



Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D ND	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 840 36D ND	50 mm	54 mm
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

Product	D	C
CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	50 mm	61.5 mm

Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

General Information

Cap-Base GU10

Light Technical

Color rendering index (CRI) 80

LLMF At End Of Nominal Lifetime (Nom) 70 %

Operating and Electrical

Input Frequency 50 to 60 Hz

Starting Time (Nom) 0.5 s

Mechanical and Housing

Bulb Shape PAR16

General Information

CorePro LED spot MV

Order Code	Full Product Name	Switching Cycle	Nominal lifetime	Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	50,000	15,000 hour(s)	929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	50,000	15,000 hour(s)
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	50,000	15,000 hour(s)	929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	50,000	15,000 hour(s)
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	50,000	15,000 hour(s)	929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	50,000	15,000 hour(s)
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	50,000	15,000 hour(s)	929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	50,000	15,000 hour(s)
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	50,000	15,000 hour(s)	929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	50,000	15,000 hour(s)
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	50,000	15,000 hour(s)	929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	50,000	15,000 hour(s)
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	50,000	15,000 hour(s)	929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	50,000	15,000 hour(s)
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50,000	15,000 hour(s)	929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	50,000	15,000 hour(s)
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	50,000	15,000 hour(s)	929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	50,000	15,000 hour(s)
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	50,000	15,000 hour(s)	929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	50,000	15,000 hour(s)
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	50,000	15,000 hour(s)	929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	50,000	15,000 hour(s)
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	50,000	15,000 hour(s)	929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	50,000	15,000 hour(s)
929002981202	Corepro LEDspot 550lm GU10 830 120D	50,000	15,000 hour(s)	929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	50,000	15,000 hour(s)
929002981302	Corepro LEDspot 550lm GU10 840 120D	50,000	15,000 hour(s)	929001218308	Essential LED 4.6-50W GU10 865 36D	50,000	15,000 hour(s)
929002981402	Corepro LEDspot 550lm GU10 865 120D	50,000	15,000 hour(s)	929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	50,000	15,000 hour(s)
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	50,000	15,000 hour(s)	929003132390	LEDspot GU10 50W 830 36D 6CT	15,000	15,000 hour(s)
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	50,000	15,000 hour(s)	929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	50,000	15,000 hour(s)
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	50,000	15,000 hour(s)	929002466702	Corepro LEDspot 670lm GU10 830 60D	50,000	25,000 hour(s)
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	50,000	15,000 hour(s)	929002466802	Corepro LEDspot 730lm GU10 840 60D	50,000	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature		Color Code	Luminous Flux	Luminous Intensity (Nom)
		Beam Angle (Nom)	(Nom)			
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	36 degree(s)	4000 K	840	240 lm	500 cd
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	36 degree(s)	3000 K	830	230 lm	500 cd
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	36 degree(s)	2700 K	827	230 lm	500 cd
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	36 degree(s)	2700 K	827	345 lm	700 cd
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	36 degree(s)	2700 K	827	345 lm	700 cd
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	36 degree(s)	6500 K	865	345 lm	700 cd
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	36 degree(s)	2700 K	827	355 lm	700 cd
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	36 degree(s)	2700 K	827	355 lm	700 cd

CorePro LED spot MV

Order Code	Full Product Name	Correlated Color Temperature		Color Code	Luminous Flux	Luminous Intensity (Nom)
		Beam Angle (Nom)	(Nom)			
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	36 degree(s)	2700 K	827	355 lm	700 cd
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	36 degree(s)	2700 K	827	215 lm	470 cd
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	36 degree(s)	2700 K	827	255 lm	545 cd
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	36 degree(s)	2700 K	827	255 lm	545 cd
929002981202	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm	-
929002981302	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm	-
929002981402	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm	-
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	36 degree(s)	4000 K	840	350 lm	700 cd
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	36 degree(s)	4000 K	840	350 lm	700 cd
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	36 degree(s)	3000 K	830	345 lm	700 cd
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	36 degree(s)	3000 K	830	345 lm	700 cd
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	36 degree(s)	3000 K	830	460 lm	800 cd
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	36 degree(s)	4000 K	840	485 lm	800 cd
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	36 degree(s)	3000 K	830	225 lm	490 cd
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	36 degree(s)	4000 K	840	230 lm	500 cd
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	36 degree(s)	3000 K	830	265 lm	565 cd
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	36 degree(s)	3000 K	830	265 lm	565 cd
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	36 degree(s)	4000 K	840	275 lm	590 cd
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	36 degree(s)	4000 K	840	275 lm	590 cd
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K	830	370 lm	740 cd
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	36 degree(s)	3000 K	830	370 lm	740 cd
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	36 degree(s)	4000 K	840	390 lm	770 cd
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	36 degree(s)	4000 K	840	390 lm	770 cd
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	390 lm	770 cd
929001218308	Essential LED 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	430 lm	770 cd
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	36 degree(s)	6500 K	865	390 lm	770 cd
929003132390	LEDspot GU10 50W 830 36D 6CT	36 degree(s)	3000 K	830	345 lm	700 cd
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	36 degree(s)	2700 K	2700/3000/4000	360 lm	550 cd
929002466702	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm	750 cd
929002466802	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm	750 cd

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	50 to 60 Hz	3 W	35 W	929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	50 to 60 Hz	4 W	50 W
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	50 to 60 Hz	3 W	35 W	929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	50 to 60 Hz	4.6 W	50 W
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	50 to 60 Hz	3 W	35 W	929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 to 60 Hz	4.6 W	50 W
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	50 to 60 Hz	4 W	50 W	929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	50 to 60 Hz	4.6 W	50 W
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	50 to 60 Hz	4 W	50 W	929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	50 to 60 Hz	2.7 W	25 W
					929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	50 to 60 Hz	3.5 W	35 W

CorePro LED spot MV

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	50 to 60 Hz	3.5 W	35 W
929002981202	Corepro LEDspot 550lm GU10 830 120D	50 to 60 Hz	4.9 W	-
929002981302	Corepro LEDspot 550lm GU10 840 120D	50 to 60 Hz	4.9 W	-
929002981402	Corepro LEDspot 550lm GU10 865 120D	50 to 60 Hz	4.9 W	-
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	50 to 60 Hz	4 W	50 W
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	50 to 60 Hz	4 W	50 W
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	50 to 60 Hz	4 W	50 W
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	50 to 60 Hz	4 W	50 W
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	50 to 60 Hz	4.9 W	65 W
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	50 to 60 Hz	4.9 W	65 W
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	50 to 60 Hz	2.7 W	25 W
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	50 to 60 Hz	2.7 W	25 W
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	50 to 60 Hz	3.5 W	35 W
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	50 to 60 Hz	3.5 W	35 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	50 to 60 Hz	3.5 W	35 W
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	50 to 60 Hz	3.5 W	35 W
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	50 to 60 Hz	4.6 W	50 W
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	50 to 60 Hz	4.6 W	50 W
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	50 to 60 Hz	4.6 W	50 W
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	50 to 60 Hz	4.6 W	50 W
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	50 to 60 Hz	4.6 W	50 W
929001218308	Essential LED 4.6-50W GU10 865 36D	50 to 60 Hz	4.6 W	50 W
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	50 to 60 Hz	4.6 W	50 W
929003132390	LEDspot GU10 50W 830 36D 6CT	50 to 60 Hz	4.7 W	50 W
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	-	4.8 W	50 W
929002466702	Corepro LEDspot 670lm GU10 830 60D	50 to 60 Hz	6.7 W	90 W
929002466802	Corepro LEDspot 730lm GU10 840 60D	50 to 60 Hz	6.7 W	100 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	55 °C
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	65 °C
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	65 °C
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	70 °C
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	70 °C
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	70 °C
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	72 °C
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	72 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	80 °C
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	50 °C
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	65 °C
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	75 °C
929002981202	Corepro LEDspot 550lm GU10 830 120D	85 °C
929002981302	Corepro LEDspot 550lm GU10 840 120D	85 °C
929002981402	Corepro LEDspot 550lm GU10 865 120D	85 °C
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	70 °C

CorePro LED spot MV

Order Code	Full Product Name	T-Case Maximum (Nom)
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	70 °C
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	70 °C
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	70 °C
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	85 °C
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	85 °C
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	50 °C
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	50 °C
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	65 °C
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	75 °C
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	65 °C
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	72 °C
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	80 °C
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	72 °C
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	80 °C
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	72 °C
929001218308	Essential LED 4.6-50W GU10 865 36D	80 °C
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	80 °C
929003132390	LEDspot GU10 50W 830 36D 6CT	75 °C
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	60 °C
929002466702	Corepro LEDspot 670lm GU10 830 60D	75 °C
929002466802	Corepro LEDspot 730lm GU10 840 60D	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	Only with specific dimmers
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	Only with specific dimmers
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	Only with specific dimmers
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	Only with specific dimmers
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	Only with specific dimmers
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	Only with specific dimmers
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	No
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	No
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	No
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	No
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	No
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	No
929002981202	Corepro LEDspot 550lm GU10 830 120D	No
929002981302	Corepro LEDspot 550lm GU10 840 120D	No
929002981402	Corepro LEDspot 550lm GU10 865 120D	No
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	Only with specific dimmers
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	Only with specific dimmers
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	Only with specific dimmers
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	No
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	No
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	No
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	No
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	No
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	No
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	No
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	No
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	No
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	No
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	No
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	No
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	No
929001218308	Essential LED 4.6-50W GU10 865 36D	No
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	No
929003132390	LEDspot GU10 50W 830 36D 6CT	No
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Only with specific dimmers
929002466702	Corepro LEDspot 670lm GU10 830 60D	No
929002466802	Corepro LEDspot 730lm GU10 840 60D	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	Clear
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	Clear
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	Clear
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	Clear
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	Clear
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	Clear

Order Code	Full Product Name	Bulb Finish
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	Clear
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	-
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	Clear
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	Clear
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	-

CorePro LED spot MV

Order Code	Full Product Name	Bulb Finish
929002981202	Corepro LEDspot 550lm GU10 830 120D	-
929002981302	Corepro LEDspot 550lm GU10 840 120D	-
929002981402	Corepro LEDspot 550lm GU10 865 120D	-
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	Clear
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	Clear
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	Clear
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	Clear
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	Clear
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	Clear
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	Clear
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	Clear
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	Clear
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	-

Order Code	Full Product Name	Bulb Finish
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	Clear
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	-
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	Clear
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	-
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	Clear
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	-
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	-
929001218308	Essential LED 4.6-50W GU10 865 36D	Clear
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	-
929003132390	LEDspot GU10 50W 830 36D 6CT	-
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Clear
929002466702	Corepro LEDspot 670lm GU10 830 60D	-
929002466802	Corepro LEDspot 730lm GU10 840 60D	-


Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	-20 to +45 °C	3 kWh
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	-20 to +45 °C	3 kWh
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	-20 to +45 °C	3 kWh
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	-20 to +45 °C	4 kWh
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	-20 to +45 °C	4 kWh
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	-20 to +45 °C	4 kWh
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	-20 to +45 °C	5 kWh
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-20 to +45 °C	5 kWh
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	-20 to +45 °C	5 kWh
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	-20 to +45 °C	3 kWh
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	-20 to +45 °C	4 kWh
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	-20 to +45 °C	4 kWh
929002981202	Corepro LEDspot 550lm GU10 830 120D	-20 to +45 °C	5 kWh
929002981302	Corepro LEDspot 550lm GU10 840 120D	-20 to +45 °C	5 kWh
929002981402	Corepro LEDspot 550lm GU10 865 120D	-20 to +45 °C	5 kWh
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	-20 to +45 °C	4 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	-20 to +45 °C	4 kWh
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	-20 to +45 °C	4 kWh
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	-20 to +45 °C	4 kWh
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	-20 to +45 °C	5 kWh
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	-20 to +45 °C	5 kWh
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	-20 to +45 °C	3 kWh
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	-20 to +45 °C	3 kWh
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	-20 to +45 °C	4 kWh
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	-20 to +45 °C	4 kWh
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	-20 to +45 °C	4 kWh
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	-20 to +45 °C	4 kWh
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	-20 to +45 °C	5 kWh
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	-20 to +45 °C	5 kWh
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	-20 to +45 °C	5 kWh
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	-20 to +45 °C	5 kWh
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	-20 to +45 °C	5 kWh

CorePro LED spot MV



Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001218308	Essential LED 4.6-50W GU10 865 36D	-20 °C to 45 °C	-
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	-20 to +45 °C	5 kWh
929003132390	LEDspot GU10 50W 830 36D 6CT	-20 to +45 °C	5 kWh
929004221002	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	-20 to +45 °C	5 kWh
929002466702	Corepro LEDspot 670lm GU10 830 60D	-20 to +45 °C	7 kWh
929002466802	Corepro LEDspot 730lm GU10 840 60D	-20 to +45 °C	7 kWh










90°

60°


CorePro LED spot MV




CorePro LED spot MV




Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND




Accent Diagram - CorePro LEDspot 4-50W GU10
865 36D DIM UK




Accent Diagram - CorePro LEDspot 2.7-25W
GU10 827 36D




Accent Diagram - CorePro LEDspot 3.5-35W
GU10 827 36D




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 827 36D UK




Accent Diagram - CorePro LEDspot 2.7-25W
GU10 840 36D



Accent Diagram - CorePro LEDspot 3.5-35W
GU10 830 36D




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 865 36D UK




Accent Diagram - CorePro LEDspot 4-50W
GU10 827 36D DIM


Accent Diagrams




Accent Diagram - CoreProLEDspot 4-50W GU10 840 36D DIM UK




Accent Diagram - CoreProLEDspot 4-50W GU10 830 36D DIM UK




Accent Diagram - CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM




Accent Diagram - CorePro LEDspot 3-35W GU10 830 36D DIM




Accent Diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Accent Diagram - Corepro LEDspot 730lm GU10 840 60D



Accent Diagram - Corepro LEDspot 670lm GU10 830 60D




Accent Diagram - LEDspot GU10 50W 830 36D 6CT




Accent Diagram - CorePro LEDspot 3-35W GU10 827 36D DIM

Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 840 36D ND


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10
840 36D DIM




Beam diagram - CorePro LEDspot 4.9-65W
GU10 840 36D ND




Beam diagram - Corepro LEDspot 2.7-25W GU10
827 36D



Beam diagram - Corepro LEDspot 3.5-35W
GU10 827 36D




Beam diagram - Corepro LEDspot 4.6-50W
GU10 827 36D UK




Beam diagram - Corepro LEDspot 2.7-25W GU10
840 36D


Beam Diagrams




Beam diagram - CorePro LEDspot 3.5-35W GU10 830 36D




Beam diagram - CorePro LEDspot 4.6-50W GU10 865 36D UK




Beam diagram - CorePro LEDspot 4-50W GU10 830 36D DIM UK




Beam diagram - CorePro LEDspot 4-50W GU10 840 36D DIM UK




Beam diagram - CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM




Beam diagram - CorePro LEDspot 730lm GU10 840 60D



Beam diagram - CorePro LEDspot 3-35W GU10 830 36D DIM




Beam diagram - LEDspot GU10 50W 830 36D 6CT




Beam diagram - CorePro LEDspot 4-50W GU10 827 36D DIM


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10
827 36D DIM



Beam diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND



Beam diagram - CorePro LEDspot 670lm GU10
830 60D



Beam diagram - CorePro LEDspot 4-50W GU10
865 36D DIM UK

