



# The affordable LEDspot solution

## CorePro LED spot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

### Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Free of mercury and hazardous materials

### Application

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets

# CorePro LED spot MV

## Versions





LEDspots switch EU PAR16 GU11



LEDspots MV PAR16 GU10

## Dimensional drawing





Product	D	C
CorePro LEDspot 3-35W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 827 36D	50 mm	53 mm
Corepro LEDspot 2.7-25W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm

Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D ND	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 840 36D ND	50 mm	54 mm
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

# CorePro LED spot MV

## Dimensional drawing



Product	D	C
CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	50 mm	61.5 mm

Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

### General Information

Cap-Base	GU10
Switching Cycle	50,000

### Light Technical

Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

### Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

### Mechanical and Housing

Bulb Shape	PAR16
------------	-------

### Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### General Information

Order Code	Full Product Name	Nominal lifetime
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	15,000 hour(s)
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	15,000 hour(s)
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	15,000 hour(s)
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	15,000 hour(s)
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	15,000 hour(s)
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	15,000 hour(s)
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	15,000 hour(s)
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	15,000 hour(s)
30875600	Corepro LEDspot 550lm GU10 830 120D	15,000 hour(s)
30865700	Corepro LEDspot 550lm GU10 840 120D	15,000 hour(s)
30867100	Corepro LEDspot 550lm GU10 865 120D	15,000 hour(s)
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	15,000 hour(s)
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	15,000 hour(s)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	15,000 hour(s)
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	15,000 hour(s)
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	15,000 hour(s)
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	15,000 hour(s)
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	15,000 hour(s)
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	15,000 hour(s)
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	15,000 hour(s)
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	15,000 hour(s)
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	15,000 hour(s)
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	15,000 hour(s)
81333101	Corepro LEDspot 670lm GU10 830 60D	25,000 hour(s)
81335501	Corepro LEDspot 730lm GU10 840 60D	25,000 hour(s)

# CorePro LED spot MV

## Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux
			Temperature (Nom)	Color Code	
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	36 degree(s)	4000 K	840	240 lm
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	36 degree(s)	3000 K	830	230 lm
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	36 degree(s)	2700 K	827	230 lm
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	36 degree(s)	2700 K	827	345 lm
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	36 degree(s)	2700 K	827	355 lm
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	36 degree(s)	2700 K	827	355 lm
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	36 degree(s)	2700 K	827	215 lm
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	36 degree(s)	2700 K	827	255 lm
30875600	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm
30865700	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm
30867100	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux
			Temperature (Nom)	Color Code	
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	36 degree(s)	4000 K	840	350 lm
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	36 degree(s)	3000 K	830	345 lm
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	36 degree(s)	3000 K	830	460 lm
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	36 degree(s)	4000 K	840	485 lm
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	36 degree(s)	3000 K	830	225 lm
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	36 degree(s)	4000 K	840	230 lm
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	36 degree(s)	3000 K	830	265 lm
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	36 degree(s)	4000 K	840	275 lm
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K	830	370 lm
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	36 degree(s)	4000 K	840	390 lm

## CorePro LED spot MV

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)		Luminous Flux
			Color	Color Code	
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	390 lm
36969600	CorePro LEDspot 4.8-50W	36 degree(s)	2700 K	2700/3000/4000	360 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)		Luminous Flux
			Color	Color Code	
	GU10 3CCT 36DDIM				
81333101	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm
81335501	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm

### Light Technical (2/2)

Order Code	Full Product Name	Luminous Intensity (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	500 cd
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	500 cd
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	500 cd
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	700 cd
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	700 cd
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	700 cd
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	470 cd
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	545 cd
30875600	Corepro LEDspot 550lm GU10 830 120D	-
30865700	Corepro LEDspot 550lm GU10 840 120D	-
30867100	Corepro LEDspot 550lm GU10 865 120D	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	700 cd
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	700 cd

Order Code	Full Product Name	Luminous Intensity (Nom)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	800 cd
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	800 cd
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	490 cd
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	500 cd
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	565 cd
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	590 cd
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	740 cd
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	770 cd
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	770 cd
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	550 cd
81333101	Corepro LEDspot 670lm GU10 830 60D	750 cd
81335501	Corepro LEDspot 730lm GU10 840 60D	750 cd

### Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	Wattage Equivalent
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	50 to 60 Hz	3 W	35 W
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	50 to 60 Hz	3 W	35 W
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	50 to 60 Hz	3 W	35 W
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	50 to 60 Hz	4 W	50 W
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	50 to 60 Hz	4.6 W	50 W

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	Wattage Equivalent
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 to 60 Hz	4.6 W	50 W
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	50 to 60 Hz	2.7 W	25 W
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	50 to 60 Hz	3.5 W	35 W
30875600	Corepro LEDspot 550lm GU10 830 120D	50 to 60 Hz	4.9 W	-
30865700	Corepro LEDspot 550lm GU10 840 120D	50 to 60 Hz	4.9 W	-
30867100	Corepro LEDspot 550lm GU10 865 120D	50 to 60 Hz	4.9 W	-

## CorePro LED spot MV

Order Code	Full Product Name	Line Frequency	Power	Wattage
			Consumption	Equivalent
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	50 to 60 Hz	4 W	50 W
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	50 to 60 Hz	4 W	50 W
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	50 to 60 Hz	4.9 W	65 W
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	50 to 60 Hz	4.9 W	65 W
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	50 to 60 Hz	2.7 W	25 W
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	50 to 60 Hz	2.7 W	25 W
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	50 to 60 Hz	3.5 W	35 W

Order Code	Full Product Name	Line Frequency	Power	Wattage
			Consumption	Equivalent
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	50 to 60 Hz	3.5 W	35 W
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	50 to 60 Hz	4.6 W	50 W
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	50 to 60 Hz	4.6 W	50 W
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	50 to 60 Hz	4.6 W	50 W
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	-	4.8 W	50 W
81333101	Corepro LEDspot 670lm GU10 830 60D	50 to 60 Hz	6.7 W	90 W
81335501	Corepro LEDspot 730lm GU10 840 60D	50 to 60 Hz	6.7 W	100 W

## Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	55 °C
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	65 °C
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	65 °C
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	70 °C
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	72 °C
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	72 °C
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	50 °C
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	65 °C
30875600	Corepro LEDspot 550lm GU10 830 120D	85 °C
30865700	Corepro LEDspot 550lm GU10 840 120D	85 °C
30867100	Corepro LEDspot 550lm GU10 865 120D	85 °C
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	70 °C
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	70 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	85 °C
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	85 °C
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	50 °C
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	50 °C
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	65 °C
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	65 °C
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	72 °C
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	72 °C
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	72 °C
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	60 °C
81333101	Corepro LEDspot 670lm GU10 830 60D	75 °C
81335501	Corepro LEDspot 730lm GU10 840 60D	75 °C

## Controls and Dimming

Order Code	Full Product Name	Dimmable
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	Only with specific dimmers
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	Only with specific dimmers
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	Only with specific dimmers
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	Only with specific dimmers
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	No
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	No
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	No
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	No

Order Code	Full Product Name	Dimmable
30875600	Corepro LEDspot 550lm GU10 830 120D	No
30865700	Corepro LEDspot 550lm GU10 840 120D	No
30867100	Corepro LEDspot 550lm GU10 865 120D	No
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	Only with specific dimmers
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	Only with specific dimmers
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	No
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	No
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	No

## CorePro LED spot MV

Order Code	Full Product Name	Dimmable
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	No
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	No
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	No
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	No
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	No

Order Code	Full Product Name	Dimmable
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	No
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Only with specific dimmers
81333101	Corepro LEDspot 670lm GU10 830 60D	No
81335501	Corepro LEDspot 730lm GU10 840 60D	No

### Mechanical and Housing


Order Code	Full Product Name	Bulb Finish
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	Clear
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	Clear
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	Clear
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	Clear
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	Clear
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	Clear
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	Clear
30875600	Corepro LEDspot 550lm GU10 830 120D	-
30865700	Corepro LEDspot 550lm GU10 840 120D	-
30867100	Corepro LEDspot 550lm GU10 865 120D	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	Clear
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	Clear

Order Code	Full Product Name	Bulb Finish
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	Clear
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	Clear
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	Clear
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	Clear
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	Clear
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	Clear
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	Clear
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	Clear
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	-
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	Clear
81333101	Corepro LEDspot 670lm GU10 830 60D	-
81335501	Corepro LEDspot 730lm GU10 840 60D	-

### Approval and Application






Order Code	Full Product Name	Energy Consumption kWh/1000 h
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	3 kWh
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	3 kWh
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	3 kWh
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	4 kWh
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	5 kWh
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	5 kWh
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	3 kWh
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	4 kWh
30875600	Corepro LEDspot 550lm GU10 830 120D	5 kWh
30865700	Corepro LEDspot 550lm GU10 840 120D	5 kWh
30867100	Corepro LEDspot 550lm GU10 865 120D	5 kWh
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	4 kWh
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	4 kWh
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	5 kWh
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	5 kWh
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	3 kWh
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	3 kWh
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	4 kWh
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	4 kWh
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	5 kWh
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	5 kWh
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	5 kWh
36969600	CorePro LEDspot 4.8-50W GU10 3CCT 36DDIM	5 kWh
81333101	Corepro LEDspot 670lm GU10 830 60D	7 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
81335501	Corepro LEDspot 730lm GU10 840 60D	7 kWh













90°


60°




# CorePro LED spot MV




# CorePro LED spot MV




## Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W  
GU10 830 36D ND




Accent Diagram - Corepro LEDspot 2.7-25W  
GU10 827 36D




Accent Diagram - Corepro LEDspot 3.5-35W  
GU10 827 36D




Accent Diagram - Corepro LEDspot 4.6-50W  
GU10 827 36D




Accent Diagram - Corepro LEDspot 2.7-25W  
GU10 840 36D




Accent Diagram - Corepro LEDspot 3.5-35W  
GU10 830 36D



Accent Diagram - Corepro LEDspot 4.6-50W  
GU10 840 36D




Accent Diagram - CorePro LEDspot 4-50W  
GU10 827 36D DIM




Accent Diagram - CorePro LEDspot 4-50W  
GU10 840 36D DIM

# CorePro LED spot MV


## Accent Diagrams




Accent Diagram - CorePro LEDspot 4-50W  
GU10 830 36D DIM




Accent Diagram - CorePro LEDspot 4.8-50W  
GU10 3CCT 36DDIM




Accent Diagram - CorePro LEDspot 3-35W GU10  
830 36D DIM




Accent Diagram - CorePro LEDspot 3-35W GU10  
840 36D DIM




Accent Diagram - CorePro LEDspot 730lm GU10  
840 60D



Accent Diagram - CorePro LEDspot 670lm GU10  
830 60D




Accent Diagram - CorePro LEDspot 3-35W GU10  
827 36D DIM




Accent Diagram - CorePro LEDspot 4.9-65W  
GU10 840 36D ND


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 4.9-65W GU10 840 36D ND




Beam diagram - CorePro LEDspot 2.7-25W GU10 827 36D




Beam diagram - CorePro LEDspot 3.5-35W GU10 827 36D




Beam diagram - CorePro LEDspot 4.6-50W GU10 827 36D




Beam diagram - CorePro LEDspot 2.7-25W GU10 840 36D



Beam diagram - CorePro LEDspot 3.5-35W GU10 830 36D




Beam diagram - CorePro LEDspot 4.6-50W GU10 840 36D




Beam diagram - CorePro LEDspot 4-50W GU10 830 36D DIM


Beam Diagrams




Beam diagram - CorePro LEDspot 4-50W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 4.8-50W GU10 30CT 36DDIM




Beam diagram - Corepro LEDspot 730lm GU10 840 60D




Beam diagram - CorePro LEDspot 3-35W GU10 830 36D DIM




Beam diagram - CorePro LEDspot 4-50W GU10 827 36D DIM



Beam diagram - CorePro LEDspot 3-35W GU10 827 36D DIM



Beam diagram - CorePro LEDspot 4.9-65W GU10 830 36D ND



Beam diagram - Corepro LEDspot 670lm GU10 830 60D

## CorePro LED spot MV

