



The affordable LED solution

CorePro LED tube EM/Mains T8

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Benefits

- Minimizes overall lighting costs
- Offers cheapest and easiest upgrade to LED lighting technology

Features

- Only 50% energy consumption compared to fluorescent tubes
- Lasts two times longer than fluorescent tubes
- Retrofit replacement of existing T8 lamps on electromagnetic (EM) ballast installations

Application

- Parking lots and covered car parks
- Warehouses and coldrooms
- Signage

Warnings and Safety

- -


CorePro LED tube EM/Mains T8

Versions



12W G13

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.5W 840 T8 AP I	28 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8 PH	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 600mm 8W 840 T8 AP I	28 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8 AP I	28 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube HO 1200mm 18W 865 T8 PH	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Corepro LEDtube HO 1200mm 18W840T8 AP	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

CorePro LED tube EM/Mains T8

General Information

Cap-Base	G13
Switching Cycle	200,000
Nominal lifetime	50,000 hour(s)

Light Technical

Beam Angle (Nom)	240 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	T8

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	4000 K	840	1,800 lm
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	6500 K	865	1,800 lm
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	4000 K	840	2,100 lm
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	6500 K	865	2,100 lm
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	4000 K	840	800 lm
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	6500 K	865	800 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	-	15.5 W	-
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	-	15.5 W	36 W
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	50 to 60 Hz	18 W	-

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	-	18 W	36 W
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	-	8 W	-
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	-	8 W	-

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	60 °C
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	60 °C
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	55 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	55 °C
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP I	50 °C
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP I	50 °C

Approval and Application

Order Code	Full Product Name	Ambient temperature range
929003519708	CorePro LEDtube 1200mm 15.5W 840 T8 AP I	-20 to +45 °C
929003519888	CorePro LEDtube 1200mm 15.5W 865 T8 PH	-20 to +45 °C

Order Code	Full Product Name	Ambient temperature range
929003520708	Corepro LEDtube HO 1200mm 18W840T8 AP	-20 °C to 45 °C
929003520888	CorePro LEDtube HO 1200mm 18W 865 T8 PH	-20 to +45 °C

CorePro LED tube EM/Mains T8

Order Code	Full Product Name	Ambient temperature range
929003547208	CorePro LEDtube 600mm 8W 840 T8 AP	-20 to +45 °C
	I	
929003547308	CorePro LEDtube 600mm 8W 865 T8 AP	-20 to +45 °C
	I	

