



The most reliable!

MASTER PL-L 4 Pin

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Long life and sustainable light output
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application

- Designed for general lighting in shops, offices, hotels and specific task lighting, as well as outdoors in residential areas and parks

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER PL-L 4 Pin

Versions



LPPR PLL4P 18W

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

