



Widest product range in the world!

MASTER PL-T 4 Pin

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Substantially more light (about 15% more) per light point than with other similar shapes
- Multiple light color choice
- Good color rendering (CRI >80)
- Dimming possible down to 10%

Features

- 4-pin base
- Philips' bridging technology applied
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life
- Fast light run-up

Application

- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units, outdoor lighting
- First choice for short switching cycles, emergency lighting and deep dimming

MASTER PL-T 4 Pin

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR PLT4PN 18W





LPPR PLT4PN 32W



LPPR PLT4PN 57W

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/840/4P 1CT/5X10BOX	41.0 mm	71.7 mm	96.0 mm	111.7 mm


Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 32W/830/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm
MASTER PL-T 32W/840/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm

MASTER PL-T 4 Pin

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 42W/827/4P 1CT/5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm
MASTER PL-T 42W/840/4P 1CT/5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 57W/840/4P 1CT/5X10BOX	41.0 mm	157.7 mm	182.0 mm	197.7 mm

Light Technical

Color rendering index (CRI) 80

Controls and Dimming

Dimmable Yes

Approval and Application

Mercury (Hg) Content (Max) 1.4 mg

Mercury (Hg) Content (Nom) 1.4 mg

General Information

Order Code	Full Product Name	Cap-Base	Order Code	Full Product Name	Cap-Base
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	GX24q-2	927914882771	MASTER PL-T 42W/827/4P 1CT/5X10BOX	GX24q-4
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	GX24q-3	927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	GX24q-4
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	GX24q-3	927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	GX24q-5

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)		Temperature (Nom)	(Rated) (Min)	
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	0.38	0.38	Cool White (CW)	4000 K	67 lm/W	1,150 lm
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	0.44	0.403	Warm White (WW)	3000 K	75 lm/W	2,350 lm

MASTER PL-T 4 Pin

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)		Temperature (Nom)	(Rated) (Min)	
927914784071	MASTER PL-T 32W/840/4P 1CT/ 5X10BOX	0.38	0.38	Cool White (CW)	4000 K	75 lm/W	2,350 lm
927914882771	MASTER PL-T 42W/827/4P 1CT/ 5X10BOX	0.463	0.42	Incandescent White	2700 K	74 lm/W	3,100 lm
927914884071	MASTER PL-T 42W/840/4P 1CT/ 5X10BOX	0.38	0.38	Cool White (CW)	4000 K	74 lm/W	3,100 lm
927914984071	MASTER PL-T 57W/840/4P 1CT/ 5X10BOX	0.38	0.38	Cool White (CW)	4000 K	75 lm/W	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927914484071	MASTER PL-T 18W/840/4P 1CT/ 5X10BOX	0.210 A	18.0 W
927914783071	MASTER PL-T 32W/830/4P 1CT/ 5X10BOX	0.320 A	32.0 W
927914784071	MASTER PL-T 32W/840/4P 1CT/ 5X10BOX	0.320 A	32.0 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927914882771	MASTER PL-T 42W/827/4P 1CT/ 5X10BOX	0.320 A	42.0 W
927914884071	MASTER PL-T 42W/840/4P 1CT/ 5X10BOX	0.320 A	42.0 W
927914984071	MASTER PL-T 57W/840/4P 1CT/ 5X10BOX	0.325 A	54.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	18 kWh
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	32 kWh
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	32 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927914882771	MASTER PL-T 42W/827/4P 1CT/5X10BOX	42 kWh
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	42 kWh
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	54 kWh

