



AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

Benefits

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

Features


- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

Application

- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only





AspiraVision Compact for CDM

Versions



GPPR IAVC 0002

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-AV C 35-70 /I CDM 220-240V 50/60Hz	4.8 mm	34.7 mm	189.2 mm	170.7 mm	83.5 mm

Product	D1	C1	A1	A2	B1	B2
HID-AV C 35-70 /S CDM 220-240V 50/60Hz	4.5 mm	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.5 mm



AspiraVision Compact for CDM

Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	58

Mechanical and Housing

Order Code	Full Product Name	Housing	Order Code	Full Product Name	Housing
913700683866	HID-AV C 35-70 /S CDM 220-240V 50/60Hz	/S	913700684066	HID-AV C 35-70 /I CDM 220-240V 50/60Hz	/I

