



Perfect sparkle, unrivalled efficiency

MASTERColour CDM-TC Elite

Compact, single-ended, very high-efficiency, long-life ceramic metal-halide discharge lamp producing crisp white sparkling light with high color rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Stable color and lumen output over life keeps your store attractive season after season
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life

Features

- Crisp white sparkling light
- Excellent color rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- Stable color performance over lifetime
- UV-blocking glass

Application

- Accent and display lighting in retail
- General and decorative indoor lighting
- Outdoor area lighting

MASTERColour CDM-TC Elite

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions




LPPR CDM-TC 0001



LPPR CDMTC-E 0003


Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	15 mm	4.8 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	15 mm	4.8 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 35W/942 G8.5 1CT	15 mm	5.2 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 35W/942 G8.5 1CT	15 mm	5.2 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	15 mm	6 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 50W/942 G8.5 1CT	15 mm	7.1 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	15 mm	7.15 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	15 mm	7.15 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/942 G8.5 1CT	15 mm	7.75 mm	51 mm	53 mm	52 mm	85 mm
MASTERC CDM-TC Elite 70W/942 G8.5 1CT	15 mm	7.75 mm	51 mm	53 mm	52 mm	85 mm

MASTERColour CDM-TC Elite

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	15 mm	0.55 inch	4 mm	51 mm	53 mm	52 mm	85 mm

General Information	
Cap-Base	G8.5
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T14

Light Technical

Order Code	Full Product Name	Chromaticity		Correlated Color		Color rendering index (CRI)	(rated) (Nom)	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Designation (Nom)	Temperature				
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	85	87 lm/W	1,750 lm	
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	0.435	0.396	Warm White (WW)	3000 K	90	102 lm/W	-	
928189105131	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	90	102 lm/W	4,000 lm	
928193805129	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	0.371	0.366	Cool White (CW)	4200 K	90	97 lm/W	-	
928193805131	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	0.371	0.366	Cool White (CW)	4200 K	90	97 lm/W	3,800 lm	
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	0.435	0.396	Warm White (WW)	3000 K	90	107 lm/W	-	
928189505131	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	90	107 lm/W	7,800 lm	
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	0.365	0.363	Cool White (CW)	4200 K	92	102 lm/W	-	
928193905131	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	0.371	0.366	Cool White (CW)	4200 K	92	102 lm/W	7,450 lm	
928080115131	MASTERC CDM-TC Elite 50W/942 G8.5 1CT	0.371	0.366	Cool White (CW)	4200 K	90	101 lm/W	5,050 lm	
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	91	108 lm/W	5,400 lm	

MASTERColour CDM-TC Elite

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	95 V	20.1 W
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	85 V	39.1 W
928189105131	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	85 V	39.1 W
928193805129	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	91 V	39.1 W
928193805131	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	91 V	39.1 W
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	85 V	73.2 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928189505131	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	85 V	73.2 W
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	88 V	73.2 W
928193905131	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	88 V	73.2 W
928080115131	MASTERC CDM-TC Elite 50W/942 G8.5 1CT	93 V	50.2 W
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	90 V	50.2 W

Mechanical and Housing


Order Code	Full Product Name	Bulb Material
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	UV-Block Quartz
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	-
928189105131	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	-
928193805129	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	-
928193805131	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	-
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	-

Order Code	Full Product Name	Bulb Material
928189505131	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	-
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	-
928193905131	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	-
928080115131	MASTERC CDM-TC Elite 50W/942 G8.5 1CT	-
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	-


Approval and Application

Order Code	Full Product Name	Mercury		Mercury	
		Energy		(Hg)	(Hg)
		Consumption	Content	Content	
928183405125	MASTERC CDM-TC Elite 20W/830 G8.5 1CT/12	21 kWh	3.5 mg	3.5 mg	
928189105129	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	43 kWh	-	4.7 mg	
928189105131	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12	40 kWh	4.7 mg	4.7 mg	
928193805129	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	43 kWh	-	4.9 mg	
928193805131	MASTERC CDM-TC Elite 35W/942 G8.5 1CT	40 kWh	4.9 mg	4.9 mg	
928189505129	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	80 kWh	-	6.6 mg	
928189505131	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	74 kWh	6.6 mg	6.6 mg	
928193905129	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	80 kWh	-	6.6 mg	
928193905131	MASTERC CDM-TC Elite 70W/942 G8.5 1CT	74 kWh	6.6 mg	6.6 mg	
928080115131	MASTERC CDM-TC Elite 50W/942 G8.5 1CT	51 kWh	5.7 mg	5.7 mg	

Order Code	Full Product Name	Mercury		Mercury	
		Energy		(Hg)	(Hg)
		Consumption	Content	Content	
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	51 kWh	6.6 mg	6.6 mg	



MASTERColour CDM-TC Elite



MASTERColour CDM-TC Elite



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2025, December 13 - data subject to change