



Beautiful sparkle, trendy design

MASTERColour CDM-R111

The MASTERColour CDM-R111 combines the trendy look of the 111 mm aluminium reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

Οφέλη

- Low operating costs
- Easy installation
- Relatively low heat output
- Less glare, comfort for shoppers and staff
- Reduced fading risks

Χαρακτηριστικά

- High lamp efficacy
- Long lamp lifetime compared to incandescent and halogen lamps
- The ceramic discharge tube is optimally and stable positioned in the reflector
- Twist & Lock system
- UV-Block burner capsule
- Anti-glare cap design

Εφαρμογή

- Accent and decorative lighting: display lighting with sparkling, theatrical effects, even in surroundings with very high background ambient light levels like shop windows
- General lighting: in downlighters, a warm and comfortable atmosphere can be created

Προειδοποίηση & ασφάλεια

- Το σύστημα ελέγχου πρέπει να διαθέτει προστασία τέλους ζωής (IEC61167, IEC 62035)
- Να χρησιμοποιείται μόνο με ηλεκτρονικό σύστημα ελέγχου. Οι λαμπτήρες 35W χρώματος 830 μπορούν να χρησιμοποιούν και ηλεκτρομαγνητικά όργανα λειτουργίας.


MASTERCcolour CDM-R111

Versions




LPPR CDM-R111 24D 40D

Σχεδιάγραμμα διαστάσεων




Product	D (max)	C (max)
MASTERC CDM-R111 35W/942 GX8.5 24D 1CT	111 mm	95 mm




MASTERColour CDM-R111

Accent Diagrams



Accent Diagram - MASTERC CDM-R111
35W/942 GX8.5 24D 1CT

Beam Diagrams



Beam diagram - MASTERC CDM-R111 35W/942
GX8.5 24D 1CT

