



# Beautiful sparkle, trendy design

## MASTERColour CDM-R111

The MASTERColour CDM-R111 combines the trendy look of 111 mm aluminum reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

### Benefits

- Low operating costs
- Easy installation
- Relatively low heat output
- Less glare, comfort for shoppers and staff
- Reduced risk of fading

### Features

- High lamp efficacy
- Long lifetime compared to incandescent and halogen lamps
- The ceramic discharge tube is optimally and stably positioned in the reflector
- Twist & Lock system
- UV-Block burner capsule
- Anti-glare cap design

### Application

- Accent and decorative lighting: display lighting with sparkling, theatrical effects, even in surroundings with very high background ambient light levels like shop windows
- General lighting: in downlighters, a warm and comfortable atmosphere can be created

# MASTERCcolour CDM-R111

## Warnings and Safety


- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions




LPPR CDM-R111 24D 40D

## Dimensional drawing




| Product                                | D (max) | C (max) |
|--|---------|---------|
| MASTERC CDM-R111 35W/942 GX8.5 24D 1CT | 111 mm  | 95 mm   |




# MASTERCoulour CDM-R111

## Accent Diagrams



Accent Diagram - MASTERC CDM-R111  
35W/942 GX8.5 24D 1CT

## Beam Diagrams



Beam diagram - MASTERC CDM-R111 35W/942  
GX8.5 24D 1CT

