



# Product Description

## MASTERColour CDM-R

Range of compact, high-efficiency, discharge reflector lamps with a stable colour over lifetime and a crisp, sparkling light

### Benefits

- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Stable colour impression over lifetime
- Unique design increases flexibility in application and allows powerful accents from small, unobtrusive luminaires
- Simplified luminaire design because CDM-R lamps can be used in open luminaires
- Relatively low heat output enhances comfort for shoppers and staff
- Integrated UV-Block shield reduces fading risks

### Features

- Warm or cool white colour impression with good colour rendering
- High beam intensities are achieved very easy and efficiently from these compact reflector lamps

### Application

- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

### Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Colour 830 lamps may also use electromagnetic gear.


# MASTERColour CDM-R

## Versions




LPPR CDM-R 0001


## Dimensional drawing



| Product                                  | D (max) | D     | C (max) | C      |
|------------------------------------------|---------|-------|---------|--------|
| MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT | 97 mm   | 95 mm | 123 mm  | 120 mm |




Accent Diagrams



Accent Diagram - MASTER CDM-R 35W/830  
 E27 PAR30L 30D 1CT

Beam Diagrams



Beam diagram - MASTER CDM-R 35W/830  
 E27 PAR30L 30D 1CT

